

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428158

Luminaire Tested: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428158
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2270.0 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75				75
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15233	15233	15233	15233
5°	15214	15494	15214	15494
10°	15375	16004	15375	16004
15°	15370	15578	15370	15578
20°	15122	15864	15122	15864
25°	15078	16518	15078	16518
30°	15062	16676	15062	16676
35°	14919	15526	14919	15526
40°	14574	13664	14574	13664
45°	13791	10805	13791	10805
50°	12539	8382	12539	8382
55°	11020	6525	11020	6525
60°	9536	5373	9536	5373
65°	8229	4703	8229	4703
70°	7402	4178	7402	4178
75°	6781	3843	6781	3843
80°	5904	3756	5904	3756
85°	4279	1778	4279	1778

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 14807 cd/sqm



TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	4.0
10°-20°	263.8	11.6
20°-30°	407.8	18.0
30°-40°	490.4	21.6
40°-50°	440.3	19.4
50°-60°	295.1	13.0
60°-70°	171.6	7.6
70°-80°	88.2	3.9
80°-90°	21.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.7	33.6
0°-40°	1253.0	55.2
0°-60°	1988.4	87.6
0°-90°	2270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2270.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	944	944	944	944	944	
5°	939	956	939	956	939	90
15°	920	932	920	932	920	258
25°	846	927	846	927	846	390
35°	757	788	757	788	757	472
45°	604	473	604	473	604	462
55°	392	232	392	232	392	352
65°	215	123	215	123	215	218
75°	109	62	109	62	109	115
85°	23	10	23	10	23	29
90°	0	0	0	0	0	



TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5
2.5°	939.7	944.8	949.9	947.6	942.8	940.6	941.0	941.5	942.5	943.5	942.5
5°	938.7	946.0	953.3	951.5	946.8	944.9	945.8	947.5	951.8	956.0	951.8
7.5°	938.5	948.9	959.2	960.0	957.6	957.7	960.1	963.4	969.1	974.7	969.1
10°	937.8	950.2	962.6	964.4	962.7	962.0	962.4	964.3	970.2	976.2	970.2
12.5°	933.1	947.6	962.0	960.5	953.7	950.0	949.4	949.7	953.0	956.2	953.0
15°	919.5	936.6	953.7	946.7	931.8	924.9	926.2	927.7	929.9	932.0	929.9
17.5°	895.4	913.3	931.2	924.9	910.7	905.8	910.4	915.0	919.1	923.3	919.1
20°	880.1	897.6	915.1	910.8	899.3	896.5	902.5	908.8	916.1	923.3	916.1
22.5°	866.2	883.7	901.3	898.5	889.0	888.5	896.9	905.6	915.6	925.6	915.6
25°	846.4	861.8	877.2	877.5	872.8	877.5	891.6	905.0	916.1	927.2	916.1
27.5°	825.6	834.7	843.7	849.7	854.7	866.7	885.8	902.0	909.8	917.6	909.8
30°	807.9	813.9	819.9	831.0	843.8	858.6	875.2	888.5	891.5	894.5	891.5
32.5°	788.7	792.3	795.9	811.5	831.2	845.4	854.2	859.9	856.0	852.2	856.0
35°	756.9	759.9	762.9	782.9	808.6	818.0	811.1	804.0	795.8	787.7	795.8
37.5°	719.2	725.4	731.5	747.8	767.5	767.3	747.3	730.0	720.7	711.4	720.7
40°	691.5	701.8	712.1	723.0	734.1	724.7	694.7	669.6	658.9	648.3	658.9
42.5°	657.7	674.1	690.5	692.9	690.7	670.5	632.4	600.6	587.5	574.4	587.5
45°	604.0	626.2	648.5	635.8	611.4	578.5	537.0	502.3	487.7	473.2	487.7
47.5°	540.7	563.6	586.4	562.4	522.8	484.5	447.5	416.3	402.7	389.1	402.7
50°	499.2	517.6	535.9	508.8	466.5	428.0	393.4	363.7	348.7	333.7	348.7
52.5°	456.9	470.1	483.4	456.5	416.2	378.8	344.1	314.8	301.2	287.6	301.2
55°	391.5	398.3	405.1	380.2	344.8	310.6	277.6	250.6	241.2	231.8	241.2
57.5°	331.4	335.8	340.2	316.6	283.6	253.2	225.3	202.6	195.6	188.7	195.6
60°	295.3	298.3	301.3	277.3	244.4	217.0	195.2	177.5	171.9	166.4	171.9
62.5°	262.2	264.5	266.8	243.7	212.2	187.7	170.4	156.3	152.1	147.9	152.1
65°	215.4	217.6	219.7	200.1	173.1	153.0	139.8	129.1	126.1	123.1	126.1
67.5°	178.3	179.4	180.5	164.3	142.4	126.2	115.7	107.2	104.4	101.6	104.4
70°	156.8	157.2	157.6	143.3	124.1	109.8	100.3	92.8	90.6	88.5	90.6
72.5°	137.5	136.9	136.3	123.6	106.7	94.4	86.8	80.6	79.2	77.7	79.2
75°	108.7	107.4	106.1	95.5	81.9	72.5	67.3	63.3	62.4	61.6	62.4
77.5°	81.2	79.8	78.4	69.6	58.3	51.9	50.1	48.9	48.9	48.9	48.9
80°	63.5	61.8	60.1	53.2	44.7	40.4	40.4	40.4	40.4	40.4	40.4
82.5°	47.3	44.9	42.5	38.3	33.6	31.2	31.2	31.1	30.7	30.4	30.7
85°	23.1	20.9	18.8	18.3	18.3	17.0	14.4	12.2	10.9	9.6	10.9
87.5°	6.2	6.2	6.2	4.9	3.2	2.3	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5
2.5°	941.5	941.0	940.6	942.8	947.6	949.9	944.8	939.7	944.8	949.9	947.6
5°	947.5	945.8	944.9	946.8	951.5	953.3	946.0	938.7	946.0	953.3	951.5
7.5°	963.4	960.1	957.7	957.6	960.0	959.2	948.9	938.5	948.9	959.2	960.0
10°	964.3	962.4	962.0	962.7	964.4	962.6	950.2	937.8	950.2	962.6	964.4
12.5°	949.7	949.4	950.0	953.7	960.5	962.0	947.6	933.1	947.6	962.0	960.5
15°	927.7	926.2	924.9	931.8	946.7	953.7	936.6	919.5	936.6	953.7	946.7
17.5°	915.0	910.4	905.8	910.7	924.9	931.2	913.3	895.4	913.3	931.2	924.9
20°	908.8	902.5	896.5	899.3	910.8	915.1	897.6	880.1	897.6	915.1	910.8
22.5°	905.6	896.9	888.5	889.0	898.5	901.3	883.7	866.2	883.7	901.3	898.5
25°	905.0	891.6	877.5	872.8	877.5	877.2	861.8	846.4	861.8	877.2	877.5
27.5°	902.0	885.8	866.7	854.7	849.7	843.7	834.7	825.6	834.7	843.7	849.7
30°	888.5	875.2	858.6	843.8	831.0	819.9	813.9	807.9	813.9	819.9	831.0
32.5°	859.9	854.2	845.4	831.2	811.5	795.9	792.3	788.7	792.3	795.9	811.5
35°	804.0	811.1	818.0	808.6	782.9	762.9	759.9	756.9	759.9	762.9	782.9
37.5°	730.0	747.3	767.3	767.5	747.8	731.5	725.4	719.2	725.4	731.5	747.8
40°	669.6	694.7	724.7	734.1	723.0	712.1	701.8	691.5	701.8	712.1	723.0
42.5°	600.6	632.4	670.5	690.7	692.9	690.5	674.1	657.7	674.1	690.5	692.9
45°	502.3	537.0	578.5	611.4	635.8	648.5	626.2	604.0	626.2	648.5	635.8
47.5°	416.3	447.5	484.5	522.8	562.4	586.4	563.6	540.7	563.6	586.4	562.4
50°	363.7	393.4	428.0	466.5	508.8	535.9	517.6	499.2	517.6	535.9	508.8
52.5°	314.8	344.1	378.8	416.2	456.5	483.4	470.1	456.9	470.1	483.4	456.5
55°	250.6	277.6	310.6	344.8	380.2	405.1	398.3	391.5	398.3	405.1	380.2
57.5°	202.6	225.3	253.2	283.6	316.6	340.2	335.8	331.4	335.8	340.2	316.6
60°	177.5	195.2	217.0	244.4	277.3	301.3	298.3	295.3	298.3	301.3	277.3
62.5°	156.3	170.4	187.7	212.2	243.7	266.8	264.5	262.2	264.5	266.8	243.7
65°	129.1	139.8	153.0	173.1	200.1	219.7	217.6	215.4	217.6	219.7	200.1
67.5°	107.2	115.7	126.2	142.4	164.3	180.5	179.4	178.3	179.4	180.5	164.3
70°	92.8	100.3	109.8	124.1	143.3	157.6	157.2	156.8	157.2	157.6	143.3
72.5°	80.6	86.8	94.4	106.7	123.6	136.3	136.9	137.5	136.9	136.3	123.6
75°	63.3	67.3	72.5	81.9	95.5	106.1	107.4	108.7	107.4	106.1	95.5
77.5°	48.9	50.1	51.9	58.3	69.6	78.4	79.8	81.2	79.8	78.4	69.6
80°	40.4	40.4	40.4	44.7	53.2	60.1	61.8	63.5	61.8	60.1	53.2
82.5°	31.1	31.2	31.2	33.6	38.3	42.5	44.9	47.3	44.9	42.5	38.3
85°	12.2	14.4	17.0	18.3	18.3	18.8	20.9	23.1	20.9	18.8	18.3
87.5°	2.3	2.3	2.3	3.2	4.9	6.2	6.2	6.2	6.2	6.2	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5	943.5
2.5°	942.8	940.6	941.0	941.5	942.5	943.5	942.5	941.5	941.0	940.6	942.8
5°	946.8	944.9	945.8	947.5	951.8	956.0	951.8	947.5	945.8	944.9	946.8
7.5°	957.6	957.7	960.1	963.4	969.1	974.7	969.1	963.4	960.1	957.7	957.6
10°	962.7	962.0	962.4	964.3	970.2	976.2	970.2	964.3	962.4	962.0	962.7
12.5°	953.7	950.0	949.4	949.7	953.0	956.2	953.0	949.7	949.4	950.0	953.7
15°	931.8	924.9	926.2	927.7	929.9	932.0	929.9	927.7	926.2	924.9	931.8
17.5°	910.7	905.8	910.4	915.0	919.1	923.3	919.1	915.0	910.4	905.8	910.7
20°	899.3	896.5	902.5	908.8	916.1	923.3	916.1	908.8	902.5	896.5	899.3
22.5°	889.0	888.5	896.9	905.6	915.6	925.6	915.6	905.6	896.9	888.5	889.0
25°	872.8	877.5	891.6	905.0	916.1	927.2	916.1	905.0	891.6	877.5	872.8
27.5°	854.7	866.7	885.8	902.0	909.8	917.6	909.8	902.0	885.8	866.7	854.7
30°	843.8	858.6	875.2	888.5	891.5	894.5	891.5	888.5	875.2	858.6	843.8
32.5°	831.2	845.4	854.2	859.9	856.0	852.2	856.0	859.9	854.2	845.4	831.2
35°	808.6	818.0	811.1	804.0	795.8	787.7	795.8	804.0	811.1	818.0	808.6
37.5°	767.5	767.3	747.3	730.0	720.7	711.4	720.7	730.0	747.3	767.3	767.5
40°	734.1	724.7	694.7	669.6	658.9	648.3	658.9	669.6	694.7	724.7	734.1
42.5°	690.7	670.5	632.4	600.6	587.5	574.4	587.5	600.6	632.4	670.5	690.7
45°	611.4	578.5	537.0	502.3	487.7	473.2	487.7	502.3	537.0	578.5	611.4
47.5°	522.8	484.5	447.5	416.3	402.7	389.1	402.7	416.3	447.5	484.5	522.8
50°	466.5	428.0	393.4	363.7	348.7	333.7	348.7	363.7	393.4	428.0	466.5
52.5°	416.2	378.8	344.1	314.8	301.2	287.6	301.2	314.8	344.1	378.8	416.2
55°	344.8	310.6	277.6	250.6	241.2	231.8	241.2	250.6	277.6	310.6	344.8
57.5°	283.6	253.2	225.3	202.6	195.6	188.7	195.6	202.6	225.3	253.2	283.6
60°	244.4	217.0	195.2	177.5	171.9	166.4	171.9	177.5	195.2	217.0	244.4
62.5°	212.2	187.7	170.4	156.3	152.1	147.9	152.1	156.3	170.4	187.7	212.2
65°	173.1	153.0	139.8	129.1	126.1	123.1	126.1	129.1	139.8	153.0	173.1
67.5°	142.4	126.2	115.7	107.2	104.4	101.6	104.4	107.2	115.7	126.2	142.4
70°	124.1	109.8	100.3	92.8	90.6	88.5	90.6	92.8	100.3	109.8	124.1
72.5°	106.7	94.4	86.8	80.6	79.2	77.7	79.2	80.6	86.8	94.4	106.7
75°	81.9	72.5	67.3	63.3	62.4	61.6	62.4	63.3	67.3	72.5	81.9
77.5°	58.3	51.9	50.1	48.9	48.9	48.9	48.9	48.9	50.1	51.9	58.3
80°	44.7	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	44.7
82.5°	33.6	31.2	31.2	31.1	30.7	30.4	30.7	31.1	31.2	31.2	33.6
85°	18.3	17.0	14.4	12.2	10.9	9.6	10.9	12.2	14.4	17.0	18.3
87.5°	3.2	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428158

CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	943.5	943.5	943.5	943.5
2.5°	947.6	949.9	944.8	939.7
5°	951.5	953.3	946.0	938.7
7.5°	960.0	959.2	948.9	938.5
10°	964.4	962.6	950.2	937.8
12.5°	960.5	962.0	947.6	933.1
15°	946.7	953.7	936.6	919.5
17.5°	924.9	931.2	913.3	895.4
20°	910.8	915.1	897.6	880.1
22.5°	898.5	901.3	883.7	866.2
25°	877.5	877.2	861.8	846.4
27.5°	849.7	843.7	834.7	825.6
30°	831.0	819.9	813.9	807.9
32.5°	811.5	795.9	792.3	788.7
35°	782.9	762.9	759.9	756.9
37.5°	747.8	731.5	725.4	719.2
40°	723.0	712.1	701.8	691.5
42.5°	692.9	690.5	674.1	657.7
45°	635.8	648.5	626.2	604.0
47.5°	562.4	586.4	563.6	540.7
50°	508.8	535.9	517.6	499.2
52.5°	456.5	483.4	470.1	456.9
55°	380.2	405.1	398.3	391.5
57.5°	316.6	340.2	335.8	331.4
60°	277.3	301.3	298.3	295.3
62.5°	243.7	266.8	264.5	262.2
65°	200.1	219.7	217.6	215.4
67.5°	164.3	180.5	179.4	178.3
70°	143.3	157.6	157.2	156.8
72.5°	123.6	136.3	136.9	137.5
75°	95.5	106.1	107.4	108.7
77.5°	69.6	78.4	79.8	81.2
80°	53.2	60.1	61.8	63.5
82.5°	38.3	42.5	44.9	47.3
85°	18.3	18.8	20.9	23.1
87.5°	4.9	6.2	6.2	6.2
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428158
 CATALOG NUMBER: SQ2W-PR1-0U-050D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.06	21.56	20.43	21.87	22.18	16.43	17.93	16.80	18.24	18.55
	3H	21.31	22.65	21.69	22.98	23.34	17.64	18.98	18.02	19.30	19.67
	4H	21.83	23.08	22.23	23.43	23.81	18.13	19.38	18.53	19.73	20.11
	6H	22.16	23.31	22.57	23.68	24.07	18.50	19.66	18.92	20.03	20.42
	8H	22.28	23.37	22.70	23.76	24.17	18.66	19.76	19.08	20.15	20.55
	12H	22.33	23.39	22.76	23.77	24.20	18.71	19.76	19.14	20.14	20.57
4H	2H	20.24	21.49	20.64	21.84	22.22	17.22	18.47	17.62	18.82	19.20
	3H	21.76	22.79	22.17	23.19	23.59	18.63	19.66	19.04	20.06	20.46
	4H	22.41	23.34	22.84	23.75	24.19	19.20	20.12	19.63	20.54	20.98
	6H	22.87	23.68	23.33	24.12	24.58	19.66	20.47	20.12	20.91	21.37
	8H	23.04	23.79	23.50	24.24	24.71	19.86	20.61	20.32	21.05	21.52
	12H	23.13	23.80	23.62	24.28	24.76	19.93	20.60	20.41	21.08	21.55
8H	4H	22.48	23.23	22.94	23.67	24.14	19.57	20.32	20.03	20.76	21.23
	6H	23.03	23.65	23.52	24.14	24.62	20.13	20.75	20.62	21.24	21.72
	8H	23.26	23.82	23.78	24.33	24.82	20.39	20.95	20.90	21.46	21.95
	12H	23.41	23.90	23.92	24.39	24.96	20.51	21.00	21.02	21.50	22.06
12H	4H	22.46	23.13	22.94	23.61	24.08	19.61	20.28	20.10	20.76	21.24
	6H	23.02	23.58	23.53	24.09	24.58	20.20	20.76	20.71	21.27	21.76
	8H	23.29	23.79	23.80	24.28	24.85	20.51	21.01	21.02	21.50	22.07