

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435844

Luminaire Tested: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435844
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7403.5 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	32	31	26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	61	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17437	17437	17437	17437
5°	17233	18047	17233	14384
10°	17157	18255	17157	13040
15°	16864	18403	16864	14413
20°	16398	18269	16398	15032
25°	15586	18121	15586	15214
30°	14359	17717	14359	15375
35°	12707	17327	12707	15100
40°	10941	16853	10941	15264
45°	10800	16248	10800	15294
50°	10303	15458	10303	15352
55°	10252	14257	10252	15200
60°	9193	12707	9193	15138
65°	7836	11194	7836	14712
70°	6326	9484	6326	13633
75°	5483	7835	5483	12532
80°	4668	5839	4668	10116
85°	3094	3094	3094	6206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 16760 cd/sqm



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	1.3
10°-20°	271.5	3.7
20°-30°	412.4	5.6
30°-40°	484.1	6.5
40°-50°	491.3	6.6
50°-60°	430.3	5.8
60°-70°	305.2	4.1
70°-80°	157.2	2.1
80°-90°	39.6	0.5
90°-100°	128.5	1.7
100°-110°	374.8	5.1
110°-120°	611.6	8.3
120°-130°	776.1	10.5
130°-140°	830.4	11.2
140°-150°	775.4	10.5
150°-160°	638.1	8.6
160°-170°	427.9	5.8
170°-180°	151.9	2.1
0°-30°	781.1	10.5
0°-40°	1265.2	17.1
0°-60°	2186.8	29.5
0°-90°	2688.8	36.3
90°-120°	1114.9	15.1
90°-150°	3496.8	47.2
90°-180°	4715.0	63.7
0°-180°	7403.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1063	1114	1063	888	1063	101
15°	1009	1101	1009	862	1009	283
25°	875	1017	875	854	875	399
35°	645	879	645	766	645	402
45°	473	712	473	670	473	362
55°	364	506	364	540	364	315
65°	205	293	205	385	205	205
75°	88	126	88	201	88	95
85°	17	17	17	34	17	21
90°	5	36	5	70	5	4
95°	51	38	51	220	51	61
105°	238	382	238	525	238	253
115°	457	633	457	780	457	450
125°	675	1003	675	956	675	604
135°	918	1313	918	1058	918	710
145°	1173	1514	1173	1081	1173	734
155°	1393	1644	1393	1122	1393	640
165°	1540	1714	1540	1292	1540	433
175°	1610	1678	1610	1515	1610	153
180°	1615	1615	1615	1615	1615	



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0
2.5°	1073.3	1080.8	1088.2	1090.1	1090.1	1090.1	1090.1	1090.1	1090.1	1090.1	1090.1
5°	1063.3	1076.3	1089.3	1095.4	1099.1	1101.9	1103.7	1106.1	1109.8	1113.5	1109.8
7.5°	1053.2	1070.7	1088.2	1096.8	1102.3	1106.8	1110.2	1113.1	1115.0	1116.9	1115.0
10°	1046.5	1067.0	1087.5	1096.8	1102.3	1106.1	1107.9	1109.8	1111.7	1113.5	1111.7
12.5°	1036.5	1058.4	1080.4	1091.2	1098.3	1102.7	1104.6	1106.4	1108.3	1110.2	1108.3
15°	1008.9	1038.6	1068.4	1080.0	1085.6	1090.3	1094.0	1097.2	1099.1	1101.0	1099.1
17.5°	974.5	1010.6	1046.7	1061.3	1068.8	1074.2	1077.5	1080.4	1081.9	1083.4	1081.9
20°	954.4	993.5	1032.6	1047.9	1055.4	1060.0	1061.9	1063.3	1063.3	1063.3	1063.3
22.5°	927.6	971.2	1014.7	1031.2	1038.6	1042.5	1042.9	1043.6	1045.0	1046.5	1045.0
25°	874.9	925.1	975.4	996.3	1007.5	1012.1	1010.3	1009.8	1013.5	1017.2	1013.5
27.5°	810.4	873.7	936.9	958.3	965.8	970.4	972.3	973.7	973.7	973.7	973.7
30°	770.2	840.9	911.6	934.9	942.3	947.0	948.9	950.3	950.3	950.3	950.3
32.5°	720.0	804.1	888.2	913.7	919.6	922.8	923.2	923.5	923.5	923.5	923.5
35°	644.7	747.0	849.3	877.7	881.4	883.3	883.3	882.8	880.9	879.1	880.9
37.5°	569.3	685.4	801.5	834.7	840.3	841.8	839.2	836.8	834.9	833.0	834.9
40°	519.1	645.6	772.1	807.9	813.5	813.5	807.9	803.3	801.4	799.6	801.4
42.5°	492.3	617.3	742.3	777.8	783.4	782.6	775.6	769.8	767.9	766.1	767.9
45°	473.0	584.7	696.3	728.4	734.0	733.0	725.6	719.1	715.4	711.6	715.4
47.5°	443.7	542.0	640.2	671.7	681.0	680.1	668.9	659.6	655.9	652.2	655.9
50°	410.2	507.0	603.7	634.9	644.2	643.3	632.1	622.8	619.1	615.4	619.1
52.5°	386.8	477.6	568.4	596.9	604.8	602.3	589.7	579.3	575.5	571.8	575.5
55°	364.2	440.5	516.8	540.0	545.6	541.9	528.8	517.7	512.1	506.5	512.1
57.5°	311.4	384.0	456.6	479.2	485.1	480.7	465.8	453.0	446.7	440.4	446.7
60°	284.7	349.8	414.9	436.8	444.2	440.5	425.6	412.1	402.8	393.5	402.8
62.5°	254.5	312.2	369.9	392.1	402.5	400.3	385.4	371.9	362.6	353.3	362.6
65°	205.1	255.4	305.6	327.9	340.9	340.0	325.1	311.6	302.3	293.0	302.3
67.5°	160.7	203.9	247.1	269.0	283.9	283.2	266.8	252.7	245.2	237.8	245.2
70°	134.0	171.2	208.4	228.8	243.7	243.7	228.8	215.8	208.4	200.9	208.4
72.5°	117.2	145.5	173.8	193.1	209.5	209.5	193.1	179.4	173.4	167.4	173.4
75°	87.9	104.7	121.4	139.5	158.1	160.0	145.1	133.0	129.3	125.6	129.3
77.5°	63.6	71.4	79.3	93.5	109.9	111.7	99.1	89.2	87.7	86.2	87.7
80°	50.2	52.1	54.0	65.6	80.5	82.3	71.2	62.8	62.8	62.8	62.8
82.5°	33.5	35.3	37.2	45.5	55.9	57.0	48.8	42.3	40.8	39.3	40.8
85°	16.7	16.7	16.7	19.5	23.3	23.3	19.5	16.7	16.7	16.7	16.7
87.5°	4.3	5.6	7.3	9.7	12.2	12.5	11.0	10.2	10.5	10.5	10.5
90°	4.9	11.4	19.6	26.1	31.0	32.6	32.6	34.3	35.9	35.9	35.9
92.5°	17.9	28.4	28.7	28.7	34.9	37.8	40.4	40.8	42.4	42.4	42.4
95°	50.6	55.5	83.2	81.6	55.5	44.0	37.5	37.5	37.5	37.5	37.5
97.5°	96.6	103.7	108.3	145.2	153.3	148.1	120.7	101.5	90.7	85.8	90.7
100°	137.0	140.3	150.1	151.7	192.5	231.6	212.0	187.6	179.4	174.5	179.4
102.5°	177.5	179.4	194.4	201.3	210.7	232.9	300.8	293.3	287.7	286.7	287.7
105°	238.1	239.8	267.5	280.5	287.1	287.1	285.4	318.1	370.2	381.7	370.2
107.5°	303.0	310.5	343.2	378.1	385.6	387.5	379.1	374.2	372.2	373.5	372.2
110°	347.4	358.8	398.0	442.0	453.4	456.7	453.4	448.5	445.3	445.3	445.3



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	390.5	407.1	451.5	502.0	521.3	531.1	523.9	520.3	517.0	519.6	517.0
115°	456.7	481.2	539.9	592.1	631.2	636.1	634.5	634.5	632.8	632.8	632.8
117.5°	518.0	557.2	623.1	683.7	729.1	742.1	748.6	746.7	744.7	748.0	744.7
120°	561.1	606.7	681.8	750.3	794.3	813.9	820.4	817.1	820.4	817.1	820.4
122.5°	606.7	662.9	736.6	807.7	859.6	881.7	889.6	890.2	890.9	888.9	890.9
125°	675.2	743.8	830.2	903.6	957.4	983.5	990.0	991.7	994.9	1003.1	994.9
127.5°	744.4	822.0	917.0	987.8	1042.9	1074.5	1084.6	1088.2	1095.1	1098.7	1095.1
130°	792.7	880.8	977.0	1043.9	1097.7	1131.9	1149.9	1154.8	1162.9	1161.3	1162.9
132.5°	843.6	935.6	1033.1	1102.6	1152.5	1189.3	1204.7	1218.7	1221.6	1223.9	1221.6
135°	918.3	1017.8	1115.6	1184.1	1231.4	1267.3	1286.9	1299.9	1308.1	1313.0	1308.1
137.5°	996.9	1101.9	1195.9	1256.9	1304.5	1335.5	1357.7	1371.4	1379.9	1383.8	1379.9
140°	1050.4	1151.5	1242.8	1306.5	1348.9	1379.9	1399.4	1415.7	1425.5	1425.5	1425.5
142.5°	1101.3	1201.1	1289.8	1353.4	1390.6	1419.0	1439.9	1452.3	1463.4	1463.4	1463.4
145°	1172.7	1272.2	1353.8	1417.4	1448.4	1474.5	1497.3	1507.1	1513.6	1513.6	1513.6
147.5°	1247.4	1335.5	1409.9	1470.9	1497.0	1527.6	1545.6	1553.4	1561.6	1558.0	1561.6
150°	1291.8	1373.3	1445.1	1502.2	1528.3	1557.6	1575.6	1582.1	1590.3	1585.4	1590.3
152.5°	1334.8	1412.5	1477.7	1530.9	1553.1	1582.4	1603.0	1609.5	1615.0	1611.5	1615.0
155°	1392.9	1461.4	1521.8	1570.7	1590.3	1618.0	1637.6	1645.7	1652.2	1644.1	1652.2
157.5°	1444.8	1503.8	1556.3	1601.3	1622.2	1646.0	1664.3	1674.4	1680.9	1677.4	1680.9
160°	1476.1	1529.9	1577.2	1619.6	1639.2	1660.4	1680.0	1691.4	1697.9	1693.0	1697.9
162.5°	1502.2	1550.8	1595.5	1634.0	1650.9	1669.5	1693.0	1703.1	1709.6	1703.5	1709.6
165°	1539.7	1578.8	1618.0	1650.6	1665.3	1680.0	1704.4	1715.8	1720.7	1714.2	1720.7
167.5°	1568.1	1598.1	1629.7	1657.8	1668.5	1682.9	1707.4	1716.8	1723.0	1714.9	1723.0
170°	1583.7	1609.8	1637.6	1660.4	1668.5	1681.6	1706.1	1714.2	1719.1	1711.0	1719.1
172.5°	1596.8	1616.4	1638.9	1659.1	1663.3	1673.8	1696.9	1705.1	1708.7	1701.8	1708.7
175°	1609.8	1621.2	1637.6	1650.6	1649.0	1655.5	1675.1	1681.6	1688.1	1678.3	1688.1
177.5°	1616.0	1621.2	1626.5	1634.3	1629.1	1629.1	1643.4	1647.3	1648.6	1643.4	1648.6
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0
2.5°	1090.1	1090.1	1090.1	1090.1	1090.1	1088.2	1080.8	1073.3	1073.3	1073.3	1067.7
5°	1106.1	1103.7	1101.9	1099.1	1095.4	1089.3	1076.3	1063.3	1057.7	1052.1	1028.4
7.5°	1113.1	1110.2	1106.8	1102.3	1096.8	1088.2	1070.7	1053.2	1028.3	1003.4	950.5
10°	1109.8	1107.9	1106.1	1102.3	1096.8	1087.5	1067.0	1046.5	996.3	946.1	895.8
12.5°	1106.4	1104.6	1102.7	1098.3	1091.2	1080.4	1058.4	1036.5	965.4	894.3	848.9
15°	1097.2	1094.0	1090.3	1085.6	1080.0	1068.4	1038.6	1008.9	928.9	848.9	810.7
17.5°	1080.4	1077.5	1074.2	1068.8	1061.3	1046.7	1010.6	974.5	890.8	807.1	782.5
20°	1063.3	1061.9	1060.0	1055.4	1047.9	1032.6	993.5	954.4	870.7	787.0	775.8
22.5°	1043.6	1042.9	1042.5	1038.6	1031.2	1014.7	971.2	927.6	845.4	763.2	763.6
25°	1009.8	1010.3	1012.1	1007.5	996.3	975.4	925.1	874.9	802.3	729.8	742.3
27.5°	973.7	972.3	970.4	965.8	958.3	936.9	873.7	810.4	753.1	695.8	716.7
30°	950.3	948.9	947.0	942.3	934.9	911.6	840.9	770.2	721.9	673.5	697.7
32.5°	923.5	923.2	922.8	919.6	913.7	888.2	804.1	720.0	685.0	650.1	675.4
35°	882.8	883.3	883.3	881.4	877.7	849.3	747.0	644.7	629.8	614.9	644.7
37.5°	836.8	839.2	841.8	840.3	834.7	801.5	685.4	569.3	574.2	579.0	615.1
40°	803.3	807.9	813.5	813.5	807.9	772.1	645.6	519.1	535.8	552.6	591.6
42.5°	769.8	775.6	782.6	783.4	777.8	742.3	617.3	492.3	510.5	528.8	569.3
45°	719.1	725.6	733.0	734.0	728.4	696.3	584.7	473.0	484.2	495.4	534.4
47.5°	659.6	668.9	680.1	681.0	671.7	640.2	542.0	443.7	451.9	460.1	500.1
50°	622.8	632.1	643.3	644.2	634.9	603.7	507.0	410.2	421.4	432.6	474.4
52.5°	579.3	589.7	602.3	604.8	596.9	568.4	477.6	386.8	393.5	400.2	445.4
55°	517.7	528.8	541.9	545.6	540.0	516.8	440.5	364.2	358.6	353.0	399.1
57.5°	453.0	465.8	480.7	485.1	479.2	456.6	384.0	311.4	306.6	301.8	351.6
60°	412.1	425.6	440.5	444.2	436.8	414.9	349.8	284.7	275.4	266.1	318.1
62.5°	371.9	385.4	400.3	402.5	392.1	369.9	312.2	254.5	248.2	241.9	292.5
65°	311.6	325.1	340.0	340.9	327.9	305.6	255.4	205.1	208.8	212.6	258.1
67.5°	252.7	266.8	283.2	283.9	269.0	247.1	203.9	160.7	173.0	185.3	226.3
70°	215.8	228.8	243.7	243.7	228.8	208.4	171.2	134.0	150.7	167.4	205.1
72.5°	179.4	193.1	209.5	209.5	193.1	173.8	145.5	117.2	134.0	150.7	181.7
75°	133.0	145.1	160.0	158.1	139.5	121.4	104.7	87.9	104.7	121.4	145.1
77.5°	89.2	99.1	111.7	109.9	93.5	79.3	71.4	63.6	77.4	91.2	107.7
80°	62.8	71.2	82.3	80.5	65.6	54.0	52.1	50.2	59.5	68.8	80.9
82.5°	42.3	48.8	57.0	55.9	45.5	37.2	35.3	33.5	41.3	49.1	57.5
85°	16.7	19.5	23.3	23.3	19.5	16.7	16.7	16.7	20.5	24.2	27.9
87.5°	10.2	11.0	12.5	12.2	9.7	7.3	5.6	4.3	7.1	9.9	12.6
90°	34.3	32.6	32.6	31.0	26.1	19.6	11.4	4.9	11.4	17.9	29.4
92.5°	40.8	40.4	37.8	34.9	28.7	28.7	28.4	17.9	31.0	44.0	63.3
95°	37.5	37.5	44.0	55.5	81.6	83.2	55.5	50.6	71.8	101.1	127.2
97.5°	101.5	120.7	148.1	153.3	145.2	108.3	103.7	96.6	131.5	160.5	202.6
100°	187.6	212.0	231.6	192.5	151.7	150.1	140.3	137.0	174.5	202.2	243.0
102.5°	293.3	300.8	232.9	210.7	201.3	194.4	179.4	177.5	215.0	253.1	287.4
105°	318.1	285.4	287.1	287.1	280.5	267.5	239.8	238.1	280.5	324.6	367.0
107.5°	374.2	379.1	387.5	385.6	378.1	343.2	310.5	303.0	341.2	394.1	440.7
110°	448.5	453.4	456.7	453.4	442.0	398.0	358.8	347.4	381.7	437.1	487.7



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	520.3	523.9	531.1	521.3	502.0	451.5	407.1	390.5	424.7	481.5	533.3
115°	634.5	634.5	636.1	631.2	592.1	539.9	481.2	456.7	486.0	538.2	595.3
117.5°	746.7	748.6	742.1	729.1	683.7	623.1	557.2	518.0	541.2	596.3	655.0
120°	817.1	820.4	813.9	794.3	750.3	681.8	606.7	561.1	579.0	632.8	691.6
122.5°	890.2	889.6	881.7	859.6	807.7	736.6	662.9	606.7	614.2	664.2	721.6
125°	991.7	990.0	983.5	957.4	903.6	830.2	743.8	675.2	665.5	707.9	766.6
127.5°	1088.2	1084.6	1074.5	1042.9	987.8	917.0	822.0	744.4	722.5	749.3	803.1
130°	1154.8	1149.9	1131.9	1097.7	1043.9	977.0	880.8	792.7	761.7	778.0	825.3
132.5°	1218.7	1204.7	1189.3	1152.5	1102.6	1033.1	935.6	843.6	800.8	808.0	844.9
135°	1299.9	1286.9	1267.3	1231.4	1184.1	1115.6	1017.8	918.3	859.6	853.0	874.2
137.5°	1371.4	1357.7	1335.5	1304.5	1256.9	1195.9	1101.9	996.9	922.8	901.0	909.1
140°	1415.7	1399.4	1379.9	1348.9	1306.5	1242.8	1151.5	1050.4	967.2	936.2	931.3
142.5°	1452.3	1439.9	1419.0	1390.6	1353.4	1289.8	1201.1	1101.3	1012.9	972.7	961.3
145°	1507.1	1497.3	1474.5	1448.4	1417.4	1353.8	1272.2	1172.7	1084.6	1032.4	1008.0
147.5°	1553.4	1545.6	1527.6	1497.0	1470.9	1409.9	1335.5	1247.4	1157.1	1092.5	1060.8
150°	1582.1	1575.6	1557.6	1528.3	1502.2	1445.1	1373.3	1291.8	1205.3	1136.8	1096.1
152.5°	1609.5	1603.0	1582.4	1553.1	1530.9	1477.7	1412.5	1334.8	1247.1	1178.6	1136.5
155°	1645.7	1637.6	1618.0	1590.3	1570.7	1521.8	1461.4	1392.9	1317.9	1246.1	1198.8
157.5°	1674.4	1664.3	1646.0	1622.2	1601.3	1556.3	1503.8	1444.8	1379.2	1310.7	1262.4
160°	1691.4	1680.0	1660.4	1639.2	1619.6	1577.2	1529.9	1476.1	1415.7	1353.8	1301.6
162.5°	1703.1	1693.0	1669.5	1650.9	1634.0	1595.5	1550.8	1502.2	1448.4	1394.2	1345.9
165°	1715.8	1704.4	1680.0	1665.3	1650.6	1618.0	1578.8	1539.7	1494.0	1450.0	1410.8
167.5°	1716.8	1707.4	1682.9	1668.5	1657.8	1629.7	1598.1	1568.1	1532.5	1497.9	1465.3
170°	1714.2	1706.1	1681.6	1668.5	1660.4	1637.6	1609.8	1583.7	1556.0	1526.6	1500.6
172.5°	1705.1	1696.9	1673.8	1663.3	1659.1	1638.9	1616.4	1596.8	1573.0	1551.4	1530.6
175°	1681.6	1675.1	1655.5	1649.0	1650.6	1637.6	1621.2	1609.8	1595.2	1582.1	1570.7
177.5°	1647.3	1643.4	1629.1	1629.1	1634.3	1626.5	1621.2	1616.0	1609.5	1605.6	1601.7
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0
2.5°	1060.3	1054.3	1049.9	1046.2	1044.7	1043.2	1044.7	1046.2	1049.9	1054.3	1060.3
5°	998.6	967.0	933.5	906.1	896.8	887.5	896.8	906.1	933.5	967.0	998.6
7.5°	888.4	850.3	836.1	824.8	821.8	818.8	821.8	824.8	836.1	850.3	888.4
10°	845.6	814.9	803.7	795.4	795.4	795.4	795.4	795.4	803.7	814.9	845.6
12.5°	812.1	793.3	792.6	793.9	801.3	808.8	801.3	793.9	792.6	793.3	812.1
15°	786.5	789.3	819.1	843.7	853.0	862.3	853.0	843.7	819.1	789.3	786.5
17.5°	777.7	793.7	830.5	860.0	867.5	874.9	867.5	860.0	830.5	793.7	777.7
20°	788.9	809.3	837.2	860.0	867.5	874.9	867.5	860.0	837.2	809.3	788.9
22.5°	791.5	816.4	838.3	856.7	864.1	871.6	864.1	856.7	838.3	816.4	791.5
25°	783.3	813.0	831.6	846.5	850.3	854.0	850.3	846.5	831.6	813.0	783.3
27.5°	763.6	796.3	814.9	829.5	832.1	834.7	832.1	829.5	814.9	796.3	763.6
30°	746.1	779.6	798.2	813.5	819.1	824.7	819.1	813.5	798.2	779.6	746.1
32.5°	720.8	755.0	778.1	795.6	796.8	797.9	796.8	795.6	778.1	755.0	720.8
35°	689.3	724.7	750.7	769.8	767.9	766.1	767.9	769.8	750.7	724.7	689.3
37.5°	661.6	696.2	718.9	736.5	738.7	740.9	738.7	736.5	718.9	696.2	661.6
40°	638.2	673.5	697.7	716.8	720.5	724.2	720.5	716.8	697.7	673.5	638.2
42.5°	617.3	653.4	677.6	696.7	700.4	704.1	700.4	696.7	677.6	653.4	617.3
45°	582.8	620.0	646.1	666.1	667.9	669.8	667.9	666.1	646.1	620.0	582.8
47.5°	550.7	588.1	612.3	630.9	632.8	634.6	632.8	630.9	612.3	588.1	550.7
50°	526.5	564.7	588.8	607.5	609.3	611.2	609.3	607.5	588.8	564.7	526.5
52.5°	503.5	543.1	564.3	580.7	582.5	584.4	582.5	580.7	564.3	543.1	503.5
55°	462.3	504.2	524.7	540.0	540.0	540.0	540.0	540.0	524.7	504.2	462.3
57.5°	419.7	462.7	480.6	494.5	496.8	499.0	496.8	494.5	480.6	462.7	419.7
60°	390.7	434.4	449.3	461.4	465.1	468.8	465.1	461.4	449.3	434.4	390.7
62.5°	362.1	404.3	419.2	430.9	433.1	435.4	433.1	430.9	419.2	404.3	362.1
65°	317.7	354.9	369.8	381.4	383.3	385.1	383.3	381.4	369.8	354.9	317.7
67.5°	276.9	307.4	317.9	326.1	327.5	329.0	327.5	326.1	317.9	307.4	276.9
70°	249.8	275.8	283.3	288.8	288.8	288.8	288.8	288.8	283.3	275.8	249.8
72.5°	217.4	239.0	246.4	252.4	253.9	255.4	253.9	252.4	246.4	239.0	217.4
75°	171.2	187.0	192.6	197.2	199.1	200.9	199.1	197.2	192.6	187.0	171.2
77.5°	125.2	135.6	139.0	142.0	143.8	145.7	143.8	142.0	139.0	135.6	125.2
80°	94.0	101.4	103.3	105.1	107.0	108.8	107.0	105.1	103.3	101.4	94.0
82.5°	66.0	71.3	73.1	74.6	75.0	75.4	75.0	74.6	73.1	71.3	66.0
85°	31.6	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	31.6
87.5°	14.2	16.5	18.8	20.1	21.4	20.7	21.4	20.1	18.8	16.5	14.2
90°	37.5	48.9	60.3	66.9	73.4	70.1	73.4	66.9	60.3	48.9	37.5
92.5°	75.4	94.6	108.6	120.4	125.6	124.9	125.6	120.4	108.6	94.6	75.4
95°	151.7	174.5	197.4	213.7	223.5	220.2	223.5	213.7	197.4	174.5	151.7
97.5°	233.9	264.6	290.0	305.3	315.1	321.6	315.1	305.3	290.0	264.6	233.9
100°	288.7	318.1	347.4	365.4	381.7	388.2	381.7	365.4	347.4	318.1	288.7
102.5°	333.1	371.5	403.5	422.8	436.5	443.0	436.5	422.8	403.5	371.5	333.1
105°	406.1	446.9	481.2	505.6	520.3	525.2	520.3	505.6	481.2	446.9	406.1
107.5°	479.2	521.3	552.9	580.0	597.9	608.4	597.9	580.0	552.9	521.3	479.2
110°	536.6	570.9	605.1	629.6	647.5	654.0	647.5	629.6	605.1	570.9	536.6



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	584.9	623.1	657.3	681.8	702.3	711.5	702.3	681.8	657.3	623.1	584.9
115°	652.4	703.0	734.0	756.8	771.5	779.6	771.5	756.8	734.0	703.0	652.4
117.5°	708.5	761.4	795.3	812.9	819.8	825.6	819.8	812.9	795.3	761.4	708.5
120°	743.8	792.7	831.8	854.7	862.8	866.1	862.8	854.7	831.8	792.7	743.8
122.5°	776.4	822.7	860.5	888.6	902.0	905.2	902.0	888.6	860.5	822.7	776.4
125°	822.0	866.1	905.2	933.0	947.6	955.8	947.6	933.0	905.2	866.1	822.0
127.5°	861.8	909.5	945.3	970.5	984.8	991.3	984.8	970.5	945.3	909.5	861.8
130°	884.0	933.0	968.8	996.6	1009.6	1016.1	1009.6	996.6	968.8	933.0	884.0
132.5°	901.0	952.5	989.7	1014.8	1029.2	1035.7	1029.2	1014.8	989.7	952.5	901.0
135°	921.5	975.4	1014.5	1039.0	1052.0	1058.5	1052.0	1039.0	1014.5	975.4	921.5
137.5°	939.5	988.4	1029.2	1055.0	1066.7	1070.9	1066.7	1055.0	1029.2	988.4	939.5
140°	952.5	994.9	1035.7	1060.2	1073.2	1074.9	1073.2	1060.2	1035.7	994.9	952.5
142.5°	969.5	1002.8	1038.3	1062.8	1075.8	1078.8	1075.8	1062.8	1038.3	1002.8	969.5
145°	999.8	1019.4	1043.9	1066.7	1078.1	1081.4	1078.1	1066.7	1043.9	1019.4	999.8
147.5°	1038.0	1044.2	1056.9	1071.9	1083.0	1085.3	1083.0	1071.9	1056.9	1044.2	1038.0
150°	1066.7	1065.1	1070.0	1079.7	1089.5	1087.9	1089.5	1079.7	1070.0	1065.1	1066.7
152.5°	1099.3	1089.9	1089.5	1094.1	1098.7	1098.3	1098.7	1094.1	1089.5	1089.9	1099.3
155°	1154.8	1136.8	1127.0	1123.8	1123.8	1122.2	1123.8	1123.8	1127.0	1136.8	1154.8
157.5°	1215.8	1190.7	1176.0	1168.1	1165.9	1162.3	1165.9	1168.1	1176.0	1190.7	1215.8
160°	1257.5	1229.8	1215.1	1202.1	1197.2	1192.3	1197.2	1202.1	1215.1	1229.8	1257.5
162.5°	1296.7	1270.2	1254.3	1242.5	1237.6	1230.1	1237.6	1242.5	1254.3	1270.2	1296.7
165°	1360.3	1332.6	1314.6	1304.8	1298.3	1291.8	1298.3	1304.8	1314.6	1332.6	1360.3
167.5°	1423.9	1393.6	1381.8	1370.7	1364.5	1352.8	1364.5	1370.7	1381.8	1393.6	1423.9
170°	1463.0	1435.3	1428.8	1419.0	1407.6	1394.5	1407.6	1419.0	1428.8	1435.3	1463.0
172.5°	1497.0	1478.4	1471.8	1462.1	1458.5	1448.0	1458.5	1462.1	1471.8	1478.4	1497.0
175°	1546.2	1531.5	1531.5	1529.9	1525.0	1515.2	1525.0	1529.9	1531.5	1531.5	1546.2
177.5°	1587.3	1579.5	1584.7	1584.7	1583.4	1574.3	1583.4	1584.7	1584.7	1579.5	1587.3
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1080.0	1080.0	1080.0	1080.0
2.5°	1067.7	1073.3	1073.3	1073.3
5°	1028.4	1052.1	1057.7	1063.3
7.5°	950.5	1003.4	1028.3	1053.2
10°	895.8	946.1	996.3	1046.5
12.5°	848.9	894.3	965.4	1036.5
15°	810.7	848.9	928.9	1008.9
17.5°	782.5	807.1	890.8	974.5
20°	775.8	787.0	870.7	954.4
22.5°	763.6	763.2	845.4	927.6
25°	742.3	729.8	802.3	874.9
27.5°	716.7	695.8	753.1	810.4
30°	697.7	673.5	721.9	770.2
32.5°	675.4	650.1	685.0	720.0
35°	644.7	614.9	629.8	644.7
37.5°	615.1	579.0	574.2	569.3
40°	591.6	552.6	535.8	519.1
42.5°	569.3	528.8	510.5	492.3
45°	534.4	495.4	484.2	473.0
47.5°	500.1	460.1	451.9	443.7
50°	474.4	432.6	421.4	410.2
52.5°	445.4	400.2	393.5	386.8
55°	399.1	353.0	358.6	364.2
57.5°	351.6	301.8	306.6	311.4
60°	318.1	266.1	275.4	284.7
62.5°	292.5	241.9	248.2	254.5
65°	258.1	212.6	208.8	205.1
67.5°	226.3	185.3	173.0	160.7
70°	205.1	167.4	150.7	134.0
72.5°	181.7	150.7	134.0	117.2
75°	145.1	121.4	104.7	87.9
77.5°	107.7	91.2	77.4	63.6
80°	80.9	68.8	59.5	50.2
82.5°	57.5	49.1	41.3	33.5
85°	27.9	24.2	20.5	16.7
87.5°	12.6	9.9	7.1	4.3
90°	29.4	17.9	11.4	4.9
92.5°	63.3	44.0	31.0	17.9
95°	127.2	101.1	71.8	50.6
97.5°	202.6	160.5	131.5	96.6
100°	243.0	202.2	174.5	137.0
102.5°	287.4	253.1	215.0	177.5
105°	367.0	324.6	280.5	238.1
107.5°	440.7	394.1	341.2	303.0
110°	487.7	437.1	381.7	347.4



TEST NUMBER: P1435844

CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	533.3	481.5	424.7	390.5
115°	595.3	538.2	486.0	456.7
117.5°	655.0	596.3	541.2	518.0
120°	691.6	632.8	579.0	561.1
122.5°	721.6	664.2	614.2	606.7
125°	766.6	707.9	665.5	675.2
127.5°	803.1	749.3	722.5	744.4
130°	825.3	778.0	761.7	792.7
132.5°	844.9	808.0	800.8	843.6
135°	874.2	853.0	859.6	918.3
137.5°	909.1	901.0	922.8	996.9
140°	931.3	936.2	967.2	1050.4
142.5°	961.3	972.7	1012.9	1101.3
145°	1008.0	1032.4	1084.6	1172.7
147.5°	1060.8	1092.5	1157.1	1247.4
150°	1096.1	1136.8	1205.3	1291.8
152.5°	1136.5	1178.6	1247.1	1334.8
155°	1198.8	1246.1	1317.9	1392.9
157.5°	1262.4	1310.7	1379.2	1444.8
160°	1301.6	1353.8	1415.7	1476.1
162.5°	1345.9	1394.2	1448.4	1502.2
165°	1410.8	1450.0	1494.0	1539.7
167.5°	1465.3	1497.9	1532.5	1568.1
170°	1500.6	1526.6	1556.0	1583.7
172.5°	1530.6	1551.4	1573.0	1596.8
175°	1570.7	1582.1	1595.2	1609.8
177.5°	1601.7	1605.6	1609.5	1616.0
180°	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1435844
 CATALOG NUMBER: SQ2W-FA-K-125U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.89	15.64	15.96	16.71	18.16	16.09	16.84	17.15	17.91	19.36
	3H	15.97	16.64	17.05	17.72	19.19	17.32	17.99	18.40	19.07	20.54
	4H	16.32	16.95	17.40	18.03	19.51	17.71	18.34	18.79	19.42	20.90
	6H	16.47	17.06	17.57	18.14	19.63	17.86	18.45	18.96	19.53	21.02
	8H	16.50	17.06	17.60	18.16	19.64	17.88	18.44	18.98	19.54	21.02
	12H	16.50	17.02	17.60	18.12	19.62	17.86	18.39	18.97	19.48	20.99
4H	2H	15.74	16.38	16.84	17.46	18.94	16.66	17.29	17.75	18.37	19.85
	3H	17.12	17.65	18.22	18.76	20.25	18.11	18.64	19.21	19.75	21.24
	4H	17.57	18.06	18.68	19.15	20.67	18.58	19.07	19.69	20.16	21.68
	6H	17.79	18.21	18.91	19.33	20.84	18.80	19.21	19.91	20.33	21.84
	8H	17.85	18.24	18.96	19.35	20.87	18.84	19.23	19.96	20.34	21.86
	12H	17.85	18.20	18.98	19.32	20.85	18.83	19.18	19.96	20.30	21.83
8H	4H	17.95	18.34	19.06	19.45	20.97	18.77	19.16	19.88	20.27	21.79
	6H	18.29	18.61	19.43	19.77	21.28	19.08	19.40	20.21	20.55	22.07
	8H	18.41	18.69	19.55	19.82	21.36	19.17	19.45	20.31	20.59	22.12
	12H	18.44	18.69	19.59	19.82	21.39	19.18	19.43	20.33	20.56	22.13
12H	4H	17.94	18.30	19.07	19.42	20.95	18.73	19.08	19.86	20.21	21.73
	6H	18.36	18.64	19.50	19.78	21.31	19.09	19.38	20.24	20.51	22.05
	8H	18.50	18.75	19.65	19.88	21.45	19.20	19.45	20.35	20.58	22.15