

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435940

Luminaire Tested: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4680.9 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 41.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	91	88	93	89	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	76	71	85	78	72	67	68	64	60	59	56	53	51	48	46	42
3	82	72	65	58	77	68	61	55	59	54	50	52	47	44	44	41	38	35
4	75	64	55	49	70	60	52	46	52	46	42	46	41	37	39	36	33	29
5	69	56	48	41	64	53	45	39	46	40	36	40	36	32	35	31	28	25
6	63	50	42	36	59	47	40	34	42	35	31	36	31	27	31	27	24	21
7	58	45	37	31	54	43	35	29	37	31	27	33	28	24	28	24	21	19
8	54	41	33	27	50	38	31	26	34	28	23	30	25	21	26	22	19	16
9	50	37	29	24	47	35	28	23	31	25	21	27	22	19	24	20	17	14
10	47	34	26	21	43	32	25	20	28	23	19	25	20	17	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4660	4660	4660	4660
5°	4543	8253	4543	8253
10°	4254	16060	4254	16060
15°	3849	18484	3849	18484
20°	3409	19357	3409	19357
25°	3016	19674	3016	19674
30°	2664	19918	2664	19918
35°	2379	21413	2379	21413
40°	2165	22752	2165	22752
45°	1996	23824	1996	23824
50°	1881	24256	1881	24256
55°	1835	24450	1835	24450
60°	1883	24328	1883	24328
65°	1960	23640	1960	23640
70°	2030	17882	2030	17882
75°	2252	9869	2252	9869
80°	2324	9158	2324	9158
85°	2316	3853	2316	3853

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 24671 cd/sqm



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	1.0
10°-20°	220.6	4.7
20°-30°	388.2	8.3
30°-40°	502.5	10.7
40°-50°	554.2	11.8
50°-60°	517.3	11.1
60°-70°	399.6	8.5
70°-80°	184.2	3.9
80°-90°	37.8	0.8
90°-100°	49.8	1.1
100°-110°	145.3	3.1
110°-120°	237.1	5.1
120°-130°	300.9	6.4
130°-140°	322.0	6.9
140°-150°	300.7	6.4
150°-160°	247.4	5.3
160°-170°	165.9	3.5
170°-180°	58.9	1.3
0°-30°	657.2	14.0
0°-40°	1159.7	24.8
0°-60°	2231.2	47.7
0°-90°	2852.9	60.9
90°-120°	432.3	9.2
90°-150°	1355.8	29.0
90°-180°	1828.0	39.1
0°-180°	4680.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	289	289	289	289	289	
5°	280	509	280	509	280	26
15°	230	1106	230	1106	230	64
25°	169	1104	169	1104	169	78
35°	121	1086	121	1086	121	76
45°	87	1043	87	1043	87	68
55°	65	869	65	869	65	59
65°	51	619	51	619	51	50
75°	36	158	36	158	36	37
85°	12	21	12	21	12	13
90°	2	14	2	27	2	2
95°	20	14	20	85	20	24
105°	92	148	92	204	92	98
115°	177	245	177	302	177	175
125°	262	389	262	371	262	234
135°	356	509	356	410	356	275
145°	455	587	455	419	455	285
155°	540	638	540	435	540	248
165°	597	665	597	501	597	168
175°	624	651	624	588	624	59
180°	626	626	626	626	626	



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
2.5°	286.4	291.8	297.2	303.0	308.9	315.4	322.3	328.2	331.1	334.1	331.1
5°	280.3	298.8	317.3	344.1	373.7	407.3	444.9	477.1	493.2	509.2	493.2
7.5°	269.4	307.1	344.7	424.4	518.1	615.4	716.3	800.0	832.0	864.1	832.0
10°	259.5	311.9	364.3	499.5	662.3	787.5	875.0	945.0	962.3	979.6	962.3
12.5°	248.4	319.5	390.7	557.6	756.4	886.5	947.9	998.4	1016.2	1033.9	1016.2
15°	230.3	332.1	433.8	622.5	840.2	974.0	1024.0	1066.3	1086.1	1105.8	1086.1
17.5°	211.7	347.1	482.6	675.1	886.6	1017.0	1066.5	1106.3	1117.0	1127.7	1117.0
20°	198.4	357.5	516.6	709.5	913.6	1036.9	1079.5	1113.1	1119.8	1126.6	1119.8
22.5°	186.2	364.0	541.9	735.0	933.2	1048.4	1080.6	1106.5	1113.8	1121.1	1113.8
25°	169.3	369.7	570.1	762.6	952.6	1057.7	1078.1	1094.6	1099.5	1104.4	1099.5
27.5°	152.9	364.7	576.4	766.5	949.4	1047.5	1060.9	1072.1	1076.9	1081.7	1076.9
30°	142.9	358.1	573.3	761.7	941.2	1035.8	1045.7	1054.8	1061.6	1068.4	1061.6
32.5°	134.0	350.2	566.4	752.5	928.5	1021.1	1030.5	1041.2	1055.9	1070.6	1055.9
35°	120.7	333.5	546.2	730.3	904.8	999.4	1014.2	1032.1	1059.3	1086.4	1059.3
37.5°	109.3	312.0	514.6	696.8	872.2	975.3	1006.3	1036.0	1062.2	1088.3	1062.2
40°	102.7	296.9	491.2	672.0	848.4	957.2	998.5	1035.1	1057.3	1079.5	1057.3
42.5°	96.0	279.9	463.8	643.1	821.0	934.0	982.2	1024.0	1046.2	1068.4	1046.2
45°	87.4	252.7	417.9	595.7	777.6	896.9	953.7	1001.4	1022.4	1043.4	1022.4
47.5°	79.4	222.9	366.5	545.0	735.2	860.4	920.5	969.5	984.8	1000.1	984.8
50°	74.9	203.2	331.5	510.6	706.7	834.3	893.5	941.0	953.3	965.7	953.3
52.5°	70.5	183.9	297.4	476.9	678.4	807.1	862.8	907.5	918.8	930.2	918.8
55°	65.2	157.7	250.2	427.8	633.8	761.1	809.8	848.8	858.7	868.6	858.7
57.5°	60.5	135.1	209.7	381.7	586.2	709.2	750.8	784.0	792.0	800.0	792.0
60°	58.3	123.0	187.8	352.9	551.4	669.5	707.1	737.4	745.4	753.4	745.4
62.5°	54.9	111.3	167.7	324.0	513.7	625.9	660.5	688.4	695.9	703.4	695.9
65°	51.3	97.0	142.6	283.5	456.2	557.0	586.0	608.9	613.9	618.8	613.9
67.5°	46.3	85.1	123.8	246.4	397.0	481.3	499.3	510.5	501.2	492.0	501.2
70°	43.0	78.8	114.5	223.8	357.7	427.6	433.8	431.8	405.3	378.8	405.3
72.5°	40.8	72.6	104.4	199.1	314.6	365.6	352.0	329.3	279.1	228.9	279.1
75°	36.1	62.0	87.9	159.1	245.4	259.0	199.8	155.7	156.9	158.2	156.9
77.5°	29.4	48.8	68.1	111.9	163.8	174.1	142.8	119.6	120.7	121.8	120.7
80°	25.0	40.4	55.8	73.1	91.0	99.3	98.0	97.3	97.9	98.5	97.9
82.5°	20.5	32.0	43.5	53.8	63.8	69.4	70.7	71.4	70.5	69.7	70.5
85°	12.5	19.3	26.1	30.1	33.1	32.2	27.3	23.3	22.0	20.8	22.0
87.5°	4.8	7.8	10.9	10.5	8.9	8.1	8.1	8.2	8.3	8.3	8.3
90°	1.9	4.4	7.6	10.1	12.0	12.6	12.6	13.3	13.9	13.9	13.9
92.5°	7.0	11.0	11.1	11.1	13.5	14.7	15.7	15.8	16.4	16.4	16.4
95°	19.6	21.5	32.3	31.6	21.5	17.1	14.5	14.5	14.5	14.5	14.5
97.5°	37.4	40.2	42.0	56.3	59.4	57.4	46.8	39.3	35.2	33.3	35.2
100°	53.1	54.4	58.2	58.8	74.6	89.8	82.2	72.7	69.6	67.7	69.6
102.5°	68.8	69.6	75.4	78.0	81.7	90.3	116.6	113.7	111.6	111.2	111.6
105°	92.3	93.0	103.7	108.8	111.3	111.3	110.7	123.3	143.6	148.0	143.6
107.5°	117.5	120.4	133.1	146.6	149.5	150.3	147.0	145.1	144.3	144.8	144.3
110°	134.7	139.1	154.3	171.4	175.8	177.1	175.8	173.9	172.6	172.6	172.6



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	151.4	157.8	175.0	194.7	202.1	205.9	203.1	201.7	200.5	201.5	200.5
115°	177.1	186.6	209.3	229.6	244.7	246.6	246.0	246.0	245.4	245.4	245.4
117.5°	200.9	216.0	241.6	265.1	282.7	287.7	290.3	289.5	288.8	290.0	288.8
120°	217.5	235.3	264.3	290.9	308.0	315.6	318.1	316.8	318.1	316.8	318.1
122.5°	235.3	257.0	285.6	313.2	333.3	341.9	344.9	345.2	345.4	344.7	345.4
125°	261.8	288.4	321.9	350.4	371.2	381.3	383.9	384.5	385.8	388.9	385.8
127.5°	288.6	318.7	355.5	383.0	404.4	416.6	420.5	421.9	424.6	426.0	424.6
130°	307.3	341.5	378.8	404.7	425.6	438.9	445.8	447.7	450.9	450.3	450.9
132.5°	327.1	362.7	400.6	427.5	446.9	461.2	467.1	472.5	473.7	474.6	473.7
135°	356.0	394.6	432.6	459.1	477.5	491.4	499.0	504.0	507.2	509.1	507.2
137.5°	386.5	427.3	463.7	487.3	505.8	517.8	526.4	531.7	535.0	536.5	535.0
140°	407.3	446.5	481.9	506.6	523.0	535.0	542.6	548.9	552.7	552.7	552.7
142.5°	427.0	465.7	500.1	524.8	539.2	550.2	558.3	563.1	567.4	567.4	567.4
145°	454.7	493.3	524.9	549.6	561.6	571.7	580.5	584.3	586.9	586.9	586.9
147.5°	483.7	517.8	546.7	570.3	580.4	592.3	599.3	602.3	605.5	604.1	605.5
150°	500.9	532.5	560.3	582.4	592.6	603.9	610.9	613.4	616.6	614.7	616.6
152.5°	517.6	547.7	573.0	593.6	602.2	613.6	621.5	624.1	626.2	624.8	626.2
155°	540.1	566.6	590.0	609.0	616.6	627.3	634.9	638.1	640.6	637.5	640.6
157.5°	560.2	583.1	603.4	620.9	629.0	638.2	645.3	649.2	651.8	650.4	651.8
160°	572.3	593.2	611.5	628.0	635.6	643.8	651.4	655.8	658.3	656.4	658.3
162.5°	582.4	601.3	618.6	633.5	640.1	647.3	656.4	660.4	662.9	660.5	662.9
165°	597.0	612.2	627.3	640.0	645.7	651.4	660.9	665.3	667.2	664.7	667.2
167.5°	608.0	619.6	631.9	642.8	647.0	652.5	662.0	665.7	668.1	664.9	668.1
170°	614.1	624.2	634.9	643.8	647.0	652.0	661.5	664.7	666.6	663.4	666.6
172.5°	619.1	626.7	635.4	643.3	644.9	649.0	658.0	661.1	662.5	659.9	662.5
175°	624.2	628.6	634.9	640.0	639.4	641.9	649.5	652.0	654.5	650.7	654.5
177.5°	626.6	628.6	630.6	633.7	631.6	631.6	637.2	638.7	639.2	637.2	639.2
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
2.5°	328.2	322.3	315.4	308.9	303.0	297.2	291.8	286.4	291.8	297.2	303.0
5°	477.1	444.9	407.3	373.7	344.1	317.3	298.8	280.3	298.8	317.3	344.1
7.5°	800.0	716.3	615.4	518.1	424.4	344.7	307.1	269.4	307.1	344.7	424.4
10°	945.0	875.0	787.5	662.3	499.5	364.3	311.9	259.5	311.9	364.3	499.5
12.5°	998.4	947.9	886.5	756.4	557.6	390.7	319.5	248.4	319.5	390.7	557.6
15°	1066.3	1024.0	974.0	840.2	622.5	433.8	332.1	230.3	332.1	433.8	622.5
17.5°	1106.3	1066.5	1017.0	886.6	675.1	482.6	347.1	211.7	347.1	482.6	675.1
20°	1113.1	1079.5	1036.9	913.6	709.5	516.6	357.5	198.4	357.5	516.6	709.5
22.5°	1106.5	1080.6	1048.4	933.2	735.0	541.9	364.0	186.2	364.0	541.9	735.0
25°	1094.6	1078.1	1057.7	952.6	762.6	570.1	369.7	169.3	369.7	570.1	762.6
27.5°	1072.1	1060.9	1047.5	949.4	766.5	576.4	364.7	152.9	364.7	576.4	766.5
30°	1054.8	1045.7	1035.8	941.2	761.7	573.3	358.1	142.9	358.1	573.3	761.7
32.5°	1041.2	1030.5	1021.1	928.5	752.5	566.4	350.2	134.0	350.2	566.4	752.5
35°	1032.1	1014.2	999.4	904.8	730.3	546.2	333.5	120.7	333.5	546.2	730.3
37.5°	1036.0	1006.3	975.3	872.2	696.8	514.6	312.0	109.3	312.0	514.6	696.8
40°	1035.1	998.5	957.2	848.4	672.0	491.2	296.9	102.7	296.9	491.2	672.0
42.5°	1024.0	982.2	934.0	821.0	643.1	463.8	279.9	96.0	279.9	463.8	643.1
45°	1001.4	953.7	896.9	777.6	595.7	417.9	252.7	87.4	252.7	417.9	595.7
47.5°	969.5	920.5	860.4	735.2	545.0	366.5	222.9	79.4	222.9	366.5	545.0
50°	941.0	893.5	834.3	706.7	510.6	331.5	203.2	74.9	203.2	331.5	510.6
52.5°	907.5	862.8	807.1	678.4	476.9	297.4	183.9	70.5	183.9	297.4	476.9
55°	848.8	809.8	761.1	633.8	427.8	250.2	157.7	65.2	157.7	250.2	427.8
57.5°	784.0	750.8	709.2	586.2	381.7	209.7	135.1	60.5	135.1	209.7	381.7
60°	737.4	707.1	669.5	551.4	352.9	187.8	123.0	58.3	123.0	187.8	352.9
62.5°	688.4	660.5	625.9	513.7	324.0	167.7	111.3	54.9	111.3	167.7	324.0
65°	608.9	586.0	557.0	456.2	283.5	142.6	97.0	51.3	97.0	142.6	283.5
67.5°	510.5	499.3	481.3	397.0	246.4	123.8	85.1	46.3	85.1	123.8	246.4
70°	431.8	433.8	427.6	357.7	223.8	114.5	78.8	43.0	78.8	114.5	223.8
72.5°	329.3	352.0	365.6	314.6	199.1	104.4	72.6	40.8	72.6	104.4	199.1
75°	155.7	199.8	259.0	245.4	159.1	87.9	62.0	36.1	62.0	87.9	159.1
77.5°	119.6	142.8	174.1	163.8	111.9	68.1	48.8	29.4	48.8	68.1	111.9
80°	97.3	98.0	99.3	91.0	73.1	55.8	40.4	25.0	40.4	55.8	73.1
82.5°	71.4	70.7	69.4	63.8	53.8	43.5	32.0	20.5	32.0	43.5	53.8
85°	23.3	27.3	32.2	33.1	30.1	26.1	19.3	12.5	19.3	26.1	30.1
87.5°	8.2	8.1	8.1	8.9	10.5	10.9	7.8	4.8	7.8	10.8	10.8
90°	13.3	12.6	12.6	12.0	10.1	7.6	4.4	1.9	4.4	7.0	11.4
92.5°	15.8	15.7	14.7	13.5	11.1	11.1	11.0	7.0	12.0	17.1	24.5
95°	14.5	14.5	17.1	21.5	31.6	32.3	21.5	19.6	27.8	39.2	49.3
97.5°	39.3	46.8	57.4	59.4	56.3	42.0	40.2	37.4	51.0	62.2	78.5
100°	72.7	82.2	89.8	74.6	58.8	58.2	54.4	53.1	67.7	78.4	94.2
102.5°	113.7	116.6	90.3	81.7	78.0	75.4	69.6	68.8	83.4	98.1	111.4
105°	123.3	110.7	111.3	111.3	108.8	103.7	93.0	92.3	108.8	125.8	142.3
107.5°	145.1	147.0	150.3	149.5	146.6	133.1	120.4	117.5	132.3	152.8	170.9
110°	173.9	175.8	177.1	175.8	171.4	154.3	139.1	134.7	148.0	169.5	189.1



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	201.7	203.1	205.9	202.1	194.7	175.0	157.8	151.4	164.7	186.7	206.8
115°	246.0	246.0	246.6	244.7	229.6	209.3	186.6	177.1	188.5	208.7	230.8
117.5°	289.5	290.3	287.7	282.7	265.1	241.6	216.0	200.9	209.8	231.2	254.0
120°	316.8	318.1	315.6	308.0	290.9	264.3	235.3	217.5	224.5	245.4	268.1
122.5°	345.2	344.9	341.9	333.3	313.2	285.6	257.0	235.3	238.2	257.5	279.8
125°	384.5	383.9	381.3	371.2	350.4	321.9	288.4	261.8	258.0	274.5	297.2
127.5°	421.9	420.5	416.6	404.4	383.0	355.5	318.7	288.6	280.2	290.5	311.4
130°	447.7	445.8	438.9	425.6	404.7	378.8	341.5	307.3	295.3	301.7	320.0
132.5°	472.5	467.1	461.2	446.9	427.5	400.6	362.7	327.1	310.5	313.3	327.6
135°	504.0	499.0	491.4	477.5	459.1	432.6	394.6	356.0	333.3	330.7	339.0
137.5°	531.7	526.4	517.8	505.8	487.3	463.7	427.3	386.5	357.8	349.3	352.5
140°	548.9	542.6	535.0	523.0	506.6	481.9	446.5	407.3	375.0	363.0	361.1
142.5°	563.1	558.3	550.2	539.2	524.8	500.1	465.7	427.0	392.7	377.2	372.7
145°	584.3	580.5	571.7	561.6	549.6	524.9	493.3	454.7	420.5	400.3	390.8
147.5°	602.3	599.3	592.3	580.4	570.3	546.7	517.8	483.7	448.6	423.6	411.3
150°	613.4	610.9	603.9	592.6	582.4	560.3	532.5	500.9	467.3	440.8	425.0
152.5°	624.1	621.5	613.6	602.2	593.6	573.0	547.7	517.6	483.5	457.0	440.7
155°	638.1	634.9	627.3	616.6	609.0	590.0	566.6	540.1	511.0	483.2	464.8
157.5°	649.2	645.3	638.2	629.0	620.9	603.4	583.1	560.2	534.8	508.2	489.5
160°	655.8	651.4	643.8	635.6	628.0	611.5	593.2	572.3	548.9	524.9	504.7
162.5°	660.4	656.4	647.3	640.1	633.5	618.6	601.3	582.4	561.6	540.6	521.9
165°	665.3	660.9	651.4	645.7	640.0	627.3	612.2	597.0	579.3	562.2	547.0
167.5°	665.7	662.0	652.5	647.0	642.8	631.9	619.6	608.0	594.2	580.8	568.2
170°	664.7	661.5	652.0	647.0	643.8	634.9	624.2	614.1	603.3	591.9	581.8
172.5°	661.1	658.0	649.0	644.9	643.3	635.4	626.7	619.1	609.9	601.5	593.4
175°	652.0	649.5	641.9	639.4	640.0	634.9	628.6	624.2	618.5	613.4	609.0
177.5°	638.7	637.2	631.6	631.6	633.7	630.6	628.6	626.6	624.1	622.5	621.0
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
2.5°	308.9	315.4	322.3	328.2	331.1	334.1	331.1	328.2	322.3	315.4	308.9
5°	373.7	407.3	444.9	477.1	493.2	509.2	493.2	477.1	444.9	407.3	373.7
7.5°	518.1	615.4	716.3	800.0	832.0	864.1	832.0	800.0	716.3	615.4	518.1
10°	662.3	787.5	875.0	945.0	962.3	979.6	962.3	945.0	875.0	787.5	662.3
12.5°	756.4	886.5	947.9	998.4	1016.2	1033.9	1016.2	998.4	947.9	886.5	756.4
15°	840.2	974.0	1024.0	1066.3	1086.1	1105.8	1086.1	1066.3	1024.0	974.0	840.2
17.5°	886.6	1017.0	1066.5	1106.3	1117.0	1127.7	1117.0	1106.3	1066.5	1017.0	886.6
20°	913.6	1036.9	1079.5	1113.1	1119.8	1126.6	1119.8	1113.1	1079.5	1036.9	913.6
22.5°	933.2	1048.4	1080.6	1106.5	1113.8	1121.1	1113.8	1106.5	1080.6	1048.4	933.2
25°	952.6	1057.7	1078.1	1094.6	1099.5	1104.4	1099.5	1094.6	1078.1	1057.7	952.6
27.5°	949.4	1047.5	1060.9	1072.1	1076.9	1081.7	1076.9	1072.1	1060.9	1047.5	949.4
30°	941.2	1035.8	1045.7	1054.8	1061.6	1068.4	1061.6	1054.8	1045.7	1035.8	941.2
32.5°	928.5	1021.1	1030.5	1041.2	1055.9	1070.6	1055.9	1041.2	1030.5	1021.1	928.5
35°	904.8	999.4	1014.2	1032.1	1059.3	1086.4	1059.3	1032.1	1014.2	999.4	904.8
37.5°	872.2	975.3	1006.3	1036.0	1062.2	1088.3	1062.2	1036.0	1006.3	975.3	872.2
40°	848.4	957.2	998.5	1035.1	1057.3	1079.5	1057.3	1035.1	998.5	957.2	848.4
42.5°	821.0	934.0	982.2	1024.0	1046.2	1068.4	1046.2	1024.0	982.2	934.0	821.0
45°	777.6	896.9	953.7	1001.4	1022.4	1043.4	1022.4	1001.4	953.7	896.9	777.6
47.5°	735.2	860.4	920.5	969.5	984.8	1000.1	984.8	969.5	920.5	860.4	735.2
50°	706.7	834.3	893.5	941.0	953.3	965.7	953.3	941.0	893.5	834.3	706.7
52.5°	678.4	807.1	862.8	907.5	918.8	930.2	918.8	907.5	862.8	807.1	678.4
55°	633.8	761.1	809.8	848.8	858.7	868.6	858.7	848.8	809.8	761.1	633.8
57.5°	586.2	709.2	750.8	784.0	792.0	800.0	792.0	784.0	750.8	709.2	586.2
60°	551.4	669.5	707.1	737.4	745.4	753.4	745.4	737.4	707.1	669.5	551.4
62.5°	513.7	625.9	660.5	688.4	695.9	703.4	695.9	688.4	660.5	625.9	513.7
65°	456.2	557.0	586.0	608.9	613.9	618.8	613.9	608.9	586.0	557.0	456.2
67.5°	397.0	481.3	499.3	510.5	501.2	492.0	501.2	510.5	499.3	481.3	397.0
70°	357.7	427.6	433.8	431.8	405.3	378.8	405.3	431.8	433.8	427.6	357.7
72.5°	314.6	365.6	352.0	329.3	279.1	228.9	279.1	329.3	352.0	365.6	314.6
75°	245.4	259.0	199.8	155.7	156.9	158.2	156.9	155.7	199.8	259.0	245.4
77.5°	163.8	174.1	142.8	119.6	120.7	121.8	120.7	119.6	142.8	174.1	163.8
80°	91.0	99.3	98.0	97.3	97.9	98.5	97.9	97.3	98.0	99.3	91.0
82.5°	63.8	69.4	70.7	71.4	70.5	69.7	70.5	71.4	70.7	69.4	63.8
85°	33.1	32.2	27.3	23.3	22.0	20.8	22.0	23.3	27.3	32.2	33.1
87.5°	9.4	9.3	10.2	10.7	11.2	11.0	11.2	10.7	10.2	9.3	9.4
90°	14.5	19.0	23.4	25.9	28.5	27.2	28.5	25.9	23.4	19.0	14.5
92.5°	29.2	36.7	42.1	46.7	48.7	48.4	48.7	46.7	42.1	36.7	29.2
95°	58.8	67.7	76.5	82.8	86.6	85.4	86.6	82.8	76.5	67.7	58.8
97.5°	90.7	102.6	112.4	118.4	122.2	124.7	122.2	118.4	112.4	102.6	90.7
100°	111.9	123.3	134.7	141.7	148.0	150.5	148.0	141.7	134.7	123.3	111.9
102.5°	129.1	144.1	156.5	163.9	169.2	171.8	169.2	163.9	156.5	144.1	129.1
105°	157.5	173.3	186.6	196.0	201.7	203.6	201.7	196.0	186.6	173.3	157.5
107.5°	185.8	202.1	214.4	224.9	231.8	235.9	231.8	224.9	214.4	202.1	185.8
110°	208.1	221.3	234.6	244.1	251.1	253.6	251.1	244.1	234.6	221.3	208.1



TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	226.8	241.6	254.9	264.3	272.3	275.9	272.3	264.3	254.9	241.6	226.8
115°	253.0	272.6	284.6	293.4	299.1	302.3	299.1	293.4	284.6	272.6	253.0
117.5°	274.7	295.2	308.4	315.2	317.8	320.1	317.8	315.2	308.4	295.2	274.7
120°	288.4	307.3	322.5	331.4	334.5	335.8	334.5	331.4	322.5	307.3	288.4
122.5°	301.0	319.0	333.7	344.5	349.7	351.0	349.7	344.5	333.7	319.0	301.0
125°	318.7	335.8	351.0	361.7	367.4	370.6	367.4	361.7	351.0	335.8	318.7
127.5°	334.2	352.6	366.5	376.3	381.8	384.4	381.8	376.3	366.5	352.6	334.2
130°	342.8	361.7	375.6	386.4	391.5	394.0	391.5	386.4	375.6	361.7	342.8
132.5°	349.3	369.3	383.7	393.5	399.0	401.6	399.0	393.5	383.7	369.3	349.3
135°	357.3	378.2	393.4	402.8	407.9	410.4	407.9	402.8	393.4	378.2	357.3
137.5°	364.3	383.2	399.0	409.0	413.6	415.2	413.6	409.0	399.0	383.2	364.3
140°	369.3	385.8	401.6	411.1	416.1	416.8	416.1	411.1	401.6	385.8	369.3
142.5°	375.9	388.8	402.6	412.1	417.1	418.3	417.1	412.1	402.6	388.8	375.9
145°	387.7	395.3	404.7	413.6	418.0	419.3	418.0	413.6	404.7	395.3	387.7
147.5°	402.5	404.9	409.8	415.6	419.9	420.8	419.9	415.6	409.8	404.9	402.5
150°	413.6	413.0	414.9	418.7	422.4	421.8	422.4	418.7	414.9	413.0	413.6
152.5°	426.2	422.6	422.4	424.2	426.0	425.9	426.0	424.2	422.4	422.6	426.2
155°	447.7	440.8	437.0	435.7	435.7	435.1	435.7	435.7	437.0	440.8	447.7
157.5°	471.4	461.7	456.0	452.9	452.0	450.7	452.0	452.9	456.0	461.7	471.4
160°	487.6	476.8	471.1	466.1	464.2	462.3	464.2	466.1	471.1	476.8	487.6
162.5°	502.8	492.5	486.3	481.8	479.9	477.0	479.9	481.8	486.3	492.5	502.8
165°	527.4	516.7	509.7	505.9	503.4	500.9	503.4	505.9	509.7	516.7	527.4
167.5°	552.1	540.3	535.8	531.5	529.1	524.5	529.1	531.5	535.8	540.3	552.1
170°	567.3	556.5	554.0	550.2	545.8	540.7	545.8	550.2	554.0	556.5	567.3
172.5°	580.4	573.2	570.7	566.9	565.5	561.4	565.5	566.9	570.7	573.2	580.4
175°	599.5	593.8	593.8	593.2	591.3	587.5	591.3	593.2	593.8	593.8	599.5
177.5°	615.5	612.4	614.4	614.4	613.9	610.4	613.9	614.4	614.4	612.4	615.5
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1

TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	288.6	288.6	288.6	288.6
2.5°	303.0	297.2	291.8	286.4
5°	344.1	317.3	298.8	280.3
7.5°	424.4	344.7	307.1	269.4
10°	499.5	364.3	311.9	259.5
12.5°	557.6	390.7	319.5	248.4
15°	622.5	433.8	332.1	230.3
17.5°	675.1	482.6	347.1	211.7
20°	709.5	516.6	357.5	198.4
22.5°	735.0	541.9	364.0	186.2
25°	762.6	570.1	369.7	169.3
27.5°	766.5	576.4	364.7	152.9
30°	761.7	573.3	358.1	142.9
32.5°	752.5	566.4	350.2	134.0
35°	730.3	546.2	333.5	120.7
37.5°	696.8	514.6	312.0	109.3
40°	672.0	491.2	296.9	102.7
42.5°	643.1	463.8	279.9	96.0
45°	595.7	417.9	252.7	87.4
47.5°	545.0	366.5	222.9	79.4
50°	510.6	331.5	203.2	74.9
52.5°	476.9	297.4	183.9	70.5
55°	427.8	250.2	157.7	65.2
57.5°	381.7	209.7	135.1	60.5
60°	352.9	187.8	123.0	58.3
62.5°	324.0	167.7	111.3	54.9
65°	283.5	142.6	97.0	51.3
67.5°	246.4	123.8	85.1	46.3
70°	223.8	114.5	78.8	43.0
72.5°	199.1	104.4	72.6	40.8
75°	159.1	87.9	62.0	36.1
77.5°	111.9	68.1	48.8	29.4
80°	73.1	55.8	40.4	25.0
82.5°	53.8	43.5	32.0	20.5
85°	30.1	26.1	19.3	12.5
87.5°	10.8	10.8	7.8	4.8
90°	11.4	7.0	4.4	1.9
92.5°	24.5	17.1	12.0	7.0
95°	49.3	39.2	27.8	19.6
97.5°	78.5	62.2	51.0	37.4
100°	94.2	78.4	67.7	53.1
102.5°	111.4	98.1	83.4	68.8
105°	142.3	125.8	108.8	92.3
107.5°	170.9	152.8	132.3	117.5
110°	189.1	169.5	148.0	134.7

TEST NUMBER: P1435940

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	206.8	186.7	164.7	151.4
115°	230.8	208.7	188.5	177.1
117.5°	254.0	231.2	209.8	200.9
120°	268.1	245.4	224.5	217.5
122.5°	279.8	257.5	238.2	235.3
125°	297.2	274.5	258.0	261.8
127.5°	311.4	290.5	280.2	288.6
130°	320.0	301.7	295.3	307.3
132.5°	327.6	313.3	310.5	327.1
135°	339.0	330.7	333.3	356.0
137.5°	352.5	349.3	357.8	386.5
140°	361.1	363.0	375.0	407.3
142.5°	372.7	377.2	392.7	427.0
145°	390.8	400.3	420.5	454.7
147.5°	411.3	423.6	448.6	483.7
150°	425.0	440.8	467.3	500.9
152.5°	440.7	457.0	483.5	517.6
155°	464.8	483.2	511.0	540.1
157.5°	489.5	508.2	534.8	560.2
160°	504.7	524.9	548.9	572.3
162.5°	521.9	540.6	561.6	582.4
165°	547.0	562.2	579.3	597.0
167.5°	568.2	580.8	594.2	608.0
170°	581.8	591.9	603.3	614.1
172.5°	593.4	601.5	609.9	619.1
175°	609.0	613.4	618.5	624.2
177.5°	621.0	622.5	624.1	626.6
180°	626.1	626.1	626.1	626.1



TEST NUMBER: P1435940
 CATALOG NUMBER: SQ2W-FB-K-050U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.46	13.47	13.31	14.35	15.45	22.06	23.06	22.91	23.94	25.05
	3H	13.41	14.32	14.28	15.20	16.33	23.68	24.58	24.54	25.47	26.60
	4H	13.82	14.67	14.70	15.56	16.70	23.86	24.71	24.74	25.61	26.75
	6H	14.08	14.87	14.97	15.77	16.92	23.94	24.73	24.84	25.63	26.78
	8H	14.18	14.93	15.08	15.85	17.00	23.97	24.72	24.87	25.63	26.79
	12H	14.23	14.95	15.14	15.86	17.04	23.95	24.66	24.86	25.57	26.75
4H	2H	17.20	18.05	18.09	18.95	20.09	22.44	23.30	23.33	24.19	25.33
	3H	18.34	19.06	19.24	19.98	21.14	24.35	25.06	25.24	25.98	27.14
	4H	18.63	19.28	19.54	20.20	21.38	24.57	25.22	25.48	26.14	27.32
	6H	18.78	19.34	19.70	20.28	21.46	24.71	25.27	25.64	26.22	27.40
	8H	18.82	19.34	19.75	20.28	21.48	24.76	25.28	25.69	26.22	27.42
	12H	18.83	19.30	19.78	20.26	21.46	24.75	25.22	25.70	26.18	27.38
8H	4H	19.84	20.36	20.76	21.30	22.50	24.68	25.20	25.60	26.14	27.33
	6H	20.10	20.53	21.06	21.51	22.71	24.88	25.31	25.83	26.29	27.49
	8H	20.20	20.58	21.17	21.55	22.77	24.97	25.35	25.94	26.33	27.54
	12H	20.25	20.59	21.22	21.55	22.81	24.99	25.32	25.95	26.28	27.55
12H	4H	19.87	20.34	20.82	21.30	22.50	24.64	25.11	25.58	26.06	27.27
	6H	20.21	20.59	21.17	21.56	22.78	24.87	25.25	25.83	26.22	27.43
	8H	20.36	20.69	21.32	21.65	22.92	24.97	25.31	25.94	26.27	27.53