

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428290

Luminaire Tested: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428290
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9124.1 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 81.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	66	61	75	68	62	57	58	53	49	48	45	42	39	37	35	31
4	75	65	57	52	69	60	54	49	51	46	42	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19
8	55	43	35	30	51	40	33	29	35	29	26	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29546	29546	29546	29546
5°	29508	30053	29508	30053
10°	29819	31043	29819	31043
15°	29810	30214	29810	30214
20°	29328	30771	29328	30771
25°	29245	32036	29245	32036
30°	29214	32344	29214	32344
35°	28936	30113	28936	30113
40°	28270	26500	28270	26500
45°	26749	20956	26749	20956
50°	24319	16259	24319	16259
55°	21371	12656	21371	12656
60°	18493	10420	18493	10420
65°	15965	9123	15965	9123
70°	14355	8101	14355	8101
75°	13150	7448	13150	7448
80°	11446	7280	11446	7280
85°	8299	3464	8299	3464

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 28717 cd/sqm



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.7	1.9
10°-20°	511.6	5.6
20°-30°	790.9	8.7
30°-40°	951.1	10.4
40°-50°	854.1	9.4
50°-60°	572.3	6.3
60°-70°	332.9	3.6
70°-80°	171.0	1.9
80°-90°	48.9	0.5
90°-100°	128.5	1.4
100°-110°	374.8	4.1
110°-120°	611.6	6.7
120°-130°	776.1	8.5
130°-140°	830.4	9.1
140°-150°	775.4	8.5
150°-160°	638.1	7.0
160°-170°	427.9	4.7
170°-180°	151.9	1.7
0°-30°	1479.2	16.2
0°-40°	2430.3	26.6
0°-60°	3856.6	42.3
0°-90°	4409.4	48.3
90°-120°	1114.9	12.2
90°-150°	3496.8	38.3
90°-180°	4715.0	51.7
0°-180°	9124.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1830	1830	1830	1830	1830	
5°	1821	1854	1821	1854	1821	174
15°	1783	1808	1783	1808	1783	501
25°	1642	1798	1642	1798	1642	757
35°	1468	1528	1468	1528	1468	915
45°	1172	918	1172	918	1172	896
55°	759	450	759	450	759	682
65°	418	239	418	239	418	423
75°	211	119	211	119	211	224
85°	45	19	45	19	45	56
90°	5	36	5	70	5	6
95°	51	38	51	220	51	61
105°	238	382	238	525	238	253
115°	457	633	457	780	457	450
125°	675	1003	675	956	675	604
135°	918	1313	918	1058	918	710
145°	1173	1514	1173	1081	1173	734
155°	1393	1644	1393	1122	1393	640
165°	1540	1714	1540	1292	1540	433
175°	1610	1678	1610	1515	1610	153
180°	1615	1615	1615	1615	1615	



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0
2.5°	1822.6	1832.5	1842.5	1838.0	1828.7	1824.4	1825.1	1826.0	1828.0	1830.0	1828.0
5°	1820.7	1834.8	1848.9	1845.6	1836.5	1832.7	1834.4	1837.7	1846.0	1854.3	1846.0
7.5°	1820.3	1840.4	1860.5	1862.0	1857.3	1857.4	1862.2	1868.6	1879.5	1890.5	1879.5
10°	1818.8	1842.9	1866.9	1870.4	1867.1	1865.9	1866.7	1870.2	1881.8	1893.5	1881.8
12.5°	1809.9	1837.9	1865.9	1863.0	1849.7	1842.5	1841.3	1842.0	1848.3	1854.7	1848.3
15°	1783.4	1816.6	1849.7	1836.2	1807.2	1794.0	1796.4	1799.3	1803.5	1807.6	1803.5
17.5°	1736.8	1771.4	1806.1	1794.0	1766.3	1756.9	1765.9	1774.6	1782.7	1790.9	1782.7
20°	1706.9	1740.9	1774.9	1766.6	1744.2	1738.8	1750.4	1762.7	1776.8	1790.9	1776.8
22.5°	1680.0	1714.0	1748.0	1742.7	1724.3	1723.2	1739.5	1756.5	1775.9	1795.3	1775.9
25°	1641.6	1671.5	1701.3	1701.9	1692.8	1701.9	1729.3	1755.2	1776.8	1798.3	1776.8
27.5°	1601.3	1618.9	1636.5	1648.1	1657.7	1681.0	1718.0	1749.5	1764.6	1779.7	1764.6
30°	1567.0	1578.6	1590.2	1611.8	1636.6	1665.2	1697.6	1723.3	1729.1	1734.9	1729.1
32.5°	1529.7	1536.6	1543.6	1574.0	1612.1	1639.7	1656.8	1667.7	1660.3	1652.8	1660.3
35°	1468.1	1473.9	1479.7	1518.5	1568.2	1586.5	1573.2	1559.3	1543.6	1527.8	1543.6
37.5°	1395.0	1406.9	1418.9	1450.5	1488.6	1488.3	1449.5	1415.9	1397.8	1379.7	1397.8
40°	1341.3	1361.2	1381.1	1402.2	1423.8	1405.5	1347.5	1298.8	1278.1	1257.3	1278.1
42.5°	1275.6	1307.4	1339.3	1344.0	1339.7	1300.6	1226.6	1164.8	1139.4	1114.1	1139.4
45°	1171.5	1214.6	1257.7	1233.1	1185.8	1122.0	1041.6	974.2	946.0	917.8	946.0
47.5°	1048.8	1093.0	1137.3	1090.8	1014.0	939.7	867.9	807.5	781.1	754.8	781.1
50°	968.2	1003.8	1039.5	986.8	904.8	830.1	763.0	705.4	676.3	647.3	676.3
52.5°	886.1	911.8	937.5	885.4	807.3	734.6	667.5	610.5	584.1	557.8	584.1
55°	759.2	772.5	785.8	737.5	668.7	602.3	538.5	486.1	467.8	449.6	467.8
57.5°	642.8	651.3	659.8	614.0	550.1	491.1	436.9	392.9	379.4	366.0	379.4
60°	572.7	578.5	584.3	537.9	474.0	421.0	378.7	344.3	333.5	322.7	333.5
62.5°	508.5	513.0	517.5	472.7	411.5	364.1	330.4	303.2	295.0	286.9	295.0
65°	417.9	422.0	426.2	388.0	335.8	296.8	271.1	250.4	244.6	238.8	244.6
67.5°	345.9	348.0	350.2	318.7	276.1	244.7	224.5	207.9	202.5	197.0	202.5
70°	304.1	304.9	305.7	278.0	240.6	212.9	194.6	179.9	175.8	171.6	175.8
72.5°	266.8	265.6	264.4	239.7	207.0	183.2	168.3	156.4	153.5	150.7	153.5
75°	210.8	208.3	205.8	185.3	158.8	140.5	130.6	122.7	121.0	119.4	121.0
77.5°	157.4	154.8	152.1	135.1	113.2	100.6	97.3	94.8	94.8	94.8	94.8
80°	123.1	119.8	116.5	103.2	86.6	78.3	78.3	78.3	78.3	78.3	78.3
82.5°	91.8	87.1	82.5	74.4	65.1	60.4	60.4	60.3	59.6	58.9	59.6
85°	44.8	40.6	36.5	35.4	35.4	33.0	28.0	23.6	21.1	18.7	21.1
87.5°	12.9	14.2	15.9	14.7	12.3	11.0	11.0	11.3	11.7	11.7	11.7
90°	4.9	11.4	19.6	26.1	31.0	32.6	32.6	34.3	35.9	35.9	35.9
92.5°	17.9	28.4	28.7	28.7	34.9	37.8	40.4	40.8	42.4	42.4	42.4
95°	50.6	55.5	83.2	81.6	55.5	44.0	37.5	37.5	37.5	37.5	37.5
97.5°	96.6	103.7	108.3	145.2	153.3	148.1	120.7	101.5	90.7	85.8	90.7
100°	137.0	140.3	150.1	151.7	192.5	231.6	212.0	187.6	179.4	174.5	179.4
102.5°	177.5	179.4	194.4	201.3	210.7	232.9	300.8	293.3	287.7	286.7	287.7
105°	238.1	239.8	267.5	280.5	287.1	287.1	285.4	318.1	370.2	381.7	370.2
107.5°	303.0	310.5	343.2	378.1	385.6	387.5	379.1	374.2	372.2	373.5	372.2
110°	347.4	358.8	398.0	442.0	453.4	456.7	453.4	448.5	445.3	445.3	445.3



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	390.5	407.1	451.5	502.0	521.3	531.1	523.9	520.3	517.0	519.6	517.0
115°	456.7	481.2	539.9	592.1	631.2	636.1	634.5	634.5	632.8	632.8	632.8
117.5°	518.0	557.2	623.1	683.7	729.1	742.1	748.6	746.7	744.7	748.0	744.7
120°	561.1	606.7	681.8	750.3	794.3	813.9	820.4	817.1	820.4	817.1	820.4
122.5°	606.7	662.9	736.6	807.7	859.6	881.7	889.6	890.2	890.9	888.9	890.9
125°	675.2	743.8	830.2	903.6	957.4	983.5	990.0	991.7	994.9	1003.1	994.9
127.5°	744.4	822.0	917.0	987.8	1042.9	1074.5	1084.6	1088.2	1095.1	1098.7	1095.1
130°	792.7	880.8	977.0	1043.9	1097.7	1131.9	1149.9	1154.8	1162.9	1161.3	1162.9
132.5°	843.6	935.6	1033.1	1102.6	1152.5	1189.3	1204.7	1218.7	1221.6	1223.9	1221.6
135°	918.3	1017.8	1115.6	1184.1	1231.4	1267.3	1286.9	1299.9	1308.1	1313.0	1308.1
137.5°	996.9	1101.9	1195.9	1256.9	1304.5	1335.5	1357.7	1371.4	1379.9	1383.8	1379.9
140°	1050.4	1151.5	1242.8	1306.5	1348.9	1379.9	1399.4	1415.7	1425.5	1425.5	1425.5
142.5°	1101.3	1201.1	1289.8	1353.4	1390.6	1419.0	1439.9	1452.3	1463.4	1463.4	1463.4
145°	1172.7	1272.2	1353.8	1417.4	1448.4	1474.5	1497.3	1507.1	1513.6	1513.6	1513.6
147.5°	1247.4	1335.5	1409.9	1470.9	1497.0	1527.6	1545.6	1553.4	1561.6	1558.0	1561.6
150°	1291.8	1373.3	1445.1	1502.2	1528.3	1557.6	1575.6	1582.1	1590.3	1585.4	1590.3
152.5°	1334.8	1412.5	1477.7	1530.9	1553.1	1582.4	1603.0	1609.5	1615.0	1611.5	1615.0
155°	1392.9	1461.4	1521.8	1570.7	1590.3	1618.0	1637.6	1645.7	1652.2	1644.1	1652.2
157.5°	1444.8	1503.8	1556.3	1601.3	1622.2	1646.0	1664.3	1674.4	1680.9	1677.4	1680.9
160°	1476.1	1529.9	1577.2	1619.6	1639.2	1660.4	1680.0	1691.4	1697.9	1693.0	1697.9
162.5°	1502.2	1550.8	1595.5	1634.0	1650.9	1669.5	1693.0	1703.1	1709.6	1703.5	1709.6
165°	1539.7	1578.8	1618.0	1650.6	1665.3	1680.0	1704.4	1715.8	1720.7	1714.2	1720.7
167.5°	1568.1	1598.1	1629.7	1657.8	1668.5	1682.9	1707.4	1716.8	1723.0	1714.9	1723.0
170°	1583.7	1609.8	1637.6	1660.4	1668.5	1681.6	1706.1	1714.2	1719.1	1711.0	1719.1
172.5°	1596.8	1616.4	1638.9	1659.1	1663.3	1673.8	1696.9	1705.1	1708.7	1701.8	1708.7
175°	1609.8	1621.2	1637.6	1650.6	1649.0	1655.5	1675.1	1681.6	1688.1	1678.3	1688.1
177.5°	1616.0	1621.2	1626.5	1634.3	1629.1	1629.1	1643.4	1647.3	1648.6	1643.4	1648.6
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0
2.5°	1826.0	1825.1	1824.4	1828.7	1838.0	1842.5	1832.5	1822.6	1832.5	1842.5	1838.0
5°	1837.7	1834.4	1832.7	1836.5	1845.6	1848.9	1834.8	1820.7	1834.8	1848.9	1845.6
7.5°	1868.6	1862.2	1857.4	1857.3	1862.0	1860.5	1840.4	1820.3	1840.4	1860.5	1862.0
10°	1870.2	1866.7	1865.9	1867.1	1870.4	1866.9	1842.9	1818.8	1842.9	1866.9	1870.4
12.5°	1842.0	1841.3	1842.5	1849.7	1863.0	1865.9	1837.9	1809.9	1837.9	1865.9	1863.0
15°	1799.3	1796.4	1794.0	1807.2	1836.2	1849.7	1816.6	1783.4	1816.6	1849.7	1836.2
17.5°	1774.6	1765.9	1756.9	1766.3	1794.0	1806.1	1771.4	1736.8	1771.4	1806.1	1794.0
20°	1762.7	1750.4	1738.8	1744.2	1766.6	1774.9	1740.9	1706.9	1740.9	1774.9	1766.6
22.5°	1756.5	1739.5	1723.2	1724.3	1742.7	1748.0	1714.0	1680.0	1714.0	1748.0	1742.7
25°	1755.2	1729.3	1701.9	1692.8	1701.9	1701.3	1671.5	1641.6	1671.5	1701.3	1701.9
27.5°	1749.5	1718.0	1681.0	1657.7	1648.1	1636.5	1618.9	1601.3	1618.9	1636.5	1648.1
30°	1723.3	1697.6	1665.2	1636.6	1611.8	1590.2	1578.6	1567.0	1578.6	1590.2	1611.8
32.5°	1667.7	1656.8	1639.7	1612.1	1574.0	1543.6	1536.6	1529.7	1536.6	1543.6	1574.0
35°	1559.3	1573.2	1586.5	1568.2	1518.5	1479.7	1473.9	1468.1	1473.9	1479.7	1518.5
37.5°	1415.9	1449.5	1488.3	1488.6	1450.5	1418.9	1406.9	1395.0	1406.9	1418.9	1450.5
40°	1298.8	1347.5	1405.5	1423.8	1402.2	1381.1	1361.2	1341.3	1361.2	1381.1	1402.2
42.5°	1164.8	1226.6	1300.6	1339.7	1344.0	1339.3	1307.4	1275.6	1307.4	1339.3	1344.0
45°	974.2	1041.6	1122.0	1185.8	1233.1	1257.7	1214.6	1171.5	1214.6	1257.7	1233.1
47.5°	807.5	867.9	939.7	1014.0	1090.8	1137.3	1093.0	1048.8	1093.0	1137.3	1090.8
50°	705.4	763.0	830.1	904.8	986.8	1039.5	1003.8	968.2	1003.8	1039.5	986.8
52.5°	610.5	667.5	734.6	807.3	885.4	937.5	911.8	886.1	911.8	937.5	885.4
55°	486.1	538.5	602.3	668.7	737.5	785.8	772.5	759.2	772.5	785.8	737.5
57.5°	392.9	436.9	491.1	550.1	614.0	659.8	651.3	642.8	651.3	659.8	614.0
60°	344.3	378.7	421.0	474.0	537.9	584.3	578.5	572.7	578.5	584.3	537.9
62.5°	303.2	330.4	364.1	411.5	472.7	517.5	513.0	508.5	513.0	517.5	472.7
65°	250.4	271.1	296.8	335.8	388.0	426.2	422.0	417.9	422.0	426.2	388.0
67.5°	207.9	224.5	244.7	276.1	318.7	350.2	348.0	345.9	348.0	350.2	318.7
70°	179.9	194.6	212.9	240.6	278.0	305.7	304.9	304.1	304.9	305.7	278.0
72.5°	156.4	168.3	183.2	207.0	239.7	264.4	265.6	266.8	265.6	264.4	239.7
75°	122.7	130.6	140.5	158.8	185.3	205.8	208.3	210.8	208.3	205.8	185.3
77.5°	94.8	97.3	100.6	113.2	135.1	152.1	154.8	157.4	154.8	152.1	135.1
80°	78.3	78.3	78.3	86.6	103.2	116.5	119.8	123.1	119.8	116.5	103.2
82.5°	60.3	60.4	60.4	65.1	74.4	82.5	87.1	91.8	87.1	82.5	74.4
85°	23.6	28.0	33.0	35.4	35.4	36.5	40.6	44.8	40.6	36.5	35.4
87.5°	11.3	11.0	11.0	12.3	14.7	15.9	14.2	12.9	14.2	15.5	15.3
90°	34.3	32.6	32.6	31.0	26.1	19.6	11.4	4.9	11.4	17.9	29.4
92.5°	40.8	40.4	37.8	34.9	28.7	28.7	28.4	17.9	31.0	44.0	63.3
95°	37.5	37.5	44.0	55.5	81.6	83.2	55.5	50.6	71.8	101.1	127.2
97.5°	101.5	120.7	148.1	153.3	145.2	108.3	103.7	96.6	131.5	160.5	202.6
100°	187.6	212.0	231.6	192.5	151.7	150.1	140.3	137.0	174.5	202.2	243.0
102.5°	293.3	300.8	232.9	210.7	201.3	194.4	179.4	177.5	215.0	253.1	287.4
105°	318.1	285.4	287.1	287.1	280.5	267.5	239.8	238.1	280.5	324.6	367.0
107.5°	374.2	379.1	387.5	385.6	378.1	343.2	310.5	303.0	341.2	394.1	440.7
110°	448.5	453.4	456.7	453.4	442.0	398.0	358.8	347.4	381.7	437.1	487.7



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	520.3	523.9	531.1	521.3	502.0	451.5	407.1	390.5	424.7	481.5	533.3
115°	634.5	634.5	636.1	631.2	592.1	539.9	481.2	456.7	486.0	538.2	595.3
117.5°	746.7	748.6	742.1	729.1	683.7	623.1	557.2	518.0	541.2	596.3	655.0
120°	817.1	820.4	813.9	794.3	750.3	681.8	606.7	561.1	579.0	632.8	691.6
122.5°	890.2	889.6	881.7	859.6	807.7	736.6	662.9	606.7	614.2	664.2	721.6
125°	991.7	990.0	983.5	957.4	903.6	830.2	743.8	675.2	665.5	707.9	766.6
127.5°	1088.2	1084.6	1074.5	1042.9	987.8	917.0	822.0	744.4	722.5	749.3	803.1
130°	1154.8	1149.9	1131.9	1097.7	1043.9	977.0	880.8	792.7	761.7	778.0	825.3
132.5°	1218.7	1204.7	1189.3	1152.5	1102.6	1033.1	935.6	843.6	800.8	808.0	844.9
135°	1299.9	1286.9	1267.3	1231.4	1184.1	1115.6	1017.8	918.3	859.6	853.0	874.2
137.5°	1371.4	1357.7	1335.5	1304.5	1256.9	1195.9	1101.9	996.9	922.8	901.0	909.1
140°	1415.7	1399.4	1379.9	1348.9	1306.5	1242.8	1151.5	1050.4	967.2	936.2	931.3
142.5°	1452.3	1439.9	1419.0	1390.6	1353.4	1289.8	1201.1	1101.3	1012.9	972.7	961.3
145°	1507.1	1497.3	1474.5	1448.4	1417.4	1353.8	1272.2	1172.7	1084.6	1032.4	1008.0
147.5°	1553.4	1545.6	1527.6	1497.0	1470.9	1409.9	1335.5	1247.4	1157.1	1092.5	1060.8
150°	1582.1	1575.6	1557.6	1528.3	1502.2	1445.1	1373.3	1291.8	1205.3	1136.8	1096.1
152.5°	1609.5	1603.0	1582.4	1553.1	1530.9	1477.7	1412.5	1334.8	1247.1	1178.6	1136.5
155°	1645.7	1637.6	1618.0	1590.3	1570.7	1521.8	1461.4	1392.9	1317.9	1246.1	1198.8
157.5°	1674.4	1664.3	1646.0	1622.2	1601.3	1556.3	1503.8	1444.8	1379.2	1310.7	1262.4
160°	1691.4	1680.0	1660.4	1639.2	1619.6	1577.2	1529.9	1476.1	1415.7	1353.8	1301.6
162.5°	1703.1	1693.0	1669.5	1650.9	1634.0	1595.5	1550.8	1502.2	1448.4	1394.2	1345.9
165°	1715.8	1704.4	1680.0	1665.3	1650.6	1618.0	1578.8	1539.7	1494.0	1450.0	1410.8
167.5°	1716.8	1707.4	1682.9	1668.5	1657.8	1629.7	1598.1	1568.1	1532.5	1497.9	1465.3
170°	1714.2	1706.1	1681.6	1668.5	1660.4	1637.6	1609.8	1583.7	1556.0	1526.6	1500.6
172.5°	1705.1	1696.9	1673.8	1663.3	1659.1	1638.9	1616.4	1596.8	1573.0	1551.4	1530.6
175°	1681.6	1675.1	1655.5	1649.0	1650.6	1637.6	1621.2	1609.8	1595.2	1582.1	1570.7
177.5°	1647.3	1643.4	1629.1	1629.1	1634.3	1626.5	1621.2	1616.0	1609.5	1605.6	1601.7
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0
2.5°	1828.7	1824.4	1825.1	1826.0	1828.0	1830.0	1828.0	1826.0	1825.1	1824.4	1828.7
5°	1836.5	1832.7	1834.4	1837.7	1846.0	1854.3	1846.0	1837.7	1834.4	1832.7	1836.5
7.5°	1857.3	1857.4	1862.2	1868.6	1879.5	1890.5	1879.5	1868.6	1862.2	1857.4	1857.3
10°	1867.1	1865.9	1866.7	1870.2	1881.8	1893.5	1881.8	1870.2	1866.7	1865.9	1867.1
12.5°	1849.7	1842.5	1841.3	1842.0	1848.3	1854.7	1848.3	1842.0	1841.3	1842.5	1849.7
15°	1807.2	1794.0	1796.4	1799.3	1803.5	1807.6	1803.5	1799.3	1796.4	1794.0	1807.2
17.5°	1766.3	1756.9	1765.9	1774.6	1782.7	1790.9	1782.7	1774.6	1765.9	1756.9	1766.3
20°	1744.2	1738.8	1750.4	1762.7	1776.8	1790.9	1776.8	1762.7	1750.4	1738.8	1744.2
22.5°	1724.3	1723.2	1739.5	1756.5	1775.9	1795.3	1775.9	1756.5	1739.5	1723.2	1724.3
25°	1692.8	1701.9	1729.3	1755.2	1776.8	1798.3	1776.8	1755.2	1729.3	1701.9	1692.8
27.5°	1657.7	1681.0	1718.0	1749.5	1764.6	1779.7	1764.6	1749.5	1718.0	1681.0	1657.7
30°	1636.6	1665.2	1697.6	1723.3	1729.1	1734.9	1729.1	1723.3	1697.6	1665.2	1636.6
32.5°	1612.1	1639.7	1656.8	1667.7	1660.3	1652.8	1660.3	1667.7	1656.8	1639.7	1612.1
35°	1568.2	1586.5	1573.2	1559.3	1543.6	1527.8	1543.6	1559.3	1573.2	1586.5	1568.2
37.5°	1488.6	1488.3	1449.5	1415.9	1397.8	1379.7	1397.8	1415.9	1449.5	1488.3	1488.6
40°	1423.8	1405.5	1347.5	1298.8	1278.1	1257.3	1278.1	1298.8	1347.5	1405.5	1423.8
42.5°	1339.7	1300.6	1226.6	1164.8	1139.4	1114.1	1139.4	1164.8	1226.6	1300.6	1339.7
45°	1185.8	1122.0	1041.6	974.2	946.0	917.8	946.0	974.2	1041.6	1122.0	1185.8
47.5°	1014.0	939.7	867.9	807.5	781.1	754.8	781.1	807.5	867.9	939.7	1014.0
50°	904.8	830.1	763.0	705.4	676.3	647.3	676.3	705.4	763.0	830.1	904.8
52.5°	807.3	734.6	667.5	610.5	584.1	557.8	584.1	610.5	667.5	734.6	807.3
55°	668.7	602.3	538.5	486.1	467.8	449.6	467.8	486.1	538.5	602.3	668.7
57.5°	550.1	491.1	436.9	392.9	379.4	366.0	379.4	392.9	436.9	491.1	550.1
60°	474.0	421.0	378.7	344.3	333.5	322.7	333.5	344.3	378.7	421.0	474.0
62.5°	411.5	364.1	330.4	303.2	295.0	286.9	295.0	303.2	330.4	364.1	411.5
65°	335.8	296.8	271.1	250.4	244.6	238.8	244.6	250.4	271.1	296.8	335.8
67.5°	276.1	244.7	224.5	207.9	202.5	197.0	202.5	207.9	224.5	244.7	276.1
70°	240.6	212.9	194.6	179.9	175.8	171.6	175.8	179.9	194.6	212.9	240.6
72.5°	207.0	183.2	168.3	156.4	153.5	150.7	153.5	156.4	168.3	183.2	207.0
75°	158.8	140.5	130.6	122.7	121.0	119.4	121.0	122.7	130.6	140.5	158.8
77.5°	113.2	100.6	97.3	94.8	94.8	94.8	94.8	94.8	97.3	100.6	113.2
80°	86.6	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	86.6
82.5°	65.1	60.4	60.4	60.3	59.6	58.9	59.6	60.3	60.4	60.4	65.1
85°	35.4	33.0	28.0	23.6	21.1	18.7	21.1	23.6	28.0	33.0	35.4
87.5°	13.6	14.3	16.5	17.9	19.2	18.5	19.2	17.9	16.5	14.3	13.6
90°	37.5	48.9	60.3	66.9	73.4	70.1	73.4	66.9	60.3	48.9	37.5
92.5°	75.4	94.6	108.6	120.4	125.6	124.9	125.6	120.4	108.6	94.6	75.4
95°	151.7	174.5	197.4	213.7	223.5	220.2	223.5	213.7	197.4	174.5	151.7
97.5°	233.9	264.6	290.0	305.3	315.1	321.6	315.1	305.3	290.0	264.6	233.9
100°	288.7	318.1	347.4	365.4	381.7	388.2	381.7	365.4	347.4	318.1	288.7
102.5°	333.1	371.5	403.5	422.8	436.5	443.0	436.5	422.8	403.5	371.5	333.1
105°	406.1	446.9	481.2	505.6	520.3	525.2	520.3	505.6	481.2	446.9	406.1
107.5°	479.2	521.3	552.9	580.0	597.9	608.4	597.9	580.0	552.9	521.3	479.2
110°	536.6	570.9	605.1	629.6	647.5	654.0	647.5	629.6	605.1	570.9	536.6



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	584.9	623.1	657.3	681.8	702.3	711.5	702.3	681.8	657.3	623.1	584.9
115°	652.4	703.0	734.0	756.8	771.5	779.6	771.5	756.8	734.0	703.0	652.4
117.5°	708.5	761.4	795.3	812.9	819.8	825.6	819.8	812.9	795.3	761.4	708.5
120°	743.8	792.7	831.8	854.7	862.8	866.1	862.8	854.7	831.8	792.7	743.8
122.5°	776.4	822.7	860.5	888.6	902.0	905.2	902.0	888.6	860.5	822.7	776.4
125°	822.0	866.1	905.2	933.0	947.6	955.8	947.6	933.0	905.2	866.1	822.0
127.5°	861.8	909.5	945.3	970.5	984.8	991.3	984.8	970.5	945.3	909.5	861.8
130°	884.0	933.0	968.8	996.6	1009.6	1016.1	1009.6	996.6	968.8	933.0	884.0
132.5°	901.0	952.5	989.7	1014.8	1029.2	1035.7	1029.2	1014.8	989.7	952.5	901.0
135°	921.5	975.4	1014.5	1039.0	1052.0	1058.5	1052.0	1039.0	1014.5	975.4	921.5
137.5°	939.5	988.4	1029.2	1055.0	1066.7	1070.9	1066.7	1055.0	1029.2	988.4	939.5
140°	952.5	994.9	1035.7	1060.2	1073.2	1074.9	1073.2	1060.2	1035.7	994.9	952.5
142.5°	969.5	1002.8	1038.3	1062.8	1075.8	1078.8	1075.8	1062.8	1038.3	1002.8	969.5
145°	999.8	1019.4	1043.9	1066.7	1078.1	1081.4	1078.1	1066.7	1043.9	1019.4	999.8
147.5°	1038.0	1044.2	1056.9	1071.9	1083.0	1085.3	1083.0	1071.9	1056.9	1044.2	1038.0
150°	1066.7	1065.1	1070.0	1079.7	1089.5	1087.9	1089.5	1079.7	1070.0	1065.1	1066.7
152.5°	1099.3	1089.9	1089.5	1094.1	1098.7	1098.3	1098.7	1094.1	1089.5	1089.9	1099.3
155°	1154.8	1136.8	1127.0	1123.8	1123.8	1122.2	1123.8	1123.8	1127.0	1136.8	1154.8
157.5°	1215.8	1190.7	1176.0	1168.1	1165.9	1162.3	1165.9	1168.1	1176.0	1190.7	1215.8
160°	1257.5	1229.8	1215.1	1202.1	1197.2	1192.3	1197.2	1202.1	1215.1	1229.8	1257.5
162.5°	1296.7	1270.2	1254.3	1242.5	1237.6	1230.1	1237.6	1242.5	1254.3	1270.2	1296.7
165°	1360.3	1332.6	1314.6	1304.8	1298.3	1291.8	1298.3	1304.8	1314.6	1332.6	1360.3
167.5°	1423.9	1393.6	1381.8	1370.7	1364.5	1352.8	1364.5	1370.7	1381.8	1393.6	1423.9
170°	1463.0	1435.3	1428.8	1419.0	1407.6	1394.5	1407.6	1419.0	1428.8	1435.3	1463.0
172.5°	1497.0	1478.4	1471.8	1462.1	1458.5	1448.0	1458.5	1462.1	1471.8	1478.4	1497.0
175°	1546.2	1531.5	1531.5	1529.9	1525.0	1515.2	1525.0	1529.9	1531.5	1531.5	1546.2
177.5°	1587.3	1579.5	1584.7	1584.7	1583.4	1574.3	1583.4	1584.7	1584.7	1579.5	1587.3
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1830.0	1830.0	1830.0	1830.0
2.5°	1838.0	1842.5	1832.5	1822.6
5°	1845.6	1848.9	1834.8	1820.7
7.5°	1862.0	1860.5	1840.4	1820.3
10°	1870.4	1866.9	1842.9	1818.8
12.5°	1863.0	1865.9	1837.9	1809.9
15°	1836.2	1849.7	1816.6	1783.4
17.5°	1794.0	1806.1	1771.4	1736.8
20°	1766.6	1774.9	1740.9	1706.9
22.5°	1742.7	1748.0	1714.0	1680.0
25°	1701.9	1701.3	1671.5	1641.6
27.5°	1648.1	1636.5	1618.9	1601.3
30°	1611.8	1590.2	1578.6	1567.0
32.5°	1574.0	1543.6	1536.6	1529.7
35°	1518.5	1479.7	1473.9	1468.1
37.5°	1450.5	1418.9	1406.9	1395.0
40°	1402.2	1381.1	1361.2	1341.3
42.5°	1344.0	1339.3	1307.4	1275.6
45°	1233.1	1257.7	1214.6	1171.5
47.5°	1090.8	1137.3	1093.0	1048.8
50°	986.8	1039.5	1003.8	968.2
52.5°	885.4	937.5	911.8	886.1
55°	737.5	785.8	772.5	759.2
57.5°	614.0	659.8	651.3	642.8
60°	537.9	584.3	578.5	572.7
62.5°	472.7	517.5	513.0	508.5
65°	388.0	426.2	422.0	417.9
67.5°	318.7	350.2	348.0	345.9
70°	278.0	305.7	304.9	304.1
72.5°	239.7	264.4	265.6	266.8
75°	185.3	205.8	208.3	210.8
77.5°	135.1	152.1	154.8	157.4
80°	103.2	116.5	119.8	123.1
82.5°	74.4	82.5	87.1	91.8
85°	35.4	36.5	40.6	44.8
87.5°	15.3	15.5	14.2	12.9
90°	29.4	17.9	11.4	4.9
92.5°	63.3	44.0	31.0	17.9
95°	127.2	101.1	71.8	50.6
97.5°	202.6	160.5	131.5	96.6
100°	243.0	202.2	174.5	137.0
102.5°	287.4	253.1	215.0	177.5
105°	367.0	324.6	280.5	238.1
107.5°	440.7	394.1	341.2	303.0
110°	487.7	437.1	381.7	347.4

TEST NUMBER: P1428290

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	533.3	481.5	424.7	390.5
115°	595.3	538.2	486.0	456.7
117.5°	655.0	596.3	541.2	518.0
120°	691.6	632.8	579.0	561.1
122.5°	721.6	664.2	614.2	606.7
125°	766.6	707.9	665.5	675.2
127.5°	803.1	749.3	722.5	744.4
130°	825.3	778.0	761.7	792.7
132.5°	844.9	808.0	800.8	843.6
135°	874.2	853.0	859.6	918.3
137.5°	909.1	901.0	922.8	996.9
140°	931.3	936.2	967.2	1050.4
142.5°	961.3	972.7	1012.9	1101.3
145°	1008.0	1032.4	1084.6	1172.7
147.5°	1060.8	1092.5	1157.1	1247.4
150°	1096.1	1136.8	1205.3	1291.8
152.5°	1136.5	1178.6	1247.1	1334.8
155°	1198.8	1246.1	1317.9	1392.9
157.5°	1262.4	1310.7	1379.2	1444.8
160°	1301.6	1353.8	1415.7	1476.1
162.5°	1345.9	1394.2	1448.4	1502.2
165°	1410.8	1450.0	1494.0	1539.7
167.5°	1465.3	1497.9	1532.5	1568.1
170°	1500.6	1526.6	1556.0	1583.7
172.5°	1530.6	1551.4	1573.0	1596.8
175°	1570.7	1582.1	1595.2	1609.8
177.5°	1601.7	1605.6	1609.5	1616.0
180°	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1428290
 CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.28	19.08	19.26	20.07	21.37	14.64	15.45	15.62	16.44	17.74
	3H	19.48	20.20	20.47	21.20	22.52	15.80	16.52	16.79	17.52	18.84
	4H	19.96	20.64	20.97	21.64	22.97	16.26	16.95	17.27	17.95	19.27
	6H	20.26	20.88	21.27	21.89	23.23	16.60	17.23	17.62	18.23	19.58
	8H	20.36	20.95	21.38	21.97	23.31	16.74	17.33	17.76	18.36	19.69
	12H	20.40	20.96	21.42	21.98	23.34	16.77	17.33	17.79	18.35	19.71
4H	2H	18.37	19.05	19.38	20.05	21.38	15.35	16.03	16.36	17.03	18.36
	3H	19.83	20.39	20.85	21.42	22.76	16.70	17.27	17.72	18.29	19.64
	4H	20.45	20.97	21.48	21.99	23.36	17.24	17.76	18.27	18.78	20.15
	6H	20.88	21.33	21.92	22.37	23.73	17.67	18.12	18.71	19.16	20.52
	8H	21.04	21.45	22.08	22.49	23.87	17.86	18.27	18.89	19.31	20.68
	12H	21.10	21.48	22.16	22.53	23.91	17.90	18.27	18.96	19.33	20.71
8H	4H	20.48	20.89	21.51	21.93	23.30	17.57	17.98	18.60	19.02	20.39
	6H	21.01	21.35	22.07	22.43	23.80	18.11	18.45	19.17	19.53	20.90
	8H	21.24	21.54	22.31	22.61	24.00	18.37	18.67	19.44	19.73	21.12
	12H	21.36	21.62	22.43	22.68	24.12	18.46	18.72	19.53	19.78	21.22
12H	4H	20.43	20.81	21.49	21.86	23.24	17.58	17.96	18.64	19.01	20.39
	6H	21.00	21.30	22.06	22.36	23.75	18.18	18.48	19.25	19.54	20.93
	8H	21.24	21.51	22.32	22.57	24.00	18.46	18.73	19.53	19.79	21.22