

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428518

Luminaire Tested: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428518
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4968.9 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63				
1	103	99	96	93	97	94	91	89	83	81	79	73	72	70	64	63	62	58				
2	96	90	85	80	90	85	80	77	76	72	69	67	65	63	59	57	56	52				
3	89	81	75	70	84	77	71	67	69	65	61	62	58	56	55	52	51	47				
4	83	74	67	62	78	70	64	59	63	58	55	57	53	50	51	48	46	43				
5	77	67	60	55	73	64	57	53	58	53	49	52	48	45	47	44	42	39				
6	72	61	54	49	68	58	52	47	53	48	44	48	44	41	43	40	38	35				
7	67	56	49	44	63	54	47	43	49	44	40	45	40	37	40	37	35	32				
8	63	52	45	40	59	49	43	39	45	40	36	41	37	34	38	34	32	30				
9	59	48	41	36	56	46	39	35	42	37	33	38	34	31	35	32	29	27				
10	55	44	38	33	52	42	36	32	39	34	30	36	32	29	33	29	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32393	32393	32393	32393
5°	32688	32672	32688	32672
10°	33019	33002	33019	33002
15°	33567	32972	33567	32972
20°	33728	32439	33728	32439
25°	33034	31527	33034	31527
30°	31343	29479	31343	29479
35°	28189	26597	28189	26597
40°	23110	21892	23110	21892
45°	14451	13572	14451	13572
50°	5654	5169	5654	5169
55°	2790	2761	2790	2761
60°	1305	1179	1305	1179
65°	1177	1104	1177	1104
70°	1133	1090	1133	1090
75°	1142	1023	1142	1023
80°	1069	986	1069	986
85°	1074	889	1074	889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°
 Vertical Angle: 45°
 Luminance: 16449 cd/sqm



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	3.9
10°-20°	560.9	11.3
20°-30°	829.3	16.7
30°-40°	858.1	17.3
40°-50°	516.1	10.4
50°-60°	123.4	2.5
60°-70°	33.7	0.7
70°-80°	18.9	0.4
80°-90°	8.5	0.2
90°-100°	49.8	1.0
100°-110°	145.3	2.9
110°-120°	237.1	4.8
120°-130°	300.9	6.1
130°-140°	322.0	6.5
140°-150°	300.7	6.1
150°-160°	247.4	5.0
160°-170°	165.9	3.3
170°-180°	58.9	1.2
0°-30°	1582.1	31.8
0°-40°	2440.2	49.1
0°-60°	3079.7	62.0
0°-90°	3140.9	63.2
90°-120°	432.3	8.7
90°-150°	1355.8	27.3
90°-180°	1828.0	36.8
0°-180°	4968.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2006	2006	2006	2006	2006	
5°	2017	2016	2017	2016	2017	192
15°	2008	1973	2008	1973	2008	566
25°	1854	1770	1854	1770	1854	848
35°	1430	1349	1430	1349	1430	878
45°	633	594	633	594	633	489
55°	99	98	99	98	99	99
65°	31	29	31	29	31	31
75°	18	16	18	16	18	19
85°	6	5	6	5	6	6
90°	2	14	2	27	2	2
95°	20	14	20	85	20	24
105°	92	148	92	204	92	98
115°	177	245	177	302	177	175
125°	262	389	262	371	262	234
135°	356	509	356	410	356	275
145°	455	587	455	419	455	285
155°	540	638	540	435	540	248
165°	597	665	597	501	597	168
175°	624	651	624	588	624	59
180°	626	626	626	626	626	



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3
2.5°	2016.3	2013.9	2011.5	2005.5	1998.4	1998.5	2006.1	2011.3	2009.6	2007.9	2009.6
5°	2016.9	2013.9	2010.9	2004.1	1995.9	1997.9	2009.8	2018.5	2017.2	2015.9	2017.2
7.5°	2014.8	2013.5	2012.2	2007.2	2001.0	2002.4	2011.4	2017.7	2015.8	2013.8	2015.8
10°	2014.0	2014.4	2014.9	2008.2	1999.3	1999.5	2008.9	2015.6	2014.3	2013.0	2014.3
12.5°	2013.2	2016.7	2020.2	2011.3	1998.2	1995.4	2002.7	2007.5	2004.5	2001.5	2004.5
15°	2008.2	2015.1	2021.9	2009.8	1991.5	1982.3	1982.3	1981.2	1976.9	1972.6	1976.9
17.5°	1986.9	1995.0	2003.1	1986.8	1962.2	1946.7	1940.1	1933.8	1928.6	1923.4	1928.6
20°	1963.0	1971.2	1979.3	1959.8	1931.2	1911.5	1900.8	1892.3	1890.1	1888.0	1890.1
22.5°	1925.3	1934.1	1942.9	1922.1	1891.4	1870.2	1858.5	1848.9	1845.3	1841.8	1845.3
25°	1854.3	1861.2	1868.0	1846.3	1815.1	1795.3	1786.7	1779.1	1774.4	1769.7	1774.4
27.5°	1759.7	1763.5	1767.2	1746.2	1717.0	1697.5	1687.8	1678.8	1672.3	1665.8	1672.3
30°	1681.2	1682.9	1684.6	1667.8	1644.7	1626.7	1613.9	1601.7	1591.5	1581.2	1591.5
32.5°	1588.1	1589.8	1591.5	1576.7	1556.4	1540.1	1528.0	1516.8	1508.6	1500.4	1508.6
35°	1430.2	1429.3	1428.5	1419.0	1406.6	1393.3	1379.2	1366.5	1358.0	1349.4	1358.0
37.5°	1232.6	1233.8	1235.0	1228.0	1218.1	1207.7	1196.5	1186.0	1177.4	1168.8	1177.4
40°	1096.5	1097.3	1098.2	1092.3	1084.2	1072.0	1055.7	1043.0	1040.9	1038.7	1040.9
42.5°	930.3	943.1	955.9	950.7	939.5	927.7	915.2	903.3	893.3	883.3	893.3
45°	632.9	671.8	710.7	720.4	720.4	712.9	697.9	676.5	635.4	594.4	635.4
47.5°	357.4	401.7	446.0	475.1	499.1	488.9	444.4	398.6	348.8	298.9	348.8
50°	225.1	255.0	284.9	322.2	362.0	351.1	289.5	239.2	222.5	205.8	222.5
52.5°	159.7	174.9	190.1	225.3	267.1	262.0	210.0	168.8	160.0	151.2	160.0
55°	99.1	104.6	110.2	127.3	148.2	146.9	123.4	104.9	101.5	98.1	101.5
57.5°	58.9	64.6	70.3	77.9	86.1	86.1	77.9	70.4	65.0	59.6	65.0
60°	40.4	45.1	49.8	56.1	62.9	62.1	53.5	46.0	41.3	36.5	41.3
62.5°	35.0	37.0	38.9	43.8	49.6	49.1	42.3	36.7	35.1	33.5	35.1
65°	30.8	31.2	31.6	32.1	32.5	32.3	31.4	30.6	29.7	28.9	29.7
67.5°	27.1	27.6	28.0	27.8	27.5	27.3	27.2	26.9	26.2	25.4	26.2
70°	24.0	24.5	24.9	25.0	25.0	24.8	24.4	23.9	23.5	23.1	23.5
72.5°	21.7	22.2	22.6	22.4	22.1	21.9	21.8	21.5	20.8	20.0	20.8
75°	18.3	18.3	18.3	18.3	18.3	18.1	17.6	17.2	16.8	16.4	16.8
77.5°	13.8	14.3	14.7	14.5	14.1	13.8	13.8	13.7	13.3	12.9	13.3
80°	11.5	12.0	12.4	12.2	11.8	11.5	11.5	11.4	11.0	10.6	11.0
82.5°	9.2	9.3	9.4	9.4	9.3	9.2	9.2	9.1	8.7	8.3	8.7
85°	5.8	5.8	5.8	5.5	5.0	4.8	4.8	4.8	4.8	4.8	4.8
87.5°	1.9	2.8	3.7	4.1	4.1	4.1	4.1	4.2	4.3	4.3	4.3
90°	1.9	4.4	7.6	10.1	12.0	12.6	12.6	13.3	13.9	13.9	13.9
92.5°	7.0	11.0	11.1	11.1	13.5	14.7	15.7	15.8	16.4	16.4	16.4
95°	19.6	21.5	32.3	31.6	21.5	17.1	14.5	14.5	14.5	14.5	14.5
97.5°	37.4	40.2	42.0	56.3	59.4	57.4	46.8	39.3	35.2	33.3	35.2
100°	53.1	54.4	58.2	58.8	74.6	89.8	82.2	72.7	69.6	67.7	69.6
102.5°	68.8	69.6	75.4	78.0	81.7	90.3	116.6	113.7	111.6	111.2	111.6
105°	92.3	93.0	103.7	108.8	111.3	111.3	110.7	123.3	143.6	148.0	143.6
107.5°	117.5	120.4	133.1	146.6	149.5	150.3	147.0	145.1	144.3	144.8	144.3
110°	134.7	139.1	154.3	171.4	175.8	177.1	175.8	173.9	172.6	172.6	172.6



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	151.4	157.8	175.0	194.7	202.1	205.9	203.1	201.7	200.5	201.5	200.5
115°	177.1	186.6	209.3	229.6	244.7	246.6	246.0	246.0	245.4	245.4	245.4
117.5°	200.9	216.0	241.6	265.1	282.7	287.7	290.3	289.5	288.8	290.0	288.8
120°	217.5	235.3	264.3	290.9	308.0	315.6	318.1	316.8	318.1	316.8	318.1
122.5°	235.3	257.0	285.6	313.2	333.3	341.9	344.9	345.2	345.4	344.7	345.4
125°	261.8	288.4	321.9	350.4	371.2	381.3	383.9	384.5	385.8	388.9	385.8
127.5°	288.6	318.7	355.5	383.0	404.4	416.6	420.5	421.9	424.6	426.0	424.6
130°	307.3	341.5	378.8	404.7	425.6	438.9	445.8	447.7	450.9	450.3	450.9
132.5°	327.1	362.7	400.6	427.5	446.9	461.2	467.1	472.5	473.7	474.6	473.7
135°	356.0	394.6	432.6	459.1	477.5	491.4	499.0	504.0	507.2	509.1	507.2
137.5°	386.5	427.3	463.7	487.3	505.8	517.8	526.4	531.7	535.0	536.5	535.0
140°	407.3	446.5	481.9	506.6	523.0	535.0	542.6	548.9	552.7	552.7	552.7
142.5°	427.0	465.7	500.1	524.8	539.2	550.2	558.3	563.1	567.4	567.4	567.4
145°	454.7	493.3	524.9	549.6	561.6	571.7	580.5	584.3	586.9	586.9	586.9
147.5°	483.7	517.8	546.7	570.3	580.4	592.3	599.3	602.3	605.5	604.1	605.5
150°	500.9	532.5	560.3	582.4	592.6	603.9	610.9	613.4	616.6	614.7	616.6
152.5°	517.6	547.7	573.0	593.6	602.2	613.6	621.5	624.1	626.2	624.8	626.2
155°	540.1	566.6	590.0	609.0	616.6	627.3	634.9	638.1	640.6	637.5	640.6
157.5°	560.2	583.1	603.4	620.9	629.0	638.2	645.3	649.2	651.8	650.4	651.8
160°	572.3	593.2	611.5	628.0	635.6	643.8	651.4	655.8	658.3	656.4	658.3
162.5°	582.4	601.3	618.6	633.5	640.1	647.3	656.4	660.4	662.9	660.5	662.9
165°	597.0	612.2	627.3	640.0	645.7	651.4	660.9	665.3	667.2	664.7	667.2
167.5°	608.0	619.6	631.9	642.8	647.0	652.5	662.0	665.7	668.1	664.9	668.1
170°	614.1	624.2	634.9	643.8	647.0	652.0	661.5	664.7	666.6	663.4	666.6
172.5°	619.1	626.7	635.4	643.3	644.9	649.0	658.0	661.1	662.5	659.9	662.5
175°	624.2	628.6	634.9	640.0	639.4	641.9	649.5	652.0	654.5	650.7	654.5
177.5°	626.6	628.6	630.6	633.7	631.6	631.6	637.2	638.7	639.2	637.2	639.2
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3
2.5°	2011.3	2006.1	1998.5	1998.4	2005.5	2011.5	2013.9	2016.3	2013.9	2011.5	2005.5
5°	2018.5	2009.8	1997.9	1995.9	2004.1	2010.9	2013.9	2016.9	2013.9	2010.9	2004.1
7.5°	2017.7	2011.4	2002.4	2001.0	2007.2	2012.2	2013.5	2014.8	2013.5	2012.2	2007.2
10°	2015.6	2008.9	1999.5	1999.3	2008.2	2014.9	2014.4	2014.0	2014.4	2014.9	2008.2
12.5°	2007.5	2002.7	1995.4	1998.2	2011.3	2020.2	2016.7	2013.2	2016.7	2020.2	2011.3
15°	1981.2	1982.3	1982.3	1991.5	2009.8	2021.9	2015.1	2008.2	2015.1	2021.9	2009.8
17.5°	1933.8	1940.1	1946.7	1962.2	1986.8	2003.1	1995.0	1986.9	1995.0	2003.1	1986.8
20°	1892.3	1900.8	1911.5	1931.2	1959.8	1979.3	1971.2	1963.0	1971.2	1979.3	1959.8
22.5°	1848.9	1858.5	1870.2	1891.4	1922.1	1942.9	1934.1	1925.3	1934.1	1942.9	1922.1
25°	1779.1	1786.7	1795.3	1815.1	1846.3	1868.0	1861.2	1854.3	1861.2	1868.0	1846.3
27.5°	1678.8	1687.8	1697.5	1717.0	1746.2	1767.2	1763.5	1759.7	1763.5	1767.2	1746.2
30°	1601.7	1613.9	1626.7	1644.7	1667.8	1684.6	1682.9	1681.2	1682.9	1684.6	1667.8
32.5°	1516.8	1528.0	1540.1	1556.4	1576.7	1591.5	1589.8	1588.1	1589.8	1591.5	1576.7
35°	1366.5	1379.2	1393.3	1406.6	1419.0	1428.5	1429.3	1430.2	1429.3	1428.5	1419.0
37.5°	1186.0	1196.5	1207.7	1218.1	1228.0	1235.0	1233.8	1232.6	1233.8	1235.0	1228.0
40°	1043.0	1055.7	1072.0	1084.2	1092.3	1098.2	1097.3	1096.5	1097.3	1098.2	1092.3
42.5°	903.3	915.2	927.7	939.5	950.7	955.9	943.1	930.3	943.1	955.9	950.7
45°	676.5	697.9	712.9	720.4	720.4	710.7	671.8	632.9	671.8	710.7	720.4
47.5°	398.6	444.4	488.9	499.1	475.1	446.0	401.7	357.4	401.7	446.0	475.1
50°	239.2	289.5	351.1	362.0	322.2	284.9	255.0	225.1	255.0	284.9	322.2
52.5°	168.8	210.0	262.0	267.1	225.3	190.1	174.9	159.7	174.9	190.1	225.3
55°	104.9	123.4	146.9	148.2	127.3	110.2	104.6	99.1	104.6	110.2	127.3
57.5°	70.4	77.9	86.1	86.1	77.9	70.3	64.6	58.9	64.6	70.3	77.9
60°	46.0	53.5	62.1	62.9	56.1	49.8	45.1	40.4	45.1	49.8	56.1
62.5°	36.7	42.3	49.1	49.6	43.8	38.9	37.0	35.0	37.0	38.9	43.8
65°	30.6	31.4	32.3	32.5	32.1	31.6	31.2	30.8	31.2	31.6	32.1
67.5°	26.9	27.2	27.3	27.5	27.8	28.0	27.6	27.1	27.6	28.0	27.8
70°	23.9	24.4	24.8	25.0	25.0	24.9	24.5	24.0	24.5	24.9	25.0
72.5°	21.5	21.8	21.9	22.1	22.4	22.6	22.2	21.7	22.2	22.6	22.4
75°	17.2	17.6	18.1	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
77.5°	13.7	13.8	13.8	14.1	14.5	14.7	14.3	13.8	14.3	14.7	14.5
80°	11.4	11.5	11.5	11.8	12.2	12.4	12.0	11.5	12.0	12.4	12.2
82.5°	9.1	9.2	9.2	9.3	9.4	9.4	9.3	9.2	9.3	9.4	9.4
85°	4.8	4.8	4.8	5.0	5.5	5.8	5.8	5.8	5.8	5.8	5.5
87.5°	4.2	4.1	4.1	4.1	4.1	3.7	2.8	1.9	2.8	3.6	4.3
90°	13.3	12.6	12.6	12.0	10.1	7.6	4.4	1.9	4.4	7.0	11.4
92.5°	15.8	15.7	14.7	13.5	11.1	11.1	11.0	7.0	12.0	17.1	24.5
95°	14.5	14.5	17.1	21.5	31.6	32.3	21.5	19.6	27.8	39.2	49.3
97.5°	39.3	46.8	57.4	59.4	56.3	42.0	40.2	37.4	51.0	62.2	78.5
100°	72.7	82.2	89.8	74.6	58.8	58.2	54.4	53.1	67.7	78.4	94.2
102.5°	113.7	116.6	90.3	81.7	78.0	75.4	69.6	68.8	83.4	98.1	111.4
105°	123.3	110.7	111.3	111.3	108.8	103.7	93.0	92.3	108.8	125.8	142.3
107.5°	145.1	147.0	150.3	149.5	146.6	133.1	120.4	117.5	132.3	152.8	170.9
110°	173.9	175.8	177.1	175.8	171.4	154.3	139.1	134.7	148.0	169.5	189.1



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	201.7	203.1	205.9	202.1	194.7	175.0	157.8	151.4	164.7	186.7	206.8
115°	246.0	246.0	246.6	244.7	229.6	209.3	186.6	177.1	188.5	208.7	230.8
117.5°	289.5	290.3	287.7	282.7	265.1	241.6	216.0	200.9	209.8	231.2	254.0
120°	316.8	318.1	315.6	308.0	290.9	264.3	235.3	217.5	224.5	245.4	268.1
122.5°	345.2	344.9	341.9	333.3	313.2	285.6	257.0	235.3	238.2	257.5	279.8
125°	384.5	383.9	381.3	371.2	350.4	321.9	288.4	261.8	258.0	274.5	297.2
127.5°	421.9	420.5	416.6	404.4	383.0	355.5	318.7	288.6	280.2	290.5	311.4
130°	447.7	445.8	438.9	425.6	404.7	378.8	341.5	307.3	295.3	301.7	320.0
132.5°	472.5	467.1	461.2	446.9	427.5	400.6	362.7	327.1	310.5	313.3	327.6
135°	504.0	499.0	491.4	477.5	459.1	432.6	394.6	356.0	333.3	330.7	339.0
137.5°	531.7	526.4	517.8	505.8	487.3	463.7	427.3	386.5	357.8	349.3	352.5
140°	548.9	542.6	535.0	523.0	506.6	481.9	446.5	407.3	375.0	363.0	361.1
142.5°	563.1	558.3	550.2	539.2	524.8	500.1	465.7	427.0	392.7	377.2	372.7
145°	584.3	580.5	571.7	561.6	549.6	524.9	493.3	454.7	420.5	400.3	390.8
147.5°	602.3	599.3	592.3	580.4	570.3	546.7	517.8	483.7	448.6	423.6	411.3
150°	613.4	610.9	603.9	592.6	582.4	560.3	532.5	500.9	467.3	440.8	425.0
152.5°	624.1	621.5	613.6	602.2	593.6	573.0	547.7	517.6	483.5	457.0	440.7
155°	638.1	634.9	627.3	616.6	609.0	590.0	566.6	540.1	511.0	483.2	464.8
157.5°	649.2	645.3	638.2	629.0	620.9	603.4	583.1	560.2	534.8	508.2	489.5
160°	655.8	651.4	643.8	635.6	628.0	611.5	593.2	572.3	548.9	524.9	504.7
162.5°	660.4	656.4	647.3	640.1	633.5	618.6	601.3	582.4	561.6	540.6	521.9
165°	665.3	660.9	651.4	645.7	640.0	627.3	612.2	597.0	579.3	562.2	547.0
167.5°	665.7	662.0	652.5	647.0	642.8	631.9	619.6	608.0	594.2	580.8	568.2
170°	664.7	661.5	652.0	647.0	643.8	634.9	624.2	614.1	603.3	591.9	581.8
172.5°	661.1	658.0	649.0	644.9	643.3	635.4	626.7	619.1	609.9	601.5	593.4
175°	652.0	649.5	641.9	639.4	640.0	634.9	628.6	624.2	618.5	613.4	609.0
177.5°	638.7	637.2	631.6	631.6	633.7	630.6	628.6	626.6	624.1	622.5	621.0
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3	2006.3
2.5°	1998.4	1998.5	2006.1	2011.3	2009.6	2007.9	2009.6	2011.3	2006.1	1998.5	1998.4
5°	1995.9	1997.9	2009.8	2018.5	2017.2	2015.9	2017.2	2018.5	2009.8	1997.9	1995.9
7.5°	2001.0	2002.4	2011.4	2017.7	2015.8	2013.8	2015.8	2017.7	2011.4	2002.4	2001.0
10°	1999.3	1999.5	2008.9	2015.6	2014.3	2013.0	2014.3	2015.6	2008.9	1999.5	1999.3
12.5°	1998.2	1995.4	2002.7	2007.5	2004.5	2001.5	2004.5	2007.5	2002.7	1995.4	1998.2
15°	1991.5	1982.3	1982.3	1981.2	1976.9	1972.6	1976.9	1981.2	1982.3	1982.3	1991.5
17.5°	1962.2	1946.7	1940.1	1933.8	1928.6	1923.4	1928.6	1933.8	1940.1	1946.7	1962.2
20°	1931.2	1911.5	1900.8	1892.3	1890.1	1888.0	1890.1	1892.3	1900.8	1911.5	1931.2
22.5°	1891.4	1870.2	1858.5	1848.9	1845.3	1841.8	1845.3	1848.9	1858.5	1870.2	1891.4
25°	1815.1	1795.3	1786.7	1779.1	1774.4	1769.7	1774.4	1779.1	1786.7	1795.3	1815.1
27.5°	1717.0	1697.5	1687.8	1678.8	1672.3	1665.8	1672.3	1678.8	1687.8	1697.5	1717.0
30°	1644.7	1626.7	1613.9	1601.7	1591.5	1581.2	1591.5	1601.7	1613.9	1626.7	1644.7
32.5°	1556.4	1540.1	1528.0	1516.8	1508.6	1500.4	1508.6	1516.8	1528.0	1540.1	1556.4
35°	1406.6	1393.3	1379.2	1366.5	1358.0	1349.4	1358.0	1366.5	1379.2	1393.3	1406.6
37.5°	1218.1	1207.7	1196.5	1186.0	1177.4	1168.8	1177.4	1186.0	1196.5	1207.7	1218.1
40°	1084.2	1072.0	1055.7	1043.0	1040.9	1038.7	1040.9	1043.0	1055.7	1072.0	1084.2
42.5°	939.5	927.7	915.2	903.3	893.3	883.3	893.3	903.3	915.2	927.7	939.5
45°	720.4	712.9	697.9	676.5	635.4	594.4	635.4	676.5	697.9	712.9	720.4
47.5°	499.1	488.9	444.4	398.6	348.8	298.9	348.8	398.6	444.4	488.9	499.1
50°	362.0	351.1	289.5	239.2	222.5	205.8	222.5	239.2	289.5	351.1	362.0
52.5°	267.1	262.0	210.0	168.8	160.0	151.2	160.0	168.8	210.0	262.0	267.1
55°	148.2	146.9	123.4	104.9	101.5	98.1	101.5	104.9	123.4	146.9	148.2
57.5°	86.1	86.1	77.9	70.4	65.0	59.6	65.0	70.4	77.9	86.1	86.1
60°	62.9	62.1	53.5	46.0	41.3	36.5	41.3	46.0	53.5	62.1	62.9
62.5°	49.6	49.1	42.3	36.7	35.1	33.5	35.1	36.7	42.3	49.1	49.6
65°	32.5	32.3	31.4	30.6	29.7	28.9	29.7	30.6	31.4	32.3	32.5
67.5°	27.5	27.3	27.2	26.9	26.2	25.4	26.2	26.9	27.2	27.3	27.5
70°	25.0	24.8	24.4	23.9	23.5	23.1	23.5	23.9	24.4	24.8	25.0
72.5°	22.1	21.9	21.8	21.5	20.8	20.0	20.8	21.5	21.8	21.9	22.1
75°	18.3	18.1	17.6	17.2	16.8	16.4	16.8	17.2	17.6	18.1	18.3
77.5°	14.1	13.8	13.8	13.7	13.3	12.9	13.3	13.7	13.8	13.8	14.1
80°	11.8	11.5	11.5	11.4	11.0	10.6	11.0	11.4	11.5	11.5	11.8
82.5°	9.3	9.2	9.2	9.1	8.7	8.3	8.7	9.1	9.2	9.2	9.3
85°	5.0	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	5.0
87.5°	4.6	5.3	6.2	6.7	7.2	7.0	7.2	6.7	6.2	5.3	4.6
90°	14.5	19.0	23.4	25.9	28.5	27.2	28.5	25.9	23.4	19.0	14.5
92.5°	29.2	36.7	42.1	46.7	48.7	48.4	48.7	46.7	42.1	36.7	29.2
95°	58.8	67.7	76.5	82.8	86.6	85.4	86.6	82.8	76.5	67.7	58.8
97.5°	90.7	102.6	112.4	118.4	122.2	124.7	122.2	118.4	112.4	102.6	90.7
100°	111.9	123.3	134.7	141.7	148.0	150.5	148.0	141.7	134.7	123.3	111.9
102.5°	129.1	144.1	156.5	163.9	169.2	171.8	169.2	163.9	156.5	144.1	129.1
105°	157.5	173.3	186.6	196.0	201.7	203.6	201.7	196.0	186.6	173.3	157.5
107.5°	185.8	202.1	214.4	224.9	231.8	235.9	231.8	224.9	214.4	202.1	185.8
110°	208.1	221.3	234.6	244.1	251.1	253.6	251.1	244.1	234.6	221.3	208.1



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	226.8	241.6	254.9	264.3	272.3	275.9	272.3	264.3	254.9	241.6	226.8
115°	253.0	272.6	284.6	293.4	299.1	302.3	299.1	293.4	284.6	272.6	253.0
117.5°	274.7	295.2	308.4	315.2	317.8	320.1	317.8	315.2	308.4	295.2	274.7
120°	288.4	307.3	322.5	331.4	334.5	335.8	334.5	331.4	322.5	307.3	288.4
122.5°	301.0	319.0	333.7	344.5	349.7	351.0	349.7	344.5	333.7	319.0	301.0
125°	318.7	335.8	351.0	361.7	367.4	370.6	367.4	361.7	351.0	335.8	318.7
127.5°	334.2	352.6	366.5	376.3	381.8	384.4	381.8	376.3	366.5	352.6	334.2
130°	342.8	361.7	375.6	386.4	391.5	394.0	391.5	386.4	375.6	361.7	342.8
132.5°	349.3	369.3	383.7	393.5	399.0	401.6	399.0	393.5	383.7	369.3	349.3
135°	357.3	378.2	393.4	402.8	407.9	410.4	407.9	402.8	393.4	378.2	357.3
137.5°	364.3	383.2	399.0	409.0	413.6	415.2	413.6	409.0	399.0	383.2	364.3
140°	369.3	385.8	401.6	411.1	416.1	416.8	416.1	411.1	401.6	385.8	369.3
142.5°	375.9	388.8	402.6	412.1	417.1	418.3	417.1	412.1	402.6	388.8	375.9
145°	387.7	395.3	404.7	413.6	418.0	419.3	418.0	413.6	404.7	395.3	387.7
147.5°	402.5	404.9	409.8	415.6	419.9	420.8	419.9	415.6	409.8	404.9	402.5
150°	413.6	413.0	414.9	418.7	422.4	421.8	422.4	418.7	414.9	413.0	413.6
152.5°	426.2	422.6	422.4	424.2	426.0	425.9	426.0	424.2	422.4	422.6	426.2
155°	447.7	440.8	437.0	435.7	435.7	435.1	435.7	435.7	437.0	440.8	447.7
157.5°	471.4	461.7	456.0	452.9	452.0	450.7	452.0	452.9	456.0	461.7	471.4
160°	487.6	476.8	471.1	466.1	464.2	462.3	464.2	466.1	471.1	476.8	487.6
162.5°	502.8	492.5	486.3	481.8	479.9	477.0	479.9	481.8	486.3	492.5	502.8
165°	527.4	516.7	509.7	505.9	503.4	500.9	503.4	505.9	509.7	516.7	527.4
167.5°	552.1	540.3	535.8	531.5	529.1	524.5	529.1	531.5	535.8	540.3	552.1
170°	567.3	556.5	554.0	550.2	545.8	540.7	545.8	550.2	554.0	556.5	567.3
172.5°	580.4	573.2	570.7	566.9	565.5	561.4	565.5	566.9	570.7	573.2	580.4
175°	599.5	593.8	593.8	593.2	591.3	587.5	591.3	593.2	593.8	593.8	599.5
177.5°	615.5	612.4	614.4	614.4	613.9	610.4	613.9	614.4	614.4	612.4	615.5
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2006.3	2006.3	2006.3	2006.3
2.5°	2005.5	2011.5	2013.9	2016.3
5°	2004.1	2010.9	2013.9	2016.9
7.5°	2007.2	2012.2	2013.5	2014.8
10°	2008.2	2014.9	2014.4	2014.0
12.5°	2011.3	2020.2	2016.7	2013.2
15°	2009.8	2021.9	2015.1	2008.2
17.5°	1986.8	2003.1	1995.0	1986.9
20°	1959.8	1979.3	1971.2	1963.0
22.5°	1922.1	1942.9	1934.1	1925.3
25°	1846.3	1868.0	1861.2	1854.3
27.5°	1746.2	1767.2	1763.5	1759.7
30°	1667.8	1684.6	1682.9	1681.2
32.5°	1576.7	1591.5	1589.8	1588.1
35°	1419.0	1428.5	1429.3	1430.2
37.5°	1228.0	1235.0	1233.8	1232.6
40°	1092.3	1098.2	1097.3	1096.5
42.5°	950.7	955.9	943.1	930.3
45°	720.4	710.7	671.8	632.9
47.5°	475.1	446.0	401.7	357.4
50°	322.2	284.9	255.0	225.1
52.5°	225.3	190.1	174.9	159.7
55°	127.3	110.2	104.6	99.1
57.5°	77.9	70.3	64.6	58.9
60°	56.1	49.8	45.1	40.4
62.5°	43.8	38.9	37.0	35.0
65°	32.1	31.6	31.2	30.8
67.5°	27.8	28.0	27.6	27.1
70°	25.0	24.9	24.5	24.0
72.5°	22.4	22.6	22.2	21.7
75°	18.3	18.3	18.3	18.3
77.5°	14.5	14.7	14.3	13.8
80°	12.2	12.4	12.0	11.5
82.5°	9.4	9.4	9.3	9.2
85°	5.5	5.8	5.8	5.8
87.5°	4.3	3.6	2.8	1.9
90°	11.4	7.0	4.4	1.9
92.5°	24.5	17.1	12.0	7.0
95°	49.3	39.2	27.8	19.6
97.5°	78.5	62.2	51.0	37.4
100°	94.2	78.4	67.7	53.1
102.5°	111.4	98.1	83.4	68.8
105°	142.3	125.8	108.8	92.3
107.5°	170.9	152.8	132.3	117.5
110°	189.1	169.5	148.0	134.7



TEST NUMBER: P1428518

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	206.8	186.7	164.7	151.4
115°	230.8	208.7	188.5	177.1
117.5°	254.0	231.2	209.8	200.9
120°	268.1	245.4	224.5	217.5
122.5°	279.8	257.5	238.2	235.3
125°	297.2	274.5	258.0	261.8
127.5°	311.4	290.5	280.2	288.6
130°	320.0	301.7	295.3	307.3
132.5°	327.6	313.3	310.5	327.1
135°	339.0	330.7	333.3	356.0
137.5°	352.5	349.3	357.8	386.5
140°	361.1	363.0	375.0	407.3
142.5°	372.7	377.2	392.7	427.0
145°	390.8	400.3	420.5	454.7
147.5°	411.3	423.6	448.6	483.7
150°	425.0	440.8	467.3	500.9
152.5°	440.7	457.0	483.5	517.6
155°	464.8	483.2	511.0	540.1
157.5°	489.5	508.2	534.8	560.2
160°	504.7	524.9	548.9	572.3
162.5°	521.9	540.6	561.6	582.4
165°	547.0	562.2	579.3	597.0
167.5°	568.2	580.8	594.2	608.0
170°	581.8	591.9	603.3	614.1
172.5°	593.4	601.5	609.9	619.1
175°	609.0	613.4	618.5	624.2
177.5°	621.0	622.5	624.1	626.6
180°	626.1	626.1	626.1	626.1



TEST NUMBER: P1428518
 CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.21	6.01	6.08	6.87	7.96	5.20	5.99	6.07	6.86	7.94
	3H	5.91	6.61	6.79	7.49	8.60	5.82	6.53	6.71	7.40	8.51
	4H	6.27	6.93	7.17	7.82	8.94	6.13	6.79	7.03	7.67	8.80
	6H	6.55	7.15	7.45	8.04	9.17	6.37	6.97	7.28	7.86	8.99
	8H	6.66	7.24	7.58	8.14	9.27	6.47	7.04	7.38	7.94	9.07
	12H	6.74	7.29	7.66	8.19	9.34	6.52	7.06	7.44	7.96	9.11
4H	2H	5.31	5.97	6.22	6.85	7.98	5.30	5.96	6.20	6.84	7.96
	3H	6.26	6.80	7.17	7.71	8.85	6.17	6.72	7.08	7.63	8.76
	4H	6.77	7.26	7.69	8.17	9.33	6.62	7.11	7.54	8.02	9.18
	6H	7.19	7.61	8.13	8.55	9.71	6.99	7.41	7.93	8.35	9.51
	8H	7.38	7.77	8.32	8.70	9.87	7.16	7.55	8.09	8.48	9.65
	12H	7.51	7.86	8.46	8.80	9.98	7.25	7.60	8.20	8.55	9.72
8H	4H	6.88	7.28	7.82	8.20	9.38	6.75	7.14	7.68	8.07	9.24
	6H	7.46	7.78	8.42	8.75	9.92	7.26	7.58	8.22	8.55	9.73
	8H	7.75	8.03	8.72	8.99	10.18	7.53	7.81	8.50	8.77	9.96
	12H	7.97	8.22	8.94	9.17	10.41	7.70	7.95	8.67	8.90	10.14
12H	4H	6.86	7.21	7.81	8.16	9.34	6.73	7.08	7.69	8.03	9.21
	6H	7.49	7.78	8.46	8.74	9.93	7.31	7.59	8.28	8.55	9.74
	8H	7.82	8.07	8.79	9.02	10.26	7.61	7.86	8.58	8.81	10.05