

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428536

Luminaire Tested: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428536
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8019.0 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 73.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65				
1	103	100	97	94	97	94	92	89	84	82	80	74	73	72	66	65	64	60				
2	96	90	85	81	91	86	81	77	77	73	71	68	66	64	61	59	58	54				
3	90	82	76	71	85	78	72	68	70	66	62	63	60	57	56	54	52	49				
4	83	74	67	62	79	71	65	60	64	59	56	58	54	51	52	49	47	44				
5	78	68	61	55	73	65	58	54	59	54	50	53	49	46	48	45	43	40				
6	72	62	55	50	68	59	53	48	54	49	45	49	45	42	45	42	39	37				
7	68	57	50	45	64	54	48	43	50	45	41	46	41	38	42	38	36	34				
8	63	52	45	40	60	50	44	39	46	41	37	42	38	35	39	35	33	31				
9	59	48	41	37	56	46	40	36	43	38	34	39	35	32	36	33	30	28				
10	56	45	38	34	53	43	37	33	40	35	31	37	32	29	34	30	28	26				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	54063	54063	54063	54063
5°	54557	54531	54557	54531
10°	55107	55081	55107	55081
15°	56024	55031	56024	55031
20°	56293	54141	56293	54141
25°	55135	52617	55135	52617
30°	52311	49200	52311	49200
35°	47048	44389	47048	44389
40°	38570	36538	38570	36538
45°	24116	22651	24116	22651
50°	9434	8628	9434	8628
55°	4653	4608	4653	4608
60°	2176	1970	2176	1970
65°	1964	1841	1964	1841
70°	1893	1817	1893	1817
75°	1903	1703	1903	1703
80°	1794	1646	1794	1646
85°	1778	1482	1778	1482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°
 Vertical Angle: 45°
 Luminance: 27452 cd/sqm



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	320.2	4.0
10°-20°	936.2	11.7
20°-30°	1384.2	17.3
30°-40°	1432.1	17.9
40°-50°	861.4	10.7
50°-60°	205.9	2.6
60°-70°	56.3	0.7
70°-80°	31.5	0.4
80°-90°	13.9	0.2
90°-100°	75.7	0.9
100°-110°	220.8	2.8
110°-120°	360.3	4.5
120°-130°	457.2	5.7
130°-140°	489.2	6.1
140°-150°	456.8	5.7
150°-160°	375.9	4.7
160°-170°	252.1	3.1
170°-180°	89.5	1.1
0°-30°	2640.5	32.9
0°-40°	4072.6	50.8
0°-60°	5140.0	64.1
0°-90°	5241.7	65.4
90°-120°	656.7	8.2
90°-150°	2059.9	25.7
90°-180°	2777.0	34.6
0°-180°	8019.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3348	3348	3348	3348	3348	
5°	3366	3365	3366	3365	3366	321
15°	3352	3292	3352	3292	3352	945
25°	3095	2954	3095	2954	3095	1415
35°	2387	2252	2387	2252	2387	1465
45°	1056	992	1056	992	1056	817
55°	165	164	165	164	165	166
65°	51	48	51	48	51	52
75°	30	27	30	27	30	32
85°	10	8	10	8	10	10
90°	3	21	3	41	3	3
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5
2.5°	3365.2	3361.2	3357.2	3347.2	3335.2	3335.5	3348.1	3356.8	3353.9	3351.1	3353.9
5°	3366.2	3361.2	3356.2	3344.8	3331.2	3334.4	3354.4	3368.8	3366.7	3364.6	3366.7
7.5°	3362.6	3360.5	3358.4	3350.0	3339.6	3341.9	3357.1	3367.6	3364.3	3361.0	3364.3
10°	3361.3	3362.1	3362.8	3351.7	3336.7	3337.1	3352.8	3364.0	3361.9	3359.7	3361.9
12.5°	3360.1	3365.9	3371.8	3356.9	3335.0	3330.2	3342.5	3350.5	3345.5	3340.5	3345.5
15°	3351.7	3363.1	3374.5	3354.4	3323.7	3308.4	3308.4	3306.6	3299.5	3292.3	3299.5
17.5°	3316.1	3329.6	3343.2	3315.9	3274.9	3248.9	3238.0	3227.5	3218.8	3210.1	3218.8
20°	3276.3	3289.8	3303.4	3270.9	3223.1	3190.3	3172.5	3158.2	3154.6	3151.1	3154.6
22.5°	3213.3	3228.0	3242.7	3208.0	3156.8	3121.4	3101.8	3085.7	3079.9	3074.0	3079.9
25°	3094.9	3106.3	3117.7	3081.5	3029.4	2996.2	2982.0	2969.3	2961.5	2953.6	2961.5
27.5°	2936.9	2943.2	2949.5	2914.5	2865.7	2833.1	2816.9	2801.9	2791.1	2780.3	2791.1
30°	2805.9	2808.8	2811.6	2783.5	2744.9	2715.0	2693.6	2673.2	2656.1	2639.0	2656.1
32.5°	2650.6	2653.4	2656.3	2631.5	2597.5	2570.4	2550.2	2531.6	2517.9	2504.2	2517.9
35°	2387.0	2385.5	2384.1	2368.2	2347.6	2325.4	2301.9	2280.7	2266.4	2252.1	2266.4
37.5°	2057.3	2059.3	2061.3	2049.4	2033.0	2015.6	1997.0	1979.5	1965.1	1950.7	1965.1
40°	1830.0	1831.4	1832.8	1823.0	1809.4	1789.1	1762.0	1740.8	1737.2	1733.6	1737.2
42.5°	1552.6	1574.0	1595.4	1586.7	1568.0	1548.3	1527.4	1507.6	1490.9	1474.2	1490.9
45°	1056.2	1121.2	1186.1	1202.3	1202.3	1189.8	1164.9	1129.0	1060.5	992.0	1060.5
47.5°	596.5	670.4	744.3	792.9	833.0	815.9	741.7	665.3	582.1	498.9	582.1
50°	375.6	425.6	475.5	537.8	604.1	585.9	483.2	399.2	371.3	343.5	371.3
52.5°	266.5	291.9	317.3	375.9	445.7	437.2	350.5	281.7	267.0	252.3	267.0
55°	165.3	174.6	183.9	212.4	247.4	245.2	206.0	175.1	169.4	163.7	169.4
57.5°	98.2	107.8	117.4	130.0	143.7	143.7	130.0	117.5	108.5	99.5	108.5
60°	67.4	75.3	83.1	93.6	105.1	103.6	89.4	76.7	68.8	61.0	68.8
62.5°	58.4	61.7	65.0	73.1	82.8	81.9	70.5	61.3	58.6	55.9	58.6
65°	51.4	52.1	52.8	53.5	54.2	53.9	52.4	51.0	49.6	48.2	49.6
67.5°	45.3	46.0	46.7	46.4	45.9	45.5	45.4	44.9	43.7	42.4	43.7
70°	40.1	40.8	41.6	41.7	41.7	41.4	40.7	40.0	39.2	38.5	39.2
72.5°	36.3	37.0	37.7	37.5	36.9	36.5	36.4	36.0	34.7	33.4	34.7
75°	30.5	30.5	30.5	30.5	30.5	30.1	29.4	28.7	28.0	27.3	28.0
77.5°	23.1	23.8	24.5	24.2	23.5	23.1	23.1	22.9	22.2	21.5	22.2
80°	19.3	20.0	20.7	20.3	19.6	19.3	19.3	19.1	18.4	17.7	18.4
82.5°	15.4	15.6	15.7	15.6	15.5	15.4	15.4	15.2	14.5	13.8	14.5
85°	9.6	9.6	9.6	9.1	8.4	8.0	8.0	8.0	8.0	8.0	8.0
87.5°	3.1	4.5	6.0	6.5	6.5	6.4	6.4	6.6	6.8	6.8	6.8
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5
2.5°	3356.8	3348.1	3335.5	3335.2	3347.2	3357.2	3361.2	3365.2	3361.2	3357.2	3347.2
5°	3368.8	3354.4	3334.4	3331.2	3344.8	3356.2	3361.2	3366.2	3361.2	3356.2	3344.8
7.5°	3367.6	3357.1	3341.9	3339.6	3350.0	3358.4	3360.5	3362.6	3360.5	3358.4	3350.0
10°	3364.0	3352.8	3337.1	3336.7	3351.7	3362.8	3362.1	3361.3	3362.1	3362.8	3351.7
12.5°	3350.5	3342.5	3330.2	3335.0	3356.9	3371.8	3365.9	3360.1	3365.9	3371.8	3356.9
15°	3306.6	3308.4	3308.4	3323.7	3354.4	3374.5	3363.1	3351.7	3363.1	3374.5	3354.4
17.5°	3227.5	3238.0	3248.9	3274.9	3315.9	3343.2	3329.6	3316.1	3329.6	3343.2	3315.9
20°	3158.2	3172.5	3190.3	3223.1	3270.9	3303.4	3289.8	3276.3	3289.8	3303.4	3270.9
22.5°	3085.7	3101.8	3121.4	3156.8	3208.0	3242.7	3228.0	3213.3	3228.0	3242.7	3208.0
25°	2969.3	2982.0	2996.2	3029.4	3081.5	3117.7	3106.3	3094.9	3106.3	3117.7	3081.5
27.5°	2801.9	2816.9	2833.1	2865.7	2914.5	2949.5	2943.2	2936.9	2943.2	2949.5	2914.5
30°	2673.2	2693.6	2715.0	2744.9	2783.5	2811.6	2808.8	2805.9	2808.8	2811.6	2783.5
32.5°	2531.6	2550.2	2570.4	2597.5	2631.5	2656.3	2653.4	2650.6	2653.4	2656.3	2631.5
35°	2280.7	2301.9	2325.4	2347.6	2368.2	2384.1	2385.5	2387.0	2385.5	2384.1	2368.2
37.5°	1979.5	1997.0	2015.6	2033.0	2049.4	2061.3	2059.3	2057.3	2059.3	2061.3	2049.4
40°	1740.8	1762.0	1789.1	1809.4	1823.0	1832.8	1831.4	1830.0	1831.4	1832.8	1823.0
42.5°	1507.6	1527.4	1548.3	1568.0	1586.7	1595.4	1574.0	1552.6	1574.0	1595.4	1586.7
45°	1129.0	1164.9	1189.8	1202.3	1202.3	1186.1	1121.2	1056.2	1121.2	1186.1	1202.3
47.5°	665.3	741.7	815.9	833.0	792.9	744.3	670.4	596.5	670.4	744.3	792.9
50°	399.2	483.2	585.9	604.1	537.8	475.5	425.6	375.6	425.6	475.5	537.8
52.5°	281.7	350.5	437.2	445.7	375.9	317.3	291.9	266.5	291.9	317.3	375.9
55°	175.1	206.0	245.2	247.4	212.4	183.9	174.6	165.3	174.6	183.9	212.4
57.5°	117.5	130.0	143.7	143.7	130.0	117.4	107.8	98.2	107.8	117.4	130.0
60°	76.7	89.4	103.6	105.1	93.6	83.1	75.3	67.4	75.3	83.1	93.6
62.5°	61.3	70.5	81.9	82.8	73.1	65.0	61.7	58.4	61.7	65.0	73.1
65°	51.0	52.4	53.9	54.2	53.5	52.8	52.1	51.4	52.1	52.8	53.5
67.5°	44.9	45.4	45.5	45.9	46.4	46.7	46.0	45.3	46.0	46.7	46.4
70°	40.0	40.7	41.4	41.7	41.7	41.6	40.8	40.1	40.8	41.6	41.7
72.5°	36.0	36.4	36.5	36.9	37.5	37.7	37.0	36.3	37.0	37.7	37.5
75°	28.7	29.4	30.1	30.5	30.5	30.5	30.5	30.5	30.5	30.5	30.5
77.5°	22.9	23.1	23.1	23.5	24.2	24.5	23.8	23.1	23.8	24.5	24.2
80°	19.1	19.3	19.3	19.6	20.3	20.7	20.0	19.3	20.0	20.7	20.3
82.5°	15.2	15.4	15.4	15.5	15.6	15.7	15.6	15.4	15.6	15.7	15.6
85°	8.0	8.0	8.0	8.4	9.1	9.6	9.6	9.6	9.6	9.6	9.1
87.5°	6.6	6.4	6.4	6.5	6.5	6.0	4.5	3.1	4.5	5.8	6.9
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5
2.5°	3335.2	3335.5	3348.1	3356.8	3353.9	3351.1	3353.9	3356.8	3348.1	3335.5	3335.2
5°	3331.2	3334.4	3354.4	3368.8	3366.7	3364.6	3366.7	3368.8	3354.4	3334.4	3331.2
7.5°	3339.6	3341.9	3357.1	3367.6	3364.3	3361.0	3364.3	3367.6	3357.1	3341.9	3339.6
10°	3336.7	3337.1	3352.8	3364.0	3361.9	3359.7	3361.9	3364.0	3352.8	3337.1	3336.7
12.5°	3335.0	3330.2	3342.5	3350.5	3345.5	3340.5	3345.5	3350.5	3342.5	3330.2	3335.0
15°	3323.7	3308.4	3308.4	3306.6	3299.5	3292.3	3299.5	3306.6	3308.4	3308.4	3323.7
17.5°	3274.9	3248.9	3238.0	3227.5	3218.8	3210.1	3218.8	3227.5	3238.0	3248.9	3274.9
20°	3223.1	3190.3	3172.5	3158.2	3154.6	3151.1	3154.6	3158.2	3172.5	3190.3	3223.1
22.5°	3156.8	3121.4	3101.8	3085.7	3079.9	3074.0	3079.9	3085.7	3101.8	3121.4	3156.8
25°	3029.4	2996.2	2982.0	2969.3	2961.5	2953.6	2961.5	2969.3	2982.0	2996.2	3029.4
27.5°	2865.7	2833.1	2816.9	2801.9	2791.1	2780.3	2791.1	2801.9	2816.9	2833.1	2865.7
30°	2744.9	2715.0	2693.6	2673.2	2656.1	2639.0	2656.1	2673.2	2693.6	2715.0	2744.9
32.5°	2597.5	2570.4	2550.2	2531.6	2517.9	2504.2	2517.9	2531.6	2550.2	2570.4	2597.5
35°	2347.6	2325.4	2301.9	2280.7	2266.4	2252.1	2266.4	2280.7	2301.9	2325.4	2347.6
37.5°	2033.0	2015.6	1997.0	1979.5	1965.1	1950.7	1965.1	1979.5	1997.0	2015.6	2033.0
40°	1809.4	1789.1	1762.0	1740.8	1737.2	1733.6	1737.2	1740.8	1762.0	1789.1	1809.4
42.5°	1568.0	1548.3	1527.4	1507.6	1490.9	1474.2	1490.9	1507.6	1527.4	1548.3	1568.0
45°	1202.3	1189.8	1164.9	1129.0	1060.5	992.0	1060.5	1129.0	1164.9	1189.8	1202.3
47.5°	833.0	815.9	741.7	665.3	582.1	498.9	582.1	665.3	741.7	815.9	833.0
50°	604.1	585.9	483.2	399.2	371.3	343.5	371.3	399.2	483.2	585.9	604.1
52.5°	445.7	437.2	350.5	281.7	267.0	252.3	267.0	281.7	350.5	437.2	445.7
55°	247.4	245.2	206.0	175.1	169.4	163.7	169.4	175.1	206.0	245.2	247.4
57.5°	143.7	143.7	130.0	117.5	108.5	99.5	108.5	117.5	130.0	143.7	143.7
60°	105.1	103.6	89.4	76.7	68.8	61.0	68.8	76.7	89.4	103.6	105.1
62.5°	82.8	81.9	70.5	61.3	58.6	55.9	58.6	61.3	70.5	81.9	82.8
65°	54.2	53.9	52.4	51.0	49.6	48.2	49.6	51.0	52.4	53.9	54.2
67.5°	45.9	45.5	45.4	44.9	43.7	42.4	43.7	44.9	45.4	45.5	45.9
70°	41.7	41.4	40.7	40.0	39.2	38.5	39.2	40.0	40.7	41.4	41.7
72.5°	36.9	36.5	36.4	36.0	34.7	33.4	34.7	36.0	36.4	36.5	36.9
75°	30.5	30.1	29.4	28.7	28.0	27.3	28.0	28.7	29.4	30.1	30.5
77.5°	23.5	23.1	23.1	22.9	22.2	21.5	22.2	22.9	23.1	23.1	23.5
80°	19.6	19.3	19.3	19.1	18.4	17.7	18.4	19.1	19.3	19.3	19.6
82.5°	15.5	15.4	15.4	15.2	14.5	13.8	14.5	15.2	15.4	15.4	15.5
85°	8.4	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.4
87.5°	7.3	8.3	9.7	10.4	11.2	10.8	11.2	10.4	9.7	8.3	7.3
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	503.5	490.0	467.0	438.1
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	3348.5	3348.5	3348.5	3348.5
2.5°	3347.2	3357.2	3361.2	3365.2
5°	3344.8	3356.2	3361.2	3366.2
7.5°	3350.0	3358.4	3360.5	3362.6
10°	3351.7	3362.8	3362.1	3361.3
12.5°	3356.9	3371.8	3365.9	3360.1
15°	3354.4	3374.5	3363.1	3351.7
17.5°	3315.9	3343.2	3329.6	3316.1
20°	3270.9	3303.4	3289.8	3276.3
22.5°	3208.0	3242.7	3228.0	3213.3
25°	3081.5	3117.7	3106.3	3094.9
27.5°	2914.5	2949.5	2943.2	2936.9
30°	2783.5	2811.6	2808.8	2805.9
32.5°	2631.5	2656.3	2653.4	2650.6
35°	2368.2	2384.1	2385.5	2387.0
37.5°	2049.4	2061.3	2059.3	2057.3
40°	1823.0	1832.8	1831.4	1830.0
42.5°	1586.7	1595.4	1574.0	1552.6
45°	1202.3	1186.1	1121.2	1056.2
47.5°	792.9	744.3	670.4	596.5
50°	537.8	475.5	425.6	375.6
52.5°	375.9	317.3	291.9	266.5
55°	212.4	183.9	174.6	165.3
57.5°	130.0	117.4	107.8	98.2
60°	93.6	83.1	75.3	67.4
62.5°	73.1	65.0	61.7	58.4
65°	53.5	52.8	52.1	51.4
67.5°	46.4	46.7	46.0	45.3
70°	41.7	41.6	40.8	40.1
72.5°	37.5	37.7	37.0	36.3
75°	30.5	30.5	30.5	30.5
77.5°	24.2	24.5	23.8	23.1
80°	20.3	20.7	20.0	19.3
82.5°	15.6	15.7	15.6	15.4
85°	9.1	9.6	9.6	9.6
87.5°	6.9	5.8	4.5	3.1
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7



TEST NUMBER: P1428536

CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1428536
 CATALOG NUMBER: SQ2W-WBM-K-075U-125D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.18	7.99	8.03	8.83	9.88	7.16	7.97	8.01	8.82	9.86
	3H	7.87	8.59	8.73	9.44	10.52	7.79	8.51	8.65	9.36	10.44
	4H	8.24	8.91	9.12	9.77	10.86	8.10	8.77	8.98	9.63	10.72
	6H	8.51	9.13	9.40	10.00	11.09	8.33	8.95	9.22	9.82	10.91
	8H	8.63	9.22	9.53	10.10	11.20	8.43	9.01	9.33	9.90	11.00
	12H	8.71	9.27	9.61	10.14	11.26	8.48	9.04	9.38	9.91	11.03
4H	2H	7.28	7.95	8.16	8.81	9.90	7.26	7.94	8.15	8.80	9.88
	3H	8.23	8.78	9.12	9.67	10.77	8.14	8.69	9.03	9.59	10.68
	4H	8.73	9.23	9.63	10.12	11.25	8.58	9.08	9.48	9.97	11.10
	6H	9.16	9.59	10.08	10.50	11.63	8.96	9.39	9.88	10.30	11.43
	8H	9.35	9.75	10.27	10.65	11.80	9.12	9.52	10.04	10.43	11.57
	12H	9.48	9.83	10.41	10.76	11.90	9.22	9.57	10.15	10.50	11.64
8H	4H	8.85	9.25	9.77	10.16	11.30	8.71	9.11	9.63	10.02	11.16
	6H	9.42	9.75	10.37	10.70	11.84	9.23	9.56	10.17	10.51	11.65
	8H	9.71	10.00	10.67	10.95	12.10	9.50	9.79	10.45	10.73	11.89
	12H	9.93	10.19	10.88	11.12	12.33	9.67	9.92	10.62	10.85	12.06
12H	4H	8.83	9.19	9.76	10.11	11.26	8.70	9.06	9.63	9.98	11.13
	6H	9.46	9.75	10.41	10.69	11.85	9.28	9.56	10.23	10.51	11.67
	8H	9.79	10.04	10.74	10.97	12.18	9.58	9.83	10.53	10.77	11.98