

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427900

Luminaire Tested: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427900
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6005.5 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46				
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	66	60	76	68	61	56	58	54	50	50	46	43	42	39	37	33				
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28				
5	69	58	49	43	64	54	47	41	47	41	37	40	35	32	34	30	28	25				
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22				
7	59	47	39	33	55	44	37	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17				
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	15				
10	48	36	28	24	44	33	27	22	29	24	20	26	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23543	23543	23543	23543
5°	23679	21520	23679	21520
10°	23134	19562	23134	19562
15°	23237	19179	23237	19179
20°	22408	19333	22408	19333
25°	21998	18884	21998	18884
30°	21522	19039	21522	19039
35°	21358	22316	21358	22316
40°	21376	17692	21376	17692
45°	21383	15239	21383	15239
50°	21084	14290	21084	14290
55°	20816	13709	20816	13709
60°	20608	12858	20608	12858
65°	20248	11186	20248	11186
70°	19123	7992	19123	7992
75°	17049	6057	17049	6057
80°	13928	5672	13928	5672
85°	8744	3853	8744	3853

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21383 cd/sqm



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	2.1
10°-20°	337.5	5.6
20°-30°	494.8	8.2
30°-40°	599.2	10.0
40°-50°	589.2	9.8
50°-60°	512.5	8.5
60°-70°	356.4	5.9
70°-80°	169.0	2.8
80°-90°	41.2	0.7
90°-100°	75.7	1.3
100°-110°	220.8	3.7
110°-120°	360.3	6.0
120°-130°	457.2	7.6
130°-140°	489.2	8.1
140°-150°	456.8	7.6
150°-160°	375.9	6.3
160°-170°	252.1	4.2
170°-180°	89.5	1.5
0°-30°	960.6	16.0
0°-40°	1559.8	26.0
0°-60°	2661.5	44.3
0°-90°	3228.2	53.8
90°-120°	656.7	10.9
90°-150°	2059.9	34.3
90°-180°	2777.0	46.2
0°-180°	6005.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1458	1458	1458	1458	1458	
5°	1461	1328	1461	1328	1461	137
15°	1390	1147	1390	1147	1390	388
25°	1235	1060	1235	1060	1235	568
35°	1084	1132	1084	1132	1084	679
45°	936	667	936	667	936	720
55°	740	487	740	487	740	661
65°	530	293	530	293	530	521
75°	273	97	273	97	273	290
85°	47	21	47	21	47	63
90°	3	21	3	41	3	4
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1454.9	1461.8	1468.7	1459.0	1443.7	1433.1	1427.2	1422.5	1421.5	1420.5	1421.5
5°	1461.0	1460.4	1459.8	1430.9	1392.7	1364.0	1344.9	1330.3	1329.0	1327.8	1329.0
7.5°	1434.4	1415.2	1396.1	1357.4	1312.1	1279.0	1257.9	1241.8	1240.8	1239.8	1240.8
10°	1411.1	1382.1	1353.1	1309.3	1260.6	1226.7	1207.6	1193.2	1193.2	1193.2	1193.2
12.5°	1405.5	1359.8	1314.0	1266.0	1217.3	1185.9	1171.7	1161.8	1164.7	1167.7	1164.7
15°	1390.2	1321.2	1252.1	1203.4	1161.5	1138.7	1135.0	1133.9	1140.7	1147.4	1140.7
17.5°	1339.7	1265.4	1191.0	1148.2	1115.9	1103.7	1111.5	1119.4	1127.3	1135.2	1127.3
20°	1304.2	1230.8	1157.5	1117.8	1089.5	1082.7	1097.5	1110.4	1117.8	1125.2	1117.8
22.5°	1274.3	1199.9	1125.5	1090.5	1068.5	1065.7	1081.9	1095.1	1099.1	1103.0	1099.1
25°	1234.8	1151.0	1067.1	1041.5	1035.4	1039.4	1053.6	1063.7	1061.9	1060.0	1061.9
27.5°	1187.7	1100.1	1012.5	996.1	1003.4	1011.3	1020.0	1026.7	1027.8	1028.9	1027.8
30°	1154.4	1066.8	979.2	966.1	977.9	988.0	996.7	1005.1	1013.2	1021.2	1013.2
32.5°	1122.2	1031.7	941.1	931.7	949.4	968.4	988.9	1008.8	1027.2	1045.6	1027.2
35°	1083.6	989.3	894.9	887.5	909.1	936.9	970.8	1011.3	1071.7	1132.2	1071.7
37.5°	1043.1	942.0	840.8	837.5	866.7	895.9	925.2	951.9	971.1	990.4	971.1
40°	1014.2	908.2	802.1	802.0	837.1	873.5	911.1	928.2	883.8	839.4	883.8
42.5°	983.2	877.1	771.0	767.9	799.1	839.2	888.2	906.1	831.2	756.2	831.2
45°	936.5	826.2	715.8	711.8	743.2	765.4	778.4	774.7	721.0	667.4	721.0
47.5°	881.6	776.4	671.2	670.3	704.2	706.7	677.7	650.8	629.8	608.8	629.8
50°	839.4	740.1	640.9	645.2	684.0	680.3	634.1	596.0	582.4	568.9	582.4
52.5°	798.4	704.0	609.7	621.1	667.9	660.5	598.9	550.5	541.4	532.2	541.4
55°	739.5	648.9	558.2	584.1	648.9	639.0	554.5	490.7	488.9	487.0	488.9
57.5°	677.1	591.4	505.7	523.6	576.2	565.8	492.6	438.4	441.6	444.8	441.6
60°	638.2	555.0	471.7	474.1	504.9	495.0	444.5	405.6	401.9	398.2	401.9
62.5°	597.2	517.9	438.6	427.1	438.2	426.6	392.3	365.6	361.9	358.2	361.9
65°	530.0	457.9	385.7	364.0	359.0	342.4	314.0	292.8	292.8	292.8	292.8
67.5°	456.2	393.3	330.4	306.1	294.6	278.1	256.5	236.6	221.8	207.0	221.8
70°	405.1	349.6	294.1	268.7	253.3	233.6	209.5	189.0	179.1	169.3	179.1
72.5°	350.8	303.1	255.5	229.5	210.6	191.4	171.8	154.2	142.9	131.5	142.9
75°	273.3	235.1	196.9	171.6	150.6	131.2	113.3	99.6	98.4	97.1	98.4
77.5°	197.6	169.7	141.8	121.4	103.4	89.8	80.8	74.1	74.2	74.4	74.2
80°	149.8	128.9	107.9	88.8	70.3	60.7	60.1	59.8	60.4	61.0	60.4
82.5°	105.4	89.9	74.4	62.2	51.1	45.9	46.8	47.5	47.6	47.7	47.6
85°	47.2	39.8	32.4	29.6	28.4	26.5	24.0	22.0	21.4	20.8	21.4
87.5°	10.6	10.8	11.3	10.8	9.9	9.4	9.4	9.6	9.8	9.8	9.8
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1422.5	1427.2	1433.1	1443.7	1459.0	1468.7	1461.8	1454.9	1461.8	1468.7	1459.0
5°	1330.3	1344.9	1364.0	1392.7	1430.9	1459.8	1460.4	1461.0	1460.4	1459.8	1430.9
7.5°	1241.8	1257.9	1279.0	1312.1	1357.4	1396.1	1415.2	1434.4	1415.2	1396.1	1357.4
10°	1193.2	1207.6	1226.7	1260.6	1309.3	1353.1	1382.1	1411.1	1382.1	1353.1	1309.3
12.5°	1161.8	1171.7	1185.9	1217.3	1266.0	1314.0	1359.8	1405.5	1359.8	1314.0	1266.0
15°	1133.9	1135.0	1138.7	1161.5	1203.4	1252.1	1321.2	1390.2	1321.2	1252.1	1203.4
17.5°	1119.4	1111.5	1103.7	1115.9	1148.2	1191.0	1265.4	1339.7	1265.4	1191.0	1148.2
20°	1110.4	1097.5	1082.7	1089.5	1117.8	1157.5	1230.8	1304.2	1230.8	1157.5	1117.8
22.5°	1095.1	1081.9	1065.7	1068.5	1090.5	1125.5	1199.9	1274.3	1199.9	1125.5	1090.5
25°	1063.7	1053.6	1039.4	1035.4	1041.5	1067.1	1151.0	1234.8	1151.0	1067.1	1041.5
27.5°	1026.7	1020.0	1011.3	1003.4	996.1	1012.5	1100.1	1187.7	1100.1	1012.5	996.1
30°	1005.1	996.7	988.0	977.9	966.1	979.2	1066.8	1154.4	1066.8	979.2	966.1
32.5°	1008.8	988.9	968.4	949.4	931.7	941.1	1031.7	1122.2	1031.7	941.1	931.7
35°	1011.3	970.8	936.9	909.1	887.5	894.9	989.3	1083.6	989.3	894.9	887.5
37.5°	951.9	925.2	895.9	866.7	837.5	840.8	942.0	1043.1	942.0	840.8	837.5
40°	928.2	911.1	873.5	837.1	802.0	802.1	908.2	1014.2	908.2	802.1	802.0
42.5°	906.1	888.2	839.2	799.1	767.9	771.0	877.1	983.2	877.1	771.0	767.9
45°	774.7	778.4	765.4	743.2	711.8	715.8	826.2	936.5	826.2	715.8	711.8
47.5°	650.8	677.7	706.7	704.2	670.3	671.2	776.4	881.6	776.4	671.2	670.3
50°	596.0	634.1	680.3	684.0	645.2	640.9	740.1	839.4	740.1	640.9	645.2
52.5°	550.5	598.9	660.5	667.9	621.1	609.7	704.0	798.4	704.0	609.7	621.1
55°	490.7	554.5	639.0	648.9	584.1	558.2	648.9	739.5	648.9	558.2	584.1
57.5°	438.4	492.6	565.8	576.2	523.6	505.7	591.4	677.1	591.4	505.7	523.6
60°	405.6	444.5	495.0	504.9	474.1	471.7	555.0	638.2	555.0	471.7	474.1
62.5°	365.6	392.3	426.6	438.2	427.1	438.6	517.9	597.2	517.9	438.6	427.1
65°	292.8	314.0	342.4	359.0	364.0	385.7	457.9	530.0	457.9	385.7	364.0
67.5°	236.6	256.5	278.1	294.6	306.1	330.4	393.3	456.2	393.3	330.4	306.1
70°	189.0	209.5	233.6	253.3	268.7	294.1	349.6	405.1	349.6	294.1	268.7
72.5°	154.2	171.8	191.4	210.6	229.5	255.5	303.1	350.8	303.1	255.5	229.5
75°	99.6	113.3	131.2	150.6	171.6	196.9	235.1	273.3	235.1	196.9	171.6
77.5°	74.1	80.8	89.8	103.4	121.4	141.8	169.7	197.6	169.7	141.8	121.4
80°	59.8	60.1	60.7	70.3	88.8	107.9	128.9	149.8	128.9	107.9	88.8
82.5°	47.5	46.8	45.9	51.1	62.2	74.4	89.9	105.4	89.9	74.4	62.2
85°	22.0	24.0	26.5	28.4	29.6	32.4	39.8	47.2	39.8	32.4	29.6
87.5°	9.6	9.4	9.4	9.9	10.8	11.3	10.8	10.6	10.8	11.1	11.2
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1443.7	1433.1	1427.2	1422.5	1421.5	1420.5	1421.5	1422.5	1427.2	1433.1	1443.7
5°	1392.7	1364.0	1344.9	1330.3	1329.0	1327.8	1329.0	1330.3	1344.9	1364.0	1392.7
7.5°	1312.1	1279.0	1257.9	1241.8	1240.8	1239.8	1240.8	1241.8	1257.9	1279.0	1312.1
10°	1260.6	1226.7	1207.6	1193.2	1193.2	1193.2	1193.2	1193.2	1207.6	1226.7	1260.6
12.5°	1217.3	1185.9	1171.7	1161.8	1164.7	1167.7	1164.7	1161.8	1171.7	1185.9	1217.3
15°	1161.5	1138.7	1135.0	1133.9	1140.7	1147.4	1140.7	1133.9	1135.0	1138.7	1161.5
17.5°	1115.9	1103.7	1111.5	1119.4	1127.3	1135.2	1127.3	1119.4	1111.5	1103.7	1115.9
20°	1089.5	1082.7	1097.5	1110.4	1117.8	1125.2	1117.8	1110.4	1097.5	1082.7	1089.5
22.5°	1068.5	1065.7	1081.9	1095.1	1099.1	1103.0	1099.1	1095.1	1081.9	1065.7	1068.5
25°	1035.4	1039.4	1053.6	1063.7	1061.9	1060.0	1061.9	1063.7	1053.6	1039.4	1035.4
27.5°	1003.4	1011.3	1020.0	1026.7	1027.8	1028.9	1027.8	1026.7	1020.0	1011.3	1003.4
30°	977.9	988.0	996.7	1005.1	1013.2	1021.2	1013.2	1005.1	996.7	988.0	977.9
32.5°	949.4	968.4	988.9	1008.8	1027.2	1045.6	1027.2	1008.8	988.9	968.4	949.4
35°	909.1	936.9	970.8	1011.3	1071.7	1132.2	1071.7	1011.3	970.8	936.9	909.1
37.5°	866.7	895.9	925.2	951.9	971.1	990.4	971.1	951.9	925.2	895.9	866.7
40°	837.1	873.5	911.1	928.2	883.8	839.4	883.8	928.2	911.1	873.5	837.1
42.5°	799.1	839.2	888.2	906.1	831.2	756.2	831.2	906.1	888.2	839.2	799.1
45°	743.2	765.4	778.4	774.7	721.0	667.4	721.0	774.7	778.4	765.4	743.2
47.5°	704.2	706.7	677.7	650.8	629.8	608.8	629.8	650.8	677.7	706.7	704.2
50°	684.0	680.3	634.1	596.0	582.4	568.9	582.4	596.0	634.1	680.3	684.0
52.5°	667.9	660.5	598.9	550.5	541.4	532.2	541.4	550.5	598.9	660.5	667.9
55°	648.9	639.0	554.5	490.7	488.9	487.0	488.9	490.7	554.5	639.0	648.9
57.5°	576.2	565.8	492.6	438.4	441.6	444.8	441.6	438.4	492.6	565.8	576.2
60°	504.9	495.0	444.5	405.6	401.9	398.2	401.9	405.6	444.5	495.0	504.9
62.5°	438.2	426.6	392.3	365.6	361.9	358.2	361.9	365.6	392.3	426.6	438.2
65°	359.0	342.4	314.0	292.8	292.8	292.8	292.8	292.8	314.0	342.4	359.0
67.5°	294.6	278.1	256.5	236.6	221.8	207.0	221.8	236.6	256.5	278.1	294.6
70°	253.3	233.6	209.5	189.0	179.1	169.3	179.1	189.0	209.5	233.6	253.3
72.5°	210.6	191.4	171.8	154.2	142.9	131.5	142.9	154.2	171.8	191.4	210.6
75°	150.6	131.2	113.3	99.6	98.4	97.1	98.4	99.6	113.3	131.2	150.6
77.5°	103.4	89.8	80.8	74.1	74.2	74.4	74.2	74.1	80.8	89.8	103.4
80°	70.3	60.7	60.1	59.8	60.4	61.0	60.4	59.8	60.1	60.7	70.3
82.5°	51.1	45.9	46.8	47.5	47.6	47.7	47.6	47.5	46.8	45.9	51.1
85°	28.4	26.5	24.0	22.0	21.4	20.8	21.4	22.0	24.0	26.5	28.4
87.5°	10.7	11.3	12.7	13.4	14.2	13.8	14.2	13.4	12.7	11.3	10.7
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	503.5	490.0	467.0	438.1
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1458.2	1458.2	1458.2	1458.2
2.5°	1459.0	1468.7	1461.8	1454.9
5°	1430.9	1459.8	1460.4	1461.0
7.5°	1357.4	1396.1	1415.2	1434.4
10°	1309.3	1353.1	1382.1	1411.1
12.5°	1266.0	1314.0	1359.8	1405.5
15°	1203.4	1252.1	1321.2	1390.2
17.5°	1148.2	1191.0	1265.4	1339.7
20°	1117.8	1157.5	1230.8	1304.2
22.5°	1090.5	1125.5	1199.9	1274.3
25°	1041.5	1067.1	1151.0	1234.8
27.5°	996.1	1012.5	1100.1	1187.7
30°	966.1	979.2	1066.8	1154.4
32.5°	931.7	941.1	1031.7	1122.2
35°	887.5	894.9	989.3	1083.6
37.5°	837.5	840.8	942.0	1043.1
40°	802.0	802.1	908.2	1014.2
42.5°	767.9	771.0	877.1	983.2
45°	711.8	715.8	826.2	936.5
47.5°	670.3	671.2	776.4	881.6
50°	645.2	640.9	740.1	839.4
52.5°	621.1	609.7	704.0	798.4
55°	584.1	558.2	648.9	739.5
57.5°	523.6	505.7	591.4	677.1
60°	474.1	471.7	555.0	638.2
62.5°	427.1	438.6	517.9	597.2
65°	364.0	385.7	457.9	530.0
67.5°	306.1	330.4	393.3	456.2
70°	268.7	294.1	349.6	405.1
72.5°	229.5	255.5	303.1	350.8
75°	171.6	196.9	235.1	273.3
77.5°	121.4	141.8	169.7	197.6
80°	88.8	107.9	128.9	149.8
82.5°	62.2	74.4	89.9	105.4
85°	29.6	32.4	39.8	47.2
87.5°	11.2	11.1	10.8	10.6
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7



TEST NUMBER: P1427900

CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1427900
 CATALOG NUMBER: SQ2W-PH1-K-075U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.19	19.08	19.12	20.02	21.24	17.02	17.91	17.95	18.85	20.07
	3H	20.37	21.16	21.31	22.12	23.36	18.07	18.87	19.01	19.82	21.06
	4H	21.18	21.94	22.14	22.89	24.14	18.32	19.07	19.27	20.03	21.28
	6H	21.65	22.34	22.62	23.31	24.57	18.46	19.15	19.42	20.12	21.38
	8H	21.80	22.46	22.78	23.44	24.70	18.52	19.18	19.49	20.16	21.42
	12H	21.86	22.49	22.84	23.46	24.75	18.53	19.16	19.51	20.13	21.42
4H	2H	18.63	19.38	19.59	20.34	21.59	17.71	18.46	18.67	19.42	20.67
	3H	20.88	21.51	21.85	22.50	23.76	18.94	19.57	19.91	20.55	21.82
	4H	21.76	22.33	22.74	23.31	24.60	19.23	19.80	20.21	20.78	22.07
	6H	22.32	22.81	23.31	23.82	25.10	19.43	19.92	20.42	20.93	22.21
	8H	22.52	22.98	23.51	23.98	25.28	19.52	19.98	20.51	20.98	22.28
	12H	22.61	23.02	23.62	24.04	25.34	19.55	19.96	20.56	20.97	22.28
8H	4H	21.78	22.24	22.77	23.24	24.54	19.46	19.92	20.45	20.92	22.22
	6H	22.41	22.79	23.43	23.83	25.13	19.73	20.11	20.75	21.15	22.45
	8H	22.68	23.01	23.70	24.04	25.36	19.88	20.21	20.90	21.24	22.56
	12H	22.81	23.10	23.84	24.12	25.49	19.94	20.24	20.97	21.26	22.62
12H	4H	21.74	22.15	22.75	23.16	24.47	19.46	19.87	20.47	20.89	22.19
	6H	22.39	22.72	23.42	23.75	25.07	19.77	20.10	20.79	21.13	22.45
	8H	22.66	22.96	23.69	23.98	25.34	19.93	20.22	20.96	21.24	22.61