

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428626

Luminaire Tested: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428626  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6874.3 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	99	95	92	89	91	88	85	83	74	72	71	61	60	59	49	49	48	43				
2	92	86	81	77	85	80	76	72	68	65	62	57	55	53	46	45	44	40				
3	86	78	72	67	79	73	68	63	62	59	56	53	50	48	44	42	41	37				
4	80	71	65	60	74	66	61	57	57	53	50	49	46	44	41	39	38	34				
5	75	65	58	54	69	61	55	51	53	49	46	46	43	40	39	37	35	32				
6	70	60	53	48	65	56	50	46	49	45	42	43	40	37	37	34	33	30				
7	66	55	49	44	61	52	46	42	46	42	38	40	37	35	35	32	31	28				
8	62	51	45	40	58	49	43	39	43	39	35	38	35	32	33	31	29	27				
9	58	48	42	37	54	45	40	36	40	36	33	36	32	30	31	29	27	25				
10	55	45	39	35	51	42	37	33	38	34	31	34	30	28	30	27	26	24				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	87598	87598	87598	87598
5°	84577	84671	84577	84671
10°	73105	73279	73105	73279
15°	58174	56566	58174	56566
20°	41326	41078	41326	41078
25°	29731	28943	29731	28943
30°	22717	22053	22717	22053
35°	17832	17073	17832	17073
40°	13510	12678	13510	12678
45°	7560	6747	7560	6747
50°	2660	2346	2660	2346
55°	1624	1545	1624	1545
60°	1243	1150	1243	1150
65°	1138	1066	1138	1066
70°	1090	1001	1090	1001
75°	1023	961	1023	961
80°	893	893	893	893
85°	889	704	889	704

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 8964 cd/sqm



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	471.0	6.9
10°-20°	936.0	13.6
20°-30°	775.2	11.3
30°-40°	557.6	8.1
40°-50°	284.1	4.1
50°-60°	73.9	1.1
60°-70°	30.7	0.4
70°-80°	17.0	0.2
80°-90°	10.3	0.2
90°-100°	101.4	1.5
100°-110°	295.6	4.3
110°-120°	482.4	7.0
120°-130°	612.1	8.9
130°-140°	655.0	9.5
140°-150°	611.6	8.9
150°-160°	503.3	7.3
160°-170°	337.5	4.9
170°-180°	119.8	1.7
0°-30°	2182.1	31.7
0°-40°	2739.8	39.9
0°-60°	3097.7	45.1
0°-90°	3155.7	45.9
90°-120°	879.3	12.8
90°-150°	2758.0	40.1
90°-180°	3719.0	54.1
0°-180°	6874.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	5426	5426	5426	5426	5426	
5°	5218	5224	5218	5224	5218	471
15°	3480	3384	3480	3384	3480	945
25°	1669	1625	1669	1625	1669	785
35°	905	866	905	866	905	568
45°	331	296	331	296	331	265
55°	58	55	58	55	58	57
65°	30	28	30	28	30	30
75°	16	15	16	15	16	17
85°	5	4	5	4	5	5
90°	4	28	4	55	4	3
95°	40	30	40	174	40	48
105°	188	301	188	414	188	200
115°	360	499	360	615	360	355
125°	533	791	533	754	533	477
135°	724	1036	724	835	724	560
145°	925	1194	925	853	925	579
155°	1099	1297	1099	885	1099	505
165°	1214	1352	1214	1019	1214	342
175°	1270	1324	1270	1195	1270	120
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5
2.5°	5417.0	5412.9	5408.8	5390.6	5367.6	5365.8	5384.9	5398.1	5393.3	5388.5	5393.3
5°	5218.5	5215.1	5211.7	5196.1	5176.4	5183.3	5216.6	5239.7	5232.0	5224.3	5232.0
7.5°	4808.7	4811.6	4814.5	4806.5	4794.9	4803.8	4833.4	4853.4	4845.2	4837.0	4845.2
10°	4459.1	4466.8	4474.5	4463.6	4446.5	4459.6	4502.8	4527.9	4498.8	4469.7	4498.8
12.5°	4073.4	4068.4	4063.5	4053.5	4041.9	4039.5	4046.4	4047.6	4031.5	4015.4	4031.5
15°	3480.3	3462.3	3444.4	3416.8	3386.0	3375.9	3386.6	3393.5	3388.8	3384.1	3388.8
17.5°	2803.3	2810.2	2817.2	2798.5	2771.3	2757.2	2756.1	2754.0	2748.7	2743.4	2748.7
20°	2405.2	2407.4	2409.5	2397.8	2381.6	2377.7	2386.3	2392.5	2391.6	2390.8	2391.6
22.5°	2084.9	2085.3	2085.8	2070.3	2049.6	2045.6	2058.3	2065.9	2058.2	2050.5	2058.2
25°	1668.9	1667.6	1666.4	1656.1	1642.8	1633.0	1626.6	1622.1	1623.4	1624.7	1623.4
27.5°	1368.6	1363.3	1358.0	1349.3	1339.3	1336.5	1340.8	1343.2	1340.0	1336.9	1340.0
30°	1218.5	1214.2	1209.9	1201.2	1190.9	1187.1	1189.6	1190.6	1186.7	1182.9	1186.7
32.5°	1083.7	1083.9	1084.1	1076.2	1065.6	1059.7	1058.5	1056.9	1054.0	1051.2	1054.0
35°	904.7	907.3	909.9	903.4	894.0	886.1	879.7	873.9	870.1	866.2	870.1
37.5°	745.0	747.4	749.7	744.4	736.4	727.7	718.3	710.5	707.2	704.0	707.2
40°	641.0	642.7	644.4	640.7	635.1	626.8	615.7	606.7	604.1	601.5	604.1
42.5°	527.8	535.0	542.2	539.8	534.3	526.3	515.8	506.6	500.9	495.3	500.9
45°	331.1	353.8	376.4	386.6	392.6	389.8	378.3	361.4	328.4	295.5	328.4
47.5°	167.5	198.9	230.3	252.8	272.4	266.2	234.1	201.9	169.6	137.2	169.6
50°	105.9	127.7	149.5	177.1	206.6	200.2	157.8	122.4	107.9	93.4	107.9
52.5°	81.2	92.4	103.6	129.9	161.1	158.1	120.9	91.0	82.9	74.9	82.9
55°	57.7	62.0	66.3	80.8	98.8	97.7	77.6	61.7	58.3	54.9	58.3
57.5°	44.7	47.1	49.4	54.9	61.3	60.7	53.1	46.8	44.7	42.5	44.7
60°	38.5	40.2	41.9	44.6	47.6	47.2	43.3	39.9	37.8	35.6	37.8
62.5°	34.6	35.7	36.7	37.9	39.2	38.6	36.1	34.1	33.3	32.5	33.3
65°	29.8	30.3	30.7	30.8	30.8	30.4	29.5	28.8	28.3	27.9	28.3
67.5°	25.4	25.8	26.3	26.3	26.2	26.0	25.5	25.1	24.7	24.3	24.7
70°	23.1	23.5	24.0	23.7	23.3	22.9	22.5	22.0	21.6	21.2	21.6
72.5°	20.0	20.4	20.9	20.7	20.2	20.0	19.9	19.7	19.3	18.9	19.3
75°	16.4	16.4	16.4	16.4	16.4	16.1	15.7	15.4	15.4	15.4	15.4
77.5°	12.7	12.8	12.9	12.6	12.1	11.9	11.9	11.8	11.5	11.2	11.5
80°	9.6	10.1	10.5	10.3	9.8	9.6	9.6	9.6	9.6	9.6	9.6
82.5°	8.1	8.2	8.3	8.0	7.5	7.3	7.3	7.3	7.3	7.3	7.3
85°	4.8	4.8	4.8	4.5	4.1	4.1	4.5	4.7	4.3	3.8	4.3
87.5°	2.3	3.3	4.6	5.7	6.4	6.7	6.7	6.9	7.2	7.2	7.2
90°	3.9	9.0	15.4	20.6	24.4	25.7	25.7	27.0	28.3	28.3	28.3
92.5°	14.2	22.4	22.6	22.6	27.5	29.8	31.9	32.2	33.4	33.4	33.4
95°	39.9	43.7	65.6	64.3	43.7	34.7	29.6	29.6	29.6	29.6	29.6
97.5°	76.2	81.8	85.4	114.5	120.9	116.8	95.2	80.0	71.5	67.7	71.5
100°	108.1	110.6	118.4	119.6	151.8	182.7	167.2	147.9	141.5	137.6	141.5
102.5°	140.0	141.5	153.3	158.7	166.2	183.7	237.2	231.3	226.9	226.2	226.9
105°	187.8	189.1	211.0	221.3	226.4	226.4	225.1	250.9	292.0	301.0	292.0
107.5°	239.0	244.9	270.7	298.2	304.1	305.7	299.0	295.1	293.6	294.6	293.6
110°	274.0	283.0	313.9	348.6	357.6	360.2	357.6	353.8	351.2	351.2	351.2



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	308.0	321.1	356.1	396.0	411.1	418.9	413.2	410.4	407.8	409.9	407.8
115°	360.2	379.5	425.8	467.0	497.9	501.7	500.4	500.4	499.1	499.1	499.1
117.5°	408.6	439.5	491.4	539.3	575.0	585.3	590.5	588.9	587.4	590.0	587.4
120°	442.5	478.6	537.7	591.8	626.5	641.9	647.1	644.5	647.1	644.5	647.1
122.5°	478.6	522.8	581.0	637.0	678.0	695.5	701.6	702.1	702.7	701.1	702.7
125°	532.6	586.6	654.8	712.7	755.1	775.7	780.9	782.2	784.7	791.2	784.7
127.5°	587.1	648.4	723.2	779.1	822.6	847.5	855.5	858.3	863.7	866.6	863.7
130°	625.2	694.7	770.6	823.3	865.8	892.8	906.9	910.8	917.2	916.0	917.2
132.5°	665.4	737.9	814.8	869.6	909.0	938.1	950.2	961.2	963.5	965.4	963.5
135°	724.3	802.7	879.9	934.0	971.3	999.6	1015.0	1025.3	1031.7	1035.6	1031.7
137.5°	786.3	869.1	943.2	991.3	1028.9	1053.3	1070.8	1081.6	1088.3	1091.4	1088.3
140°	828.5	908.2	980.3	1030.4	1063.9	1088.3	1103.8	1116.6	1124.4	1124.4	1124.4
142.5°	868.6	947.3	1017.3	1067.5	1096.8	1119.2	1135.7	1145.5	1154.2	1154.2	1154.2
145°	925.0	1003.4	1067.8	1117.9	1142.4	1162.9	1181.0	1188.7	1193.8	1193.8	1193.8
147.5°	983.9	1053.3	1112.0	1160.1	1180.7	1204.9	1219.0	1225.2	1231.6	1228.8	1231.6
150°	1018.9	1083.2	1139.8	1184.8	1205.4	1228.6	1242.7	1247.9	1254.3	1250.4	1254.3
152.5°	1052.8	1114.1	1165.5	1207.5	1225.0	1248.1	1264.3	1269.5	1273.8	1271.0	1273.8
155°	1098.6	1152.7	1200.3	1238.8	1254.3	1276.2	1291.6	1298.0	1303.2	1296.7	1303.2
157.5°	1139.5	1186.1	1227.5	1263.0	1279.5	1298.3	1312.7	1320.7	1325.8	1323.0	1325.8
160°	1164.2	1206.7	1244.0	1277.4	1292.9	1309.6	1325.0	1334.0	1339.2	1335.3	1339.2
162.5°	1184.8	1223.2	1258.4	1288.8	1302.1	1316.8	1335.3	1343.3	1348.5	1343.6	1348.5
165°	1214.4	1245.3	1276.2	1301.9	1313.5	1325.0	1344.3	1353.3	1357.2	1352.1	1357.2
167.5°	1236.8	1260.5	1285.4	1307.5	1316.0	1327.4	1346.7	1354.1	1359.0	1352.6	1359.0
170°	1249.1	1269.7	1291.6	1309.6	1316.0	1326.3	1345.6	1352.1	1355.9	1349.5	1355.9
172.5°	1259.4	1274.9	1292.6	1308.6	1311.9	1320.2	1338.4	1344.9	1347.7	1342.3	1347.7
175°	1269.7	1278.7	1291.6	1301.9	1300.6	1305.7	1321.2	1326.3	1331.5	1323.8	1331.5
177.5°	1274.6	1278.7	1282.8	1289.0	1284.9	1284.9	1296.2	1299.3	1300.3	1296.2	1300.3
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5
2.5°	5398.1	5384.9	5365.8	5367.6	5390.6	5408.8	5412.9	5417.0	5412.9	5408.8	5390.6
5°	5239.7	5216.6	5183.3	5176.4	5196.1	5211.7	5215.1	5218.5	5215.1	5211.7	5196.1
7.5°	4853.4	4833.4	4803.8	4794.9	4806.5	4814.5	4811.6	4808.7	4811.6	4814.5	4806.5
10°	4527.9	4502.8	4459.6	4446.5	4463.6	4474.5	4466.8	4459.1	4466.8	4474.5	4463.6
12.5°	4047.6	4046.4	4039.5	4041.9	4053.5	4063.5	4068.4	4073.4	4068.4	4063.5	4053.5
15°	3393.5	3386.6	3375.9	3386.0	3416.8	3444.4	3462.3	3480.3	3462.3	3444.4	3416.8
17.5°	2754.0	2756.1	2757.2	2771.3	2798.5	2817.2	2810.2	2803.3	2810.2	2817.2	2798.5
20°	2392.5	2386.3	2377.7	2381.6	2397.8	2409.5	2407.4	2405.2	2407.4	2409.5	2397.8
22.5°	2065.9	2058.3	2045.6	2049.6	2070.3	2085.8	2085.3	2084.9	2085.3	2085.8	2070.3
25°	1622.1	1626.6	1633.0	1642.8	1656.1	1666.4	1667.6	1668.9	1667.6	1666.4	1656.1
27.5°	1343.2	1340.8	1336.5	1339.3	1349.3	1358.0	1363.3	1368.6	1363.3	1358.0	1349.3
30°	1190.6	1189.6	1187.1	1190.9	1201.2	1209.9	1214.2	1218.5	1214.2	1209.9	1201.2
32.5°	1056.9	1058.5	1059.7	1065.6	1076.2	1084.1	1083.9	1083.7	1083.9	1084.1	1076.2
35°	873.9	879.7	886.1	894.0	903.4	909.9	907.3	904.7	907.3	909.9	903.4
37.5°	710.5	718.3	727.7	736.4	744.4	749.7	747.4	745.0	747.4	749.7	744.4
40°	606.7	615.7	626.8	635.1	640.7	644.4	642.7	641.0	642.7	644.4	640.7
42.5°	506.6	515.8	526.3	534.3	539.8	542.2	535.0	527.8	535.0	542.2	539.8
45°	361.4	378.3	389.8	392.6	386.6	376.4	353.8	331.1	353.8	376.4	386.6
47.5°	201.9	234.1	266.2	272.4	252.8	230.3	198.9	167.5	198.9	230.3	252.8
50°	122.4	157.8	200.2	206.6	177.1	149.5	127.7	105.9	127.7	149.5	177.1
52.5°	91.0	120.9	158.1	161.1	129.9	103.6	92.4	81.2	92.4	103.6	129.9
55°	61.7	77.6	97.7	98.8	80.8	66.3	62.0	57.7	62.0	66.3	80.8
57.5°	46.8	53.1	60.7	61.3	54.9	49.4	47.1	44.7	47.1	49.4	54.9
60°	39.9	43.3	47.2	47.6	44.6	41.9	40.2	38.5	40.2	41.9	44.6
62.5°	34.1	36.1	38.6	39.2	37.9	36.7	35.7	34.6	35.7	36.7	37.9
65°	28.8	29.5	30.4	30.8	30.8	30.7	30.3	29.8	30.3	30.7	30.8
67.5°	25.1	25.5	26.0	26.2	26.3	26.3	25.8	25.4	25.8	26.3	26.3
70°	22.0	22.5	22.9	23.3	23.7	24.0	23.5	23.1	23.5	24.0	23.7
72.5°	19.7	19.9	20.0	20.2	20.7	20.9	20.4	20.0	20.4	20.9	20.7
75°	15.4	15.7	16.1	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4
77.5°	11.8	11.9	11.9	12.1	12.6	12.9	12.8	12.7	12.8	12.9	12.6
80°	9.6	9.6	9.6	9.8	10.3	10.5	10.1	9.6	10.1	10.5	10.3
82.5°	7.3	7.3	7.3	7.5	8.0	8.3	8.2	8.1	8.2	8.3	8.0
85°	4.7	4.5	4.1	4.1	4.5	4.8	4.8	4.8	4.8	4.8	4.5
87.5°	6.9	6.7	6.7	6.4	5.7	4.6	3.3	2.3	3.3	4.4	6.2
90°	27.0	25.7	25.7	24.4	20.6	15.4	9.0	3.9	9.0	14.2	23.2
92.5°	32.2	31.9	29.8	27.5	22.6	22.6	22.4	14.2	24.4	34.7	49.9
95°	29.6	29.6	34.7	43.7	64.3	65.6	43.7	39.9	56.6	79.8	100.3
97.5°	80.0	95.2	116.8	120.9	114.5	85.4	81.8	76.2	103.7	126.6	159.8
100°	147.9	167.2	182.7	151.8	119.6	118.4	110.6	108.1	137.6	159.5	191.7
102.5°	231.3	237.2	183.7	166.2	158.7	153.3	141.5	140.0	169.6	199.7	226.7
105°	250.9	225.1	226.4	226.4	221.3	211.0	189.1	187.8	221.3	256.0	289.5
107.5°	295.1	299.0	305.7	304.1	298.2	270.7	244.9	239.0	269.1	310.8	347.6
110°	353.8	357.6	360.2	357.6	348.6	313.9	283.0	274.0	301.0	344.8	384.6



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	410.4	413.2	418.9	411.1	396.0	356.1	321.1	308.0	335.0	379.8	420.7
115°	500.4	500.4	501.7	497.9	467.0	425.8	379.5	360.2	383.4	424.5	469.6
117.5°	588.9	590.5	585.3	575.0	539.3	491.4	439.5	408.6	426.8	470.3	516.6
120°	644.5	647.1	641.9	626.5	591.8	537.7	478.6	442.5	456.7	499.1	545.5
122.5°	702.1	701.6	695.5	678.0	637.0	581.0	522.8	478.6	484.5	523.8	569.1
125°	782.2	780.9	775.7	755.1	712.7	654.8	586.6	532.6	524.9	558.3	604.6
127.5°	858.3	855.5	847.5	822.6	779.1	723.2	648.4	587.1	569.9	591.0	633.4
130°	910.8	906.9	892.8	865.8	823.3	770.6	694.7	625.2	600.8	613.6	650.9
132.5°	961.2	950.2	938.1	909.0	869.6	814.8	737.9	665.4	631.6	637.3	666.4
135°	1025.3	1015.0	999.6	971.3	934.0	879.9	802.7	724.3	678.0	672.8	689.5
137.5°	1081.6	1070.8	1053.3	1028.9	991.3	943.2	869.1	786.3	727.9	710.6	717.1
140°	1116.6	1103.8	1088.3	1063.9	1030.4	980.3	908.2	828.5	762.9	738.4	734.6
142.5°	1145.5	1135.7	1119.2	1096.8	1067.5	1017.3	947.3	868.6	798.9	767.2	758.2
145°	1188.7	1181.0	1162.9	1142.4	1117.9	1067.8	1003.4	925.0	855.5	814.3	795.0
147.5°	1225.2	1219.0	1204.9	1180.7	1160.1	1112.0	1053.3	983.9	912.6	861.7	836.7
150°	1247.9	1242.7	1228.6	1205.4	1184.8	1139.8	1083.2	1018.9	950.7	896.7	864.5
152.5°	1269.5	1264.3	1248.1	1225.0	1207.5	1165.5	1114.1	1052.8	983.6	929.6	896.4
155°	1298.0	1291.6	1276.2	1254.3	1238.8	1200.3	1152.7	1098.6	1039.4	982.8	945.5
157.5°	1320.7	1312.7	1298.3	1279.5	1263.0	1227.5	1186.1	1139.5	1087.8	1033.8	995.7
160°	1334.0	1325.0	1309.6	1292.9	1277.4	1244.0	1206.7	1164.2	1116.6	1067.8	1026.6
162.5°	1343.3	1335.3	1316.8	1302.1	1288.8	1258.4	1223.2	1184.8	1142.4	1099.7	1061.6
165°	1353.3	1344.3	1325.0	1313.5	1301.9	1276.2	1245.3	1214.4	1178.4	1143.7	1112.8
167.5°	1354.1	1346.7	1327.4	1316.0	1307.5	1285.4	1260.5	1236.8	1208.7	1181.5	1155.7
170°	1352.1	1345.6	1326.3	1316.0	1309.6	1291.6	1269.7	1249.1	1227.3	1204.1	1183.5
172.5°	1344.9	1338.4	1320.2	1311.9	1308.6	1292.6	1274.9	1259.4	1240.7	1223.7	1207.2
175°	1326.3	1321.2	1305.7	1300.6	1301.9	1291.6	1278.7	1269.7	1258.1	1247.9	1238.8
177.5°	1299.3	1296.2	1284.9	1284.9	1289.0	1282.8	1278.7	1274.6	1269.5	1266.4	1263.3
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5
2.5°	5367.6	5365.8	5384.9	5398.1	5393.3	5388.5	5393.3	5398.1	5384.9	5365.8	5367.6
5°	5176.4	5183.3	5216.6	5239.7	5232.0	5224.3	5232.0	5239.7	5216.6	5183.3	5176.4
7.5°	4794.9	4803.8	4833.4	4853.4	4845.2	4837.0	4845.2	4853.4	4833.4	4803.8	4794.9
10°	4446.5	4459.6	4502.8	4527.9	4498.8	4469.7	4498.8	4527.9	4502.8	4459.6	4446.5
12.5°	4041.9	4039.5	4046.4	4047.6	4031.5	4015.4	4031.5	4047.6	4046.4	4039.5	4041.9
15°	3386.0	3375.9	3386.6	3393.5	3388.8	3384.1	3388.8	3393.5	3386.6	3375.9	3386.0
17.5°	2771.3	2757.2	2756.1	2754.0	2748.7	2743.4	2748.7	2754.0	2756.1	2757.2	2771.3
20°	2381.6	2377.7	2386.3	2392.5	2391.6	2390.8	2391.6	2392.5	2386.3	2377.7	2381.6
22.5°	2049.6	2045.6	2058.3	2065.9	2058.2	2050.5	2058.2	2065.9	2058.3	2045.6	2049.6
25°	1642.8	1633.0	1626.6	1622.1	1623.4	1624.7	1623.4	1622.1	1626.6	1633.0	1642.8
27.5°	1339.3	1336.5	1340.8	1343.2	1340.0	1336.9	1340.0	1343.2	1340.8	1336.5	1339.3
30°	1190.9	1187.1	1189.6	1190.6	1186.7	1182.9	1186.7	1190.6	1189.6	1187.1	1190.9
32.5°	1065.6	1059.7	1058.5	1056.9	1054.0	1051.2	1054.0	1056.9	1058.5	1059.7	1065.6
35°	894.0	886.1	879.7	873.9	870.1	866.2	870.1	873.9	879.7	886.1	894.0
37.5°	736.4	727.7	718.3	710.5	707.2	704.0	707.2	710.5	718.3	727.7	736.4
40°	635.1	626.8	615.7	606.7	604.1	601.5	604.1	606.7	615.7	626.8	635.1
42.5°	534.3	526.3	515.8	506.6	500.9	495.3	500.9	506.6	515.8	526.3	534.3
45°	392.6	389.8	378.3	361.4	328.4	295.5	328.4	361.4	378.3	389.8	392.6
47.5°	272.4	266.2	234.1	201.9	169.6	137.2	169.6	201.9	234.1	266.2	272.4
50°	206.6	200.2	157.8	122.4	107.9	93.4	107.9	122.4	157.8	200.2	206.6
52.5°	161.1	158.1	120.9	91.0	82.9	74.9	82.9	91.0	120.9	158.1	161.1
55°	98.8	97.7	77.6	61.7	58.3	54.9	58.3	61.7	77.6	97.7	98.8
57.5°	61.3	60.7	53.1	46.8	44.7	42.5	44.7	46.8	53.1	60.7	61.3
60°	47.6	47.2	43.3	39.9	37.8	35.6	37.8	39.9	43.3	47.2	47.6
62.5°	39.2	38.6	36.1	34.1	33.3	32.5	33.3	34.1	36.1	38.6	39.2
65°	30.8	30.4	29.5	28.8	28.3	27.9	28.3	28.8	29.5	30.4	30.8
67.5°	26.2	26.0	25.5	25.1	24.7	24.3	24.7	25.1	25.5	26.0	26.2
70°	23.3	22.9	22.5	22.0	21.6	21.2	21.6	22.0	22.5	22.9	23.3
72.5°	20.2	20.0	19.9	19.7	19.3	18.9	19.3	19.7	19.9	20.0	20.2
75°	16.4	16.1	15.7	15.4	15.4	15.4	15.4	15.4	15.7	16.1	16.4
77.5°	12.1	11.9	11.9	11.8	11.5	11.2	11.5	11.8	11.9	11.9	12.1
80°	9.8	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.8
82.5°	7.5	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.5
85°	4.1	4.1	4.5	4.7	4.3	3.8	4.3	4.7	4.5	4.1	4.1
87.5°	7.5	9.3	11.1	12.1	13.1	12.6	13.1	12.1	11.1	9.3	7.5
90°	29.6	38.6	47.6	52.7	57.9	55.3	57.9	52.7	47.6	38.6	29.6
92.5°	59.4	74.6	85.7	94.9	99.1	98.5	99.1	94.9	85.7	74.6	59.4
95°	119.6	137.6	155.7	168.5	176.2	173.7	176.2	168.5	155.7	137.6	119.6
97.5°	184.5	208.7	228.7	240.8	248.5	253.7	248.5	240.8	228.7	208.7	184.5
100°	227.7	250.9	274.0	288.2	301.0	306.2	301.0	288.2	274.0	250.9	227.7
102.5°	262.7	293.1	318.3	333.4	344.3	349.4	344.3	318.3	293.1	262.7	
105°	320.3	352.5	379.5	398.8	410.4	414.2	410.4	398.8	379.5	352.5	320.3
107.5°	378.0	411.1	436.1	457.5	471.6	479.8	471.6	457.5	436.1	411.1	378.0
110°	423.2	450.3	477.3	496.6	510.7	515.9	510.7	496.6	477.3	450.3	423.2



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	461.3	491.4	518.4	537.7	553.9	561.1	553.9	537.7	518.4	491.4	461.3
115°	514.6	554.5	578.9	596.9	608.5	614.9	608.5	596.9	578.9	554.5	514.6
117.5°	558.8	600.5	627.3	641.2	646.6	651.2	646.6	641.2	627.3	600.5	558.8
120°	586.6	625.2	656.1	674.1	680.5	683.1	680.5	674.1	656.1	625.2	586.6
122.5°	612.3	648.9	678.7	700.9	711.4	714.0	711.4	700.9	678.7	648.9	612.3
125°	648.4	683.1	714.0	735.8	747.4	753.9	747.4	735.8	714.0	683.1	648.4
127.5°	679.8	717.3	745.6	765.4	776.8	781.9	776.8	765.4	745.6	717.3	679.8
130°	697.3	735.8	764.1	786.0	796.3	801.5	796.3	786.0	764.1	735.8	697.3
132.5°	710.6	751.3	780.6	800.4	811.7	816.9	811.7	800.4	780.6	751.3	710.6
135°	726.8	769.3	800.2	819.5	829.8	834.9	829.8	819.5	800.2	769.3	726.8
137.5°	741.0	779.6	811.7	832.1	841.3	844.7	841.3	832.1	811.7	779.6	741.0
140°	751.3	784.7	816.9	836.2	846.5	847.8	846.5	836.2	816.9	784.7	751.3
142.5°	764.7	790.9	819.0	838.2	848.5	850.9	848.5	838.2	819.0	790.9	764.7
145°	788.6	804.0	823.3	841.3	850.3	852.9	850.3	841.3	823.3	804.0	788.6
147.5°	818.7	823.6	833.6	845.5	854.2	856.0	854.2	845.5	833.6	823.6	818.7
150°	841.3	840.1	843.9	851.6	859.3	858.1	859.3	851.6	843.9	840.1	841.3
152.5°	867.1	859.6	859.3	862.9	866.6	866.3	866.6	862.9	859.3	859.6	867.1
155°	910.8	896.7	888.9	886.4	886.4	885.1	886.4	886.4	888.9	896.7	910.8
157.5°	958.9	939.1	927.5	921.4	919.6	916.7	919.6	921.4	927.5	939.1	958.9
160°	991.9	970.0	958.4	948.1	944.3	940.4	944.3	948.1	958.4	970.0	991.9
162.5°	1022.7	1001.9	989.3	980.0	976.2	970.2	976.2	980.0	989.3	1001.9	1022.7
165°	1072.9	1051.0	1036.9	1029.2	1024.0	1018.9	1024.0	1029.2	1036.9	1051.0	1072.9
167.5°	1123.1	1099.1	1089.9	1081.1	1076.2	1067.0	1076.2	1081.1	1089.9	1099.1	1123.1
170°	1153.9	1132.1	1126.9	1119.2	1110.2	1099.9	1110.2	1119.2	1126.9	1132.1	1153.9
172.5°	1180.7	1166.0	1160.9	1153.2	1150.3	1142.1	1150.3	1153.2	1160.9	1166.0	1180.7
175°	1219.6	1208.0	1208.0	1206.7	1202.8	1195.1	1202.8	1206.7	1208.0	1208.0	1219.6
177.5°	1252.0	1245.8	1249.9	1249.9	1248.9	1241.7	1248.9	1249.9	1249.9	1245.8	1252.0
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	5425.5	5425.5	5425.5	5425.5
2.5°	5390.6	5408.8	5412.9	5417.0
5°	5196.1	5211.7	5215.1	5218.5
7.5°	4806.5	4814.5	4811.6	4808.7
10°	4463.6	4474.5	4466.8	4459.1
12.5°	4053.5	4063.5	4068.4	4073.4
15°	3416.8	3444.4	3462.3	3480.3
17.5°	2798.5	2817.2	2810.2	2803.3
20°	2397.8	2409.5	2407.4	2405.2
22.5°	2070.3	2085.8	2085.3	2084.9
25°	1656.1	1666.4	1667.6	1668.9
27.5°	1349.3	1358.0	1363.3	1368.6
30°	1201.2	1209.9	1214.2	1218.5
32.5°	1076.2	1084.1	1083.9	1083.7
35°	903.4	909.9	907.3	904.7
37.5°	744.4	749.7	747.4	745.0
40°	640.7	644.4	642.7	641.0
42.5°	539.8	542.2	535.0	527.8
45°	386.6	376.4	353.8	331.1
47.5°	252.8	230.3	198.9	167.5
50°	177.1	149.5	127.7	105.9
52.5°	129.9	103.6	92.4	81.2
55°	80.8	66.3	62.0	57.7
57.5°	54.9	49.4	47.1	44.7
60°	44.6	41.9	40.2	38.5
62.5°	37.9	36.7	35.7	34.6
65°	30.8	30.7	30.3	29.8
67.5°	26.3	26.3	25.8	25.4
70°	23.7	24.0	23.5	23.1
72.5°	20.7	20.9	20.4	20.0
75°	16.4	16.4	16.4	16.4
77.5°	12.6	12.9	12.8	12.7
80°	10.3	10.5	10.1	9.6
82.5°	8.0	8.3	8.2	8.1
85°	4.5	4.8	4.8	4.8
87.5°	6.2	4.4	3.3	2.3
90°	23.2	14.2	9.0	3.9
92.5°	49.9	34.7	24.4	14.2
95°	100.3	79.8	56.6	39.9
97.5°	159.8	126.6	103.7	76.2
100°	191.7	159.5	137.6	108.1
102.5°	226.7	199.7	169.6	140.0
105°	289.5	256.0	221.3	187.8
107.5°	347.6	310.8	269.1	239.0
110°	384.6	344.8	301.0	274.0



TEST NUMBER: P1428626

CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	420.7	379.8	335.0	308.0
115°	469.6	424.5	383.4	360.2
117.5°	516.6	470.3	426.8	408.6
120°	545.5	499.1	456.7	442.5
122.5°	569.1	523.8	484.5	478.6
125°	604.6	558.3	524.9	532.6
127.5°	633.4	591.0	569.9	587.1
130°	650.9	613.6	600.8	625.2
132.5°	666.4	637.3	631.6	665.4
135°	689.5	672.8	678.0	724.3
137.5°	717.1	710.6	727.9	786.3
140°	734.6	738.4	762.9	828.5
142.5°	758.2	767.2	798.9	868.6
145°	795.0	814.3	855.5	925.0
147.5°	836.7	861.7	912.6	983.9
150°	864.5	896.7	950.7	1018.9
152.5°	896.4	929.6	983.6	1052.8
155°	945.5	982.8	1039.4	1098.6
157.5°	995.7	1033.8	1087.8	1139.5
160°	1026.6	1067.8	1116.6	1164.2
162.5°	1061.6	1099.7	1142.4	1184.8
165°	1112.8	1143.7	1178.4	1214.4
167.5°	1155.7	1181.5	1208.7	1236.8
170°	1183.5	1204.1	1227.3	1249.1
172.5°	1207.2	1223.7	1240.7	1259.4
175°	1238.8	1247.9	1258.1	1269.7
177.5°	1263.3	1266.4	1269.5	1274.6
180°	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428626  
 CATALOG NUMBER: SQ2W-WBN-K-100U-075D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.28	1.95	2.31	2.96	4.30	0.91	1.58	1.94	2.59	3.93
	3H	2.51	3.10	3.54	4.12	5.48	2.12	2.71	3.16	3.73	5.09
	4H	3.02	3.58	4.07	4.61	5.98	2.63	3.19	3.68	4.21	5.58
	6H	3.38	3.89	4.43	4.92	6.30	2.96	3.47	4.02	4.50	5.88
	8H	3.52	4.01	4.58	5.05	6.43	3.10	3.58	4.16	4.62	6.00
	12H	3.61	4.08	4.68	5.11	6.51	3.17	3.63	4.23	4.66	6.06
4H	2H	1.60	2.16	2.66	3.18	4.55	1.29	1.85	2.35	2.87	4.25
	3H	3.09	3.56	4.15	4.61	5.99	2.76	3.22	3.82	4.27	5.65
	4H	3.74	4.17	4.81	5.21	6.61	3.39	3.81	4.45	4.86	6.26
	6H	4.23	4.59	5.30	5.66	7.06	3.84	4.21	4.92	5.27	6.67
	8H	4.44	4.78	5.52	5.84	7.25	4.04	4.38	5.11	5.43	6.85
	12H	4.58	4.88	5.67	5.95	7.37	4.14	4.45	5.23	5.52	6.94
8H	4H	3.90	4.24	4.97	5.30	6.71	3.59	3.92	4.66	4.98	6.39
	6H	4.54	4.81	5.63	5.91	7.32	4.18	4.46	5.27	5.56	6.97
	8H	4.86	5.10	5.96	6.18	7.61	4.47	4.71	5.57	5.79	7.22
	12H	5.09	5.30	6.19	6.37	7.85	4.67	4.88	5.77	5.96	7.43
12H	4H	3.88	4.18	4.97	5.25	6.67	3.57	3.88	4.66	4.95	6.37
	6H	4.57	4.81	5.67	5.90	7.33	4.23	4.47	5.33	5.55	6.99
	8H	4.92	5.13	6.02	6.21	7.68	4.55	4.76	5.65	5.84	7.31