

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428632

Luminaire Tested: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428632
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8992.1 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	102	99	96	93	96	93	90	88	81	79	78	70	69	68	61	60	59	55				
2	96	90	85	81	90	85	81	77	75	72	69	66	64	62	57	56	55	51				
3	90	82	77	72	84	78	73	69	69	66	63	61	59	56	54	52	51	47				
4	84	76	69	65	79	72	66	62	64	60	57	57	54	52	51	49	47	44				
5	79	70	63	58	74	66	60	56	60	55	52	54	50	48	48	46	44	41				
6	74	64	58	53	70	61	56	51	56	51	48	50	47	44	45	43	41	39				
7	70	60	53	49	66	57	51	47	52	48	44	47	44	41	43	40	38	36				
8	66	56	50	45	63	54	48	44	49	45	41	45	41	39	41	38	36	34				
9	63	52	46	42	59	50	45	41	46	42	39	42	39	36	39	36	34	32				
10	59	49	43	39	56	47	42	38	44	39	36	40	37	34	37	34	32	31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	146480	146480	146480	146480
5°	141432	141588	141432	141588
10°	122248	122538	122248	122538
15°	97279	94589	97279	94589
20°	69105	68691	69105	68691
25°	49717	48399	49717	48399
30°	37988	36876	37988	36876
35°	29819	28550	29819	28550
40°	22592	21201	22592	21201
45°	12643	11282	12643	11282
50°	4446	3921	4446	3921
55°	2719	2581	2719	2581
60°	2080	1921	2080	1921
65°	1906	1784	1906	1784
70°	1822	1671	1822	1671
75°	1709	1609	1709	1609
80°	1497	1497	1497	1497
85°	1482	1186	1482	1186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 14990 cd/sqm



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	787.5	8.8
10°-20°	1565.2	17.4
20°-30°	1296.2	14.4
30°-40°	932.5	10.4
40°-50°	475.0	5.3
50°-60°	123.5	1.4
60°-70°	51.3	0.6
70°-80°	28.5	0.3
80°-90°	13.7	0.2
90°-100°	101.4	1.1
100°-110°	295.6	3.3
110°-120°	482.4	5.4
120°-130°	612.1	6.8
130°-140°	655.0	7.3
140°-150°	611.6	6.8
150°-160°	503.3	5.6
160°-170°	337.5	3.8
170°-180°	119.8	1.3
0°-30°	3649.0	40.6
0°-40°	4581.5	51.0
0°-60°	5180.0	57.6
0°-90°	5273.5	58.6
90°-120°	879.3	9.8
90°-150°	2758.0	30.7
90°-180°	3719.0	41.4
0°-180°	8992.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9072	9072	9072	9072	9072	
5°	8726	8736	8726	8736	8726	787
15°	5820	5659	5820	5659	5820	1580
25°	2791	2717	2791	2717	2791	1313
35°	1513	1448	1513	1448	1513	949
45°	554	494	554	494	554	442
55°	97	92	97	92	97	95
65°	50	47	50	47	50	50
75°	27	26	27	26	27	29
85°	8	6	8	6	8	8
90°	4	28	4	55	4	3
95°	40	30	40	174	40	48
105°	188	301	188	414	188	200
115°	360	499	360	615	360	355
125°	533	791	533	754	533	477
135°	724	1036	724	835	724	560
145°	925	1194	925	853	925	579
155°	1099	1297	1099	885	1099	505
165°	1214	1352	1214	1019	1214	342
175°	1270	1324	1270	1195	1270	120
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5
2.5°	9058.4	9051.5	9044.6	9014.1	8975.8	8972.7	9004.7	9026.7	9018.7	9010.7	9018.7
5°	8726.5	8720.8	8715.0	8688.9	8656.0	8667.5	8723.3	8761.9	8749.0	8736.1	8749.0
7.5°	8041.2	8046.0	8050.9	8037.5	8018.1	8033.0	8082.4	8116.0	8102.2	8088.5	8102.2
10°	7456.6	7469.5	7482.4	7464.1	7435.5	7457.3	7529.6	7571.6	7523.0	7474.3	7523.0
12.5°	6811.5	6803.3	6795.0	6778.3	6758.8	6754.9	6766.5	6768.4	6741.6	6714.7	6741.6
15°	5819.8	5789.8	5759.7	5713.6	5662.1	5645.3	5663.1	5674.6	5666.7	5658.9	5666.7
17.5°	4687.7	4699.3	4710.9	4679.7	4634.2	4610.6	4608.8	4605.3	4596.5	4587.6	4596.5
20°	4022.0	4025.6	4029.2	4009.7	3982.5	3976.1	3990.4	4000.8	3999.3	3997.9	3999.3
22.5°	3486.4	3487.1	3487.8	3462.1	3427.4	3420.7	3441.9	3454.5	3441.7	3428.8	3441.7
25°	2790.8	2788.7	2786.5	2769.3	2747.2	2730.7	2720.0	2712.5	2714.6	2716.8	2714.6
27.5°	2288.6	2279.8	2270.9	2256.2	2239.7	2234.9	2242.1	2246.1	2240.8	2235.5	2240.8
30°	2037.6	2030.4	2023.3	2008.6	1991.4	1985.0	1989.3	1990.9	1984.5	1978.0	1984.5
32.5°	1812.2	1812.5	1812.8	1799.6	1781.8	1772.0	1770.0	1767.3	1762.6	1757.8	1762.6
35°	1512.9	1517.2	1521.5	1510.7	1495.0	1481.8	1471.0	1461.4	1454.9	1448.5	1454.9
37.5°	1245.7	1249.7	1253.7	1244.8	1231.4	1216.9	1201.2	1188.0	1182.6	1177.2	1182.6
40°	1071.9	1074.8	1077.6	1071.4	1062.1	1048.1	1029.5	1014.5	1010.2	1005.9	1010.2
42.5°	882.6	894.6	906.7	902.7	893.4	880.0	862.6	847.1	837.7	828.2	837.7
45°	553.7	591.6	629.5	646.5	656.5	651.8	632.5	604.3	549.2	494.1	549.2
47.5°	280.0	332.5	385.1	422.8	455.5	445.1	391.4	337.7	283.6	229.5	283.6
50°	177.0	213.5	250.0	296.1	345.5	334.8	264.0	204.8	180.4	156.1	180.4
52.5°	135.8	154.6	173.3	217.2	269.4	264.4	202.1	152.1	138.7	125.2	138.7
55°	96.6	103.7	110.9	135.2	165.2	163.4	129.8	103.2	97.5	91.7	97.5
57.5°	74.7	78.7	82.7	91.7	102.5	101.5	88.7	78.3	74.7	71.1	74.7
60°	64.4	67.2	70.1	74.6	79.6	78.9	72.4	66.7	63.1	59.5	63.1
62.5°	57.9	59.7	61.4	63.4	65.6	64.6	60.4	57.0	55.7	54.4	55.7
65°	49.9	50.6	51.3	51.5	51.5	50.8	49.4	48.1	47.4	46.7	47.4
67.5°	42.5	43.2	43.9	44.0	43.8	43.4	42.7	42.0	41.3	40.6	41.3
70°	38.6	39.3	40.1	39.7	39.0	38.3	37.6	36.8	36.1	35.4	36.1
72.5°	33.5	34.2	34.9	34.5	33.8	33.4	33.3	33.0	32.3	31.5	32.3
75°	27.4	27.4	27.4	27.4	27.4	27.0	26.3	25.8	25.8	25.8	25.8
77.5°	21.2	21.4	21.5	21.0	20.3	20.0	20.0	19.8	19.2	18.7	19.2
80°	16.1	16.8	17.5	17.2	16.5	16.1	16.1	16.1	16.1	16.1	16.1
82.5°	13.5	13.7	13.8	13.3	12.6	12.2	12.2	12.2	12.2	12.2	12.2
85°	8.0	8.0	8.0	7.5	6.8	6.8	7.5	7.9	7.2	6.4	7.2
87.5°	3.3	4.4	5.7	6.7	7.5	7.7	7.7	8.0	8.2	8.2	8.2
90°	3.9	9.0	15.4	20.6	24.4	25.7	25.7	27.0	28.3	28.3	28.3
92.5°	14.2	22.4	22.6	22.6	27.5	29.8	31.9	32.2	33.4	33.4	33.4
95°	39.9	43.7	65.6	64.3	43.7	34.7	29.6	29.6	29.6	29.6	29.6
97.5°	76.2	81.8	85.4	114.5	120.9	116.8	95.2	80.0	71.5	67.7	71.5
100°	108.1	110.6	118.4	119.6	151.8	182.7	167.2	147.9	141.5	137.6	141.5
102.5°	140.0	141.5	153.3	158.7	166.2	183.7	237.2	231.3	226.9	226.2	226.9
105°	187.8	189.1	211.0	221.3	226.4	226.4	225.1	250.9	292.0	301.0	292.0
107.5°	239.0	244.9	270.7	298.2	304.1	305.7	299.0	295.1	293.6	294.6	293.6
110°	274.0	283.0	313.9	348.6	357.6	360.2	357.6	353.8	351.2	351.2	351.2



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	308.0	321.1	356.1	396.0	411.1	418.9	413.2	410.4	407.8	409.9	407.8
115°	360.2	379.5	425.8	467.0	497.9	501.7	500.4	500.4	499.1	499.1	499.1
117.5°	408.6	439.5	491.4	539.3	575.0	585.3	590.5	588.9	587.4	590.0	587.4
120°	442.5	478.6	537.7	591.8	626.5	641.9	647.1	644.5	647.1	644.5	647.1
122.5°	478.6	522.8	581.0	637.0	678.0	695.5	701.6	702.1	702.7	701.1	702.7
125°	532.6	586.6	654.8	712.7	755.1	775.7	780.9	782.2	784.7	791.2	784.7
127.5°	587.1	648.4	723.2	779.1	822.6	847.5	855.5	858.3	863.7	866.6	863.7
130°	625.2	694.7	770.6	823.3	865.8	892.8	906.9	910.8	917.2	916.0	917.2
132.5°	665.4	737.9	814.8	869.6	909.0	938.1	950.2	961.2	963.5	965.4	963.5
135°	724.3	802.7	879.9	934.0	971.3	999.6	1015.0	1025.3	1031.7	1035.6	1031.7
137.5°	786.3	869.1	943.2	991.3	1028.9	1053.3	1070.8	1081.6	1088.3	1091.4	1088.3
140°	828.5	908.2	980.3	1030.4	1063.9	1088.3	1103.8	1116.6	1124.4	1124.4	1124.4
142.5°	868.6	947.3	1017.3	1067.5	1096.8	1119.2	1135.7	1145.5	1154.2	1154.2	1154.2
145°	925.0	1003.4	1067.8	1117.9	1142.4	1162.9	1181.0	1188.7	1193.8	1193.8	1193.8
147.5°	983.9	1053.3	1112.0	1160.1	1180.7	1204.9	1219.0	1225.2	1231.6	1228.8	1231.6
150°	1018.9	1083.2	1139.8	1184.8	1205.4	1228.6	1242.7	1247.9	1254.3	1250.4	1254.3
152.5°	1052.8	1114.1	1165.5	1207.5	1225.0	1248.1	1264.3	1269.5	1273.8	1271.0	1273.8
155°	1098.6	1152.7	1200.3	1238.8	1254.3	1276.2	1291.6	1298.0	1303.2	1296.7	1303.2
157.5°	1139.5	1186.1	1227.5	1263.0	1279.5	1298.3	1312.7	1320.7	1325.8	1323.0	1325.8
160°	1164.2	1206.7	1244.0	1277.4	1292.9	1309.6	1325.0	1334.0	1339.2	1335.3	1339.2
162.5°	1184.8	1223.2	1258.4	1288.8	1302.1	1316.8	1335.3	1343.3	1348.5	1343.6	1348.5
165°	1214.4	1245.3	1276.2	1301.9	1313.5	1325.0	1344.3	1353.3	1357.2	1352.1	1357.2
167.5°	1236.8	1260.5	1285.4	1307.5	1316.0	1327.4	1346.7	1354.1	1359.0	1352.6	1359.0
170°	1249.1	1269.7	1291.6	1309.6	1316.0	1326.3	1345.6	1352.1	1355.9	1349.5	1355.9
172.5°	1259.4	1274.9	1292.6	1308.6	1311.9	1320.2	1338.4	1344.9	1347.7	1342.3	1347.7
175°	1269.7	1278.7	1291.6	1301.9	1300.6	1305.7	1321.2	1326.3	1331.5	1323.8	1331.5
177.5°	1274.6	1278.7	1282.8	1289.0	1284.9	1284.9	1296.2	1299.3	1300.3	1296.2	1300.3
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5
2.5°	9026.7	9004.7	8972.7	8975.8	9014.1	9044.6	9051.5	9058.4	9051.5	9044.6	9014.1
5°	8761.9	8723.3	8667.5	8656.0	8688.9	8715.0	8720.8	8726.5	8720.8	8715.0	8688.9
7.5°	8116.0	8082.4	8033.0	8018.1	8037.5	8050.9	8046.0	8041.2	8046.0	8050.9	8037.5
10°	7571.6	7529.6	7457.3	7435.5	7464.1	7482.4	7469.5	7456.6	7469.5	7482.4	7464.1
12.5°	6768.4	6766.5	6754.9	6758.8	6778.3	6795.0	6803.3	6811.5	6803.3	6795.0	6778.3
15°	5674.6	5663.1	5645.3	5662.1	5713.6	5759.7	5789.8	5819.8	5789.8	5759.7	5713.6
17.5°	4605.3	4608.8	4610.6	4634.2	4679.7	4710.9	4699.3	4687.7	4699.3	4710.9	4679.7
20°	4000.8	3990.4	3976.1	3982.5	4009.7	4029.2	4025.6	4022.0	4025.6	4029.2	4009.7
22.5°	3454.5	3441.9	3420.7	3427.4	3462.1	3487.8	3487.1	3486.4	3487.1	3487.8	3462.1
25°	2712.5	2720.0	2730.7	2747.2	2769.3	2786.5	2788.7	2790.8	2788.7	2786.5	2769.3
27.5°	2246.1	2242.1	2234.9	2239.7	2256.2	2270.9	2279.8	2288.6	2279.8	2270.9	2256.2
30°	1990.9	1989.3	1985.0	1991.4	2008.6	2023.3	2030.4	2037.6	2030.4	2023.3	2008.6
32.5°	1767.3	1770.0	1772.0	1781.8	1799.6	1812.8	1812.5	1812.2	1812.5	1812.8	1799.6
35°	1461.4	1471.0	1481.8	1495.0	1510.7	1521.5	1517.2	1512.9	1517.2	1521.5	1510.7
37.5°	1188.0	1201.2	1216.9	1231.4	1244.8	1253.7	1249.7	1245.7	1249.7	1253.7	1244.8
40°	1014.5	1029.5	1048.1	1062.1	1071.4	1077.6	1074.8	1071.9	1074.8	1077.6	1071.4
42.5°	847.1	862.6	880.0	893.4	902.7	906.7	894.6	882.6	894.6	906.7	902.7
45°	604.3	632.5	651.8	656.5	646.5	629.5	591.6	553.7	591.6	629.5	646.5
47.5°	337.7	391.4	445.1	455.5	422.8	385.1	332.5	280.0	332.5	385.1	422.8
50°	204.8	264.0	334.8	345.5	296.1	250.0	213.5	177.0	213.5	250.0	296.1
52.5°	152.1	202.1	264.4	269.4	217.2	173.3	154.6	135.8	154.6	173.3	217.2
55°	103.2	129.8	163.4	165.2	135.2	110.9	103.7	96.6	103.7	110.9	135.2
57.5°	78.3	88.7	101.5	102.5	91.7	82.7	78.7	74.7	78.7	82.7	91.7
60°	66.7	72.4	78.9	79.6	74.6	70.1	67.2	64.4	67.2	70.1	74.6
62.5°	57.0	60.4	64.6	65.6	63.4	61.4	59.7	57.9	59.7	61.4	63.4
65°	48.1	49.4	50.8	51.5	51.5	51.3	50.6	49.9	50.6	51.3	51.5
67.5°	42.0	42.7	43.4	43.8	44.0	43.9	43.2	42.5	43.2	43.9	44.0
70°	36.8	37.6	38.3	39.0	39.7	40.1	39.3	38.6	39.3	40.1	39.7
72.5°	33.0	33.3	33.4	33.8	34.5	34.9	34.2	33.5	34.2	34.9	34.5
75°	25.8	26.3	27.0	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
77.5°	19.8	20.0	20.0	20.3	21.0	21.5	21.4	21.2	21.4	21.5	21.0
80°	16.1	16.1	16.1	16.5	17.2	17.5	16.8	16.1	16.8	17.5	17.2
82.5°	12.2	12.2	12.2	12.6	13.3	13.8	13.7	13.5	13.7	13.8	13.3
85°	7.9	7.5	6.8	6.8	7.5	8.0	8.0	8.0	8.0	8.0	7.5
87.5°	8.0	7.7	7.7	7.5	6.7	5.7	4.4	3.3	4.4	5.4	7.2
90°	27.0	25.7	25.7	24.4	20.6	15.4	9.0	3.9	9.0	14.2	23.2
92.5°	32.2	31.9	29.8	27.5	22.6	22.6	22.4	14.2	24.4	34.7	49.9
95°	29.6	29.6	34.7	43.7	64.3	65.6	43.7	39.9	56.6	79.8	100.3
97.5°	80.0	95.2	116.8	120.9	114.5	85.4	81.8	76.2	103.7	126.6	159.8
100°	147.9	167.2	182.7	151.8	119.6	118.4	110.6	108.1	137.6	159.5	191.7
102.5°	231.3	237.2	183.7	166.2	158.7	153.3	141.5	140.0	169.6	199.7	226.7
105°	250.9	225.1	226.4	226.4	221.3	211.0	189.1	187.8	221.3	256.0	289.5
107.5°	295.1	299.0	305.7	304.1	298.2	270.7	244.9	239.0	269.1	310.8	347.6
110°	353.8	357.6	360.2	357.6	348.6	313.9	283.0	274.0	301.0	344.8	384.6



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	410.4	413.2	418.9	411.1	396.0	356.1	321.1	308.0	335.0	379.8	420.7
115°	500.4	500.4	501.7	497.9	467.0	425.8	379.5	360.2	383.4	424.5	469.6
117.5°	588.9	590.5	585.3	575.0	539.3	491.4	439.5	408.6	426.8	470.3	516.6
120°	644.5	647.1	641.9	626.5	591.8	537.7	478.6	442.5	456.7	499.1	545.5
122.5°	702.1	701.6	695.5	678.0	637.0	581.0	522.8	478.6	484.5	523.8	569.1
125°	782.2	780.9	775.7	755.1	712.7	654.8	586.6	532.6	524.9	558.3	604.6
127.5°	858.3	855.5	847.5	822.6	779.1	723.2	648.4	587.1	569.9	591.0	633.4
130°	910.8	906.9	892.8	865.8	823.3	770.6	694.7	625.2	600.8	613.6	650.9
132.5°	961.2	950.2	938.1	909.0	869.6	814.8	737.9	665.4	631.6	637.3	666.4
135°	1025.3	1015.0	999.6	971.3	934.0	879.9	802.7	724.3	678.0	672.8	689.5
137.5°	1081.6	1070.8	1053.3	1028.9	991.3	943.2	869.1	786.3	727.9	710.6	717.1
140°	1116.6	1103.8	1088.3	1063.9	1030.4	980.3	908.2	828.5	762.9	738.4	734.6
142.5°	1145.5	1135.7	1119.2	1096.8	1067.5	1017.3	947.3	868.6	798.9	767.2	758.2
145°	1188.7	1181.0	1162.9	1142.4	1117.9	1067.8	1003.4	925.0	855.5	814.3	795.0
147.5°	1225.2	1219.0	1204.9	1180.7	1160.1	1112.0	1053.3	983.9	912.6	861.7	836.7
150°	1247.9	1242.7	1228.6	1205.4	1184.8	1139.8	1083.2	1018.9	950.7	896.7	864.5
152.5°	1269.5	1264.3	1248.1	1225.0	1207.5	1165.5	1114.1	1052.8	983.6	929.6	896.4
155°	1298.0	1291.6	1276.2	1254.3	1238.8	1200.3	1152.7	1098.6	1039.4	982.8	945.5
157.5°	1320.7	1312.7	1298.3	1279.5	1263.0	1227.5	1186.1	1139.5	1087.8	1033.8	995.7
160°	1334.0	1325.0	1309.6	1292.9	1277.4	1244.0	1206.7	1164.2	1116.6	1067.8	1026.6
162.5°	1343.3	1335.3	1316.8	1302.1	1288.8	1258.4	1223.2	1184.8	1142.4	1099.7	1061.6
165°	1353.3	1344.3	1325.0	1313.5	1301.9	1276.2	1245.3	1214.4	1178.4	1143.7	1112.8
167.5°	1354.1	1346.7	1327.4	1316.0	1307.5	1285.4	1260.5	1236.8	1208.7	1181.5	1155.7
170°	1352.1	1345.6	1326.3	1316.0	1309.6	1291.6	1269.7	1249.1	1227.3	1204.1	1183.5
172.5°	1344.9	1338.4	1320.2	1311.9	1308.6	1292.6	1274.9	1259.4	1240.7	1223.7	1207.2
175°	1326.3	1321.2	1305.7	1300.6	1301.9	1291.6	1278.7	1269.7	1258.1	1247.9	1238.8
177.5°	1299.3	1296.2	1284.9	1284.9	1289.0	1282.8	1278.7	1274.6	1269.5	1266.4	1263.3
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5
2.5°	8975.8	8972.7	9004.7	9026.7	9018.7	9010.7	9018.7	9026.7	9004.7	8972.7	8975.8
5°	8656.0	8667.5	8723.3	8761.9	8749.0	8736.1	8749.0	8761.9	8723.3	8667.5	8656.0
7.5°	8018.1	8033.0	8082.4	8116.0	8102.2	8088.5	8102.2	8116.0	8082.4	8033.0	8018.1
10°	7435.5	7457.3	7529.6	7571.6	7523.0	7474.3	7523.0	7571.6	7529.6	7457.3	7435.5
12.5°	6758.8	6754.9	6766.5	6768.4	6741.6	6714.7	6741.6	6768.4	6766.5	6754.9	6758.8
15°	5662.1	5645.3	5663.1	5674.6	5666.7	5658.9	5666.7	5674.6	5663.1	5645.3	5662.1
17.5°	4634.2	4610.6	4608.8	4605.3	4596.5	4587.6	4596.5	4605.3	4608.8	4610.6	4634.2
20°	3982.5	3976.1	3990.4	4000.8	3999.3	3997.9	3999.3	4000.8	3990.4	3976.1	3982.5
22.5°	3427.4	3420.7	3441.9	3454.5	3441.7	3428.8	3441.7	3454.5	3441.9	3420.7	3427.4
25°	2747.2	2730.7	2720.0	2712.5	2714.6	2716.8	2714.6	2712.5	2720.0	2730.7	2747.2
27.5°	2239.7	2234.9	2242.1	2246.1	2240.8	2235.5	2240.8	2246.1	2242.1	2234.9	2239.7
30°	1991.4	1985.0	1989.3	1990.9	1984.5	1978.0	1984.5	1990.9	1989.3	1985.0	1991.4
32.5°	1781.8	1772.0	1770.0	1767.3	1762.6	1757.8	1762.6	1767.3	1770.0	1772.0	1781.8
35°	1495.0	1481.8	1471.0	1461.4	1454.9	1448.5	1454.9	1461.4	1471.0	1481.8	1495.0
37.5°	1231.4	1216.9	1201.2	1188.0	1182.6	1177.2	1182.6	1188.0	1201.2	1216.9	1231.4
40°	1062.1	1048.1	1029.5	1014.5	1010.2	1005.9	1010.2	1014.5	1029.5	1048.1	1062.1
42.5°	893.4	880.0	862.6	847.1	837.7	828.2	837.7	847.1	862.6	880.0	893.4
45°	656.5	651.8	632.5	604.3	549.2	494.1	549.2	604.3	632.5	651.8	656.5
47.5°	455.5	445.1	391.4	337.7	283.6	229.5	283.6	337.7	391.4	445.1	455.5
50°	345.5	334.8	264.0	204.8	180.4	156.1	180.4	204.8	264.0	334.8	345.5
52.5°	269.4	264.4	202.1	152.1	138.7	125.2	138.7	152.1	202.1	264.4	269.4
55°	165.2	163.4	129.8	103.2	97.5	91.7	97.5	103.2	129.8	163.4	165.2
57.5°	102.5	101.5	88.7	78.3	74.7	71.1	74.7	78.3	88.7	101.5	102.5
60°	79.6	78.9	72.4	66.7	63.1	59.5	63.1	66.7	72.4	78.9	79.6
62.5°	65.6	64.6	60.4	57.0	55.7	54.4	55.7	57.0	60.4	64.6	65.6
65°	51.5	50.8	49.4	48.1	47.4	46.7	47.4	48.1	49.4	50.8	51.5
67.5°	43.8	43.4	42.7	42.0	41.3	40.6	41.3	42.0	42.7	43.4	43.8
70°	39.0	38.3	37.6	36.8	36.1	35.4	36.1	36.8	37.6	38.3	39.0
72.5°	33.8	33.4	33.3	33.0	32.3	31.5	32.3	33.0	33.3	33.4	33.8
75°	27.4	27.0	26.3	25.8	25.8	25.8	25.8	25.8	26.3	27.0	27.4
77.5°	20.3	20.0	20.0	19.8	19.2	18.7	19.2	19.8	20.0	20.0	20.3
80°	16.5	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.5
82.5°	12.6	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.6
85°	6.8	6.8	7.5	7.9	7.2	6.4	7.2	7.9	7.5	6.8	6.8
87.5°	8.5	10.3	12.1	13.1	14.2	13.6	14.2	13.1	12.1	10.3	8.5
90°	29.6	38.6	47.6	52.7	57.9	55.3	57.9	52.7	47.6	38.6	29.6
92.5°	59.4	74.6	85.7	94.9	99.1	98.5	99.1	94.9	85.7	74.6	59.4
95°	119.6	137.6	155.7	168.5	176.2	173.7	176.2	168.5	155.7	137.6	119.6
97.5°	184.5	208.7	228.7	240.8	248.5	253.7	248.5	240.8	228.7	208.7	184.5
100°	227.7	250.9	274.0	288.2	301.0	306.2	301.0	288.2	274.0	250.9	227.7
102.5°	262.7	293.1	318.3	333.4	344.3	349.4	344.3	318.3	293.1	262.7	
105°	320.3	352.5	379.5	398.8	410.4	414.2	410.4	398.8	379.5	352.5	320.3
107.5°	378.0	411.1	436.1	457.5	471.6	479.8	471.6	457.5	436.1	411.1	378.0
110°	423.2	450.3	477.3	496.6	510.7	515.9	510.7	496.6	477.3	450.3	423.2



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	461.3	491.4	518.4	537.7	553.9	561.1	553.9	537.7	518.4	491.4	461.3
115°	514.6	554.5	578.9	596.9	608.5	614.9	608.5	596.9	578.9	554.5	514.6
117.5°	558.8	600.5	627.3	641.2	646.6	651.2	646.6	641.2	627.3	600.5	558.8
120°	586.6	625.2	656.1	674.1	680.5	683.1	680.5	674.1	656.1	625.2	586.6
122.5°	612.3	648.9	678.7	700.9	711.4	714.0	711.4	700.9	678.7	648.9	612.3
125°	648.4	683.1	714.0	735.8	747.4	753.9	747.4	735.8	714.0	683.1	648.4
127.5°	679.8	717.3	745.6	765.4	776.8	781.9	776.8	765.4	745.6	717.3	679.8
130°	697.3	735.8	764.1	786.0	796.3	801.5	796.3	786.0	764.1	735.8	697.3
132.5°	710.6	751.3	780.6	800.4	811.7	816.9	811.7	800.4	780.6	751.3	710.6
135°	726.8	769.3	800.2	819.5	829.8	834.9	829.8	819.5	800.2	769.3	726.8
137.5°	741.0	779.6	811.7	832.1	841.3	844.7	841.3	832.1	811.7	779.6	741.0
140°	751.3	784.7	816.9	836.2	846.5	847.8	846.5	836.2	816.9	784.7	751.3
142.5°	764.7	790.9	819.0	838.2	848.5	850.9	848.5	838.2	819.0	790.9	764.7
145°	788.6	804.0	823.3	841.3	850.3	852.9	850.3	841.3	823.3	804.0	788.6
147.5°	818.7	823.6	833.6	845.5	854.2	856.0	854.2	845.5	833.6	823.6	818.7
150°	841.3	840.1	843.9	851.6	859.3	858.1	859.3	851.6	843.9	840.1	841.3
152.5°	867.1	859.6	859.3	862.9	866.6	866.3	866.6	862.9	859.3	859.6	867.1
155°	910.8	896.7	888.9	886.4	886.4	885.1	886.4	886.4	888.9	896.7	910.8
157.5°	958.9	939.1	927.5	921.4	919.6	916.7	919.6	921.4	927.5	939.1	958.9
160°	991.9	970.0	958.4	948.1	944.3	940.4	944.3	948.1	958.4	970.0	991.9
162.5°	1022.7	1001.9	989.3	980.0	976.2	970.2	976.2	980.0	989.3	1001.9	1022.7
165°	1072.9	1051.0	1036.9	1029.2	1024.0	1018.9	1024.0	1029.2	1036.9	1051.0	1072.9
167.5°	1123.1	1099.1	1089.9	1081.1	1076.2	1067.0	1076.2	1081.1	1089.9	1099.1	1123.1
170°	1153.9	1132.1	1126.9	1119.2	1110.2	1099.9	1110.2	1119.2	1126.9	1132.1	1153.9
172.5°	1180.7	1166.0	1160.9	1153.2	1150.3	1142.1	1150.3	1153.2	1160.9	1166.0	1180.7
175°	1219.6	1208.0	1208.0	1206.7	1202.8	1195.1	1202.8	1206.7	1208.0	1208.0	1219.6
177.5°	1252.0	1245.8	1249.9	1249.9	1248.9	1241.7	1248.9	1249.9	1249.9	1245.8	1252.0
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	9072.5	9072.5	9072.5	9072.5
2.5°	9014.1	9044.6	9051.5	9058.4
5°	8688.9	8715.0	8720.8	8726.5
7.5°	8037.5	8050.9	8046.0	8041.2
10°	7464.1	7482.4	7469.5	7456.6
12.5°	6778.3	6795.0	6803.3	6811.5
15°	5713.6	5759.7	5789.8	5819.8
17.5°	4679.7	4710.9	4699.3	4687.7
20°	4009.7	4029.2	4025.6	4022.0
22.5°	3462.1	3487.8	3487.1	3486.4
25°	2769.3	2786.5	2788.7	2790.8
27.5°	2256.2	2270.9	2279.8	2288.6
30°	2008.6	2023.3	2030.4	2037.6
32.5°	1799.6	1812.8	1812.5	1812.2
35°	1510.7	1521.5	1517.2	1512.9
37.5°	1244.8	1253.7	1249.7	1245.7
40°	1071.4	1077.6	1074.8	1071.9
42.5°	902.7	906.7	894.6	882.6
45°	646.5	629.5	591.6	553.7
47.5°	422.8	385.1	332.5	280.0
50°	296.1	250.0	213.5	177.0
52.5°	217.2	173.3	154.6	135.8
55°	135.2	110.9	103.7	96.6
57.5°	91.7	82.7	78.7	74.7
60°	74.6	70.1	67.2	64.4
62.5°	63.4	61.4	59.7	57.9
65°	51.5	51.3	50.6	49.9
67.5°	44.0	43.9	43.2	42.5
70°	39.7	40.1	39.3	38.6
72.5°	34.5	34.9	34.2	33.5
75°	27.4	27.4	27.4	27.4
77.5°	21.0	21.5	21.4	21.2
80°	17.2	17.5	16.8	16.1
82.5°	13.3	13.8	13.7	13.5
85°	7.5	8.0	8.0	8.0
87.5°	7.2	5.4	4.4	3.3
90°	23.2	14.2	9.0	3.9
92.5°	49.9	34.7	24.4	14.2
95°	100.3	79.8	56.6	39.9
97.5°	159.8	126.6	103.7	76.2
100°	191.7	159.5	137.6	108.1
102.5°	226.7	199.7	169.6	140.0
105°	289.5	256.0	221.3	187.8
107.5°	347.6	310.8	269.1	239.0
110°	384.6	344.8	301.0	274.0



TEST NUMBER: P1428632

CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	420.7	379.8	335.0	308.0
115°	469.6	424.5	383.4	360.2
117.5°	516.6	470.3	426.8	408.6
120°	545.5	499.1	456.7	442.5
122.5°	569.1	523.8	484.5	478.6
125°	604.6	558.3	524.9	532.6
127.5°	633.4	591.0	569.9	587.1
130°	650.9	613.6	600.8	625.2
132.5°	666.4	637.3	631.6	665.4
135°	689.5	672.8	678.0	724.3
137.5°	717.1	710.6	727.9	786.3
140°	734.6	738.4	762.9	828.5
142.5°	758.2	767.2	798.9	868.6
145°	795.0	814.3	855.5	925.0
147.5°	836.7	861.7	912.6	983.9
150°	864.5	896.7	950.7	1018.9
152.5°	896.4	929.6	983.6	1052.8
155°	945.5	982.8	1039.4	1098.6
157.5°	995.7	1033.8	1087.8	1139.5
160°	1026.6	1067.8	1116.6	1164.2
162.5°	1061.6	1099.7	1142.4	1184.8
165°	1112.8	1143.7	1178.4	1214.4
167.5°	1155.7	1181.5	1208.7	1236.8
170°	1183.5	1204.1	1227.3	1249.1
172.5°	1207.2	1223.7	1240.7	1259.4
175°	1238.8	1247.9	1258.1	1269.7
177.5°	1263.3	1266.4	1269.5	1274.6
180°	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1428632
 CATALOG NUMBER: SQ2W-WBN-K-100U-125D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.31	5.03	5.23	5.94	7.10	3.93	4.65	4.86	5.56	6.72
	3H	5.53	6.17	6.47	7.09	8.28	5.14	5.78	6.07	6.70	7.88
	4H	6.05	6.65	7.00	7.58	8.77	5.66	6.26	6.60	7.18	8.38
	6H	6.40	6.96	7.36	7.89	9.09	5.99	6.54	6.94	7.47	8.67
	8H	6.55	7.07	7.51	8.02	9.22	6.12	6.65	7.09	7.59	8.79
	12H	6.64	7.14	7.61	8.08	9.30	6.19	6.69	7.16	7.63	8.85
4H	2H	4.63	5.23	5.58	6.15	7.35	4.32	4.92	5.27	5.84	7.04
	3H	6.12	6.62	7.08	7.57	8.78	5.78	6.28	6.74	7.23	8.44
	4H	6.77	7.22	7.73	8.17	9.40	6.42	6.87	7.38	7.82	9.05
	6H	7.26	7.64	8.24	8.61	9.85	6.87	7.26	7.85	8.23	9.47
	8H	7.47	7.83	8.45	8.79	10.03	7.07	7.43	8.05	8.39	9.64
	12H	7.60	7.92	8.60	8.91	10.15	7.17	7.50	8.17	8.48	9.73
8H	4H	6.93	7.29	7.91	8.25	9.50	6.62	6.98	7.59	7.94	9.18
	6H	7.56	7.86	8.56	8.86	10.11	7.21	7.50	8.21	8.51	9.75
	8H	7.88	8.14	8.89	9.13	10.39	7.50	7.75	8.51	8.75	10.01
	12H	8.11	8.33	9.12	9.32	10.63	7.70	7.92	8.71	8.91	10.22
12H	4H	6.91	7.23	7.90	8.21	9.46	6.60	6.93	7.60	7.91	9.16
	6H	7.60	7.85	8.61	8.85	10.11	7.26	7.51	8.27	8.51	9.77
	8H	7.95	8.17	8.96	9.16	10.47	7.58	7.80	8.59	8.79	10.10