

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428026

Luminaire Tested: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428026  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE PRISM LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5376.8 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	101	101	101	93	93	93	86	86	86	83
1	106	102	98	95	102	98	95	92	91	88	86	84	82	80	78	76	75	72
2	97	90	84	79	93	87	81	77	80	76	72	75	71	68	69	67	64	61
3	89	80	72	67	85	77	70	65	72	66	62	67	62	59	62	59	55	53
4	82	71	63	57	79	69	61	56	64	58	53	60	55	51	56	52	48	46
5	76	64	56	50	72	62	54	49	58	51	46	54	49	44	51	46	42	40
6	70	58	49	44	67	56	48	43	52	46	41	49	44	39	46	41	38	35
7	65	52	44	39	62	51	43	38	48	41	36	45	39	35	42	37	34	31
8	60	48	40	34	58	46	39	34	44	37	33	41	36	31	39	34	30	28
9	56	44	36	31	54	43	35	30	40	34	29	38	32	28	36	31	27	25
10	53	40	33	28	51	39	32	28	37	31	27	35	30	26	33	28	25	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28492	28492	28492	28492
5°	28269	28782	28269	28782
10°	28412	28994	28412	28994
15°	28344	29061	28344	29061
20°	28142	29649	28142	29649
25°	27981	31206	27981	31206
30°	27823	31858	27823	31858
35°	27429	31915	27429	31915
40°	26698	29488	26698	29488
45°	25897	22447	25897	22447
50°	24882	18695	24882	18695
55°	23158	13444	23158	13444
60°	19940	9639	19940	9639
65°	16821	9478	16821	9478
70°	14001	9068	14001	9068
75°	11871	8496	11871	8496
80°	10060	7634	10060	7634
85°	7947	4150	7947	4150

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 28329 cd/sqm



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.0	3.1
10°-20°	486.3	9.0
20°-30°	761.9	14.2
30°-40°	939.9	17.5
40°-50°	884.8	16.5
50°-60°	626.6	11.7
60°-70°	357.0	6.6
70°-80°	176.7	3.3
80°-90°	44.5	0.8
90°-100°	25.4	0.5
100°-110°	74.0	1.4
110°-120°	120.8	2.2
120°-130°	153.3	2.9
130°-140°	164.0	3.0
140°-150°	153.1	2.8
150°-160°	126.0	2.3
160°-170°	84.5	1.6
170°-180°	30.0	0.6
0°-30°	1416.3	26.3
0°-40°	2356.1	43.8
0°-60°	3867.5	71.9
0°-90°	4445.8	82.7
90°-120°	220.2	4.1
90°-150°	690.5	12.8
90°-180°	931.0	17.3
0°-180°	5376.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1765	1765	1765	1765	1765	
5°	1744	1776	1744	1776	1744	166
15°	1696	1739	1696	1739	1696	478
25°	1571	1752	1571	1752	1571	723
35°	1392	1619	1392	1619	1392	868
45°	1134	983	1134	983	1134	873
55°	823	478	823	478	823	726
65°	440	248	440	248	440	442
75°	190	136	190	136	190	206
85°	43	22	43	22	43	50
90°	1	7	1	14	1	3
95°	10	7	10	44	10	12
105°	47	75	47	104	47	50
115°	90	125	90	154	90	89
125°	133	198	133	189	133	119
135°	181	259	181	209	181	140
145°	232	299	232	214	232	145
155°	275	325	275	222	275	126
165°	304	338	304	255	304	86
175°	318	331	318	299	318	30
180°	319	319	319	319	319	



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1751.3	1762.6	1773.9	1771.2	1763.9	1760.9	1762.2	1763.6	1764.9	1766.2	1764.9
5°	1744.2	1758.3	1772.4	1770.3	1762.9	1760.0	1761.6	1764.3	1770.1	1775.9	1770.1
7.5°	1737.5	1751.9	1766.4	1764.5	1757.2	1755.0	1757.8	1761.7	1768.8	1775.9	1768.8
10°	1733.0	1745.5	1757.9	1756.0	1749.4	1748.2	1752.3	1756.9	1762.7	1768.5	1762.7
12.5°	1719.6	1731.4	1743.1	1741.6	1735.6	1735.4	1740.9	1746.2	1751.4	1756.5	1751.4
15°	1695.7	1706.5	1717.3	1717.5	1714.2	1716.2	1723.7	1730.3	1734.5	1738.6	1734.5
17.5°	1663.3	1676.4	1689.5	1692.5	1692.1	1697.3	1707.9	1716.9	1721.2	1725.6	1721.2
20°	1637.9	1653.6	1669.4	1674.6	1676.2	1683.7	1697.0	1709.0	1717.3	1725.6	1717.3
22.5°	1611.0	1629.4	1647.8	1654.7	1657.7	1669.1	1689.0	1707.5	1721.7	1736.0	1721.7
25°	1570.7	1589.0	1607.2	1620.5	1632.1	1652.4	1681.4	1708.6	1730.1	1751.7	1730.1
27.5°	1523.7	1541.8	1559.9	1582.7	1607.0	1635.6	1668.2	1697.0	1714.1	1731.2	1714.1
30°	1492.4	1509.8	1527.2	1553.3	1582.3	1613.8	1647.8	1677.3	1693.0	1708.8	1693.0
32.5°	1453.6	1471.6	1489.7	1517.5	1548.5	1582.3	1619.0	1650.1	1664.5	1678.9	1664.5
35°	1391.6	1409.1	1426.5	1458.8	1496.1	1533.8	1572.0	1602.6	1610.9	1619.2	1610.9
37.5°	1320.4	1340.1	1359.8	1396.1	1437.9	1469.5	1490.9	1507.1	1507.5	1508.0	1507.5
40°	1266.7	1292.4	1318.1	1354.3	1394.1	1416.1	1420.2	1420.7	1409.9	1399.1	1409.9
42.5°	1214.4	1247.4	1280.4	1309.6	1337.4	1343.1	1326.7	1302.4	1254.5	1206.6	1254.5
45°	1134.2	1173.2	1212.1	1230.0	1240.7	1204.3	1120.5	1049.4	1016.3	983.1	1016.3
47.5°	1048.8	1087.2	1125.7	1120.8	1101.4	1046.2	955.1	881.1	858.2	835.4	858.2
50°	990.6	1027.0	1063.5	1037.2	989.9	927.8	850.7	787.4	765.9	744.3	765.9
52.5°	924.9	957.4	989.9	950.1	886.3	820.8	753.6	695.1	662.2	629.4	662.2
55°	822.7	845.1	867.4	823.9	758.4	686.3	607.5	540.6	509.1	477.6	509.1
57.5°	699.6	715.3	731.1	696.8	645.9	574.2	481.7	403.4	368.1	332.8	368.1
60°	617.5	629.9	642.3	611.3	565.7	497.3	406.1	333.3	315.9	298.5	315.9
62.5°	542.9	554.0	565.1	532.7	485.7	424.6	349.3	291.3	285.2	279.1	285.2
65°	440.3	451.0	461.8	427.8	378.9	331.2	284.8	249.8	248.9	248.1	248.9
67.5°	350.3	362.1	373.9	341.9	295.3	260.0	236.2	218.0	217.0	216.0	217.0
70°	296.6	309.0	321.5	291.6	247.7	219.1	205.8	195.5	193.8	192.1	193.8
72.5°	251.8	263.6	275.4	249.4	210.7	187.1	178.5	171.7	170.8	169.8	170.8
75°	190.3	199.4	208.5	189.7	161.5	145.3	141.2	137.8	137.0	136.2	137.0
77.5°	138.0	143.8	149.7	137.3	118.9	108.6	106.5	104.6	103.8	103.0	103.8
80°	108.2	110.7	113.2	104.5	92.0	85.4	84.6	83.7	82.9	82.1	82.9
82.5°	81.3	80.5	79.7	74.6	68.2	64.5	63.7	62.7	61.2	59.7	61.2
85°	42.9	41.2	39.6	37.9	36.3	33.8	30.5	27.4	24.9	22.4	24.9
87.5°	13.6	13.9	14.2	12.0	8.9	6.9	6.3	5.8	5.9	5.9	5.9
90°	1.0	2.3	3.9	5.2	6.1	6.4	6.4	6.8	7.1	7.1	7.1
92.5°	3.5	5.6	5.7	5.7	6.9	7.5	8.0	8.1	8.4	8.4	8.4
95°	10.0	11.0	16.4	16.1	11.0	8.7	7.4	7.4	7.4	7.4	7.4
97.5°	19.1	20.5	21.4	28.7	30.3	29.2	23.8	20.0	17.9	16.9	17.9
100°	27.1	27.7	29.6	30.0	38.0	45.7	41.9	37.0	35.4	34.5	35.4
102.5°	35.0	35.4	38.4	39.7	41.6	46.0	59.4	57.9	56.8	56.6	56.8
105°	47.0	47.3	52.8	55.4	56.7	56.7	56.4	62.8	73.1	75.4	73.1
107.5°	59.8	61.3	67.8	74.7	76.1	76.5	74.9	73.9	73.5	73.8	73.5
110°	68.6	70.9	78.6	87.3	89.5	90.2	89.5	88.6	87.9	87.9	87.9

TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	77.1	80.4	89.2	99.1	102.9	104.9	103.5	102.7	102.1	102.6	102.1
115°	90.2	95.0	106.6	116.9	124.6	125.6	125.3	125.3	125.0	125.0	125.0
117.5°	102.3	110.0	123.0	135.0	144.0	146.5	147.8	147.5	147.1	147.7	147.1
120°	110.8	119.8	134.6	148.2	156.9	160.7	162.0	161.4	162.0	161.4	162.0
122.5°	119.8	130.9	145.5	159.5	169.7	174.1	175.7	175.8	175.9	175.5	175.9
125°	133.3	146.9	163.9	178.4	189.1	194.2	195.5	195.8	196.5	198.1	196.5
127.5°	147.0	162.3	181.1	195.1	205.9	212.2	214.2	214.9	216.2	217.0	216.2
130°	156.5	173.9	192.9	206.1	216.8	223.5	227.1	228.0	229.6	229.3	229.6
132.5°	166.6	184.7	204.0	217.7	227.6	234.9	237.9	240.7	241.2	241.7	241.2
135°	181.3	201.0	220.3	233.8	243.2	250.3	254.1	256.7	258.3	259.3	258.3
137.5°	196.9	217.6	236.2	248.2	257.6	263.7	268.1	270.8	272.5	273.3	272.5
140°	207.4	227.4	245.4	258.0	266.4	272.5	276.3	279.6	281.5	281.5	281.5
142.5°	217.5	237.2	254.7	267.3	274.6	280.2	284.3	286.8	289.0	289.0	289.0
145°	231.6	251.2	267.3	279.9	286.0	291.2	295.7	297.6	298.9	298.9	298.9
147.5°	246.3	263.7	278.4	290.5	295.6	301.7	305.2	306.8	308.4	307.7	308.4
150°	255.1	271.2	285.4	296.6	301.8	307.6	311.1	312.4	314.0	313.1	314.0
152.5°	263.6	278.9	291.8	302.3	306.7	312.5	316.5	317.8	318.9	318.2	318.9
155°	275.1	288.6	300.5	310.2	314.0	319.5	323.4	325.0	326.3	324.7	326.3
157.5°	285.3	297.0	307.3	316.2	320.3	325.0	328.7	330.7	331.9	331.2	331.9
160°	291.5	302.1	311.5	319.8	323.7	327.9	331.7	334.0	335.3	334.3	335.3
162.5°	296.6	306.2	315.1	322.7	326.0	329.7	334.3	336.3	337.6	336.4	337.6
165°	304.0	311.8	319.5	326.0	328.8	331.7	336.6	338.8	339.8	338.5	339.8
167.5°	309.7	315.6	321.8	327.4	329.5	332.3	337.2	339.0	340.3	338.6	340.3
170°	312.7	317.9	323.4	327.9	329.5	332.1	336.9	338.5	339.5	337.9	339.5
172.5°	315.3	319.2	323.6	327.6	328.5	330.5	335.1	336.7	337.4	336.1	337.4
175°	317.9	320.2	323.4	326.0	325.6	326.9	330.8	332.1	333.4	331.4	333.4
177.5°	319.1	320.2	321.2	322.7	321.7	321.7	324.5	325.3	325.6	324.5	325.6
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1763.6	1762.2	1760.9	1763.9	1771.2	1773.9	1762.6	1751.3	1762.6	1773.9	1771.2
5°	1764.3	1761.6	1760.0	1762.9	1770.3	1772.4	1758.3	1744.2	1758.3	1772.4	1770.3
7.5°	1761.7	1757.8	1755.0	1757.2	1764.5	1766.4	1751.9	1737.5	1751.9	1766.4	1764.5
10°	1756.9	1752.3	1748.2	1749.4	1756.0	1757.9	1745.5	1733.0	1745.5	1757.9	1756.0
12.5°	1746.2	1740.9	1735.4	1735.6	1741.6	1743.1	1731.4	1719.6	1731.4	1743.1	1741.6
15°	1730.3	1723.7	1716.2	1714.2	1717.5	1717.3	1706.5	1695.7	1706.5	1717.3	1717.5
17.5°	1716.9	1707.9	1697.3	1692.1	1692.5	1689.5	1676.4	1663.3	1676.4	1689.5	1692.5
20°	1709.0	1697.0	1683.7	1676.2	1674.6	1669.4	1653.6	1637.9	1653.6	1669.4	1674.6
22.5°	1707.5	1689.0	1669.1	1657.7	1654.7	1647.8	1629.4	1611.0	1629.4	1647.8	1654.7
25°	1708.6	1681.4	1652.4	1632.1	1620.5	1607.2	1589.0	1570.7	1589.0	1607.2	1620.5
27.5°	1697.0	1668.2	1635.6	1607.0	1582.7	1559.9	1541.8	1523.7	1541.8	1559.9	1582.7
30°	1677.3	1647.8	1613.8	1582.3	1553.3	1527.2	1509.8	1492.4	1509.8	1527.2	1553.3
32.5°	1650.1	1619.0	1582.3	1548.5	1517.5	1489.7	1471.6	1453.6	1471.6	1489.7	1517.5
35°	1602.6	1572.0	1533.8	1496.1	1458.8	1426.5	1409.1	1391.6	1409.1	1426.5	1458.8
37.5°	1507.1	1490.9	1469.5	1437.9	1396.1	1359.8	1340.1	1320.4	1340.1	1359.8	1396.1
40°	1420.7	1420.2	1416.1	1394.1	1354.3	1318.1	1292.4	1266.7	1292.4	1318.1	1354.3
42.5°	1302.4	1326.7	1343.1	1337.4	1309.6	1280.4	1247.4	1214.4	1247.4	1280.4	1309.6
45°	1049.4	1120.5	1204.3	1240.7	1230.0	1212.1	1173.2	1134.2	1173.2	1212.1	1230.0
47.5°	881.1	955.1	1046.2	1101.4	1120.8	1125.7	1087.2	1048.8	1087.2	1125.7	1120.8
50°	787.4	850.7	927.8	989.9	1037.2	1063.5	1027.0	990.6	1027.0	1063.5	1037.2
52.5°	695.1	753.6	820.8	886.3	950.1	989.9	957.4	924.9	957.4	989.9	950.1
55°	540.6	607.5	686.3	758.4	823.9	867.4	845.1	822.7	845.1	867.4	823.9
57.5°	403.4	481.7	574.2	645.9	696.8	731.1	715.3	699.6	715.3	731.1	696.8
60°	333.3	406.1	497.3	565.7	611.3	642.3	629.9	617.5	629.9	642.3	611.3
62.5°	291.3	349.3	424.6	485.7	532.7	565.1	554.0	542.9	554.0	565.1	532.7
65°	249.8	284.8	331.2	378.9	427.8	461.8	451.0	440.3	451.0	461.8	427.8
67.5°	218.0	236.2	260.0	295.3	341.9	373.9	362.1	350.3	362.1	373.9	341.9
70°	195.5	205.8	219.1	247.7	291.6	321.5	309.0	296.6	309.0	321.5	291.6
72.5°	171.7	178.5	187.1	210.7	249.4	275.4	263.6	251.8	263.6	275.4	249.4
75°	137.8	141.2	145.3	161.5	189.7	208.5	199.4	190.3	199.4	208.5	189.7
77.5°	104.6	106.5	108.6	118.9	137.3	149.7	143.8	138.0	143.8	149.7	137.3
80°	83.7	84.6	85.4	92.0	104.5	113.2	110.7	108.2	110.7	113.2	104.5
82.5°	62.7	63.7	64.5	68.2	74.6	79.7	80.5	81.3	80.5	79.7	74.6
85°	27.4	30.5	33.8	36.3	37.9	39.6	41.2	42.9	41.2	39.6	37.9
87.5°	5.8	6.3	6.9	8.9	12.0	14.2	13.9	13.6	13.9	14.1	12.1
90°	6.8	6.4	6.4	6.1	5.2	3.9	2.3	1.0	2.3	3.5	5.8
92.5°	8.1	8.0	7.5	6.9	5.7	5.7	5.6	3.5	6.1	8.7	12.5
95°	7.4	7.4	8.7	11.0	16.1	16.4	11.0	10.0	14.2	20.0	25.1
97.5°	20.0	23.8	29.2	30.3	28.7	21.4	20.5	19.1	26.0	31.7	40.0
100°	37.0	41.9	45.7	38.0	30.0	29.6	27.7	27.1	34.5	39.9	48.0
102.5°	57.9	59.4	46.0	41.6	39.7	38.4	35.4	35.0	42.5	50.0	56.8
105°	62.8	56.4	56.7	56.7	55.4	52.8	47.3	47.0	55.4	64.1	72.5
107.5°	73.9	74.9	76.5	76.1	74.7	67.8	61.3	59.8	67.4	77.8	87.0
110°	88.6	89.5	90.2	89.5	87.3	78.6	70.9	68.6	75.4	86.3	96.3



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	102.7	103.5	104.9	102.9	99.1	89.2	80.4	77.1	83.9	95.1	105.3
115°	125.3	125.3	125.6	124.6	116.9	106.6	95.0	90.2	96.0	106.3	117.6
117.5°	147.5	147.8	146.5	144.0	135.0	123.0	110.0	102.3	106.9	117.8	129.3
120°	161.4	162.0	160.7	156.9	148.2	134.6	119.8	110.8	114.3	125.0	136.6
122.5°	175.8	175.7	174.1	169.7	159.5	145.5	130.9	119.8	121.3	131.2	142.5
125°	195.8	195.5	194.2	189.1	178.4	163.9	146.9	133.3	131.4	139.8	151.4
127.5°	214.9	214.2	212.2	205.9	195.1	181.1	162.3	147.0	142.7	148.0	158.6
130°	228.0	227.1	223.5	216.8	206.1	192.9	173.9	156.5	150.4	153.6	163.0
132.5°	240.7	237.9	234.9	227.6	217.7	204.0	184.7	166.6	158.1	159.6	166.8
135°	256.7	254.1	250.3	243.2	233.8	220.3	201.0	181.3	169.7	168.5	172.6
137.5°	270.8	268.1	263.7	257.6	248.2	236.2	217.6	196.9	182.2	177.9	179.5
140°	279.6	276.3	272.5	266.4	258.0	245.4	227.4	207.4	191.0	184.9	183.9
142.5°	286.8	284.3	280.2	274.6	267.3	254.7	237.2	217.5	200.0	192.1	189.8
145°	297.6	295.7	291.2	286.0	279.9	267.3	251.2	231.6	214.2	203.9	199.0
147.5°	306.8	305.2	301.7	295.6	290.5	278.4	263.7	246.3	228.5	215.7	209.5
150°	312.4	311.1	307.6	301.8	296.6	285.4	271.2	255.1	238.0	224.5	216.4
152.5°	317.8	316.5	312.5	306.7	302.3	291.8	278.9	263.6	246.3	232.7	224.4
155°	325.0	323.4	319.5	314.0	310.2	300.5	288.6	275.1	260.2	246.1	236.7
157.5°	330.7	328.7	325.0	320.3	316.2	307.3	297.0	285.3	272.4	258.8	249.3
160°	334.0	331.7	327.9	323.7	319.8	311.5	302.1	291.5	279.6	267.3	257.0
162.5°	336.3	334.3	329.7	326.0	322.7	315.1	306.2	296.6	286.0	275.3	265.8
165°	338.8	336.6	331.7	328.8	326.0	319.5	311.8	304.0	295.0	286.3	278.6
167.5°	339.0	337.2	332.3	329.5	327.4	321.8	315.6	309.7	302.6	295.8	289.4
170°	338.5	336.9	332.1	329.5	327.9	323.4	317.9	312.7	307.3	301.5	296.3
172.5°	336.7	335.1	330.5	328.5	327.6	323.6	319.2	315.3	310.6	306.4	302.2
175°	332.1	330.8	326.9	325.6	326.0	323.4	320.2	317.9	315.0	312.4	310.2
177.5°	325.3	324.5	321.7	321.7	322.7	321.2	320.2	319.1	317.8	317.1	316.3
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1763.9	1760.9	1762.2	1763.6	1764.9	1766.2	1764.9	1763.6	1762.2	1760.9	1763.9
5°	1762.9	1760.0	1761.6	1764.3	1770.1	1775.9	1770.1	1764.3	1761.6	1760.0	1762.9
7.5°	1757.2	1755.0	1757.8	1761.7	1768.8	1775.9	1768.8	1761.7	1757.8	1755.0	1757.2
10°	1749.4	1748.2	1752.3	1756.9	1762.7	1768.5	1762.7	1756.9	1752.3	1748.2	1749.4
12.5°	1735.6	1735.4	1740.9	1746.2	1751.4	1756.5	1751.4	1746.2	1740.9	1735.4	1735.6
15°	1714.2	1716.2	1723.7	1730.3	1734.5	1738.6	1734.5	1730.3	1723.7	1716.2	1714.2
17.5°	1692.1	1697.3	1707.9	1716.9	1721.2	1725.6	1721.2	1716.9	1707.9	1697.3	1692.1
20°	1676.2	1683.7	1697.0	1709.0	1717.3	1725.6	1717.3	1709.0	1697.0	1683.7	1676.2
22.5°	1657.7	1669.1	1689.0	1707.5	1721.7	1736.0	1721.7	1707.5	1689.0	1669.1	1657.7
25°	1632.1	1652.4	1681.4	1708.6	1730.1	1751.7	1730.1	1708.6	1681.4	1652.4	1632.1
27.5°	1607.0	1635.6	1668.2	1697.0	1714.1	1731.2	1714.1	1697.0	1668.2	1635.6	1607.0
30°	1582.3	1613.8	1647.8	1677.3	1693.0	1708.8	1693.0	1677.3	1647.8	1613.8	1582.3
32.5°	1548.5	1582.3	1619.0	1650.1	1664.5	1678.9	1664.5	1650.1	1619.0	1582.3	1548.5
35°	1496.1	1533.8	1572.0	1602.6	1610.9	1619.2	1610.9	1602.6	1572.0	1533.8	1496.1
37.5°	1437.9	1469.5	1490.9	1507.1	1507.5	1508.0	1507.5	1507.1	1490.9	1469.5	1437.9
40°	1394.1	1416.1	1420.2	1420.7	1409.9	1399.1	1409.9	1420.7	1420.2	1416.1	1394.1
42.5°	1337.4	1343.1	1326.7	1302.4	1254.5	1206.6	1254.5	1302.4	1326.7	1343.1	1337.4
45°	1240.7	1204.3	1120.5	1049.4	1016.3	983.1	1016.3	1049.4	1120.5	1204.3	1240.7
47.5°	1101.4	1046.2	955.1	881.1	858.2	835.4	858.2	881.1	955.1	1046.2	1101.4
50°	989.9	927.8	850.7	787.4	765.9	744.3	765.9	787.4	850.7	927.8	989.9
52.5°	886.3	820.8	753.6	695.1	662.2	629.4	662.2	695.1	753.6	820.8	886.3
55°	758.4	686.3	607.5	540.6	509.1	477.6	509.1	540.6	607.5	686.3	758.4
57.5°	645.9	574.2	481.7	403.4	368.1	332.8	368.1	403.4	481.7	574.2	645.9
60°	565.7	497.3	406.1	333.3	315.9	298.5	315.9	333.3	406.1	497.3	565.7
62.5°	485.7	424.6	349.3	291.3	285.2	279.1	285.2	291.3	349.3	424.6	485.7
65°	378.9	331.2	284.8	249.8	248.9	248.1	248.9	249.8	284.8	331.2	378.9
67.5°	295.3	260.0	236.2	218.0	217.0	216.0	217.0	218.0	236.2	260.0	295.3
70°	247.7	219.1	205.8	195.5	193.8	192.1	193.8	195.5	205.8	219.1	247.7
72.5°	210.7	187.1	178.5	171.7	170.8	169.8	170.8	171.7	178.5	187.1	210.7
75°	161.5	145.3	141.2	137.8	137.0	136.2	137.0	137.8	141.2	145.3	161.5
77.5°	118.9	108.6	106.5	104.6	103.8	103.0	103.8	104.6	106.5	108.6	118.9
80°	92.0	85.4	84.6	83.7	82.9	82.1	82.9	83.7	84.6	85.4	92.0
82.5°	68.2	64.5	63.7	62.7	61.2	59.7	61.2	62.7	63.7	64.5	68.2
85°	36.3	33.8	30.5	27.4	24.9	22.4	24.9	27.4	30.5	33.8	36.3
87.5°	9.1	7.6	7.4	7.1	7.4	7.2	7.4	7.1	7.4	7.6	9.1
90°	7.4	9.7	11.9	13.2	14.5	13.8	14.5	13.2	11.9	9.7	7.4
92.5°	14.9	18.7	21.5	23.8	24.8	24.7	24.8	23.8	21.5	18.7	14.9
95°	30.0	34.5	39.0	42.2	44.1	43.5	44.1	42.2	39.0	34.5	30.0
97.5°	46.2	52.2	57.3	60.3	62.2	63.5	62.2	60.3	57.3	52.2	46.2
100°	57.0	62.8	68.6	72.1	75.4	76.7	75.4	72.1	68.6	62.8	57.0
102.5°	65.8	73.4	79.7	83.5	86.2	87.5	86.2	83.5	79.7	73.4	65.8
105°	80.2	88.3	95.0	99.8	102.7	103.7	102.7	99.8	95.0	88.3	80.2
107.5°	94.6	102.9	109.2	114.5	118.1	120.1	118.1	114.5	109.2	102.9	94.6
110°	106.0	112.7	119.5	124.3	127.9	129.2	127.9	124.3	119.5	112.7	106.0



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	115.5	123.0	129.8	134.6	138.7	140.5	138.7	134.6	129.8	123.0	115.5
115°	128.8	138.8	144.9	149.4	152.3	154.0	152.3	149.4	144.9	138.8	128.8
117.5°	139.9	150.3	157.0	160.5	161.9	163.0	161.9	160.5	157.0	150.3	139.9
120°	146.9	156.5	164.3	168.8	170.4	171.0	170.4	168.8	164.3	156.5	146.9
122.5°	153.3	162.5	169.9	175.5	178.1	178.8	178.1	175.5	169.9	162.5	153.3
125°	162.3	171.0	178.8	184.2	187.1	188.7	187.1	184.2	178.8	171.0	162.3
127.5°	170.2	179.6	186.7	191.6	194.5	195.8	194.5	191.6	186.7	179.6	170.2
130°	174.6	184.2	191.3	196.8	199.4	200.7	199.4	196.8	191.3	184.2	174.6
132.5°	177.9	188.1	195.4	200.4	203.2	204.5	203.2	200.4	195.4	188.1	177.9
135°	182.0	192.6	200.3	205.2	207.7	209.0	207.7	205.2	200.3	192.6	182.0
137.5°	185.5	195.2	203.2	208.3	210.6	211.5	210.6	208.3	203.2	195.2	185.5
140°	188.1	196.5	204.5	209.4	211.9	212.3	211.9	209.4	204.5	196.5	188.1
142.5°	191.4	198.0	205.0	209.9	212.4	213.0	212.4	209.9	205.0	198.0	191.4
145°	197.4	201.3	206.1	210.6	212.9	213.5	212.9	210.6	206.1	201.3	197.4
147.5°	205.0	206.2	208.7	211.7	213.9	214.3	213.9	211.7	208.7	206.2	205.0
150°	210.6	210.3	211.3	213.2	215.2	214.8	215.2	213.2	211.3	210.3	210.6
152.5°	217.1	215.2	215.2	216.1	217.0	216.9	217.0	216.1	215.2	215.2	217.1
155°	228.0	224.5	222.6	221.9	221.9	221.6	221.9	221.9	222.6	224.5	228.0
157.5°	240.1	235.1	232.2	230.7	230.2	229.5	230.2	230.7	232.2	235.1	240.1
160°	248.3	242.9	240.0	237.4	236.4	235.4	236.4	237.4	240.0	242.9	248.3
162.5°	256.1	250.8	247.7	245.4	244.4	242.9	244.4	245.4	247.7	250.8	256.1
165°	268.6	263.1	259.6	257.7	256.4	255.1	256.4	257.7	259.6	263.1	268.6
167.5°	281.2	275.2	272.9	270.7	269.5	267.1	269.5	270.7	272.9	275.2	281.2
170°	288.9	283.4	282.1	280.2	278.0	275.4	278.0	280.2	282.1	283.4	288.9
172.5°	295.6	291.9	290.6	288.7	288.0	285.9	288.0	288.7	290.6	291.9	295.6
175°	305.3	302.4	302.4	302.1	301.1	299.2	301.1	302.1	302.4	302.4	305.3
177.5°	313.5	311.9	312.9	312.9	312.7	310.9	312.7	312.9	312.9	311.9	313.5
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1764.7	1764.7	1764.7	1764.7
2.5°	1771.2	1773.9	1762.6	1751.3
5°	1770.3	1772.4	1758.3	1744.2
7.5°	1764.5	1766.4	1751.9	1737.5
10°	1756.0	1757.9	1745.5	1733.0
12.5°	1741.6	1743.1	1731.4	1719.6
15°	1717.5	1717.3	1706.5	1695.7
17.5°	1692.5	1689.5	1676.4	1663.3
20°	1674.6	1669.4	1653.6	1637.9
22.5°	1654.7	1647.8	1629.4	1611.0
25°	1620.5	1607.2	1589.0	1570.7
27.5°	1582.7	1559.9	1541.8	1523.7
30°	1553.3	1527.2	1509.8	1492.4
32.5°	1517.5	1489.7	1471.6	1453.6
35°	1458.8	1426.5	1409.1	1391.6
37.5°	1396.1	1359.8	1340.1	1320.4
40°	1354.3	1318.1	1292.4	1266.7
42.5°	1309.6	1280.4	1247.4	1214.4
45°	1230.0	1212.1	1173.2	1134.2
47.5°	1120.8	1125.7	1087.2	1048.8
50°	1037.2	1063.5	1027.0	990.6
52.5°	950.1	989.9	957.4	924.9
55°	823.9	867.4	845.1	822.7
57.5°	696.8	731.1	715.3	699.6
60°	611.3	642.3	629.9	617.5
62.5°	532.7	565.1	554.0	542.9
65°	427.8	461.8	451.0	440.3
67.5°	341.9	373.9	362.1	350.3
70°	291.6	321.5	309.0	296.6
72.5°	249.4	275.4	263.6	251.8
75°	189.7	208.5	199.4	190.3
77.5°	137.3	149.7	143.8	138.0
80°	104.5	113.2	110.7	108.2
82.5°	74.6	79.7	80.5	81.3
85°	37.9	39.6	41.2	42.9
87.5°	12.1	14.1	13.9	13.6
90°	5.8	3.5	2.3	1.0
92.5°	12.5	8.7	6.1	3.5
95°	25.1	20.0	14.2	10.0
97.5°	40.0	31.7	26.0	19.1
100°	48.0	39.9	34.5	27.1
102.5°	56.8	50.0	42.5	35.0
105°	72.5	64.1	55.4	47.0
107.5°	87.0	77.8	67.4	59.8
110°	96.3	86.3	75.4	68.6



TEST NUMBER: P1428026

CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	105.3	95.1	83.9	77.1
115°	117.6	106.3	96.0	90.2
117.5°	129.3	117.8	106.9	102.3
120°	136.6	125.0	114.3	110.8
122.5°	142.5	131.2	121.3	119.8
125°	151.4	139.8	131.4	133.3
127.5°	158.6	148.0	142.7	147.0
130°	163.0	153.6	150.4	156.5
132.5°	166.8	159.6	158.1	166.6
135°	172.6	168.5	169.7	181.3
137.5°	179.5	177.9	182.2	196.9
140°	183.9	184.9	191.0	207.4
142.5°	189.8	192.1	200.0	217.5
145°	199.0	203.9	214.2	231.6
147.5°	209.5	215.7	228.5	246.3
150°	216.4	224.5	238.0	255.1
152.5°	224.4	232.7	246.3	263.6
155°	236.7	246.1	260.2	275.1
157.5°	249.3	258.8	272.4	285.3
160°	257.0	267.3	279.6	291.5
162.5°	265.8	275.3	286.0	296.6
165°	278.6	286.3	295.0	304.0
167.5°	289.4	295.8	302.6	309.7
170°	296.3	301.5	307.3	312.7
172.5°	302.2	306.4	310.6	315.3
175°	310.2	312.4	315.0	317.9
177.5°	316.3	317.1	317.8	319.1
180°	318.9	318.9	318.9	318.9



TEST NUMBER: P1428026  
 CATALOG NUMBER: SQ2W-PP3-K-025U-100D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.74	22.94	22.36	23.56	24.28	17.51	18.71	18.13	19.33	20.05
	3H	22.83	23.90	23.46	24.53	25.29	18.85	19.92	19.48	20.55	21.31
	4H	23.21	24.22	23.87	24.87	25.63	19.42	20.42	20.08	21.07	21.84
	6H	23.42	24.35	24.09	25.01	25.79	19.80	20.73	20.47	21.39	22.17
	8H	23.49	24.37	24.17	25.06	25.84	19.94	20.82	20.62	21.50	22.28
	12H	23.53	24.36	24.21	25.04	25.85	19.99	20.82	20.67	21.50	22.31
4H	2H	21.90	22.91	22.56	23.56	24.32	18.46	19.47	19.12	20.12	20.88
	3H	23.23	24.06	23.90	24.75	25.53	19.92	20.75	20.59	21.44	22.22
	4H	23.75	24.50	24.44	25.19	26.01	20.55	21.30	21.24	21.99	22.81
	6H	24.08	24.73	24.79	25.45	26.27	21.02	21.66	21.72	22.38	23.21
	8H	24.20	24.80	24.91	25.52	26.35	21.19	21.80	21.90	22.51	23.35
	12H	24.26	24.80	24.99	25.54	26.38	21.26	21.80	21.99	22.54	23.38
8H	4H	23.79	24.40	24.50	25.11	25.95	20.88	21.49	21.60	22.21	23.04
	6H	24.22	24.72	24.96	25.48	26.31	21.46	21.96	22.20	22.72	23.55
	8H	24.40	24.84	25.15	25.61	26.46	21.70	22.15	22.46	22.91	23.77
	12H	24.51	24.90	25.26	25.65	26.57	21.82	22.21	22.57	22.96	23.88
12H	4H	23.77	24.31	24.50	25.05	25.89	20.91	21.45	21.64	22.20	23.04
	6H	24.21	24.66	24.96	25.42	26.27	21.52	21.97	22.28	22.73	23.59
	8H	24.42	24.81	25.17	25.56	26.48	21.81	22.21	22.57	22.96	23.87