

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428650

Luminaire Tested: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428650
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8750.7 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 82.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36				
1	96	93	89	87	87	84	82	79	69	67	65	54	53	52	41	40	40	34				
2	89	83	78	74	81	76	72	68	62	59	57	50	48	46	38	37	36	31				
3	83	75	69	64	75	69	64	59	57	53	50	46	44	42	36	35	33	29				
4	77	68	61	56	70	62	57	52	52	48	45	43	40	38	34	32	31	27				
5	72	62	55	50	65	57	51	47	48	44	41	39	37	35	32	30	29	25				
6	67	56	50	45	61	52	46	42	44	40	37	37	34	32	30	28	27	24				
7	62	52	45	40	57	48	42	38	41	37	34	34	31	29	28	26	25	22				
8	59	48	41	37	54	45	39	35	38	34	31	32	29	27	27	25	23	21				
9	55	44	38	34	51	41	36	32	36	32	29	30	27	25	25	23	22	20				
10	52	41	35	31	48	39	33	29	34	29	27	29	26	24	24	22	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	87598	87598	87598	87598
5°	84577	84671	84577	84671
10°	73105	73279	73105	73279
15°	58174	56566	58174	56566
20°	41326	41078	41326	41078
25°	29731	28943	29731	28943
30°	22717	22053	22717	22053
35°	17832	17073	17832	17073
40°	13510	12678	13510	12678
45°	7560	6747	7560	6747
50°	2660	2346	2660	2346
55°	1624	1545	1624	1545
60°	1243	1150	1243	1150
65°	1138	1066	1138	1066
70°	1090	1001	1090	1001
75°	1023	961	1023	961
80°	893	893	893	893
85°	889	704	889	704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 8964 cd/sqm



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	471.0	5.4
10°-20°	936.0	10.7
20°-30°	775.2	8.9
30°-40°	557.6	6.4
40°-50°	284.1	3.2
50°-60°	73.9	0.8
60°-70°	30.7	0.4
70°-80°	17.0	0.2
80°-90°	13.0	0.1
90°-100°	152.4	1.7
100°-110°	444.5	5.1
110°-120°	725.4	8.3
120°-130°	920.5	10.5
130°-140°	985.0	11.3
140°-150°	919.8	10.5
150°-160°	756.8	8.6
160°-170°	507.6	5.8
170°-180°	180.2	2.1
0°-30°	2182.1	24.9
0°-40°	2739.8	31.3
0°-60°	3097.7	35.4
0°-90°	3158.4	36.1
90°-120°	1322.4	15.1
90°-150°	4147.7	47.4
90°-180°	5592.0	63.9
0°-180°	8750.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5426	5426	5426	5426	5426	
5°	5218	5224	5218	5224	5218	471
15°	3480	3384	3480	3384	3480	945
25°	1669	1625	1669	1625	1669	785
35°	905	866	905	866	905	568
45°	331	296	331	296	331	265
55°	58	55	58	55	58	57
65°	30	28	30	28	30	30
75°	16	15	16	15	16	17
85°	5	4	5	4	5	5
90°	6	43	6	83	6	5
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5
2.5°	5417.0	5412.9	5408.8	5390.6	5367.6	5365.8	5384.9	5398.1	5393.3	5388.5	5393.3
5°	5218.5	5215.1	5211.7	5196.1	5176.4	5183.3	5216.6	5239.7	5232.0	5224.3	5232.0
7.5°	4808.7	4811.6	4814.5	4806.5	4794.9	4803.8	4833.4	4853.4	4845.2	4837.0	4845.2
10°	4459.1	4466.8	4474.5	4463.6	4446.5	4459.6	4502.8	4527.9	4498.8	4469.7	4498.8
12.5°	4073.4	4068.4	4063.5	4053.5	4041.9	4039.5	4046.4	4047.6	4031.5	4015.4	4031.5
15°	3480.3	3462.3	3444.4	3416.8	3386.0	3375.9	3386.6	3393.5	3388.8	3384.1	3388.8
17.5°	2803.3	2810.2	2817.2	2798.5	2771.3	2757.2	2756.1	2754.0	2748.7	2743.4	2748.7
20°	2405.2	2407.4	2409.5	2397.8	2381.6	2377.7	2386.3	2392.5	2391.6	2390.8	2391.6
22.5°	2084.9	2085.3	2085.8	2070.3	2049.6	2045.6	2058.3	2065.9	2058.2	2050.5	2058.2
25°	1668.9	1667.6	1666.4	1656.1	1642.8	1633.0	1626.6	1622.1	1623.4	1624.7	1623.4
27.5°	1368.6	1363.3	1358.0	1349.3	1339.3	1336.5	1340.8	1343.2	1340.0	1336.9	1340.0
30°	1218.5	1214.2	1209.9	1201.2	1190.9	1187.1	1189.6	1190.6	1186.7	1182.9	1186.7
32.5°	1083.7	1083.9	1084.1	1076.2	1065.6	1059.7	1058.5	1056.9	1054.0	1051.2	1054.0
35°	904.7	907.3	909.9	903.4	894.0	886.1	879.7	873.9	870.1	866.2	870.1
37.5°	745.0	747.4	749.7	744.4	736.4	727.7	718.3	710.5	707.2	704.0	707.2
40°	641.0	642.7	644.4	640.7	635.1	626.8	615.7	606.7	604.1	601.5	604.1
42.5°	527.8	535.0	542.2	539.8	534.3	526.3	515.8	506.6	500.9	495.3	500.9
45°	331.1	353.8	376.4	386.6	392.6	389.8	378.3	361.4	328.4	295.5	328.4
47.5°	167.5	198.9	230.3	252.8	272.4	266.2	234.1	201.9	169.6	137.2	169.6
50°	105.9	127.7	149.5	177.1	206.6	200.2	157.8	122.4	107.9	93.4	107.9
52.5°	81.2	92.4	103.6	129.9	161.1	158.1	120.9	91.0	82.9	74.9	82.9
55°	57.7	62.0	66.3	80.8	98.8	97.7	77.6	61.7	58.3	54.9	58.3
57.5°	44.7	47.1	49.4	54.9	61.3	60.7	53.1	46.8	44.7	42.5	44.7
60°	38.5	40.2	41.9	44.6	47.6	47.2	43.3	39.9	37.8	35.6	37.8
62.5°	34.6	35.7	36.7	37.9	39.2	38.6	36.1	34.1	33.3	32.5	33.3
65°	29.8	30.3	30.7	30.8	30.8	30.4	29.5	28.8	28.3	27.9	28.3
67.5°	25.4	25.8	26.3	26.3	26.2	26.0	25.5	25.1	24.7	24.3	24.7
70°	23.1	23.5	24.0	23.7	23.3	22.9	22.5	22.0	21.6	21.2	21.6
72.5°	20.0	20.4	20.9	20.7	20.2	20.0	19.9	19.7	19.3	18.9	19.3
75°	16.4	16.4	16.4	16.4	16.4	16.1	15.7	15.4	15.4	15.4	15.4
77.5°	12.7	12.8	12.9	12.6	12.1	11.9	11.9	11.8	11.5	11.2	11.5
80°	9.6	10.1	10.5	10.3	9.8	9.6	9.6	9.6	9.6	9.6	9.6
82.5°	8.1	8.2	8.3	8.0	7.5	7.3	7.3	7.3	7.3	7.3	7.3
85°	4.8	4.8	4.8	4.5	4.1	4.1	4.5	4.7	4.3	3.8	4.3
87.5°	2.7	4.2	6.2	7.7	8.9	9.3	9.3	9.7	10.1	10.1	10.1
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5
2.5°	5398.1	5384.9	5365.8	5367.6	5390.6	5408.8	5412.9	5417.0	5412.9	5408.8	5390.6
5°	5239.7	5216.6	5183.3	5176.4	5196.1	5211.7	5215.1	5218.5	5215.1	5211.7	5196.1
7.5°	4853.4	4833.4	4803.8	4794.9	4806.5	4814.5	4811.6	4808.7	4811.6	4814.5	4806.5
10°	4527.9	4502.8	4459.6	4446.5	4463.6	4474.5	4466.8	4459.1	4466.8	4474.5	4463.6
12.5°	4047.6	4046.4	4039.5	4041.9	4053.5	4063.5	4068.4	4073.4	4068.4	4063.5	4053.5
15°	3393.5	3386.6	3375.9	3386.0	3416.8	3444.4	3462.3	3480.3	3462.3	3444.4	3416.8
17.5°	2754.0	2756.1	2757.2	2771.3	2798.5	2817.2	2810.2	2803.3	2810.2	2817.2	2798.5
20°	2392.5	2386.3	2377.7	2381.6	2397.8	2409.5	2407.4	2405.2	2407.4	2409.5	2397.8
22.5°	2065.9	2058.3	2045.6	2049.6	2070.3	2085.8	2085.3	2084.9	2085.3	2085.8	2070.3
25°	1622.1	1626.6	1633.0	1642.8	1656.1	1666.4	1667.6	1668.9	1667.6	1666.4	1656.1
27.5°	1343.2	1340.8	1336.5	1339.3	1349.3	1358.0	1363.3	1368.6	1363.3	1358.0	1349.3
30°	1190.6	1189.6	1187.1	1190.9	1201.2	1209.9	1214.2	1218.5	1214.2	1209.9	1201.2
32.5°	1056.9	1058.5	1059.7	1065.6	1076.2	1084.1	1083.9	1083.7	1083.9	1084.1	1076.2
35°	873.9	879.7	886.1	894.0	903.4	909.9	907.3	904.7	907.3	909.9	903.4
37.5°	710.5	718.3	727.7	736.4	744.4	749.7	747.4	745.0	747.4	749.7	744.4
40°	606.7	615.7	626.8	635.1	640.7	644.4	642.7	641.0	642.7	644.4	640.7
42.5°	506.6	515.8	526.3	534.3	539.8	542.2	535.0	527.8	535.0	542.2	539.8
45°	361.4	378.3	389.8	392.6	386.6	376.4	353.8	331.1	353.8	376.4	386.6
47.5°	201.9	234.1	266.2	272.4	252.8	230.3	198.9	167.5	198.9	230.3	252.8
50°	122.4	157.8	200.2	206.6	177.1	149.5	127.7	105.9	127.7	149.5	177.1
52.5°	91.0	120.9	158.1	161.1	129.9	103.6	92.4	81.2	92.4	103.6	129.9
55°	61.7	77.6	97.7	98.8	80.8	66.3	62.0	57.7	62.0	66.3	80.8
57.5°	46.8	53.1	60.7	61.3	54.9	49.4	47.1	44.7	47.1	49.4	54.9
60°	39.9	43.3	47.2	47.6	44.6	41.9	40.2	38.5	40.2	41.9	44.6
62.5°	34.1	36.1	38.6	39.2	37.9	36.7	35.7	34.6	35.7	36.7	37.9
65°	28.8	29.5	30.4	30.8	30.8	30.7	30.3	29.8	30.3	30.7	30.8
67.5°	25.1	25.5	26.0	26.2	26.3	26.3	25.8	25.4	25.8	26.3	26.3
70°	22.0	22.5	22.9	23.3	23.7	24.0	23.5	23.1	23.5	24.0	23.7
72.5°	19.7	19.9	20.0	20.2	20.7	20.9	20.4	20.0	20.4	20.9	20.7
75°	15.4	15.7	16.1	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4
77.5°	11.8	11.9	11.9	12.1	12.6	12.9	12.8	12.7	12.8	12.9	12.6
80°	9.6	9.6	9.6	9.8	10.3	10.5	10.1	9.6	10.1	10.5	10.3
82.5°	7.3	7.3	7.3	7.5	8.0	8.3	8.2	8.1	8.2	8.3	8.0
85°	4.7	4.5	4.1	4.1	4.5	4.8	4.8	4.8	4.8	4.8	4.5
87.5°	9.7	9.3	9.3	8.9	7.7	6.2	4.2	2.7	4.2	5.8	8.5
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5	5425.5
2.5°	5367.6	5365.8	5384.9	5398.1	5393.3	5388.5	5393.3	5398.1	5384.9	5365.8	5367.6
5°	5176.4	5183.3	5216.6	5239.7	5232.0	5224.3	5232.0	5239.7	5216.6	5183.3	5176.4
7.5°	4794.9	4803.8	4833.4	4853.4	4845.2	4837.0	4845.2	4853.4	4833.4	4803.8	4794.9
10°	4446.5	4459.6	4502.8	4527.9	4498.8	4469.7	4498.8	4527.9	4502.8	4459.6	4446.5
12.5°	4041.9	4039.5	4046.4	4047.6	4031.5	4015.4	4031.5	4047.6	4046.4	4039.5	4041.9
15°	3386.0	3375.9	3386.6	3393.5	3388.8	3384.1	3388.8	3393.5	3386.6	3375.9	3386.0
17.5°	2771.3	2757.2	2756.1	2754.0	2748.7	2743.4	2748.7	2754.0	2756.1	2757.2	2771.3
20°	2381.6	2377.7	2386.3	2392.5	2391.6	2390.8	2391.6	2392.5	2386.3	2377.7	2381.6
22.5°	2049.6	2045.6	2058.3	2065.9	2058.2	2050.5	2058.2	2065.9	2058.3	2045.6	2049.6
25°	1642.8	1633.0	1626.6	1622.1	1623.4	1624.7	1623.4	1622.1	1626.6	1633.0	1642.8
27.5°	1339.3	1336.5	1340.8	1343.2	1340.0	1336.9	1340.0	1343.2	1340.8	1336.5	1339.3
30°	1190.9	1187.1	1189.6	1190.6	1186.7	1182.9	1186.7	1190.6	1189.6	1187.1	1190.9
32.5°	1065.6	1059.7	1058.5	1056.9	1054.0	1051.2	1054.0	1056.9	1058.5	1059.7	1065.6
35°	894.0	886.1	879.7	873.9	870.1	866.2	870.1	873.9	879.7	886.1	894.0
37.5°	736.4	727.7	718.3	710.5	707.2	704.0	707.2	710.5	718.3	727.7	736.4
40°	635.1	626.8	615.7	606.7	604.1	601.5	604.1	606.7	615.7	626.8	635.1
42.5°	534.3	526.3	515.8	506.6	500.9	495.3	500.9	506.6	515.8	526.3	534.3
45°	392.6	389.8	378.3	361.4	328.4	295.5	328.4	361.4	378.3	389.8	392.6
47.5°	272.4	266.2	234.1	201.9	169.6	137.2	169.6	201.9	234.1	266.2	272.4
50°	206.6	200.2	157.8	122.4	107.9	93.4	107.9	122.4	157.8	200.2	206.6
52.5°	161.1	158.1	120.9	91.0	82.9	74.9	82.9	91.0	120.9	158.1	161.1
55°	98.8	97.7	77.6	61.7	58.3	54.9	58.3	61.7	77.6	97.7	98.8
57.5°	61.3	60.7	53.1	46.8	44.7	42.5	44.7	46.8	53.1	60.7	61.3
60°	47.6	47.2	43.3	39.9	37.8	35.6	37.8	39.9	43.3	47.2	47.6
62.5°	39.2	38.6	36.1	34.1	33.3	32.5	33.3	34.1	36.1	38.6	39.2
65°	30.8	30.4	29.5	28.8	28.3	27.9	28.3	28.8	29.5	30.4	30.8
67.5°	26.2	26.0	25.5	25.1	24.7	24.3	24.7	25.1	25.5	26.0	26.2
70°	23.3	22.9	22.5	22.0	21.6	21.2	21.6	22.0	22.5	22.9	23.3
72.5°	20.2	20.0	19.9	19.7	19.3	18.9	19.3	19.7	19.9	20.0	20.2
75°	16.4	16.1	15.7	15.4	15.4	15.4	15.4	15.4	15.7	16.1	16.4
77.5°	12.1	11.9	11.9	11.8	11.5	11.2	11.5	11.8	11.9	11.9	12.1
80°	9.8	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.8
82.5°	7.5	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.5
85°	4.1	4.1	4.5	4.7	4.3	3.8	4.3	4.7	4.5	4.1	4.1
87.5°	10.4	13.1	15.9	17.4	19.0	18.2	19.0	17.4	15.9	13.1	10.4
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	128.8	112.2	89.4	89.4
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	234.1	207.0	179.9	179.9
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	344.0	313.8	277.4	277.4
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	412.1	377.3	342.4	342.4
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	478.6	440.7	395.1	395.1
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	570.7	530.1	481.7	481.7
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	655.8	618.3	568.4	568.4
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	717.8	677.1	636.5	636.5



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	5425.5	5425.5	5425.5	5425.5
2.5°	5390.6	5408.8	5412.9	5417.0
5°	5196.1	5211.7	5215.1	5218.5
7.5°	4806.5	4814.5	4811.6	4808.7
10°	4463.6	4474.5	4466.8	4459.1
12.5°	4053.5	4063.5	4068.4	4073.4
15°	3416.8	3444.4	3462.3	3480.3
17.5°	2798.5	2817.2	2810.2	2803.3
20°	2397.8	2409.5	2407.4	2405.2
22.5°	2070.3	2085.8	2085.3	2084.9
25°	1656.1	1666.4	1667.6	1668.9
27.5°	1349.3	1358.0	1363.3	1368.6
30°	1201.2	1209.9	1214.2	1218.5
32.5°	1076.2	1084.1	1083.9	1083.7
35°	903.4	909.9	907.3	904.7
37.5°	744.4	749.7	747.4	745.0
40°	640.7	644.4	642.7	641.0
42.5°	539.8	542.2	535.0	527.8
45°	386.6	376.4	353.8	331.1
47.5°	252.8	230.3	198.9	167.5
50°	177.1	149.5	127.7	105.9
52.5°	129.9	103.6	92.4	81.2
55°	80.8	66.3	62.0	57.7
57.5°	54.9	49.4	47.1	44.7
60°	44.6	41.9	40.2	38.5
62.5°	37.9	36.7	35.7	34.6
65°	30.8	30.7	30.3	29.8
67.5°	26.3	26.3	25.8	25.4
70°	23.7	24.0	23.5	23.1
72.5°	20.7	20.9	20.4	20.0
75°	16.4	16.4	16.4	16.4
77.5°	12.6	12.9	12.8	12.7
80°	10.3	10.5	10.1	9.6
82.5°	8.0	8.3	8.2	8.1
85°	4.5	4.8	4.8	4.8
87.5°	8.5	5.8	4.2	2.7
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1428650

CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428650
 CATALOG NUMBER: SQ2W-WBN-K-150U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.18	0.81	1.28	1.89	3.35	0.00	0.44	0.91	1.51	2.98
	3H	1.40	1.96	2.51	3.05	4.53	1.01	1.57	2.12	2.66	4.14
	4H	1.92	2.45	3.03	3.53	5.03	1.52	2.06	2.64	3.14	4.63
	6H	2.27	2.76	3.39	3.85	5.35	1.85	2.34	2.98	3.43	4.93
	8H	2.41	2.88	3.54	3.98	5.47	1.99	2.45	3.11	3.55	5.05
	12H	2.50	2.94	3.63	4.04	5.56	2.06	2.50	3.19	3.59	5.11
4H	2H	0.49	1.03	1.62	2.11	3.60	0.18	0.72	1.31	1.80	3.30
	3H	1.98	2.43	3.11	3.54	5.04	1.65	2.09	2.77	3.20	4.71
	4H	2.63	3.04	3.76	4.14	5.67	2.28	2.69	3.41	3.79	5.31
	6H	3.12	3.47	4.26	4.59	6.11	2.74	3.08	3.87	4.21	5.72
	8H	3.33	3.66	4.47	4.77	6.30	2.93	3.25	4.06	4.37	5.90
	12H	3.47	3.76	4.62	4.89	6.42	3.04	3.33	4.18	4.46	5.99
8H	4H	2.79	3.12	3.93	4.23	5.76	2.48	2.80	3.61	3.92	5.45
	6H	3.43	3.69	4.58	4.85	6.38	3.07	3.34	4.23	4.49	6.02
	8H	3.75	3.98	4.91	5.12	6.67	3.36	3.59	4.52	4.73	6.28
	12H	3.98	4.18	5.14	5.31	6.90	3.56	3.76	4.72	4.90	6.48
12H	4H	2.77	3.06	3.92	4.19	5.72	2.46	2.76	3.61	3.88	5.42
	6H	3.47	3.70	4.63	4.83	6.38	3.12	3.35	4.28	4.49	6.04
	8H	3.82	4.02	4.98	5.15	6.74	3.44	3.64	4.60	4.78	6.36