

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427700

Luminaire Tested: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427700  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4485.7 lumens  
Efficiency: N/A  
Efficacy: 137.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 32.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	49	45	43	41	36
3	81	72	64	58	75	66	60	55	57	52	48	48	44	41	39	37	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	30	26
5	68	56	48	42	63	52	45	39	45	39	35	38	34	30	32	28	26	22
6	63	50	42	36	58	47	40	34	40	35	30	34	30	26	29	25	22	20
7	58	45	37	32	53	42	35	30	37	31	27	31	27	23	26	23	20	17
8	54	41	33	28	50	39	31	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	28	24	31	25	21	26	22	19	22	19	16	14
10	47	34	27	22	43	32	26	21	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13377	13377	13377	13377
5°	13296	13447	13296	13447
10°	13248	13401	13248	13401
15°	13177	13342	13177	13342
20°	13092	13223	13092	13223
25°	12951	13065	12951	13065
30°	12814	12901	12814	12901
35°	12650	12731	12650	12731
40°	12507	12543	12507	12543
45°	12323	12323	12323	12323
50°	12077	12104	12077	12104
55°	11792	11808	11792	11808
60°	11473	11473	11473	11473
65°	11102	11056	11102	11056
70°	10579	10466	10579	10466
75°	9863	9644	9863	9644
80°	8786	8359	8786	8359
85°	7021	5947	7021	5947

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 12405 cd/sqm



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.4	1.7
10°-20°	224.0	5.0
20°-30°	337.2	7.5
30°-40°	403.2	9.0
40°-50°	416.4	9.3
50°-60°	375.5	8.4
60°-70°	287.7	6.4
70°-80°	166.3	3.7
80°-90°	46.2	1.0
90°-100°	58.6	1.3
100°-110°	171.0	3.8
110°-120°	279.0	6.2
120°-130°	354.0	7.9
130°-140°	378.8	8.4
140°-150°	353.8	7.9
150°-160°	291.1	6.5
160°-170°	195.2	4.4
170°-180°	69.3	1.5
0°-30°	639.6	14.3
0°-40°	1042.8	23.2
0°-60°	1834.7	40.9
0°-90°	2334.8	52.1
90°-120°	508.6	11.3
90°-150°	1595.3	35.6
90°-180°	2151.0	48.0
0°-180°	4485.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	828	828	828	828	828	
5°	820	830	820	830	820	78
15°	788	798	788	798	788	222
25°	727	733	727	733	727	335
35°	642	646	642	646	642	402
45°	540	540	540	540	540	416
55°	419	420	419	420	419	374
65°	291	289	291	289	291	287
75°	158	155	158	155	158	167
85°	38	32	38	32	38	44
90°	2	16	2	32	2	3
95°	23	17	23	100	23	28
105°	109	174	109	240	109	116
115°	208	289	208	356	208	205
125°	308	458	308	436	308	276
135°	419	599	419	483	419	324
145°	535	690	535	493	535	335
155°	636	750	636	512	636	292
165°	702	782	702	589	702	198
175°	734	766	734	691	734	70
180°	737	737	737	737	737	



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5
2.5°	824.3	828.3	832.2	830.5	827.0	825.7	826.5	827.2	827.6	828.1	827.6
5°	820.4	825.5	830.7	828.9	824.8	822.9	823.5	824.5	827.1	829.7	827.1
7.5°	813.7	818.9	824.1	822.4	818.5	816.8	817.4	818.6	821.3	824.0	821.3
10°	808.1	813.3	818.5	816.7	812.5	811.0	812.0	813.3	815.4	817.4	815.4
12.5°	801.1	806.3	811.5	810.0	806.2	804.7	805.3	806.3	808.6	810.9	808.6
15°	788.3	793.5	798.6	797.2	793.6	792.2	792.9	794.0	796.1	798.2	796.1
17.5°	772.7	777.6	782.5	781.2	777.8	776.6	777.5	778.6	780.4	782.2	780.4
20°	762.0	766.7	771.3	770.0	766.6	765.1	765.3	766.0	767.8	769.6	767.8
22.5°	748.9	753.6	758.3	757.1	753.9	752.0	751.5	751.6	753.8	756.1	753.8
25°	727.0	731.7	736.3	735.4	732.5	730.7	729.9	729.8	731.6	733.4	731.6
27.5°	704.1	708.0	711.9	711.1	708.7	707.3	706.7	706.7	708.0	709.3	708.0
30°	687.3	691.2	695.1	694.1	691.5	690.0	689.5	689.4	690.7	692.0	690.7
32.5°	669.6	673.3	677.0	675.6	672.6	671.1	670.9	671.2	672.8	674.3	672.8
35°	641.8	644.9	648.0	646.7	643.8	642.5	642.8	643.3	644.6	645.9	644.6
37.5°	613.9	616.3	618.7	617.3	614.7	613.3	613.3	613.5	614.6	615.7	614.6
40°	593.4	596.0	598.6	597.1	594.2	592.7	592.4	592.5	593.8	595.1	593.8
42.5°	572.4	574.4	576.3	575.0	572.6	571.4	571.6	571.9	572.5	573.2	572.5
45°	539.7	541.5	543.3	542.0	539.7	538.5	538.5	538.7	539.2	539.7	539.2
47.5°	505.5	506.9	508.3	507.3	505.5	504.4	504.1	504.1	504.9	505.7	504.9
50°	480.8	482.6	484.4	483.5	481.7	480.5	480.0	479.9	480.9	481.9	480.9
52.5°	456.5	458.5	460.6	459.7	457.9	456.6	455.9	455.5	456.4	457.2	456.4
55°	418.9	421.3	423.6	423.0	421.5	420.2	419.1	418.5	419.0	419.5	419.0
57.5°	380.5	382.8	385.1	384.7	383.3	382.0	380.8	380.0	380.7	381.5	380.7
60°	355.3	357.4	359.5	358.8	357.3	356.0	354.9	354.3	354.8	355.3	354.8
62.5°	329.7	331.7	333.8	333.0	331.2	329.8	328.8	328.2	328.7	329.2	328.7
65°	290.6	292.4	294.2	293.5	291.9	290.6	289.6	288.9	289.1	289.4	289.1
67.5°	251.1	252.7	254.2	253.5	252.0	250.5	249.0	248.0	248.4	248.8	248.4
70°	224.1	225.6	227.2	226.6	225.3	224.0	222.7	221.7	221.7	221.7	221.7
72.5°	197.9	199.3	200.6	199.8	198.3	197.0	195.9	195.1	195.1	195.1	195.1
75°	158.1	158.9	159.7	159.3	158.5	157.5	156.2	155.1	154.9	154.6	154.9
77.5°	119.7	119.7	119.7	119.0	118.0	117.0	116.0	115.2	114.9	114.6	114.9
80°	94.5	94.5	94.5	93.9	93.2	92.4	91.6	90.9	90.4	89.9	90.4
82.5°	71.2	70.8	70.4	69.7	68.9	67.9	66.7	65.9	66.5	67.0	66.5
85°	37.9	37.4	36.9	36.2	35.4	34.5	33.5	32.6	32.4	32.1	32.4
87.5°	12.1	12.3	12.6	12.7	12.5	11.9	11.1	10.5	10.5	10.3	10.5
90°	2.2	5.2	8.9	11.9	14.1	14.9	14.9	15.6	16.4	16.4	16.4
92.5°	8.2	12.9	13.1	13.1	15.9	17.3	18.5	18.6	19.3	19.3	19.3
95°	23.1	25.3	37.9	37.2	25.3	20.1	17.1	17.1	17.1	17.1	17.1
97.5°	44.1	47.3	49.4	66.2	69.9	67.6	55.1	46.3	41.4	39.1	41.4
100°	62.5	64.0	68.5	69.2	87.8	105.7	96.7	85.6	81.9	79.6	81.9
102.5°	81.0	81.9	88.7	91.8	96.1	106.3	137.2	133.8	131.3	130.8	131.3
105°	108.6	109.4	122.0	128.0	131.0	131.0	130.2	145.1	168.9	174.1	168.9
107.5°	138.3	141.7	156.6	172.5	175.9	176.8	172.9	170.7	169.8	170.4	169.8
110°	158.5	163.7	181.6	201.7	206.9	208.3	206.9	204.6	203.1	203.1	203.1



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	178.1	185.7	206.0	229.0	237.8	242.3	239.0	237.4	235.9	237.1	235.9
115°	208.3	219.5	246.3	270.1	288.0	290.2	289.5	289.5	288.7	288.7	288.7
117.5°	236.3	254.2	284.2	311.9	332.6	338.6	341.5	340.6	339.8	341.2	339.8
120°	256.0	276.8	311.0	342.3	362.4	371.3	374.3	372.8	374.3	372.8	374.3
122.5°	276.8	302.4	336.0	368.5	392.1	402.3	405.8	406.1	406.4	405.5	406.4
125°	308.1	339.3	378.7	412.2	436.8	448.7	451.7	452.4	453.9	457.6	453.9
127.5°	339.6	375.0	418.3	450.6	475.8	490.2	494.8	496.5	499.6	501.2	499.6
130°	361.6	401.8	445.7	476.2	500.8	516.4	524.6	526.8	530.5	529.8	530.5
132.5°	384.8	426.8	471.3	503.0	525.8	542.6	549.6	556.0	557.3	558.4	557.3
135°	418.9	464.3	509.0	540.2	561.8	578.2	587.1	593.0	596.8	599.0	596.8
137.5°	454.8	502.7	545.6	573.4	595.1	609.3	619.4	625.6	629.5	631.3	629.5
140°	479.2	525.3	567.0	596.0	615.4	629.5	638.4	645.9	650.3	650.3	650.3
142.5°	502.4	548.0	588.4	617.5	634.4	647.4	656.9	662.5	667.6	667.6	667.6
145°	535.0	580.4	617.6	646.6	660.8	672.7	683.1	687.5	690.5	690.5	690.5
147.5°	569.1	609.3	643.2	671.0	682.9	696.9	705.1	708.7	712.4	710.8	712.4
150°	589.3	626.5	659.3	685.3	697.2	710.6	718.8	721.8	725.5	723.3	725.5
152.5°	609.0	644.4	674.2	698.4	708.5	721.9	731.3	734.3	736.8	735.2	736.8
155°	635.5	666.7	694.2	716.6	725.5	738.1	747.1	750.8	753.8	750.0	753.8
157.5°	659.1	686.1	710.0	730.6	740.1	750.9	759.3	763.9	766.9	765.2	766.9
160°	673.4	698.0	719.5	738.9	747.8	757.5	766.4	771.6	774.6	772.4	774.6
162.5°	685.3	707.5	727.9	745.4	753.2	761.7	772.4	777.0	780.0	777.1	780.0
165°	702.4	720.3	738.1	753.0	759.7	766.4	777.6	782.8	785.0	782.0	785.0
167.5°	715.4	729.1	743.5	756.3	761.2	767.8	778.9	783.2	786.1	782.3	786.1
170°	722.5	734.4	747.1	757.5	761.2	767.2	778.3	782.0	784.3	780.6	784.3
172.5°	728.5	737.4	747.7	756.9	758.8	763.6	774.2	777.9	779.5	776.4	779.5
175°	734.4	739.6	747.1	753.0	752.3	755.3	764.2	767.2	770.1	765.7	770.1
177.5°	737.3	739.6	742.0	745.6	743.2	743.2	749.8	751.5	752.1	749.8	752.1
180°	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5
2.5°	827.2	826.5	825.7	827.0	830.5	832.2	828.3	824.3	828.3	832.2	830.5
5°	824.5	823.5	822.9	824.8	828.9	830.7	825.5	820.4	825.5	830.7	828.9
7.5°	818.6	817.4	816.8	818.5	822.4	824.1	818.9	813.7	818.9	824.1	822.4
10°	813.3	812.0	811.0	812.5	816.7	818.5	813.3	808.1	813.3	818.5	816.7
12.5°	806.3	805.3	804.7	806.2	810.0	811.5	806.3	801.1	806.3	811.5	810.0
15°	794.0	792.9	792.2	793.6	797.2	798.6	793.5	788.3	793.5	798.6	797.2
17.5°	778.6	777.5	776.6	777.8	781.2	782.5	777.6	772.7	777.6	782.5	781.2
20°	766.0	765.3	765.1	766.6	770.0	771.3	766.7	762.0	766.7	771.3	770.0
22.5°	751.6	751.5	752.0	753.9	757.1	758.3	753.6	748.9	753.6	758.3	757.1
25°	729.8	729.9	730.7	732.5	735.4	736.3	731.7	727.0	731.7	736.3	735.4
27.5°	706.7	706.7	707.3	708.7	711.1	711.9	708.0	704.1	708.0	711.9	711.1
30°	689.4	689.5	690.0	691.5	694.1	695.1	691.2	687.3	691.2	695.1	694.1
32.5°	671.2	670.9	671.1	672.6	675.6	677.0	673.3	669.6	673.3	677.0	675.6
35°	643.3	642.8	642.5	643.8	646.7	648.0	644.9	641.8	644.9	648.0	646.7
37.5°	613.5	613.3	613.3	614.7	617.3	618.7	616.3	613.9	616.3	618.7	617.3
40°	592.5	592.4	592.7	594.2	597.1	598.6	596.0	593.4	596.0	598.6	597.1
42.5°	571.9	571.6	571.4	572.6	575.0	576.3	574.4	572.4	574.4	576.3	575.0
45°	538.7	538.5	538.5	539.7	542.0	543.3	541.5	539.7	541.5	543.3	542.0
47.5°	504.1	504.1	504.4	505.5	507.3	508.3	506.9	505.5	506.9	508.3	507.3
50°	479.9	480.0	480.5	481.7	483.5	484.4	482.6	480.8	482.6	484.4	483.5
52.5°	455.5	455.9	456.6	457.9	459.7	460.6	458.5	456.5	458.5	460.6	459.7
55°	418.5	419.1	420.2	421.5	423.0	423.6	421.3	418.9	421.3	423.6	423.0
57.5°	380.0	380.8	382.0	383.3	384.7	385.1	382.8	380.5	382.8	385.1	384.7
60°	354.3	354.9	356.0	357.3	358.8	359.5	357.4	355.3	357.4	359.5	358.8
62.5°	328.2	328.8	329.8	331.2	333.0	333.8	331.7	329.7	331.7	333.8	333.0
65°	288.9	289.6	290.6	291.9	293.5	294.2	292.4	290.6	292.4	294.2	293.5
67.5°	248.0	249.0	250.5	252.0	253.5	254.2	252.7	251.1	252.7	254.2	253.5
70°	221.7	222.7	224.0	225.3	226.6	227.2	225.6	224.1	225.6	227.2	226.6
72.5°	195.1	195.9	197.0	198.3	199.8	200.6	199.3	197.9	199.3	200.6	199.8
75°	155.1	156.2	157.5	158.5	159.3	159.7	158.9	158.1	158.9	159.7	159.3
77.5°	115.2	116.0	117.0	118.0	119.0	119.7	119.7	119.7	119.7	119.7	119.0
80°	90.9	91.6	92.4	93.2	93.9	94.5	94.5	94.5	94.5	94.5	93.9
82.5°	65.9	66.7	67.9	68.9	69.7	70.4	70.8	71.2	70.8	70.4	69.7
85°	32.6	33.5	34.5	35.4	36.2	36.9	37.4	37.9	37.4	36.9	36.2
87.5°	10.5	11.1	11.9	12.5	12.7	12.6	12.3	12.1	12.3	12.5	12.9
90°	15.6	14.9	14.9	14.1	11.9	8.9	5.2	2.2	5.2	8.2	13.4
92.5°	18.6	18.5	17.3	15.9	13.1	13.1	12.9	8.2	14.1	20.1	28.9
95°	17.1	17.1	20.1	25.3	37.2	37.9	25.3	23.1	32.7	46.1	58.0
97.5°	46.3	55.1	67.6	69.9	66.2	49.4	47.3	44.1	60.0	73.2	92.4
100°	85.6	96.7	105.7	87.8	69.2	68.5	64.0	62.5	79.6	92.3	110.9
102.5°	133.8	137.2	106.3	96.1	91.8	88.7	81.9	81.0	98.1	115.5	131.1
105°	145.1	130.2	131.0	131.0	128.0	122.0	109.4	108.6	128.0	148.1	167.4
107.5°	170.7	172.9	176.8	175.9	172.5	156.6	141.7	138.3	155.7	179.8	201.1
110°	204.6	206.9	208.3	206.9	201.7	181.6	163.7	158.5	174.1	199.4	222.5



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	237.4	239.0	242.3	237.8	229.0	206.0	185.7	178.1	193.8	219.7	243.3
115°	289.5	289.5	290.2	288.0	270.1	246.3	219.5	208.3	221.7	245.6	271.6
117.5°	340.6	341.5	338.6	332.6	311.9	284.2	254.2	236.3	246.9	272.0	298.8
120°	372.8	374.3	371.3	362.4	342.3	311.0	276.8	256.0	264.2	288.7	315.5
122.5°	406.1	405.8	402.3	392.1	368.5	336.0	302.4	276.8	280.2	303.0	329.2
125°	452.4	451.7	448.7	436.8	412.2	378.7	339.3	308.1	303.6	322.9	349.7
127.5°	496.5	494.8	490.2	475.8	450.6	418.3	375.0	339.6	329.6	341.8	366.4
130°	526.8	524.6	516.4	500.8	476.2	445.7	401.8	361.6	347.5	354.9	376.5
132.5°	556.0	549.6	542.6	525.8	503.0	471.3	426.8	384.8	365.4	368.6	385.4
135°	593.0	587.1	578.2	561.8	540.2	509.0	464.3	418.9	392.1	389.2	398.8
137.5°	625.6	619.4	609.3	595.1	573.4	545.6	502.7	454.8	421.0	411.0	414.8
140°	645.9	638.4	629.5	615.4	596.0	567.0	525.3	479.2	441.2	427.1	424.9
142.5°	662.5	656.9	647.4	634.4	617.5	588.4	548.0	502.4	462.1	443.8	438.6
145°	687.5	683.1	672.7	660.8	646.6	617.6	580.4	535.0	494.8	471.0	459.9
147.5°	708.7	705.1	696.9	682.9	671.0	643.2	609.3	569.1	527.9	498.4	484.0
150°	721.8	718.8	710.6	697.2	685.3	659.3	626.5	589.3	549.9	518.6	500.0
152.5°	734.3	731.3	721.9	708.5	698.4	674.2	644.4	609.0	568.9	537.7	518.5
155°	750.8	747.1	738.1	725.5	716.6	694.2	666.7	635.5	601.2	568.5	546.9
157.5°	763.9	759.3	750.9	740.1	730.6	710.0	686.1	659.1	629.2	598.0	575.9
160°	771.6	766.4	757.5	747.8	738.9	719.5	698.0	673.4	645.9	617.6	593.8
162.5°	777.0	772.4	761.7	753.2	745.4	727.9	707.5	685.3	660.8	636.1	614.0
165°	782.8	777.6	766.4	759.7	753.0	738.1	720.3	702.4	681.6	661.5	643.6
167.5°	783.2	778.9	767.8	761.2	756.3	743.5	729.1	715.4	699.2	683.4	668.5
170°	782.0	778.3	767.2	761.2	757.5	747.1	734.4	722.5	709.9	696.5	684.6
172.5°	777.9	774.2	763.6	758.8	756.9	747.7	737.4	728.5	717.6	707.8	698.3
175°	767.2	764.2	755.3	752.3	753.0	747.1	739.6	734.4	727.7	721.8	716.6
177.5°	751.5	749.8	743.2	743.2	745.6	742.0	739.6	737.3	734.3	732.5	730.7
180°	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5	828.5
2.5°	827.0	825.7	826.5	827.2	827.6	828.1	827.6	827.2	826.5	825.7	827.0
5°	824.8	822.9	823.5	824.5	827.1	829.7	827.1	824.5	823.5	822.9	824.8
7.5°	818.5	816.8	817.4	818.6	821.3	824.0	821.3	818.6	817.4	816.8	818.5
10°	812.5	811.0	812.0	813.3	815.4	817.4	815.4	813.3	812.0	811.0	812.5
12.5°	806.2	804.7	805.3	806.3	808.6	810.9	808.6	806.3	805.3	804.7	806.2
15°	793.6	792.2	792.9	794.0	796.1	798.2	796.1	794.0	792.9	792.2	793.6
17.5°	777.8	776.6	777.5	778.6	780.4	782.2	780.4	778.6	777.5	776.6	777.8
20°	766.6	765.1	765.3	766.0	767.8	769.6	767.8	766.0	765.3	765.1	766.6
22.5°	753.9	752.0	751.5	751.6	753.8	756.1	753.8	751.6	751.5	752.0	753.9
25°	732.5	730.7	729.9	729.8	731.6	733.4	731.6	729.8	729.9	730.7	732.5
27.5°	708.7	707.3	706.7	706.7	708.0	709.3	708.0	706.7	706.7	707.3	708.7
30°	691.5	690.0	689.5	689.4	690.7	692.0	690.7	689.4	689.5	690.0	691.5
32.5°	672.6	671.1	670.9	671.2	672.8	674.3	672.8	671.2	670.9	671.1	672.6
35°	643.8	642.5	642.8	643.3	644.6	645.9	644.6	643.3	642.8	642.5	643.8
37.5°	614.7	613.3	613.3	613.5	614.6	615.7	614.6	613.5	613.3	613.3	614.7
40°	594.2	592.7	592.4	592.5	593.8	595.1	593.8	592.5	592.4	592.7	594.2
42.5°	572.6	571.4	571.6	571.9	572.5	573.2	572.5	571.9	571.6	571.4	572.6
45°	539.7	538.5	538.5	538.7	539.2	539.7	539.2	538.7	538.5	538.5	539.7
47.5°	505.5	504.4	504.1	504.1	504.9	505.7	504.9	504.1	504.1	504.4	505.5
50°	481.7	480.5	480.0	479.9	480.9	481.9	480.9	479.9	480.0	480.5	481.7
52.5°	457.9	456.6	455.9	455.5	456.4	457.2	456.4	455.5	455.9	456.6	457.9
55°	421.5	420.2	419.1	418.5	419.0	419.5	419.0	418.5	419.1	420.2	421.5
57.5°	383.3	382.0	380.8	380.0	380.7	381.5	380.7	380.0	380.8	382.0	383.3
60°	357.3	356.0	354.9	354.3	354.8	355.3	354.8	354.3	354.9	356.0	357.3
62.5°	331.2	329.8	328.8	328.2	328.7	329.2	328.7	328.2	328.8	329.8	331.2
65°	291.9	290.6	289.6	288.9	289.1	289.4	289.1	288.9	289.6	290.6	291.9
67.5°	252.0	250.5	249.0	248.0	248.4	248.8	248.4	248.0	249.0	250.5	252.0
70°	225.3	224.0	222.7	221.7	221.7	221.7	221.7	221.7	222.7	224.0	225.3
72.5°	198.3	197.0	195.9	195.1	195.1	195.1	195.1	195.1	195.9	197.0	198.3
75°	158.5	157.5	156.2	155.1	154.9	154.6	154.9	155.1	156.2	157.5	158.5
77.5°	118.0	117.0	116.0	115.2	114.9	114.6	114.9	115.2	116.0	117.0	118.0
80°	93.2	92.4	91.6	90.9	90.4	89.9	90.4	90.9	91.6	92.4	93.2
82.5°	68.9	67.9	66.7	65.9	66.5	67.0	66.5	65.9	66.7	67.9	68.9
85°	35.4	34.5	33.5	32.6	32.4	32.1	32.4	32.6	33.5	34.5	35.4
87.5°	13.1	13.4	13.6	13.5	13.9	13.4	13.9	13.5	13.6	13.4	13.1
90°	17.1	22.3	27.5	30.5	33.5	32.0	33.5	30.5	27.5	22.3	17.1
92.5°	34.4	43.2	49.6	54.9	57.3	57.0	57.3	54.9	49.6	43.2	34.4
95°	69.2	79.6	90.0	97.5	101.9	100.5	101.9	97.5	90.0	79.6	69.2
97.5°	106.7	120.7	132.3	139.3	143.8	146.7	143.8	139.3	132.3	120.7	106.7
100°	131.7	145.1	158.5	166.7	174.1	177.1	174.1	166.7	158.5	145.1	131.7
102.5°	151.9	169.5	184.1	192.9	199.1	202.1	199.1	192.9	184.1	169.5	151.9
105°	185.3	203.9	219.5	230.7	237.4	239.6	237.4	230.7	219.5	203.9	185.3
107.5°	218.6	237.8	252.2	264.6	272.8	277.5	272.8	264.6	252.2	237.8	218.6
110°	244.8	260.4	276.1	287.2	295.4	298.4	295.4	287.2	276.1	260.4	244.8



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	266.8	284.2	299.9	311.0	320.4	324.6	320.4	311.0	299.9	284.2	266.8
115°	297.6	320.7	334.8	345.3	352.0	355.7	352.0	345.3	334.8	320.7	297.6
117.5°	323.2	347.3	362.8	370.9	374.0	376.7	374.0	370.9	362.8	347.3	323.2
120°	339.3	361.6	379.5	389.9	393.6	395.1	393.6	389.9	379.5	361.6	339.3
122.5°	354.2	375.3	392.6	405.4	411.5	413.0	411.5	405.4	392.6	375.3	354.2
125°	375.0	395.1	413.0	425.6	432.3	436.0	432.3	425.6	413.0	395.1	375.0
127.5°	393.2	414.9	431.3	442.7	449.3	452.3	449.3	442.7	431.3	414.9	393.2
130°	403.3	425.6	442.0	454.6	460.6	463.6	460.6	454.6	442.0	425.6	403.3
132.5°	411.0	434.6	451.5	463.0	469.5	472.5	469.5	463.0	451.5	434.6	411.0
135°	420.4	445.0	462.8	474.0	479.9	482.9	479.9	474.0	462.8	445.0	420.4
137.5°	428.6	450.9	469.5	481.3	486.6	488.6	486.6	481.3	469.5	450.9	428.6
140°	434.6	453.9	472.5	483.7	489.6	490.4	489.6	483.7	472.5	453.9	434.6
142.5°	442.3	457.5	473.7	484.9	490.8	492.1	490.8	484.9	473.7	457.5	442.3
145°	456.1	465.1	476.2	486.6	491.8	493.3	491.8	486.6	476.2	465.1	456.1
147.5°	473.5	476.4	482.2	489.0	494.1	495.1	494.1	489.0	482.2	476.4	473.5
150°	486.6	485.9	488.1	492.6	497.1	496.3	497.1	492.6	488.1	485.9	486.6
152.5°	501.5	497.2	497.1	499.1	501.2	501.1	501.2	499.1	497.1	497.2	501.5
155°	526.8	518.6	514.2	512.7	512.7	511.9	512.7	512.7	514.2	518.6	526.8
157.5°	554.6	543.2	536.5	532.9	531.9	530.2	531.9	532.9	536.5	543.2	554.6
160°	573.7	561.0	554.4	548.4	546.2	543.9	546.2	548.4	554.4	561.0	573.7
162.5°	591.6	579.5	572.2	566.9	564.6	561.2	564.6	566.9	572.2	579.5	591.6
165°	620.6	607.9	599.7	595.3	592.3	589.3	592.3	595.3	599.7	607.9	620.6
167.5°	649.6	635.8	630.4	625.3	622.5	617.2	622.5	625.3	630.4	635.8	649.6
170°	667.5	654.8	651.8	647.4	642.2	636.2	642.2	647.4	651.8	654.8	667.5
172.5°	682.9	674.4	671.5	667.0	665.4	660.6	665.4	667.0	671.5	674.4	682.9
175°	705.4	698.7	698.7	698.0	695.7	691.3	695.7	698.0	698.7	698.7	705.4
177.5°	724.2	720.6	723.0	723.0	722.4	718.2	722.4	723.0	723.0	720.6	724.2
180°	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7



TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	828.5	828.5	828.5	828.5
2.5°	830.5	832.2	828.3	824.3
5°	828.9	830.7	825.5	820.4
7.5°	822.4	824.1	818.9	813.7
10°	816.7	818.5	813.3	808.1
12.5°	810.0	811.5	806.3	801.1
15°	797.2	798.6	793.5	788.3
17.5°	781.2	782.5	777.6	772.7
20°	770.0	771.3	766.7	762.0
22.5°	757.1	758.3	753.6	748.9
25°	735.4	736.3	731.7	727.0
27.5°	711.1	711.9	708.0	704.1
30°	694.1	695.1	691.2	687.3
32.5°	675.6	677.0	673.3	669.6
35°	646.7	648.0	644.9	641.8
37.5°	617.3	618.7	616.3	613.9
40°	597.1	598.6	596.0	593.4
42.5°	575.0	576.3	574.4	572.4
45°	542.0	543.3	541.5	539.7
47.5°	507.3	508.3	506.9	505.5
50°	483.5	484.4	482.6	480.8
52.5°	459.7	460.6	458.5	456.5
55°	423.0	423.6	421.3	418.9
57.5°	384.7	385.1	382.8	380.5
60°	358.8	359.5	357.4	355.3
62.5°	333.0	333.8	331.7	329.7
65°	293.5	294.2	292.4	290.6
67.5°	253.5	254.2	252.7	251.1
70°	226.6	227.2	225.6	224.1
72.5°	199.8	200.6	199.3	197.9
75°	159.3	159.7	158.9	158.1
77.5°	119.0	119.7	119.7	119.7
80°	93.9	94.5	94.5	94.5
82.5°	69.7	70.4	70.8	71.2
85°	36.2	36.9	37.4	37.9
87.5°	12.9	12.5	12.3	12.1
90°	13.4	8.2	5.2	2.2
92.5°	28.9	20.1	14.1	8.2
95°	58.0	46.1	32.7	23.1
97.5°	92.4	73.2	60.0	44.1
100°	110.9	92.3	79.6	62.5
102.5°	131.1	115.5	98.1	81.0
105°	167.4	148.1	128.0	108.6
107.5°	201.1	179.8	155.7	138.3
110°	222.5	199.4	174.1	158.5

TEST NUMBER: P1427700

CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	243.3	219.7	193.8	178.1
115°	271.6	245.6	221.7	208.3
117.5°	298.8	272.0	246.9	236.3
120°	315.5	288.7	264.2	256.0
122.5°	329.2	303.0	280.2	276.8
125°	349.7	322.9	303.6	308.1
127.5°	366.4	341.8	329.6	339.6
130°	376.5	354.9	347.5	361.6
132.5°	385.4	368.6	365.4	384.8
135°	398.8	389.2	392.1	418.9
137.5°	414.8	411.0	421.0	454.8
140°	424.9	427.1	441.2	479.2
142.5°	438.6	443.8	462.1	502.4
145°	459.9	471.0	494.8	535.0
147.5°	484.0	498.4	527.9	569.1
150°	500.0	518.6	549.9	589.3
152.5°	518.5	537.7	568.9	609.0
155°	546.9	568.5	601.2	635.5
157.5°	575.9	598.0	629.2	659.1
160°	593.8	617.6	645.9	673.4
162.5°	614.0	636.1	660.8	685.3
165°	643.6	661.5	681.6	702.4
167.5°	668.5	683.4	699.2	715.4
170°	684.6	696.5	709.9	722.5
172.5°	698.3	707.8	717.6	728.5
175°	716.6	721.8	727.7	734.4
177.5°	730.7	732.5	734.3	737.3
180°	736.7	736.7	736.7	736.7



TEST NUMBER: P1427700  
 CATALOG NUMBER: SQ2W-F-K-050U-050D-L835-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.06	17.95	18.00	18.91	20.15	16.97	17.87	17.91	18.82	20.06
	3H	18.85	19.65	19.80	20.62	21.88	18.75	19.55	19.70	20.51	21.78
	4H	19.55	20.31	20.51	21.28	22.55	19.43	20.19	20.40	21.16	22.43
	6H	19.99	20.69	20.96	21.66	22.95	19.85	20.55	20.82	21.52	22.81
	8H	20.15	20.82	21.13	21.81	23.09	19.99	20.66	20.97	21.65	22.93
	12H	20.23	20.87	21.22	21.85	23.16	20.06	20.69	21.04	21.68	22.99
4H	2H	17.64	18.40	18.61	19.37	20.64	17.58	18.34	18.54	19.30	20.58
	3H	19.67	20.30	20.65	21.30	22.59	19.57	20.21	20.55	21.21	22.49
	4H	20.48	21.06	21.47	22.05	23.37	20.37	20.95	21.36	21.94	23.25
	6H	21.04	21.54	22.04	22.55	23.86	20.90	21.40	21.89	22.41	23.72
	8H	21.25	21.72	22.25	22.73	24.05	21.09	21.56	22.09	22.57	23.89
	12H	21.37	21.79	22.39	22.81	24.14	21.18	21.60	22.20	22.63	23.96
8H	4H	20.73	21.20	21.73	22.21	23.53	20.63	21.10	21.63	22.11	23.43
	6H	21.42	21.81	22.45	22.86	24.18	21.29	21.68	22.31	22.73	24.05
	8H	21.73	22.07	22.76	23.10	24.44	21.57	21.91	22.60	22.95	24.29
	12H	21.91	22.21	22.95	23.24	24.62	21.72	22.02	22.76	23.05	24.43
12H	4H	20.73	21.15	21.75	22.17	23.50	20.63	21.05	21.65	22.08	23.41
	6H	21.47	21.81	22.50	22.85	24.19	21.35	21.69	22.38	22.72	24.06
	8H	21.81	22.11	22.84	23.14	24.52	21.66	21.96	22.69	22.99	24.37