

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427718

Luminaire Tested: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427718  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7785.3 lumens  
Efficiency: N/A  
Efficacy: 121.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 64.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	72	
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	66	64	64	64	64	60	
2	93	85	79	73	88	81	75	70	73	69	65	66	62	59	59	56	54	54	54	54	50	
3	85	75	67	61	80	71	64	59	64	59	54	58	54	50	52	49	46	46	46	46	42	
4	78	66	58	51	73	63	55	50	57	51	46	52	47	42	46	42	39	39	39	39	36	
5	71	59	50	44	67	56	48	43	51	45	40	46	41	37	42	37	34	34	34	34	31	
6	66	53	44	38	62	51	43	37	46	39	35	42	36	32	38	33	30	30	30	30	27	
7	61	48	40	34	57	46	38	33	42	35	30	38	33	28	35	30	26	26	26	26	24	
8	57	44	35	30	53	42	34	29	38	32	27	35	29	25	32	27	24	24	24	24	21	
9	53	40	32	27	50	38	31	26	35	29	24	32	27	23	29	25	21	21	21	21	19	
10	49	37	29	24	47	35	28	23	32	26	22	30	24	21	27	23	19	19	19	19	17	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	32306	32306	32306	32306
5°	32110	32474	32110	32474
10°	31996	32365	31996	32365
15°	31821	32220	31821	32220
20°	31620	31934	31620	31934
25°	31277	31553	31277	31553
30°	30946	31157	30946	31157
35°	30551	30746	30551	30746
40°	30205	30293	30205	30293
45°	29761	29761	29761	29761
50°	29165	29235	29165	29235
55°	28478	28518	28478	28518
60°	27709	27709	27709	27709
65°	26807	26701	26807	26701
70°	25543	25279	25543	25279
75°	23824	23293	23824	23293
80°	21227	20176	21227	20176
85°	16969	14357	16969	14357

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 29962 cd/sqm



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.3	2.4
10°-20°	541.0	6.9
20°-30°	814.3	10.5
30°-40°	973.8	12.5
40°-50°	1005.5	12.9
50°-60°	906.9	11.6
60°-70°	694.7	8.9
70°-80°	401.5	5.2
80°-90°	107.3	1.4
90°-100°	58.6	0.8
100°-110°	171.0	2.2
110°-120°	279.0	3.6
120°-130°	354.0	4.5
130°-140°	378.8	4.9
140°-150°	353.8	4.5
150°-160°	291.1	3.7
160°-170°	195.2	2.5
170°-180°	69.3	0.9
0°-30°	1544.6	19.8
0°-40°	2518.3	32.3
0°-60°	4430.8	56.9
0°-90°	5634.4	72.4
90°-120°	508.6	6.5
90°-150°	1595.3	20.5
90°-180°	2151.0	27.6
0°-180°	7785.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	1981	2004	1981	2004	1981	188
15°	1904	1928	1904	1928	1904	537
25°	1756	1771	1756	1771	1756	809
35°	1550	1560	1550	1560	1550	970
45°	1303	1303	1303	1303	1303	1004
55°	1012	1013	1012	1013	1012	904
65°	702	699	702	699	702	694
75°	382	373	382	373	382	404
85°	92	78	92	78	92	107
90°	2	16	2	32	2	6
95°	23	17	23	100	23	28
105°	109	174	109	240	109	116
115°	208	289	208	356	208	205
125°	308	458	308	436	308	276
135°	419	599	419	483	419	324
145°	535	690	535	493	535	335
155°	636	750	636	512	636	292
165°	702	782	702	589	702	198
175°	734	766	734	691	734	70
180°	737	737	737	737	737	



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9
2.5°	1990.8	2000.3	2009.8	2005.8	1997.3	1994.0	1996.0	1997.8	1998.8	1999.8	1998.8
5°	1981.2	1993.7	2006.2	2001.9	1991.8	1987.5	1988.7	1991.2	1997.5	2003.7	1997.5
7.5°	1965.1	1977.7	1990.2	1986.2	1976.6	1972.6	1974.1	1976.9	1983.4	1989.9	1983.4
10°	1951.6	1964.1	1976.6	1972.3	1962.2	1958.5	1961.0	1964.1	1969.1	1974.1	1969.1
12.5°	1934.7	1947.2	1959.7	1956.1	1947.1	1943.3	1944.8	1947.3	1952.9	1958.4	1952.9
15°	1903.7	1916.2	1928.7	1925.3	1916.5	1913.1	1915.0	1917.6	1922.6	1927.6	1922.6
17.5°	1866.2	1878.0	1889.8	1886.6	1878.5	1875.4	1877.6	1880.3	1884.7	1889.0	1884.7
20°	1840.3	1851.6	1862.8	1859.5	1851.4	1847.6	1848.3	1849.8	1854.2	1858.6	1854.2
22.5°	1808.7	1820.0	1831.3	1828.3	1820.7	1816.2	1814.8	1815.1	1820.5	1825.9	1820.5
25°	1755.7	1767.0	1778.3	1775.9	1769.0	1764.7	1762.8	1762.5	1766.8	1771.2	1766.8
27.5°	1700.5	1709.9	1719.3	1717.3	1711.6	1708.0	1706.8	1706.6	1709.8	1712.9	1709.8
30°	1659.9	1669.3	1678.7	1676.4	1670.1	1666.3	1665.1	1664.9	1668.1	1671.2	1668.1
32.5°	1617.1	1626.0	1634.9	1631.6	1624.4	1620.6	1620.4	1621.1	1624.7	1628.4	1624.7
35°	1550.0	1557.5	1565.0	1561.7	1554.9	1551.7	1552.4	1553.6	1556.7	1559.9	1556.7
37.5°	1482.7	1488.4	1494.2	1490.8	1484.4	1481.2	1481.1	1481.6	1484.2	1486.9	1484.2
40°	1433.1	1439.3	1445.6	1442.0	1435.1	1431.3	1430.7	1431.0	1434.1	1437.3	1434.1
42.5°	1382.3	1387.1	1391.8	1388.6	1382.7	1380.0	1380.4	1381.0	1382.7	1384.3	1382.7
45°	1303.4	1307.8	1312.2	1309.1	1303.4	1300.6	1300.6	1300.9	1302.2	1303.4	1302.2
47.5°	1220.8	1224.2	1227.6	1225.2	1220.8	1218.2	1217.5	1217.4	1219.4	1221.4	1219.4
50°	1161.1	1165.5	1169.9	1167.7	1163.3	1160.5	1159.2	1158.9	1161.4	1163.9	1161.4
52.5°	1102.5	1107.4	1112.2	1110.2	1105.8	1102.7	1101.0	1100.2	1102.2	1104.2	1102.2
55°	1011.7	1017.4	1023.0	1021.6	1017.8	1014.7	1012.2	1010.6	1011.9	1013.1	1011.9
57.5°	919.0	924.5	930.0	929.0	925.7	922.6	919.6	917.8	919.5	921.3	919.5
60°	858.1	863.1	868.2	866.6	862.8	859.7	857.2	855.6	856.9	858.1	856.9
62.5°	796.1	801.1	806.2	804.2	800.0	796.6	794.1	792.5	793.8	795.0	793.8
65°	701.7	706.1	710.5	708.8	705.0	701.9	699.4	697.7	698.3	698.9	698.3
67.5°	606.5	610.2	614.0	612.2	608.6	604.9	601.3	598.8	599.8	600.8	599.8
70°	541.1	544.9	548.6	547.2	544.1	540.9	537.8	535.5	535.5	535.5	535.5
72.5°	478.0	481.2	484.5	482.6	478.9	475.8	473.2	471.2	471.2	471.2	471.2
75°	381.9	383.7	385.6	384.7	382.8	380.3	377.2	374.7	374.0	373.4	374.0
77.5°	289.1	289.1	289.1	287.4	285.0	282.6	280.2	278.2	277.5	276.7	277.5
80°	228.3	228.3	228.3	226.9	225.0	223.1	221.2	219.5	218.3	217.0	218.3
82.5°	171.9	170.9	169.9	168.2	166.4	164.0	161.1	159.3	160.5	161.8	160.5
85°	91.6	90.3	89.1	87.4	85.5	83.3	80.8	78.8	78.1	77.5	78.1
87.5°	28.6	28.2	28.0	27.2	26.1	24.5	22.5	21.0	20.7	20.2	20.7
90°	2.2	5.2	8.9	11.9	14.1	14.9	14.9	15.6	16.4	16.4	16.4
92.5°	8.2	12.9	13.1	13.1	15.9	17.3	18.5	18.6	19.3	19.3	19.3
95°	23.1	25.3	37.9	37.2	25.3	20.1	17.1	17.1	17.1	17.1	17.1
97.5°	44.1	47.3	49.4	66.2	69.9	67.6	55.1	46.3	41.4	39.1	41.4
100°	62.5	64.0	68.5	69.2	87.8	105.7	96.7	85.6	81.9	79.6	81.9
102.5°	81.0	81.9	88.7	91.8	96.1	106.3	137.2	133.8	131.3	130.8	131.3
105°	108.6	109.4	122.0	128.0	131.0	131.0	130.2	145.1	168.9	174.1	168.9
107.5°	138.3	141.7	156.6	172.5	175.9	176.8	172.9	170.7	169.8	170.4	169.8
110°	158.5	163.7	181.6	201.7	206.9	208.3	206.9	204.6	203.1	203.1	203.1



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	178.1	185.7	206.0	229.0	237.8	242.3	239.0	237.4	235.9	237.1	235.9
115°	208.3	219.5	246.3	270.1	288.0	290.2	289.5	289.5	288.7	288.7	288.7
117.5°	236.3	254.2	284.2	311.9	332.6	338.6	341.5	340.6	339.8	341.2	339.8
120°	256.0	276.8	311.0	342.3	362.4	371.3	374.3	372.8	374.3	372.8	374.3
122.5°	276.8	302.4	336.0	368.5	392.1	402.3	405.8	406.1	406.4	405.5	406.4
125°	308.1	339.3	378.7	412.2	436.8	448.7	451.7	452.4	453.9	457.6	453.9
127.5°	339.6	375.0	418.3	450.6	475.8	490.2	494.8	496.5	499.6	501.2	499.6
130°	361.6	401.8	445.7	476.2	500.8	516.4	524.6	526.8	530.5	529.8	530.5
132.5°	384.8	426.8	471.3	503.0	525.8	542.6	549.6	556.0	557.3	558.4	557.3
135°	418.9	464.3	509.0	540.2	561.8	578.2	587.1	593.0	596.8	599.0	596.8
137.5°	454.8	502.7	545.6	573.4	595.1	609.3	619.4	625.6	629.5	631.3	629.5
140°	479.2	525.3	567.0	596.0	615.4	629.5	638.4	645.9	650.3	650.3	650.3
142.5°	502.4	548.0	588.4	617.5	634.4	647.4	656.9	662.5	667.6	667.6	667.6
145°	535.0	580.4	617.6	646.6	660.8	672.7	683.1	687.5	690.5	690.5	690.5
147.5°	569.1	609.3	643.2	671.0	682.9	696.9	705.1	708.7	712.4	710.8	712.4
150°	589.3	626.5	659.3	685.3	697.2	710.6	718.8	721.8	725.5	723.3	725.5
152.5°	609.0	644.4	674.2	698.4	708.5	721.9	731.3	734.3	736.8	735.2	736.8
155°	635.5	666.7	694.2	716.6	725.5	738.1	747.1	750.8	753.8	750.0	753.8
157.5°	659.1	686.1	710.0	730.6	740.1	750.9	759.3	763.9	766.9	765.2	766.9
160°	673.4	698.0	719.5	738.9	747.8	757.5	766.4	771.6	774.6	772.4	774.6
162.5°	685.3	707.5	727.9	745.4	753.2	761.7	772.4	777.0	780.0	777.1	780.0
165°	702.4	720.3	738.1	753.0	759.7	766.4	777.6	782.8	785.0	782.0	785.0
167.5°	715.4	729.1	743.5	756.3	761.2	767.8	778.9	783.2	786.1	782.3	786.1
170°	722.5	734.4	747.1	757.5	761.2	767.2	778.3	782.0	784.3	780.6	784.3
172.5°	728.5	737.4	747.7	756.9	758.8	763.6	774.2	777.9	779.5	776.4	779.5
175°	734.4	739.6	747.1	753.0	752.3	755.3	764.2	767.2	770.1	765.7	770.1
177.5°	737.3	739.6	742.0	745.6	743.2	743.2	749.8	751.5	752.1	749.8	752.1
180°	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9
2.5°	1997.8	1996.0	1994.0	1997.3	2005.8	2009.8	2000.3	1990.8	2000.3	2009.8	2005.8
5°	1991.2	1988.7	1987.5	1991.8	2001.9	2006.2	1993.7	1981.2	1993.7	2006.2	2001.9
7.5°	1976.9	1974.1	1972.6	1976.6	1986.2	1990.2	1977.7	1965.1	1977.7	1990.2	1986.2
10°	1964.1	1961.0	1958.5	1962.2	1972.3	1976.6	1964.1	1951.6	1964.1	1976.6	1972.3
12.5°	1947.3	1944.8	1943.3	1947.1	1956.1	1959.7	1947.2	1934.7	1947.2	1959.7	1956.1
15°	1917.6	1915.0	1913.1	1916.5	1925.3	1928.7	1916.2	1903.7	1916.2	1928.7	1925.3
17.5°	1880.3	1877.6	1875.4	1878.5	1886.6	1889.8	1878.0	1866.2	1878.0	1889.8	1886.6
20°	1849.8	1848.3	1847.6	1851.4	1859.5	1862.8	1851.6	1840.3	1851.6	1862.8	1859.5
22.5°	1815.1	1814.8	1816.2	1820.7	1828.3	1831.3	1820.0	1808.7	1820.0	1831.3	1828.3
25°	1762.5	1762.8	1764.7	1769.0	1775.9	1778.3	1767.0	1755.7	1767.0	1778.3	1775.9
27.5°	1706.6	1706.8	1708.0	1711.6	1717.3	1719.3	1709.9	1700.5	1709.9	1719.3	1717.3
30°	1664.9	1665.1	1666.3	1670.1	1676.4	1678.7	1669.3	1659.9	1669.3	1678.7	1676.4
32.5°	1621.1	1620.4	1620.6	1624.4	1631.6	1634.9	1626.0	1617.1	1626.0	1634.9	1631.6
35°	1553.6	1552.4	1551.7	1554.9	1561.7	1565.0	1557.5	1550.0	1557.5	1565.0	1561.7
37.5°	1481.6	1481.1	1481.2	1484.4	1490.8	1494.2	1488.4	1482.7	1488.4	1494.2	1490.8
40°	1431.0	1430.7	1431.3	1435.1	1442.0	1445.6	1439.3	1433.1	1439.3	1445.6	1442.0
42.5°	1381.0	1380.4	1380.0	1382.7	1388.6	1391.8	1387.1	1382.3	1387.1	1391.8	1388.6
45°	1300.9	1300.6	1300.6	1303.4	1309.1	1312.2	1307.8	1303.4	1307.8	1312.2	1309.1
47.5°	1217.4	1217.5	1218.2	1220.8	1225.2	1227.6	1224.2	1220.8	1224.2	1227.6	1225.2
50°	1158.9	1159.2	1160.5	1163.3	1167.7	1169.9	1165.5	1161.1	1165.5	1169.9	1167.7
52.5°	1100.2	1101.0	1102.7	1105.8	1110.2	1112.2	1107.4	1102.5	1107.4	1112.2	1110.2
55°	1010.6	1012.2	1014.7	1017.8	1021.6	1023.0	1017.4	1011.7	1017.4	1023.0	1021.6
57.5°	917.8	919.6	922.6	925.7	929.0	930.0	924.5	919.0	924.5	930.0	929.0
60°	855.6	857.2	859.7	862.8	866.6	868.2	863.1	858.1	863.1	868.2	866.6
62.5°	792.5	794.1	796.6	800.0	804.2	806.2	801.1	796.1	801.1	806.2	804.2
65°	697.7	699.4	701.9	705.0	708.8	710.5	706.1	701.7	706.1	710.5	708.8
67.5°	598.8	601.3	604.9	608.6	612.2	614.0	610.2	606.5	610.2	614.0	612.2
70°	535.5	537.8	540.9	544.1	547.2	548.6	544.9	541.1	544.9	548.6	547.2
72.5°	471.2	473.2	475.8	478.9	482.6	484.5	481.2	478.0	481.2	484.5	482.6
75°	374.7	377.2	380.3	382.8	384.7	385.6	383.7	381.9	383.7	385.6	384.7
77.5°	278.2	280.2	282.6	285.0	287.4	289.1	289.1	289.1	289.1	289.1	287.4
80°	219.5	221.2	223.1	225.0	226.9	228.3	228.3	228.3	228.3	228.3	226.9
82.5°	159.3	161.1	164.0	166.4	168.2	169.9	170.9	171.9	170.9	169.9	168.2
85°	78.8	80.8	83.3	85.5	87.4	89.1	90.3	91.6	90.3	89.1	87.4
87.5°	21.0	22.5	24.5	26.1	27.2	28.0	28.2	28.6	28.2	27.8	27.5
90°	15.6	14.9	14.9	14.1	11.9	8.9	5.2	2.2	5.2	8.2	13.4
92.5°	18.6	18.5	17.3	15.9	13.1	13.1	12.9	8.2	14.1	20.1	28.9
95°	17.1	17.1	20.1	25.3	37.2	37.9	25.3	23.1	32.7	46.1	58.0
97.5°	46.3	55.1	67.6	69.9	66.2	49.4	47.3	44.1	60.0	73.2	92.4
100°	85.6	96.7	105.7	87.8	69.2	68.5	64.0	62.5	79.6	92.3	110.9
102.5°	133.8	137.2	106.3	96.1	91.8	88.7	81.9	81.0	98.1	115.5	131.1
105°	145.1	130.2	131.0	131.0	128.0	122.0	109.4	108.6	128.0	148.1	167.4
107.5°	170.7	172.9	176.8	175.9	172.5	156.6	141.7	138.3	155.7	179.8	201.1
110°	204.6	206.9	208.3	206.9	201.7	181.6	163.7	158.5	174.1	199.4	222.5



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	237.4	239.0	242.3	237.8	229.0	206.0	185.7	178.1	193.8	219.7	243.3
115°	289.5	289.5	290.2	288.0	270.1	246.3	219.5	208.3	221.7	245.6	271.6
117.5°	340.6	341.5	338.6	332.6	311.9	284.2	254.2	236.3	246.9	272.0	298.8
120°	372.8	374.3	371.3	362.4	342.3	311.0	276.8	256.0	264.2	288.7	315.5
122.5°	406.1	405.8	402.3	392.1	368.5	336.0	302.4	276.8	280.2	303.0	329.2
125°	452.4	451.7	448.7	436.8	412.2	378.7	339.3	308.1	303.6	322.9	349.7
127.5°	496.5	494.8	490.2	475.8	450.6	418.3	375.0	339.6	329.6	341.8	366.4
130°	526.8	524.6	516.4	500.8	476.2	445.7	401.8	361.6	347.5	354.9	376.5
132.5°	556.0	549.6	542.6	525.8	503.0	471.3	426.8	384.8	365.4	368.6	385.4
135°	593.0	587.1	578.2	561.8	540.2	509.0	464.3	418.9	392.1	389.2	398.8
137.5°	625.6	619.4	609.3	595.1	573.4	545.6	502.7	454.8	421.0	411.0	414.8
140°	645.9	638.4	629.5	615.4	596.0	567.0	525.3	479.2	441.2	427.1	424.9
142.5°	662.5	656.9	647.4	634.4	617.5	588.4	548.0	502.4	462.1	443.8	438.6
145°	687.5	683.1	672.7	660.8	646.6	617.6	580.4	535.0	494.8	471.0	459.9
147.5°	708.7	705.1	696.9	682.9	671.0	643.2	609.3	569.1	527.9	498.4	484.0
150°	721.8	718.8	710.6	697.2	685.3	659.3	626.5	589.3	549.9	518.6	500.0
152.5°	734.3	731.3	721.9	708.5	698.4	674.2	644.4	609.0	568.9	537.7	518.5
155°	750.8	747.1	738.1	725.5	716.6	694.2	666.7	635.5	601.2	568.5	546.9
157.5°	763.9	759.3	750.9	740.1	730.6	710.0	686.1	659.1	629.2	598.0	575.9
160°	771.6	766.4	757.5	747.8	738.9	719.5	698.0	673.4	645.9	617.6	593.8
162.5°	777.0	772.4	761.7	753.2	745.4	727.9	707.5	685.3	660.8	636.1	614.0
165°	782.8	777.6	766.4	759.7	753.0	738.1	720.3	702.4	681.6	661.5	643.6
167.5°	783.2	778.9	767.8	761.2	756.3	743.5	729.1	715.4	699.2	683.4	668.5
170°	782.0	778.3	767.2	761.2	757.5	747.1	734.4	722.5	709.9	696.5	684.6
172.5°	777.9	774.2	763.6	758.8	756.9	747.7	737.4	728.5	717.6	707.8	698.3
175°	767.2	764.2	755.3	752.3	753.0	747.1	739.6	734.4	727.7	721.8	716.6
177.5°	751.5	749.8	743.2	743.2	745.6	742.0	739.6	737.3	734.3	732.5	730.7
180°	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9
2.5°	1997.3	1994.0	1996.0	1997.8	1998.8	1999.8	1998.8	1997.8	1996.0	1994.0	1997.3
5°	1991.8	1987.5	1988.7	1991.2	1997.5	2003.7	1997.5	1991.2	1988.7	1987.5	1991.8
7.5°	1976.6	1972.6	1974.1	1976.9	1983.4	1989.9	1983.4	1976.9	1974.1	1972.6	1976.6
10°	1962.2	1958.5	1961.0	1964.1	1969.1	1974.1	1969.1	1964.1	1961.0	1958.5	1962.2
12.5°	1947.1	1943.3	1944.8	1947.3	1952.9	1958.4	1952.9	1947.3	1944.8	1943.3	1947.1
15°	1916.5	1913.1	1915.0	1917.6	1922.6	1927.6	1922.6	1917.6	1915.0	1913.1	1916.5
17.5°	1878.5	1875.4	1877.6	1880.3	1884.7	1889.0	1884.7	1880.3	1877.6	1875.4	1878.5
20°	1851.4	1847.6	1848.3	1849.8	1854.2	1858.6	1854.2	1849.8	1848.3	1847.6	1851.4
22.5°	1820.7	1816.2	1814.8	1815.1	1820.5	1825.9	1820.5	1815.1	1814.8	1816.2	1820.7
25°	1769.0	1764.7	1762.8	1762.5	1766.8	1771.2	1766.8	1762.5	1762.8	1764.7	1769.0
27.5°	1711.6	1708.0	1706.8	1706.6	1709.8	1712.9	1709.8	1706.6	1706.8	1708.0	1711.6
30°	1670.1	1666.3	1665.1	1664.9	1668.1	1671.2	1668.1	1664.9	1665.1	1666.3	1670.1
32.5°	1624.4	1620.6	1620.4	1621.1	1624.7	1628.4	1624.7	1621.1	1620.4	1620.6	1624.4
35°	1554.9	1551.7	1552.4	1553.6	1556.7	1559.9	1556.7	1553.6	1552.4	1551.7	1554.9
37.5°	1484.4	1481.2	1481.1	1481.6	1484.2	1486.9	1484.2	1481.6	1481.1	1481.2	1484.4
40°	1435.1	1431.3	1430.7	1431.0	1434.1	1437.3	1434.1	1431.0	1430.7	1431.3	1435.1
42.5°	1382.7	1380.0	1380.4	1381.0	1382.7	1384.3	1382.7	1381.0	1380.4	1380.0	1382.7
45°	1303.4	1300.6	1300.6	1300.9	1302.2	1303.4	1302.2	1300.9	1300.6	1300.6	1303.4
47.5°	1220.8	1218.2	1217.5	1217.4	1219.4	1221.4	1219.4	1217.4	1217.5	1218.2	1220.8
50°	1163.3	1160.5	1159.2	1158.9	1161.4	1163.9	1161.4	1158.9	1159.2	1160.5	1163.3
52.5°	1105.8	1102.7	1101.0	1100.2	1102.2	1104.2	1102.2	1100.2	1101.0	1102.7	1105.8
55°	1017.8	1014.7	1012.2	1010.6	1011.9	1013.1	1011.9	1010.6	1012.2	1014.7	1017.8
57.5°	925.7	922.6	919.6	917.8	919.5	921.3	919.5	917.8	919.6	922.6	925.7
60°	862.8	859.7	857.2	855.6	856.9	858.1	856.9	855.6	857.2	859.7	862.8
62.5°	800.0	796.6	794.1	792.5	793.8	795.0	793.8	792.5	794.1	796.6	800.0
65°	705.0	701.9	699.4	697.7	698.3	698.9	698.3	697.7	699.4	701.9	705.0
67.5°	608.6	604.9	601.3	598.8	599.8	600.8	599.8	598.8	601.3	604.9	608.6
70°	544.1	540.9	537.8	535.5	535.5	535.5	535.5	535.5	537.8	540.9	544.1
72.5°	478.9	475.8	473.2	471.2	471.2	471.2	471.2	471.2	473.2	475.8	478.9
75°	382.8	380.3	377.2	374.7	374.0	373.4	374.0	374.7	377.2	380.3	382.8
77.5°	285.0	282.6	280.2	278.2	277.5	276.7	277.5	278.2	280.2	282.6	285.0
80°	225.0	223.1	221.2	219.5	218.3	217.0	218.3	219.5	221.2	223.1	225.0
82.5°	166.4	164.0	161.1	159.3	160.5	161.8	160.5	159.3	161.1	164.0	166.4
85°	85.5	83.3	80.8	78.8	78.1	77.5	78.1	78.8	80.8	83.3	85.5
87.5°	26.7	26.0	25.0	24.0	24.1	23.3	24.1	24.0	25.0	26.0	26.7
90°	17.1	22.3	27.5	30.5	33.5	32.0	33.5	30.5	27.5	22.3	17.1
92.5°	34.4	43.2	49.6	54.9	57.3	57.0	57.3	54.9	49.6	43.2	34.4
95°	69.2	79.6	90.0	97.5	101.9	100.5	101.9	97.5	90.0	79.6	69.2
97.5°	106.7	120.7	132.3	139.3	143.8	146.7	143.8	139.3	132.3	120.7	106.7
100°	131.7	145.1	158.5	166.7	174.1	177.1	174.1	166.7	158.5	145.1	131.7
102.5°	151.9	169.5	184.1	192.9	199.1	202.1	199.1	192.9	184.1	169.5	151.9
105°	185.3	203.9	219.5	230.7	237.4	239.6	237.4	230.7	219.5	203.9	185.3
107.5°	218.6	237.8	252.2	264.6	272.8	277.5	272.8	264.6	252.2	237.8	218.6
110°	244.8	260.4	276.1	287.2	295.4	298.4	295.4	287.2	276.1	260.4	244.8



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	266.8	284.2	299.9	311.0	320.4	324.6	320.4	311.0	299.9	284.2	266.8
115°	297.6	320.7	334.8	345.3	352.0	355.7	352.0	345.3	334.8	320.7	297.6
117.5°	323.2	347.3	362.8	370.9	374.0	376.7	374.0	370.9	362.8	347.3	323.2
120°	339.3	361.6	379.5	389.9	393.6	395.1	393.6	389.9	379.5	361.6	339.3
122.5°	354.2	375.3	392.6	405.4	411.5	413.0	411.5	405.4	392.6	375.3	354.2
125°	375.0	395.1	413.0	425.6	432.3	436.0	432.3	425.6	413.0	395.1	375.0
127.5°	393.2	414.9	431.3	442.7	449.3	452.3	449.3	442.7	431.3	414.9	393.2
130°	403.3	425.6	442.0	454.6	460.6	463.6	460.6	454.6	442.0	425.6	403.3
132.5°	411.0	434.6	451.5	463.0	469.5	472.5	469.5	463.0	451.5	434.6	411.0
135°	420.4	445.0	462.8	474.0	479.9	482.9	479.9	474.0	462.8	445.0	420.4
137.5°	428.6	450.9	469.5	481.3	486.6	488.6	486.6	481.3	469.5	450.9	428.6
140°	434.6	453.9	472.5	483.7	489.6	490.4	489.6	483.7	472.5	453.9	434.6
142.5°	442.3	457.5	473.7	484.9	490.8	492.1	490.8	484.9	473.7	457.5	442.3
145°	456.1	465.1	476.2	486.6	491.8	493.3	491.8	486.6	476.2	465.1	456.1
147.5°	473.5	476.4	482.2	489.0	494.1	495.1	494.1	489.0	482.2	476.4	473.5
150°	486.6	485.9	488.1	492.6	497.1	496.3	497.1	492.6	488.1	485.9	486.6
152.5°	501.5	497.2	497.1	499.1	501.2	501.1	501.2	499.1	497.1	497.2	501.5
155°	526.8	518.6	514.2	512.7	512.7	511.9	512.7	512.7	514.2	518.6	526.8
157.5°	554.6	543.2	536.5	532.9	531.9	530.2	531.9	532.9	536.5	543.2	554.6
160°	573.7	561.0	554.4	548.4	546.2	543.9	546.2	548.4	554.4	561.0	573.7
162.5°	591.6	579.5	572.2	566.9	564.6	561.2	564.6	566.9	572.2	579.5	591.6
165°	620.6	607.9	599.7	595.3	592.3	589.3	592.3	595.3	599.7	607.9	620.6
167.5°	649.6	635.8	630.4	625.3	622.5	617.2	622.5	625.3	630.4	635.8	649.6
170°	667.5	654.8	651.8	647.4	642.2	636.2	642.2	647.4	651.8	654.8	667.5
172.5°	682.9	674.4	671.5	667.0	665.4	660.6	665.4	667.0	671.5	674.4	682.9
175°	705.4	698.7	698.7	698.0	695.7	691.3	695.7	698.0	698.7	698.7	705.4
177.5°	724.2	720.6	723.0	723.0	722.4	718.2	722.4	723.0	723.0	720.6	724.2
180°	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7	736.7



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2000.9	2000.9	2000.9	2000.9
2.5°	2005.8	2009.8	2000.3	1990.8
5°	2001.9	2006.2	1993.7	1981.2
7.5°	1986.2	1990.2	1977.7	1965.1
10°	1972.3	1976.6	1964.1	1951.6
12.5°	1956.1	1959.7	1947.2	1934.7
15°	1925.3	1928.7	1916.2	1903.7
17.5°	1886.6	1889.8	1878.0	1866.2
20°	1859.5	1862.8	1851.6	1840.3
22.5°	1828.3	1831.3	1820.0	1808.7
25°	1775.9	1778.3	1767.0	1755.7
27.5°	1717.3	1719.3	1709.9	1700.5
30°	1676.4	1678.7	1669.3	1659.9
32.5°	1631.6	1634.9	1626.0	1617.1
35°	1561.7	1565.0	1557.5	1550.0
37.5°	1490.8	1494.2	1488.4	1482.7
40°	1442.0	1445.6	1439.3	1433.1
42.5°	1388.6	1391.8	1387.1	1382.3
45°	1309.1	1312.2	1307.8	1303.4
47.5°	1225.2	1227.6	1224.2	1220.8
50°	1167.7	1169.9	1165.5	1161.1
52.5°	1110.2	1112.2	1107.4	1102.5
55°	1021.6	1023.0	1017.4	1011.7
57.5°	929.0	930.0	924.5	919.0
60°	866.6	868.2	863.1	858.1
62.5°	804.2	806.2	801.1	796.1
65°	708.8	710.5	706.1	701.7
67.5°	612.2	614.0	610.2	606.5
70°	547.2	548.6	544.9	541.1
72.5°	482.6	484.5	481.2	478.0
75°	384.7	385.6	383.7	381.9
77.5°	287.4	289.1	289.1	289.1
80°	226.9	228.3	228.3	228.3
82.5°	168.2	169.9	170.9	171.9
85°	87.4	89.1	90.3	91.6
87.5°	27.5	27.8	28.2	28.6
90°	13.4	8.2	5.2	2.2
92.5°	28.9	20.1	14.1	8.2
95°	58.0	46.1	32.7	23.1
97.5°	92.4	73.2	60.0	44.1
100°	110.9	92.3	79.6	62.5
102.5°	131.1	115.5	98.1	81.0
105°	167.4	148.1	128.0	108.6
107.5°	201.1	179.8	155.7	138.3
110°	222.5	199.4	174.1	158.5

TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	243.3	219.7	193.8	178.1
115°	271.6	245.6	221.7	208.3
117.5°	298.8	272.0	246.9	236.3
120°	315.5	288.7	264.2	256.0
122.5°	329.2	303.0	280.2	276.8
125°	349.7	322.9	303.6	308.1
127.5°	366.4	341.8	329.6	339.6
130°	376.5	354.9	347.5	361.6
132.5°	385.4	368.6	365.4	384.8
135°	398.8	389.2	392.1	418.9
137.5°	414.8	411.0	421.0	454.8
140°	424.9	427.1	441.2	479.2
142.5°	438.6	443.8	462.1	502.4
145°	459.9	471.0	494.8	535.0
147.5°	484.0	498.4	527.9	569.1
150°	500.0	518.6	549.9	589.3
152.5°	518.5	537.7	568.9	609.0
155°	546.9	568.5	601.2	635.5
157.5°	575.9	598.0	629.2	659.1
160°	593.8	617.6	645.9	673.4
162.5°	614.0	636.1	660.8	685.3
165°	643.6	661.5	681.6	702.4
167.5°	668.5	683.4	699.2	715.4
170°	684.6	696.5	709.9	722.5
172.5°	698.3	707.8	717.6	728.5
175°	716.6	721.8	727.7	734.4
177.5°	730.7	732.5	734.3	737.3
180°	736.7	736.7	736.7	736.7



TEST NUMBER: P1427718

CATALOG NUMBER: SQ2W-F-K-050U-125D-L835-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.78	22.90	22.51	23.66	24.57	21.69	22.82	22.43	23.58	24.49
	3H	23.59	24.60	24.33	25.37	26.31	23.48	24.50	24.23	25.26	26.21
	4H	24.29	25.25	25.06	26.03	26.98	24.18	25.14	24.95	25.91	26.87
	6H	24.74	25.63	25.52	26.41	27.38	24.60	25.49	25.38	26.27	27.24
	8H	24.91	25.75	25.70	26.56	27.53	24.76	25.60	25.55	26.41	27.37
	12H	25.01	25.81	25.80	26.61	27.60	24.83	25.63	25.62	26.43	27.43
4H	2H	22.39	23.34	23.16	24.12	25.07	22.32	23.28	23.09	24.06	25.01
	3H	24.43	25.23	25.22	26.05	27.02	24.34	25.14	25.12	25.95	26.92
	4H	25.26	25.99	26.06	26.80	27.80	25.15	25.88	25.95	26.69	27.69
	6H	25.83	26.46	26.64	27.29	28.30	25.68	26.32	26.50	27.15	28.16
	8H	26.05	26.64	26.87	27.47	28.49	25.89	26.48	26.71	27.31	28.33
	12H	26.17	26.71	27.01	27.56	28.58	25.99	26.52	26.83	27.37	28.40
8H	4H	25.52	26.11	26.34	26.95	27.96	25.43	26.02	26.25	26.85	27.87
	6H	26.22	26.71	27.07	27.59	28.61	26.09	26.58	26.94	27.46	28.48
	8H	26.53	26.97	27.39	27.84	28.87	26.38	26.81	27.24	27.68	28.72
	12H	26.73	27.11	27.59	27.97	29.06	26.54	26.92	27.40	27.78	28.87
12H	4H	25.53	26.06	26.37	26.92	27.94	25.44	25.97	26.28	26.82	27.85
	6H	26.28	26.71	27.14	27.58	28.62	26.15	26.59	27.01	27.46	28.49
	8H	26.62	27.01	27.49	27.87	28.96	26.47	26.86	27.34	27.72	28.81