

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428146

Luminaire Tested: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428146
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE PRISM LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10044.7 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	36	34	32	28				
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24				
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28492	28492	28492	28492
5°	28269	28782	28269	28782
10°	28412	28994	28412	28994
15°	28344	29061	28344	29061
20°	28142	29649	28142	29649
25°	27981	31206	27981	31206
30°	27823	31858	27823	31858
35°	27429	31915	27429	31915
40°	26698	29488	26698	29488
45°	25897	22447	25897	22447
50°	24882	18695	24882	18695
55°	23158	13444	23158	13444
60°	19940	9639	19940	9639
65°	16821	9478	16821	9478
70°	14001	9068	14001	9068
75°	11871	8496	11871	8496
80°	10060	7634	10060	7634
85°	7947	4150	7947	4150

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 28329 cd/sqm



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.0	1.7
10°-20°	486.3	4.8
20°-30°	761.9	7.6
30°-40°	939.9	9.4
40°-50°	884.8	8.8
50°-60°	626.6	6.2
60°-70°	357.0	3.6
70°-80°	176.7	1.8
80°-90°	51.1	0.5
90°-100°	152.4	1.5
100°-110°	444.5	4.4
110°-120°	725.4	7.2
120°-130°	920.5	9.2
130°-140°	985.0	9.8
140°-150°	919.8	9.2
150°-160°	756.8	7.5
160°-170°	507.6	5.1
170°-180°	180.2	1.8
0°-30°	1416.3	14.1
0°-40°	2356.1	23.5
0°-60°	3867.5	38.5
0°-90°	4452.4	44.3
90°-120°	1322.4	13.2
90°-150°	4147.7	41.3
90°-180°	5592.0	55.7
0°-180°	10044.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1765	1765	1765	1765	1765	
5°	1744	1776	1744	1776	1744	166
15°	1696	1739	1696	1739	1696	478
25°	1571	1752	1571	1752	1571	723
35°	1392	1619	1392	1619	1392	868
45°	1134	983	1134	983	1134	873
55°	823	478	823	478	823	726
65°	440	248	440	248	440	442
75°	190	136	190	136	190	206
85°	43	22	43	22	43	50
90°	6	43	6	83	6	7
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1751.3	1762.6	1773.9	1771.2	1763.9	1760.9	1762.2	1763.6	1764.9	1766.2	1764.9
5°	1744.2	1758.3	1772.4	1770.3	1762.9	1760.0	1761.6	1764.3	1770.1	1775.9	1770.1
7.5°	1737.5	1751.9	1766.4	1764.5	1757.2	1755.0	1757.8	1761.7	1768.8	1775.9	1768.8
10°	1733.0	1745.5	1757.9	1756.0	1749.4	1748.2	1752.3	1756.9	1762.7	1768.5	1762.7
12.5°	1719.6	1731.4	1743.1	1741.6	1735.6	1735.4	1740.9	1746.2	1751.4	1756.5	1751.4
15°	1695.7	1706.5	1717.3	1717.5	1714.2	1716.2	1723.7	1730.3	1734.5	1738.6	1734.5
17.5°	1663.3	1676.4	1689.5	1692.5	1692.1	1697.3	1707.9	1716.9	1721.2	1725.6	1721.2
20°	1637.9	1653.6	1669.4	1674.6	1676.2	1683.7	1697.0	1709.0	1717.3	1725.6	1717.3
22.5°	1611.0	1629.4	1647.8	1654.7	1657.7	1669.1	1689.0	1707.5	1721.7	1736.0	1721.7
25°	1570.7	1589.0	1607.2	1620.5	1632.1	1652.4	1681.4	1708.6	1730.1	1751.7	1730.1
27.5°	1523.7	1541.8	1559.9	1582.7	1607.0	1635.6	1668.2	1697.0	1714.1	1731.2	1714.1
30°	1492.4	1509.8	1527.2	1553.3	1582.3	1613.8	1647.8	1677.3	1693.0	1708.8	1693.0
32.5°	1453.6	1471.6	1489.7	1517.5	1548.5	1582.3	1619.0	1650.1	1664.5	1678.9	1664.5
35°	1391.6	1409.1	1426.5	1458.8	1496.1	1533.8	1572.0	1602.6	1610.9	1619.2	1610.9
37.5°	1320.4	1340.1	1359.8	1396.1	1437.9	1469.5	1490.9	1507.1	1507.5	1508.0	1507.5
40°	1266.7	1292.4	1318.1	1354.3	1394.1	1416.1	1420.2	1420.7	1409.9	1399.1	1409.9
42.5°	1214.4	1247.4	1280.4	1309.6	1337.4	1343.1	1326.7	1302.4	1254.5	1206.6	1254.5
45°	1134.2	1173.2	1212.1	1230.0	1240.7	1204.3	1120.5	1049.4	1016.3	983.1	1016.3
47.5°	1048.8	1087.2	1125.7	1120.8	1101.4	1046.2	955.1	881.1	858.2	835.4	858.2
50°	990.6	1027.0	1063.5	1037.2	989.9	927.8	850.7	787.4	765.9	744.3	765.9
52.5°	924.9	957.4	989.9	950.1	886.3	820.8	753.6	695.1	662.2	629.4	662.2
55°	822.7	845.1	867.4	823.9	758.4	686.3	607.5	540.6	509.1	477.6	509.1
57.5°	699.6	715.3	731.1	696.8	645.9	574.2	481.7	403.4	368.1	332.8	368.1
60°	617.5	629.9	642.3	611.3	565.7	497.3	406.1	333.3	315.9	298.5	315.9
62.5°	542.9	554.0	565.1	532.7	485.7	424.6	349.3	291.3	285.2	279.1	285.2
65°	440.3	451.0	461.8	427.8	378.9	331.2	284.8	249.8	248.9	248.1	248.9
67.5°	350.3	362.1	373.9	341.9	295.3	260.0	236.2	218.0	217.0	216.0	217.0
70°	296.6	309.0	321.5	291.6	247.7	219.1	205.8	195.5	193.8	192.1	193.8
72.5°	251.8	263.6	275.4	249.4	210.7	187.1	178.5	171.7	170.8	169.8	170.8
75°	190.3	199.4	208.5	189.7	161.5	145.3	141.2	137.8	137.0	136.2	137.0
77.5°	138.0	143.8	149.7	137.3	118.9	108.6	106.5	104.6	103.8	103.0	103.8
80°	108.2	110.7	113.2	104.5	92.0	85.4	84.6	83.7	82.9	82.1	82.9
82.5°	81.3	80.5	79.7	74.6	68.2	64.5	63.7	62.7	61.2	59.7	61.2
85°	42.9	41.2	39.6	37.9	36.3	33.8	30.5	27.4	24.9	22.4	24.9
87.5°	14.6	16.1	18.1	17.1	15.0	13.4	12.7	12.6	13.0	13.0	13.0
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1763.6	1762.2	1760.9	1763.9	1771.2	1773.9	1762.6	1751.3	1762.6	1773.9	1771.2
5°	1764.3	1761.6	1760.0	1762.9	1770.3	1772.4	1758.3	1744.2	1758.3	1772.4	1770.3
7.5°	1761.7	1757.8	1755.0	1757.2	1764.5	1766.4	1751.9	1737.5	1751.9	1766.4	1764.5
10°	1756.9	1752.3	1748.2	1749.4	1756.0	1757.9	1745.5	1733.0	1745.5	1757.9	1756.0
12.5°	1746.2	1740.9	1735.4	1735.6	1741.6	1743.1	1731.4	1719.6	1731.4	1743.1	1741.6
15°	1730.3	1723.7	1716.2	1714.2	1717.5	1717.3	1706.5	1695.7	1706.5	1717.3	1717.5
17.5°	1716.9	1707.9	1697.3	1692.1	1692.5	1689.5	1676.4	1663.3	1676.4	1689.5	1692.5
20°	1709.0	1697.0	1683.7	1676.2	1674.6	1669.4	1653.6	1637.9	1653.6	1669.4	1674.6
22.5°	1707.5	1689.0	1669.1	1657.7	1654.7	1647.8	1629.4	1611.0	1629.4	1647.8	1654.7
25°	1708.6	1681.4	1652.4	1632.1	1620.5	1607.2	1589.0	1570.7	1589.0	1607.2	1620.5
27.5°	1697.0	1668.2	1635.6	1607.0	1582.7	1559.9	1541.8	1523.7	1541.8	1559.9	1582.7
30°	1677.3	1647.8	1613.8	1582.3	1553.3	1527.2	1509.8	1492.4	1509.8	1527.2	1553.3
32.5°	1650.1	1619.0	1582.3	1548.5	1517.5	1489.7	1471.6	1453.6	1471.6	1489.7	1517.5
35°	1602.6	1572.0	1533.8	1496.1	1458.8	1426.5	1409.1	1391.6	1409.1	1426.5	1458.8
37.5°	1507.1	1490.9	1469.5	1437.9	1396.1	1359.8	1340.1	1320.4	1340.1	1359.8	1396.1
40°	1420.7	1420.2	1416.1	1394.1	1354.3	1318.1	1292.4	1266.7	1292.4	1318.1	1354.3
42.5°	1302.4	1326.7	1343.1	1337.4	1309.6	1280.4	1247.4	1214.4	1247.4	1280.4	1309.6
45°	1049.4	1120.5	1204.3	1240.7	1230.0	1212.1	1173.2	1134.2	1173.2	1212.1	1230.0
47.5°	881.1	955.1	1046.2	1101.4	1120.8	1125.7	1087.2	1048.8	1087.2	1125.7	1120.8
50°	787.4	850.7	927.8	989.9	1037.2	1063.5	1027.0	990.6	1027.0	1063.5	1037.2
52.5°	695.1	753.6	820.8	886.3	950.1	989.9	957.4	924.9	957.4	989.9	950.1
55°	540.6	607.5	686.3	758.4	823.9	867.4	845.1	822.7	845.1	867.4	823.9
57.5°	403.4	481.7	574.2	645.9	696.8	731.1	715.3	699.6	715.3	731.1	696.8
60°	333.3	406.1	497.3	565.7	611.3	642.3	629.9	617.5	629.9	642.3	611.3
62.5°	291.3	349.3	424.6	485.7	532.7	565.1	554.0	542.9	554.0	565.1	532.7
65°	249.8	284.8	331.2	378.9	427.8	461.8	451.0	440.3	451.0	461.8	427.8
67.5°	218.0	236.2	260.0	295.3	341.9	373.9	362.1	350.3	362.1	373.9	341.9
70°	195.5	205.8	219.1	247.7	291.6	321.5	309.0	296.6	309.0	321.5	291.6
72.5°	171.7	178.5	187.1	210.7	249.4	275.4	263.6	251.8	263.6	275.4	249.4
75°	137.8	141.2	145.3	161.5	189.7	208.5	199.4	190.3	199.4	208.5	189.7
77.5°	104.6	106.5	108.6	118.9	137.3	149.7	143.8	138.0	143.8	149.7	137.3
80°	83.7	84.6	85.4	92.0	104.5	113.2	110.7	108.2	110.7	113.2	104.5
82.5°	62.7	63.7	64.5	68.2	74.6	79.7	80.5	81.3	80.5	79.7	74.6
85°	27.4	30.5	33.8	36.3	37.9	39.6	41.2	42.9	41.2	39.6	37.9
87.5°	12.6	12.7	13.4	15.0	17.1	18.1	16.1	14.6	16.1	17.7	17.9
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1763.9	1760.9	1762.2	1763.6	1764.9	1766.2	1764.9	1763.6	1762.2	1760.9	1763.9
5°	1762.9	1760.0	1761.6	1764.3	1770.1	1775.9	1770.1	1764.3	1761.6	1760.0	1762.9
7.5°	1757.2	1755.0	1757.8	1761.7	1768.8	1775.9	1768.8	1761.7	1757.8	1755.0	1757.2
10°	1749.4	1748.2	1752.3	1756.9	1762.7	1768.5	1762.7	1756.9	1752.3	1748.2	1749.4
12.5°	1735.6	1735.4	1740.9	1746.2	1751.4	1756.5	1751.4	1746.2	1740.9	1735.4	1735.6
15°	1714.2	1716.2	1723.7	1730.3	1734.5	1738.6	1734.5	1730.3	1723.7	1716.2	1714.2
17.5°	1692.1	1697.3	1707.9	1716.9	1721.2	1725.6	1721.2	1716.9	1707.9	1697.3	1692.1
20°	1676.2	1683.7	1697.0	1709.0	1717.3	1725.6	1717.3	1709.0	1697.0	1683.7	1676.2
22.5°	1657.7	1669.1	1689.0	1707.5	1721.7	1736.0	1721.7	1707.5	1689.0	1669.1	1657.7
25°	1632.1	1652.4	1681.4	1708.6	1730.1	1751.7	1730.1	1708.6	1681.4	1652.4	1632.1
27.5°	1607.0	1635.6	1668.2	1697.0	1714.1	1731.2	1714.1	1697.0	1668.2	1635.6	1607.0
30°	1582.3	1613.8	1647.8	1677.3	1693.0	1708.8	1693.0	1677.3	1647.8	1613.8	1582.3
32.5°	1548.5	1582.3	1619.0	1650.1	1664.5	1678.9	1664.5	1650.1	1619.0	1582.3	1548.5
35°	1496.1	1533.8	1572.0	1602.6	1610.9	1619.2	1610.9	1602.6	1572.0	1533.8	1496.1
37.5°	1437.9	1469.5	1490.9	1507.1	1507.5	1508.0	1507.5	1507.1	1490.9	1469.5	1437.9
40°	1394.1	1416.1	1420.2	1420.7	1409.9	1399.1	1409.9	1420.7	1420.2	1416.1	1394.1
42.5°	1337.4	1343.1	1326.7	1302.4	1254.5	1206.6	1254.5	1302.4	1326.7	1343.1	1337.4
45°	1240.7	1204.3	1120.5	1049.4	1016.3	983.1	1016.3	1049.4	1120.5	1204.3	1240.7
47.5°	1101.4	1046.2	955.1	881.1	858.2	835.4	858.2	881.1	955.1	1046.2	1101.4
50°	989.9	927.8	850.7	787.4	765.9	744.3	765.9	787.4	850.7	927.8	989.9
52.5°	886.3	820.8	753.6	695.1	662.2	629.4	662.2	695.1	753.6	820.8	886.3
55°	758.4	686.3	607.5	540.6	509.1	477.6	509.1	540.6	607.5	686.3	758.4
57.5°	645.9	574.2	481.7	403.4	368.1	332.8	368.1	403.4	481.7	574.2	645.9
60°	565.7	497.3	406.1	333.3	315.9	298.5	315.9	333.3	406.1	497.3	565.7
62.5°	485.7	424.6	349.3	291.3	285.2	279.1	285.2	291.3	349.3	424.6	485.7
65°	378.9	331.2	284.8	249.8	248.9	248.1	248.9	249.8	284.8	331.2	378.9
67.5°	295.3	260.0	236.2	218.0	217.0	216.0	217.0	218.0	236.2	260.0	295.3
70°	247.7	219.1	205.8	195.5	193.8	192.1	193.8	195.5	205.8	219.1	247.7
72.5°	210.7	187.1	178.5	171.7	170.8	169.8	170.8	171.7	178.5	187.1	210.7
75°	161.5	145.3	141.2	137.8	137.0	136.2	137.0	137.8	141.2	145.3	161.5
77.5°	118.9	108.6	106.5	104.6	103.8	103.0	103.8	104.6	106.5	108.6	118.9
80°	92.0	85.4	84.6	83.7	82.9	82.1	82.9	83.7	84.6	85.4	92.0
82.5°	68.2	64.5	63.7	62.7	61.2	59.7	61.2	62.7	63.7	64.5	68.2
85°	36.3	33.8	30.5	27.4	24.9	22.4	24.9	27.4	30.5	33.8	36.3
87.5°	16.5	17.2	19.3	20.3	21.9	21.1	21.9	20.3	19.3	17.2	16.5
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	142.8	128.8	112.2	89.4
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	253.4	234.1	207.0	179.9
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	362.2	344.0	313.8	277.4
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	433.4	412.1	377.3	342.4
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	501.5	478.6	440.7	395.1
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	599.7	570.7	530.1	481.7
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	688.0	655.8	618.3	568.4
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	746.8	717.8	677.1	636.5



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1764.7	1764.7	1764.7	1764.7
2.5°	1771.2	1773.9	1762.6	1751.3
5°	1770.3	1772.4	1758.3	1744.2
7.5°	1764.5	1766.4	1751.9	1737.5
10°	1756.0	1757.9	1745.5	1733.0
12.5°	1741.6	1743.1	1731.4	1719.6
15°	1717.5	1717.3	1706.5	1695.7
17.5°	1692.5	1689.5	1676.4	1663.3
20°	1674.6	1669.4	1653.6	1637.9
22.5°	1654.7	1647.8	1629.4	1611.0
25°	1620.5	1607.2	1589.0	1570.7
27.5°	1582.7	1559.9	1541.8	1523.7
30°	1553.3	1527.2	1509.8	1492.4
32.5°	1517.5	1489.7	1471.6	1453.6
35°	1458.8	1426.5	1409.1	1391.6
37.5°	1396.1	1359.8	1340.1	1320.4
40°	1354.3	1318.1	1292.4	1266.7
42.5°	1309.6	1280.4	1247.4	1214.4
45°	1230.0	1212.1	1173.2	1134.2
47.5°	1120.8	1125.7	1087.2	1048.8
50°	1037.2	1063.5	1027.0	990.6
52.5°	950.1	989.9	957.4	924.9
55°	823.9	867.4	845.1	822.7
57.5°	696.8	731.1	715.3	699.6
60°	611.3	642.3	629.9	617.5
62.5°	532.7	565.1	554.0	542.9
65°	427.8	461.8	451.0	440.3
67.5°	341.9	373.9	362.1	350.3
70°	291.6	321.5	309.0	296.6
72.5°	249.4	275.4	263.6	251.8
75°	189.7	208.5	199.4	190.3
77.5°	137.3	149.7	143.8	138.0
80°	104.5	113.2	110.7	108.2
82.5°	74.6	79.7	80.5	81.3
85°	37.9	39.6	41.2	42.9
87.5°	17.9	17.7	16.1	14.6
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1428146

CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428146
 CATALOG NUMBER: SQ2W-PP3-K-150U-100D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.54	19.32	19.55	20.34	21.69	14.31	15.09	15.32	16.11	17.46
	3H	19.59	20.29	20.61	21.32	22.69	15.61	16.31	16.63	17.34	18.71
	4H	19.96	20.62	20.99	21.65	23.03	16.16	16.83	17.20	17.86	19.24
	6H	20.15	20.76	21.19	21.79	23.18	16.52	17.13	17.57	18.17	19.56
	8H	20.21	20.79	21.25	21.83	23.22	16.65	17.23	17.70	18.28	19.67
	12H	20.22	20.78	21.28	21.82	23.23	16.68	17.23	17.74	18.28	19.69
4H	2H	18.65	19.31	19.69	20.34	21.72	15.21	15.87	16.25	16.90	18.28
	3H	19.93	20.48	20.98	21.54	22.93	16.62	17.17	17.67	18.23	19.62
	4H	20.44	20.94	21.49	21.99	23.40	17.24	17.74	18.30	18.79	20.21
	6H	20.75	21.18	21.81	22.25	23.66	17.68	18.11	18.75	19.19	20.60
	8H	20.86	21.26	21.92	22.32	23.75	17.85	18.25	18.92	19.32	20.74
	12H	20.90	21.26	21.98	22.34	23.77	17.90	18.26	18.98	19.34	20.77
8H	4H	20.45	20.85	21.52	21.92	23.34	17.54	17.95	18.61	19.01	20.44
	6H	20.86	21.19	21.95	22.30	23.72	18.10	18.43	19.19	19.54	20.96
	8H	21.04	21.33	22.14	22.42	23.87	18.35	18.64	19.44	19.73	21.17
	12H	21.14	21.39	22.23	22.48	23.96	18.45	18.70	19.54	19.79	21.27
12H	4H	20.41	20.77	21.49	21.85	23.28	17.55	17.92	18.64	18.99	20.43
	6H	20.85	21.15	21.95	22.23	23.68	18.17	18.46	19.26	19.55	20.99
	8H	21.05	21.30	22.14	22.39	23.87	18.44	18.70	19.54	19.78	21.26