

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428170

Luminaire Tested: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428170  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE RIPPLE LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4402.7 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428170  
CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428170

CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75				75
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	29546	29546	29546	29546
5°	29508	30053	29508	30053
10°	29819	31043	29819	31043
15°	29810	30214	29810	30214
20°	29328	30771	29328	30771
25°	29245	32036	29245	32036
30°	29214	32344	29214	32344
35°	28936	30113	28936	30113
40°	28270	26500	28270	26500
45°	26749	20956	26749	20956
50°	24319	16259	24319	16259
55°	21371	12656	21371	12656
60°	18493	10420	18493	10420
65°	15965	9123	15965	9123
70°	14355	8101	14355	8101
75°	13150	7448	13150	7448
80°	11446	7280	11446	7280
85°	8299	3464	8299	3464

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 28717 cd/sqm

TEST NUMBER: P1428170

CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.7	4.0
10°-20°	511.6	11.6
20°-30°	790.9	18.0
30°-40°	951.1	21.6
40°-50°	854.1	19.4
50°-60°	572.3	13.0
60°-70°	332.9	7.6
70°-80°	171.0	3.9
80°-90°	42.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1479.2	33.6
0°-40°	2430.3	55.2
0°-60°	3856.6	87.6
0°-90°	4402.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4402.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1830	1830	1830	1830	1830	
5°	1821	1854	1821	1854	1821	174
15°	1783	1808	1783	1808	1783	501
25°	1642	1798	1642	1798	1642	757
35°	1468	1528	1468	1528	1468	915
45°	1172	918	1172	918	1172	896
55°	759	450	759	450	759	682
65°	418	239	418	239	418	423
75°	211	119	211	119	211	224
85°	45	19	45	19	45	57
90°	0	0	0	0	0	



TEST NUMBER: P1428170

CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0
2.5°	1822.6	1832.5	1842.5	1838.0	1828.7	1824.4	1825.1	1826.0	1828.0	1830.0	1828.0
5°	1820.7	1834.8	1848.9	1845.6	1836.5	1832.7	1834.4	1837.7	1846.0	1854.3	1846.0
7.5°	1820.3	1840.4	1860.5	1862.0	1857.3	1857.4	1862.2	1868.6	1879.5	1890.5	1879.5
10°	1818.8	1842.9	1866.9	1870.4	1867.1	1865.9	1866.7	1870.2	1881.8	1893.5	1881.8
12.5°	1809.9	1837.9	1865.9	1863.0	1849.7	1842.5	1841.3	1842.0	1848.3	1854.7	1848.3
15°	1783.4	1816.6	1849.7	1836.2	1807.2	1794.0	1796.4	1799.3	1803.5	1807.6	1803.5
17.5°	1736.8	1771.4	1806.1	1794.0	1766.3	1756.9	1765.9	1774.6	1782.7	1790.9	1782.7
20°	1706.9	1740.9	1774.9	1766.6	1744.2	1738.8	1750.4	1762.7	1776.8	1790.9	1776.8
22.5°	1680.0	1714.0	1748.0	1742.7	1724.3	1723.2	1739.5	1756.5	1775.9	1795.3	1775.9
25°	1641.6	1671.5	1701.3	1701.9	1692.8	1701.9	1729.3	1755.2	1776.8	1798.3	1776.8
27.5°	1601.3	1618.9	1636.5	1648.1	1657.7	1681.0	1718.0	1749.5	1764.6	1779.7	1764.6
30°	1567.0	1578.6	1590.2	1611.8	1636.6	1665.2	1697.6	1723.3	1729.1	1734.9	1729.1
32.5°	1529.7	1536.6	1543.6	1574.0	1612.1	1639.7	1656.8	1667.7	1660.3	1652.8	1660.3
35°	1468.1	1473.9	1479.7	1518.5	1568.2	1586.5	1573.2	1559.3	1543.6	1527.8	1543.6
37.5°	1395.0	1406.9	1418.9	1450.5	1488.6	1488.3	1449.5	1415.9	1397.8	1379.7	1397.8
40°	1341.3	1361.2	1381.1	1402.2	1423.8	1405.5	1347.5	1298.8	1278.1	1257.3	1278.1
42.5°	1275.6	1307.4	1339.3	1344.0	1339.7	1300.6	1226.6	1164.8	1139.4	1114.1	1139.4
45°	1171.5	1214.6	1257.7	1233.1	1185.8	1122.0	1041.6	974.2	946.0	917.8	946.0
47.5°	1048.8	1093.0	1137.3	1090.8	1014.0	939.7	867.9	807.5	781.1	754.8	781.1
50°	968.2	1003.8	1039.5	986.8	904.8	830.1	763.0	705.4	676.3	647.3	676.3
52.5°	886.1	911.8	937.5	885.4	807.3	734.6	667.5	610.5	584.1	557.8	584.1
55°	759.2	772.5	785.8	737.5	668.7	602.3	538.5	486.1	467.8	449.6	467.8
57.5°	642.8	651.3	659.8	614.0	550.1	491.1	436.9	392.9	379.4	366.0	379.4
60°	572.7	578.5	584.3	537.9	474.0	421.0	378.7	344.3	333.5	322.7	333.5
62.5°	508.5	513.0	517.5	472.7	411.5	364.1	330.4	303.2	295.0	286.9	295.0
65°	417.9	422.0	426.2	388.0	335.8	296.8	271.1	250.4	244.6	238.8	244.6
67.5°	345.9	348.0	350.2	318.7	276.1	244.7	224.5	207.9	202.5	197.0	202.5
70°	304.1	304.9	305.7	278.0	240.6	212.9	194.6	179.9	175.8	171.6	175.8
72.5°	266.8	265.6	264.4	239.7	207.0	183.2	168.3	156.4	153.5	150.7	153.5
75°	210.8	208.3	205.8	185.3	158.8	140.5	130.6	122.7	121.0	119.4	121.0
77.5°	157.4	154.8	152.1	135.1	113.2	100.6	97.3	94.8	94.8	94.8	94.8
80°	123.1	119.8	116.5	103.2	86.6	78.3	78.3	78.3	78.3	78.3	78.3
82.5°	91.8	87.1	82.5	74.4	65.1	60.4	60.4	60.3	59.6	58.9	59.6
85°	44.8	40.6	36.5	35.4	35.4	33.0	28.0	23.6	21.1	18.7	21.1
87.5°	11.9	11.9	11.9	9.5	6.1	4.5	4.5	4.5	4.5	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428170

CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0
2.5°	1826.0	1825.1	1824.4	1828.7	1838.0	1842.5	1832.5	1822.6	1832.5	1842.5	1838.0
5°	1837.7	1834.4	1832.7	1836.5	1845.6	1848.9	1834.8	1820.7	1834.8	1848.9	1845.6
7.5°	1868.6	1862.2	1857.4	1857.3	1862.0	1860.5	1840.4	1820.3	1840.4	1860.5	1862.0
10°	1870.2	1866.7	1865.9	1867.1	1870.4	1866.9	1842.9	1818.8	1842.9	1866.9	1870.4
12.5°	1842.0	1841.3	1842.5	1849.7	1863.0	1865.9	1837.9	1809.9	1837.9	1865.9	1863.0
15°	1799.3	1796.4	1794.0	1807.2	1836.2	1849.7	1816.6	1783.4	1816.6	1849.7	1836.2
17.5°	1774.6	1765.9	1756.9	1766.3	1794.0	1806.1	1771.4	1736.8	1771.4	1806.1	1794.0
20°	1762.7	1750.4	1738.8	1744.2	1766.6	1774.9	1740.9	1706.9	1740.9	1774.9	1766.6
22.5°	1756.5	1739.5	1723.2	1724.3	1742.7	1748.0	1714.0	1680.0	1714.0	1748.0	1742.7
25°	1755.2	1729.3	1701.9	1692.8	1701.9	1701.3	1671.5	1641.6	1671.5	1701.3	1701.9
27.5°	1749.5	1718.0	1681.0	1657.7	1648.1	1636.5	1618.9	1601.3	1618.9	1636.5	1648.1
30°	1723.3	1697.6	1665.2	1636.6	1611.8	1590.2	1578.6	1567.0	1578.6	1590.2	1611.8
32.5°	1667.7	1656.8	1639.7	1612.1	1574.0	1543.6	1536.6	1529.7	1536.6	1543.6	1574.0
35°	1559.3	1573.2	1586.5	1568.2	1518.5	1479.7	1473.9	1468.1	1473.9	1479.7	1518.5
37.5°	1415.9	1449.5	1488.3	1488.6	1450.5	1418.9	1406.9	1395.0	1406.9	1418.9	1450.5
40°	1298.8	1347.5	1405.5	1423.8	1402.2	1381.1	1361.2	1341.3	1361.2	1381.1	1402.2
42.5°	1164.8	1226.6	1300.6	1339.7	1344.0	1339.3	1307.4	1275.6	1307.4	1339.3	1344.0
45°	974.2	1041.6	1122.0	1185.8	1233.1	1257.7	1214.6	1171.5	1214.6	1257.7	1233.1
47.5°	807.5	867.9	939.7	1014.0	1090.8	1137.3	1093.0	1048.8	1093.0	1137.3	1090.8
50°	705.4	763.0	830.1	904.8	986.8	1039.5	1003.8	968.2	1003.8	1039.5	986.8
52.5°	610.5	667.5	734.6	807.3	885.4	937.5	911.8	886.1	911.8	937.5	885.4
55°	486.1	538.5	602.3	668.7	737.5	785.8	772.5	759.2	772.5	785.8	737.5
57.5°	392.9	436.9	491.1	550.1	614.0	659.8	651.3	642.8	651.3	659.8	614.0
60°	344.3	378.7	421.0	474.0	537.9	584.3	578.5	572.7	578.5	584.3	537.9
62.5°	303.2	330.4	364.1	411.5	472.7	517.5	513.0	508.5	513.0	517.5	472.7
65°	250.4	271.1	296.8	335.8	388.0	426.2	422.0	417.9	422.0	426.2	388.0
67.5°	207.9	224.5	244.7	276.1	318.7	350.2	348.0	345.9	348.0	350.2	318.7
70°	179.9	194.6	212.9	240.6	278.0	305.7	304.9	304.1	304.9	305.7	278.0
72.5°	156.4	168.3	183.2	207.0	239.7	264.4	265.6	266.8	265.6	264.4	239.7
75°	122.7	130.6	140.5	158.8	185.3	205.8	208.3	210.8	208.3	205.8	185.3
77.5°	94.8	97.3	100.6	113.2	135.1	152.1	154.8	157.4	154.8	152.1	135.1
80°	78.3	78.3	78.3	86.6	103.2	116.5	119.8	123.1	119.8	116.5	103.2
82.5°	60.3	60.4	60.4	65.1	74.4	82.5	87.1	91.8	87.1	82.5	74.4
85°	23.6	28.0	33.0	35.4	35.4	36.5	40.6	44.8	40.6	36.5	35.4
87.5°	4.5	4.5	4.5	6.1	9.5	11.9	11.9	11.9	11.9	11.9	9.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428170

CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0	1830.0
2.5°	1828.7	1824.4	1825.1	1826.0	1828.0	1830.0	1828.0	1826.0	1825.1	1824.4	1828.7
5°	1836.5	1832.7	1834.4	1837.7	1846.0	1854.3	1846.0	1837.7	1834.4	1832.7	1836.5
7.5°	1857.3	1857.4	1862.2	1868.6	1879.5	1890.5	1879.5	1868.6	1862.2	1857.4	1857.3
10°	1867.1	1865.9	1866.7	1870.2	1881.8	1893.5	1881.8	1870.2	1866.7	1865.9	1867.1
12.5°	1849.7	1842.5	1841.3	1842.0	1848.3	1854.7	1848.3	1842.0	1841.3	1842.5	1849.7
15°	1807.2	1794.0	1796.4	1799.3	1803.5	1807.6	1803.5	1799.3	1796.4	1794.0	1807.2
17.5°	1766.3	1756.9	1765.9	1774.6	1782.7	1790.9	1782.7	1774.6	1765.9	1756.9	1766.3
20°	1744.2	1738.8	1750.4	1762.7	1776.8	1790.9	1776.8	1762.7	1750.4	1738.8	1744.2
22.5°	1724.3	1723.2	1739.5	1756.5	1775.9	1795.3	1775.9	1756.5	1739.5	1723.2	1724.3
25°	1692.8	1701.9	1729.3	1755.2	1776.8	1798.3	1776.8	1755.2	1729.3	1701.9	1692.8
27.5°	1657.7	1681.0	1718.0	1749.5	1764.6	1779.7	1764.6	1749.5	1718.0	1681.0	1657.7
30°	1636.6	1665.2	1697.6	1723.3	1729.1	1734.9	1729.1	1723.3	1697.6	1665.2	1636.6
32.5°	1612.1	1639.7	1656.8	1667.7	1660.3	1652.8	1660.3	1667.7	1656.8	1639.7	1612.1
35°	1568.2	1586.5	1573.2	1559.3	1543.6	1527.8	1543.6	1559.3	1573.2	1586.5	1568.2
37.5°	1488.6	1488.3	1449.5	1415.9	1397.8	1379.7	1397.8	1415.9	1449.5	1488.3	1488.6
40°	1423.8	1405.5	1347.5	1298.8	1278.1	1257.3	1278.1	1298.8	1347.5	1405.5	1423.8
42.5°	1339.7	1300.6	1226.6	1164.8	1139.4	1114.1	1139.4	1164.8	1226.6	1300.6	1339.7
45°	1185.8	1122.0	1041.6	974.2	946.0	917.8	946.0	974.2	1041.6	1122.0	1185.8
47.5°	1014.0	939.7	867.9	807.5	781.1	754.8	781.1	807.5	867.9	939.7	1014.0
50°	904.8	830.1	763.0	705.4	676.3	647.3	676.3	705.4	763.0	830.1	904.8
52.5°	807.3	734.6	667.5	610.5	584.1	557.8	584.1	610.5	667.5	734.6	807.3
55°	668.7	602.3	538.5	486.1	467.8	449.6	467.8	486.1	538.5	602.3	668.7
57.5°	550.1	491.1	436.9	392.9	379.4	366.0	379.4	392.9	436.9	491.1	550.1
60°	474.0	421.0	378.7	344.3	333.5	322.7	333.5	344.3	378.7	421.0	474.0
62.5°	411.5	364.1	330.4	303.2	295.0	286.9	295.0	303.2	330.4	364.1	411.5
65°	335.8	296.8	271.1	250.4	244.6	238.8	244.6	250.4	271.1	296.8	335.8
67.5°	276.1	244.7	224.5	207.9	202.5	197.0	202.5	207.9	224.5	244.7	276.1
70°	240.6	212.9	194.6	179.9	175.8	171.6	175.8	179.9	194.6	212.9	240.6
72.5°	207.0	183.2	168.3	156.4	153.5	150.7	153.5	156.4	168.3	183.2	207.0
75°	158.8	140.5	130.6	122.7	121.0	119.4	121.0	122.7	130.6	140.5	158.8
77.5°	113.2	100.6	97.3	94.8	94.8	94.8	94.8	94.8	97.3	100.6	113.2
80°	86.6	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	86.6
82.5°	65.1	60.4	60.4	60.3	59.6	58.9	59.6	60.3	60.4	60.4	65.1
85°	35.4	33.0	28.0	23.6	21.1	18.7	21.1	23.6	28.0	33.0	35.4
87.5°	6.1	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428170

CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1830.0	1830.0	1830.0	1830.0
2.5°	1838.0	1842.5	1832.5	1822.6
5°	1845.6	1848.9	1834.8	1820.7
7.5°	1862.0	1860.5	1840.4	1820.3
10°	1870.4	1866.9	1842.9	1818.8
12.5°	1863.0	1865.9	1837.9	1809.9
15°	1836.2	1849.7	1816.6	1783.4
17.5°	1794.0	1806.1	1771.4	1736.8
20°	1766.6	1774.9	1740.9	1706.9
22.5°	1742.7	1748.0	1714.0	1680.0
25°	1701.9	1701.3	1671.5	1641.6
27.5°	1648.1	1636.5	1618.9	1601.3
30°	1611.8	1590.2	1578.6	1567.0
32.5°	1574.0	1543.6	1536.6	1529.7
35°	1518.5	1479.7	1473.9	1468.1
37.5°	1450.5	1418.9	1406.9	1395.0
40°	1402.2	1381.1	1361.2	1341.3
42.5°	1344.0	1339.3	1307.4	1275.6
45°	1233.1	1257.7	1214.6	1171.5
47.5°	1090.8	1137.3	1093.0	1048.8
50°	986.8	1039.5	1003.8	968.2
52.5°	885.4	937.5	911.8	886.1
55°	737.5	785.8	772.5	759.2
57.5°	614.0	659.8	651.3	642.8
60°	537.9	584.3	578.5	572.7
62.5°	472.7	517.5	513.0	508.5
65°	388.0	426.2	422.0	417.9
67.5°	318.7	350.2	348.0	345.9
70°	278.0	305.7	304.9	304.1
72.5°	239.7	264.4	265.6	266.8
75°	185.3	205.8	208.3	210.8
77.5°	135.1	152.1	154.8	157.4
80°	103.2	116.5	119.8	123.1
82.5°	74.4	82.5	87.1	91.8
85°	35.4	36.5	40.6	44.8
87.5°	9.5	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428170  
 CATALOG NUMBER: SQ2W-PR1-0U-100D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.36	23.86	22.73	24.17	24.49	18.73	20.23	19.10	20.54	20.86
	3H	23.62	24.95	23.99	25.28	25.64	19.94	21.28	20.32	21.61	21.97
	4H	24.13	25.38	24.53	25.73	26.11	20.43	21.68	20.83	22.03	22.41
	6H	24.46	25.61	24.87	25.98	26.37	20.80	21.96	21.22	22.33	22.72
	8H	24.58	25.68	25.00	26.07	26.47	20.96	22.06	21.39	22.45	22.85
	12H	24.64	25.69	25.07	26.07	26.50	21.01	22.06	21.44	22.44	22.87
4H	2H	22.54	23.79	22.94	24.14	24.52	19.52	20.77	19.92	21.12	21.50
	3H	24.06	25.09	24.47	25.49	25.89	20.93	21.96	21.34	22.36	22.77
	4H	24.71	25.64	25.14	26.05	26.49	21.50	22.43	21.93	22.84	23.28
	6H	25.17	25.98	25.63	26.42	26.88	21.96	22.77	22.42	23.21	23.67
	8H	25.34	26.09	25.81	26.54	27.01	22.16	22.91	22.62	23.35	23.82
	12H	25.43	26.11	25.92	26.59	27.06	22.23	22.90	22.71	23.38	23.85
8H	4H	24.78	25.53	25.24	25.97	26.44	21.87	22.62	22.33	23.07	23.53
	6H	25.33	25.95	25.83	26.44	26.92	22.43	23.05	22.93	23.54	24.02
	8H	25.56	26.12	26.08	26.63	27.12	22.69	23.25	23.20	23.76	24.25
	12H	25.71	26.20	26.22	26.70	27.26	22.81	23.30	23.32	23.80	24.36
12H	4H	24.76	25.43	25.25	25.91	26.39	21.91	22.59	22.40	23.07	23.54
	6H	25.32	25.88	25.83	26.39	26.88	22.50	23.06	23.01	23.57	24.06
	8H	25.59	26.09	26.11	26.58	27.15	22.81	23.31	23.32	23.80	24.37