

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435728

Luminaire Tested: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2024
Report Number: P1435728
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4243.1 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	66	89	79	72	66	76	70	65	73	68	64	71	66	62	60
4	83	72	63	57	81	70	62	56	68	61	55	66	60	55	63	58	54	52
5	77	64	55	49	75	63	55	49	61	54	48	59	53	47	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	53	47	42	52	46	41	39
7	66	53	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27586	27586	27586	27586
5°	27262	28549	27262	22753
10°	27143	28879	27143	20628
15°	26677	29113	26677	22803
20°	25943	28901	25943	23781
25°	24657	28667	24657	24068
30°	22717	28026	22717	24322
35°	20100	27411	20100	23887
40°	17308	26660	17308	24147
45°	17086	25706	17086	24194
50°	16302	24452	16302	24287
55°	16217	22556	16217	24048
60°	14541	20101	14541	23950
65°	12397	17711	12397	23277
70°	10003	15007	10003	21569
75°	8677	12395	8677	19831
80°	7392	9233	7392	16011
85°	4909	4909	4909	9818

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 26512 cd/sqm



TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	3.6
10°-20°	429.6	10.1
20°-30°	652.3	15.4
30°-40°	765.9	18.1
40°-50°	777.2	18.3
50°-60°	680.8	16.0
60°-70°	482.9	11.4
70°-80°	248.6	5.9
80°-90°	52.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1235.6	29.1
0°-40°	2001.5	47.2
0°-60°	3459.5	81.5
0°-90°	4243.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4243.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1709	1709	1709	1709	1709	
5°	1682	1762	1682	1404	1682	160
15°	1596	1742	1596	1364	1596	448
25°	1384	1609	1384	1351	1384	632
35°	1020	1391	1020	1212	1020	635
45°	748	1126	748	1060	748	572
55°	576	801	576	854	576	498
65°	324	464	324	609	324	324
75°	139	199	139	318	139	150
85°	26	26	26	53	26	34
90°	0	0	0	0	0	



TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6
2.5°	1698.0	1709.7	1721.5	1724.5	1724.5	1724.5	1724.5	1724.5	1724.5	1724.5	1724.5
5°	1682.1	1702.7	1723.3	1732.8	1738.7	1743.1	1746.1	1749.8	1755.7	1761.5	1755.7
7.5°	1666.2	1693.8	1721.5	1735.1	1743.9	1750.9	1756.2	1761.0	1763.9	1766.8	1763.9
10°	1655.6	1688.0	1720.3	1735.1	1743.9	1749.8	1752.7	1755.7	1758.6	1761.5	1758.6
12.5°	1639.7	1674.4	1709.2	1726.2	1737.4	1744.5	1747.4	1750.4	1753.3	1756.2	1753.3
15°	1596.0	1643.1	1690.2	1708.6	1717.4	1724.8	1730.6	1735.8	1738.7	1741.7	1738.7
17.5°	1541.7	1598.8	1655.9	1679.0	1690.8	1699.3	1704.6	1709.2	1711.5	1713.9	1711.5
20°	1509.9	1571.7	1633.5	1657.8	1669.6	1676.9	1679.9	1682.1	1682.1	1682.1	1682.1
22.5°	1467.5	1536.4	1605.3	1631.3	1643.1	1649.3	1649.8	1650.9	1653.2	1655.6	1653.2
25°	1384.1	1463.5	1543.0	1576.1	1593.8	1601.1	1598.2	1597.5	1603.3	1609.2	1603.3
27.5°	1282.1	1382.2	1482.2	1516.1	1527.8	1535.2	1538.1	1540.4	1540.4	1540.4	1540.4
30°	1218.5	1330.4	1442.2	1479.0	1490.8	1498.1	1501.1	1503.3	1503.3	1503.3	1503.3
32.5°	1139.0	1272.1	1405.1	1445.4	1454.9	1459.9	1460.4	1460.9	1460.9	1460.9	1460.9
35°	1019.8	1181.7	1343.6	1388.5	1394.4	1397.3	1397.3	1396.6	1393.6	1390.7	1393.6
37.5°	900.6	1084.3	1268.0	1320.5	1329.3	1331.7	1327.6	1323.7	1320.8	1317.8	1320.8
40°	821.2	1021.3	1221.5	1278.1	1286.9	1286.9	1278.1	1270.8	1267.8	1264.9	1267.8
42.5°	778.8	976.6	1174.4	1230.4	1239.3	1238.1	1226.9	1217.8	1214.8	1211.9	1214.8
45°	748.3	924.9	1101.5	1152.3	1161.1	1159.6	1147.9	1137.6	1131.7	1125.8	1131.7
47.5°	702.0	857.4	1012.8	1062.7	1077.4	1075.9	1058.2	1043.5	1037.6	1031.8	1037.6
50°	649.0	802.0	955.1	1004.4	1019.1	1017.6	1000.0	985.3	979.4	973.5	979.4
52.5°	611.9	755.5	899.2	944.3	956.7	952.9	932.9	916.4	910.5	904.6	910.5
55°	576.1	696.8	817.5	854.3	863.1	857.2	836.6	819.0	810.1	801.3	810.1
57.5°	492.7	607.5	722.3	758.0	767.5	760.4	736.8	716.7	706.7	696.7	706.7
60°	450.3	553.3	656.3	690.9	702.7	696.8	673.3	651.9	637.2	622.5	637.2
62.5°	402.6	493.9	585.1	620.3	636.8	633.2	609.7	588.4	573.6	558.9	573.6
65°	324.5	404.0	483.4	518.7	539.4	537.9	514.3	493.0	478.3	463.6	478.3
67.5°	254.3	322.6	390.9	425.6	449.1	448.0	422.1	399.7	387.9	376.1	387.9
70°	211.9	270.8	329.6	362.0	385.6	385.6	362.0	341.4	329.6	317.9	329.6
72.5°	185.4	230.2	274.9	305.5	331.4	331.4	305.5	283.7	274.3	264.9	274.3
75°	139.1	165.6	192.0	220.7	250.2	253.1	229.6	210.4	204.6	198.7	204.6
77.5°	100.7	113.0	125.4	147.9	173.8	176.7	156.7	141.1	138.8	136.4	138.8
80°	79.5	82.4	85.4	103.7	127.3	130.2	112.6	99.3	99.3	99.3	99.3
82.5°	53.0	55.9	58.9	72.0	88.4	90.2	77.3	67.0	64.6	62.2	64.6
85°	26.5	26.5	26.5	30.9	36.8	36.8	30.9	26.5	26.5	26.5	26.5
87.5°	5.3	5.3	5.3	7.1	9.4	9.4	7.1	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6
2.5°	1724.5	1724.5	1724.5	1724.5	1724.5	1721.5	1709.7	1698.0	1698.0	1698.0	1689.1
5°	1749.8	1746.1	1743.1	1738.7	1732.8	1723.3	1702.7	1682.1	1673.2	1664.4	1626.9
7.5°	1761.0	1756.2	1750.9	1743.9	1735.1	1721.5	1693.8	1666.2	1626.7	1587.3	1503.7
10°	1755.7	1752.7	1749.8	1743.9	1735.1	1720.3	1688.0	1655.6	1576.1	1496.6	1417.2
12.5°	1750.4	1747.4	1744.5	1737.4	1726.2	1709.2	1674.4	1639.7	1527.3	1414.8	1343.0
15°	1735.8	1730.6	1724.8	1717.4	1708.6	1690.2	1643.1	1596.0	1469.4	1342.9	1282.5
17.5°	1709.2	1704.6	1699.3	1690.8	1679.0	1655.9	1598.8	1541.7	1409.2	1276.8	1237.9
20°	1682.1	1679.9	1676.9	1669.6	1657.8	1633.5	1571.7	1509.9	1377.4	1245.0	1227.3
22.5°	1650.9	1649.8	1649.3	1643.1	1631.3	1605.3	1536.4	1467.5	1337.4	1207.3	1207.9
25°	1597.5	1598.2	1601.1	1593.8	1576.1	1543.0	1463.5	1384.1	1269.3	1154.5	1174.4
27.5°	1540.4	1538.1	1535.2	1527.8	1516.1	1482.2	1382.2	1282.1	1191.4	1100.8	1133.7
30°	1503.3	1501.1	1498.1	1490.8	1479.0	1442.2	1330.4	1218.5	1142.0	1065.5	1103.7
32.5°	1460.9	1460.4	1459.9	1454.9	1445.4	1405.1	1272.1	1139.0	1083.7	1028.4	1068.4
35°	1396.6	1397.3	1397.3	1394.4	1388.5	1343.6	1181.7	1019.8	996.3	972.7	1019.8
37.5°	1323.7	1327.6	1331.7	1329.3	1320.5	1268.0	1084.3	900.6	908.3	915.9	973.0
40°	1270.8	1278.1	1286.9	1286.9	1278.1	1221.5	1021.3	821.2	847.7	874.1	936.0
42.5°	1217.8	1226.9	1238.1	1239.3	1230.4	1174.4	976.6	778.8	807.6	836.5	900.6
45°	1137.6	1147.9	1159.6	1161.1	1152.3	1101.5	924.9	748.3	766.0	783.6	845.5
47.5°	1043.5	1058.2	1075.9	1077.4	1062.7	1012.8	857.4	702.0	714.9	727.9	791.1
50°	985.3	1000.0	1017.6	1019.1	1004.4	955.1	802.0	649.0	666.6	684.3	750.5
52.5°	916.4	932.9	952.9	956.7	944.3	899.2	755.5	611.9	622.5	633.1	704.6
55°	819.0	836.6	857.2	863.1	854.3	817.5	696.8	576.1	567.3	558.5	631.3
57.5°	716.7	736.8	760.4	767.5	758.0	722.3	607.5	492.7	485.0	477.4	556.3
60°	651.9	673.3	696.8	702.7	690.9	656.3	553.3	450.3	435.6	420.9	503.3
62.5°	588.4	609.7	633.2	636.8	620.3	585.1	493.9	402.6	392.6	382.6	462.7
65°	493.0	514.3	537.9	539.4	518.7	483.4	404.0	324.5	330.4	336.3	408.4
67.5°	399.7	422.1	448.0	449.1	425.6	390.9	322.6	254.3	273.7	293.1	358.0
70°	341.4	362.0	385.6	385.6	362.0	329.6	270.8	211.9	238.4	264.9	324.5
72.5°	283.7	305.5	331.4	331.4	305.5	274.9	230.2	185.4	211.9	238.4	287.4
75°	210.4	229.6	253.1	250.2	220.7	192.0	165.6	139.1	165.6	192.0	229.6
77.5°	141.1	156.7	176.7	173.8	147.9	125.4	113.0	100.7	122.4	144.2	170.4
80°	99.3	112.6	130.2	127.3	103.7	85.4	82.4	79.5	94.2	108.9	128.0
82.5°	67.0	77.3	90.2	88.4	72.0	58.9	55.9	53.0	65.3	77.7	90.9
85°	26.5	30.9	36.8	36.8	30.9	26.5	26.5	26.5	32.4	38.3	44.1
87.5°	5.3	7.1	9.4	9.4	7.1	5.3	5.3	5.3	7.7	10.0	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6	1708.6
2.5°	1677.4	1667.9	1660.9	1655.0	1652.6	1650.3	1652.6	1655.0	1660.9	1667.9	1677.4
5°	1579.8	1529.8	1476.8	1433.4	1418.7	1403.9	1418.7	1433.4	1476.8	1529.8	1579.8
7.5°	1405.4	1345.1	1322.7	1304.7	1300.0	1295.3	1300.0	1304.7	1322.7	1345.1	1405.4
10°	1337.7	1289.1	1271.5	1258.2	1258.2	1258.2	1258.2	1258.2	1271.5	1289.1	1337.7
12.5°	1284.7	1255.0	1253.8	1255.9	1267.7	1279.4	1267.7	1255.9	1253.8	1255.0	1284.7
15°	1244.3	1248.7	1295.8	1334.8	1349.5	1364.2	1349.5	1334.8	1295.8	1248.7	1244.3
17.5°	1230.3	1255.6	1313.9	1360.5	1372.3	1384.1	1372.3	1360.5	1313.9	1255.6	1230.3
20°	1247.9	1280.3	1324.5	1360.5	1372.3	1384.1	1372.3	1360.5	1324.5	1280.3	1247.9
22.5°	1252.1	1291.5	1326.2	1355.2	1367.0	1378.8	1367.0	1355.2	1326.2	1291.5	1252.1
25°	1239.1	1286.2	1315.6	1339.2	1345.1	1351.0	1345.1	1339.2	1315.6	1286.2	1239.1
27.5°	1207.9	1259.7	1289.1	1312.3	1316.4	1320.5	1316.4	1312.3	1289.1	1259.7	1207.9
30°	1180.2	1233.2	1262.7	1286.9	1295.8	1304.6	1295.8	1286.9	1262.7	1233.2	1180.2
32.5°	1140.2	1194.4	1230.9	1258.7	1260.5	1262.2	1260.5	1258.7	1230.9	1194.4	1140.2
35°	1090.5	1146.4	1187.6	1217.8	1214.8	1211.9	1214.8	1217.8	1187.6	1146.4	1090.5
37.5°	1046.6	1101.4	1137.3	1165.1	1168.6	1172.2	1168.6	1165.1	1137.3	1101.4	1046.6
40°	1009.5	1065.5	1103.7	1133.9	1139.8	1145.7	1139.8	1133.9	1103.7	1065.5	1009.5
42.5°	976.6	1033.7	1071.9	1102.1	1108.0	1113.9	1108.0	1102.1	1071.9	1033.7	976.6
45°	922.0	980.8	1022.0	1053.7	1056.6	1059.6	1056.6	1053.7	1022.0	980.8	922.0
47.5°	871.2	930.4	968.6	998.1	1001.0	1003.9	1001.0	998.1	968.6	930.4	871.2
50°	832.9	893.3	931.5	961.0	963.9	966.9	963.9	961.0	931.5	893.3	832.9
52.5°	796.4	859.1	892.7	918.6	921.5	924.5	921.5	918.6	892.7	859.1	796.4
55°	731.4	797.6	830.0	854.3	854.3	854.3	854.3	854.3	830.0	797.6	731.4
57.5°	664.0	732.0	760.2	782.3	785.9	789.4	785.9	782.3	760.2	732.0	664.0
60°	618.1	687.3	710.8	729.9	735.8	741.7	735.8	729.9	710.8	687.3	618.1
62.5°	572.8	639.6	663.1	681.7	685.2	688.7	685.2	681.7	663.1	639.6	572.8
65°	502.6	561.4	585.0	603.4	606.3	609.3	606.3	603.4	585.0	561.4	502.6
67.5°	438.1	486.4	502.9	515.8	518.2	520.5	518.2	515.8	502.9	486.4	438.1
70°	395.1	436.3	448.1	456.9	456.9	456.9	456.9	456.9	448.1	436.3	395.1
72.5°	343.9	378.1	389.8	399.3	401.6	404.0	401.6	399.3	389.8	378.1	343.9
75°	270.8	295.8	304.6	312.0	314.9	317.9	314.9	312.0	304.6	295.8	270.8
77.5°	198.1	214.6	219.9	224.6	227.5	230.5	227.5	224.6	219.9	214.6	198.1
80°	148.6	160.4	163.4	166.3	169.2	172.2	169.2	166.3	163.4	160.4	148.6
82.5°	104.5	112.7	115.7	118.0	118.6	119.2	118.6	118.0	115.7	112.7	104.5
85°	50.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	50.0
87.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1708.6	1708.6	1708.6	1708.6
2.5°	1689.1	1698.0	1698.0	1698.0
5°	1626.9	1664.4	1673.2	1682.1
7.5°	1503.7	1587.3	1626.7	1666.2
10°	1417.2	1496.6	1576.1	1655.6
12.5°	1343.0	1414.8	1527.3	1639.7
15°	1282.5	1342.9	1469.4	1596.0
17.5°	1237.9	1276.8	1409.2	1541.7
20°	1227.3	1245.0	1377.4	1509.9
22.5°	1207.9	1207.3	1337.4	1467.5
25°	1174.4	1154.5	1269.3	1384.1
27.5°	1133.7	1100.8	1191.4	1282.1
30°	1103.7	1065.5	1142.0	1218.5
32.5°	1068.4	1028.4	1083.7	1139.0
35°	1019.8	972.7	996.3	1019.8
37.5°	973.0	915.9	908.3	900.6
40°	936.0	874.1	847.7	821.2
42.5°	900.6	836.5	807.6	778.8
45°	845.5	783.6	766.0	748.3
47.5°	791.1	727.9	714.9	702.0
50°	750.5	684.3	666.6	649.0
52.5°	704.6	633.1	622.5	611.9
55°	631.3	558.5	567.3	576.1
57.5°	556.3	477.4	485.0	492.7
60°	503.3	420.9	435.6	450.3
62.5°	462.7	382.6	392.6	402.6
65°	408.4	336.3	330.4	324.5
67.5°	358.0	293.1	273.7	254.3
70°	324.5	264.9	238.4	211.9
72.5°	287.4	238.4	211.9	185.4
75°	229.6	192.0	165.6	139.1
77.5°	170.4	144.2	122.4	100.7
80°	128.0	108.9	94.2	79.5
82.5°	90.9	77.7	65.3	53.0
85°	44.1	38.3	32.4	26.5
87.5°	10.6	10.0	7.7	5.3
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1435728

CATALOG NUMBER: SQ2W-FA-0U-100D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.73	23.34	22.10	23.65	23.97	22.93	24.54	23.30	24.85	25.17
	3H	22.88	24.32	23.25	24.65	25.01	24.23	25.68	24.61	26.00	26.36
	4H	23.26	24.62	23.66	24.97	25.35	24.65	26.01	25.05	26.36	26.74
	6H	23.46	24.72	23.87	25.08	25.47	24.85	26.11	25.26	26.47	26.86
	8H	23.51	24.72	23.94	25.10	25.50	24.89	26.10	25.32	26.49	26.88
	12H	23.53	24.68	23.96	25.07	25.50	24.90	26.05	25.33	26.44	26.86
4H	2H	22.69	24.05	23.09	24.40	24.77	23.60	24.96	24.00	25.31	25.69
	3H	24.14	25.28	24.55	25.68	26.08	25.13	26.27	25.54	26.66	27.07
	4H	24.63	25.65	25.06	26.06	26.50	25.64	26.66	26.07	27.08	27.51
	6H	24.90	25.79	25.35	26.23	26.69	25.90	26.79	26.36	27.23	27.69
	8H	24.97	25.81	25.43	26.25	26.71	25.97	26.80	26.43	27.24	27.71
	12H	25.01	25.76	25.49	26.23	26.70	25.99	26.74	26.47	27.21	27.68
8H	4H	25.07	25.90	25.53	26.35	26.81	25.89	26.72	26.35	27.17	27.63
	6H	25.45	26.14	25.94	26.63	27.11	26.24	26.93	26.73	27.42	27.89
	8H	25.57	26.19	26.08	26.70	27.19	26.34	26.96	26.85	27.46	27.95
	12H	25.64	26.19	26.15	26.68	27.24	26.39	26.93	26.89	27.42	27.99
12H	4H	25.11	25.85	25.59	26.33	26.80	25.89	26.64	26.37	27.12	27.59
	6H	25.52	26.15	26.04	26.65	27.14	26.26	26.88	26.77	27.39	27.87
	8H	25.71	26.25	26.21	26.74	27.31	26.41	26.95	26.92	27.45	28.01