

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428188

Luminaire Tested: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428188
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4206.9 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78				78
1	105	101	97	94	100	97	93	90	88	86	83	81	79	77	74	72	71	68				68
2	96	89	83	78	92	86	80	76	79	74	71	72	69	66	66	64	61	58				58
3	89	79	72	66	84	76	70	64	70	65	61	65	60	57	59	56	53	50				50
4	82	71	63	57	78	68	61	56	63	57	52	58	53	49	54	50	47	44				44
5	75	64	56	50	72	61	54	48	57	51	46	53	47	43	49	44	41	39				39
6	70	58	49	44	66	56	48	43	52	45	41	48	43	39	44	40	37	34				34
7	65	52	44	39	62	51	43	38	47	41	36	44	38	34	41	36	33	31				31
8	60	48	40	35	58	46	39	34	43	37	32	40	35	31	38	33	29	27				27
9	56	44	36	31	54	42	35	31	40	34	29	37	32	28	35	30	27	25				25
10	53	40	33	28	50	39	32	28	37	31	27	34	29	25	32	28	24	23				23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21976	21976	21976	21976
5°	21948	22351	21948	22351
10°	22179	23089	22179	23089
15°	22171	22473	22171	22473
20°	21812	22886	21812	22886
25°	21752	23827	21752	23827
30°	21729	24055	21729	24055
35°	21521	22397	21521	22397
40°	21026	19711	21026	19711
45°	19895	15586	19895	15586
50°	18087	12094	18087	12094
55°	15896	9413	15896	9413
60°	13756	7750	13756	7750
65°	11874	6785	11874	6785
70°	10678	6024	10678	6024
75°	9781	5539	9781	5539
80°	8517	5421	8517	5421
85°	6169	2575	6169	2575

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 21361 cd/sqm



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.4	3.1
10°-20°	380.5	9.0
20°-30°	588.2	14.0
30°-40°	707.4	16.8
40°-50°	635.2	15.1
50°-60°	425.6	10.1
60°-70°	247.6	5.9
70°-80°	127.2	3.0
80°-90°	32.7	0.8
90°-100°	25.4	0.6
100°-110°	74.0	1.8
110°-120°	120.8	2.9
120°-130°	153.3	3.6
130°-140°	164.0	3.9
140°-150°	153.1	3.6
150°-160°	126.0	3.0
160°-170°	84.5	2.0
170°-180°	30.0	0.7
0°-30°	1100.2	26.2
0°-40°	1807.6	43.0
0°-60°	2868.4	68.2
0°-90°	3275.9	77.9
90°-120°	220.2	5.2
90°-150°	690.5	16.4
90°-180°	931.0	22.1
0°-180°	4206.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1361	1361	1361	1361	1361	
5°	1354	1379	1354	1379	1354	129
15°	1326	1344	1326	1344	1326	372
25°	1221	1338	1221	1338	1221	563
35°	1092	1136	1092	1136	1092	681
45°	871	683	871	683	871	667
55°	565	334	565	334	565	507
65°	311	178	311	178	311	314
75°	157	89	157	89	157	166
85°	33	14	33	14	33	41
90°	1	7	1	14	1	2
95°	10	7	10	44	10	12
105°	47	75	47	104	47	50
115°	90	125	90	154	90	89
125°	133	198	133	189	133	119
135°	181	259	181	209	181	140
145°	232	299	232	214	232	145
155°	275	325	275	222	275	126
165°	304	338	304	255	304	86
175°	318	331	318	299	318	30
180°	319	319	319	319	319	



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1
2.5°	1355.6	1363.0	1370.4	1367.0	1360.1	1356.9	1357.4	1358.1	1359.6	1361.1	1359.6
5°	1354.2	1364.7	1375.1	1372.7	1365.9	1363.1	1364.3	1366.8	1373.0	1379.1	1373.0
7.5°	1353.9	1368.8	1383.7	1384.9	1381.4	1381.5	1385.1	1389.8	1397.9	1406.1	1397.9
10°	1352.8	1370.7	1388.5	1391.2	1388.7	1387.8	1388.4	1391.0	1399.6	1408.3	1399.6
12.5°	1346.1	1367.0	1387.8	1385.6	1375.8	1370.4	1369.5	1370.0	1374.7	1379.4	1374.7
15°	1326.4	1351.1	1375.8	1365.7	1344.2	1334.3	1336.1	1338.3	1341.4	1344.5	1341.4
17.5°	1291.7	1317.5	1343.3	1334.3	1313.7	1306.7	1313.4	1319.9	1325.9	1332.0	1325.9
20°	1269.5	1294.8	1320.1	1313.9	1297.3	1293.3	1301.9	1311.0	1321.5	1332.0	1321.5
22.5°	1249.6	1274.8	1300.1	1296.2	1282.5	1281.7	1293.8	1306.4	1320.9	1335.3	1320.9
25°	1221.0	1243.2	1265.4	1265.8	1259.1	1265.8	1286.2	1305.5	1321.5	1337.5	1321.5
27.5°	1191.0	1204.1	1217.2	1225.8	1232.9	1250.3	1277.8	1301.2	1312.4	1323.6	1312.4
30°	1165.5	1174.1	1182.7	1198.8	1217.3	1238.5	1262.6	1281.7	1286.0	1290.3	1286.0
32.5°	1137.7	1142.9	1148.1	1170.7	1199.0	1219.6	1232.3	1240.4	1234.8	1229.3	1234.8
35°	1091.9	1096.3	1100.6	1129.4	1166.4	1180.0	1170.1	1159.8	1148.1	1136.3	1148.1
37.5°	1037.6	1046.4	1055.3	1078.8	1107.2	1106.9	1078.1	1053.1	1039.6	1026.2	1039.6
40°	997.6	1012.4	1027.2	1042.9	1058.9	1045.4	1002.2	966.0	950.6	935.2	950.6
42.5°	948.8	972.4	996.1	999.6	996.4	967.3	912.3	866.3	847.5	828.6	847.5
45°	871.3	903.4	935.5	917.1	882.0	834.5	774.7	724.6	703.6	682.6	703.6
47.5°	780.0	813.0	845.9	811.3	754.2	698.9	645.5	600.6	581.0	561.4	581.0
50°	720.1	746.6	773.1	734.0	672.9	617.4	567.5	524.6	503.0	481.5	503.0
52.5°	659.0	678.2	697.3	658.5	600.4	546.4	496.4	454.1	434.5	414.9	434.5
55°	564.7	574.6	584.4	548.5	497.3	448.0	400.5	361.5	347.9	334.4	347.9
57.5°	478.1	484.4	490.7	456.7	409.2	365.3	324.9	292.2	282.2	272.2	282.2
60°	426.0	430.3	434.6	400.1	352.6	313.1	281.7	256.1	248.0	240.0	248.0
62.5°	378.2	381.6	384.9	351.6	306.1	270.8	245.8	225.5	219.4	213.4	219.4
65°	310.8	313.9	317.0	288.6	249.7	220.8	201.6	186.2	181.9	177.6	181.9
67.5°	257.2	258.8	260.4	237.1	205.4	182.0	167.0	154.7	150.6	146.5	150.6
70°	226.2	226.8	227.4	206.7	179.0	158.3	144.8	133.8	130.7	127.6	130.7
72.5°	198.4	197.5	196.7	178.2	153.9	136.2	125.1	116.3	114.2	112.1	114.2
75°	156.8	154.9	153.1	137.8	118.1	104.5	97.1	91.3	90.0	88.8	90.0
77.5°	117.1	115.1	113.2	100.5	84.2	74.8	72.3	70.5	70.5	70.5	70.5
80°	91.6	89.1	86.6	76.8	64.4	58.3	58.3	58.3	58.3	58.3	58.3
82.5°	68.3	64.8	61.4	55.3	48.4	45.0	45.0	44.8	44.3	43.8	44.3
85°	33.3	30.2	27.1	26.4	26.4	24.5	20.8	17.6	15.7	13.9	15.7
87.5°	9.1	9.3	9.7	8.1	5.8	4.6	4.6	4.7	4.7	4.7	4.7
90°	1.0	2.3	3.9	5.2	6.1	6.4	6.4	6.8	7.1	7.1	7.1
92.5°	3.5	5.6	5.7	5.7	6.9	7.5	8.0	8.1	8.4	8.4	8.4
95°	10.0	11.0	16.4	16.1	11.0	8.7	7.4	7.4	7.4	7.4	7.4
97.5°	19.1	20.5	21.4	28.7	30.3	29.2	23.8	20.0	17.9	16.9	17.9
100°	27.1	27.7	29.6	30.0	38.0	45.7	41.9	37.0	35.4	34.5	35.4
102.5°	35.0	35.4	38.4	39.7	41.6	46.0	59.4	57.9	56.8	56.6	56.8
105°	47.0	47.3	52.8	55.4	56.7	56.7	56.4	62.8	73.1	75.4	73.1
107.5°	59.8	61.3	67.8	74.7	76.1	76.5	74.9	73.9	73.5	73.8	73.5
110°	68.6	70.9	78.6	87.3	89.5	90.2	89.5	88.6	87.9	87.9	87.9



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	77.1	80.4	89.2	99.1	102.9	104.9	103.5	102.7	102.1	102.6	102.1
115°	90.2	95.0	106.6	116.9	124.6	125.6	125.3	125.3	125.0	125.0	125.0
117.5°	102.3	110.0	123.0	135.0	144.0	146.5	147.8	147.5	147.1	147.7	147.1
120°	110.8	119.8	134.6	148.2	156.9	160.7	162.0	161.4	162.0	161.4	162.0
122.5°	119.8	130.9	145.5	159.5	169.7	174.1	175.7	175.8	175.9	175.5	175.9
125°	133.3	146.9	163.9	178.4	189.1	194.2	195.5	195.8	196.5	198.1	196.5
127.5°	147.0	162.3	181.1	195.1	205.9	212.2	214.2	214.9	216.2	217.0	216.2
130°	156.5	173.9	192.9	206.1	216.8	223.5	227.1	228.0	229.6	229.3	229.6
132.5°	166.6	184.7	204.0	217.7	227.6	234.9	237.9	240.7	241.2	241.7	241.2
135°	181.3	201.0	220.3	233.8	243.2	250.3	254.1	256.7	258.3	259.3	258.3
137.5°	196.9	217.6	236.2	248.2	257.6	263.7	268.1	270.8	272.5	273.3	272.5
140°	207.4	227.4	245.4	258.0	266.4	272.5	276.3	279.6	281.5	281.5	281.5
142.5°	217.5	237.2	254.7	267.3	274.6	280.2	284.3	286.8	289.0	289.0	289.0
145°	231.6	251.2	267.3	279.9	286.0	291.2	295.7	297.6	298.9	298.9	298.9
147.5°	246.3	263.7	278.4	290.5	295.6	301.7	305.2	306.8	308.4	307.7	308.4
150°	255.1	271.2	285.4	296.6	301.8	307.6	311.1	312.4	314.0	313.1	314.0
152.5°	263.6	278.9	291.8	302.3	306.7	312.5	316.5	317.8	318.9	318.2	318.9
155°	275.1	288.6	300.5	310.2	314.0	319.5	323.4	325.0	326.3	324.7	326.3
157.5°	285.3	297.0	307.3	316.2	320.3	325.0	328.7	330.7	331.9	331.2	331.9
160°	291.5	302.1	311.5	319.8	323.7	327.9	331.7	334.0	335.3	334.3	335.3
162.5°	296.6	306.2	315.1	322.7	326.0	329.7	334.3	336.3	337.6	336.4	337.6
165°	304.0	311.8	319.5	326.0	328.8	331.7	336.6	338.8	339.8	338.5	339.8
167.5°	309.7	315.6	321.8	327.4	329.5	332.3	337.2	339.0	340.3	338.6	340.3
170°	312.7	317.9	323.4	327.9	329.5	332.1	336.9	338.5	339.5	337.9	339.5
172.5°	315.3	319.2	323.6	327.6	328.5	330.5	335.1	336.7	337.4	336.1	337.4
175°	317.9	320.2	323.4	326.0	325.6	326.9	330.8	332.1	333.4	331.4	333.4
177.5°	319.1	320.2	321.2	322.7	321.7	321.7	324.5	325.3	325.6	324.5	325.6
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1
2.5°	1358.1	1357.4	1356.9	1360.1	1367.0	1370.4	1363.0	1355.6	1363.0	1370.4	1367.0
5°	1366.8	1364.3	1363.1	1365.9	1372.7	1375.1	1364.7	1354.2	1364.7	1375.1	1372.7
7.5°	1389.8	1385.1	1381.5	1381.4	1384.9	1383.7	1368.8	1353.9	1368.8	1383.7	1384.9
10°	1391.0	1388.4	1387.8	1388.7	1391.2	1388.5	1370.7	1352.8	1370.7	1388.5	1391.2
12.5°	1370.0	1369.5	1370.4	1375.8	1385.6	1387.8	1367.0	1346.1	1367.0	1387.8	1385.6
15°	1338.3	1336.1	1334.3	1344.2	1365.7	1375.8	1351.1	1326.4	1351.1	1375.8	1365.7
17.5°	1319.9	1313.4	1306.7	1313.7	1334.3	1343.3	1317.5	1291.7	1317.5	1343.3	1334.3
20°	1311.0	1301.9	1293.3	1297.3	1313.9	1320.1	1294.8	1269.5	1294.8	1320.1	1313.9
22.5°	1306.4	1293.8	1281.7	1282.5	1296.2	1300.1	1274.8	1249.6	1274.8	1300.1	1296.2
25°	1305.5	1286.2	1265.8	1259.1	1265.8	1265.4	1243.2	1221.0	1243.2	1265.4	1265.8
27.5°	1301.2	1277.8	1250.3	1232.9	1225.8	1217.2	1204.1	1191.0	1204.1	1217.2	1225.8
30°	1281.7	1262.6	1238.5	1217.3	1198.8	1182.7	1174.1	1165.5	1174.1	1182.7	1198.8
32.5°	1240.4	1232.3	1219.6	1199.0	1170.7	1148.1	1142.9	1137.7	1142.9	1148.1	1170.7
35°	1159.8	1170.1	1180.0	1166.4	1129.4	1100.6	1096.3	1091.9	1096.3	1100.6	1129.4
37.5°	1053.1	1078.1	1106.9	1107.2	1078.8	1055.3	1046.4	1037.6	1046.4	1055.3	1078.8
40°	966.0	1002.2	1045.4	1058.9	1042.9	1027.2	1012.4	997.6	1012.4	1027.2	1042.9
42.5°	866.3	912.3	967.3	996.4	999.6	996.1	972.4	948.8	972.4	996.1	999.6
45°	724.6	774.7	834.5	882.0	917.1	935.5	903.4	871.3	903.4	935.5	917.1
47.5°	600.6	645.5	698.9	754.2	811.3	845.9	813.0	780.0	813.0	845.9	811.3
50°	524.6	567.5	617.4	672.9	734.0	773.1	746.6	720.1	746.6	773.1	734.0
52.5°	454.1	496.4	546.4	600.4	658.5	697.3	678.2	659.0	678.2	697.3	658.5
55°	361.5	400.5	448.0	497.3	548.5	584.4	574.6	564.7	574.6	584.4	548.5
57.5°	292.2	324.9	365.3	409.2	456.7	490.7	484.4	478.1	484.4	490.7	456.7
60°	256.1	281.7	313.1	352.6	400.1	434.6	430.3	426.0	430.3	434.6	400.1
62.5°	225.5	245.8	270.8	306.1	351.6	384.9	381.6	378.2	381.6	384.9	351.6
65°	186.2	201.6	220.8	249.7	288.6	317.0	313.9	310.8	313.9	317.0	288.6
67.5°	154.7	167.0	182.0	205.4	237.1	260.4	258.8	257.2	258.8	260.4	237.1
70°	133.8	144.8	158.3	179.0	206.7	227.4	226.8	226.2	226.8	227.4	206.7
72.5°	116.3	125.1	136.2	153.9	178.2	196.7	197.5	198.4	197.5	196.7	178.2
75°	91.3	97.1	104.5	118.1	137.8	153.1	154.9	156.8	154.9	153.1	137.8
77.5°	70.5	72.3	74.8	84.2	100.5	113.2	115.1	117.1	115.1	113.2	100.5
80°	58.3	58.3	58.3	64.4	76.8	86.6	89.1	91.6	89.1	86.6	76.8
82.5°	44.8	45.0	45.0	48.4	55.3	61.4	64.8	68.3	64.8	61.4	55.3
85°	17.6	20.8	24.5	26.4	26.4	27.1	30.2	33.3	30.2	27.1	26.4
87.5°	4.7	4.6	4.6	5.8	8.1	9.7	9.3	9.1	9.3	9.6	8.2
90°	6.8	6.4	6.4	6.1	5.2	3.9	2.3	1.0	2.3	3.5	5.8
92.5°	8.1	8.0	7.5	6.9	5.7	5.7	5.6	3.5	6.1	8.7	12.5
95°	7.4	7.4	8.7	11.0	16.1	16.4	11.0	10.0	14.2	20.0	25.1
97.5°	20.0	23.8	29.2	30.3	28.7	21.4	20.5	19.1	26.0	31.7	40.0
100°	37.0	41.9	45.7	38.0	30.0	29.6	27.7	27.1	34.5	39.9	48.0
102.5°	57.9	59.4	46.0	41.6	39.7	38.4	35.4	35.0	42.5	50.0	56.8
105°	62.8	56.4	56.7	56.7	55.4	52.8	47.3	47.0	55.4	64.1	72.5
107.5°	73.9	74.9	76.5	76.1	74.7	67.8	61.3	59.8	67.4	77.8	87.0
110°	88.6	89.5	90.2	89.5	87.3	78.6	70.9	68.6	75.4	86.3	96.3



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	102.7	103.5	104.9	102.9	99.1	89.2	80.4	77.1	83.9	95.1	105.3
115°	125.3	125.3	125.6	124.6	116.9	106.6	95.0	90.2	96.0	106.3	117.6
117.5°	147.5	147.8	146.5	144.0	135.0	123.0	110.0	102.3	106.9	117.8	129.3
120°	161.4	162.0	160.7	156.9	148.2	134.6	119.8	110.8	114.3	125.0	136.6
122.5°	175.8	175.7	174.1	169.7	159.5	145.5	130.9	119.8	121.3	131.2	142.5
125°	195.8	195.5	194.2	189.1	178.4	163.9	146.9	133.3	131.4	139.8	151.4
127.5°	214.9	214.2	212.2	205.9	195.1	181.1	162.3	147.0	142.7	148.0	158.6
130°	228.0	227.1	223.5	216.8	206.1	192.9	173.9	156.5	150.4	153.6	163.0
132.5°	240.7	237.9	234.9	227.6	217.7	204.0	184.7	166.6	158.1	159.6	166.8
135°	256.7	254.1	250.3	243.2	233.8	220.3	201.0	181.3	169.7	168.5	172.6
137.5°	270.8	268.1	263.7	257.6	248.2	236.2	217.6	196.9	182.2	177.9	179.5
140°	279.6	276.3	272.5	266.4	258.0	245.4	227.4	207.4	191.0	184.9	183.9
142.5°	286.8	284.3	280.2	274.6	267.3	254.7	237.2	217.5	200.0	192.1	189.8
145°	297.6	295.7	291.2	286.0	279.9	267.3	251.2	231.6	214.2	203.9	199.0
147.5°	306.8	305.2	301.7	295.6	290.5	278.4	263.7	246.3	228.5	215.7	209.5
150°	312.4	311.1	307.6	301.8	296.6	285.4	271.2	255.1	238.0	224.5	216.4
152.5°	317.8	316.5	312.5	306.7	302.3	291.8	278.9	263.6	246.3	232.7	224.4
155°	325.0	323.4	319.5	314.0	310.2	300.5	288.6	275.1	260.2	246.1	236.7
157.5°	330.7	328.7	325.0	320.3	316.2	307.3	297.0	285.3	272.4	258.8	249.3
160°	334.0	331.7	327.9	323.7	319.8	311.5	302.1	291.5	279.6	267.3	257.0
162.5°	336.3	334.3	329.7	326.0	322.7	315.1	306.2	296.6	286.0	275.3	265.8
165°	338.8	336.6	331.7	328.8	326.0	319.5	311.8	304.0	295.0	286.3	278.6
167.5°	339.0	337.2	332.3	329.5	327.4	321.8	315.6	309.7	302.6	295.8	289.4
170°	338.5	336.9	332.1	329.5	327.9	323.4	317.9	312.7	307.3	301.5	296.3
172.5°	336.7	335.1	330.5	328.5	327.6	323.6	319.2	315.3	310.6	306.4	302.2
175°	332.1	330.8	326.9	325.6	326.0	323.4	320.2	317.9	315.0	312.4	310.2
177.5°	325.3	324.5	321.7	321.7	322.7	321.2	320.2	319.1	317.8	317.1	316.3
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1
2.5°	1360.1	1356.9	1357.4	1358.1	1359.6	1361.1	1359.6	1358.1	1357.4	1356.9	1360.1
5°	1365.9	1363.1	1364.3	1366.8	1373.0	1379.1	1373.0	1366.8	1364.3	1363.1	1365.9
7.5°	1381.4	1381.5	1385.1	1389.8	1397.9	1406.1	1397.9	1389.8	1385.1	1381.5	1381.4
10°	1388.7	1387.8	1388.4	1391.0	1399.6	1408.3	1399.6	1391.0	1388.4	1387.8	1388.7
12.5°	1375.8	1370.4	1369.5	1370.0	1374.7	1379.4	1374.7	1370.0	1369.5	1370.4	1375.8
15°	1344.2	1334.3	1336.1	1338.3	1341.4	1344.5	1341.4	1338.3	1336.1	1334.3	1344.2
17.5°	1313.7	1306.7	1313.4	1319.9	1325.9	1332.0	1325.9	1319.9	1313.4	1306.7	1313.7
20°	1297.3	1293.3	1301.9	1311.0	1321.5	1332.0	1321.5	1311.0	1301.9	1293.3	1297.3
22.5°	1282.5	1281.7	1293.8	1306.4	1320.9	1335.3	1320.9	1306.4	1293.8	1281.7	1282.5
25°	1259.1	1265.8	1286.2	1305.5	1321.5	1337.5	1321.5	1305.5	1286.2	1265.8	1259.1
27.5°	1232.9	1250.3	1277.8	1301.2	1312.4	1323.6	1312.4	1301.2	1277.8	1250.3	1232.9
30°	1217.3	1238.5	1262.6	1281.7	1286.0	1290.3	1286.0	1281.7	1262.6	1238.5	1217.3
32.5°	1199.0	1219.6	1232.3	1240.4	1234.8	1229.3	1234.8	1240.4	1232.3	1219.6	1199.0
35°	1166.4	1180.0	1170.1	1159.8	1148.1	1136.3	1148.1	1159.8	1170.1	1180.0	1166.4
37.5°	1107.2	1106.9	1078.1	1053.1	1039.6	1026.2	1039.6	1053.1	1078.1	1106.9	1107.2
40°	1058.9	1045.4	1002.2	966.0	950.6	935.2	950.6	966.0	1002.2	1045.4	1058.9
42.5°	996.4	967.3	912.3	866.3	847.5	828.6	847.5	866.3	912.3	967.3	996.4
45°	882.0	834.5	774.7	724.6	703.6	682.6	703.6	724.6	774.7	834.5	882.0
47.5°	754.2	698.9	645.5	600.6	581.0	561.4	581.0	600.6	645.5	698.9	754.2
50°	672.9	617.4	567.5	524.6	503.0	481.5	503.0	524.6	567.5	617.4	672.9
52.5°	600.4	546.4	496.4	454.1	434.5	414.9	434.5	454.1	496.4	546.4	600.4
55°	497.3	448.0	400.5	361.5	347.9	334.4	347.9	361.5	400.5	448.0	497.3
57.5°	409.2	365.3	324.9	292.2	282.2	272.2	282.2	292.2	324.9	365.3	409.2
60°	352.6	313.1	281.7	256.1	248.0	240.0	248.0	256.1	281.7	313.1	352.6
62.5°	306.1	270.8	245.8	225.5	219.4	213.4	219.4	225.5	245.8	270.8	306.1
65°	249.7	220.8	201.6	186.2	181.9	177.6	181.9	186.2	201.6	220.8	249.7
67.5°	205.4	182.0	167.0	154.7	150.6	146.5	150.6	154.7	167.0	182.0	205.4
70°	179.0	158.3	144.8	133.8	130.7	127.6	130.7	133.8	144.8	158.3	179.0
72.5°	153.9	136.2	125.1	116.3	114.2	112.1	114.2	116.3	125.1	136.2	153.9
75°	118.1	104.5	97.1	91.3	90.0	88.8	90.0	91.3	97.1	104.5	118.1
77.5°	84.2	74.8	72.3	70.5	70.5	70.5	70.5	70.5	72.3	74.8	84.2
80°	64.4	58.3	58.3	58.3	58.3	58.3	58.3	58.3	58.3	58.3	64.4
82.5°	48.4	45.0	45.0	44.8	44.3	43.8	44.3	44.8	45.0	45.0	48.4
85°	26.4	24.5	20.8	17.6	15.7	13.9	15.7	17.6	20.8	24.5	26.4
87.5°	6.0	5.3	5.7	6.0	6.2	6.1	6.2	6.0	5.7	5.3	6.0
90°	7.4	9.7	11.9	13.2	14.5	13.8	14.5	13.2	11.9	9.7	7.4
92.5°	14.9	18.7	21.5	23.8	24.8	24.7	24.8	23.8	21.5	18.7	14.9
95°	30.0	34.5	39.0	42.2	44.1	43.5	44.1	42.2	39.0	34.5	30.0
97.5°	46.2	52.2	57.3	60.3	62.2	63.5	62.2	60.3	57.3	52.2	46.2
100°	57.0	62.8	68.6	72.1	75.4	76.7	75.4	72.1	68.6	62.8	57.0
102.5°	65.8	73.4	79.7	83.5	86.2	87.5	86.2	83.5	79.7	73.4	65.8
105°	80.2	88.3	95.0	99.8	102.7	103.7	102.7	99.8	95.0	88.3	80.2
107.5°	94.6	102.9	109.2	114.5	118.1	120.1	118.1	114.5	109.2	102.9	94.6
110°	106.0	112.7	119.5	124.3	127.9	129.2	127.9	124.3	119.5	112.7	106.0



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	115.5	123.0	129.8	134.6	138.7	140.5	138.7	134.6	129.8	123.0	115.5
115°	128.8	138.8	144.9	149.4	152.3	154.0	152.3	149.4	144.9	138.8	128.8
117.5°	139.9	150.3	157.0	160.5	161.9	163.0	161.9	160.5	157.0	150.3	139.9
120°	146.9	156.5	164.3	168.8	170.4	171.0	170.4	168.8	164.3	156.5	146.9
122.5°	153.3	162.5	169.9	175.5	178.1	178.8	178.1	175.5	169.9	162.5	153.3
125°	162.3	171.0	178.8	184.2	187.1	188.7	187.1	184.2	178.8	171.0	162.3
127.5°	170.2	179.6	186.7	191.6	194.5	195.8	194.5	191.6	186.7	179.6	170.2
130°	174.6	184.2	191.3	196.8	199.4	200.7	199.4	196.8	191.3	184.2	174.6
132.5°	177.9	188.1	195.4	200.4	203.2	204.5	203.2	200.4	195.4	188.1	177.9
135°	182.0	192.6	200.3	205.2	207.7	209.0	207.7	205.2	200.3	192.6	182.0
137.5°	185.5	195.2	203.2	208.3	210.6	211.5	210.6	208.3	203.2	195.2	185.5
140°	188.1	196.5	204.5	209.4	211.9	212.3	211.9	209.4	204.5	196.5	188.1
142.5°	191.4	198.0	205.0	209.9	212.4	213.0	212.4	209.9	205.0	198.0	191.4
145°	197.4	201.3	206.1	210.6	212.9	213.5	212.9	210.6	206.1	201.3	197.4
147.5°	205.0	206.2	208.7	211.7	213.9	214.3	213.9	211.7	208.7	206.2	205.0
150°	210.6	210.3	211.3	213.2	215.2	214.8	215.2	213.2	211.3	210.3	210.6
152.5°	217.1	215.2	215.2	216.1	217.0	216.9	217.0	216.1	215.2	215.2	217.1
155°	228.0	224.5	222.6	221.9	221.9	221.6	221.9	221.9	222.6	224.5	228.0
157.5°	240.1	235.1	232.2	230.7	230.2	229.5	230.2	230.7	232.2	235.1	240.1
160°	248.3	242.9	240.0	237.4	236.4	235.4	236.4	237.4	240.0	242.9	248.3
162.5°	256.1	250.8	247.7	245.4	244.4	242.9	244.4	245.4	247.7	250.8	256.1
165°	268.6	263.1	259.6	257.7	256.4	255.1	256.4	257.7	259.6	263.1	268.6
167.5°	281.2	275.2	272.9	270.7	269.5	267.1	269.5	270.7	272.9	275.2	281.2
170°	288.9	283.4	282.1	280.2	278.0	275.4	278.0	280.2	282.1	283.4	288.9
172.5°	295.6	291.9	290.6	288.7	288.0	285.9	288.0	288.7	290.6	291.9	295.6
175°	305.3	302.4	302.4	302.1	301.1	299.2	301.1	302.1	302.4	302.4	305.3
177.5°	313.5	311.9	312.9	312.9	312.7	310.9	312.7	312.9	312.9	311.9	313.5
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1361.1	1361.1	1361.1	1361.1
2.5°	1367.0	1370.4	1363.0	1355.6
5°	1372.7	1375.1	1364.7	1354.2
7.5°	1384.9	1383.7	1368.8	1353.9
10°	1391.2	1388.5	1370.7	1352.8
12.5°	1385.6	1387.8	1367.0	1346.1
15°	1365.7	1375.8	1351.1	1326.4
17.5°	1334.3	1343.3	1317.5	1291.7
20°	1313.9	1320.1	1294.8	1269.5
22.5°	1296.2	1300.1	1274.8	1249.6
25°	1265.8	1265.4	1243.2	1221.0
27.5°	1225.8	1217.2	1204.1	1191.0
30°	1198.8	1182.7	1174.1	1165.5
32.5°	1170.7	1148.1	1142.9	1137.7
35°	1129.4	1100.6	1096.3	1091.9
37.5°	1078.8	1055.3	1046.4	1037.6
40°	1042.9	1027.2	1012.4	997.6
42.5°	999.6	996.1	972.4	948.8
45°	917.1	935.5	903.4	871.3
47.5°	811.3	845.9	813.0	780.0
50°	734.0	773.1	746.6	720.1
52.5°	658.5	697.3	678.2	659.0
55°	548.5	584.4	574.6	564.7
57.5°	456.7	490.7	484.4	478.1
60°	400.1	434.6	430.3	426.0
62.5°	351.6	384.9	381.6	378.2
65°	288.6	317.0	313.9	310.8
67.5°	237.1	260.4	258.8	257.2
70°	206.7	227.4	226.8	226.2
72.5°	178.2	196.7	197.5	198.4
75°	137.8	153.1	154.9	156.8
77.5°	100.5	113.2	115.1	117.1
80°	76.8	86.6	89.1	91.6
82.5°	55.3	61.4	64.8	68.3
85°	26.4	27.1	30.2	33.3
87.5°	8.2	9.6	9.3	9.1
90°	5.8	3.5	2.3	1.0
92.5°	12.5	8.7	6.1	3.5
95°	25.1	20.0	14.2	10.0
97.5°	40.0	31.7	26.0	19.1
100°	48.0	39.9	34.5	27.1
102.5°	56.8	50.0	42.5	35.0
105°	72.5	64.1	55.4	47.0
107.5°	87.0	77.8	67.4	59.8
110°	96.3	86.3	75.4	68.6

TEST NUMBER: P1428188

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	105.3	95.1	83.9	77.1
115°	117.6	106.3	96.0	90.2
117.5°	129.3	117.8	106.9	102.3
120°	136.6	125.0	114.3	110.8
122.5°	142.5	131.2	121.3	119.8
125°	151.4	139.8	131.4	133.3
127.5°	158.6	148.0	142.7	147.0
130°	163.0	153.6	150.4	156.5
132.5°	166.8	159.6	158.1	166.6
135°	172.6	168.5	169.7	181.3
137.5°	179.5	177.9	182.2	196.9
140°	183.9	184.9	191.0	207.4
142.5°	189.8	192.1	200.0	217.5
145°	199.0	203.9	214.2	231.6
147.5°	209.5	215.7	228.5	246.3
150°	216.4	224.5	238.0	255.1
152.5°	224.4	232.7	246.3	263.6
155°	236.7	246.1	260.2	275.1
157.5°	249.3	258.8	272.4	285.3
160°	257.0	267.3	279.6	291.5
162.5°	265.8	275.3	286.0	296.6
165°	278.6	286.3	295.0	304.0
167.5°	289.4	295.8	302.6	309.7
170°	296.3	301.5	307.3	312.7
172.5°	302.2	306.4	310.6	315.3
175°	310.2	312.4	315.0	317.9
177.5°	316.3	317.1	317.8	319.1
180°	318.9	318.9	318.9	318.9



TEST NUMBER: P1428188
 CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.71	20.82	20.39	21.51	22.32	16.08	17.19	16.76	17.88	18.69
	3H	20.94	21.93	21.63	22.63	23.48	17.26	18.25	17.96	18.95	19.80
	4H	21.43	22.36	22.15	23.08	23.94	17.74	18.67	18.45	19.38	20.24
	6H	21.74	22.60	22.47	23.33	24.20	18.09	18.95	18.82	19.67	20.54
	8H	21.85	22.67	22.59	23.41	24.29	18.23	19.05	18.97	19.79	20.67
	12H	21.90	22.68	22.65	23.41	24.32	18.27	19.05	19.02	19.79	20.69
4H	2H	19.85	20.77	20.56	21.49	22.35	16.82	17.75	17.54	18.47	19.33
	3H	21.33	22.10	22.06	22.85	23.73	18.20	18.97	18.93	19.72	20.60
	4H	21.97	22.66	22.71	23.42	24.32	18.75	19.45	19.50	20.20	21.11
	6H	22.41	23.01	23.18	23.79	24.70	19.20	19.80	19.97	20.58	21.50
	8H	22.57	23.13	23.34	23.91	24.83	19.39	19.95	20.16	20.72	21.65
	12H	22.65	23.15	23.44	23.95	24.88	19.45	19.95	20.24	20.75	21.68
8H	4H	22.01	22.57	22.78	23.34	24.27	19.10	19.66	19.87	20.43	21.36
	6H	22.55	23.01	23.35	23.83	24.76	19.65	20.11	20.45	20.93	21.86
	8H	22.78	23.20	23.59	24.01	24.96	19.91	20.32	20.72	21.14	22.08
	12H	22.91	23.28	23.72	24.08	25.09	20.01	20.38	20.82	21.18	22.19
12H	4H	21.98	22.48	22.77	23.28	24.21	19.13	19.63	19.92	20.43	21.36
	6H	22.54	22.95	23.35	23.77	24.71	19.72	20.13	20.53	20.95	21.89
	8H	22.80	23.16	23.61	23.97	24.97	20.02	20.38	20.83	21.19	22.19