

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435962

Luminaire Tested: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435962  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6626.2 lumens  
Efficiency: N/A  
Efficacy: 131.7 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 50.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	49	48	42				
2	89	81	75	69	82	75	70	65	64	60	56	53	50	48	43	41	39	35				
3	81	71	63	57	74	66	59	54	56	51	46	46	43	40	38	35	33	29				
4	73	62	54	48	67	58	50	45	49	44	39	41	37	33	34	30	28	24				
5	67	55	47	41	62	51	44	38	44	38	33	36	32	29	30	27	24	21				
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	23	21	18				
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	24	21	18	15				
8	53	40	32	26	48	37	30	25	32	26	22	27	22	19	22	19	16	14				
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12				
10	45	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5483	5483	5483	5483
5°	5345	9710	5345	9710
10°	5005	18896	5005	18896
15°	4530	21748	4530	21748
20°	4010	22776	4010	22776
25°	3549	23150	3549	23150
30°	3134	23435	3134	23435
35°	2799	25195	2799	25195
40°	2546	26769	2546	26769
45°	2347	28032	2347	28032
50°	2215	28539	2215	28539
55°	2159	28768	2159	28768
60°	2215	28626	2215	28626
65°	2307	27816	2307	27816
70°	2389	21040	2389	21040
75°	2645	11609	2645	11609
80°	2734	10776	2734	10776
85°	2723	4539	2723	4539

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 29026 cd/sqm



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.9	0.9
10°-20°	259.6	3.9
20°-30°	456.8	6.9
30°-40°	591.3	8.9
40°-50°	652.1	9.8
50°-60°	608.6	9.2
60°-70°	470.2	7.1
70°-80°	216.8	3.3
80°-90°	46.1	0.7
90°-100°	89.1	1.3
100°-110°	259.7	3.9
110°-120°	423.9	6.4
120°-130°	537.9	8.1
130°-140°	575.6	8.7
140°-150°	537.5	8.1
150°-160°	442.3	6.7
160°-170°	296.6	4.5
170°-180°	105.3	1.6
0°-30°	773.3	11.7
0°-40°	1364.6	20.6
0°-60°	2625.3	39.6
0°-90°	3358.3	50.7
90°-120°	772.7	11.7
90°-150°	2423.6	36.6
90°-180°	3268.0	49.3
0°-180°	6626.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	340	340	340	340	340	
5°	330	599	330	599	330	31
15°	271	1301	271	1301	271	76
25°	199	1300	199	1300	199	91
35°	142	1278	142	1278	142	89
45°	103	1228	103	1228	103	80
55°	77	1022	77	1022	77	69
65°	60	728	60	728	60	59
75°	42	186	42	186	42	44
85°	15	24	15	24	15	15
90°	3	25	3	49	3	3
95°	35	26	35	153	35	42
105°	165	264	165	364	165	176
115°	316	439	316	540	316	312
125°	468	695	468	662	468	419
135°	636	910	636	734	636	492
145°	813	1049	813	750	813	509
155°	965	1140	965	778	965	444
165°	1067	1188	1067	895	1067	300
175°	1116	1163	1116	1050	1116	106
180°	1119	1119	1119	1119	1119	



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6
2.5°	337.0	343.3	349.7	356.5	363.5	371.1	379.2	386.1	389.6	393.1	389.6
5°	329.8	351.5	373.3	404.9	439.7	479.2	523.5	561.4	580.3	599.1	580.3
7.5°	317.0	361.3	405.6	499.3	609.6	724.1	842.8	941.3	979.0	1016.7	979.0
10°	305.3	367.0	428.6	587.7	779.3	926.5	1029.6	1111.9	1132.2	1152.6	1132.2
12.5°	292.2	375.9	459.7	656.1	890.0	1043.1	1115.3	1174.8	1195.7	1216.5	1195.7
15°	271.0	390.7	510.4	732.5	988.6	1146.0	1204.8	1254.7	1277.9	1301.1	1277.9
17.5°	249.1	408.5	567.8	794.3	1043.1	1196.7	1254.9	1301.7	1314.3	1326.9	1314.3
20°	233.4	420.6	607.8	834.8	1074.9	1220.0	1270.1	1309.6	1317.6	1325.6	1317.6
22.5°	219.1	428.3	637.6	864.8	1098.0	1233.5	1271.4	1301.9	1310.5	1319.1	1310.5
25°	199.2	435.0	670.8	897.3	1120.8	1244.5	1268.5	1287.9	1293.7	1299.5	1293.7
27.5°	179.9	429.1	678.2	901.9	1117.1	1232.5	1248.2	1261.4	1267.0	1272.7	1267.0
30°	168.1	421.4	674.6	896.3	1107.4	1218.8	1230.4	1241.1	1249.1	1257.0	1249.1
32.5°	157.7	412.1	666.5	885.4	1092.4	1201.5	1212.5	1225.1	1242.4	1259.6	1242.4
35°	142.0	392.3	642.7	859.2	1064.6	1176.0	1193.4	1214.4	1246.3	1278.3	1246.3
37.5°	128.6	367.1	605.5	819.8	1026.2	1147.6	1184.0	1219.0	1249.8	1280.5	1249.8
40°	120.8	349.4	577.9	790.7	998.2	1126.3	1174.9	1217.9	1244.0	1270.1	1244.0
42.5°	113.0	329.3	545.7	756.7	966.0	1099.0	1155.7	1204.8	1230.9	1257.0	1230.9
45°	102.8	297.3	491.7	700.9	914.9	1055.3	1122.1	1178.3	1203.0	1227.7	1203.0
47.5°	93.4	262.3	431.2	641.3	865.0	1012.3	1083.1	1140.7	1158.7	1176.7	1158.7
50°	88.2	239.1	390.0	600.8	831.5	981.7	1051.3	1107.2	1121.7	1136.2	1121.7
52.5°	82.9	216.4	349.9	561.1	798.3	949.6	1015.2	1067.7	1081.1	1094.4	1081.1
55°	76.7	185.6	294.4	503.4	745.7	895.5	952.8	998.7	1010.3	1022.0	1010.3
57.5°	71.2	159.0	246.8	449.2	689.8	834.5	883.4	922.4	931.9	941.3	931.9
60°	68.6	144.7	220.9	415.2	648.8	787.8	832.0	867.6	877.0	886.5	877.0
62.5°	64.6	131.0	197.3	381.2	604.4	736.4	777.2	810.0	818.8	827.7	818.8
65°	60.4	114.1	167.8	333.6	536.7	655.4	689.5	716.5	722.3	728.1	722.3
67.5°	54.5	100.1	145.7	289.9	467.1	566.3	587.5	600.7	589.8	578.9	589.8
70°	50.6	92.7	134.8	263.4	420.8	503.2	510.4	508.1	476.9	445.7	476.9
72.5°	48.0	85.4	122.9	234.2	370.2	430.2	414.2	387.5	328.4	269.4	328.4
75°	42.4	72.9	103.4	187.2	288.8	304.7	235.1	183.2	184.7	186.1	184.7
77.5°	34.6	57.4	80.2	131.7	192.8	204.9	168.0	140.7	142.0	143.3	142.0
80°	29.4	47.5	65.7	86.0	107.0	116.8	115.4	114.5	115.2	115.9	115.2
82.5°	24.2	37.7	51.2	63.3	75.1	81.7	83.1	84.0	83.0	82.0	83.0
85°	14.7	22.7	30.7	35.4	39.0	37.9	32.1	27.4	25.9	24.5	25.9
87.5°	5.9	9.7	13.7	13.6	12.0	11.1	11.1	11.3	11.5	11.5	11.5
90°	3.4	7.9	13.6	18.1	21.5	22.6	22.6	23.7	24.9	24.9	24.9
92.5°	12.4	19.7	19.9	19.9	24.2	26.2	28.0	28.3	29.4	29.4	29.4
95°	35.0	38.4	57.7	56.5	38.4	30.5	26.0	26.0	26.0	26.0	26.0
97.5°	66.9	71.9	75.1	100.6	106.3	102.6	83.7	70.3	62.9	59.5	62.9
100°	95.0	97.2	104.0	105.1	133.4	160.5	147.0	130.0	124.4	121.0	124.4
102.5°	123.0	124.4	134.8	139.5	146.1	161.4	208.5	203.3	199.4	198.7	199.4
105°	165.1	166.2	185.4	194.4	199.0	199.0	197.8	220.4	256.6	264.5	256.6
107.5°	210.0	215.2	237.9	262.0	267.2	268.6	262.7	259.3	258.0	258.9	258.0
110°	240.8	248.7	275.8	306.4	314.3	316.5	314.3	310.9	308.6	308.6	308.6



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	270.6	282.2	312.9	348.0	361.3	368.1	363.1	360.6	358.4	360.2	358.4
115°	316.5	333.5	374.2	410.4	437.5	440.9	439.8	439.8	438.6	438.6	438.6
117.5°	359.0	386.2	431.8	473.9	505.3	514.4	518.9	517.5	516.2	518.4	516.2
120°	388.9	420.5	472.5	520.0	550.6	564.1	568.6	566.4	568.6	566.4	568.6
122.5°	420.5	459.4	510.5	559.8	595.8	611.1	616.6	617.0	617.5	616.1	617.5
125°	468.0	515.5	575.4	626.3	663.6	681.7	686.2	687.3	689.6	695.3	689.6
127.5°	516.0	569.8	635.6	684.6	722.8	744.8	751.8	754.3	759.0	761.5	759.0
130°	549.4	610.5	677.2	723.5	760.8	784.6	797.0	800.4	806.0	804.9	806.0
132.5°	584.7	648.5	716.1	764.2	798.8	824.4	835.0	844.7	846.7	848.3	846.7
135°	636.5	705.4	773.3	820.7	853.5	878.4	892.0	901.0	906.7	910.0	906.7
137.5°	691.0	763.8	828.9	871.2	904.2	925.7	941.0	950.5	956.4	959.1	956.4
140°	728.0	798.1	861.4	905.5	934.9	956.4	970.0	981.3	988.1	988.1	988.1
142.5°	763.3	832.5	894.0	938.1	963.9	983.5	998.0	1006.6	1014.3	1014.3	1014.3
145°	812.8	881.8	938.3	982.4	1003.9	1022.0	1037.8	1044.6	1049.1	1049.1	1049.1
147.5°	864.6	925.7	977.2	1019.5	1037.6	1058.8	1071.3	1076.7	1082.3	1079.9	1082.3
150°	895.4	951.9	1001.6	1041.2	1059.3	1079.6	1092.1	1096.6	1102.2	1098.8	1102.2
152.5°	925.2	979.0	1024.2	1061.1	1076.5	1096.8	1111.1	1115.6	1119.4	1116.9	1119.4
155°	965.4	1012.9	1054.8	1088.7	1102.2	1121.5	1135.0	1140.7	1145.2	1139.5	1145.2
157.5°	1001.4	1042.3	1078.7	1109.9	1124.4	1140.9	1153.6	1160.6	1165.1	1162.6	1165.1
160°	1023.1	1060.4	1093.2	1122.6	1136.1	1150.8	1164.4	1172.3	1176.8	1173.5	1176.8
162.5°	1041.2	1074.9	1105.9	1132.5	1144.3	1157.2	1173.5	1180.5	1185.0	1180.7	1185.0
165°	1067.2	1094.3	1121.5	1144.1	1154.2	1164.4	1181.4	1189.3	1192.7	1188.2	1192.7
167.5°	1086.9	1107.7	1129.6	1149.0	1156.5	1166.4	1183.4	1190.0	1194.3	1188.6	1194.3
170°	1097.7	1115.8	1135.0	1150.8	1156.5	1165.5	1182.5	1188.2	1191.5	1185.9	1191.5
172.5°	1106.8	1120.3	1135.9	1149.9	1152.9	1160.1	1176.2	1181.8	1184.3	1179.6	1184.3
175°	1115.8	1123.7	1135.0	1144.1	1142.9	1147.5	1161.0	1165.5	1170.1	1163.3	1170.1
177.5°	1120.1	1123.7	1127.3	1132.8	1129.1	1129.1	1139.1	1141.8	1142.7	1139.1	1142.7
180°	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6
2.5°	386.1	379.2	371.1	363.5	356.5	349.7	343.3	337.0	343.3	349.7	356.5
5°	561.4	523.5	479.2	439.7	404.9	373.3	351.5	329.8	351.5	373.3	404.9
7.5°	941.3	842.8	724.1	609.6	499.3	405.6	361.3	317.0	361.3	405.6	499.3
10°	1111.9	1029.6	926.5	779.3	587.7	428.6	367.0	305.3	367.0	428.6	587.7
12.5°	1174.8	1115.3	1043.1	890.0	656.1	459.7	375.9	292.2	375.9	459.7	656.1
15°	1254.7	1204.8	1146.0	988.6	732.5	510.4	390.7	271.0	390.7	510.4	732.5
17.5°	1301.7	1254.9	1196.7	1043.1	794.3	567.8	408.5	249.1	408.5	567.8	794.3
20°	1309.6	1270.1	1220.0	1074.9	834.8	607.8	420.6	233.4	420.6	607.8	834.8
22.5°	1301.9	1271.4	1233.5	1098.0	864.8	637.6	428.3	219.1	428.3	637.6	864.8
25°	1287.9	1268.5	1244.5	1120.8	897.3	670.8	435.0	199.2	435.0	670.8	897.3
27.5°	1261.4	1248.2	1232.5	1117.1	901.9	678.2	429.1	179.9	429.1	678.2	901.9
30°	1241.1	1230.4	1218.8	1107.4	896.3	674.6	421.4	168.1	421.4	674.6	896.3
32.5°	1225.1	1212.5	1201.5	1092.4	885.4	666.5	412.1	157.7	412.1	666.5	885.4
35°	1214.4	1193.4	1176.0	1064.6	859.2	642.7	392.3	142.0	392.3	642.7	859.2
37.5°	1219.0	1184.0	1147.6	1026.2	819.8	605.5	367.1	128.6	367.1	605.5	819.8
40°	1217.9	1174.9	1126.3	998.2	790.7	577.9	349.4	120.8	349.4	577.9	790.7
42.5°	1204.8	1155.7	1099.0	966.0	756.7	545.7	329.3	113.0	329.3	545.7	756.7
45°	1178.3	1122.1	1055.3	914.9	700.9	491.7	297.3	102.8	297.3	491.7	700.9
47.5°	1140.7	1083.1	1012.3	865.0	641.3	431.2	262.3	93.4	262.3	431.2	641.3
50°	1107.2	1051.3	981.7	831.5	600.8	390.0	239.1	88.2	239.1	390.0	600.8
52.5°	1067.7	1015.2	949.6	798.3	561.1	349.9	216.4	82.9	216.4	349.9	561.1
55°	998.7	952.8	895.5	745.7	503.4	294.4	185.6	76.7	185.6	294.4	503.4
57.5°	922.4	883.4	834.5	689.8	449.2	246.8	159.0	71.2	159.0	246.8	449.2
60°	867.6	832.0	787.8	648.8	415.2	220.9	144.7	68.6	144.7	220.9	415.2
62.5°	810.0	777.2	736.4	604.4	381.2	197.3	131.0	64.6	131.0	197.3	381.2
65°	716.5	689.5	655.4	536.7	333.6	167.8	114.1	60.4	114.1	167.8	333.6
67.5°	600.7	587.5	566.3	467.1	289.9	145.7	100.1	54.5	100.1	145.7	289.9
70°	508.1	510.4	503.2	420.8	263.4	134.8	92.7	50.6	92.7	134.8	263.4
72.5°	387.5	414.2	430.2	370.2	234.2	122.9	85.4	48.0	85.4	122.9	234.2
75°	183.2	235.1	304.7	288.8	187.2	103.4	72.9	42.4	72.9	103.4	187.2
77.5°	140.7	168.0	204.9	192.8	131.7	80.2	57.4	34.6	57.4	80.2	131.7
80°	114.5	115.4	116.8	107.0	86.0	65.7	47.5	29.4	47.5	65.7	86.0
82.5°	84.0	83.1	81.7	75.1	63.3	51.2	37.7	24.2	37.7	51.2	63.3
85°	27.4	32.1	37.9	39.0	35.4	30.7	22.7	14.7	22.7	30.7	35.4
87.5°	11.3	11.1	11.1	12.0	13.6	13.7	9.7	5.9	9.7	13.5	14.1
90°	23.7	22.6	22.6	21.5	18.1	13.6	7.9	3.4	7.9	12.4	20.3
92.5°	28.3	28.0	26.2	24.2	19.9	19.9	19.7	12.4	21.5	30.5	43.9
95°	26.0	26.0	30.5	38.4	56.5	57.7	38.4	35.0	49.7	70.1	88.2
97.5°	70.3	83.7	102.6	106.3	100.6	75.1	71.9	66.9	91.1	111.2	140.4
100°	130.0	147.0	160.5	133.4	105.1	104.0	97.2	95.0	121.0	140.2	168.4
102.5°	203.3	208.5	161.4	146.1	139.5	134.8	124.4	123.0	149.0	175.5	199.2
105°	220.4	197.8	199.0	199.0	194.4	185.4	166.2	165.1	194.4	225.0	254.4
107.5°	259.3	262.7	268.6	267.2	262.0	237.9	215.2	210.0	236.5	273.1	305.5
110°	310.9	314.3	316.5	314.3	306.4	275.8	248.7	240.8	264.5	303.0	338.0



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	360.6	363.1	368.1	361.3	348.0	312.9	282.2	270.6	294.4	333.7	369.7
115°	439.8	439.8	440.9	437.5	410.4	374.2	333.5	316.5	336.9	373.1	412.6
117.5°	517.5	518.9	514.4	505.3	473.9	431.8	386.2	359.0	375.1	413.3	454.0
120°	566.4	568.6	564.1	550.6	520.0	472.5	420.5	388.9	401.3	438.6	479.3
122.5°	617.0	616.6	611.1	595.8	559.8	510.5	459.4	420.5	425.7	460.3	500.1
125°	687.3	686.2	681.7	663.6	626.3	575.4	515.5	468.0	461.2	490.6	531.3
127.5°	754.3	751.8	744.8	722.8	684.6	635.6	569.8	516.0	500.8	519.4	556.7
130°	800.4	797.0	784.6	760.8	723.5	677.2	610.5	549.4	527.9	539.2	572.0
132.5°	844.7	835.0	824.4	798.8	764.2	716.1	648.5	584.7	555.1	560.0	585.6
135°	901.0	892.0	878.4	853.5	820.7	773.3	705.4	636.5	595.8	591.2	605.9
137.5°	950.5	941.0	925.7	904.2	871.2	828.9	763.8	691.0	639.6	624.5	630.1
140°	981.3	970.0	956.4	934.9	905.5	861.4	798.1	728.0	670.4	648.9	645.5
142.5°	1006.6	998.0	983.5	963.9	938.1	894.0	832.5	763.3	702.0	674.2	666.3
145°	1044.6	1037.8	1022.0	1003.9	982.4	938.3	881.8	812.8	751.8	715.6	698.6
147.5°	1076.7	1071.3	1058.8	1037.6	1019.5	977.2	925.7	864.6	802.0	757.2	735.3
150°	1096.6	1092.1	1079.6	1059.3	1041.2	1001.6	951.9	895.4	835.4	788.0	759.7
152.5°	1115.6	1111.1	1096.8	1076.5	1061.1	1024.2	979.0	925.2	864.4	816.9	787.7
155°	1140.7	1135.0	1121.5	1102.2	1088.7	1054.8	1012.9	965.4	913.4	863.7	830.9
157.5°	1160.6	1153.6	1140.9	1124.4	1109.9	1078.7	1042.3	1001.4	955.9	908.5	875.0
160°	1172.3	1164.4	1150.8	1136.1	1122.6	1093.2	1060.4	1023.1	981.3	938.3	902.1
162.5°	1180.5	1173.5	1157.2	1144.3	1132.5	1105.9	1074.9	1041.2	1003.9	966.3	932.9
165°	1189.3	1181.4	1164.4	1154.2	1144.1	1121.5	1094.3	1067.2	1035.5	1005.0	977.9
167.5°	1190.0	1183.4	1166.4	1156.5	1149.0	1129.6	1107.7	1086.9	1062.2	1038.2	1015.6
170°	1188.2	1182.5	1165.5	1156.5	1150.8	1135.0	1115.8	1097.7	1078.5	1058.1	1040.1
172.5°	1181.8	1176.2	1160.1	1152.9	1149.9	1135.9	1120.3	1106.8	1090.3	1075.3	1060.9
175°	1165.5	1161.0	1147.5	1142.9	1144.1	1135.0	1123.7	1115.8	1105.6	1096.6	1088.7
177.5°	1141.8	1139.1	1129.1	1129.1	1132.8	1127.3	1123.7	1120.1	1115.6	1112.9	1110.1
180°	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6	339.6
2.5°	363.5	371.1	379.2	386.1	389.6	393.1	389.6	386.1	379.2	371.1	363.5
5°	439.7	479.2	523.5	561.4	580.3	599.1	580.3	561.4	523.5	479.2	439.7
7.5°	609.6	724.1	842.8	941.3	979.0	1016.7	979.0	941.3	842.8	724.1	609.6
10°	779.3	926.5	1029.6	1111.9	1132.2	1152.6	1132.2	1111.9	1029.6	926.5	779.3
12.5°	890.0	1043.1	1115.3	1174.8	1195.7	1216.5	1195.7	1174.8	1115.3	1043.1	890.0
15°	988.6	1146.0	1204.8	1254.7	1277.9	1301.1	1277.9	1254.7	1204.8	1146.0	988.6
17.5°	1043.1	1196.7	1254.9	1301.7	1314.3	1326.9	1314.3	1301.7	1254.9	1196.7	1043.1
20°	1074.9	1220.0	1270.1	1309.6	1317.6	1325.6	1317.6	1309.6	1270.1	1220.0	1074.9
22.5°	1098.0	1233.5	1271.4	1301.9	1310.5	1319.1	1310.5	1301.9	1271.4	1233.5	1098.0
25°	1120.8	1244.5	1268.5	1287.9	1293.7	1299.5	1293.7	1287.9	1268.5	1244.5	1120.8
27.5°	1117.1	1232.5	1248.2	1261.4	1267.0	1272.7	1267.0	1261.4	1248.2	1232.5	1117.1
30°	1107.4	1218.8	1230.4	1241.1	1249.1	1257.0	1249.1	1241.1	1230.4	1218.8	1107.4
32.5°	1092.4	1201.5	1212.5	1225.1	1242.4	1259.6	1242.4	1225.1	1212.5	1201.5	1092.4
35°	1064.6	1176.0	1193.4	1214.4	1246.3	1278.3	1246.3	1214.4	1193.4	1176.0	1064.6
37.5°	1026.2	1147.6	1184.0	1219.0	1249.8	1280.5	1249.8	1219.0	1184.0	1147.6	1026.2
40°	998.2	1126.3	1174.9	1217.9	1244.0	1270.1	1244.0	1217.9	1174.9	1126.3	998.2
42.5°	966.0	1099.0	1155.7	1204.8	1230.9	1257.0	1230.9	1204.8	1155.7	1099.0	966.0
45°	914.9	1055.3	1122.1	1178.3	1203.0	1227.7	1203.0	1178.3	1122.1	1055.3	914.9
47.5°	865.0	1012.3	1083.1	1140.7	1158.7	1176.7	1158.7	1140.7	1083.1	1012.3	865.0
50°	831.5	981.7	1051.3	1107.2	1121.7	1136.2	1121.7	1107.2	1051.3	981.7	831.5
52.5°	798.3	949.6	1015.2	1067.7	1081.1	1094.4	1081.1	1067.7	1015.2	949.6	798.3
55°	745.7	895.5	952.8	998.7	1010.3	1022.0	1010.3	998.7	952.8	895.5	745.7
57.5°	689.8	834.5	883.4	922.4	931.9	941.3	931.9	922.4	883.4	834.5	689.8
60°	648.8	787.8	832.0	867.6	877.0	886.5	877.0	867.6	832.0	787.8	648.8
62.5°	604.4	736.4	777.2	810.0	818.8	827.7	818.8	810.0	777.2	736.4	604.4
65°	536.7	655.4	689.5	716.5	722.3	728.1	722.3	716.5	689.5	655.4	536.7
67.5°	467.1	566.3	587.5	600.7	589.8	578.9	589.8	600.7	587.5	566.3	467.1
70°	420.8	503.2	510.4	508.1	476.9	445.7	476.9	508.1	510.4	503.2	420.8
72.5°	370.2	430.2	414.2	387.5	328.4	269.4	328.4	387.5	414.2	430.2	370.2
75°	288.8	304.7	235.1	183.2	184.7	186.1	184.7	183.2	235.1	304.7	288.8
77.5°	192.8	204.9	168.0	140.7	142.0	143.3	142.0	140.7	168.0	204.9	192.8
80°	107.0	116.8	115.4	114.5	115.2	115.9	115.2	114.5	115.4	116.8	107.0
82.5°	75.1	81.7	83.1	84.0	83.0	82.0	83.0	84.0	83.1	81.7	75.1
85°	39.0	37.9	32.1	27.4	25.9	24.5	25.9	27.4	32.1	37.9	39.0
87.5°	12.9	13.3	14.9	15.8	16.7	16.3	16.7	15.8	14.9	13.3	12.9
90°	26.0	33.9	41.8	46.4	50.9	48.6	50.9	46.4	41.8	33.9	26.0
92.5°	52.2	65.6	75.3	83.4	87.0	86.6	87.0	83.4	75.3	65.6	52.2
95°	105.1	121.0	136.8	148.1	154.9	152.6	154.9	148.1	136.8	121.0	105.1
97.5°	162.1	183.4	201.0	211.6	218.4	222.9	218.4	211.6	201.0	183.4	162.1
100°	200.1	220.4	240.8	253.2	264.5	269.1	264.5	253.2	240.8	220.4	200.1
102.5°	230.8	257.5	279.7	293.0	302.5	307.0	302.5	293.0	279.7	257.5	230.8
105°	281.5	309.8	333.5	350.5	360.6	364.0	360.6	350.5	333.5	309.8	281.5
107.5°	332.1	361.3	383.2	402.0	414.4	421.7	414.4	402.0	383.2	361.3	332.1
110°	371.9	395.7	419.4	436.4	448.8	453.3	448.8	436.4	419.4	395.7	371.9



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	405.4	431.8	455.6	472.5	486.8	493.1	486.8	472.5	455.6	431.8	405.4
115°	452.2	487.2	508.7	524.6	534.7	540.4	534.7	524.6	508.7	487.2	452.2
117.5°	491.1	527.7	551.2	563.4	568.2	572.3	568.2	563.4	551.2	527.7	491.1
120°	515.5	549.4	576.6	592.4	598.0	600.3	598.0	592.4	576.6	549.4	515.5
122.5°	538.1	570.2	596.5	615.9	625.2	627.4	625.2	615.9	596.5	570.2	538.1
125°	569.8	600.3	627.4	646.6	656.8	662.5	656.8	646.6	627.4	600.3	569.8
127.5°	597.4	630.4	655.2	672.6	682.6	687.1	682.6	672.6	655.2	630.4	597.4
130°	612.7	646.6	671.5	690.7	699.8	704.3	699.8	690.7	671.5	646.6	612.7
132.5°	624.5	660.2	686.0	703.4	713.3	717.9	713.3	703.4	686.0	660.2	624.5
135°	638.7	676.0	703.2	720.1	729.2	733.7	729.2	720.1	703.2	676.0	638.7
137.5°	651.2	685.1	713.3	731.2	739.3	742.3	739.3	731.2	713.3	685.1	651.2
140°	660.2	689.6	717.9	734.8	743.9	745.0	743.9	734.8	717.9	689.6	660.2
142.5°	672.0	695.0	719.7	736.6	745.7	747.7	745.7	736.6	719.7	695.0	672.0
145°	693.0	706.6	723.5	739.3	747.3	749.5	747.3	739.3	723.5	706.6	693.0
147.5°	719.4	723.7	732.6	743.0	750.6	752.2	750.6	743.0	732.6	723.7	719.4
150°	739.3	738.2	741.6	748.4	755.2	754.0	755.2	748.4	741.6	738.2	739.3
152.5°	762.0	755.4	755.2	758.3	761.5	761.3	761.5	758.3	755.2	755.4	762.0
155°	800.4	788.0	781.2	778.9	778.9	777.8	778.9	778.9	781.2	788.0	800.4
157.5°	842.7	825.3	815.1	809.7	808.1	805.6	808.1	809.7	815.1	825.3	842.7
160°	871.6	852.4	842.2	833.2	829.8	826.4	829.8	833.2	842.2	852.4	871.6
162.5°	898.7	880.4	869.4	861.2	857.8	852.6	857.8	861.2	869.4	880.4	898.7
165°	942.8	923.6	911.2	904.4	899.9	895.4	899.9	904.4	911.2	923.6	942.8
167.5°	986.9	965.9	957.8	950.1	945.8	937.6	945.8	950.1	957.8	965.9	986.9
170°	1014.1	994.8	990.3	983.5	975.6	966.6	975.6	983.5	990.3	994.8	1014.1
172.5°	1037.6	1024.7	1020.2	1013.4	1010.9	1003.7	1010.9	1013.4	1020.2	1024.7	1037.6
175°	1071.7	1061.5	1061.5	1060.4	1057.0	1050.2	1057.0	1060.4	1061.5	1061.5	1071.7
177.5°	1100.2	1094.8	1098.4	1098.4	1097.5	1091.2	1097.5	1098.4	1098.4	1094.8	1100.2
180°	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2

TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	339.6	339.6	339.6	339.6
2.5°	356.5	349.7	343.3	337.0
5°	404.9	373.3	351.5	329.8
7.5°	499.3	405.6	361.3	317.0
10°	587.7	428.6	367.0	305.3
12.5°	656.1	459.7	375.9	292.2
15°	732.5	510.4	390.7	271.0
17.5°	794.3	567.8	408.5	249.1
20°	834.8	607.8	420.6	233.4
22.5°	864.8	637.6	428.3	219.1
25°	897.3	670.8	435.0	199.2
27.5°	901.9	678.2	429.1	179.9
30°	896.3	674.6	421.4	168.1
32.5°	885.4	666.5	412.1	157.7
35°	859.2	642.7	392.3	142.0
37.5°	819.8	605.5	367.1	128.6
40°	790.7	577.9	349.4	120.8
42.5°	756.7	545.7	329.3	113.0
45°	700.9	491.7	297.3	102.8
47.5°	641.3	431.2	262.3	93.4
50°	600.8	390.0	239.1	88.2
52.5°	561.1	349.9	216.4	82.9
55°	503.4	294.4	185.6	76.7
57.5°	449.2	246.8	159.0	71.2
60°	415.2	220.9	144.7	68.6
62.5°	381.2	197.3	131.0	64.6
65°	333.6	167.8	114.1	60.4
67.5°	289.9	145.7	100.1	54.5
70°	263.4	134.8	92.7	50.6
72.5°	234.2	122.9	85.4	48.0
75°	187.2	103.4	72.9	42.4
77.5°	131.7	80.2	57.4	34.6
80°	86.0	65.7	47.5	29.4
82.5°	63.3	51.2	37.7	24.2
85°	35.4	30.7	22.7	14.7
87.5°	14.1	13.5	9.7	5.9
90°	20.3	12.4	7.9	3.4
92.5°	43.9	30.5	21.5	12.4
95°	88.2	70.1	49.7	35.0
97.5°	140.4	111.2	91.1	66.9
100°	168.4	140.2	121.0	95.0
102.5°	199.2	175.5	149.0	123.0
105°	254.4	225.0	194.4	165.1
107.5°	305.5	273.1	236.5	210.0
110°	338.0	303.0	264.5	240.8



TEST NUMBER: P1435962

CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	369.7	333.7	294.4	270.6
115°	412.6	373.1	336.9	316.5
117.5°	454.0	413.3	375.1	359.0
120°	479.3	438.6	401.3	388.9
122.5°	500.1	460.3	425.7	420.5
125°	531.3	490.6	461.2	468.0
127.5°	556.7	519.4	500.8	516.0
130°	572.0	539.2	527.9	549.4
132.5°	585.6	560.0	555.1	584.7
135°	605.9	591.2	595.8	636.5
137.5°	630.1	624.5	639.6	691.0
140°	645.5	648.9	670.4	728.0
142.5°	666.3	674.2	702.0	763.3
145°	698.6	715.6	751.8	812.8
147.5°	735.3	757.2	802.0	864.6
150°	759.7	788.0	835.4	895.4
152.5°	787.7	816.9	864.4	925.2
155°	830.9	863.7	913.4	965.4
157.5°	875.0	908.5	955.9	1001.4
160°	902.1	938.3	981.3	1023.1
162.5°	932.9	966.3	1003.9	1041.2
165°	977.9	1005.0	1035.5	1067.2
167.5°	1015.6	1038.2	1062.2	1086.9
170°	1040.1	1058.1	1078.5	1097.7
172.5°	1060.9	1075.3	1090.3	1106.8
175°	1088.7	1096.6	1105.6	1115.8
177.5°	1110.1	1112.9	1115.6	1120.1
180°	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1435962  
 CATALOG NUMBER: SQ2W-FB-K-075U-075D-L835-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.15	13.04	13.09	14.01	15.27	21.74	22.64	22.69	23.61	24.86
	3H	13.09	13.89	14.05	14.87	16.15	23.35	24.16	24.31	25.13	26.41
	4H	13.49	14.25	14.46	15.23	16.52	23.53	24.29	24.50	25.27	26.56
	6H	13.75	14.45	14.73	15.43	16.73	23.61	24.31	24.59	25.29	26.60
	8H	13.84	14.51	14.83	15.51	16.81	23.63	24.30	24.62	25.30	26.60
	12H	13.89	14.52	14.88	15.52	16.85	23.61	24.24	24.60	25.24	26.56
4H	2H	16.87	17.63	17.85	18.61	19.90	22.11	22.87	23.09	23.85	25.14
	3H	18.00	18.64	18.99	19.65	20.95	24.01	24.64	24.99	25.65	26.95
	4H	18.29	18.87	19.28	19.87	21.20	24.23	24.81	25.23	25.81	27.14
	6H	18.42	18.92	19.43	19.95	21.27	24.36	24.86	25.37	25.89	27.21
	8H	18.47	18.93	19.48	19.95	21.29	24.41	24.87	25.42	25.89	27.23
	12H	18.47	18.89	19.50	19.92	21.27	24.39	24.81	25.42	25.85	27.19
8H	4H	19.48	19.95	20.49	20.97	22.31	24.32	24.79	25.33	25.81	27.15
	6H	19.74	20.13	20.78	21.19	22.53	24.52	24.91	25.56	25.97	27.30
	8H	19.84	20.18	20.88	21.23	22.58	24.61	24.95	25.66	26.00	27.35
	12H	19.89	20.18	20.93	21.22	22.62	24.62	24.92	25.67	25.96	27.36
12H	4H	19.51	19.93	20.54	20.96	22.31	24.28	24.70	25.31	25.73	27.08
	6H	19.85	20.19	20.89	21.23	22.59	24.50	24.84	25.55	25.89	27.25
	8H	19.99	20.29	21.04	21.33	22.73	24.61	24.90	25.65	25.94	27.34