

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428308

Luminaire Tested: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428308  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE RIPPLE LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8874.8 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 81.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	70	79	73	68	64	59	56	53	47	45	43	35	34	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	28	24
4	73	63	55	50	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	43	61	51	45	40	42	37	33	34	30	28	26	24	22	18
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	21	22	19	17	14
8	53	41	34	29	48	38	31	27	31	26	23	26	22	19	20	17	15	13
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21976	21976	21976	21976
5°	21948	22351	21948	22351
10°	22179	23089	22179	23089
15°	22171	22473	22171	22473
20°	21812	22886	21812	22886
25°	21752	23827	21752	23827
30°	21729	24055	21729	24055
35°	21521	22397	21521	22397
40°	21026	19711	21026	19711
45°	19895	15586	19895	15586
50°	18087	12094	18087	12094
55°	15896	9413	15896	9413
60°	13756	7750	13756	7750
65°	11874	6785	11874	6785
70°	10678	6024	10678	6024
75°	9781	5539	9781	5539
80°	8517	5421	8517	5421
85°	6169	2575	6169	2575

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 21361 cd/sqm



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.4	1.5
10°-20°	380.5	4.3
20°-30°	588.2	6.6
30°-40°	707.4	8.0
40°-50°	635.2	7.2
50°-60°	425.6	4.8
60°-70°	247.6	2.8
70°-80°	127.2	1.4
80°-90°	39.3	0.4
90°-100°	152.4	1.7
100°-110°	444.5	5.0
110°-120°	725.4	8.2
120°-130°	920.5	10.4
130°-140°	985.0	11.1
140°-150°	919.8	10.4
150°-160°	756.8	8.5
160°-170°	507.6	5.7
170°-180°	180.2	2.0
0°-30°	1100.2	12.4
0°-40°	1807.6	20.4
0°-60°	2868.4	32.3
0°-90°	3282.5	37.0
90°-120°	1322.4	14.9
90°-150°	4147.7	46.7
90°-180°	5592.0	63.0
0°-180°	8874.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1361	1361	1361	1361	1361	
5°	1354	1379	1354	1379	1354	129
15°	1326	1344	1326	1344	1326	372
25°	1221	1338	1221	1338	1221	563
35°	1092	1136	1092	1136	1092	681
45°	871	683	871	683	871	667
55°	565	334	565	334	565	507
65°	311	178	311	178	311	314
75°	157	89	157	89	157	166
85°	33	14	33	14	33	41
90°	6	43	6	83	6	6
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1
2.5°	1355.6	1363.0	1370.4	1367.0	1360.1	1356.9	1357.4	1358.1	1359.6	1361.1	1359.6
5°	1354.2	1364.7	1375.1	1372.7	1365.9	1363.1	1364.3	1366.8	1373.0	1379.1	1373.0
7.5°	1353.9	1368.8	1383.7	1384.9	1381.4	1381.5	1385.1	1389.8	1397.9	1406.1	1397.9
10°	1352.8	1370.7	1388.5	1391.2	1388.7	1387.8	1388.4	1391.0	1399.6	1408.3	1399.6
12.5°	1346.1	1367.0	1387.8	1385.6	1375.8	1370.4	1369.5	1370.0	1374.7	1379.4	1374.7
15°	1326.4	1351.1	1375.8	1365.7	1344.2	1334.3	1336.1	1338.3	1341.4	1344.5	1341.4
17.5°	1291.7	1317.5	1343.3	1334.3	1313.7	1306.7	1313.4	1319.9	1325.9	1332.0	1325.9
20°	1269.5	1294.8	1320.1	1313.9	1297.3	1293.3	1301.9	1311.0	1321.5	1332.0	1321.5
22.5°	1249.6	1274.8	1300.1	1296.2	1282.5	1281.7	1293.8	1306.4	1320.9	1335.3	1320.9
25°	1221.0	1243.2	1265.4	1265.8	1259.1	1265.8	1286.2	1305.5	1321.5	1337.5	1321.5
27.5°	1191.0	1204.1	1217.2	1225.8	1232.9	1250.3	1277.8	1301.2	1312.4	1323.6	1312.4
30°	1165.5	1174.1	1182.7	1198.8	1217.3	1238.5	1262.6	1281.7	1286.0	1290.3	1286.0
32.5°	1137.7	1142.9	1148.1	1170.7	1199.0	1219.6	1232.3	1240.4	1234.8	1229.3	1234.8
35°	1091.9	1096.3	1100.6	1129.4	1166.4	1180.0	1170.1	1159.8	1148.1	1136.3	1148.1
37.5°	1037.6	1046.4	1055.3	1078.8	1107.2	1106.9	1078.1	1053.1	1039.6	1026.2	1039.6
40°	997.6	1012.4	1027.2	1042.9	1058.9	1045.4	1002.2	966.0	950.6	935.2	950.6
42.5°	948.8	972.4	996.1	999.6	996.4	967.3	912.3	866.3	847.5	828.6	847.5
45°	871.3	903.4	935.5	917.1	882.0	834.5	774.7	724.6	703.6	682.6	703.6
47.5°	780.0	813.0	845.9	811.3	754.2	698.9	645.5	600.6	581.0	561.4	581.0
50°	720.1	746.6	773.1	734.0	672.9	617.4	567.5	524.6	503.0	481.5	503.0
52.5°	659.0	678.2	697.3	658.5	600.4	546.4	496.4	454.1	434.5	414.9	434.5
55°	564.7	574.6	584.4	548.5	497.3	448.0	400.5	361.5	347.9	334.4	347.9
57.5°	478.1	484.4	490.7	456.7	409.2	365.3	324.9	292.2	282.2	272.2	282.2
60°	426.0	430.3	434.6	400.1	352.6	313.1	281.7	256.1	248.0	240.0	248.0
62.5°	378.2	381.6	384.9	351.6	306.1	270.8	245.8	225.5	219.4	213.4	219.4
65°	310.8	313.9	317.0	288.6	249.7	220.8	201.6	186.2	181.9	177.6	181.9
67.5°	257.2	258.8	260.4	237.1	205.4	182.0	167.0	154.7	150.6	146.5	150.6
70°	226.2	226.8	227.4	206.7	179.0	158.3	144.8	133.8	130.7	127.6	130.7
72.5°	198.4	197.5	196.7	178.2	153.9	136.2	125.1	116.3	114.2	112.1	114.2
75°	156.8	154.9	153.1	137.8	118.1	104.5	97.1	91.3	90.0	88.8	90.0
77.5°	117.1	115.1	113.2	100.5	84.2	74.8	72.3	70.5	70.5	70.5	70.5
80°	91.6	89.1	86.6	76.8	64.4	58.3	58.3	58.3	58.3	58.3	58.3
82.5°	68.3	64.8	61.4	55.3	48.4	45.0	45.0	44.8	44.3	43.8	44.3
85°	33.3	30.2	27.1	26.4	26.4	24.5	20.8	17.6	15.7	13.9	15.7
87.5°	10.0	11.6	13.5	13.2	11.9	11.1	11.1	11.5	11.8	11.8	11.8
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1
2.5°	1358.1	1357.4	1356.9	1360.1	1367.0	1370.4	1363.0	1355.6	1363.0	1370.4	1367.0
5°	1366.8	1364.3	1363.1	1365.9	1372.7	1375.1	1364.7	1354.2	1364.7	1375.1	1372.7
7.5°	1389.8	1385.1	1381.5	1381.4	1384.9	1383.7	1368.8	1353.9	1368.8	1383.7	1384.9
10°	1391.0	1388.4	1387.8	1388.7	1391.2	1388.5	1370.7	1352.8	1370.7	1388.5	1391.2
12.5°	1370.0	1369.5	1370.4	1375.8	1385.6	1387.8	1367.0	1346.1	1367.0	1387.8	1385.6
15°	1338.3	1336.1	1334.3	1344.2	1365.7	1375.8	1351.1	1326.4	1351.1	1375.8	1365.7
17.5°	1319.9	1313.4	1306.7	1313.7	1334.3	1343.3	1317.5	1291.7	1317.5	1343.3	1334.3
20°	1311.0	1301.9	1293.3	1297.3	1313.9	1320.1	1294.8	1269.5	1294.8	1320.1	1313.9
22.5°	1306.4	1293.8	1281.7	1282.5	1296.2	1300.1	1274.8	1249.6	1274.8	1300.1	1296.2
25°	1305.5	1286.2	1265.8	1259.1	1265.8	1265.4	1243.2	1221.0	1243.2	1265.4	1265.8
27.5°	1301.2	1277.8	1250.3	1232.9	1225.8	1217.2	1204.1	1191.0	1204.1	1217.2	1225.8
30°	1281.7	1262.6	1238.5	1217.3	1198.8	1182.7	1174.1	1165.5	1174.1	1182.7	1198.8
32.5°	1240.4	1232.3	1219.6	1199.0	1170.7	1148.1	1142.9	1137.7	1142.9	1148.1	1170.7
35°	1159.8	1170.1	1180.0	1166.4	1129.4	1100.6	1096.3	1091.9	1096.3	1100.6	1129.4
37.5°	1053.1	1078.1	1106.9	1107.2	1078.8	1055.3	1046.4	1037.6	1046.4	1055.3	1078.8
40°	966.0	1002.2	1045.4	1058.9	1042.9	1027.2	1012.4	997.6	1012.4	1027.2	1042.9
42.5°	866.3	912.3	967.3	996.4	999.6	996.1	972.4	948.8	972.4	996.1	999.6
45°	724.6	774.7	834.5	882.0	917.1	935.5	903.4	871.3	903.4	935.5	917.1
47.5°	600.6	645.5	698.9	754.2	811.3	845.9	813.0	780.0	813.0	845.9	811.3
50°	524.6	567.5	617.4	672.9	734.0	773.1	746.6	720.1	746.6	773.1	734.0
52.5°	454.1	496.4	546.4	600.4	658.5	697.3	678.2	659.0	678.2	697.3	658.5
55°	361.5	400.5	448.0	497.3	548.5	584.4	574.6	564.7	574.6	584.4	548.5
57.5°	292.2	324.9	365.3	409.2	456.7	490.7	484.4	478.1	484.4	490.7	456.7
60°	256.1	281.7	313.1	352.6	400.1	434.6	430.3	426.0	430.3	434.6	400.1
62.5°	225.5	245.8	270.8	306.1	351.6	384.9	381.6	378.2	381.6	384.9	351.6
65°	186.2	201.6	220.8	249.7	288.6	317.0	313.9	310.8	313.9	317.0	288.6
67.5°	154.7	167.0	182.0	205.4	237.1	260.4	258.8	257.2	258.8	260.4	237.1
70°	133.8	144.8	158.3	179.0	206.7	227.4	226.8	226.2	226.8	227.4	206.7
72.5°	116.3	125.1	136.2	153.9	178.2	196.7	197.5	198.4	197.5	196.7	178.2
75°	91.3	97.1	104.5	118.1	137.8	153.1	154.9	156.8	154.9	153.1	137.8
77.5°	70.5	72.3	74.8	84.2	100.5	113.2	115.1	117.1	115.1	113.2	100.5
80°	58.3	58.3	58.3	64.4	76.8	86.6	89.1	91.6	89.1	86.6	76.8
82.5°	44.8	45.0	45.0	48.4	55.3	61.4	64.8	68.3	64.8	61.4	55.3
85°	17.6	20.8	24.5	26.4	26.4	27.1	30.2	33.3	30.2	27.1	26.4
87.5°	11.5	11.1	11.1	11.9	13.2	13.5	11.6	10.0	11.6	13.1	14.0
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1	1361.1
2.5°	1360.1	1356.9	1357.4	1358.1	1359.6	1361.1	1359.6	1358.1	1357.4	1356.9	1360.1
5°	1365.9	1363.1	1364.3	1366.8	1373.0	1379.1	1373.0	1366.8	1364.3	1363.1	1365.9
7.5°	1381.4	1381.5	1385.1	1389.8	1397.9	1406.1	1397.9	1389.8	1385.1	1381.5	1381.4
10°	1388.7	1387.8	1388.4	1391.0	1399.6	1408.3	1399.6	1391.0	1388.4	1387.8	1388.7
12.5°	1375.8	1370.4	1369.5	1370.0	1374.7	1379.4	1374.7	1370.0	1369.5	1370.4	1375.8
15°	1344.2	1334.3	1336.1	1338.3	1341.4	1344.5	1341.4	1338.3	1336.1	1334.3	1344.2
17.5°	1313.7	1306.7	1313.4	1319.9	1325.9	1332.0	1325.9	1319.9	1313.4	1306.7	1313.7
20°	1297.3	1293.3	1301.9	1311.0	1321.5	1332.0	1321.5	1311.0	1301.9	1293.3	1297.3
22.5°	1282.5	1281.7	1293.8	1306.4	1320.9	1335.3	1320.9	1306.4	1293.8	1281.7	1282.5
25°	1259.1	1265.8	1286.2	1305.5	1321.5	1337.5	1321.5	1305.5	1286.2	1265.8	1259.1
27.5°	1232.9	1250.3	1277.8	1301.2	1312.4	1323.6	1312.4	1301.2	1277.8	1250.3	1232.9
30°	1217.3	1238.5	1262.6	1281.7	1286.0	1290.3	1286.0	1281.7	1262.6	1238.5	1217.3
32.5°	1199.0	1219.6	1232.3	1240.4	1234.8	1229.3	1234.8	1240.4	1232.3	1219.6	1199.0
35°	1166.4	1180.0	1170.1	1159.8	1148.1	1136.3	1148.1	1159.8	1170.1	1180.0	1166.4
37.5°	1107.2	1106.9	1078.1	1053.1	1039.6	1026.2	1039.6	1053.1	1078.1	1106.9	1107.2
40°	1058.9	1045.4	1002.2	966.0	950.6	935.2	950.6	966.0	1002.2	1045.4	1058.9
42.5°	996.4	967.3	912.3	866.3	847.5	828.6	847.5	866.3	912.3	967.3	996.4
45°	882.0	834.5	774.7	724.6	703.6	682.6	703.6	724.6	774.7	834.5	882.0
47.5°	754.2	698.9	645.5	600.6	581.0	561.4	581.0	600.6	645.5	698.9	754.2
50°	672.9	617.4	567.5	524.6	503.0	481.5	503.0	524.6	567.5	617.4	672.9
52.5°	600.4	546.4	496.4	454.1	434.5	414.9	434.5	454.1	496.4	546.4	600.4
55°	497.3	448.0	400.5	361.5	347.9	334.4	347.9	361.5	400.5	448.0	497.3
57.5°	409.2	365.3	324.9	292.2	282.2	272.2	282.2	292.2	324.9	365.3	409.2
60°	352.6	313.1	281.7	256.1	248.0	240.0	248.0	256.1	281.7	313.1	352.6
62.5°	306.1	270.8	245.8	225.5	219.4	213.4	219.4	225.5	245.8	270.8	306.1
65°	249.7	220.8	201.6	186.2	181.9	177.6	181.9	186.2	201.6	220.8	249.7
67.5°	205.4	182.0	167.0	154.7	150.6	146.5	150.6	154.7	167.0	182.0	205.4
70°	179.0	158.3	144.8	133.8	130.7	127.6	130.7	133.8	144.8	158.3	179.0
72.5°	153.9	136.2	125.1	116.3	114.2	112.1	114.2	116.3	125.1	136.2	153.9
75°	118.1	104.5	97.1	91.3	90.0	88.8	90.0	91.3	97.1	104.5	118.1
77.5°	84.2	74.8	72.3	70.5	70.5	70.5	70.5	70.5	72.3	74.8	84.2
80°	64.4	58.3	58.3	58.3	58.3	58.3	58.3	58.3	58.3	58.3	64.4
82.5°	48.4	45.0	45.0	44.8	44.3	43.8	44.3	44.8	45.0	45.0	48.4
85°	26.4	24.5	20.8	17.6	15.7	13.9	15.7	17.6	20.8	24.5	26.4
87.5°	13.5	14.9	17.6	19.2	20.7	20.0	20.7	19.2	17.6	14.9	13.5
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	128.8	112.2	89.4	
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	234.1	207.0	179.9	
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	344.0	313.8	277.4	
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	412.1	377.3	342.4	
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	478.6	440.7	395.1	
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	570.7	530.1	481.7	
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	655.8	618.3	568.4	
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	717.8	677.1	636.5	



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1361.1	1361.1	1361.1	1361.1
2.5°	1367.0	1370.4	1363.0	1355.6
5°	1372.7	1375.1	1364.7	1354.2
7.5°	1384.9	1383.7	1368.8	1353.9
10°	1391.2	1388.5	1370.7	1352.8
12.5°	1385.6	1387.8	1367.0	1346.1
15°	1365.7	1375.8	1351.1	1326.4
17.5°	1334.3	1343.3	1317.5	1291.7
20°	1313.9	1320.1	1294.8	1269.5
22.5°	1296.2	1300.1	1274.8	1249.6
25°	1265.8	1265.4	1243.2	1221.0
27.5°	1225.8	1217.2	1204.1	1191.0
30°	1198.8	1182.7	1174.1	1165.5
32.5°	1170.7	1148.1	1142.9	1137.7
35°	1129.4	1100.6	1096.3	1091.9
37.5°	1078.8	1055.3	1046.4	1037.6
40°	1042.9	1027.2	1012.4	997.6
42.5°	999.6	996.1	972.4	948.8
45°	917.1	935.5	903.4	871.3
47.5°	811.3	845.9	813.0	780.0
50°	734.0	773.1	746.6	720.1
52.5°	658.5	697.3	678.2	659.0
55°	548.5	584.4	574.6	564.7
57.5°	456.7	490.7	484.4	478.1
60°	400.1	434.6	430.3	426.0
62.5°	351.6	384.9	381.6	378.2
65°	288.6	317.0	313.9	310.8
67.5°	237.1	260.4	258.8	257.2
70°	206.7	227.4	226.8	226.2
72.5°	178.2	196.7	197.5	198.4
75°	137.8	153.1	154.9	156.8
77.5°	100.5	113.2	115.1	117.1
80°	76.8	86.6	89.1	91.6
82.5°	55.3	61.4	64.8	68.3
85°	26.4	27.1	30.2	33.3
87.5°	14.0	13.1	11.6	10.0
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1428308

CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428308  
 CATALOG NUMBER: SQ2W-PR1-K-150U-075D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.05	16.78	17.12	17.84	19.29	12.42	13.15	13.49	14.21	15.66
	3H	17.25	17.90	18.32	18.97	20.44	13.57	14.22	14.65	15.29	16.76
	4H	17.72	18.34	18.81	19.42	20.89	14.03	14.64	15.12	15.72	17.19
	6H	18.02	18.58	19.11	19.66	21.15	14.36	14.93	15.46	16.01	17.49
	8H	18.11	18.65	19.22	19.75	21.23	14.50	15.03	15.60	16.13	17.61
	12H	18.15	18.66	19.26	19.75	21.25	14.52	15.03	15.63	16.12	17.62
4H	2H	16.14	16.75	17.23	17.83	19.30	13.11	13.73	14.21	14.80	16.28
	3H	17.58	18.10	18.69	19.20	20.68	14.46	14.97	15.56	16.07	17.56
	4H	18.21	18.68	19.31	19.77	21.28	15.00	15.47	16.10	16.56	18.07
	6H	18.63	19.03	19.75	20.15	21.65	15.42	15.82	16.54	16.94	18.44
	8H	18.79	19.16	19.90	20.27	21.79	15.60	15.98	16.72	17.09	18.60
	12H	18.85	19.19	19.98	20.31	21.83	15.64	15.98	16.78	17.10	18.62
8H	4H	18.22	18.60	19.34	19.71	21.22	15.31	15.69	16.43	16.80	18.31
	6H	18.75	19.06	19.89	20.21	21.72	15.85	16.16	16.99	17.31	18.82
	8H	18.99	19.26	20.13	20.39	21.92	16.11	16.38	17.25	17.51	19.05
	12H	19.10	19.34	20.24	20.46	22.03	16.20	16.44	17.34	17.57	19.14
12H	4H	18.18	18.52	19.31	19.64	21.16	15.33	15.67	16.46	16.79	18.31
	6H	18.74	19.01	19.88	20.14	21.68	15.92	16.19	17.06	17.32	18.86
	8H	18.99	19.22	20.13	20.35	21.92	16.21	16.44	17.35	17.57	19.14