

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428338

Luminaire Tested: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428338
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4346.4 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87	
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	82	79	76	74			74	
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64			64	
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56	
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49			49	
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44	
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	46	41	39			39	
8	64	52	44	38	63	51	43	38	50	43	38	48	42	37	47	42	37	35			35	
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32	
10	57	44	37	32	55	44	36	31	43	36	31	42	36	31	41	35	31	29			29	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31624	31624	31624	31624
5°	31413	31957	31413	31957
10°	31471	32235	31471	32235
15°	31463	32429	31463	32429
20°	31475	31797	31475	31797
25°	31306	29544	31306	29544
30°	31091	26710	31091	26710
35°	30848	24121	30848	24121
40°	30236	21310	30236	21310
45°	29051	18614	29051	18614
50°	27037	15932	27037	15932
55°	24732	12918	24732	12918
60°	22168	11144	22168	11144
65°	19385	9906	19385	9906
70°	15852	8983	15852	8983
75°	12333	8259	12333	8259
80°	9196	7280	9196	7280
85°	6224	4150	6224	4150

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29051 cd/sqm

TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.5	4.3
10°-20°	540.4	12.4
20°-30°	795.3	18.3
30°-40°	869.6	20.0
40°-50°	780.1	17.9
50°-60°	581.9	13.4
60°-70°	367.8	8.5
70°-80°	182.2	4.2
80°-90°	42.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1522.2	35.0
0°-40°	2391.8	55.0
0°-60°	3753.7	86.4
0°-90°	4346.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4346.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1959	1959	1959	1959	1959	
5°	1938	1972	1938	1972	1938	184
15°	1882	1940	1882	1940	1882	531
25°	1757	1658	1757	1658	1757	809
35°	1565	1224	1565	1224	1565	976
45°	1272	815	1272	815	1272	976
55°	879	459	879	459	879	785
65°	507	259	507	259	507	503
75°	198	132	198	132	198	218
85°	34	22	34	22	34	44
90°	0	0	0	0	0	



TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7
2.5°	1945.3	1956.6	1967.9	1965.2	1957.9	1954.6	1955.3	1956.3	1958.3	1960.2	1958.3
5°	1938.2	1952.3	1966.4	1964.3	1956.9	1953.6	1954.4	1956.9	1964.3	1971.8	1964.3
7.5°	1928.5	1942.8	1957.0	1956.4	1950.7	1949.3	1952.2	1956.1	1963.4	1970.7	1963.4
10°	1919.6	1934.5	1949.4	1949.4	1944.4	1944.0	1948.2	1952.9	1959.6	1966.2	1959.6
12.5°	1907.6	1923.2	1938.8	1940.0	1936.3	1936.9	1941.7	1947.0	1953.6	1960.2	1953.6
15°	1882.3	1898.8	1915.4	1919.0	1918.1	1920.6	1926.4	1931.8	1935.9	1940.1	1935.9
17.5°	1852.8	1869.4	1886.0	1889.2	1888.1	1888.2	1889.7	1891.3	1893.3	1895.3	1893.3
20°	1831.9	1848.5	1865.1	1867.3	1864.9	1860.7	1854.9	1850.6	1850.6	1850.6	1850.6
22.5°	1802.0	1820.0	1837.9	1838.0	1832.2	1821.4	1805.7	1792.5	1787.2	1781.9	1787.2
25°	1757.3	1774.7	1792.1	1784.0	1767.4	1743.0	1710.6	1683.3	1670.8	1658.4	1670.8
27.5°	1705.0	1719.1	1733.2	1712.1	1679.3	1639.9	1594.0	1555.2	1538.0	1520.7	1538.0
30°	1667.7	1678.5	1689.3	1655.9	1607.8	1558.5	1507.9	1465.8	1449.3	1432.7	1449.3
32.5°	1628.9	1633.1	1637.2	1593.2	1533.2	1476.9	1424.4	1380.5	1362.5	1344.6	1362.5
35°	1565.1	1557.7	1550.2	1491.8	1416.3	1352.1	1299.0	1255.3	1239.5	1223.8	1239.5
37.5°	1489.8	1467.5	1445.3	1379.5	1299.0	1231.0	1175.5	1129.5	1112.1	1094.7	1112.1
40°	1434.6	1403.0	1371.5	1300.9	1217.1	1147.5	1091.9	1045.9	1028.5	1011.1	1028.5
42.5°	1373.4	1333.9	1294.4	1221.8	1138.0	1068.4	1012.8	966.6	948.6	930.5	948.6
45°	1272.3	1225.8	1179.4	1103.7	1018.3	948.7	894.8	850.0	832.6	815.2	832.6
47.5°	1158.5	1112.4	1066.3	990.8	905.6	836.9	784.6	741.7	726.8	711.9	726.8
50°	1076.4	1031.6	986.8	914.7	833.5	766.7	714.5	670.7	652.5	634.3	652.5
52.5°	992.8	952.7	912.5	843.1	763.8	697.4	643.8	597.4	572.6	547.7	572.6
55°	878.6	840.5	802.4	736.9	662.2	595.1	535.4	487.1	473.0	458.9	473.0
57.5°	761.1	728.1	695.1	636.3	568.8	507.9	453.7	410.1	398.5	386.9	398.5
60°	686.5	657.5	628.5	572.1	506.6	451.0	405.4	368.3	356.7	345.1	356.7
62.5°	614.9	589.2	563.5	509.4	445.9	396.0	359.7	330.0	320.4	310.8	320.4
65°	507.4	488.3	469.3	424.7	371.6	330.2	300.3	275.9	267.6	259.3	267.6
67.5°	402.9	392.3	381.7	348.3	307.4	273.8	247.6	226.6	221.1	215.6	221.1
70°	335.8	332.5	329.2	301.6	265.9	237.3	215.8	198.6	194.4	190.3	194.4
72.5°	277.6	278.9	280.2	257.3	226.3	202.3	185.4	172.0	169.2	166.4	169.2
75°	197.7	204.4	211.0	195.9	173.5	156.5	144.9	135.8	134.1	132.4	134.1
77.5°	134.7	144.6	154.6	144.8	128.3	115.8	107.2	100.4	99.1	97.8	99.1
80°	98.9	108.8	118.8	111.9	99.5	90.0	83.3	78.3	78.3	78.3	78.3
82.5°	69.0	77.0	84.9	80.1	71.0	64.8	61.4	58.9	58.9	58.9	58.9
85°	33.6	37.7	41.9	40.4	37.1	33.0	28.0	24.0	23.2	22.4	23.2
87.5°	9.0	10.9	12.9	10.9	7.6	5.6	5.0	4.5	4.5	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7
2.5°	1956.3	1955.3	1954.6	1957.9	1965.2	1967.9	1956.6	1945.3	1956.6	1967.9	1965.2
5°	1956.9	1954.4	1953.6	1956.9	1964.3	1966.4	1952.3	1938.2	1952.3	1966.4	1964.3
7.5°	1956.1	1952.2	1949.3	1950.7	1956.4	1957.0	1942.8	1928.5	1942.8	1957.0	1956.4
10°	1952.9	1948.2	1944.0	1944.4	1949.4	1949.4	1934.5	1919.6	1934.5	1949.4	1949.4
12.5°	1947.0	1941.7	1936.9	1936.3	1940.0	1938.8	1923.2	1907.6	1923.2	1938.8	1940.0
15°	1931.8	1926.4	1920.6	1918.1	1919.0	1915.4	1898.8	1882.3	1898.8	1915.4	1919.0
17.5°	1891.3	1889.7	1888.2	1888.1	1889.2	1886.0	1869.4	1852.8	1869.4	1886.0	1889.2
20°	1850.6	1854.9	1860.7	1864.9	1867.3	1865.1	1848.5	1831.9	1848.5	1865.1	1867.3
22.5°	1792.5	1805.7	1821.4	1832.2	1838.0	1837.9	1820.0	1802.0	1820.0	1837.9	1838.0
25°	1683.3	1710.6	1743.0	1767.4	1784.0	1792.1	1774.7	1757.3	1774.7	1792.1	1784.0
27.5°	1555.2	1594.0	1639.9	1679.3	1712.1	1733.2	1719.1	1705.0	1719.1	1733.2	1712.1
30°	1465.8	1507.9	1558.5	1607.8	1655.9	1689.3	1678.5	1667.7	1678.5	1689.3	1655.9
32.5°	1380.5	1424.4	1476.9	1533.2	1593.2	1637.2	1633.1	1628.9	1633.1	1637.2	1593.2
35°	1255.3	1299.0	1352.1	1416.3	1491.8	1550.2	1557.7	1565.1	1557.7	1550.2	1491.8
37.5°	1129.5	1175.5	1231.0	1299.0	1379.5	1445.3	1467.5	1489.8	1467.5	1445.3	1379.5
40°	1045.9	1091.9	1147.5	1217.1	1300.9	1371.5	1403.0	1434.6	1403.0	1371.5	1300.9
42.5°	966.6	1012.8	1068.4	1138.0	1221.8	1294.4	1333.9	1373.4	1333.9	1294.4	1221.8
45°	850.0	894.8	948.7	1018.3	1103.7	1179.4	1225.8	1272.3	1225.8	1179.4	1103.7
47.5°	741.7	784.6	836.9	905.6	990.8	1066.3	1112.4	1158.5	1112.4	1066.3	990.8
50°	670.7	714.5	766.7	833.5	914.7	986.8	1031.6	1076.4	1031.6	986.8	914.7
52.5°	597.4	643.8	697.4	763.8	843.1	912.5	952.7	992.8	952.7	912.5	843.1
55°	487.1	535.4	595.1	662.2	736.9	802.4	840.5	878.6	840.5	802.4	736.9
57.5°	410.1	453.7	507.9	568.8	636.3	695.1	728.1	761.1	728.1	695.1	636.3
60°	368.3	405.4	451.0	506.6	572.1	628.5	657.5	686.5	657.5	628.5	572.1
62.5°	330.0	359.7	396.0	445.9	509.4	563.5	589.2	614.9	589.2	563.5	509.4
65°	275.9	300.3	330.2	371.6	424.7	469.3	488.3	507.4	488.3	469.3	424.7
67.5°	226.6	247.6	273.8	307.4	348.3	381.7	392.3	402.9	392.3	381.7	348.3
70°	198.6	215.8	237.3	265.9	301.6	329.2	332.5	335.8	332.5	329.2	301.6
72.5°	172.0	185.4	202.3	226.3	257.3	280.2	278.9	277.6	278.9	280.2	257.3
75°	135.8	144.9	156.5	173.5	195.9	211.0	204.4	197.7	204.4	211.0	195.9
77.5°	100.4	107.2	115.8	128.3	144.8	154.6	144.6	134.7	144.6	154.6	144.8
80°	78.3	83.3	90.0	99.5	111.9	118.8	108.8	98.9	108.8	118.8	111.9
82.5°	58.9	61.4	64.8	71.0	80.1	84.9	77.0	69.0	77.0	84.9	80.1
85°	24.0	28.0	33.0	37.1	40.4	41.9	37.7	33.6	37.7	41.9	40.4
87.5°	4.5	5.0	5.6	7.6	10.9	12.9	10.9	9.0	10.9	12.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7
2.5°	1957.9	1954.6	1955.3	1956.3	1958.3	1960.2	1958.3	1956.3	1955.3	1954.6	1957.9
5°	1956.9	1953.6	1954.4	1956.9	1964.3	1971.8	1964.3	1956.9	1954.4	1953.6	1956.9
7.5°	1950.7	1949.3	1952.2	1956.1	1963.4	1970.7	1963.4	1956.1	1952.2	1949.3	1950.7
10°	1944.4	1944.0	1948.2	1952.9	1959.6	1966.2	1959.6	1952.9	1948.2	1944.0	1944.4
12.5°	1936.3	1936.9	1941.7	1947.0	1953.6	1960.2	1953.6	1947.0	1941.7	1936.9	1936.3
15°	1918.1	1920.6	1926.4	1931.8	1935.9	1940.1	1935.9	1931.8	1926.4	1920.6	1918.1
17.5°	1888.1	1888.2	1889.7	1891.3	1893.3	1895.3	1893.3	1891.3	1889.7	1888.2	1888.1
20°	1864.9	1860.7	1854.9	1850.6	1850.6	1850.6	1850.6	1850.6	1854.9	1860.7	1864.9
22.5°	1832.2	1821.4	1805.7	1792.5	1787.2	1781.9	1787.2	1792.5	1805.7	1821.4	1832.2
25°	1767.4	1743.0	1710.6	1683.3	1670.8	1658.4	1670.8	1683.3	1710.6	1743.0	1767.4
27.5°	1679.3	1639.9	1594.0	1555.2	1538.0	1520.7	1538.0	1555.2	1594.0	1639.9	1679.3
30°	1607.8	1558.5	1507.9	1465.8	1449.3	1432.7	1449.3	1465.8	1507.9	1558.5	1607.8
32.5°	1533.2	1476.9	1424.4	1380.5	1362.5	1344.6	1362.5	1380.5	1424.4	1476.9	1533.2
35°	1416.3	1352.1	1299.0	1255.3	1239.5	1223.8	1239.5	1255.3	1299.0	1352.1	1416.3
37.5°	1299.0	1231.0	1175.5	1129.5	1112.1	1094.7	1112.1	1129.5	1175.5	1231.0	1299.0
40°	1217.1	1147.5	1091.9	1045.9	1028.5	1011.1	1028.5	1045.9	1091.9	1147.5	1217.1
42.5°	1138.0	1068.4	1012.8	966.6	948.6	930.5	948.6	966.6	1012.8	1068.4	1138.0
45°	1018.3	948.7	894.8	850.0	832.6	815.2	832.6	850.0	894.8	948.7	1018.3
47.5°	905.6	836.9	784.6	741.7	726.8	711.9	726.8	741.7	784.6	836.9	905.6
50°	833.5	766.7	714.5	670.7	652.5	634.3	652.5	670.7	714.5	766.7	833.5
52.5°	763.8	697.4	643.8	597.4	572.6	547.7	572.6	597.4	643.8	697.4	763.8
55°	662.2	595.1	535.4	487.1	473.0	458.9	473.0	487.1	535.4	595.1	662.2
57.5°	568.8	507.9	453.7	410.1	398.5	386.9	398.5	410.1	453.7	507.9	568.8
60°	506.6	451.0	405.4	368.3	356.7	345.1	356.7	368.3	405.4	451.0	506.6
62.5°	445.9	396.0	359.7	330.0	320.4	310.8	320.4	330.0	359.7	396.0	445.9
65°	371.6	330.2	300.3	275.9	267.6	259.3	267.6	275.9	300.3	330.2	371.6
67.5°	307.4	273.8	247.6	226.6	221.1	215.6	221.1	226.6	247.6	273.8	307.4
70°	265.9	237.3	215.8	198.6	194.4	190.3	194.4	198.6	215.8	237.3	265.9
72.5°	226.3	202.3	185.4	172.0	169.2	166.4	169.2	172.0	185.4	202.3	226.3
75°	173.5	156.5	144.9	135.8	134.1	132.4	134.1	135.8	144.9	156.5	173.5
77.5°	128.3	115.8	107.2	100.4	99.1	97.8	99.1	100.4	107.2	115.8	128.3
80°	99.5	90.0	83.3	78.3	78.3	78.3	78.3	78.3	83.3	90.0	99.5
82.5°	71.0	64.8	61.4	58.9	58.9	58.9	58.9	58.9	61.4	64.8	71.0
85°	37.1	33.0	28.0	24.0	23.2	22.4	23.2	24.0	28.0	33.0	37.1
87.5°	7.6	5.6	5.0	4.5	4.5	4.5	4.5	4.5	5.0	5.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428338

CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1958.7	1958.7	1958.7	1958.7
2.5°	1965.2	1967.9	1956.6	1945.3
5°	1964.3	1966.4	1952.3	1938.2
7.5°	1956.4	1957.0	1942.8	1928.5
10°	1949.4	1949.4	1934.5	1919.6
12.5°	1940.0	1938.8	1923.2	1907.6
15°	1919.0	1915.4	1898.8	1882.3
17.5°	1889.2	1886.0	1869.4	1852.8
20°	1867.3	1865.1	1848.5	1831.9
22.5°	1838.0	1837.9	1820.0	1802.0
25°	1784.0	1792.1	1774.7	1757.3
27.5°	1712.1	1733.2	1719.1	1705.0
30°	1655.9	1689.3	1678.5	1667.7
32.5°	1593.2	1637.2	1633.1	1628.9
35°	1491.8	1550.2	1557.7	1565.1
37.5°	1379.5	1445.3	1467.5	1489.8
40°	1300.9	1371.5	1403.0	1434.6
42.5°	1221.8	1294.4	1333.9	1373.4
45°	1103.7	1179.4	1225.8	1272.3
47.5°	990.8	1066.3	1112.4	1158.5
50°	914.7	986.8	1031.6	1076.4
52.5°	843.1	912.5	952.7	992.8
55°	736.9	802.4	840.5	878.6
57.5°	636.3	695.1	728.1	761.1
60°	572.1	628.5	657.5	686.5
62.5°	509.4	563.5	589.2	614.9
65°	424.7	469.3	488.3	507.4
67.5°	348.3	381.7	392.3	402.9
70°	301.6	329.2	332.5	335.8
72.5°	257.3	280.2	278.9	277.6
75°	195.9	211.0	204.4	197.7
77.5°	144.8	154.6	144.6	134.7
80°	111.9	118.8	108.8	98.9
82.5°	80.1	84.9	77.0	69.0
85°	40.4	41.9	37.7	33.6
87.5°	10.9	12.9	10.9	9.0
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428338
 CATALOG NUMBER: SQ2W-PW1-0U-100D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.84	24.34	23.20	24.65	24.97	19.08	20.59	19.45	20.90	21.21
	3H	24.18	25.53	24.56	25.86	26.22	20.40	21.74	20.78	22.07	22.43
	4H	24.62	25.88	25.02	26.23	26.61	20.93	22.19	21.33	22.54	22.92
	6H	24.83	25.99	25.24	26.36	26.75	21.27	22.44	21.68	22.80	23.19
	8H	24.89	26.00	25.32	26.39	26.79	21.40	22.51	21.83	22.90	23.30
	12H	24.91	25.97	25.34	26.35	26.78	21.45	22.51	21.88	22.89	23.32
4H	2H	23.04	24.30	23.44	24.65	25.03	19.97	21.23	20.37	21.58	21.96
	3H	24.64	25.68	25.05	26.08	26.48	21.47	22.51	21.88	22.91	23.31
	4H	25.21	26.14	25.64	26.56	27.00	22.07	23.01	22.50	23.43	23.86
	6H	25.55	26.36	26.01	26.81	27.27	22.49	23.30	22.95	23.75	24.21
	8H	25.65	26.41	26.12	26.86	27.33	22.65	23.41	23.11	23.86	24.32
	12H	25.70	26.38	26.18	26.86	27.33	22.72	23.40	23.20	23.88	24.35
8H	4H	25.29	26.05	25.75	26.49	26.96	22.46	23.22	22.92	23.66	24.13
	6H	25.73	26.36	26.23	26.85	27.33	22.97	23.60	23.47	24.09	24.57
	8H	25.90	26.47	26.42	26.98	27.47	23.19	23.76	23.71	24.27	24.76
	12H	26.01	26.51	26.52	27.00	27.56	23.30	23.80	23.81	24.29	24.86
12H	4H	25.28	25.95	25.76	26.43	26.90	22.50	23.18	22.99	23.66	24.13
	6H	25.73	26.29	26.24	26.80	27.29	23.05	23.61	23.56	24.12	24.61
	8H	25.94	26.44	26.45	26.93	27.50	23.32	23.82	23.83	24.31	24.88