

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428350

Luminaire Tested: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428350
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3173.2 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71				71
1	103	99	95	92	98	94	91	88	84	82	80	76	74	72	68	66	65	61				61
2	95	88	82	77	89	83	78	73	75	71	67	68	64	62	61	58	56	53				53
3	87	78	71	65	82	74	68	62	67	62	58	60	56	53	54	51	49	45				45
4	80	69	62	56	76	66	59	54	60	54	50	54	50	46	49	46	43	40				40
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35				35
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	33	31				31
7	63	51	43	38	60	49	42	37	45	39	34	41	36	32	37	33	30	28				28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25				25
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25	23				23
10	52	40	32	28	49	38	31	27	35	29	25	32	27	24	30	26	23	21				21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16305	16305	16305	16305
5°	16196	16476	16196	16476
10°	16226	16619	16226	16619
15°	16222	16720	16222	16720
20°	16228	16393	16228	16393
25°	16140	15232	16140	15232
30°	16031	13772	16031	13772
35°	15906	12435	15906	12435
40°	15588	10987	15588	10987
45°	14979	9597	14979	9597
50°	13940	8214	13940	8214
55°	12751	6660	12751	6660
60°	11428	5745	11428	5745
65°	9994	5108	9994	5108
70°	8171	4631	8171	4631
75°	6363	4261	6363	4261
80°	4742	3756	4742	3756
85°	3205	2130	3205	2130

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14979 cd/sqm



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	3.0
10°-20°	278.6	8.8
20°-30°	410.0	12.9
30°-40°	448.3	14.1
40°-50°	402.2	12.7
50°-60°	300.0	9.5
60°-70°	189.6	6.0
70°-80°	93.9	3.0
80°-90°	23.3	0.7
90°-100°	25.4	0.8
100°-110°	74.0	2.3
110°-120°	120.8	3.8
120°-130°	153.3	4.8
130°-140°	164.0	5.2
140°-150°	153.1	4.8
150°-160°	126.0	4.0
160°-170°	84.5	2.7
170°-180°	30.0	0.9
0°-30°	784.8	24.7
0°-40°	1233.2	38.9
0°-60°	1935.4	61.0
0°-90°	2242.2	70.7
90°-120°	220.2	6.9
90°-150°	690.5	21.8
90°-180°	931.0	29.3
0°-180°	3173.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1010	1010	1010	1010	1010	
5°	999	1017	999	1017	999	95
15°	970	1000	970	1000	970	274
25°	906	855	906	855	906	417
35°	807	631	807	631	807	503
45°	656	420	656	420	656	503
55°	453	237	453	237	453	405
65°	262	134	262	134	262	259
75°	102	68	102	68	102	112
85°	17	12	17	12	17	22
90°	1	7	1	14	1	1
95°	10	7	10	44	10	12
105°	47	75	47	104	47	50
115°	90	125	90	154	90	89
125°	133	198	133	189	133	119
135°	181	259	181	209	181	140
145°	232	299	232	214	232	145
155°	275	325	275	222	275	126
165°	304	338	304	255	304	86
175°	318	331	318	299	318	30
180°	319	319	319	319	319	



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9
2.5°	1003.0	1008.8	1014.6	1013.2	1009.5	1007.8	1008.1	1008.6	1009.6	1010.7	1009.6
5°	999.3	1006.6	1013.9	1012.8	1008.9	1007.2	1007.7	1008.9	1012.8	1016.6	1012.8
7.5°	994.3	1001.7	1009.0	1008.7	1005.8	1005.0	1006.5	1008.5	1012.3	1016.1	1012.3
10°	989.7	997.4	1005.1	1005.1	1002.5	1002.3	1004.4	1006.9	1010.3	1013.7	1010.3
12.5°	983.5	991.6	999.6	1000.2	998.3	998.6	1001.1	1003.8	1007.2	1010.7	1007.2
15°	970.5	979.0	987.6	989.4	989.0	990.2	993.2	996.0	998.1	1000.3	998.1
17.5°	955.3	963.8	972.4	974.1	973.5	973.5	974.3	975.1	976.2	977.2	976.2
20°	944.5	953.0	961.6	962.8	961.5	959.4	956.4	954.1	954.1	954.1	954.1
22.5°	929.1	938.3	947.6	947.6	944.6	939.1	931.0	924.2	921.5	918.7	921.5
25°	906.0	915.0	924.0	919.8	911.3	898.6	882.0	867.9	861.5	855.0	861.5
27.5°	879.1	886.4	893.6	882.7	865.8	845.5	821.8	801.8	793.0	784.1	793.0
30°	859.9	865.4	871.0	853.8	829.0	803.5	777.5	755.8	747.2	738.7	747.2
32.5°	839.9	842.0	844.1	821.4	790.5	761.5	734.4	711.7	702.5	693.3	702.5
35°	807.0	803.1	799.3	769.1	730.2	697.1	669.7	647.2	639.1	630.9	639.1
37.5°	768.1	756.6	745.2	711.2	669.8	634.7	606.1	582.3	573.4	564.4	573.4
40°	739.6	723.4	707.1	670.7	627.5	591.6	563.0	539.3	530.3	521.3	530.3
42.5°	708.1	687.7	667.4	629.9	586.7	550.8	522.2	498.4	489.1	479.8	489.1
45°	656.0	632.0	608.1	569.1	525.0	489.1	461.3	438.3	429.3	420.3	429.3
47.5°	597.3	573.5	549.7	510.8	466.9	431.5	404.5	382.4	374.7	367.0	374.7
50°	555.0	531.9	508.8	471.6	429.7	395.3	368.4	345.8	336.4	327.0	336.4
52.5°	511.9	491.2	470.5	434.7	393.8	359.6	332.0	308.0	295.2	282.4	295.2
55°	453.0	433.3	413.7	379.9	341.4	306.8	276.0	251.1	243.9	236.6	243.9
57.5°	392.4	375.4	358.4	328.0	293.2	261.9	233.9	211.4	205.5	199.5	205.5
60°	353.9	339.0	324.0	295.0	261.2	232.5	209.0	189.9	183.9	177.9	183.9
62.5°	317.0	303.8	290.5	262.6	229.9	204.2	185.4	170.2	165.2	160.2	165.2
65°	261.6	251.8	241.9	219.0	191.6	170.2	154.9	142.2	138.0	133.7	138.0
67.5°	207.8	202.3	196.8	179.6	158.5	141.2	127.7	116.8	114.0	111.2	114.0
70°	173.1	171.4	169.7	155.5	137.1	122.4	111.2	102.4	100.2	98.1	100.2
72.5°	143.1	143.8	144.5	132.7	116.7	104.3	95.6	88.7	87.2	85.8	87.2
75°	102.0	105.4	108.8	101.0	89.4	80.7	74.7	70.0	69.1	68.3	69.1
77.5°	69.4	74.6	79.7	74.6	66.2	59.7	55.3	51.8	51.1	50.4	51.1
80°	51.0	56.1	61.2	57.7	51.3	46.4	43.0	40.4	40.4	40.4	40.4
82.5°	35.6	39.7	43.8	41.3	36.6	33.4	31.7	30.4	30.4	30.4	30.4
85°	17.3	19.4	21.6	20.8	19.1	17.0	14.4	12.4	12.0	11.5	12.0
87.5°	4.8	6.1	7.4	6.7	5.2	4.2	3.9	3.7	3.7	3.7	3.7
90°	1.0	2.3	3.9	5.2	6.1	6.4	6.4	6.8	7.1	7.1	7.1
92.5°	3.5	5.6	5.7	5.7	6.9	7.5	8.0	8.1	8.4	8.4	8.4
95°	10.0	11.0	16.4	16.1	11.0	8.7	7.4	7.4	7.4	7.4	7.4
97.5°	19.1	20.5	21.4	28.7	30.3	29.2	23.8	20.0	17.9	16.9	17.9
100°	27.1	27.7	29.6	30.0	38.0	45.7	41.9	37.0	35.4	34.5	35.4
102.5°	35.0	35.4	38.4	39.7	41.6	46.0	59.4	57.9	56.8	56.6	56.8
105°	47.0	47.3	52.8	55.4	56.7	56.7	56.4	62.8	73.1	75.4	73.1
107.5°	59.8	61.3	67.8	74.7	76.1	76.5	74.9	73.9	73.5	73.8	73.5
110°	68.6	70.9	78.6	87.3	89.5	90.2	89.5	88.6	87.9	87.9	87.9



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	77.1	80.4	89.2	99.1	102.9	104.9	103.5	102.7	102.1	102.6	102.1
115°	90.2	95.0	106.6	116.9	124.6	125.6	125.3	125.3	125.0	125.0	125.0
117.5°	102.3	110.0	123.0	135.0	144.0	146.5	147.8	147.5	147.1	147.7	147.1
120°	110.8	119.8	134.6	148.2	156.9	160.7	162.0	161.4	162.0	161.4	162.0
122.5°	119.8	130.9	145.5	159.5	169.7	174.1	175.7	175.8	175.9	175.5	175.9
125°	133.3	146.9	163.9	178.4	189.1	194.2	195.5	195.8	196.5	198.1	196.5
127.5°	147.0	162.3	181.1	195.1	205.9	212.2	214.2	214.9	216.2	217.0	216.2
130°	156.5	173.9	192.9	206.1	216.8	223.5	227.1	228.0	229.6	229.3	229.6
132.5°	166.6	184.7	204.0	217.7	227.6	234.9	237.9	240.7	241.2	241.7	241.2
135°	181.3	201.0	220.3	233.8	243.2	250.3	254.1	256.7	258.3	259.3	258.3
137.5°	196.9	217.6	236.2	248.2	257.6	263.7	268.1	270.8	272.5	273.3	272.5
140°	207.4	227.4	245.4	258.0	266.4	272.5	276.3	279.6	281.5	281.5	281.5
142.5°	217.5	237.2	254.7	267.3	274.6	280.2	284.3	286.8	289.0	289.0	289.0
145°	231.6	251.2	267.3	279.9	286.0	291.2	295.7	297.6	298.9	298.9	298.9
147.5°	246.3	263.7	278.4	290.5	295.6	301.7	305.2	306.8	308.4	307.7	308.4
150°	255.1	271.2	285.4	296.6	301.8	307.6	311.1	312.4	314.0	313.1	314.0
152.5°	263.6	278.9	291.8	302.3	306.7	312.5	316.5	317.8	318.9	318.2	318.9
155°	275.1	288.6	300.5	310.2	314.0	319.5	323.4	325.0	326.3	324.7	326.3
157.5°	285.3	297.0	307.3	316.2	320.3	325.0	328.7	330.7	331.9	331.2	331.9
160°	291.5	302.1	311.5	319.8	323.7	327.9	331.7	334.0	335.3	334.3	335.3
162.5°	296.6	306.2	315.1	322.7	326.0	329.7	334.3	336.3	337.6	336.4	337.6
165°	304.0	311.8	319.5	326.0	328.8	331.7	336.6	338.8	339.8	338.5	339.8
167.5°	309.7	315.6	321.8	327.4	329.5	332.3	337.2	339.0	340.3	338.6	340.3
170°	312.7	317.9	323.4	327.9	329.5	332.1	336.9	338.5	339.5	337.9	339.5
172.5°	315.3	319.2	323.6	327.6	328.5	330.5	335.1	336.7	337.4	336.1	337.4
175°	317.9	320.2	323.4	326.0	325.6	326.9	330.8	332.1	333.4	331.4	333.4
177.5°	319.1	320.2	321.2	322.7	321.7	321.7	324.5	325.3	325.6	324.5	325.6
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9
2.5°	1008.6	1008.1	1007.8	1009.5	1013.2	1014.6	1008.8	1003.0	1008.8	1014.6	1013.2
5°	1008.9	1007.7	1007.2	1008.9	1012.8	1013.9	1006.6	999.3	1006.6	1013.9	1012.8
7.5°	1008.5	1006.5	1005.0	1005.8	1008.7	1009.0	1001.7	994.3	1001.7	1009.0	1008.7
10°	1006.9	1004.4	1002.3	1002.5	1005.1	1005.1	997.4	989.7	997.4	1005.1	1005.1
12.5°	1003.8	1001.1	998.6	998.3	1000.2	999.6	991.6	983.5	991.6	999.6	1000.2
15°	996.0	993.2	990.2	989.0	989.4	987.6	979.0	970.5	979.0	987.6	989.4
17.5°	975.1	974.3	973.5	973.5	974.1	972.4	963.8	955.3	963.8	972.4	974.1
20°	954.1	956.4	959.4	961.5	962.8	961.6	953.0	944.5	953.0	961.6	962.8
22.5°	924.2	931.0	939.1	944.6	947.6	947.6	938.3	929.1	938.3	947.6	947.6
25°	867.9	882.0	898.6	911.3	919.8	924.0	915.0	906.0	915.0	924.0	919.8
27.5°	801.8	821.8	845.5	865.8	882.7	893.6	886.4	879.1	886.4	893.6	882.7
30°	755.8	777.5	803.5	829.0	853.8	871.0	865.4	859.9	865.4	871.0	853.8
32.5°	711.7	734.4	761.5	790.5	821.4	844.1	842.0	839.9	842.0	844.1	821.4
35°	647.2	669.7	697.1	730.2	769.1	799.3	803.1	807.0	803.1	799.3	769.1
37.5°	582.3	606.1	634.7	669.8	711.2	745.2	756.6	768.1	756.6	745.2	711.2
40°	539.3	563.0	591.6	627.5	670.7	707.1	723.4	739.6	723.4	707.1	670.7
42.5°	498.4	522.2	550.8	586.7	629.9	667.4	687.7	708.1	687.7	667.4	629.9
45°	438.3	461.3	489.1	525.0	569.1	608.1	632.0	656.0	632.0	608.1	569.1
47.5°	382.4	404.5	431.5	466.9	510.8	549.7	573.5	597.3	573.5	549.7	510.8
50°	345.8	368.4	395.3	429.7	471.6	508.8	531.9	555.0	531.9	508.8	471.6
52.5°	308.0	332.0	359.6	393.8	434.7	470.5	491.2	511.9	491.2	470.5	434.7
55°	251.1	276.0	306.8	341.4	379.9	413.7	433.3	453.0	433.3	413.7	379.9
57.5°	211.4	233.9	261.9	293.2	328.0	358.4	375.4	392.4	375.4	358.4	328.0
60°	189.9	209.0	232.5	261.2	295.0	324.0	339.0	353.9	339.0	324.0	295.0
62.5°	170.2	185.4	204.2	229.9	262.6	290.5	303.8	317.0	303.8	290.5	262.6
65°	142.2	154.9	170.2	191.6	219.0	241.9	251.8	261.6	251.8	241.9	219.0
67.5°	116.8	127.7	141.2	158.5	179.6	196.8	202.3	207.8	202.3	196.8	179.6
70°	102.4	111.2	122.4	137.1	155.5	169.7	171.4	173.1	171.4	169.7	155.5
72.5°	88.7	95.6	104.3	116.7	132.7	144.5	143.8	143.1	143.8	144.5	132.7
75°	70.0	74.7	80.7	89.4	101.0	108.8	105.4	102.0	105.4	108.8	101.0
77.5°	51.8	55.3	59.7	66.2	74.6	79.7	74.6	69.4	74.6	79.7	74.6
80°	40.4	43.0	46.4	51.3	57.7	61.2	56.1	51.0	56.1	61.2	57.7
82.5°	30.4	31.7	33.4	36.6	41.3	43.8	39.7	35.6	39.7	43.8	41.3
85°	12.4	14.4	17.0	19.1	20.8	21.6	19.4	17.3	19.4	21.6	20.8
87.5°	3.7	3.9	4.2	5.2	6.7	7.4	6.1	4.8	6.1	7.4	6.8
90°	6.8	6.4	6.4	6.1	5.2	3.9	2.3	1.0	2.3	3.5	5.8
92.5°	8.1	8.0	7.5	6.9	5.7	5.7	5.6	3.5	6.1	8.7	12.5
95°	7.4	7.4	8.7	11.0	16.1	16.4	11.0	10.0	14.2	20.0	25.1
97.5°	20.0	23.8	29.2	30.3	28.7	21.4	20.5	19.1	26.0	31.7	40.0
100°	37.0	41.9	45.7	38.0	30.0	29.6	27.7	27.1	34.5	39.9	48.0
102.5°	57.9	59.4	46.0	41.6	39.7	38.4	35.4	35.0	42.5	50.0	56.8
105°	62.8	56.4	56.7	56.7	55.4	52.8	47.3	47.0	55.4	64.1	72.5
107.5°	73.9	74.9	76.5	76.1	74.7	67.8	61.3	59.8	67.4	77.8	87.0
110°	88.6	89.5	90.2	89.5	87.3	78.6	70.9	68.6	75.4	86.3	96.3



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	102.7	103.5	104.9	102.9	99.1	89.2	80.4	77.1	83.9	95.1	105.3
115°	125.3	125.3	125.6	124.6	116.9	106.6	95.0	90.2	96.0	106.3	117.6
117.5°	147.5	147.8	146.5	144.0	135.0	123.0	110.0	102.3	106.9	117.8	129.3
120°	161.4	162.0	160.7	156.9	148.2	134.6	119.8	110.8	114.3	125.0	136.6
122.5°	175.8	175.7	174.1	169.7	159.5	145.5	130.9	119.8	121.3	131.2	142.5
125°	195.8	195.5	194.2	189.1	178.4	163.9	146.9	133.3	131.4	139.8	151.4
127.5°	214.9	214.2	212.2	205.9	195.1	181.1	162.3	147.0	142.7	148.0	158.6
130°	228.0	227.1	223.5	216.8	206.1	192.9	173.9	156.5	150.4	153.6	163.0
132.5°	240.7	237.9	234.9	227.6	217.7	204.0	184.7	166.6	158.1	159.6	166.8
135°	256.7	254.1	250.3	243.2	233.8	220.3	201.0	181.3	169.7	168.5	172.6
137.5°	270.8	268.1	263.7	257.6	248.2	236.2	217.6	196.9	182.2	177.9	179.5
140°	279.6	276.3	272.5	266.4	258.0	245.4	227.4	207.4	191.0	184.9	183.9
142.5°	286.8	284.3	280.2	274.6	267.3	254.7	237.2	217.5	200.0	192.1	189.8
145°	297.6	295.7	291.2	286.0	279.9	267.3	251.2	231.6	214.2	203.9	199.0
147.5°	306.8	305.2	301.7	295.6	290.5	278.4	263.7	246.3	228.5	215.7	209.5
150°	312.4	311.1	307.6	301.8	296.6	285.4	271.2	255.1	238.0	224.5	216.4
152.5°	317.8	316.5	312.5	306.7	302.3	291.8	278.9	263.6	246.3	232.7	224.4
155°	325.0	323.4	319.5	314.0	310.2	300.5	288.6	275.1	260.2	246.1	236.7
157.5°	330.7	328.7	325.0	320.3	316.2	307.3	297.0	285.3	272.4	258.8	249.3
160°	334.0	331.7	327.9	323.7	319.8	311.5	302.1	291.5	279.6	267.3	257.0
162.5°	336.3	334.3	329.7	326.0	322.7	315.1	306.2	296.6	286.0	275.3	265.8
165°	338.8	336.6	331.7	328.8	326.0	319.5	311.8	304.0	295.0	286.3	278.6
167.5°	339.0	337.2	332.3	329.5	327.4	321.8	315.6	309.7	302.6	295.8	289.4
170°	338.5	336.9	332.1	329.5	327.9	323.4	317.9	312.7	307.3	301.5	296.3
172.5°	336.7	335.1	330.5	328.5	327.6	323.6	319.2	315.3	310.6	306.4	302.2
175°	332.1	330.8	326.9	325.6	326.0	323.4	320.2	317.9	315.0	312.4	310.2
177.5°	325.3	324.5	321.7	321.7	322.7	321.2	320.2	319.1	317.8	317.1	316.3
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9	1009.9
2.5°	1009.5	1007.8	1008.1	1008.6	1009.6	1010.7	1009.6	1008.6	1008.1	1007.8	1009.5
5°	1008.9	1007.2	1007.7	1008.9	1012.8	1016.6	1012.8	1008.9	1007.7	1007.2	1008.9
7.5°	1005.8	1005.0	1006.5	1008.5	1012.3	1016.1	1012.3	1008.5	1006.5	1005.0	1005.8
10°	1002.5	1002.3	1004.4	1006.9	1010.3	1013.7	1010.3	1006.9	1004.4	1002.3	1002.5
12.5°	998.3	998.6	1001.1	1003.8	1007.2	1010.7	1007.2	1003.8	1001.1	998.6	998.3
15°	989.0	990.2	993.2	996.0	998.1	1000.3	998.1	996.0	993.2	990.2	989.0
17.5°	973.5	973.5	974.3	975.1	976.2	977.2	976.2	975.1	974.3	973.5	973.5
20°	961.5	959.4	956.4	954.1	954.1	954.1	954.1	954.1	956.4	959.4	961.5
22.5°	944.6	939.1	931.0	924.2	921.5	918.7	921.5	924.2	931.0	939.1	944.6
25°	911.3	898.6	882.0	867.9	861.5	855.0	861.5	867.9	882.0	898.6	911.3
27.5°	865.8	845.5	821.8	801.8	793.0	784.1	793.0	801.8	821.8	845.5	865.8
30°	829.0	803.5	777.5	755.8	747.2	738.7	747.2	755.8	777.5	803.5	829.0
32.5°	790.5	761.5	734.4	711.7	702.5	693.3	702.5	711.7	734.4	761.5	790.5
35°	730.2	697.1	669.7	647.2	639.1	630.9	639.1	647.2	669.7	697.1	730.2
37.5°	669.8	634.7	606.1	582.3	573.4	564.4	573.4	582.3	606.1	634.7	669.8
40°	627.5	591.6	563.0	539.3	530.3	521.3	530.3	539.3	563.0	591.6	627.5
42.5°	586.7	550.8	522.2	498.4	489.1	479.8	489.1	498.4	522.2	550.8	586.7
45°	525.0	489.1	461.3	438.3	429.3	420.3	429.3	438.3	461.3	489.1	525.0
47.5°	466.9	431.5	404.5	382.4	374.7	367.0	374.7	382.4	404.5	431.5	466.9
50°	429.7	395.3	368.4	345.8	336.4	327.0	336.4	345.8	368.4	395.3	429.7
52.5°	393.8	359.6	332.0	308.0	295.2	282.4	295.2	308.0	332.0	359.6	393.8
55°	341.4	306.8	276.0	251.1	243.9	236.6	243.9	251.1	276.0	306.8	341.4
57.5°	293.2	261.9	233.9	211.4	205.5	199.5	205.5	211.4	233.9	261.9	293.2
60°	261.2	232.5	209.0	189.9	183.9	177.9	183.9	189.9	209.0	232.5	261.2
62.5°	229.9	204.2	185.4	170.2	165.2	160.2	165.2	170.2	185.4	204.2	229.9
65°	191.6	170.2	154.9	142.2	138.0	133.7	138.0	142.2	154.9	170.2	191.6
67.5°	158.5	141.2	127.7	116.8	114.0	111.2	114.0	116.8	127.7	141.2	158.5
70°	137.1	122.4	111.2	102.4	100.2	98.1	100.2	102.4	111.2	122.4	137.1
72.5°	116.7	104.3	95.6	88.7	87.2	85.8	87.2	88.7	95.6	104.3	116.7
75°	89.4	80.7	74.7	70.0	69.1	68.3	69.1	70.0	74.7	80.7	89.4
77.5°	66.2	59.7	55.3	51.8	51.1	50.4	51.1	51.8	55.3	59.7	66.2
80°	51.3	46.4	43.0	40.4	40.4	40.4	40.4	40.4	43.0	46.4	51.3
82.5°	36.6	33.4	31.7	30.4	30.4	30.4	30.4	30.4	31.7	33.4	36.6
85°	19.1	17.0	14.4	12.4	12.0	11.5	12.0	12.4	14.4	17.0	19.1
87.5°	5.4	4.8	4.9	4.9	5.2	5.1	5.2	4.9	4.9	4.8	5.4
90°	7.4	9.7	11.9	13.2	14.5	13.8	14.5	13.2	11.9	9.7	7.4
92.5°	14.9	18.7	21.5	23.8	24.8	24.7	24.8	23.8	21.5	18.7	14.9
95°	30.0	34.5	39.0	42.2	44.1	43.5	44.1	42.2	39.0	34.5	30.0
97.5°	46.2	52.2	57.3	60.3	62.2	63.5	62.2	60.3	57.3	52.2	46.2
100°	57.0	62.8	68.6	72.1	75.4	76.7	75.4	72.1	68.6	62.8	57.0
102.5°	65.8	73.4	79.7	83.5	86.2	87.5	86.2	83.5	79.7	73.4	65.8
105°	80.2	88.3	95.0	99.8	102.7	103.7	102.7	99.8	95.0	88.3	80.2
107.5°	94.6	102.9	109.2	114.5	118.1	120.1	118.1	114.5	109.2	102.9	94.6
110°	106.0	112.7	119.5	124.3	127.9	129.2	127.9	124.3	119.5	112.7	106.0



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	115.5	123.0	129.8	134.6	138.7	140.5	138.7	134.6	129.8	123.0	115.5
115°	128.8	138.8	144.9	149.4	152.3	154.0	152.3	149.4	144.9	138.8	128.8
117.5°	139.9	150.3	157.0	160.5	161.9	163.0	161.9	160.5	157.0	150.3	139.9
120°	146.9	156.5	164.3	168.8	170.4	171.0	170.4	168.8	164.3	156.5	146.9
122.5°	153.3	162.5	169.9	175.5	178.1	178.8	178.1	175.5	169.9	162.5	153.3
125°	162.3	171.0	178.8	184.2	187.1	188.7	187.1	184.2	178.8	171.0	162.3
127.5°	170.2	179.6	186.7	191.6	194.5	195.8	194.5	191.6	186.7	179.6	170.2
130°	174.6	184.2	191.3	196.8	199.4	200.7	199.4	196.8	191.3	184.2	174.6
132.5°	177.9	188.1	195.4	200.4	203.2	204.5	203.2	200.4	195.4	188.1	177.9
135°	182.0	192.6	200.3	205.2	207.7	209.0	207.7	205.2	200.3	192.6	182.0
137.5°	185.5	195.2	203.2	208.3	210.6	211.5	210.6	208.3	203.2	195.2	185.5
140°	188.1	196.5	204.5	209.4	211.9	212.3	211.9	209.4	204.5	196.5	188.1
142.5°	191.4	198.0	205.0	209.9	212.4	213.0	212.4	209.9	205.0	198.0	191.4
145°	197.4	201.3	206.1	210.6	212.9	213.5	212.9	210.6	206.1	201.3	197.4
147.5°	205.0	206.2	208.7	211.7	213.9	214.3	213.9	211.7	208.7	206.2	205.0
150°	210.6	210.3	211.3	213.2	215.2	214.8	215.2	213.2	211.3	210.3	210.6
152.5°	217.1	215.2	215.2	216.1	217.0	216.9	217.0	216.1	215.2	215.2	217.1
155°	228.0	224.5	222.6	221.9	221.9	221.6	221.9	221.9	222.6	224.5	228.0
157.5°	240.1	235.1	232.2	230.7	230.2	229.5	230.2	230.7	232.2	235.1	240.1
160°	248.3	242.9	240.0	237.4	236.4	235.4	236.4	237.4	240.0	242.9	248.3
162.5°	256.1	250.8	247.7	245.4	244.4	242.9	244.4	245.4	247.7	250.8	256.1
165°	268.6	263.1	259.6	257.7	256.4	255.1	256.4	257.7	259.6	263.1	268.6
167.5°	281.2	275.2	272.9	270.7	269.5	267.1	269.5	270.7	272.9	275.2	281.2
170°	288.9	283.4	282.1	280.2	278.0	275.4	278.0	280.2	282.1	283.4	288.9
172.5°	295.6	291.9	290.6	288.7	288.0	285.9	288.0	288.7	290.6	291.9	295.6
175°	305.3	302.4	302.4	302.1	301.1	299.2	301.1	302.1	302.4	302.4	305.3
177.5°	313.5	311.9	312.9	312.9	312.7	310.9	312.7	312.9	312.9	311.9	313.5
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1009.9	1009.9	1009.9	1009.9
2.5°	1013.2	1014.6	1008.8	1003.0
5°	1012.8	1013.9	1006.6	999.3
7.5°	1008.7	1009.0	1001.7	994.3
10°	1005.1	1005.1	997.4	989.7
12.5°	1000.2	999.6	991.6	983.5
15°	989.4	987.6	979.0	970.5
17.5°	974.1	972.4	963.8	955.3
20°	962.8	961.6	953.0	944.5
22.5°	947.6	947.6	938.3	929.1
25°	919.8	924.0	915.0	906.0
27.5°	882.7	893.6	886.4	879.1
30°	853.8	871.0	865.4	859.9
32.5°	821.4	844.1	842.0	839.9
35°	769.1	799.3	803.1	807.0
37.5°	711.2	745.2	756.6	768.1
40°	670.7	707.1	723.4	739.6
42.5°	629.9	667.4	687.7	708.1
45°	569.1	608.1	632.0	656.0
47.5°	510.8	549.7	573.5	597.3
50°	471.6	508.8	531.9	555.0
52.5°	434.7	470.5	491.2	511.9
55°	379.9	413.7	433.3	453.0
57.5°	328.0	358.4	375.4	392.4
60°	295.0	324.0	339.0	353.9
62.5°	262.6	290.5	303.8	317.0
65°	219.0	241.9	251.8	261.6
67.5°	179.6	196.8	202.3	207.8
70°	155.5	169.7	171.4	173.1
72.5°	132.7	144.5	143.8	143.1
75°	101.0	108.8	105.4	102.0
77.5°	74.6	79.7	74.6	69.4
80°	57.7	61.2	56.1	51.0
82.5°	41.3	43.8	39.7	35.6
85°	20.8	21.6	19.4	17.3
87.5°	6.8	7.4	6.1	4.8
90°	5.8	3.5	2.3	1.0
92.5°	12.5	8.7	6.1	3.5
95°	25.1	20.0	14.2	10.0
97.5°	40.0	31.7	26.0	19.1
100°	48.0	39.9	34.5	27.1
102.5°	56.8	50.0	42.5	35.0
105°	72.5	64.1	55.4	47.0
107.5°	87.0	77.8	67.4	59.8
110°	96.3	86.3	75.4	68.6



TEST NUMBER: P1428350

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	105.3	95.1	83.9	77.1
115°	117.6	106.3	96.0	90.2
117.5°	129.3	117.8	106.9	102.3
120°	136.6	125.0	114.3	110.8
122.5°	142.5	131.2	121.3	119.8
125°	151.4	139.8	131.4	133.3
127.5°	158.6	148.0	142.7	147.0
130°	163.0	153.6	150.4	156.5
132.5°	166.8	159.6	158.1	166.6
135°	172.6	168.5	169.7	181.3
137.5°	179.5	177.9	182.2	196.9
140°	183.9	184.9	191.0	207.4
142.5°	189.8	192.1	200.0	217.5
145°	199.0	203.9	214.2	231.6
147.5°	209.5	215.7	228.5	246.3
150°	216.4	224.5	238.0	255.1
152.5°	224.4	232.7	246.3	263.6
155°	236.7	246.1	260.2	275.1
157.5°	249.3	258.8	272.4	285.3
160°	257.0	267.3	279.6	291.5
162.5°	265.8	275.3	286.0	296.6
165°	278.6	286.3	295.0	304.0
167.5°	289.4	295.8	302.6	309.7
170°	296.3	301.5	307.3	312.7
172.5°	302.2	306.4	310.6	315.3
175°	310.2	312.4	315.0	317.9
177.5°	316.3	317.1	317.8	319.1
180°	318.9	318.9	318.9	318.9



TEST NUMBER: P1428350
 CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.36	19.39	19.13	20.17	21.11	14.61	15.63	15.38	16.41	17.36
	3H	19.68	20.59	20.46	21.38	22.36	15.89	16.81	16.67	17.60	18.57
	4H	20.09	20.95	20.89	21.75	22.74	16.41	17.27	17.20	18.07	19.05
	6H	20.28	21.07	21.09	21.88	22.88	16.72	17.51	17.53	18.32	19.32
	8H	20.33	21.08	21.15	21.91	22.91	16.84	17.59	17.66	18.42	19.42
	12H	20.33	21.05	21.16	21.87	22.90	16.88	17.59	17.70	18.41	19.44
4H	2H	18.51	19.38	19.32	20.18	21.16	15.44	16.30	16.24	17.10	18.09
	3H	20.07	20.78	20.88	21.62	22.62	16.90	17.61	17.71	18.45	19.45
	4H	20.62	21.27	21.45	22.10	23.13	17.49	18.13	18.31	18.97	20.00
	6H	20.94	21.50	21.78	22.36	23.39	17.88	18.44	18.72	19.29	20.33
	8H	21.03	21.56	21.88	22.41	23.46	18.03	18.55	18.88	19.41	20.46
	12H	21.06	21.53	21.93	22.41	23.46	18.08	18.55	18.95	19.42	20.48
8H	4H	20.67	21.19	21.52	22.04	23.09	17.84	18.36	18.69	19.21	20.26
	6H	21.10	21.53	21.97	22.42	23.47	18.34	18.77	19.21	19.66	20.71
	8H	21.27	21.65	22.15	22.54	23.61	18.56	18.94	19.44	19.83	20.90
	12H	21.35	21.69	22.24	22.57	23.69	18.65	18.99	19.54	19.87	20.99
12H	4H	20.64	21.11	21.50	21.98	23.03	17.87	18.33	18.73	19.21	20.26
	6H	21.09	21.47	21.98	22.36	23.43	18.41	18.80	19.30	19.69	20.75
	8H	21.29	21.63	22.18	22.51	23.63	18.67	19.00	19.55	19.88	21.00