

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428404

Luminaire Tested: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428404  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE WAVES LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6013.9 lumens  
Efficiency: N/A  
Efficacy: 119.6 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 50.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54	54	54	54	
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47	47	47	47	
2	91	84	78	73	84	78	73	69	67	63	60	57	54	52	48	46	44	40	40	40	40	
3	83	74	67	62	77	69	63	58	60	55	51	51	48	45	43	41	38	35	35	35	35	
4	76	66	58	53	71	62	55	50	54	48	44	46	42	39	39	36	34	30	30	30	30	
5	70	59	51	45	65	55	48	43	48	43	39	42	37	34	35	32	30	27	27	27	27	
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24	24	24	24	
7	60	48	41	35	56	45	38	33	40	34	30	34	30	27	30	26	24	21	21	21	21	
8	56	44	36	31	52	41	35	30	36	31	27	32	27	24	27	24	21	19	19	19	19	
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17	
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	23	20	18	16	16	16	16	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23521	23521	23521	23521
5°	23364	23770	23364	23770
10°	23407	23975	23407	23975
15°	23401	24120	23401	24120
20°	23410	23649	23410	23649
25°	23284	21974	23284	21974
30°	23125	19866	23125	19866
35°	22945	17940	22945	17940
40°	22489	15850	22489	15850
45°	21607	13844	21607	13844
50°	20109	11848	20109	11848
55°	18395	9607	18395	9607
60°	16488	8289	16488	8289
65°	14418	7369	14418	7369
70°	11787	6680	11787	6680
75°	9176	6145	9176	6145
80°	6834	5421	6834	5421
85°	4631	3075	4631	3075

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21607 cd/sqm



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.7	2.3
10°-20°	402.0	6.7
20°-30°	591.5	9.8
30°-40°	646.7	10.8
40°-50°	580.2	9.6
50°-60°	432.8	7.2
60°-70°	273.5	4.5
70°-80°	135.5	2.3
80°-90°	35.7	0.6
90°-100°	75.7	1.3
100°-110°	220.8	3.7
110°-120°	360.3	6.0
120°-130°	457.2	7.6
130°-140°	489.2	8.1
140°-150°	456.8	7.6
150°-160°	375.9	6.3
160°-170°	252.1	4.2
170°-180°	89.5	1.5
0°-30°	1132.2	18.8
0°-40°	1778.9	29.6
0°-60°	2791.9	46.4
0°-90°	3236.6	53.8
90°-120°	656.7	10.9
90°-150°	2059.9	34.3
90°-180°	2777.0	46.2
0°-180°	6013.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1457	1457	1457	1457	1457	
5°	1442	1467	1442	1467	1442	137
15°	1400	1443	1400	1443	1400	395
25°	1307	1234	1307	1234	1307	602
35°	1164	910	1164	910	1164	726
45°	946	606	946	606	946	726
55°	654	341	654	341	654	584
65°	377	193	377	193	377	374
75°	147	98	147	98	147	162
85°	25	17	25	17	25	32
90°	3	21	3	41	3	3
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8
2.5°	1446.9	1455.2	1463.6	1461.7	1456.2	1453.8	1454.3	1455.0	1456.5	1458.0	1456.5
5°	1441.6	1452.1	1462.6	1461.0	1455.5	1453.0	1453.6	1455.5	1461.0	1466.6	1461.0
7.5°	1434.4	1445.0	1455.6	1455.1	1450.9	1449.8	1451.9	1454.9	1460.3	1465.7	1460.3
10°	1427.7	1438.8	1449.9	1449.9	1446.2	1445.9	1449.0	1452.5	1457.5	1462.4	1457.5
12.5°	1418.8	1430.4	1442.0	1442.9	1440.2	1440.6	1444.2	1448.1	1453.0	1458.0	1453.0
15°	1400.0	1412.3	1424.6	1427.2	1426.6	1428.5	1432.8	1436.8	1439.9	1443.0	1439.9
17.5°	1378.0	1390.4	1402.7	1405.1	1404.3	1404.4	1405.5	1406.7	1408.2	1409.7	1408.2
20°	1362.5	1374.8	1387.2	1388.9	1387.0	1383.9	1379.6	1376.4	1376.4	1376.4	1376.4
22.5°	1340.3	1353.6	1366.9	1367.0	1362.7	1354.7	1343.0	1333.2	1329.3	1325.3	1329.3
25°	1307.0	1320.0	1332.9	1326.9	1314.6	1296.4	1272.3	1252.0	1242.7	1233.5	1242.7
27.5°	1268.2	1278.6	1289.1	1273.4	1249.0	1219.7	1185.6	1156.7	1143.9	1131.1	1143.9
30°	1240.4	1248.4	1256.4	1231.6	1195.8	1159.2	1121.5	1090.2	1077.9	1065.6	1077.9
32.5°	1211.5	1214.6	1217.7	1185.0	1140.3	1098.5	1059.4	1026.7	1013.4	1000.1	1013.4
35°	1164.1	1158.5	1153.0	1109.5	1053.4	1005.6	966.1	933.6	921.9	910.2	921.9
37.5°	1108.0	1091.5	1075.0	1026.0	966.2	915.6	874.3	840.1	827.1	814.2	827.1
40°	1067.0	1043.5	1020.1	967.5	905.2	853.5	812.1	777.9	765.0	752.0	765.0
42.5°	1021.5	992.1	962.8	908.7	846.4	794.6	753.3	719.0	705.5	692.1	705.5
45°	946.3	911.7	877.2	820.9	757.4	705.6	665.5	632.2	619.3	606.3	619.3
47.5°	861.6	827.3	793.0	736.9	673.5	622.4	583.6	551.7	540.6	529.5	540.6
50°	800.6	767.3	734.0	680.3	619.9	570.3	531.4	498.9	485.3	471.7	485.3
52.5°	738.4	708.6	678.7	627.0	568.1	518.7	478.9	444.4	425.9	407.4	425.9
55°	653.5	625.1	596.8	548.1	492.6	442.6	398.2	362.3	351.8	341.3	351.8
57.5°	566.1	541.5	517.0	473.2	423.0	377.8	337.4	305.0	296.4	287.8	296.4
60°	510.6	489.0	467.4	425.5	376.8	335.5	301.5	273.9	265.3	256.7	265.3
62.5°	457.3	438.2	419.1	378.9	331.6	294.5	267.5	245.5	238.3	231.2	238.3
65°	377.4	363.2	349.0	315.9	276.4	245.6	223.4	205.2	199.0	192.9	199.0
67.5°	299.7	291.8	283.9	259.1	228.6	203.7	184.2	168.5	164.5	160.4	164.5
70°	249.7	247.3	244.8	224.3	197.8	176.5	160.5	147.7	144.6	141.5	144.6
72.5°	206.5	207.4	208.4	191.4	168.3	150.5	137.9	128.0	125.9	123.8	125.9
75°	147.1	152.0	156.9	145.7	129.0	116.4	107.8	101.0	99.7	98.5	99.7
77.5°	100.2	107.6	115.0	107.7	95.5	86.1	79.7	74.7	73.7	72.7	73.7
80°	73.5	80.9	88.3	83.2	74.0	66.9	62.0	58.3	58.3	58.3	58.3
82.5°	51.3	57.3	63.2	59.6	52.8	48.2	45.7	43.8	43.8	43.8	43.8
85°	25.0	28.1	31.1	30.1	27.6	24.5	20.8	17.9	17.3	16.6	17.3
87.5°	7.2	9.5	11.9	11.2	9.3	8.0	7.5	7.4	7.6	7.6	7.6
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8
2.5°	1455.0	1454.3	1453.8	1456.2	1461.7	1463.6	1455.2	1446.9	1455.2	1463.6	1461.7
5°	1455.5	1453.6	1453.0	1455.5	1461.0	1462.6	1452.1	1441.6	1452.1	1462.6	1461.0
7.5°	1454.9	1451.9	1449.8	1450.9	1455.1	1455.6	1445.0	1434.4	1445.0	1455.6	1455.1
10°	1452.5	1449.0	1445.9	1446.2	1449.9	1449.9	1438.8	1427.7	1438.8	1449.9	1449.9
12.5°	1448.1	1444.2	1440.6	1440.2	1442.9	1442.0	1430.4	1418.8	1430.4	1442.0	1442.9
15°	1436.8	1432.8	1428.5	1426.6	1427.2	1424.6	1412.3	1400.0	1412.3	1424.6	1427.2
17.5°	1406.7	1405.5	1404.4	1404.3	1405.1	1402.7	1390.4	1378.0	1390.4	1402.7	1405.1
20°	1376.4	1379.6	1383.9	1387.0	1388.9	1387.2	1374.8	1362.5	1374.8	1387.2	1388.9
22.5°	1333.2	1343.0	1354.7	1362.7	1367.0	1366.9	1353.6	1340.3	1353.6	1366.9	1367.0
25°	1252.0	1272.3	1296.4	1314.6	1326.9	1332.9	1320.0	1307.0	1320.0	1332.9	1326.9
27.5°	1156.7	1185.6	1219.7	1249.0	1273.4	1289.1	1278.6	1268.2	1278.6	1289.1	1273.4
30°	1090.2	1121.5	1159.2	1195.8	1231.6	1256.4	1248.4	1240.4	1248.4	1256.4	1231.6
32.5°	1026.7	1059.4	1098.5	1140.3	1185.0	1217.7	1214.6	1211.5	1214.6	1217.7	1185.0
35°	933.6	966.1	1005.6	1053.4	1109.5	1153.0	1158.5	1164.1	1158.5	1153.0	1109.5
37.5°	840.1	874.3	915.6	966.2	1026.0	1075.0	1091.5	1108.0	1091.5	1075.0	1026.0
40°	777.9	812.1	853.5	905.2	967.5	1020.1	1043.5	1067.0	1043.5	1020.1	967.5
42.5°	719.0	753.3	794.6	846.4	908.7	962.8	992.1	1021.5	992.1	962.8	908.7
45°	632.2	665.5	705.6	757.4	820.9	877.2	911.7	946.3	911.7	877.2	820.9
47.5°	551.7	583.6	622.4	673.5	736.9	793.0	827.3	861.6	827.3	793.0	736.9
50°	498.9	531.4	570.3	619.9	680.3	734.0	767.3	800.6	767.3	734.0	680.3
52.5°	444.4	478.9	518.7	568.1	627.0	678.7	708.6	738.4	708.6	678.7	627.0
55°	362.3	398.2	442.6	492.6	548.1	596.8	625.1	653.5	625.1	596.8	548.1
57.5°	305.0	337.4	377.8	423.0	473.2	517.0	541.5	566.1	541.5	517.0	473.2
60°	273.9	301.5	335.5	376.8	425.5	467.4	489.0	510.6	489.0	467.4	425.5
62.5°	245.5	267.5	294.5	331.6	378.9	419.1	438.2	457.3	438.2	419.1	378.9
65°	205.2	223.4	245.6	276.4	315.9	349.0	363.2	377.4	363.2	349.0	315.9
67.5°	168.5	184.2	203.7	228.6	259.1	283.9	291.8	299.7	291.8	283.9	259.1
70°	147.7	160.5	176.5	197.8	224.3	244.8	247.3	249.7	247.3	244.8	224.3
72.5°	128.0	137.9	150.5	168.3	191.4	208.4	207.4	206.5	207.4	208.4	191.4
75°	101.0	107.8	116.4	129.0	145.7	156.9	152.0	147.1	152.0	156.9	145.7
77.5°	74.7	79.7	86.1	95.5	107.7	115.0	107.6	100.2	107.6	115.0	107.7
80°	58.3	62.0	66.9	74.0	83.2	88.3	80.9	73.5	80.9	88.3	83.2
82.5°	43.8	45.7	48.2	52.8	59.6	63.2	57.3	51.3	57.3	63.2	59.6
85°	17.9	20.8	24.5	27.6	30.1	31.1	28.1	25.0	28.1	31.1	30.1
87.5°	7.4	7.5	8.0	9.3	11.2	11.9	9.5	7.2	9.5	11.7	11.6
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8	1456.8
2.5°	1456.2	1453.8	1454.3	1455.0	1456.5	1458.0	1456.5	1455.0	1454.3	1453.8	1456.2
5°	1455.5	1453.0	1453.6	1455.5	1461.0	1466.6	1461.0	1455.5	1453.6	1453.0	1455.5
7.5°	1450.9	1449.8	1451.9	1454.9	1460.3	1465.7	1460.3	1454.9	1451.9	1449.8	1450.9
10°	1446.2	1445.9	1449.0	1452.5	1457.5	1462.4	1457.5	1452.5	1449.0	1445.9	1446.2
12.5°	1440.2	1440.6	1444.2	1448.1	1453.0	1458.0	1453.0	1448.1	1444.2	1440.6	1440.2
15°	1426.6	1428.5	1432.8	1436.8	1439.9	1443.0	1439.9	1436.8	1432.8	1428.5	1426.6
17.5°	1404.3	1404.4	1405.5	1406.7	1408.2	1409.7	1408.2	1406.7	1405.5	1404.4	1404.3
20°	1387.0	1383.9	1379.6	1376.4	1376.4	1376.4	1376.4	1376.4	1379.6	1383.9	1387.0
22.5°	1362.7	1354.7	1343.0	1333.2	1329.3	1325.3	1329.3	1333.2	1343.0	1354.7	1362.7
25°	1314.6	1296.4	1272.3	1252.0	1242.7	1233.5	1242.7	1252.0	1272.3	1296.4	1314.6
27.5°	1249.0	1219.7	1185.6	1156.7	1143.9	1131.1	1143.9	1156.7	1185.6	1219.7	1249.0
30°	1195.8	1159.2	1121.5	1090.2	1077.9	1065.6	1077.9	1090.2	1121.5	1159.2	1195.8
32.5°	1140.3	1098.5	1059.4	1026.7	1013.4	1000.1	1013.4	1026.7	1059.4	1098.5	1140.3
35°	1053.4	1005.6	966.1	933.6	921.9	910.2	921.9	933.6	966.1	1005.6	1053.4
37.5°	966.2	915.6	874.3	840.1	827.1	814.2	827.1	840.1	874.3	915.6	966.2
40°	905.2	853.5	812.1	777.9	765.0	752.0	765.0	777.9	812.1	853.5	905.2
42.5°	846.4	794.6	753.3	719.0	705.5	692.1	705.5	719.0	753.3	794.6	846.4
45°	757.4	705.6	665.5	632.2	619.3	606.3	619.3	632.2	665.5	705.6	757.4
47.5°	673.5	622.4	583.6	551.7	540.6	529.5	540.6	551.7	583.6	622.4	673.5
50°	619.9	570.3	531.4	498.9	485.3	471.7	485.3	498.9	531.4	570.3	619.9
52.5°	568.1	518.7	478.9	444.4	425.9	407.4	425.9	444.4	478.9	518.7	568.1
55°	492.6	442.6	398.2	362.3	351.8	341.3	351.8	362.3	398.2	442.6	492.6
57.5°	423.0	377.8	337.4	305.0	296.4	287.8	296.4	305.0	337.4	377.8	423.0
60°	376.8	335.5	301.5	273.9	265.3	256.7	265.3	273.9	301.5	335.5	376.8
62.5°	331.6	294.5	267.5	245.5	238.3	231.2	238.3	245.5	267.5	294.5	331.6
65°	276.4	245.6	223.4	205.2	199.0	192.9	199.0	205.2	223.4	245.6	276.4
67.5°	228.6	203.7	184.2	168.5	164.5	160.4	164.5	168.5	184.2	203.7	228.6
70°	197.8	176.5	160.5	147.7	144.6	141.5	144.6	147.7	160.5	176.5	197.8
72.5°	168.3	150.5	137.9	128.0	125.9	123.8	125.9	128.0	137.9	150.5	168.3
75°	129.0	116.4	107.8	101.0	99.7	98.5	99.7	101.0	107.8	116.4	129.0
77.5°	95.5	86.1	79.7	74.7	73.7	72.7	73.7	74.7	79.7	86.1	95.5
80°	74.0	66.9	62.0	58.3	58.3	58.3	58.3	58.3	62.0	66.9	74.0
82.5°	52.8	48.2	45.7	43.8	43.8	43.8	43.8	43.8	45.7	48.2	52.8
85°	27.6	24.5	20.8	17.9	17.3	16.6	17.3	17.9	20.8	24.5	27.6
87.5°	10.1	10.0	10.8	11.2	12.0	11.6	12.0	11.2	10.8	10.0	10.1
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	490.0	467.0	438.1	
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1456.8	1456.8	1456.8	1456.8
2.5°	1461.7	1463.6	1455.2	1446.9
5°	1461.0	1462.6	1452.1	1441.6
7.5°	1455.1	1455.6	1445.0	1434.4
10°	1449.9	1449.9	1438.8	1427.7
12.5°	1442.9	1442.0	1430.4	1418.8
15°	1427.2	1424.6	1412.3	1400.0
17.5°	1405.1	1402.7	1390.4	1378.0
20°	1388.9	1387.2	1374.8	1362.5
22.5°	1367.0	1366.9	1353.6	1340.3
25°	1326.9	1332.9	1320.0	1307.0
27.5°	1273.4	1289.1	1278.6	1268.2
30°	1231.6	1256.4	1248.4	1240.4
32.5°	1185.0	1217.7	1214.6	1211.5
35°	1109.5	1153.0	1158.5	1164.1
37.5°	1026.0	1075.0	1091.5	1108.0
40°	967.5	1020.1	1043.5	1067.0
42.5°	908.7	962.8	992.1	1021.5
45°	820.9	877.2	911.7	946.3
47.5°	736.9	793.0	827.3	861.6
50°	680.3	734.0	767.3	800.6
52.5°	627.0	678.7	708.6	738.4
55°	548.1	596.8	625.1	653.5
57.5°	473.2	517.0	541.5	566.1
60°	425.5	467.4	489.0	510.6
62.5°	378.9	419.1	438.2	457.3
65°	315.9	349.0	363.2	377.4
67.5°	259.1	283.9	291.8	299.7
70°	224.3	244.8	247.3	249.7
72.5°	191.4	208.4	207.4	206.5
75°	145.7	156.9	152.0	147.1
77.5°	107.7	115.0	107.6	100.2
80°	83.2	88.3	80.9	73.5
82.5°	59.6	63.2	57.3	51.3
85°	30.1	31.1	28.1	25.0
87.5°	11.6	11.7	9.5	7.2
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7



TEST NUMBER: P1428404

CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1428404  
 CATALOG NUMBER: SQ2W-PW1-K-075U-075D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.24	19.09	19.17	20.04	21.25	14.48	15.34	15.42	16.28	17.50
	3H	19.54	20.30	20.48	21.26	22.50	15.75	16.52	16.70	17.47	18.71
	4H	19.95	20.67	20.90	21.63	22.88	16.26	16.98	17.22	17.94	19.19
	6H	20.13	20.79	21.10	21.75	23.02	16.57	17.23	17.54	18.20	19.46
	8H	20.17	20.80	21.14	21.78	23.04	16.68	17.31	17.66	18.29	19.55
	12H	20.17	20.77	21.15	21.74	23.03	16.71	17.31	17.69	18.29	19.57
4H	2H	18.37	19.09	19.33	20.05	21.30	15.29	16.02	16.26	16.97	18.22
	3H	19.91	20.51	20.88	21.49	22.76	16.74	17.34	17.71	18.33	19.59
	4H	20.45	21.00	21.43	21.98	23.27	17.32	17.86	18.30	18.85	20.14
	6H	20.76	21.23	21.76	22.24	23.53	17.70	18.17	18.70	19.18	20.47
	8H	20.85	21.29	21.85	22.29	23.59	17.85	18.29	18.85	19.29	20.59
	12H	20.88	21.27	21.89	22.28	23.59	17.89	18.29	18.91	19.30	20.61
8H	4H	20.49	20.93	21.49	21.93	23.23	17.66	18.10	18.66	19.10	20.40
	6H	20.91	21.27	21.93	22.31	23.61	18.15	18.52	19.17	19.56	20.86
	8H	21.08	21.40	22.11	22.43	23.75	18.37	18.69	19.40	19.72	21.04
	12H	21.16	21.44	22.19	22.46	23.83	18.46	18.74	19.49	19.76	21.12
12H	4H	20.45	20.84	21.46	21.86	23.17	17.68	18.07	18.69	19.09	20.40
	6H	20.91	21.22	21.93	22.25	23.57	18.23	18.55	19.26	19.57	20.89
	8H	21.10	21.38	22.13	22.40	23.76	18.47	18.75	19.50	19.77	21.14