

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428410

Luminaire Tested: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428410  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE WAVES LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7127.6 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	58	57	57	57	57	53	
2	93	85	79	75	86	80	75	71	71	67	63	62	59	56	53	51	49	49	49	49	45	
3	85	76	69	63	79	71	65	60	63	58	54	55	51	48	48	45	43	43	43	43	39	
4	78	67	60	54	73	64	57	51	56	51	47	50	45	42	43	40	37	37	37	37	34	
5	72	61	53	47	67	57	50	45	51	45	41	45	40	37	39	36	33	33	33	33	30	
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	29	29	29	29	27	
7	62	50	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	26	26	26	24	
8	57	45	38	32	54	43	36	31	38	33	29	34	30	26	30	27	24	24	24	24	22	
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	24	22	22	22	22	20	
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	20	20	20	18	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	31624	31624	31624	31624
5°	31413	31957	31413	31957
10°	31471	32235	31471	32235
15°	31463	32429	31463	32429
20°	31475	31797	31475	31797
25°	31306	29544	31306	29544
30°	31091	26710	31091	26710
35°	30848	24121	30848	24121
40°	30236	21310	30236	21310
45°	29051	18614	29051	18614
50°	27037	15932	27037	15932
55°	24732	12918	24732	12918
60°	22168	11144	22168	11144
65°	19385	9906	19385	9906
70°	15852	8983	15852	8983
75°	12333	8259	12333	8259
80°	9196	7280	9196	7280
85°	6224	4150	6224	4150

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29051 cd/sqm



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.5	2.6
10°-20°	540.4	7.6
20°-30°	795.3	11.2
30°-40°	869.6	12.2
40°-50°	780.1	10.9
50°-60°	581.9	8.2
60°-70°	367.8	5.2
70°-80°	182.2	2.6
80°-90°	46.6	0.7
90°-100°	75.7	1.1
100°-110°	220.8	3.1
110°-120°	360.3	5.1
120°-130°	457.2	6.4
130°-140°	489.2	6.9
140°-150°	456.8	6.4
150°-160°	375.9	5.3
160°-170°	252.1	3.5
170°-180°	89.5	1.3
0°-30°	1522.2	21.4
0°-40°	2391.8	33.6
0°-60°	3753.7	52.7
0°-90°	4350.3	61.0
90°-120°	656.7	9.2
90°-150°	2059.9	28.9
90°-180°	2777.0	39.0
0°-180°	7127.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1959	1959	1959	1959	1959	
5°	1938	1972	1938	1972	1938	184
15°	1882	1940	1882	1940	1882	531
25°	1757	1658	1757	1658	1757	809
35°	1565	1224	1565	1224	1565	976
45°	1272	815	1272	815	1272	976
55°	879	459	879	459	879	785
65°	507	259	507	259	507	503
75°	198	132	198	132	198	218
85°	34	22	34	22	34	43
90°	3	21	3	41	3	4
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7
2.5°	1945.3	1956.6	1967.9	1965.2	1957.9	1954.6	1955.3	1956.3	1958.3	1960.2	1958.3
5°	1938.2	1952.3	1966.4	1964.3	1956.9	1953.6	1954.4	1956.9	1964.3	1971.8	1964.3
7.5°	1928.5	1942.8	1957.0	1956.4	1950.7	1949.3	1952.2	1956.1	1963.4	1970.7	1963.4
10°	1919.6	1934.5	1949.4	1949.4	1944.4	1944.0	1948.2	1952.9	1959.6	1966.2	1959.6
12.5°	1907.6	1923.2	1938.8	1940.0	1936.3	1936.9	1941.7	1947.0	1953.6	1960.2	1953.6
15°	1882.3	1898.8	1915.4	1919.0	1918.1	1920.6	1926.4	1931.8	1935.9	1940.1	1935.9
17.5°	1852.8	1869.4	1886.0	1889.2	1888.1	1888.2	1889.7	1891.3	1893.3	1895.3	1893.3
20°	1831.9	1848.5	1865.1	1867.3	1864.9	1860.7	1854.9	1850.6	1850.6	1850.6	1850.6
22.5°	1802.0	1820.0	1837.9	1838.0	1832.2	1821.4	1805.7	1792.5	1787.2	1781.9	1787.2
25°	1757.3	1774.7	1792.1	1784.0	1767.4	1743.0	1710.6	1683.3	1670.8	1658.4	1670.8
27.5°	1705.0	1719.1	1733.2	1712.1	1679.3	1639.9	1594.0	1555.2	1538.0	1520.7	1538.0
30°	1667.7	1678.5	1689.3	1655.9	1607.8	1558.5	1507.9	1465.8	1449.3	1432.7	1449.3
32.5°	1628.9	1633.1	1637.2	1593.2	1533.2	1476.9	1424.4	1380.5	1362.5	1344.6	1362.5
35°	1565.1	1557.7	1550.2	1491.8	1416.3	1352.1	1299.0	1255.3	1239.5	1223.8	1239.5
37.5°	1489.8	1467.5	1445.3	1379.5	1299.0	1231.0	1175.5	1129.5	1112.1	1094.7	1112.1
40°	1434.6	1403.0	1371.5	1300.9	1217.1	1147.5	1091.9	1045.9	1028.5	1011.1	1028.5
42.5°	1373.4	1333.9	1294.4	1221.8	1138.0	1068.4	1012.8	966.6	948.6	930.5	948.6
45°	1272.3	1225.8	1179.4	1103.7	1018.3	948.7	894.8	850.0	832.6	815.2	832.6
47.5°	1158.5	1112.4	1066.3	990.8	905.6	836.9	784.6	741.7	726.8	711.9	726.8
50°	1076.4	1031.6	986.8	914.7	833.5	766.7	714.5	670.7	652.5	634.3	652.5
52.5°	992.8	952.7	912.5	843.1	763.8	697.4	643.8	597.4	572.6	547.7	572.6
55°	878.6	840.5	802.4	736.9	662.2	595.1	535.4	487.1	473.0	458.9	473.0
57.5°	761.1	728.1	695.1	636.3	568.8	507.9	453.7	410.1	398.5	386.9	398.5
60°	686.5	657.5	628.5	572.1	506.6	451.0	405.4	368.3	356.7	345.1	356.7
62.5°	614.9	589.2	563.5	509.4	445.9	396.0	359.7	330.0	320.4	310.8	320.4
65°	507.4	488.3	469.3	424.7	371.6	330.2	300.3	275.9	267.6	259.3	267.6
67.5°	402.9	392.3	381.7	348.3	307.4	273.8	247.6	226.6	221.1	215.6	221.1
70°	335.8	332.5	329.2	301.6	265.9	237.3	215.8	198.6	194.4	190.3	194.4
72.5°	277.6	278.9	280.2	257.3	226.3	202.3	185.4	172.0	169.2	166.4	169.2
75°	197.7	204.4	211.0	195.9	173.5	156.5	144.9	135.8	134.1	132.4	134.1
77.5°	134.7	144.6	154.6	144.8	128.3	115.8	107.2	100.4	99.1	97.8	99.1
80°	98.9	108.8	118.8	111.9	99.5	90.0	83.3	78.3	78.3	78.3	78.3
82.5°	69.0	77.0	84.9	80.1	71.0	64.8	61.4	58.9	58.9	58.9	58.9
85°	33.6	37.7	41.9	40.4	37.1	33.0	28.0	24.0	23.2	22.4	23.2
87.5°	9.5	12.3	15.2	14.0	11.3	9.5	8.8	8.5	8.7	8.7	8.7
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3

TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2

TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7
2.5°	1956.3	1955.3	1954.6	1957.9	1965.2	1967.9	1956.6	1945.3	1956.6	1967.9	1965.2
5°	1956.9	1954.4	1953.6	1956.9	1964.3	1966.4	1952.3	1938.2	1952.3	1966.4	1964.3
7.5°	1956.1	1952.2	1949.3	1950.7	1956.4	1957.0	1942.8	1928.5	1942.8	1957.0	1956.4
10°	1952.9	1948.2	1944.0	1944.4	1949.4	1949.4	1934.5	1919.6	1934.5	1949.4	1949.4
12.5°	1947.0	1941.7	1936.9	1936.3	1940.0	1938.8	1923.2	1907.6	1923.2	1938.8	1940.0
15°	1931.8	1926.4	1920.6	1918.1	1919.0	1915.4	1898.8	1882.3	1898.8	1915.4	1919.0
17.5°	1891.3	1889.7	1888.2	1888.1	1889.2	1886.0	1869.4	1852.8	1869.4	1886.0	1889.2
20°	1850.6	1854.9	1860.7	1864.9	1867.3	1865.1	1848.5	1831.9	1848.5	1865.1	1867.3
22.5°	1792.5	1805.7	1821.4	1832.2	1838.0	1837.9	1820.0	1802.0	1820.0	1837.9	1838.0
25°	1683.3	1710.6	1743.0	1767.4	1784.0	1792.1	1774.7	1757.3	1774.7	1792.1	1784.0
27.5°	1555.2	1594.0	1639.9	1679.3	1712.1	1733.2	1719.1	1705.0	1719.1	1733.2	1712.1
30°	1465.8	1507.9	1558.5	1607.8	1655.9	1689.3	1678.5	1667.7	1678.5	1689.3	1655.9
32.5°	1380.5	1424.4	1476.9	1533.2	1593.2	1637.2	1633.1	1628.9	1633.1	1637.2	1593.2
35°	1255.3	1299.0	1352.1	1416.3	1491.8	1550.2	1557.7	1565.1	1557.7	1550.2	1491.8
37.5°	1129.5	1175.5	1231.0	1299.0	1379.5	1445.3	1467.5	1489.8	1467.5	1445.3	1379.5
40°	1045.9	1091.9	1147.5	1217.1	1300.9	1371.5	1403.0	1434.6	1403.0	1371.5	1300.9
42.5°	966.6	1012.8	1068.4	1138.0	1221.8	1294.4	1333.9	1373.4	1333.9	1294.4	1221.8
45°	850.0	894.8	948.7	1018.3	1103.7	1179.4	1225.8	1272.3	1225.8	1179.4	1103.7
47.5°	741.7	784.6	836.9	905.6	990.8	1066.3	1112.4	1158.5	1112.4	1066.3	990.8
50°	670.7	714.5	766.7	833.5	914.7	986.8	1031.6	1076.4	1031.6	986.8	914.7
52.5°	597.4	643.8	697.4	763.8	843.1	912.5	952.7	992.8	952.7	912.5	843.1
55°	487.1	535.4	595.1	662.2	736.9	802.4	840.5	878.6	840.5	802.4	736.9
57.5°	410.1	453.7	507.9	568.8	636.3	695.1	728.1	761.1	728.1	695.1	636.3
60°	368.3	405.4	451.0	506.6	572.1	628.5	657.5	686.5	657.5	628.5	572.1
62.5°	330.0	359.7	396.0	445.9	509.4	563.5	589.2	614.9	589.2	563.5	509.4
65°	275.9	300.3	330.2	371.6	424.7	469.3	488.3	507.4	488.3	469.3	424.7
67.5°	226.6	247.6	273.8	307.4	348.3	381.7	392.3	402.9	392.3	381.7	348.3
70°	198.6	215.8	237.3	265.9	301.6	329.2	332.5	335.8	332.5	329.2	301.6
72.5°	172.0	185.4	202.3	226.3	257.3	280.2	278.9	277.6	278.9	280.2	257.3
75°	135.8	144.9	156.5	173.5	195.9	211.0	204.4	197.7	204.4	211.0	195.9
77.5°	100.4	107.2	115.8	128.3	144.8	154.6	144.6	134.7	144.6	154.6	144.8
80°	78.3	83.3	90.0	99.5	111.9	118.8	108.8	98.9	108.8	118.8	111.9
82.5°	58.9	61.4	64.8	71.0	80.1	84.9	77.0	69.0	77.0	84.9	80.1
85°	24.0	28.0	33.0	37.1	40.4	41.9	37.7	33.6	37.7	41.9	40.4
87.5°	8.5	8.8	9.5	11.3	14.0	15.2	12.3	9.5	12.3	15.0	14.4
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7	1958.7
2.5°	1957.9	1954.6	1955.3	1956.3	1958.3	1960.2	1958.3	1956.3	1955.3	1954.6	1957.9
5°	1956.9	1953.6	1954.4	1956.9	1964.3	1971.8	1964.3	1956.9	1954.4	1953.6	1956.9
7.5°	1950.7	1949.3	1952.2	1956.1	1963.4	1970.7	1963.4	1956.1	1952.2	1949.3	1950.7
10°	1944.4	1944.0	1948.2	1952.9	1959.6	1966.2	1959.6	1952.9	1948.2	1944.0	1944.4
12.5°	1936.3	1936.9	1941.7	1947.0	1953.6	1960.2	1953.6	1947.0	1941.7	1936.9	1936.3
15°	1918.1	1920.6	1926.4	1931.8	1935.9	1940.1	1935.9	1931.8	1926.4	1920.6	1918.1
17.5°	1888.1	1888.2	1889.7	1891.3	1893.3	1895.3	1893.3	1891.3	1889.7	1888.2	1888.1
20°	1864.9	1860.7	1854.9	1850.6	1850.6	1850.6	1850.6	1850.6	1854.9	1860.7	1864.9
22.5°	1832.2	1821.4	1805.7	1792.5	1787.2	1781.9	1787.2	1792.5	1805.7	1821.4	1832.2
25°	1767.4	1743.0	1710.6	1683.3	1670.8	1658.4	1670.8	1683.3	1710.6	1743.0	1767.4
27.5°	1679.3	1639.9	1594.0	1555.2	1538.0	1520.7	1538.0	1555.2	1594.0	1639.9	1679.3
30°	1607.8	1558.5	1507.9	1465.8	1449.3	1432.7	1449.3	1465.8	1507.9	1558.5	1607.8
32.5°	1533.2	1476.9	1424.4	1380.5	1362.5	1344.6	1362.5	1380.5	1424.4	1476.9	1533.2
35°	1416.3	1352.1	1299.0	1255.3	1239.5	1223.8	1239.5	1255.3	1299.0	1352.1	1416.3
37.5°	1299.0	1231.0	1175.5	1129.5	1112.1	1094.7	1112.1	1129.5	1175.5	1231.0	1299.0
40°	1217.1	1147.5	1091.9	1045.9	1028.5	1011.1	1028.5	1045.9	1091.9	1147.5	1217.1
42.5°	1138.0	1068.4	1012.8	966.6	948.6	930.5	948.6	966.6	1012.8	1068.4	1138.0
45°	1018.3	948.7	894.8	850.0	832.6	815.2	832.6	850.0	894.8	948.7	1018.3
47.5°	905.6	836.9	784.6	741.7	726.8	711.9	726.8	741.7	784.6	836.9	905.6
50°	833.5	766.7	714.5	670.7	652.5	634.3	652.5	670.7	714.5	766.7	833.5
52.5°	763.8	697.4	643.8	597.4	572.6	547.7	572.6	597.4	643.8	697.4	763.8
55°	662.2	595.1	535.4	487.1	473.0	458.9	473.0	487.1	535.4	595.1	662.2
57.5°	568.8	507.9	453.7	410.1	398.5	386.9	398.5	410.1	453.7	507.9	568.8
60°	506.6	451.0	405.4	368.3	356.7	345.1	356.7	368.3	405.4	451.0	506.6
62.5°	445.9	396.0	359.7	330.0	320.4	310.8	320.4	330.0	359.7	396.0	445.9
65°	371.6	330.2	300.3	275.9	267.6	259.3	267.6	275.9	300.3	330.2	371.6
67.5°	307.4	273.8	247.6	226.6	221.1	215.6	221.1	226.6	247.6	273.8	307.4
70°	265.9	237.3	215.8	198.6	194.4	190.3	194.4	198.6	215.8	237.3	265.9
72.5°	226.3	202.3	185.4	172.0	169.2	166.4	169.2	172.0	185.4	202.3	226.3
75°	173.5	156.5	144.9	135.8	134.1	132.4	134.1	135.8	144.9	156.5	173.5
77.5°	128.3	115.8	107.2	100.4	99.1	97.8	99.1	100.4	107.2	115.8	128.3
80°	99.5	90.0	83.3	78.3	78.3	78.3	78.3	78.3	83.3	90.0	99.5
82.5°	71.0	64.8	61.4	58.9	58.9	58.9	58.9	58.9	61.4	64.8	71.0
85°	37.1	33.0	28.0	24.0	23.2	22.4	23.2	24.0	28.0	33.0	37.1
87.5°	12.0	11.4	12.1	12.4	13.1	12.7	13.1	12.4	12.1	11.4	12.0
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	503.5	490.0	467.0	438.1
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1958.7	1958.7	1958.7	1958.7
2.5°	1965.2	1967.9	1956.6	1945.3
5°	1964.3	1966.4	1952.3	1938.2
7.5°	1956.4	1957.0	1942.8	1928.5
10°	1949.4	1949.4	1934.5	1919.6
12.5°	1940.0	1938.8	1923.2	1907.6
15°	1919.0	1915.4	1898.8	1882.3
17.5°	1889.2	1886.0	1869.4	1852.8
20°	1867.3	1865.1	1848.5	1831.9
22.5°	1838.0	1837.9	1820.0	1802.0
25°	1784.0	1792.1	1774.7	1757.3
27.5°	1712.1	1733.2	1719.1	1705.0
30°	1655.9	1689.3	1678.5	1667.7
32.5°	1593.2	1637.2	1633.1	1628.9
35°	1491.8	1550.2	1557.7	1565.1
37.5°	1379.5	1445.3	1467.5	1489.8
40°	1300.9	1371.5	1403.0	1434.6
42.5°	1221.8	1294.4	1333.9	1373.4
45°	1103.7	1179.4	1225.8	1272.3
47.5°	990.8	1066.3	1112.4	1158.5
50°	914.7	986.8	1031.6	1076.4
52.5°	843.1	912.5	952.7	992.8
55°	736.9	802.4	840.5	878.6
57.5°	636.3	695.1	728.1	761.1
60°	572.1	628.5	657.5	686.5
62.5°	509.4	563.5	589.2	614.9
65°	424.7	469.3	488.3	507.4
67.5°	348.3	381.7	392.3	402.9
70°	301.6	329.2	332.5	335.8
72.5°	257.3	280.2	278.9	277.6
75°	195.9	211.0	204.4	197.7
77.5°	144.8	154.6	144.6	134.7
80°	111.9	118.8	108.8	98.9
82.5°	80.1	84.9	77.0	69.0
85°	40.4	41.9	37.7	33.6
87.5°	14.4	15.0	12.3	9.5
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7

TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1428410

CATALOG NUMBER: SQ2W-PW1-K-075U-100D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.89	20.81	20.75	21.69	22.80	16.14	17.06	17.00	17.94	19.05
	3H	21.20	22.02	22.07	22.91	24.04	17.41	18.23	18.29	19.12	20.26
	4H	21.61	22.38	22.50	23.28	24.42	17.92	18.70	18.81	19.59	20.74
	6H	21.79	22.50	22.70	23.41	24.56	18.23	18.95	19.14	19.85	21.01
	8H	21.83	22.51	22.75	23.43	24.59	18.35	19.03	19.26	19.95	21.10
	12H	21.84	22.48	22.76	23.40	24.58	18.38	19.03	19.30	19.94	21.12
4H	2H	20.03	20.80	20.93	21.70	22.85	16.95	17.73	17.85	18.63	19.77
	3H	21.57	22.22	22.48	23.14	24.30	18.41	19.05	19.32	19.98	21.14
	4H	22.12	22.71	23.04	23.63	24.82	18.99	19.57	19.91	20.50	21.68
	6H	22.44	22.94	23.37	23.89	25.07	19.37	19.88	20.31	20.83	22.01
	8H	22.53	23.00	23.46	23.94	25.14	19.53	20.00	20.46	20.94	22.14
	12H	22.55	22.98	23.51	23.94	25.14	19.57	19.99	20.53	20.95	22.16
8H	4H	22.16	22.64	23.10	23.58	24.78	19.34	19.81	20.27	20.75	21.95
	6H	22.59	22.98	23.55	23.96	25.16	19.83	20.22	20.79	21.20	22.40
	8H	22.76	23.10	23.73	24.08	25.29	20.05	20.39	21.02	21.37	22.58
	12H	22.84	23.14	23.81	24.11	25.37	20.13	20.44	21.11	21.40	22.67
12H	4H	22.13	22.55	23.08	23.51	24.71	19.36	19.78	20.31	20.74	21.94
	6H	22.58	22.93	23.55	23.90	25.12	19.91	20.25	20.88	21.22	22.44
	8H	22.78	23.08	23.75	24.04	25.31	20.15	20.45	21.13	21.42	22.69