

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428468

Luminaire Tested: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428468
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9226.0 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	73	68	76	70	66	61	56	52	49	42	40	38	29	28	27	21
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20	16
5	65	54	47	41	58	49	43	38	39	35	31	30	27	24	21	19	18	14
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	19	17	16	13
7	56	44	37	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	52	40	33	28	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	23	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19186	19186	19186	19186
5°	19056	19387	19056	19387
10°	19092	19556	19092	19556
15°	19087	19672	19087	19672
20°	19094	19288	19094	19288
25°	18990	17923	18990	17923
30°	18861	16203	18861	16203
35°	18715	14633	18715	14633
40°	18343	12928	18343	12928
45°	17623	11291	17623	11291
50°	16402	9665	16402	9665
55°	15003	7837	15003	7837
60°	13449	6762	13449	6762
65°	11759	6009	11759	6009
70°	9616	5448	9616	5448
75°	7486	5009	7486	5009
80°	5579	4416	5579	4416
85°	3779	2519	3779	2519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17623 cd/sqm



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	1.2
10°-20°	327.8	3.6
20°-30°	482.5	5.2
30°-40°	527.5	5.7
40°-50°	473.2	5.1
50°-60°	353.0	3.8
60°-70°	223.1	2.4
70°-80°	110.5	1.2
80°-90°	35.2	0.4
90°-100°	179.4	1.9
100°-110°	523.0	5.7
110°-120°	853.6	9.3
120°-130°	1083.1	11.7
130°-140°	1158.9	12.6
140°-150°	1082.2	11.7
150°-160°	890.5	9.7
160°-170°	597.2	6.5
170°-180°	212.1	2.3
0°-30°	923.5	10.0
0°-40°	1451.0	15.7
0°-60°	2277.2	24.7
0°-90°	2646.0	28.7
90°-120°	1556.0	16.9
90°-150°	4880.2	52.9
90°-180°	6580.0	71.3
0°-180°	9226.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1188	1188	1188	1188	1188	
5°	1176	1196	1176	1196	1176	112
15°	1142	1177	1142	1177	1142	322
25°	1066	1006	1066	1006	1066	491
35°	950	742	950	742	950	592
45°	772	494	772	494	772	592
55°	533	278	533	278	533	476
65°	308	157	308	157	308	305
75°	120	80	120	80	120	132
85°	20	14	20	14	20	26
90°	7	50	7	98	7	6
95°	71	52	71	307	71	85
105°	332	533	332	733	332	353
115°	637	883	637	1088	637	628
125°	942	1400	942	1334	942	843
135°	1282	1832	1282	1477	1282	990
145°	1637	2112	1637	1509	1637	1024
155°	1944	2294	1944	1566	1944	894
165°	2149	2392	2149	1803	2149	605
175°	2247	2342	2247	2115	2247	213
180°	2254	2254	2254	2254	2254	



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1180.1	1187.0	1193.8	1192.2	1187.8	1185.7	1186.1	1186.8	1188.0	1189.2	1188.0
5°	1175.8	1184.4	1192.9	1191.7	1187.1	1185.1	1185.6	1187.1	1191.7	1196.2	1191.7
7.5°	1169.9	1178.6	1187.2	1186.8	1183.4	1182.6	1184.3	1186.7	1191.1	1195.5	1191.1
10°	1164.5	1173.5	1182.6	1182.6	1179.6	1179.3	1181.8	1184.7	1188.8	1192.8	1188.8
12.5°	1157.3	1166.7	1176.2	1176.9	1174.7	1175.0	1177.9	1181.1	1185.1	1189.2	1185.1
15°	1141.9	1151.9	1162.0	1164.1	1163.6	1165.1	1168.6	1171.9	1174.4	1176.9	1174.4
17.5°	1124.0	1134.0	1144.1	1146.1	1145.4	1145.5	1146.4	1147.4	1148.6	1149.8	1148.6
20°	1111.3	1121.4	1131.4	1132.8	1131.3	1128.8	1125.3	1122.6	1122.6	1122.6	1122.6
22.5°	1093.2	1104.1	1114.9	1115.0	1111.5	1104.9	1095.4	1087.4	1084.2	1081.0	1084.2
25°	1066.0	1076.6	1087.2	1082.3	1072.2	1057.4	1037.7	1021.1	1013.6	1006.1	1013.6
27.5°	1034.4	1042.9	1051.5	1038.7	1018.7	994.8	967.0	943.5	933.0	922.5	933.0
30°	1011.7	1018.3	1024.8	1004.6	975.4	945.5	914.8	889.2	879.2	869.1	879.2
32.5°	988.2	990.7	993.2	966.5	930.1	896.0	864.1	837.4	826.6	815.7	826.6
35°	949.5	945.0	940.4	905.0	859.2	820.2	788.0	761.5	751.9	742.4	751.9
37.5°	903.8	890.3	876.8	836.8	788.0	746.8	713.1	685.2	674.6	664.1	674.6
40°	870.3	851.1	832.0	789.2	738.4	696.1	662.4	634.5	623.9	613.4	623.9
42.5°	833.1	809.2	785.3	741.2	690.4	648.1	614.4	586.4	575.4	564.5	575.4
45°	771.8	743.6	715.5	669.6	617.8	575.5	542.8	515.7	505.1	494.5	505.1
47.5°	702.8	674.8	646.8	601.1	549.4	507.7	476.0	450.0	440.9	431.8	440.9
50°	653.0	625.8	598.7	554.9	505.6	465.1	433.4	406.9	395.8	384.8	395.8
52.5°	602.3	577.9	553.6	511.4	463.4	423.1	390.6	362.4	347.3	332.3	347.3
55°	533.0	509.9	486.7	447.0	401.7	361.0	324.8	295.5	286.9	278.4	286.9
57.5°	461.7	441.7	421.7	386.0	345.0	308.1	275.2	248.8	241.8	234.7	241.8
60°	416.5	398.9	381.2	347.0	307.3	273.6	246.0	223.4	216.4	209.4	216.4
62.5°	373.0	357.4	341.8	309.0	270.5	240.2	218.2	200.2	194.4	188.5	194.4
65°	307.8	296.2	284.7	257.6	225.5	200.3	182.2	167.4	162.3	157.3	162.3
67.5°	244.4	238.0	231.6	211.3	186.5	166.1	150.2	137.5	134.1	130.8	134.1
70°	203.7	201.7	199.7	183.0	161.3	144.0	130.9	120.5	117.9	115.4	117.9
72.5°	168.4	169.2	170.0	156.1	137.3	122.7	112.5	104.4	102.7	100.9	102.7
75°	120.0	124.0	128.0	118.8	105.2	94.9	87.9	82.4	81.4	80.3	81.4
77.5°	81.7	87.7	93.8	87.8	77.9	70.3	65.0	60.9	60.1	59.3	60.1
80°	60.0	66.0	72.1	67.9	60.4	54.6	50.5	47.5	47.5	47.5	47.5
82.5°	41.9	46.7	51.5	48.6	43.1	39.3	37.3	35.8	35.8	35.8	35.8
85°	20.4	22.9	25.4	24.5	22.5	20.0	17.0	14.6	14.1	13.6	14.1
87.5°	6.8	9.8	13.3	13.9	13.3	12.5	12.1	12.3	12.7	12.7	12.7
90°	6.8	15.9	27.3	36.4	43.3	45.5	45.5	47.8	50.1	50.1	50.1
92.5°	25.0	39.6	40.1	40.1	48.7	52.8	56.5	56.9	59.2	59.2	59.2
95°	70.6	77.4	116.1	113.8	77.4	61.5	52.4	52.4	52.4	52.4	52.4
97.5°	134.8	144.8	151.1	202.6	214.0	206.7	168.4	141.6	126.6	119.7	126.6
100°	191.2	195.8	209.4	211.7	268.6	323.2	295.9	261.8	250.4	243.6	250.4
102.5°	247.7	250.4	271.3	280.9	294.1	325.1	419.8	409.3	401.5	400.2	401.5
105°	332.3	334.6	373.3	391.5	400.6	400.6	398.4	443.9	516.7	532.7	516.7
107.5°	422.9	433.4	478.9	527.7	538.1	540.9	529.0	522.2	519.5	521.3	519.5
110°	484.9	500.8	555.4	616.9	632.8	637.4	632.8	626.0	621.4	621.4	621.4



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	545.0	568.2	630.1	700.7	727.5	741.2	731.2	726.1	721.6	725.2	721.6
115°	637.4	671.5	753.5	826.3	880.9	887.8	885.5	885.5	883.2	883.2	883.2
117.5°	723.0	777.6	869.6	954.2	1017.5	1035.7	1044.8	1042.1	1039.4	1043.9	1039.4
120°	783.1	846.8	951.5	1047.1	1108.6	1135.9	1145.0	1140.4	1145.0	1140.4	1145.0
122.5°	846.8	925.1	1028.0	1127.2	1199.6	1230.6	1241.5	1242.4	1243.3	1240.6	1243.3
125°	942.4	1038.0	1158.6	1261.1	1336.2	1372.6	1381.7	1384.0	1388.6	1399.9	1388.6
127.5°	1038.9	1147.3	1279.7	1378.5	1455.5	1499.6	1513.8	1518.8	1528.3	1533.3	1528.3
130°	1106.3	1229.2	1363.5	1456.8	1532.0	1579.8	1604.8	1611.6	1623.0	1620.7	1623.0
132.5°	1177.3	1305.7	1441.8	1538.8	1608.4	1659.9	1681.3	1700.9	1705.0	1708.2	1705.0
135°	1281.6	1420.4	1557.0	1652.6	1718.6	1768.7	1796.0	1814.2	1825.6	1832.4	1825.6
137.5°	1391.3	1537.9	1669.0	1754.1	1820.6	1863.9	1894.8	1913.9	1925.8	1931.2	1925.8
140°	1466.0	1607.1	1734.6	1823.3	1882.5	1925.8	1953.1	1975.8	1989.5	1989.5	1989.5
142.5°	1537.0	1676.3	1800.1	1888.9	1940.8	1980.4	2009.5	2026.8	2042.3	2042.3	2042.3
145°	1636.7	1775.5	1889.3	1978.1	2021.4	2057.8	2089.7	2103.3	2112.4	2112.4	2112.4
147.5°	1740.9	1863.9	1967.7	2052.8	2089.2	2132.0	2157.0	2168.0	2179.4	2174.3	2179.4
150°	1802.8	1916.7	2016.8	2096.5	2132.9	2173.9	2198.9	2208.0	2219.4	2212.6	2219.4
152.5°	1862.9	1971.3	2062.3	2136.6	2167.5	2208.5	2237.2	2246.3	2254.0	2249.0	2254.0
155°	1944.0	2039.6	2123.8	2192.1	2219.4	2258.1	2285.4	2296.8	2305.9	2294.5	2305.9
157.5°	2016.4	2098.8	2172.1	2234.9	2264.0	2297.3	2322.8	2336.9	2346.0	2341.0	2346.0
160°	2060.1	2135.2	2201.2	2260.4	2287.7	2317.3	2344.6	2360.5	2369.7	2362.8	2369.7
162.5°	2096.5	2164.3	2226.7	2280.4	2304.1	2330.0	2362.8	2376.9	2386.0	2377.4	2386.0
165°	2148.8	2203.5	2258.1	2303.6	2324.1	2344.6	2378.8	2394.7	2401.5	2392.4	2401.5
167.5°	2188.5	2230.3	2274.5	2313.7	2328.7	2348.7	2382.9	2396.1	2404.7	2393.3	2404.7
170°	2210.3	2246.7	2285.4	2317.3	2328.7	2346.9	2381.0	2392.4	2399.2	2387.9	2399.2
172.5°	2228.5	2255.8	2287.2	2315.5	2321.4	2336.0	2368.3	2379.7	2384.7	2375.1	2384.7
175°	2246.7	2262.7	2285.4	2303.6	2301.4	2310.5	2337.8	2346.9	2356.0	2342.3	2356.0
177.5°	2255.4	2262.7	2269.9	2280.9	2273.6	2273.6	2293.6	2299.1	2300.9	2293.6	2300.9
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1186.8	1186.1	1185.7	1187.8	1192.2	1193.8	1187.0	1180.1	1187.0	1193.8	1192.2
5°	1187.1	1185.6	1185.1	1187.1	1191.7	1192.9	1184.4	1175.8	1184.4	1192.9	1191.7
7.5°	1186.7	1184.3	1182.6	1183.4	1186.8	1187.2	1178.6	1169.9	1178.6	1187.2	1186.8
10°	1184.7	1181.8	1179.3	1179.6	1182.6	1182.6	1173.5	1164.5	1173.5	1182.6	1182.6
12.5°	1181.1	1177.9	1175.0	1174.7	1176.9	1176.2	1166.7	1157.3	1166.7	1176.2	1176.9
15°	1171.9	1168.6	1165.1	1163.6	1164.1	1162.0	1151.9	1141.9	1151.9	1162.0	1164.1
17.5°	1147.4	1146.4	1145.5	1145.4	1146.1	1144.1	1134.0	1124.0	1134.0	1144.1	1146.1
20°	1122.6	1125.3	1128.8	1131.3	1132.8	1131.4	1121.4	1111.3	1121.4	1131.4	1132.8
22.5°	1087.4	1095.4	1104.9	1111.5	1115.0	1114.9	1104.1	1093.2	1104.1	1114.9	1115.0
25°	1021.1	1037.7	1057.4	1072.2	1082.3	1087.2	1076.6	1066.0	1076.6	1087.2	1082.3
27.5°	943.5	967.0	994.8	1018.7	1038.7	1051.5	1042.9	1034.4	1042.9	1051.5	1038.7
30°	889.2	914.8	945.5	975.4	1004.6	1024.8	1018.3	1011.7	1018.3	1024.8	1004.6
32.5°	837.4	864.1	896.0	930.1	966.5	993.2	990.7	988.2	990.7	993.2	966.5
35°	761.5	788.0	820.2	859.2	905.0	940.4	945.0	949.5	945.0	940.4	905.0
37.5°	685.2	713.1	746.8	788.0	836.8	876.8	890.3	903.8	890.3	876.8	836.8
40°	634.5	662.4	696.1	738.4	789.2	832.0	851.1	870.3	851.1	832.0	789.2
42.5°	586.4	614.4	648.1	690.4	741.2	785.3	809.2	833.1	809.2	785.3	741.2
45°	515.7	542.8	575.5	617.8	669.6	715.5	743.6	771.8	743.6	715.5	669.6
47.5°	450.0	476.0	507.7	549.4	601.1	646.8	674.8	702.8	674.8	646.8	601.1
50°	406.9	433.4	465.1	505.6	554.9	598.7	625.8	653.0	625.8	598.7	554.9
52.5°	362.4	390.6	423.1	463.4	511.4	553.6	577.9	602.3	577.9	553.6	511.4
55°	295.5	324.8	361.0	401.7	447.0	486.7	509.9	533.0	509.9	486.7	447.0
57.5°	248.8	275.2	308.1	345.0	386.0	421.7	441.7	461.7	441.7	421.7	386.0
60°	223.4	246.0	273.6	307.3	347.0	381.2	398.9	416.5	398.9	381.2	347.0
62.5°	200.2	218.2	240.2	270.5	309.0	341.8	357.4	373.0	357.4	341.8	309.0
65°	167.4	182.2	200.3	225.5	257.6	284.7	296.2	307.8	296.2	284.7	257.6
67.5°	137.5	150.2	166.1	186.5	211.3	231.6	238.0	244.4	238.0	231.6	211.3
70°	120.5	130.9	144.0	161.3	183.0	199.7	201.7	203.7	201.7	199.7	183.0
72.5°	104.4	112.5	122.7	137.3	156.1	170.0	169.2	168.4	169.2	170.0	156.1
75°	82.4	87.9	94.9	105.2	118.8	128.0	124.0	120.0	124.0	128.0	118.8
77.5°	60.9	65.0	70.3	77.9	87.8	93.8	87.7	81.7	87.7	93.8	87.8
80°	47.5	50.5	54.6	60.4	67.9	72.1	66.0	60.0	66.0	72.1	67.9
82.5°	35.8	37.3	39.3	43.1	48.6	51.5	46.7	41.9	46.7	51.5	48.6
85°	14.6	17.0	20.0	22.5	24.5	25.4	22.9	20.4	22.9	25.4	24.5
87.5°	12.3	12.1	12.5	13.3	13.9	13.3	9.8	6.8	9.8	12.9	14.8
90°	47.8	45.5	45.5	43.3	36.4	27.3	15.9	6.8	15.9	25.0	41.0
92.5°	56.9	56.5	52.8	48.7	40.1	40.1	39.6	25.0	43.3	61.5	88.3
95°	52.4	52.4	61.5	77.4	113.8	116.1	77.4	70.6	100.2	141.1	177.6
97.5°	141.6	168.4	206.7	214.0	202.6	151.1	144.8	134.8	183.5	224.0	282.7
100°	261.8	295.9	323.2	268.6	211.7	209.4	195.8	191.2	243.6	282.3	339.2
102.5°	409.3	419.8	325.1	294.1	280.9	271.3	250.4	247.7	300.0	353.3	401.1
105°	443.9	398.4	400.6	400.6	391.5	373.3	334.6	332.3	391.5	453.0	512.2
107.5°	522.2	529.0	540.9	538.1	527.7	478.9	433.4	422.9	476.2	550.0	615.1
110°	626.0	632.8	637.4	632.8	616.9	555.4	500.8	484.9	532.7	610.1	680.6



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	726.1	731.2	741.2	727.5	700.7	630.1	568.2	545.0	592.8	672.0	744.4
115°	885.5	885.5	887.8	880.9	826.3	753.5	671.5	637.4	678.3	751.2	830.9
117.5°	1042.1	1044.8	1035.7	1017.5	954.2	869.6	777.6	723.0	755.3	832.2	914.2
120°	1140.4	1145.0	1135.9	1108.6	1047.1	951.5	846.8	783.1	808.1	883.2	965.2
122.5°	1242.4	1241.5	1230.6	1199.6	1127.2	1028.0	925.1	846.8	857.3	926.9	1007.0
125°	1384.0	1381.7	1372.6	1336.2	1261.1	1158.6	1038.0	942.4	928.7	987.9	1069.9
127.5°	1518.8	1513.8	1499.6	1455.5	1378.5	1279.7	1147.3	1038.9	1008.4	1045.7	1120.9
130°	1611.6	1604.8	1579.8	1532.0	1456.8	1363.5	1229.2	1106.3	1063.0	1085.8	1151.8
132.5°	1700.9	1681.3	1659.9	1608.4	1538.8	1441.8	1305.7	1177.3	1117.7	1127.7	1179.1
135°	1814.2	1796.0	1768.7	1718.6	1652.6	1557.0	1420.4	1281.6	1199.6	1190.5	1220.1
137.5°	1913.9	1894.8	1863.9	1820.6	1754.1	1669.0	1537.9	1391.3	1287.9	1257.4	1268.8
140°	1975.8	1953.1	1925.8	1882.5	1823.3	1734.6	1607.1	1466.0	1349.9	1306.6	1299.8
142.5°	2026.8	2009.5	1980.4	1940.8	1888.9	1800.1	1676.3	1537.0	1413.6	1357.6	1341.7
145°	2103.3	2089.7	2057.8	2021.4	1978.1	1889.3	1775.5	1636.7	1513.8	1440.9	1406.8
147.5°	2168.0	2157.0	2132.0	2089.2	2052.8	1967.7	1863.9	1740.9	1614.8	1524.7	1480.5
150°	2208.0	2198.9	2173.9	2132.9	2096.5	2016.8	1916.7	1802.8	1682.2	1586.6	1529.7
152.5°	2246.3	2237.2	2208.5	2167.5	2136.6	2062.3	1971.3	1862.9	1740.5	1644.9	1586.1
155°	2296.8	2285.4	2258.1	2219.4	2192.1	2123.8	2039.6	1944.0	1839.3	1739.1	1673.1
157.5°	2336.9	2322.8	2297.3	2264.0	2234.9	2172.1	2098.8	2016.4	1924.9	1829.3	1761.9
160°	2360.5	2344.6	2317.3	2287.7	2260.4	2201.2	2135.2	2060.1	1975.8	1889.3	1816.5
162.5°	2376.9	2362.8	2330.0	2304.1	2280.4	2226.7	2164.3	2096.5	2021.4	1945.8	1878.4
165°	2394.7	2378.8	2344.6	2324.1	2303.6	2258.1	2203.5	2148.8	2085.1	2023.7	1969.0
167.5°	2396.1	2382.9	2348.7	2328.7	2313.7	2274.5	2230.3	2188.5	2138.8	2090.6	2045.0
170°	2392.4	2381.0	2346.9	2328.7	2317.3	2285.4	2246.7	2210.3	2171.6	2130.6	2094.2
172.5°	2379.7	2368.3	2336.0	2321.4	2315.5	2287.2	2255.8	2228.5	2195.3	2165.2	2136.1
175°	2346.9	2337.8	2310.5	2301.4	2303.6	2285.4	2262.7	2246.7	2226.2	2208.0	2192.1
177.5°	2299.1	2293.6	2273.6	2273.6	2280.9	2269.9	2262.7	2255.4	2246.3	2240.8	2235.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1187.8	1185.7	1186.1	1186.8	1188.0	1189.2	1188.0	1186.8	1186.1	1185.7	1187.8
5°	1187.1	1185.1	1185.6	1187.1	1191.7	1196.2	1191.7	1187.1	1185.6	1185.1	1187.1
7.5°	1183.4	1182.6	1184.3	1186.7	1191.1	1195.5	1191.1	1186.7	1184.3	1182.6	1183.4
10°	1179.6	1179.3	1181.8	1184.7	1188.8	1192.8	1188.8	1184.7	1181.8	1179.3	1179.6
12.5°	1174.7	1175.0	1177.9	1181.1	1185.1	1189.2	1185.1	1181.1	1177.9	1175.0	1174.7
15°	1163.6	1165.1	1168.6	1171.9	1174.4	1176.9	1174.4	1171.9	1168.6	1165.1	1163.6
17.5°	1145.4	1145.5	1146.4	1147.4	1148.6	1149.8	1148.6	1147.4	1146.4	1145.5	1145.4
20°	1131.3	1128.8	1125.3	1122.6	1122.6	1122.6	1122.6	1122.6	1125.3	1128.8	1131.3
22.5°	1111.5	1104.9	1095.4	1087.4	1084.2	1081.0	1084.2	1087.4	1095.4	1104.9	1111.5
25°	1072.2	1057.4	1037.7	1021.1	1013.6	1006.1	1013.6	1021.1	1037.7	1057.4	1072.2
27.5°	1018.7	994.8	967.0	943.5	933.0	922.5	933.0	943.5	967.0	994.8	1018.7
30°	975.4	945.5	914.8	889.2	879.2	869.1	879.2	889.2	914.8	945.5	975.4
32.5°	930.1	896.0	864.1	837.4	826.6	815.7	826.6	837.4	864.1	896.0	930.1
35°	859.2	820.2	788.0	761.5	751.9	742.4	751.9	761.5	788.0	820.2	859.2
37.5°	788.0	746.8	713.1	685.2	674.6	664.1	674.6	685.2	713.1	746.8	788.0
40°	738.4	696.1	662.4	634.5	623.9	613.4	623.9	634.5	662.4	696.1	738.4
42.5°	690.4	648.1	614.4	586.4	575.4	564.5	575.4	586.4	614.4	648.1	690.4
45°	617.8	575.5	542.8	515.7	505.1	494.5	505.1	515.7	542.8	575.5	617.8
47.5°	549.4	507.7	476.0	450.0	440.9	431.8	440.9	450.0	476.0	507.7	549.4
50°	505.6	465.1	433.4	406.9	395.8	384.8	395.8	406.9	433.4	465.1	505.6
52.5°	463.4	423.1	390.6	362.4	347.3	332.3	347.3	362.4	390.6	423.1	463.4
55°	401.7	361.0	324.8	295.5	286.9	278.4	286.9	295.5	324.8	361.0	401.7
57.5°	345.0	308.1	275.2	248.8	241.8	234.7	241.8	248.8	275.2	308.1	345.0
60°	307.3	273.6	246.0	223.4	216.4	209.4	216.4	223.4	246.0	273.6	307.3
62.5°	270.5	240.2	218.2	200.2	194.4	188.5	194.4	200.2	218.2	240.2	270.5
65°	225.5	200.3	182.2	167.4	162.3	157.3	162.3	167.4	182.2	200.3	225.5
67.5°	186.5	166.1	150.2	137.5	134.1	130.8	134.1	137.5	150.2	166.1	186.5
70°	161.3	144.0	130.9	120.5	117.9	115.4	117.9	120.5	130.9	144.0	161.3
72.5°	137.3	122.7	112.5	104.4	102.7	100.9	102.7	104.4	112.5	122.7	137.3
75°	105.2	94.9	87.9	82.4	81.4	80.3	81.4	82.4	87.9	94.9	105.2
77.5°	77.9	70.3	65.0	60.9	60.1	59.3	60.1	60.9	65.0	70.3	77.9
80°	60.4	54.6	50.5	47.5	47.5	47.5	47.5	47.5	50.5	54.6	60.4
82.5°	43.1	39.3	37.3	35.8	35.8	35.8	35.8	35.8	37.3	39.3	43.1
85°	22.5	20.0	17.0	14.6	14.1	13.6	14.1	14.6	17.0	20.0	22.5
87.5°	15.1	17.1	19.9	21.4	23.2	22.3	23.2	21.4	19.9	17.1	15.1
90°	52.4	68.3	84.2	93.3	102.4	97.9	102.4	93.3	84.2	68.3	52.4
92.5°	105.2	132.0	151.6	168.0	175.3	174.4	175.3	168.0	151.6	132.0	105.2
95°	211.7	243.6	275.4	298.2	311.9	307.3	311.9	298.2	275.4	243.6	211.7
97.5°	326.4	369.2	404.7	426.1	439.8	448.9	439.8	426.1	404.7	369.2	326.4
100°	402.9	443.9	484.9	509.9	532.7	541.8	532.7	509.9	484.9	443.9	402.9
102.5°	464.8	518.5	563.2	590.0	609.1	618.2	609.1	590.0	563.2	518.5	464.8
105°	566.8	623.7	671.5	705.7	726.1	733.0	726.1	705.7	671.5	623.7	566.8
107.5°	668.8	727.5	771.7	809.5	834.5	849.1	834.5	809.5	771.7	727.5	668.8
110°	748.9	796.7	844.5	878.7	903.7	912.8	903.7	878.7	844.5	796.7	748.9



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	816.3	869.6	917.4	951.5	980.2	992.9	980.2	951.5	917.4	869.6	816.3
115°	910.5	981.1	1024.3	1056.2	1076.7	1088.1	1076.7	1056.2	1024.3	981.1	910.5
117.5°	988.8	1062.6	1109.9	1134.5	1144.1	1152.3	1144.1	1134.5	1109.9	1062.6	988.8
120°	1038.0	1106.3	1160.9	1192.8	1204.2	1208.7	1204.2	1192.8	1160.9	1106.3	1038.0
122.5°	1083.5	1148.2	1201.0	1240.1	1258.8	1263.4	1258.8	1240.1	1201.0	1148.2	1083.5
125°	1147.3	1208.7	1263.4	1302.1	1322.5	1333.9	1322.5	1302.1	1263.4	1208.7	1147.3
127.5°	1202.8	1269.3	1319.4	1354.4	1374.4	1383.5	1374.4	1354.4	1319.4	1269.3	1202.8
130°	1233.8	1302.1	1352.1	1390.8	1409.0	1418.1	1409.0	1390.8	1352.1	1302.1	1233.8
132.5°	1257.4	1329.4	1381.3	1416.3	1436.4	1445.5	1436.4	1416.3	1381.3	1329.4	1257.4
135°	1286.1	1361.2	1415.9	1450.0	1468.2	1477.3	1468.2	1450.0	1415.9	1361.2	1286.1
137.5°	1311.2	1379.5	1436.4	1472.3	1488.7	1494.6	1488.7	1472.3	1436.4	1379.5	1311.2
140°	1329.4	1388.6	1445.5	1479.6	1497.8	1500.1	1497.8	1479.6	1445.5	1388.6	1329.4
142.5°	1353.0	1399.5	1449.1	1483.3	1501.5	1505.6	1501.5	1483.3	1449.1	1399.5	1353.0
145°	1395.4	1422.7	1456.8	1488.7	1504.6	1509.2	1504.6	1488.7	1456.8	1422.7	1395.4
147.5°	1448.7	1457.3	1475.1	1496.0	1511.5	1514.7	1511.5	1496.0	1475.1	1457.3	1448.7
150°	1488.7	1486.4	1493.3	1506.9	1520.6	1518.3	1520.6	1506.9	1493.3	1486.4	1488.7
152.5°	1534.2	1521.0	1520.6	1527.0	1533.3	1532.9	1533.3	1527.0	1520.6	1521.0	1534.2
155°	1611.6	1586.6	1572.9	1568.4	1568.4	1566.1	1568.4	1568.4	1572.9	1586.6	1611.6
157.5°	1696.8	1661.7	1641.2	1630.3	1627.1	1622.1	1627.1	1630.3	1641.2	1661.7	1696.8
160°	1755.0	1716.3	1695.9	1677.6	1670.8	1664.0	1670.8	1677.6	1695.9	1716.3	1755.0
162.5°	1809.7	1772.8	1750.5	1734.1	1727.3	1716.8	1727.3	1734.1	1750.5	1772.8	1809.7
165°	1898.5	1859.8	1834.7	1821.1	1812.0	1802.8	1812.0	1821.1	1834.7	1859.8	1898.5
167.5°	1987.2	1944.9	1928.5	1913.0	1904.4	1888.0	1904.4	1913.0	1928.5	1944.9	1987.2
170°	2041.9	2003.2	1994.1	1980.4	1964.5	1946.3	1964.5	1980.4	1994.1	2003.2	2041.9
172.5°	2089.2	2063.3	2054.2	2040.5	2035.5	2020.9	2035.5	2040.5	2054.2	2063.3	2089.2
175°	2158.0	2137.5	2137.5	2135.2	2128.4	2114.7	2128.4	2135.2	2137.5	2137.5	2158.0
177.5°	2215.3	2204.4	2211.7	2211.7	2209.9	2197.1	2209.9	2211.7	2211.7	2204.4	2215.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1188.3	1188.3	1188.3	1188.3
2.5°	1192.2	1193.8	1187.0	1180.1
5°	1191.7	1192.9	1184.4	1175.8
7.5°	1186.8	1187.2	1178.6	1169.9
10°	1182.6	1182.6	1173.5	1164.5
12.5°	1176.9	1176.2	1166.7	1157.3
15°	1164.1	1162.0	1151.9	1141.9
17.5°	1146.1	1144.1	1134.0	1124.0
20°	1132.8	1131.4	1121.4	1111.3
22.5°	1115.0	1114.9	1104.1	1093.2
25°	1082.3	1087.2	1076.6	1066.0
27.5°	1038.7	1051.5	1042.9	1034.4
30°	1004.6	1024.8	1018.3	1011.7
32.5°	966.5	993.2	990.7	988.2
35°	905.0	940.4	945.0	949.5
37.5°	836.8	876.8	890.3	903.8
40°	789.2	832.0	851.1	870.3
42.5°	741.2	785.3	809.2	833.1
45°	669.6	715.5	743.6	771.8
47.5°	601.1	646.8	674.8	702.8
50°	554.9	598.7	625.8	653.0
52.5°	511.4	553.6	577.9	602.3
55°	447.0	486.7	509.9	533.0
57.5°	386.0	421.7	441.7	461.7
60°	347.0	381.2	398.9	416.5
62.5°	309.0	341.8	357.4	373.0
65°	257.6	284.7	296.2	307.8
67.5°	211.3	231.6	238.0	244.4
70°	183.0	199.7	201.7	203.7
72.5°	156.1	170.0	169.2	168.4
75°	118.8	128.0	124.0	120.0
77.5°	87.8	93.8	87.7	81.7
80°	67.9	72.1	66.0	60.0
82.5°	48.6	51.5	46.7	41.9
85°	24.5	25.4	22.9	20.4
87.5°	14.8	12.9	9.8	6.8
90°	41.0	25.0	15.9	6.8
92.5°	88.3	61.5	43.3	25.0
95°	177.6	141.1	100.2	70.6
97.5°	282.7	224.0	183.5	134.8
100°	339.2	282.3	243.6	191.2
102.5°	401.1	353.3	300.0	247.7
105°	512.2	453.0	391.5	332.3
107.5°	615.1	550.0	476.2	422.9
110°	680.6	610.1	532.7	484.9



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	744.4	672.0	592.8	545.0
115°	830.9	751.2	678.3	637.4
117.5°	914.2	832.2	755.3	723.0
120°	965.2	883.2	808.1	783.1
122.5°	1007.0	926.9	857.3	846.8
125°	1069.9	987.9	928.7	942.4
127.5°	1120.9	1045.7	1008.4	1038.9
130°	1151.8	1085.8	1063.0	1106.3
132.5°	1179.1	1127.7	1117.7	1177.3
135°	1220.1	1190.5	1199.6	1281.6
137.5°	1268.8	1257.4	1287.9	1391.3
140°	1299.8	1306.6	1349.9	1466.0
142.5°	1341.7	1357.6	1413.6	1537.0
145°	1406.8	1440.9	1513.8	1636.7
147.5°	1480.5	1524.7	1614.8	1740.9
150°	1529.7	1586.6	1682.2	1802.8
152.5°	1586.1	1644.9	1740.5	1862.9
155°	1673.1	1739.1	1839.3	1944.0
157.5°	1761.9	1829.3	1924.9	2016.4
160°	1816.5	1889.3	1975.8	2060.1
162.5°	1878.4	1945.8	2021.4	2096.5
165°	1969.0	2023.7	2085.1	2148.8
167.5°	2045.0	2090.6	2138.8	2188.5
170°	2094.2	2130.6	2171.6	2210.3
172.5°	2136.1	2165.2	2195.3	2228.5
175°	2192.1	2208.0	2226.2	2246.7
177.5°	2235.3	2240.8	2246.3	2255.4
180°	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428468

CATALOG NUMBER: SQ2W-PW1-K-150U-050D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.75	15.43	15.88	16.55	18.10	11.00	11.68	12.13	12.79	14.34
	3H	16.04	16.65	17.17	17.77	19.34	12.26	12.86	13.39	13.99	15.55
	4H	16.44	17.02	17.58	18.14	19.71	12.75	13.33	13.90	14.45	16.02
	6H	16.61	17.14	17.76	18.27	19.85	13.05	13.58	14.20	14.71	16.29
	8H	16.65	17.15	17.80	18.29	19.87	13.16	13.67	14.32	14.81	16.38
	12H	16.64	17.12	17.80	18.26	19.85	13.19	13.66	14.34	14.80	16.40
4H	2H	14.86	15.44	16.01	16.56	18.13	11.79	12.36	12.94	13.49	15.06
	3H	16.38	16.86	17.54	18.01	19.59	13.22	13.70	14.37	14.85	16.43
	4H	16.92	17.36	18.08	18.50	20.10	13.79	14.23	14.95	15.37	16.97
	6H	17.22	17.60	18.39	18.76	20.35	14.16	14.54	15.33	15.70	17.29
	8H	17.31	17.66	18.48	18.82	20.43	14.31	14.66	15.47	15.82	17.42
	12H	17.33	17.64	18.50	18.81	20.42	14.35	14.66	15.52	15.83	17.44
8H	4H	16.95	17.30	18.11	18.45	20.06	14.12	14.47	15.28	15.62	17.23
	6H	17.36	17.65	18.55	18.85	20.45	14.61	14.89	15.79	16.09	17.70
	8H	17.53	17.79	18.72	18.96	20.59	14.82	15.08	16.01	16.25	17.88
	12H	17.60	17.83	18.80	19.00	20.66	14.90	15.12	16.09	16.29	17.95
12H	4H	16.90	17.22	18.08	18.38	20.00	14.13	14.45	15.31	15.61	17.23
	6H	17.36	17.61	18.55	18.78	20.41	14.68	14.93	15.87	16.11	17.73
	8H	17.54	17.76	18.73	18.93	20.59	14.92	15.14	16.11	16.31	17.97