

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428474

Luminaire Tested: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428474
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10392.9 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	25	21
5	67	56	48	43	61	51	44	39	42	37	33	34	30	27	26	23	22	18
6	62	50	43	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	22	19	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27675	27675	27675	27675
5°	27491	27967	27491	27967
10°	27541	28210	27541	28210
15°	27533	28379	27533	28379
20°	27544	27826	27544	27826
25°	27395	25854	27395	25854
30°	27210	23375	27210	23375
35°	26997	21108	26997	21108
40°	26459	18649	26459	18649
45°	25423	16289	25423	16289
50°	23661	13943	23661	13943
55°	21644	11305	21644	11305
60°	19400	9752	19400	9752
65°	16962	8668	16962	8668
70°	13874	7860	13874	7860
75°	10792	7230	10792	7230
80°	8043	6378	8043	6378
85°	5446	3631	5446	3631

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25423 cd/sqm



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.2	1.6
10°-20°	472.9	4.6
20°-30°	696.0	6.7
30°-40°	761.0	7.3
40°-50°	682.7	6.6
50°-60°	509.2	4.9
60°-70°	321.8	3.1
70°-80°	159.5	1.5
80°-90°	46.6	0.4
90°-100°	179.4	1.7
100°-110°	523.0	5.0
110°-120°	853.6	8.2
120°-130°	1083.1	10.4
130°-140°	1158.9	11.2
140°-150°	1082.2	10.4
150°-160°	890.5	8.6
160°-170°	597.2	5.7
170°-180°	212.1	2.0
0°-30°	1332.1	12.8
0°-40°	2093.1	20.1
0°-60°	3285.0	31.6
0°-90°	3812.9	36.7
90°-120°	1556.0	15.0
90°-150°	4880.2	47.0
90°-180°	6580.0	63.3
0°-180°	10392.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1714	1714	1714	1714	1714	
5°	1696	1726	1696	1726	1696	161
15°	1647	1698	1647	1698	1647	465
25°	1538	1451	1538	1451	1538	708
35°	1370	1071	1370	1071	1370	854
45°	1113	713	1113	713	1113	854
55°	769	402	769	402	769	687
65°	444	227	444	227	444	440
75°	173	116	173	116	173	191
85°	29	20	29	20	29	37
90°	7	50	7	98	7	7
95°	71	52	71	307	71	85
105°	332	533	332	733	332	353
115°	637	883	637	1088	637	628
125°	942	1400	942	1334	942	843
135°	1282	1832	1282	1477	1282	990
145°	1637	2112	1637	1509	1637	1024
155°	1944	2294	1944	1566	1944	894
165°	2149	2392	2149	1803	2149	605
175°	2247	2342	2247	2115	2247	213
180°	2254	2254	2254	2254	2254	



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1702.4	1712.3	1722.1	1719.8	1713.4	1710.5	1711.1	1712.0	1713.7	1715.5	1713.7
5°	1696.2	1708.5	1720.9	1719.0	1712.5	1709.6	1710.3	1712.5	1719.0	1725.6	1719.0
7.5°	1687.7	1700.2	1712.7	1712.1	1707.1	1705.9	1708.4	1711.8	1718.2	1724.6	1718.2
10°	1679.9	1692.9	1706.0	1706.0	1701.6	1701.3	1704.9	1709.1	1714.9	1720.7	1714.9
12.5°	1669.4	1683.1	1696.7	1697.7	1694.5	1695.0	1699.2	1703.8	1709.6	1715.5	1709.6
15°	1647.2	1661.7	1676.2	1679.3	1678.6	1680.8	1685.8	1690.6	1694.2	1697.8	1694.2
17.5°	1621.4	1635.9	1650.4	1653.3	1652.3	1652.4	1653.7	1655.2	1656.9	1658.6	1656.9
20°	1603.1	1617.6	1632.2	1634.2	1632.0	1628.3	1623.3	1619.5	1619.5	1619.5	1619.5
22.5°	1577.0	1592.7	1608.4	1608.5	1603.4	1594.0	1580.2	1568.7	1564.0	1559.4	1564.0
25°	1537.8	1553.1	1568.3	1561.2	1546.7	1525.3	1497.0	1473.1	1462.2	1451.3	1462.2
27.5°	1492.1	1504.5	1516.8	1498.3	1469.6	1435.1	1394.9	1361.0	1345.9	1330.8	1345.9
30°	1459.5	1468.9	1478.3	1449.1	1407.1	1363.9	1319.6	1282.8	1268.3	1253.8	1268.3
32.5°	1425.5	1429.1	1432.8	1394.3	1341.8	1292.5	1246.5	1208.1	1192.4	1176.7	1192.4
35°	1369.7	1363.2	1356.6	1305.5	1239.4	1183.2	1136.8	1098.5	1084.7	1070.9	1084.7
37.5°	1303.7	1284.3	1264.8	1207.2	1136.8	1077.3	1028.7	988.4	973.2	958.0	973.2
40°	1255.4	1227.8	1200.3	1138.4	1065.1	1004.2	955.6	915.3	900.1	884.8	900.1
42.5°	1201.9	1167.3	1132.8	1069.2	995.9	935.0	886.3	845.9	830.1	814.3	830.1
45°	1113.4	1072.7	1032.1	965.9	891.2	830.2	783.1	743.9	728.6	713.4	728.6
47.5°	1013.8	973.5	933.1	867.1	792.5	732.3	686.6	649.1	636.0	623.0	636.0
50°	942.0	902.8	863.6	800.5	729.4	671.0	625.3	587.0	571.0	555.1	571.0
52.5°	868.8	833.7	798.6	737.8	668.4	610.3	563.4	522.8	501.1	479.3	501.1
55°	768.9	735.5	702.2	644.8	579.5	520.8	468.5	426.3	413.9	401.6	413.9
57.5°	666.1	637.2	608.3	556.8	497.7	444.5	397.0	358.9	348.7	338.6	348.7
60°	600.8	575.4	550.0	500.6	443.3	394.7	354.8	322.3	312.2	302.0	312.2
62.5°	538.1	515.6	493.1	445.8	390.2	346.5	314.7	288.8	280.4	272.0	280.4
65°	444.0	427.4	410.7	371.7	325.2	289.0	262.8	241.4	234.2	226.9	234.2
67.5°	352.6	343.3	334.0	304.8	269.0	239.6	216.7	198.3	193.5	188.7	193.5
70°	293.9	291.0	288.0	263.9	232.7	207.7	188.8	173.8	170.1	166.5	170.1
72.5°	242.9	244.1	245.2	225.2	198.0	177.1	162.3	150.6	148.1	145.6	148.1
75°	173.0	178.9	184.7	171.4	151.8	137.0	126.8	118.8	117.4	115.9	117.4
77.5°	117.9	126.6	135.3	126.7	112.3	101.4	93.8	87.9	86.7	85.5	86.7
80°	86.5	95.2	103.9	98.0	87.1	78.7	72.9	68.6	68.6	68.6	68.6
82.5°	60.4	67.4	74.3	70.1	62.1	56.7	53.8	51.6	51.6	51.6	51.6
85°	29.4	33.0	36.6	35.4	32.5	28.8	24.5	21.0	20.3	19.6	20.3
87.5°	9.2	12.8	16.8	16.9	15.3	14.0	13.5	13.5	13.9	13.9	13.9
90°	6.8	15.9	27.3	36.4	43.3	45.5	45.5	47.8	50.1	50.1	50.1
92.5°	25.0	39.6	40.1	40.1	48.7	52.8	56.5	56.9	59.2	59.2	59.2
95°	70.6	77.4	116.1	113.8	77.4	61.5	52.4	52.4	52.4	52.4	52.4
97.5°	134.8	144.8	151.1	202.6	214.0	206.7	168.4	141.6	126.6	119.7	126.6
100°	191.2	195.8	209.4	211.7	268.6	323.2	295.9	261.8	250.4	243.6	250.4
102.5°	247.7	250.4	271.3	280.9	294.1	325.1	419.8	409.3	401.5	400.2	401.5
105°	332.3	334.6	373.3	391.5	400.6	400.6	398.4	443.9	516.7	532.7	516.7
107.5°	422.9	433.4	478.9	527.7	538.1	540.9	529.0	522.2	519.5	521.3	519.5
110°	484.9	500.8	555.4	616.9	632.8	637.4	632.8	626.0	621.4	621.4	621.4



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	545.0	568.2	630.1	700.7	727.5	741.2	731.2	726.1	721.6	725.2	721.6
115°	637.4	671.5	753.5	826.3	880.9	887.8	885.5	885.5	883.2	883.2	883.2
117.5°	723.0	777.6	869.6	954.2	1017.5	1035.7	1044.8	1042.1	1039.4	1043.9	1039.4
120°	783.1	846.8	951.5	1047.1	1108.6	1135.9	1145.0	1140.4	1145.0	1140.4	1145.0
122.5°	846.8	925.1	1028.0	1127.2	1199.6	1230.6	1241.5	1242.4	1243.3	1240.6	1243.3
125°	942.4	1038.0	1158.6	1261.1	1336.2	1372.6	1381.7	1384.0	1388.6	1399.9	1388.6
127.5°	1038.9	1147.3	1279.7	1378.5	1455.5	1499.6	1513.8	1518.8	1528.3	1533.3	1528.3
130°	1106.3	1229.2	1363.5	1456.8	1532.0	1579.8	1604.8	1611.6	1623.0	1620.7	1623.0
132.5°	1177.3	1305.7	1441.8	1538.8	1608.4	1659.9	1681.3	1700.9	1705.0	1708.2	1705.0
135°	1281.6	1420.4	1557.0	1652.6	1718.6	1768.7	1796.0	1814.2	1825.6	1832.4	1825.6
137.5°	1391.3	1537.9	1669.0	1754.1	1820.6	1863.9	1894.8	1913.9	1925.8	1931.2	1925.8
140°	1466.0	1607.1	1734.6	1823.3	1882.5	1925.8	1953.1	1975.8	1989.5	1989.5	1989.5
142.5°	1537.0	1676.3	1800.1	1888.9	1940.8	1980.4	2009.5	2026.8	2042.3	2042.3	2042.3
145°	1636.7	1775.5	1889.3	1978.1	2021.4	2057.8	2089.7	2103.3	2112.4	2112.4	2112.4
147.5°	1740.9	1863.9	1967.7	2052.8	2089.2	2132.0	2157.0	2168.0	2179.4	2174.3	2179.4
150°	1802.8	1916.7	2016.8	2096.5	2132.9	2173.9	2198.9	2208.0	2219.4	2212.6	2219.4
152.5°	1862.9	1971.3	2062.3	2136.6	2167.5	2208.5	2237.2	2246.3	2254.0	2249.0	2254.0
155°	1944.0	2039.6	2123.8	2192.1	2219.4	2258.1	2285.4	2296.8	2305.9	2294.5	2305.9
157.5°	2016.4	2098.8	2172.1	2234.9	2264.0	2297.3	2322.8	2336.9	2346.0	2341.0	2346.0
160°	2060.1	2135.2	2201.2	2260.4	2287.7	2317.3	2344.6	2360.5	2369.7	2362.8	2369.7
162.5°	2096.5	2164.3	2226.7	2280.4	2304.1	2330.0	2362.8	2376.9	2386.0	2377.4	2386.0
165°	2148.8	2203.5	2258.1	2303.6	2324.1	2344.6	2378.8	2394.7	2401.5	2392.4	2401.5
167.5°	2188.5	2230.3	2274.5	2313.7	2328.7	2348.7	2382.9	2396.1	2404.7	2393.3	2404.7
170°	2210.3	2246.7	2285.4	2317.3	2328.7	2346.9	2381.0	2392.4	2399.2	2387.9	2399.2
172.5°	2228.5	2255.8	2287.2	2315.5	2321.4	2336.0	2368.3	2379.7	2384.7	2375.1	2384.7
175°	2246.7	2262.7	2285.4	2303.6	2301.4	2310.5	2337.8	2346.9	2356.0	2342.3	2356.0
177.5°	2255.4	2262.7	2269.9	2280.9	2273.6	2273.6	2293.6	2299.1	2300.9	2293.6	2300.9
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1712.0	1711.1	1710.5	1713.4	1719.8	1722.1	1712.3	1702.4	1712.3	1722.1	1719.8
5°	1712.5	1710.3	1709.6	1712.5	1719.0	1720.9	1708.5	1696.2	1708.5	1720.9	1719.0
7.5°	1711.8	1708.4	1705.9	1707.1	1712.1	1712.7	1700.2	1687.7	1700.2	1712.7	1712.1
10°	1709.1	1704.9	1701.3	1701.6	1706.0	1706.0	1692.9	1679.9	1692.9	1706.0	1706.0
12.5°	1703.8	1699.2	1695.0	1694.5	1697.7	1696.7	1683.1	1669.4	1683.1	1696.7	1697.7
15°	1690.6	1685.8	1680.8	1678.6	1679.3	1676.2	1661.7	1647.2	1661.7	1676.2	1679.3
17.5°	1655.2	1653.7	1652.4	1652.3	1653.3	1650.4	1635.9	1621.4	1635.9	1650.4	1653.3
20°	1619.5	1623.3	1628.3	1632.0	1634.2	1632.2	1617.6	1603.1	1617.6	1632.2	1634.2
22.5°	1568.7	1580.2	1594.0	1603.4	1608.5	1608.4	1592.7	1577.0	1592.7	1608.4	1608.5
25°	1473.1	1497.0	1525.3	1546.7	1561.2	1568.3	1553.1	1537.8	1553.1	1568.3	1561.2
27.5°	1361.0	1394.9	1435.1	1469.6	1498.3	1516.8	1504.5	1492.1	1504.5	1516.8	1498.3
30°	1282.8	1319.6	1363.9	1407.1	1449.1	1478.3	1468.9	1459.5	1468.9	1478.3	1449.1
32.5°	1208.1	1246.5	1292.5	1341.8	1394.3	1432.8	1429.1	1425.5	1429.1	1432.8	1394.3
35°	1098.5	1136.8	1183.2	1239.4	1305.5	1356.6	1363.2	1369.7	1363.2	1356.6	1305.5
37.5°	988.4	1028.7	1077.3	1136.8	1207.2	1264.8	1284.3	1303.7	1284.3	1264.8	1207.2
40°	915.3	955.6	1004.2	1065.1	1138.4	1200.3	1227.8	1255.4	1227.8	1200.3	1138.4
42.5°	845.9	886.3	935.0	995.9	1069.2	1132.8	1167.3	1201.9	1167.3	1132.8	1069.2
45°	743.9	783.1	830.2	891.2	965.9	1032.1	1072.7	1113.4	1072.7	1032.1	965.9
47.5°	649.1	686.6	732.3	792.5	867.1	933.1	973.5	1013.8	973.5	933.1	867.1
50°	587.0	625.3	671.0	729.4	800.5	863.6	902.8	942.0	902.8	863.6	800.5
52.5°	522.8	563.4	610.3	668.4	737.8	798.6	833.7	868.8	833.7	798.6	737.8
55°	426.3	468.5	520.8	579.5	644.8	702.2	735.5	768.9	735.5	702.2	644.8
57.5°	358.9	397.0	444.5	497.7	556.8	608.3	637.2	666.1	637.2	608.3	556.8
60°	322.3	354.8	394.7	443.3	500.6	550.0	575.4	600.8	575.4	550.0	500.6
62.5°	288.8	314.7	346.5	390.2	445.8	493.1	515.6	538.1	515.6	493.1	445.8
65°	241.4	262.8	289.0	325.2	371.7	410.7	427.4	444.0	427.4	410.7	371.7
67.5°	198.3	216.7	239.6	269.0	304.8	334.0	343.3	352.6	343.3	334.0	304.8
70°	173.8	188.8	207.7	232.7	263.9	288.0	291.0	293.9	291.0	288.0	263.9
72.5°	150.6	162.3	177.1	198.0	225.2	245.2	244.1	242.9	244.1	245.2	225.2
75°	118.8	126.8	137.0	151.8	171.4	184.7	178.9	173.0	178.9	184.7	171.4
77.5°	87.9	93.8	101.4	112.3	126.7	135.3	126.6	117.9	126.6	135.3	126.7
80°	68.6	72.9	78.7	87.1	98.0	103.9	95.2	86.5	95.2	103.9	98.0
82.5°	51.6	53.8	56.7	62.1	70.1	74.3	67.4	60.4	67.4	74.3	70.1
85°	21.0	24.5	28.8	32.5	35.4	36.6	33.0	29.4	33.0	36.6	35.4
87.5°	13.5	13.5	14.0	15.3	16.9	16.8	12.8	9.2	12.8	16.3	17.8
90°	47.8	45.5	45.5	43.3	36.4	27.3	15.9	6.8	15.9	25.0	41.0
92.5°	56.9	56.5	52.8	48.7	40.1	40.1	39.6	25.0	43.3	61.5	88.3
95°	52.4	52.4	61.5	77.4	113.8	116.1	77.4	70.6	100.2	141.1	177.6
97.5°	141.6	168.4	206.7	214.0	202.6	151.1	144.8	134.8	183.5	224.0	282.7
100°	261.8	295.9	323.2	268.6	211.7	209.4	195.8	191.2	243.6	282.3	339.2
102.5°	409.3	419.8	325.1	294.1	280.9	271.3	250.4	247.7	300.0	353.3	401.1
105°	443.9	398.4	400.6	400.6	391.5	373.3	334.6	332.3	391.5	453.0	512.2
107.5°	522.2	529.0	540.9	538.1	527.7	478.9	433.4	422.9	476.2	550.0	615.1
110°	626.0	632.8	637.4	632.8	616.9	555.4	500.8	484.9	532.7	610.1	680.6



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	726.1	731.2	741.2	727.5	700.7	630.1	568.2	545.0	592.8	672.0	744.4
115°	885.5	885.5	887.8	880.9	826.3	753.5	671.5	637.4	678.3	751.2	830.9
117.5°	1042.1	1044.8	1035.7	1017.5	954.2	869.6	777.6	723.0	755.3	832.2	914.2
120°	1140.4	1145.0	1135.9	1108.6	1047.1	951.5	846.8	783.1	808.1	883.2	965.2
122.5°	1242.4	1241.5	1230.6	1199.6	1127.2	1028.0	925.1	846.8	857.3	926.9	1007.0
125°	1384.0	1381.7	1372.6	1336.2	1261.1	1158.6	1038.0	942.4	928.7	987.9	1069.9
127.5°	1518.8	1513.8	1499.6	1455.5	1378.5	1279.7	1147.3	1038.9	1008.4	1045.7	1120.9
130°	1611.6	1604.8	1579.8	1532.0	1456.8	1363.5	1229.2	1106.3	1063.0	1085.8	1151.8
132.5°	1700.9	1681.3	1659.9	1608.4	1538.8	1441.8	1305.7	1177.3	1117.7	1127.7	1179.1
135°	1814.2	1796.0	1768.7	1718.6	1652.6	1557.0	1420.4	1281.6	1199.6	1190.5	1220.1
137.5°	1913.9	1894.8	1863.9	1820.6	1754.1	1669.0	1537.9	1391.3	1287.9	1257.4	1268.8
140°	1975.8	1953.1	1925.8	1882.5	1823.3	1734.6	1607.1	1466.0	1349.9	1306.6	1299.8
142.5°	2026.8	2009.5	1980.4	1940.8	1888.9	1800.1	1676.3	1537.0	1413.6	1357.6	1341.7
145°	2103.3	2089.7	2057.8	2021.4	1978.1	1889.3	1775.5	1636.7	1513.8	1440.9	1406.8
147.5°	2168.0	2157.0	2132.0	2089.2	2052.8	1967.7	1863.9	1740.9	1614.8	1524.7	1480.5
150°	2208.0	2198.9	2173.9	2132.9	2096.5	2016.8	1916.7	1802.8	1682.2	1586.6	1529.7
152.5°	2246.3	2237.2	2208.5	2167.5	2136.6	2062.3	1971.3	1862.9	1740.5	1644.9	1586.1
155°	2296.8	2285.4	2258.1	2219.4	2192.1	2123.8	2039.6	1944.0	1839.3	1739.1	1673.1
157.5°	2336.9	2322.8	2297.3	2264.0	2234.9	2172.1	2098.8	2016.4	1924.9	1829.3	1761.9
160°	2360.5	2344.6	2317.3	2287.7	2260.4	2201.2	2135.2	2060.1	1975.8	1889.3	1816.5
162.5°	2376.9	2362.8	2330.0	2304.1	2280.4	2226.7	2164.3	2096.5	2021.4	1945.8	1878.4
165°	2394.7	2378.8	2344.6	2324.1	2303.6	2258.1	2203.5	2148.8	2085.1	2023.7	1969.0
167.5°	2396.1	2382.9	2348.7	2328.7	2313.7	2274.5	2230.3	2188.5	2138.8	2090.6	2045.0
170°	2392.4	2381.0	2346.9	2328.7	2317.3	2285.4	2246.7	2210.3	2171.6	2130.6	2094.2
172.5°	2379.7	2368.3	2336.0	2321.4	2315.5	2287.2	2255.8	2228.5	2195.3	2165.2	2136.1
175°	2346.9	2337.8	2310.5	2301.4	2303.6	2285.4	2262.7	2246.7	2226.2	2208.0	2192.1
177.5°	2299.1	2293.6	2273.6	2273.6	2280.9	2269.9	2262.7	2255.4	2246.3	2240.8	2235.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1713.4	1710.5	1711.1	1712.0	1713.7	1715.5	1713.7	1712.0	1711.1	1710.5	1713.4
5°	1712.5	1709.6	1710.3	1712.5	1719.0	1725.6	1719.0	1712.5	1710.3	1709.6	1712.5
7.5°	1707.1	1705.9	1708.4	1711.8	1718.2	1724.6	1718.2	1711.8	1708.4	1705.9	1707.1
10°	1701.6	1701.3	1704.9	1709.1	1714.9	1720.7	1714.9	1709.1	1704.9	1701.3	1701.6
12.5°	1694.5	1695.0	1699.2	1703.8	1709.6	1715.5	1709.6	1703.8	1699.2	1695.0	1694.5
15°	1678.6	1680.8	1685.8	1690.6	1694.2	1697.8	1694.2	1690.6	1685.8	1680.8	1678.6
17.5°	1652.3	1652.4	1653.7	1655.2	1656.9	1658.6	1656.9	1655.2	1653.7	1652.4	1652.3
20°	1632.0	1628.3	1623.3	1619.5	1619.5	1619.5	1619.5	1619.5	1623.3	1628.3	1632.0
22.5°	1603.4	1594.0	1580.2	1568.7	1564.0	1559.4	1564.0	1568.7	1580.2	1594.0	1603.4
25°	1546.7	1525.3	1497.0	1473.1	1462.2	1451.3	1462.2	1473.1	1497.0	1525.3	1546.7
27.5°	1469.6	1435.1	1394.9	1361.0	1345.9	1330.8	1345.9	1361.0	1394.9	1435.1	1469.6
30°	1407.1	1363.9	1319.6	1282.8	1268.3	1253.8	1268.3	1282.8	1319.6	1363.9	1407.1
32.5°	1341.8	1292.5	1246.5	1208.1	1192.4	1176.7	1192.4	1208.1	1246.5	1292.5	1341.8
35°	1239.4	1183.2	1136.8	1098.5	1084.7	1070.9	1084.7	1098.5	1136.8	1183.2	1239.4
37.5°	1136.8	1077.3	1028.7	988.4	973.2	958.0	973.2	988.4	1028.7	1077.3	1136.8
40°	1065.1	1004.2	955.6	915.3	900.1	884.8	900.1	915.3	955.6	1004.2	1065.1
42.5°	995.9	935.0	886.3	845.9	830.1	814.3	830.1	845.9	886.3	935.0	995.9
45°	891.2	830.2	783.1	743.9	728.6	713.4	728.6	743.9	783.1	830.2	891.2
47.5°	792.5	732.3	686.6	649.1	636.0	623.0	636.0	649.1	686.6	732.3	792.5
50°	729.4	671.0	625.3	587.0	571.0	555.1	571.0	587.0	625.3	671.0	729.4
52.5°	668.4	610.3	563.4	522.8	501.1	479.3	501.1	522.8	563.4	610.3	668.4
55°	579.5	520.8	468.5	426.3	413.9	401.6	413.9	426.3	468.5	520.8	579.5
57.5°	497.7	444.5	397.0	358.9	348.7	338.6	348.7	358.9	397.0	444.5	497.7
60°	443.3	394.7	354.8	322.3	312.2	302.0	312.2	322.3	354.8	394.7	443.3
62.5°	390.2	346.5	314.7	288.8	280.4	272.0	280.4	288.8	314.7	346.5	390.2
65°	325.2	289.0	262.8	241.4	234.2	226.9	234.2	241.4	262.8	289.0	325.2
67.5°	269.0	239.6	216.7	198.3	193.5	188.7	193.5	198.3	216.7	239.6	269.0
70°	232.7	207.7	188.8	173.8	170.1	166.5	170.1	173.8	188.8	207.7	232.7
72.5°	198.0	177.1	162.3	150.6	148.1	145.6	148.1	150.6	162.3	177.1	198.0
75°	151.8	137.0	126.8	118.8	117.4	115.9	117.4	118.8	126.8	137.0	151.8
77.5°	112.3	101.4	93.8	87.9	86.7	85.5	86.7	87.9	93.8	101.4	112.3
80°	87.1	78.7	72.9	68.6	68.6	68.6	68.6	68.6	72.9	78.7	87.1
82.5°	62.1	56.7	53.8	51.6	51.6	51.6	51.6	51.6	53.8	56.7	62.1
85°	32.5	28.8	24.5	21.0	20.3	19.6	20.3	21.0	24.5	28.8	32.5
87.5°	17.1	18.6	21.2	22.6	24.4	23.5	24.4	22.6	21.2	18.6	17.1
90°	52.4	68.3	84.2	93.3	102.4	97.9	102.4	93.3	84.2	68.3	52.4
92.5°	105.2	132.0	151.6	168.0	175.3	174.4	175.3	168.0	151.6	132.0	105.2
95°	211.7	243.6	275.4	298.2	311.9	307.3	311.9	298.2	275.4	243.6	211.7
97.5°	326.4	369.2	404.7	426.1	439.8	448.9	439.8	426.1	404.7	369.2	326.4
100°	402.9	443.9	484.9	509.9	532.7	541.8	532.7	509.9	484.9	443.9	402.9
102.5°	464.8	518.5	563.2	590.0	609.1	618.2	609.1	590.0	563.2	518.5	464.8
105°	566.8	623.7	671.5	705.7	726.1	733.0	726.1	705.7	671.5	623.7	566.8
107.5°	668.8	727.5	771.7	809.5	834.5	849.1	834.5	809.5	771.7	727.5	668.8
110°	748.9	796.7	844.5	878.7	903.7	912.8	903.7	878.7	844.5	796.7	748.9



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	816.3	869.6	917.4	951.5	980.2	992.9	980.2	951.5	917.4	869.6	816.3
115°	910.5	981.1	1024.3	1056.2	1076.7	1088.1	1076.7	1056.2	1024.3	981.1	910.5
117.5°	988.8	1062.6	1109.9	1134.5	1144.1	1152.3	1144.1	1134.5	1109.9	1062.6	988.8
120°	1038.0	1106.3	1160.9	1192.8	1204.2	1208.7	1204.2	1192.8	1160.9	1106.3	1038.0
122.5°	1083.5	1148.2	1201.0	1240.1	1258.8	1263.4	1258.8	1240.1	1201.0	1148.2	1083.5
125°	1147.3	1208.7	1263.4	1302.1	1322.5	1333.9	1322.5	1302.1	1263.4	1208.7	1147.3
127.5°	1202.8	1269.3	1319.4	1354.4	1374.4	1383.5	1374.4	1354.4	1319.4	1269.3	1202.8
130°	1233.8	1302.1	1352.1	1390.8	1409.0	1418.1	1409.0	1390.8	1352.1	1302.1	1233.8
132.5°	1257.4	1329.4	1381.3	1416.3	1436.4	1445.5	1436.4	1416.3	1381.3	1329.4	1257.4
135°	1286.1	1361.2	1415.9	1450.0	1468.2	1477.3	1468.2	1450.0	1415.9	1361.2	1286.1
137.5°	1311.2	1379.5	1436.4	1472.3	1488.7	1494.6	1488.7	1472.3	1436.4	1379.5	1311.2
140°	1329.4	1388.6	1445.5	1479.6	1497.8	1500.1	1497.8	1479.6	1445.5	1388.6	1329.4
142.5°	1353.0	1399.5	1449.1	1483.3	1501.5	1505.6	1501.5	1483.3	1449.1	1399.5	1353.0
145°	1395.4	1422.7	1456.8	1488.7	1504.6	1509.2	1504.6	1488.7	1456.8	1422.7	1395.4
147.5°	1448.7	1457.3	1475.1	1496.0	1511.5	1514.7	1511.5	1496.0	1475.1	1457.3	1448.7
150°	1488.7	1486.4	1493.3	1506.9	1520.6	1518.3	1520.6	1506.9	1493.3	1486.4	1488.7
152.5°	1534.2	1521.0	1520.6	1527.0	1533.3	1532.9	1533.3	1527.0	1520.6	1521.0	1534.2
155°	1611.6	1586.6	1572.9	1568.4	1568.4	1566.1	1568.4	1568.4	1572.9	1586.6	1611.6
157.5°	1696.8	1661.7	1641.2	1630.3	1627.1	1622.1	1627.1	1630.3	1641.2	1661.7	1696.8
160°	1755.0	1716.3	1695.9	1677.6	1670.8	1664.0	1670.8	1677.6	1695.9	1716.3	1755.0
162.5°	1809.7	1772.8	1750.5	1734.1	1727.3	1716.8	1727.3	1734.1	1750.5	1772.8	1809.7
165°	1898.5	1859.8	1834.7	1821.1	1812.0	1802.8	1812.0	1821.1	1834.7	1859.8	1898.5
167.5°	1987.2	1944.9	1928.5	1913.0	1904.4	1888.0	1904.4	1913.0	1928.5	1944.9	1987.2
170°	2041.9	2003.2	1994.1	1980.4	1964.5	1946.3	1964.5	1980.4	1994.1	2003.2	2041.9
172.5°	2089.2	2063.3	2054.2	2040.5	2035.5	2020.9	2035.5	2040.5	2054.2	2063.3	2089.2
175°	2158.0	2137.5	2137.5	2135.2	2128.4	2114.7	2128.4	2135.2	2137.5	2137.5	2158.0
177.5°	2215.3	2204.4	2211.7	2211.7	2209.9	2197.1	2209.9	2211.7	2211.7	2204.4	2215.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1714.1	1714.1	1714.1	1714.1
2.5°	1719.8	1722.1	1712.3	1702.4
5°	1719.0	1720.9	1708.5	1696.2
7.5°	1712.1	1712.7	1700.2	1687.7
10°	1706.0	1706.0	1692.9	1679.9
12.5°	1697.7	1696.7	1683.1	1669.4
15°	1679.3	1676.2	1661.7	1647.2
17.5°	1653.3	1650.4	1635.9	1621.4
20°	1634.2	1632.2	1617.6	1603.1
22.5°	1608.5	1608.4	1592.7	1577.0
25°	1561.2	1568.3	1553.1	1537.8
27.5°	1498.3	1516.8	1504.5	1492.1
30°	1449.1	1478.3	1468.9	1459.5
32.5°	1394.3	1432.8	1429.1	1425.5
35°	1305.5	1356.6	1363.2	1369.7
37.5°	1207.2	1264.8	1284.3	1303.7
40°	1138.4	1200.3	1227.8	1255.4
42.5°	1069.2	1132.8	1167.3	1201.9
45°	965.9	1032.1	1072.7	1113.4
47.5°	867.1	933.1	973.5	1013.8
50°	800.5	863.6	902.8	942.0
52.5°	737.8	798.6	833.7	868.8
55°	644.8	702.2	735.5	768.9
57.5°	556.8	608.3	637.2	666.1
60°	500.6	550.0	575.4	600.8
62.5°	445.8	493.1	515.6	538.1
65°	371.7	410.7	427.4	444.0
67.5°	304.8	334.0	343.3	352.6
70°	263.9	288.0	291.0	293.9
72.5°	225.2	245.2	244.1	242.9
75°	171.4	184.7	178.9	173.0
77.5°	126.7	135.3	126.6	117.9
80°	98.0	103.9	95.2	86.5
82.5°	70.1	74.3	67.4	60.4
85°	35.4	36.6	33.0	29.4
87.5°	17.8	16.3	12.8	9.2
90°	41.0	25.0	15.9	6.8
92.5°	88.3	61.5	43.3	25.0
95°	177.6	141.1	100.2	70.6
97.5°	282.7	224.0	183.5	134.8
100°	339.2	282.3	243.6	191.2
102.5°	401.1	353.3	300.0	247.7
105°	512.2	453.0	391.5	332.3
107.5°	615.1	550.0	476.2	422.9
110°	680.6	610.1	532.7	484.9



TEST NUMBER: P1428474

CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	744.4	672.0	592.8	545.0
115°	830.9	751.2	678.3	637.4
117.5°	914.2	832.2	755.3	723.0
120°	965.2	883.2	808.1	783.1
122.5°	1007.0	926.9	857.3	846.8
125°	1069.9	987.9	928.7	942.4
127.5°	1120.9	1045.7	1008.4	1038.9
130°	1151.8	1085.8	1063.0	1106.3
132.5°	1179.1	1127.7	1117.7	1177.3
135°	1220.1	1190.5	1199.6	1281.6
137.5°	1268.8	1257.4	1287.9	1391.3
140°	1299.8	1306.6	1349.9	1466.0
142.5°	1341.7	1357.6	1413.6	1537.0
145°	1406.8	1440.9	1513.8	1636.7
147.5°	1480.5	1524.7	1614.8	1740.9
150°	1529.7	1586.6	1682.2	1802.8
152.5°	1586.1	1644.9	1740.5	1862.9
155°	1673.1	1739.1	1839.3	1944.0
157.5°	1761.9	1829.3	1924.9	2016.4
160°	1816.5	1889.3	1975.8	2060.1
162.5°	1878.4	1945.8	2021.4	2096.5
165°	1969.0	2023.7	2085.1	2148.8
167.5°	2045.0	2090.6	2138.8	2188.5
170°	2094.2	2130.6	2171.6	2210.3
172.5°	2136.1	2165.2	2195.3	2228.5
175°	2192.1	2208.0	2226.2	2246.7
177.5°	2235.3	2240.8	2246.3	2255.4
180°	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428474
 CATALOG NUMBER: SQ2W-PW1-K-150U-075D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.06	17.79	18.13	18.86	20.31	13.31	14.04	14.38	15.10	16.56
	3H	18.35	19.00	19.43	20.08	21.55	14.57	15.22	15.65	16.29	17.76
	4H	18.75	19.37	19.84	20.45	21.92	15.07	15.68	16.16	16.76	18.24
	6H	18.93	19.49	20.03	20.57	22.06	15.37	15.94	16.47	17.02	18.50
	8H	18.97	19.50	20.07	20.60	22.08	15.48	16.02	16.58	17.11	18.60
	12H	18.96	19.47	20.07	20.56	22.07	15.51	16.02	16.61	17.11	18.61
4H	2H	17.17	17.79	18.27	18.87	20.35	14.10	14.72	15.20	15.80	17.27
	3H	18.70	19.21	19.81	20.32	21.81	15.54	16.05	16.64	17.15	18.64
	4H	19.24	19.71	20.35	20.81	22.32	16.11	16.58	17.22	17.67	19.18
	6H	19.55	19.95	20.66	21.07	22.57	16.49	16.89	17.60	18.01	19.51
	8H	19.64	20.01	20.75	21.12	22.64	16.63	17.01	17.75	18.12	19.64
	12H	19.65	19.99	20.78	21.11	22.64	16.67	17.01	17.80	18.13	19.66
8H	4H	19.27	19.65	20.39	20.76	22.28	16.44	16.82	17.56	17.93	19.45
	6H	19.69	20.00	20.83	21.15	22.67	16.93	17.24	18.07	18.39	19.91
	8H	19.86	20.13	21.00	21.26	22.80	17.15	17.42	18.29	18.55	20.09
	12H	19.93	20.17	21.08	21.30	22.87	17.23	17.47	18.37	18.59	20.17
12H	4H	19.23	19.56	20.36	20.69	22.21	16.45	16.79	17.59	17.92	19.44
	6H	19.68	19.95	20.83	21.09	22.62	17.01	17.28	18.15	18.41	19.94
	8H	19.87	20.10	21.01	21.23	22.81	17.24	17.48	18.39	18.61	20.18