

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428509

Luminaire Tested: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428509  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5125.8 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	101	101	101	93	93	93	85	85	85	82
1	108	104	101	99	103	100	98	95	93	91	89	86	85	83	80	79	78	75
2	101	95	90	86	97	92	87	84	85	82	79	80	77	75	74	72	70	68
3	94	86	80	76	90	84	78	74	78	74	70	73	70	67	69	66	64	61
4	88	79	72	67	85	76	70	66	72	67	63	68	64	60	64	61	58	56
5	82	72	65	60	79	70	64	59	66	61	57	63	58	55	59	55	53	50
6	77	66	59	54	74	65	58	53	61	56	51	58	53	50	55	51	48	46
7	72	61	54	49	69	60	53	48	56	51	47	54	49	45	51	47	44	42
8	68	56	50	45	65	55	49	44	52	47	43	50	45	42	48	43	40	39
9	63	52	46	41	61	51	45	40	49	43	39	47	42	38	44	40	37	35
10	60	49	42	38	58	48	41	37	45	40	36	43	39	35	42	37	34	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	43285	43285	43285	43285
5°	43678	43657	43678	43657
10°	44121	44100	44121	44100
15°	44853	44059	44853	44059
20°	45068	43346	45068	43346
25°	44141	42126	44141	42126
30°	41882	39390	41882	39390
35°	37668	35539	37668	35539
40°	30879	29254	30879	29254
45°	19308	18134	19308	18134
50°	7553	6907	7553	6907
55°	3727	3690	3727	3690
60°	1744	1576	1744	1576
65°	1570	1475	1570	1475
70°	1515	1454	1515	1454
75°	1522	1360	1522	1360
80°	1432	1311	1432	1311
85°	1426	1186	1426	1186

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 30°  
 Vertical Angle: 45°  
 Luminance: 21979 cd/sqm



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	256.3	5.0
10°-20°	749.5	14.6
20°-30°	1108.2	21.6
30°-40°	1146.6	22.4
40°-50°	689.7	13.5
50°-60°	164.9	3.2
60°-70°	45.1	0.9
70°-80°	25.2	0.5
80°-90°	9.3	0.2
90°-100°	25.4	0.5
100°-110°	74.0	1.4
110°-120°	120.8	2.4
120°-130°	153.3	3.0
130°-140°	164.0	3.2
140°-150°	153.1	3.0
150°-160°	126.0	2.5
160°-170°	84.5	1.6
170°-180°	30.0	0.6
0°-30°	2114.0	41.2
0°-40°	3260.6	63.6
0°-60°	4115.2	80.3
0°-90°	4194.8	81.8
90°-120°	220.2	4.3
90°-150°	690.5	13.5
90°-180°	931.0	18.2
0°-180°	5125.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2681	2681	2681	2681	2681	
5°	2695	2694	2695	2694	2695	257
15°	2683	2636	2683	2636	2683	756
25°	2478	2365	2478	2365	2478	1133
35°	1911	1803	1911	1803	1911	1173
45°	846	794	846	794	846	654
55°	132	131	132	131	132	133
65°	41	39	41	39	41	41
75°	24	22	24	22	24	25
85°	8	6	8	6	8	8
90°	1	7	1	14	1	1
95°	10	7	10	44	10	12
105°	47	75	47	104	47	50
115°	90	125	90	154	90	89
125°	133	198	133	189	133	119
135°	181	259	181	209	181	140
145°	232	299	232	214	232	145
155°	275	325	275	222	275	126
165°	304	338	304	255	304	86
175°	318	331	318	299	318	30
180°	319	319	319	319	319	



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9
2.5°	2694.2	2691.0	2687.8	2679.8	2670.2	2670.5	2680.5	2687.5	2685.2	2682.9	2685.2
5°	2695.0	2691.0	2687.0	2677.9	2667.0	2669.6	2685.6	2697.2	2695.4	2693.7	2695.4
7.5°	2692.2	2690.5	2688.8	2682.1	2673.7	2675.6	2687.7	2696.2	2693.5	2690.9	2693.5
10°	2691.2	2691.7	2692.3	2683.4	2671.4	2671.7	2684.3	2693.3	2691.6	2689.9	2691.6
12.5°	2690.1	2694.8	2699.5	2687.6	2670.1	2666.3	2676.1	2682.4	2678.4	2674.4	2678.4
15°	2683.4	2692.6	2701.7	2685.6	2661.0	2648.7	2648.7	2647.3	2641.6	2635.9	2641.6
17.5°	2654.9	2665.8	2676.6	2654.7	2622.0	2601.2	2592.4	2584.0	2577.1	2570.1	2577.1
20°	2623.0	2633.9	2644.7	2618.8	2580.5	2554.2	2539.9	2528.5	2525.7	2522.8	2525.7
22.5°	2572.7	2584.4	2596.2	2568.4	2527.4	2499.0	2483.4	2470.5	2465.8	2461.1	2465.8
25°	2477.8	2487.0	2496.1	2467.1	2425.4	2398.8	2387.4	2377.3	2371.0	2364.7	2371.0
27.5°	2351.4	2356.4	2361.4	2333.4	2294.3	2268.2	2255.2	2243.3	2234.6	2225.9	2234.6
30°	2246.5	2248.8	2251.1	2228.5	2197.6	2173.7	2156.5	2140.2	2126.5	2112.8	2126.5
32.5°	2122.1	2124.4	2126.6	2106.8	2079.6	2057.9	2041.7	2026.8	2015.8	2004.9	2015.8
35°	1911.1	1909.9	1908.8	1896.1	1879.5	1861.8	1842.9	1825.9	1814.5	1803.1	1814.5
37.5°	1647.1	1648.7	1650.3	1640.8	1627.7	1613.7	1598.8	1584.8	1573.3	1561.7	1573.3
40°	1465.1	1466.2	1467.4	1459.5	1448.7	1432.4	1410.7	1393.7	1390.8	1388.0	1390.8
42.5°	1243.0	1260.2	1277.3	1270.4	1255.4	1239.6	1222.9	1207.0	1193.7	1180.3	1193.7
45°	845.6	897.6	949.6	962.6	962.6	952.6	932.6	903.9	849.1	794.2	849.1
47.5°	477.6	536.7	595.9	634.8	666.9	653.2	593.8	532.6	466.0	399.4	466.0
50°	300.7	340.7	380.7	430.5	483.7	469.1	386.8	319.6	297.3	275.0	297.3
52.5°	213.3	233.7	254.0	301.0	356.9	350.1	280.6	225.6	213.8	202.0	213.8
55°	132.4	139.8	147.2	170.1	198.1	196.3	164.9	140.2	135.7	131.1	135.7
57.5°	78.7	86.3	94.0	104.1	115.1	115.1	104.1	94.1	86.9	79.7	86.9
60°	54.0	60.3	66.5	75.0	84.1	83.0	71.5	61.4	55.1	48.8	55.1
62.5°	46.8	49.4	52.0	58.5	66.3	65.6	56.5	49.1	46.9	44.7	46.9
65°	41.1	41.7	42.3	42.8	43.4	43.1	42.0	40.8	39.7	38.6	39.7
67.5°	36.2	36.8	37.4	37.2	36.7	36.4	36.3	36.0	35.0	33.9	35.0
70°	32.1	32.7	33.3	33.4	33.4	33.1	32.6	32.0	31.4	30.8	31.4
72.5°	29.0	29.6	30.2	30.0	29.5	29.2	29.1	28.8	27.8	26.7	27.8
75°	24.4	24.4	24.4	24.4	24.4	24.1	23.6	23.0	22.4	21.8	22.4
77.5°	18.5	19.1	19.6	19.4	18.8	18.5	18.5	18.4	17.8	17.2	17.8
80°	15.4	16.0	16.6	16.3	15.7	15.4	15.4	15.3	14.7	14.1	14.7
82.5°	12.3	12.5	12.6	12.5	12.4	12.3	12.3	12.2	11.6	11.1	11.6
85°	7.7	7.7	7.7	7.3	6.7	6.4	6.4	6.4	6.4	6.4	6.4
87.5°	2.2	3.0	3.7	3.8	3.5	3.3	3.3	3.4	3.5	3.5	3.5
90°	1.0	2.3	3.9	5.2	6.1	6.4	6.4	6.8	7.1	7.1	7.1
92.5°	3.5	5.6	5.7	5.7	6.9	7.5	8.0	8.1	8.4	8.4	8.4
95°	10.0	11.0	16.4	16.1	11.0	8.7	7.4	7.4	7.4	7.4	7.4
97.5°	19.1	20.5	21.4	28.7	30.3	29.2	23.8	20.0	17.9	16.9	17.9
100°	27.1	27.7	29.6	30.0	38.0	45.7	41.9	37.0	35.4	34.5	35.4
102.5°	35.0	35.4	38.4	39.7	41.6	46.0	59.4	57.9	56.8	56.6	56.8
105°	47.0	47.3	52.8	55.4	56.7	56.7	56.4	62.8	73.1	75.4	73.1
107.5°	59.8	61.3	67.8	74.7	76.1	76.5	74.9	73.9	73.5	73.8	73.5
110°	68.6	70.9	78.6	87.3	89.5	90.2	89.5	88.6	87.9	87.9	87.9



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	77.1	80.4	89.2	99.1	102.9	104.9	103.5	102.7	102.1	102.6	102.1
115°	90.2	95.0	106.6	116.9	124.6	125.6	125.3	125.3	125.0	125.0	125.0
117.5°	102.3	110.0	123.0	135.0	144.0	146.5	147.8	147.5	147.1	147.7	147.1
120°	110.8	119.8	134.6	148.2	156.9	160.7	162.0	161.4	162.0	161.4	162.0
122.5°	119.8	130.9	145.5	159.5	169.7	174.1	175.7	175.8	175.9	175.5	175.9
125°	133.3	146.9	163.9	178.4	189.1	194.2	195.5	195.8	196.5	198.1	196.5
127.5°	147.0	162.3	181.1	195.1	205.9	212.2	214.2	214.9	216.2	217.0	216.2
130°	156.5	173.9	192.9	206.1	216.8	223.5	227.1	228.0	229.6	229.3	229.6
132.5°	166.6	184.7	204.0	217.7	227.6	234.9	237.9	240.7	241.2	241.7	241.2
135°	181.3	201.0	220.3	233.8	243.2	250.3	254.1	256.7	258.3	259.3	258.3
137.5°	196.9	217.6	236.2	248.2	257.6	263.7	268.1	270.8	272.5	273.3	272.5
140°	207.4	227.4	245.4	258.0	266.4	272.5	276.3	279.6	281.5	281.5	281.5
142.5°	217.5	237.2	254.7	267.3	274.6	280.2	284.3	286.8	289.0	289.0	289.0
145°	231.6	251.2	267.3	279.9	286.0	291.2	295.7	297.6	298.9	298.9	298.9
147.5°	246.3	263.7	278.4	290.5	295.6	301.7	305.2	306.8	308.4	307.7	308.4
150°	255.1	271.2	285.4	296.6	301.8	307.6	311.1	312.4	314.0	313.1	314.0
152.5°	263.6	278.9	291.8	302.3	306.7	312.5	316.5	317.8	318.9	318.2	318.9
155°	275.1	288.6	300.5	310.2	314.0	319.5	323.4	325.0	326.3	324.7	326.3
157.5°	285.3	297.0	307.3	316.2	320.3	325.0	328.7	330.7	331.9	331.2	331.9
160°	291.5	302.1	311.5	319.8	323.7	327.9	331.7	334.0	335.3	334.3	335.3
162.5°	296.6	306.2	315.1	322.7	326.0	329.7	334.3	336.3	337.6	336.4	337.6
165°	304.0	311.8	319.5	326.0	328.8	331.7	336.6	338.8	339.8	338.5	339.8
167.5°	309.7	315.6	321.8	327.4	329.5	332.3	337.2	339.0	340.3	338.6	340.3
170°	312.7	317.9	323.4	327.9	329.5	332.1	336.9	338.5	339.5	337.9	339.5
172.5°	315.3	319.2	323.6	327.6	328.5	330.5	335.1	336.7	337.4	336.1	337.4
175°	317.9	320.2	323.4	326.0	325.6	326.9	330.8	332.1	333.4	331.4	333.4
177.5°	319.1	320.2	321.2	322.7	321.7	321.7	324.5	325.3	325.6	324.5	325.6
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9
2.5°	2687.5	2680.5	2670.5	2670.2	2679.8	2687.8	2691.0	2694.2	2691.0	2687.8	2679.8
5°	2697.2	2685.6	2669.6	2667.0	2677.9	2687.0	2691.0	2695.0	2691.0	2687.0	2677.9
7.5°	2696.2	2687.7	2675.6	2673.7	2682.1	2688.8	2690.5	2692.2	2690.5	2688.8	2682.1
10°	2693.3	2684.3	2671.7	2671.4	2683.4	2692.3	2691.7	2691.2	2691.7	2692.3	2683.4
12.5°	2682.4	2676.1	2666.3	2670.1	2687.6	2699.5	2694.8	2690.1	2694.8	2699.5	2687.6
15°	2647.3	2648.7	2648.7	2661.0	2685.6	2701.7	2692.6	2683.4	2692.6	2701.7	2685.6
17.5°	2584.0	2592.4	2601.2	2622.0	2654.7	2676.6	2665.8	2654.9	2665.8	2676.6	2654.7
20°	2528.5	2539.9	2554.2	2580.5	2618.8	2644.7	2633.9	2623.0	2633.9	2644.7	2618.8
22.5°	2470.5	2483.4	2499.0	2527.4	2568.4	2596.2	2584.4	2572.7	2584.4	2596.2	2568.4
25°	2377.3	2387.4	2398.8	2425.4	2467.1	2496.1	2487.0	2477.8	2487.0	2496.1	2467.1
27.5°	2243.3	2255.2	2268.2	2294.3	2333.4	2361.4	2356.4	2351.4	2356.4	2361.4	2333.4
30°	2140.2	2156.5	2173.7	2197.6	2228.5	2251.1	2248.8	2246.5	2248.8	2251.1	2228.5
32.5°	2026.8	2041.7	2057.9	2079.6	2106.8	2126.6	2124.4	2122.1	2124.4	2126.6	2106.8
35°	1825.9	1842.9	1861.8	1879.5	1896.1	1908.8	1909.9	1911.1	1909.9	1908.8	1896.1
37.5°	1584.8	1598.8	1613.7	1627.7	1640.8	1650.3	1648.7	1647.1	1648.7	1650.3	1640.8
40°	1393.7	1410.7	1432.4	1448.7	1459.5	1467.4	1466.2	1465.1	1466.2	1467.4	1459.5
42.5°	1207.0	1222.9	1239.6	1255.4	1270.4	1277.3	1260.2	1243.0	1260.2	1277.3	1270.4
45°	903.9	932.6	952.6	962.6	962.6	949.6	897.6	845.6	897.6	949.6	962.6
47.5°	532.6	593.8	653.2	666.9	634.8	595.9	536.7	477.6	536.7	595.9	634.8
50°	319.6	386.8	469.1	483.7	430.5	380.7	340.7	300.7	340.7	380.7	430.5
52.5°	225.6	280.6	350.1	356.9	301.0	254.0	233.7	213.3	233.7	254.0	301.0
55°	140.2	164.9	196.3	198.1	170.1	147.2	139.8	132.4	139.8	147.2	170.1
57.5°	94.1	104.1	115.1	115.1	104.1	94.0	86.3	78.7	86.3	94.0	104.1
60°	61.4	71.5	83.0	84.1	75.0	66.5	60.3	54.0	60.3	66.5	75.0
62.5°	49.1	56.5	65.6	66.3	58.5	52.0	49.4	46.8	49.4	52.0	58.5
65°	40.8	42.0	43.1	43.4	42.8	42.3	41.7	41.1	41.7	42.3	42.8
67.5°	36.0	36.3	36.4	36.7	37.2	37.4	36.8	36.2	36.8	37.4	37.2
70°	32.0	32.6	33.1	33.4	33.4	33.3	32.7	32.1	32.7	33.3	33.4
72.5°	28.8	29.1	29.2	29.5	30.0	30.2	29.6	29.0	29.6	30.2	30.0
75°	23.0	23.6	24.1	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
77.5°	18.4	18.5	18.5	18.8	19.4	19.6	19.1	18.5	19.1	19.6	19.4
80°	15.3	15.4	15.4	15.7	16.3	16.6	16.0	15.4	16.0	16.6	16.3
82.5°	12.2	12.3	12.3	12.4	12.5	12.6	12.5	12.3	12.5	12.6	12.5
85°	6.4	6.4	6.4	6.7	7.3	7.7	7.7	7.7	7.7	7.7	7.3
87.5°	3.4	3.3	3.3	3.5	3.8	3.7	3.0	2.2	3.0	3.7	3.9
90°	6.8	6.4	6.4	6.1	5.2	3.9	2.3	1.0	2.3	3.5	5.8
92.5°	8.1	8.0	7.5	6.9	5.7	5.7	5.6	3.5	6.1	8.7	12.5
95°	7.4	7.4	8.7	11.0	16.1	16.4	11.0	10.0	14.2	20.0	25.1
97.5°	20.0	23.8	29.2	30.3	28.7	21.4	20.5	19.1	26.0	31.7	40.0
100°	37.0	41.9	45.7	38.0	30.0	29.6	27.7	27.1	34.5	39.9	48.0
102.5°	57.9	59.4	46.0	41.6	39.7	38.4	35.4	35.0	42.5	50.0	56.8
105°	62.8	56.4	56.7	56.7	55.4	52.8	47.3	47.0	55.4	64.1	72.5
107.5°	73.9	74.9	76.5	76.1	74.7	67.8	61.3	59.8	67.4	77.8	87.0
110°	88.6	89.5	90.2	89.5	87.3	78.6	70.9	68.6	75.4	86.3	96.3



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	102.7	103.5	104.9	102.9	99.1	89.2	80.4	77.1	83.9	95.1	105.3
115°	125.3	125.3	125.6	124.6	116.9	106.6	95.0	90.2	96.0	106.3	117.6
117.5°	147.5	147.8	146.5	144.0	135.0	123.0	110.0	102.3	106.9	117.8	129.3
120°	161.4	162.0	160.7	156.9	148.2	134.6	119.8	110.8	114.3	125.0	136.6
122.5°	175.8	175.7	174.1	169.7	159.5	145.5	130.9	119.8	121.3	131.2	142.5
125°	195.8	195.5	194.2	189.1	178.4	163.9	146.9	133.3	131.4	139.8	151.4
127.5°	214.9	214.2	212.2	205.9	195.1	181.1	162.3	147.0	142.7	148.0	158.6
130°	228.0	227.1	223.5	216.8	206.1	192.9	173.9	156.5	150.4	153.6	163.0
132.5°	240.7	237.9	234.9	227.6	217.7	204.0	184.7	166.6	158.1	159.6	166.8
135°	256.7	254.1	250.3	243.2	233.8	220.3	201.0	181.3	169.7	168.5	172.6
137.5°	270.8	268.1	263.7	257.6	248.2	236.2	217.6	196.9	182.2	177.9	179.5
140°	279.6	276.3	272.5	266.4	258.0	245.4	227.4	207.4	191.0	184.9	183.9
142.5°	286.8	284.3	280.2	274.6	267.3	254.7	237.2	217.5	200.0	192.1	189.8
145°	297.6	295.7	291.2	286.0	279.9	267.3	251.2	231.6	214.2	203.9	199.0
147.5°	306.8	305.2	301.7	295.6	290.5	278.4	263.7	246.3	228.5	215.7	209.5
150°	312.4	311.1	307.6	301.8	296.6	285.4	271.2	255.1	238.0	224.5	216.4
152.5°	317.8	316.5	312.5	306.7	302.3	291.8	278.9	263.6	246.3	232.7	224.4
155°	325.0	323.4	319.5	314.0	310.2	300.5	288.6	275.1	260.2	246.1	236.7
157.5°	330.7	328.7	325.0	320.3	316.2	307.3	297.0	285.3	272.4	258.8	249.3
160°	334.0	331.7	327.9	323.7	319.8	311.5	302.1	291.5	279.6	267.3	257.0
162.5°	336.3	334.3	329.7	326.0	322.7	315.1	306.2	296.6	286.0	275.3	265.8
165°	338.8	336.6	331.7	328.8	326.0	319.5	311.8	304.0	295.0	286.3	278.6
167.5°	339.0	337.2	332.3	329.5	327.4	321.8	315.6	309.7	302.6	295.8	289.4
170°	338.5	336.9	332.1	329.5	327.9	323.4	317.9	312.7	307.3	301.5	296.3
172.5°	336.7	335.1	330.5	328.5	327.6	323.6	319.2	315.3	310.6	306.4	302.2
175°	332.1	330.8	326.9	325.6	326.0	323.4	320.2	317.9	315.0	312.4	310.2
177.5°	325.3	324.5	321.7	321.7	322.7	321.2	320.2	319.1	317.8	317.1	316.3
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9	2680.9
2.5°	2670.2	2670.5	2680.5	2687.5	2685.2	2682.9	2685.2	2687.5	2680.5	2670.5	2670.2
5°	2667.0	2669.6	2685.6	2697.2	2695.4	2693.7	2695.4	2697.2	2685.6	2669.6	2667.0
7.5°	2673.7	2675.6	2687.7	2696.2	2693.5	2690.9	2693.5	2696.2	2687.7	2675.6	2673.7
10°	2671.4	2671.7	2684.3	2693.3	2691.6	2689.9	2691.6	2693.3	2684.3	2671.7	2671.4
12.5°	2670.1	2666.3	2676.1	2682.4	2678.4	2674.4	2678.4	2682.4	2676.1	2666.3	2670.1
15°	2661.0	2648.7	2648.7	2647.3	2641.6	2635.9	2641.6	2647.3	2648.7	2648.7	2661.0
17.5°	2622.0	2601.2	2592.4	2584.0	2577.1	2570.1	2577.1	2584.0	2592.4	2601.2	2622.0
20°	2580.5	2554.2	2539.9	2528.5	2525.7	2522.8	2525.7	2528.5	2539.9	2554.2	2580.5
22.5°	2527.4	2499.0	2483.4	2470.5	2465.8	2461.1	2465.8	2470.5	2483.4	2499.0	2527.4
25°	2425.4	2398.8	2387.4	2377.3	2371.0	2364.7	2371.0	2377.3	2387.4	2398.8	2425.4
27.5°	2294.3	2268.2	2255.2	2243.3	2234.6	2225.9	2234.6	2243.3	2255.2	2268.2	2294.3
30°	2197.6	2173.7	2156.5	2140.2	2126.5	2112.8	2126.5	2140.2	2156.5	2173.7	2197.6
32.5°	2079.6	2057.9	2041.7	2026.8	2015.8	2004.9	2015.8	2026.8	2041.7	2057.9	2079.6
35°	1879.5	1861.8	1842.9	1825.9	1814.5	1803.1	1814.5	1825.9	1842.9	1861.8	1879.5
37.5°	1627.7	1613.7	1598.8	1584.8	1573.3	1561.7	1573.3	1584.8	1598.8	1613.7	1627.7
40°	1448.7	1432.4	1410.7	1393.7	1390.8	1388.0	1390.8	1393.7	1410.7	1432.4	1448.7
42.5°	1255.4	1239.6	1222.9	1207.0	1193.7	1180.3	1193.7	1207.0	1222.9	1239.6	1255.4
45°	962.6	952.6	932.6	903.9	849.1	794.2	849.1	903.9	932.6	952.6	962.6
47.5°	666.9	653.2	593.8	532.6	466.0	399.4	466.0	532.6	593.8	653.2	666.9
50°	483.7	469.1	386.8	319.6	297.3	275.0	297.3	319.6	386.8	469.1	483.7
52.5°	356.9	350.1	280.6	225.6	213.8	202.0	213.8	225.6	280.6	350.1	356.9
55°	198.1	196.3	164.9	140.2	135.7	131.1	135.7	140.2	164.9	196.3	198.1
57.5°	115.1	115.1	104.1	94.1	86.9	79.7	86.9	94.1	104.1	115.1	115.1
60°	84.1	83.0	71.5	61.4	55.1	48.8	55.1	61.4	71.5	83.0	84.1
62.5°	66.3	65.6	56.5	49.1	46.9	44.7	46.9	49.1	56.5	65.6	66.3
65°	43.4	43.1	42.0	40.8	39.7	38.6	39.7	40.8	42.0	43.1	43.4
67.5°	36.7	36.4	36.3	36.0	35.0	33.9	35.0	36.0	36.3	36.4	36.7
70°	33.4	33.1	32.6	32.0	31.4	30.8	31.4	32.0	32.6	33.1	33.4
72.5°	29.5	29.2	29.1	28.8	27.8	26.7	27.8	28.8	29.1	29.2	29.5
75°	24.4	24.1	23.6	23.0	22.4	21.8	22.4	23.0	23.6	24.1	24.4
77.5°	18.8	18.5	18.5	18.4	17.8	17.2	17.8	18.4	18.5	18.5	18.8
80°	15.7	15.4	15.4	15.3	14.7	14.1	14.7	15.3	15.4	15.4	15.7
82.5°	12.4	12.3	12.3	12.2	11.6	11.1	11.6	12.2	12.3	12.3	12.4
85°	6.7	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.7
87.5°	3.8	4.0	4.4	4.7	5.0	4.8	5.0	4.7	4.4	4.0	3.8
90°	7.4	9.7	11.9	13.2	14.5	13.8	14.5	13.2	11.9	9.7	7.4
92.5°	14.9	18.7	21.5	23.8	24.8	24.7	24.8	23.8	21.5	18.7	14.9
95°	30.0	34.5	39.0	42.2	44.1	43.5	44.1	42.2	39.0	34.5	30.0
97.5°	46.2	52.2	57.3	60.3	62.2	63.5	62.2	60.3	57.3	52.2	46.2
100°	57.0	62.8	68.6	72.1	75.4	76.7	75.4	72.1	68.6	62.8	57.0
102.5°	65.8	73.4	79.7	83.5	86.2	87.5	86.2	83.5	79.7	73.4	65.8
105°	80.2	88.3	95.0	99.8	102.7	103.7	102.7	99.8	95.0	88.3	80.2
107.5°	94.6	102.9	109.2	114.5	118.1	120.1	118.1	114.5	109.2	102.9	94.6
110°	106.0	112.7	119.5	124.3	127.9	129.2	127.9	124.3	119.5	112.7	106.0



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	115.5	123.0	129.8	134.6	138.7	140.5	138.7	134.6	129.8	123.0	115.5
115°	128.8	138.8	144.9	149.4	152.3	154.0	152.3	149.4	144.9	138.8	128.8
117.5°	139.9	150.3	157.0	160.5	161.9	163.0	161.9	160.5	157.0	150.3	139.9
120°	146.9	156.5	164.3	168.8	170.4	171.0	170.4	168.8	164.3	156.5	146.9
122.5°	153.3	162.5	169.9	175.5	178.1	178.8	178.1	175.5	169.9	162.5	153.3
125°	162.3	171.0	178.8	184.2	187.1	188.7	187.1	184.2	178.8	171.0	162.3
127.5°	170.2	179.6	186.7	191.6	194.5	195.8	194.5	191.6	186.7	179.6	170.2
130°	174.6	184.2	191.3	196.8	199.4	200.7	199.4	196.8	191.3	184.2	174.6
132.5°	177.9	188.1	195.4	200.4	203.2	204.5	203.2	200.4	195.4	188.1	177.9
135°	182.0	192.6	200.3	205.2	207.7	209.0	207.7	205.2	200.3	192.6	182.0
137.5°	185.5	195.2	203.2	208.3	210.6	211.5	210.6	208.3	203.2	195.2	185.5
140°	188.1	196.5	204.5	209.4	211.9	212.3	211.9	209.4	204.5	196.5	188.1
142.5°	191.4	198.0	205.0	209.9	212.4	213.0	212.4	209.9	205.0	198.0	191.4
145°	197.4	201.3	206.1	210.6	212.9	213.5	212.9	210.6	206.1	201.3	197.4
147.5°	205.0	206.2	208.7	211.7	213.9	214.3	213.9	211.7	208.7	206.2	205.0
150°	210.6	210.3	211.3	213.2	215.2	214.8	215.2	213.2	211.3	210.3	210.6
152.5°	217.1	215.2	215.2	216.1	217.0	216.9	217.0	216.1	215.2	215.2	217.1
155°	228.0	224.5	222.6	221.9	221.9	221.6	221.9	221.9	222.6	224.5	228.0
157.5°	240.1	235.1	232.2	230.7	230.2	229.5	230.2	230.7	232.2	235.1	240.1
160°	248.3	242.9	240.0	237.4	236.4	235.4	236.4	237.4	240.0	242.9	248.3
162.5°	256.1	250.8	247.7	245.4	244.4	242.9	244.4	245.4	247.7	250.8	256.1
165°	268.6	263.1	259.6	257.7	256.4	255.1	256.4	257.7	259.6	263.1	268.6
167.5°	281.2	275.2	272.9	270.7	269.5	267.1	269.5	270.7	272.9	275.2	281.2
170°	288.9	283.4	282.1	280.2	278.0	275.4	278.0	280.2	282.1	283.4	288.9
172.5°	295.6	291.9	290.6	288.7	288.0	285.9	288.0	288.7	290.6	291.9	295.6
175°	305.3	302.4	302.4	302.1	301.1	299.2	301.1	302.1	302.4	302.4	305.3
177.5°	313.5	311.9	312.9	312.9	312.7	310.9	312.7	312.9	312.9	311.9	313.5
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2680.9	2680.9	2680.9	2680.9
2.5°	2679.8	2687.8	2691.0	2694.2
5°	2677.9	2687.0	2691.0	2695.0
7.5°	2682.1	2688.8	2690.5	2692.2
10°	2683.4	2692.3	2691.7	2691.2
12.5°	2687.6	2699.5	2694.8	2690.1
15°	2685.6	2701.7	2692.6	2683.4
17.5°	2654.7	2676.6	2665.8	2654.9
20°	2618.8	2644.7	2633.9	2623.0
22.5°	2568.4	2596.2	2584.4	2572.7
25°	2467.1	2496.1	2487.0	2477.8
27.5°	2333.4	2361.4	2356.4	2351.4
30°	2228.5	2251.1	2248.8	2246.5
32.5°	2106.8	2126.6	2124.4	2122.1
35°	1896.1	1908.8	1909.9	1911.1
37.5°	1640.8	1650.3	1648.7	1647.1
40°	1459.5	1467.4	1466.2	1465.1
42.5°	1270.4	1277.3	1260.2	1243.0
45°	962.6	949.6	897.6	845.6
47.5°	634.8	595.9	536.7	477.6
50°	430.5	380.7	340.7	300.7
52.5°	301.0	254.0	233.7	213.3
55°	170.1	147.2	139.8	132.4
57.5°	104.1	94.0	86.3	78.7
60°	75.0	66.5	60.3	54.0
62.5°	58.5	52.0	49.4	46.8
65°	42.8	42.3	41.7	41.1
67.5°	37.2	37.4	36.8	36.2
70°	33.4	33.3	32.7	32.1
72.5°	30.0	30.2	29.6	29.0
75°	24.4	24.4	24.4	24.4
77.5°	19.4	19.6	19.1	18.5
80°	16.3	16.6	16.0	15.4
82.5°	12.5	12.6	12.5	12.3
85°	7.3	7.7	7.7	7.7
87.5°	3.9	3.7	3.0	2.2
90°	5.8	3.5	2.3	1.0
92.5°	12.5	8.7	6.1	3.5
95°	25.1	20.0	14.2	10.0
97.5°	40.0	31.7	26.0	19.1
100°	48.0	39.9	34.5	27.1
102.5°	56.8	50.0	42.5	35.0
105°	72.5	64.1	55.4	47.0
107.5°	87.0	77.8	67.4	59.8
110°	96.3	86.3	75.4	68.6



TEST NUMBER: P1428509

CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	105.3	95.1	83.9	77.1
115°	117.6	106.3	96.0	90.2
117.5°	129.3	117.8	106.9	102.3
120°	136.6	125.0	114.3	110.8
122.5°	142.5	131.2	121.3	119.8
125°	151.4	139.8	131.4	133.3
127.5°	158.6	148.0	142.7	147.0
130°	163.0	153.6	150.4	156.5
132.5°	166.8	159.6	158.1	166.6
135°	172.6	168.5	169.7	181.3
137.5°	179.5	177.9	182.2	196.9
140°	183.9	184.9	191.0	207.4
142.5°	189.8	192.1	200.0	217.5
145°	199.0	203.9	214.2	231.6
147.5°	209.5	215.7	228.5	246.3
150°	216.4	224.5	238.0	255.1
152.5°	224.4	232.7	246.3	263.6
155°	236.7	246.1	260.2	275.1
157.5°	249.3	258.8	272.4	285.3
160°	257.0	267.3	279.6	291.5
162.5°	265.8	275.3	286.0	296.6
165°	278.6	286.3	295.0	304.0
167.5°	289.4	295.8	302.6	309.7
170°	296.3	301.5	307.3	312.7
172.5°	302.2	306.4	310.6	315.3
175°	310.2	312.4	315.0	317.9
177.5°	316.3	317.1	317.8	319.1
180°	318.9	318.9	318.9	318.9



TEST NUMBER: P1428509  
 CATALOG NUMBER: SQ2W-WBM-K-025U-100D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.76	8.71	8.42	9.35	10.09	7.74	8.69	8.40	9.33	10.07
	3H	8.46	9.30	9.13	9.95	10.73	8.38	9.22	9.05	9.87	10.65
	4H	8.83	9.61	9.52	10.28	11.07	8.69	9.47	9.38	10.14	10.93
	6H	9.11	9.82	9.81	10.51	11.31	8.93	9.65	9.63	10.33	11.13
	8H	9.23	9.91	9.95	10.61	11.41	9.03	9.71	9.75	10.41	11.21
	12H	9.32	9.96	10.03	10.65	11.48	9.09	9.73	9.81	10.42	11.25
4H	2H	7.87	8.65	8.57	9.32	10.12	7.86	8.64	8.55	9.31	10.10
	3H	8.83	9.46	9.53	10.17	10.98	8.75	9.38	9.45	10.09	10.90
	4H	9.34	9.91	10.05	10.62	11.46	9.19	9.76	9.91	10.47	11.31
	6H	9.77	10.26	10.51	10.99	11.85	9.57	10.06	10.31	10.80	11.65
	8H	9.96	10.41	10.70	11.15	12.01	9.74	10.19	10.48	10.92	11.78
	12H	10.09	10.49	10.85	11.25	12.11	9.83	10.23	10.59	10.99	11.86
8H	4H	9.46	9.91	10.20	10.65	11.51	9.32	9.78	10.07	10.51	11.37
	6H	10.03	10.41	10.80	11.18	12.05	9.84	10.21	10.61	10.99	11.86
	8H	10.32	10.65	11.10	11.43	12.31	10.10	10.44	10.89	11.22	12.09
	12H	10.54	10.83	11.32	11.60	12.54	10.28	10.57	11.06	11.33	12.28
12H	4H	9.44	9.85	10.20	10.60	11.47	9.32	9.72	10.07	10.48	11.34
	6H	10.06	10.40	10.85	11.18	12.05	9.88	10.21	10.67	10.99	11.87
	8H	10.40	10.69	11.18	11.45	12.40	10.19	10.48	10.97	11.25	12.19