

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428524

Luminaire Tested: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428524  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7068.4 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 64.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	106	102	99	97	101	98	95	93	89	87	85	81	79	78	73	72	71	68		
2	99	93	88	84	94	89	84	81	81	78	75	74	72	70	68	66	64	61		
3	92	84	78	73	88	81	75	71	74	70	67	68	65	62	63	60	58	55		
4	86	77	70	65	82	74	68	63	68	63	60	63	59	56	58	55	53	50		
5	80	70	63	58	76	68	61	56	63	58	54	58	54	51	54	51	48	46		
6	75	64	57	52	71	62	56	51	58	52	48	54	49	46	50	47	44	42		
7	70	59	52	47	67	57	51	46	53	48	44	50	45	42	47	43	40	38		
8	66	54	47	43	63	53	46	42	49	44	40	46	42	38	43	40	37	35		
9	62	50	44	39	59	49	43	38	46	41	37	43	39	35	41	37	34	32		
10	58	47	40	36	56	45	39	35	43	37	34	40	36	33	38	34	31	30		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	54063	54063	54063	54063
5°	54557	54531	54557	54531
10°	55107	55081	55107	55081
15°	56024	55031	56024	55031
20°	56293	54141	56293	54141
25°	55135	52617	55135	52617
30°	52311	49200	52311	49200
35°	47048	44389	47048	44389
40°	38570	36538	38570	36538
45°	24116	22651	24116	22651
50°	9434	8628	9434	8628
55°	4653	4608	4653	4608
60°	2176	1970	2176	1970
65°	1964	1841	1964	1841
70°	1893	1817	1893	1817
75°	1903	1703	1903	1703
80°	1794	1646	1794	1646
85°	1778	1482	1778	1482

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 30°  
 Vertical Angle: 45°  
 Luminance: 27452 cd/sqm



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	320.2	4.5
10°-20°	936.2	13.2
20°-30°	1384.2	19.6
30°-40°	1432.1	20.3
40°-50°	861.4	12.2
50°-60°	205.9	2.9
60°-70°	56.3	0.8
70°-80°	31.5	0.4
80°-90°	12.5	0.2
90°-100°	49.8	0.7
100°-110°	145.3	2.1
110°-120°	237.1	3.4
120°-130°	300.9	4.3
130°-140°	322.0	4.6
140°-150°	300.7	4.3
150°-160°	247.4	3.5
160°-170°	165.9	2.3
170°-180°	58.9	0.8
0°-30°	2640.5	37.4
0°-40°	4072.6	57.6
0°-60°	5140.0	72.7
0°-90°	5240.3	74.1
90°-120°	432.3	6.1
90°-150°	1355.8	19.2
90°-180°	1828.0	25.9
0°-180°	7068.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	3348	3348	3348	3348	3348	
5°	3366	3365	3366	3365	3366	321
15°	3352	3292	3352	3292	3352	945
25°	3095	2954	3095	2954	3095	1415
35°	2387	2252	2387	2252	2387	1465
45°	1056	992	1056	992	1056	817
55°	165	164	165	164	165	166
65°	51	48	51	48	51	52
75°	30	27	30	27	30	32
85°	10	8	10	8	10	10
90°	2	14	2	27	2	2
95°	20	14	20	85	20	24
105°	92	148	92	204	92	98
115°	177	245	177	302	177	175
125°	262	389	262	371	262	234
135°	356	509	356	410	356	275
145°	455	587	455	419	455	285
155°	540	638	540	435	540	248
165°	597	665	597	501	597	168
175°	624	651	624	588	624	59
180°	626	626	626	626	626	



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5
2.5°	3365.2	3361.2	3357.2	3347.2	3335.2	3335.5	3348.1	3356.8	3353.9	3351.1	3353.9
5°	3366.2	3361.2	3356.2	3344.8	3331.2	3334.4	3354.4	3368.8	3366.7	3364.6	3366.7
7.5°	3362.6	3360.5	3358.4	3350.0	3339.6	3341.9	3357.1	3367.6	3364.3	3361.0	3364.3
10°	3361.3	3362.1	3362.8	3351.7	3336.7	3337.1	3352.8	3364.0	3361.9	3359.7	3361.9
12.5°	3360.1	3365.9	3371.8	3356.9	3335.0	3330.2	3342.5	3350.5	3345.5	3340.5	3345.5
15°	3351.7	3363.1	3374.5	3354.4	3323.7	3308.4	3308.4	3306.6	3299.5	3292.3	3299.5
17.5°	3316.1	3329.6	3343.2	3315.9	3274.9	3248.9	3238.0	3227.5	3218.8	3210.1	3218.8
20°	3276.3	3289.8	3303.4	3270.9	3223.1	3190.3	3172.5	3158.2	3154.6	3151.1	3154.6
22.5°	3213.3	3228.0	3242.7	3208.0	3156.8	3121.4	3101.8	3085.7	3079.9	3074.0	3079.9
25°	3094.9	3106.3	3117.7	3081.5	3029.4	2996.2	2982.0	2969.3	2961.5	2953.6	2961.5
27.5°	2936.9	2943.2	2949.5	2914.5	2865.7	2833.1	2816.9	2801.9	2791.1	2780.3	2791.1
30°	2805.9	2808.8	2811.6	2783.5	2744.9	2715.0	2693.6	2673.2	2656.1	2639.0	2656.1
32.5°	2650.6	2653.4	2656.3	2631.5	2597.5	2570.4	2550.2	2531.6	2517.9	2504.2	2517.9
35°	2387.0	2385.5	2384.1	2368.2	2347.6	2325.4	2301.9	2280.7	2266.4	2252.1	2266.4
37.5°	2057.3	2059.3	2061.3	2049.4	2033.0	2015.6	1997.0	1979.5	1965.1	1950.7	1965.1
40°	1830.0	1831.4	1832.8	1823.0	1809.4	1789.1	1762.0	1740.8	1737.2	1733.6	1737.2
42.5°	1552.6	1574.0	1595.4	1586.7	1568.0	1548.3	1527.4	1507.6	1490.9	1474.2	1490.9
45°	1056.2	1121.2	1186.1	1202.3	1202.3	1189.8	1164.9	1129.0	1060.5	992.0	1060.5
47.5°	596.5	670.4	744.3	792.9	833.0	815.9	741.7	665.3	582.1	498.9	582.1
50°	375.6	425.6	475.5	537.8	604.1	585.9	483.2	399.2	371.3	343.5	371.3
52.5°	266.5	291.9	317.3	375.9	445.7	437.2	350.5	281.7	267.0	252.3	267.0
55°	165.3	174.6	183.9	212.4	247.4	245.2	206.0	175.1	169.4	163.7	169.4
57.5°	98.2	107.8	117.4	130.0	143.7	143.7	130.0	117.5	108.5	99.5	108.5
60°	67.4	75.3	83.1	93.6	105.1	103.6	89.4	76.7	68.8	61.0	68.8
62.5°	58.4	61.7	65.0	73.1	82.8	81.9	70.5	61.3	58.6	55.9	58.6
65°	51.4	52.1	52.8	53.5	54.2	53.9	52.4	51.0	49.6	48.2	49.6
67.5°	45.3	46.0	46.7	46.4	45.9	45.5	45.4	44.9	43.7	42.4	43.7
70°	40.1	40.8	41.6	41.7	41.7	41.4	40.7	40.0	39.2	38.5	39.2
72.5°	36.3	37.0	37.7	37.5	36.9	36.5	36.4	36.0	34.7	33.4	34.7
75°	30.5	30.5	30.5	30.5	30.5	30.1	29.4	28.7	28.0	27.3	28.0
77.5°	23.1	23.8	24.5	24.2	23.5	23.1	23.1	22.9	22.2	21.5	22.2
80°	19.3	20.0	20.7	20.3	19.6	19.3	19.3	19.1	18.4	17.7	18.4
82.5°	15.4	15.6	15.7	15.6	15.5	15.4	15.4	15.2	14.5	13.8	14.5
85°	9.6	9.6	9.6	9.1	8.4	8.0	8.0	8.0	8.0	8.0	8.0
87.5°	2.9	4.0	5.2	5.4	5.3	5.1	5.1	5.2	5.4	5.4	5.4
90°	1.9	4.4	7.6	10.1	12.0	12.6	12.6	13.3	13.9	13.9	13.9
92.5°	7.0	11.0	11.1	11.1	13.5	14.7	15.7	15.8	16.4	16.4	16.4
95°	19.6	21.5	32.3	31.6	21.5	17.1	14.5	14.5	14.5	14.5	14.5
97.5°	37.4	40.2	42.0	56.3	59.4	57.4	46.8	39.3	35.2	33.3	35.2
100°	53.1	54.4	58.2	58.8	74.6	89.8	82.2	72.7	69.6	67.7	69.6
102.5°	68.8	69.6	75.4	78.0	81.7	90.3	116.6	113.7	111.6	111.2	111.6
105°	92.3	93.0	103.7	108.8	111.3	111.3	110.7	123.3	143.6	148.0	143.6
107.5°	117.5	120.4	133.1	146.6	149.5	150.3	147.0	145.1	144.3	144.8	144.3
110°	134.7	139.1	154.3	171.4	175.8	177.1	175.8	173.9	172.6	172.6	172.6



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	151.4	157.8	175.0	194.7	202.1	205.9	203.1	201.7	200.5	201.5	200.5
115°	177.1	186.6	209.3	229.6	244.7	246.6	246.0	246.0	245.4	245.4	245.4
117.5°	200.9	216.0	241.6	265.1	282.7	287.7	290.3	289.5	288.8	290.0	288.8
120°	217.5	235.3	264.3	290.9	308.0	315.6	318.1	316.8	318.1	316.8	318.1
122.5°	235.3	257.0	285.6	313.2	333.3	341.9	344.9	345.2	345.4	344.7	345.4
125°	261.8	288.4	321.9	350.4	371.2	381.3	383.9	384.5	385.8	388.9	385.8
127.5°	288.6	318.7	355.5	383.0	404.4	416.6	420.5	421.9	424.6	426.0	424.6
130°	307.3	341.5	378.8	404.7	425.6	438.9	445.8	447.7	450.9	450.3	450.9
132.5°	327.1	362.7	400.6	427.5	446.9	461.2	467.1	472.5	473.7	474.6	473.7
135°	356.0	394.6	432.6	459.1	477.5	491.4	499.0	504.0	507.2	509.1	507.2
137.5°	386.5	427.3	463.7	487.3	505.8	517.8	526.4	531.7	535.0	536.5	535.0
140°	407.3	446.5	481.9	506.6	523.0	535.0	542.6	548.9	552.7	552.7	552.7
142.5°	427.0	465.7	500.1	524.8	539.2	550.2	558.3	563.1	567.4	567.4	567.4
145°	454.7	493.3	524.9	549.6	561.6	571.7	580.5	584.3	586.9	586.9	586.9
147.5°	483.7	517.8	546.7	570.3	580.4	592.3	599.3	602.3	605.5	604.1	605.5
150°	500.9	532.5	560.3	582.4	592.6	603.9	610.9	613.4	616.6	614.7	616.6
152.5°	517.6	547.7	573.0	593.6	602.2	613.6	621.5	624.1	626.2	624.8	626.2
155°	540.1	566.6	590.0	609.0	616.6	627.3	634.9	638.1	640.6	637.5	640.6
157.5°	560.2	583.1	603.4	620.9	629.0	638.2	645.3	649.2	651.8	650.4	651.8
160°	572.3	593.2	611.5	628.0	635.6	643.8	651.4	655.8	658.3	656.4	658.3
162.5°	582.4	601.3	618.6	633.5	640.1	647.3	656.4	660.4	662.9	660.5	662.9
165°	597.0	612.2	627.3	640.0	645.7	651.4	660.9	665.3	667.2	664.7	667.2
167.5°	608.0	619.6	631.9	642.8	647.0	652.5	662.0	665.7	668.1	664.9	668.1
170°	614.1	624.2	634.9	643.8	647.0	652.0	661.5	664.7	666.6	663.4	666.6
172.5°	619.1	626.7	635.4	643.3	644.9	649.0	658.0	661.1	662.5	659.9	662.5
175°	624.2	628.6	634.9	640.0	639.4	641.9	649.5	652.0	654.5	650.7	654.5
177.5°	626.6	628.6	630.6	633.7	631.6	631.6	637.2	638.7	639.2	637.2	639.2
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5
2.5°	3356.8	3348.1	3335.5	3335.2	3347.2	3357.2	3361.2	3365.2	3361.2	3357.2	3347.2
5°	3368.8	3354.4	3334.4	3331.2	3344.8	3356.2	3361.2	3366.2	3361.2	3356.2	3344.8
7.5°	3367.6	3357.1	3341.9	3339.6	3350.0	3358.4	3360.5	3362.6	3360.5	3358.4	3350.0
10°	3364.0	3352.8	3337.1	3336.7	3351.7	3362.8	3362.1	3361.3	3362.1	3362.8	3351.7
12.5°	3350.5	3342.5	3330.2	3335.0	3356.9	3371.8	3365.9	3360.1	3365.9	3371.8	3356.9
15°	3306.6	3308.4	3308.4	3323.7	3354.4	3374.5	3363.1	3351.7	3363.1	3374.5	3354.4
17.5°	3227.5	3238.0	3248.9	3274.9	3315.9	3343.2	3329.6	3316.1	3329.6	3343.2	3315.9
20°	3158.2	3172.5	3190.3	3223.1	3270.9	3303.4	3289.8	3276.3	3289.8	3303.4	3270.9
22.5°	3085.7	3101.8	3121.4	3156.8	3208.0	3242.7	3228.0	3213.3	3228.0	3242.7	3208.0
25°	2969.3	2982.0	2996.2	3029.4	3081.5	3117.7	3106.3	3094.9	3106.3	3117.7	3081.5
27.5°	2801.9	2816.9	2833.1	2865.7	2914.5	2949.5	2943.2	2936.9	2943.2	2949.5	2914.5
30°	2673.2	2693.6	2715.0	2744.9	2783.5	2811.6	2808.8	2805.9	2808.8	2811.6	2783.5
32.5°	2531.6	2550.2	2570.4	2597.5	2631.5	2656.3	2653.4	2650.6	2653.4	2656.3	2631.5
35°	2280.7	2301.9	2325.4	2347.6	2368.2	2384.1	2385.5	2387.0	2385.5	2384.1	2368.2
37.5°	1979.5	1997.0	2015.6	2033.0	2049.4	2061.3	2059.3	2057.3	2059.3	2061.3	2049.4
40°	1740.8	1762.0	1789.1	1809.4	1823.0	1832.8	1831.4	1830.0	1831.4	1832.8	1823.0
42.5°	1507.6	1527.4	1548.3	1568.0	1586.7	1595.4	1574.0	1552.6	1574.0	1595.4	1586.7
45°	1129.0	1164.9	1189.8	1202.3	1202.3	1186.1	1121.2	1056.2	1121.2	1186.1	1202.3
47.5°	665.3	741.7	815.9	833.0	792.9	744.3	670.4	596.5	670.4	744.3	792.9
50°	399.2	483.2	585.9	604.1	537.8	475.5	425.6	375.6	425.6	475.5	537.8
52.5°	281.7	350.5	437.2	445.7	375.9	317.3	291.9	266.5	291.9	317.3	375.9
55°	175.1	206.0	245.2	247.4	212.4	183.9	174.6	165.3	174.6	183.9	212.4
57.5°	117.5	130.0	143.7	143.7	130.0	117.4	107.8	98.2	107.8	117.4	130.0
60°	76.7	89.4	103.6	105.1	93.6	83.1	75.3	67.4	75.3	83.1	93.6
62.5°	61.3	70.5	81.9	82.8	73.1	65.0	61.7	58.4	61.7	65.0	73.1
65°	51.0	52.4	53.9	54.2	53.5	52.8	52.1	51.4	52.1	52.8	53.5
67.5°	44.9	45.4	45.5	45.9	46.4	46.7	46.0	45.3	46.0	46.7	46.4
70°	40.0	40.7	41.4	41.7	41.7	41.6	40.8	40.1	40.8	41.6	41.7
72.5°	36.0	36.4	36.5	36.9	37.5	37.7	37.0	36.3	37.0	37.7	37.5
75°	28.7	29.4	30.1	30.5	30.5	30.5	30.5	30.5	30.5	30.5	30.5
77.5°	22.9	23.1	23.1	23.5	24.2	24.5	23.8	23.1	23.8	24.5	24.2
80°	19.1	19.3	19.3	19.6	20.3	20.7	20.0	19.3	20.0	20.7	20.3
82.5°	15.2	15.4	15.4	15.5	15.6	15.7	15.6	15.4	15.6	15.7	15.6
85°	8.0	8.0	8.0	8.4	9.1	9.6	9.6	9.6	9.6	9.6	9.1
87.5°	5.2	5.1	5.1	5.3	5.4	5.2	4.0	2.9	4.0	5.1	5.7
90°	13.3	12.6	12.6	12.0	10.1	7.6	4.4	1.9	4.4	7.0	11.4
92.5°	15.8	15.7	14.7	13.5	11.1	11.1	11.0	7.0	12.0	17.1	24.5
95°	14.5	14.5	17.1	21.5	31.6	32.3	21.5	19.6	27.8	39.2	49.3
97.5°	39.3	46.8	57.4	59.4	56.3	42.0	40.2	37.4	51.0	62.2	78.5
100°	72.7	82.2	89.8	74.6	58.8	58.2	54.4	53.1	67.7	78.4	94.2
102.5°	113.7	116.6	90.3	81.7	78.0	75.4	69.6	68.8	83.4	98.1	111.4
105°	123.3	110.7	111.3	111.3	108.8	103.7	93.0	92.3	108.8	125.8	142.3
107.5°	145.1	147.0	150.3	149.5	146.6	133.1	120.4	117.5	132.3	152.8	170.9
110°	173.9	175.8	177.1	175.8	171.4	154.3	139.1	134.7	148.0	169.5	189.1



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	201.7	203.1	205.9	202.1	194.7	175.0	157.8	151.4	164.7	186.7	206.8
115°	246.0	246.0	246.6	244.7	229.6	209.3	186.6	177.1	188.5	208.7	230.8
117.5°	289.5	290.3	287.7	282.7	265.1	241.6	216.0	200.9	209.8	231.2	254.0
120°	316.8	318.1	315.6	308.0	290.9	264.3	235.3	217.5	224.5	245.4	268.1
122.5°	345.2	344.9	341.9	333.3	313.2	285.6	257.0	235.3	238.2	257.5	279.8
125°	384.5	383.9	381.3	371.2	350.4	321.9	288.4	261.8	258.0	274.5	297.2
127.5°	421.9	420.5	416.6	404.4	383.0	355.5	318.7	288.6	280.2	290.5	311.4
130°	447.7	445.8	438.9	425.6	404.7	378.8	341.5	307.3	295.3	301.7	320.0
132.5°	472.5	467.1	461.2	446.9	427.5	400.6	362.7	327.1	310.5	313.3	327.6
135°	504.0	499.0	491.4	477.5	459.1	432.6	394.6	356.0	333.3	330.7	339.0
137.5°	531.7	526.4	517.8	505.8	487.3	463.7	427.3	386.5	357.8	349.3	352.5
140°	548.9	542.6	535.0	523.0	506.6	481.9	446.5	407.3	375.0	363.0	361.1
142.5°	563.1	558.3	550.2	539.2	524.8	500.1	465.7	427.0	392.7	377.2	372.7
145°	584.3	580.5	571.7	561.6	549.6	524.9	493.3	454.7	420.5	400.3	390.8
147.5°	602.3	599.3	592.3	580.4	570.3	546.7	517.8	483.7	448.6	423.6	411.3
150°	613.4	610.9	603.9	592.6	582.4	560.3	532.5	500.9	467.3	440.8	425.0
152.5°	624.1	621.5	613.6	602.2	593.6	573.0	547.7	517.6	483.5	457.0	440.7
155°	638.1	634.9	627.3	616.6	609.0	590.0	566.6	540.1	511.0	483.2	464.8
157.5°	649.2	645.3	638.2	629.0	620.9	603.4	583.1	560.2	534.8	508.2	489.5
160°	655.8	651.4	643.8	635.6	628.0	611.5	593.2	572.3	548.9	524.9	504.7
162.5°	660.4	656.4	647.3	640.1	633.5	618.6	601.3	582.4	561.6	540.6	521.9
165°	665.3	660.9	651.4	645.7	640.0	627.3	612.2	597.0	579.3	562.2	547.0
167.5°	665.7	662.0	652.5	647.0	642.8	631.9	619.6	608.0	594.2	580.8	568.2
170°	664.7	661.5	652.0	647.0	643.8	634.9	624.2	614.1	603.3	591.9	581.8
172.5°	661.1	658.0	649.0	644.9	643.3	635.4	626.7	619.1	609.9	601.5	593.4
175°	652.0	649.5	641.9	639.4	640.0	634.9	628.6	624.2	618.5	613.4	609.0
177.5°	638.7	637.2	631.6	631.6	633.7	630.6	628.6	626.6	624.1	622.5	621.0
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5	3348.5
2.5°	3335.2	3335.5	3348.1	3356.8	3353.9	3351.1	3353.9	3356.8	3348.1	3335.5	3335.2
5°	3331.2	3334.4	3354.4	3368.8	3366.7	3364.6	3366.7	3368.8	3354.4	3334.4	3331.2
7.5°	3339.6	3341.9	3357.1	3367.6	3364.3	3361.0	3364.3	3367.6	3357.1	3341.9	3339.6
10°	3336.7	3337.1	3352.8	3364.0	3361.9	3359.7	3361.9	3364.0	3352.8	3337.1	3336.7
12.5°	3335.0	3330.2	3342.5	3350.5	3345.5	3340.5	3345.5	3350.5	3342.5	3330.2	3335.0
15°	3323.7	3308.4	3308.4	3306.6	3299.5	3292.3	3299.5	3306.6	3308.4	3308.4	3323.7
17.5°	3274.9	3248.9	3238.0	3227.5	3218.8	3210.1	3218.8	3227.5	3238.0	3248.9	3274.9
20°	3223.1	3190.3	3172.5	3158.2	3154.6	3151.1	3154.6	3158.2	3172.5	3190.3	3223.1
22.5°	3156.8	3121.4	3101.8	3085.7	3079.9	3074.0	3079.9	3085.7	3101.8	3121.4	3156.8
25°	3029.4	2996.2	2982.0	2969.3	2961.5	2953.6	2961.5	2969.3	2982.0	2996.2	3029.4
27.5°	2865.7	2833.1	2816.9	2801.9	2791.1	2780.3	2791.1	2801.9	2816.9	2833.1	2865.7
30°	2744.9	2715.0	2693.6	2673.2	2656.1	2639.0	2656.1	2673.2	2693.6	2715.0	2744.9
32.5°	2597.5	2570.4	2550.2	2531.6	2517.9	2504.2	2517.9	2531.6	2550.2	2570.4	2597.5
35°	2347.6	2325.4	2301.9	2280.7	2266.4	2252.1	2266.4	2280.7	2301.9	2325.4	2347.6
37.5°	2033.0	2015.6	1997.0	1979.5	1965.1	1950.7	1965.1	1979.5	1997.0	2015.6	2033.0
40°	1809.4	1789.1	1762.0	1740.8	1737.2	1733.6	1737.2	1740.8	1762.0	1789.1	1809.4
42.5°	1568.0	1548.3	1527.4	1507.6	1490.9	1474.2	1490.9	1507.6	1527.4	1548.3	1568.0
45°	1202.3	1189.8	1164.9	1129.0	1060.5	992.0	1060.5	1129.0	1164.9	1189.8	1202.3
47.5°	833.0	815.9	741.7	665.3	582.1	498.9	582.1	665.3	741.7	815.9	833.0
50°	604.1	585.9	483.2	399.2	371.3	343.5	371.3	399.2	483.2	585.9	604.1
52.5°	445.7	437.2	350.5	281.7	267.0	252.3	267.0	281.7	350.5	437.2	445.7
55°	247.4	245.2	206.0	175.1	169.4	163.7	169.4	175.1	206.0	245.2	247.4
57.5°	143.7	143.7	130.0	117.5	108.5	99.5	108.5	117.5	130.0	143.7	143.7
60°	105.1	103.6	89.4	76.7	68.8	61.0	68.8	76.7	89.4	103.6	105.1
62.5°	82.8	81.9	70.5	61.3	58.6	55.9	58.6	61.3	70.5	81.9	82.8
65°	54.2	53.9	52.4	51.0	49.6	48.2	49.6	51.0	52.4	53.9	54.2
67.5°	45.9	45.5	45.4	44.9	43.7	42.4	43.7	44.9	45.4	45.5	45.9
70°	41.7	41.4	40.7	40.0	39.2	38.5	39.2	40.0	40.7	41.4	41.7
72.5°	36.9	36.5	36.4	36.0	34.7	33.4	34.7	36.0	36.4	36.5	36.9
75°	30.5	30.1	29.4	28.7	28.0	27.3	28.0	28.7	29.4	30.1	30.5
77.5°	23.5	23.1	23.1	22.9	22.2	21.5	22.2	22.9	23.1	23.1	23.5
80°	19.6	19.3	19.3	19.1	18.4	17.7	18.4	19.1	19.3	19.3	19.6
82.5°	15.5	15.4	15.4	15.2	14.5	13.8	14.5	15.2	15.4	15.4	15.5
85°	8.4	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.4
87.5°	5.8	6.4	7.2	7.8	8.3	8.0	8.3	7.8	7.2	6.4	5.8
90°	14.5	19.0	23.4	25.9	28.5	27.2	28.5	25.9	23.4	19.0	14.5
92.5°	29.2	36.7	42.1	46.7	48.7	48.4	48.7	46.7	42.1	36.7	29.2
95°	58.8	67.7	76.5	82.8	86.6	85.4	86.6	82.8	76.5	67.7	58.8
97.5°	90.7	102.6	112.4	118.4	122.2	124.7	122.2	118.4	112.4	102.6	90.7
100°	111.9	123.3	134.7	141.7	148.0	150.5	148.0	141.7	134.7	123.3	111.9
102.5°	129.1	144.1	156.5	163.9	169.2	171.8	169.2	163.9	156.5	144.1	129.1
105°	157.5	173.3	186.6	196.0	201.7	203.6	201.7	196.0	186.6	173.3	157.5
107.5°	185.8	202.1	214.4	224.9	231.8	235.9	231.8	224.9	214.4	202.1	185.8
110°	208.1	221.3	234.6	244.1	251.1	253.6	251.1	244.1	234.6	221.3	208.1

TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	226.8	241.6	254.9	264.3	272.3	275.9	272.3	264.3	254.9	241.6	226.8
115°	253.0	272.6	284.6	293.4	299.1	302.3	299.1	293.4	284.6	272.6	253.0
117.5°	274.7	295.2	308.4	315.2	317.8	320.1	317.8	315.2	308.4	295.2	274.7
120°	288.4	307.3	322.5	331.4	334.5	335.8	334.5	331.4	322.5	307.3	288.4
122.5°	301.0	319.0	333.7	344.5	349.7	351.0	349.7	344.5	333.7	319.0	301.0
125°	318.7	335.8	351.0	361.7	367.4	370.6	367.4	361.7	351.0	335.8	318.7
127.5°	334.2	352.6	366.5	376.3	381.8	384.4	381.8	376.3	366.5	352.6	334.2
130°	342.8	361.7	375.6	386.4	391.5	394.0	391.5	386.4	375.6	361.7	342.8
132.5°	349.3	369.3	383.7	393.5	399.0	401.6	399.0	393.5	383.7	369.3	349.3
135°	357.3	378.2	393.4	402.8	407.9	410.4	407.9	402.8	393.4	378.2	357.3
137.5°	364.3	383.2	399.0	409.0	413.6	415.2	413.6	409.0	399.0	383.2	364.3
140°	369.3	385.8	401.6	411.1	416.1	416.8	416.1	411.1	401.6	385.8	369.3
142.5°	375.9	388.8	402.6	412.1	417.1	418.3	417.1	412.1	402.6	388.8	375.9
145°	387.7	395.3	404.7	413.6	418.0	419.3	418.0	413.6	404.7	395.3	387.7
147.5°	402.5	404.9	409.8	415.6	419.9	420.8	419.9	415.6	409.8	404.9	402.5
150°	413.6	413.0	414.9	418.7	422.4	421.8	422.4	418.7	414.9	413.0	413.6
152.5°	426.2	422.6	422.4	424.2	426.0	425.9	426.0	424.2	422.4	422.6	426.2
155°	447.7	440.8	437.0	435.7	435.7	435.1	435.7	435.7	437.0	440.8	447.7
157.5°	471.4	461.7	456.0	452.9	452.0	450.7	452.0	452.9	456.0	461.7	471.4
160°	487.6	476.8	471.1	466.1	464.2	462.3	464.2	466.1	471.1	476.8	487.6
162.5°	502.8	492.5	486.3	481.8	479.9	477.0	479.9	481.8	486.3	492.5	502.8
165°	527.4	516.7	509.7	505.9	503.4	500.9	503.4	505.9	509.7	516.7	527.4
167.5°	552.1	540.3	535.8	531.5	529.1	524.5	529.1	531.5	535.8	540.3	552.1
170°	567.3	556.5	554.0	550.2	545.8	540.7	545.8	550.2	554.0	556.5	567.3
172.5°	580.4	573.2	570.7	566.9	565.5	561.4	565.5	566.9	570.7	573.2	580.4
175°	599.5	593.8	593.8	593.2	591.3	587.5	591.3	593.2	593.8	593.8	599.5
177.5°	615.5	612.4	614.4	614.4	613.9	610.4	613.9	614.4	614.4	612.4	615.5
180°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1



TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	3348.5	3348.5	3348.5	3348.5
2.5°	3347.2	3357.2	3361.2	3365.2
5°	3344.8	3356.2	3361.2	3366.2
7.5°	3350.0	3358.4	3360.5	3362.6
10°	3351.7	3362.8	3362.1	3361.3
12.5°	3356.9	3371.8	3365.9	3360.1
15°	3354.4	3374.5	3363.1	3351.7
17.5°	3315.9	3343.2	3329.6	3316.1
20°	3270.9	3303.4	3289.8	3276.3
22.5°	3208.0	3242.7	3228.0	3213.3
25°	3081.5	3117.7	3106.3	3094.9
27.5°	2914.5	2949.5	2943.2	2936.9
30°	2783.5	2811.6	2808.8	2805.9
32.5°	2631.5	2656.3	2653.4	2650.6
35°	2368.2	2384.1	2385.5	2387.0
37.5°	2049.4	2061.3	2059.3	2057.3
40°	1823.0	1832.8	1831.4	1830.0
42.5°	1586.7	1595.4	1574.0	1552.6
45°	1202.3	1186.1	1121.2	1056.2
47.5°	792.9	744.3	670.4	596.5
50°	537.8	475.5	425.6	375.6
52.5°	375.9	317.3	291.9	266.5
55°	212.4	183.9	174.6	165.3
57.5°	130.0	117.4	107.8	98.2
60°	93.6	83.1	75.3	67.4
62.5°	73.1	65.0	61.7	58.4
65°	53.5	52.8	52.1	51.4
67.5°	46.4	46.7	46.0	45.3
70°	41.7	41.6	40.8	40.1
72.5°	37.5	37.7	37.0	36.3
75°	30.5	30.5	30.5	30.5
77.5°	24.2	24.5	23.8	23.1
80°	20.3	20.7	20.0	19.3
82.5°	15.6	15.7	15.6	15.4
85°	9.1	9.6	9.6	9.6
87.5°	5.7	5.1	4.0	2.9
90°	11.4	7.0	4.4	1.9
92.5°	24.5	17.1	12.0	7.0
95°	49.3	39.2	27.8	19.6
97.5°	78.5	62.2	51.0	37.4
100°	94.2	78.4	67.7	53.1
102.5°	111.4	98.1	83.4	68.8
105°	142.3	125.8	108.8	92.3
107.5°	170.9	152.8	132.3	117.5
110°	189.1	169.5	148.0	134.7

TEST NUMBER: P1428524

CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	206.8	186.7	164.7	151.4
115°	230.8	208.7	188.5	177.1
117.5°	254.0	231.2	209.8	200.9
120°	268.1	245.4	224.5	217.5
122.5°	279.8	257.5	238.2	235.3
125°	297.2	274.5	258.0	261.8
127.5°	311.4	290.5	280.2	288.6
130°	320.0	301.7	295.3	307.3
132.5°	327.6	313.3	310.5	327.1
135°	339.0	330.7	333.3	356.0
137.5°	352.5	349.3	357.8	386.5
140°	361.1	363.0	375.0	407.3
142.5°	372.7	377.2	392.7	427.0
145°	390.8	400.3	420.5	454.7
147.5°	411.3	423.6	448.6	483.7
150°	425.0	440.8	467.3	500.9
152.5°	440.7	457.0	483.5	517.6
155°	464.8	483.2	511.0	540.1
157.5°	489.5	508.2	534.8	560.2
160°	504.7	524.9	548.9	572.3
162.5°	521.9	540.6	561.6	582.4
165°	547.0	562.2	579.3	597.0
167.5°	568.2	580.8	594.2	608.0
170°	581.8	591.9	603.3	614.1
172.5°	593.4	601.5	609.9	619.1
175°	609.0	613.4	618.5	624.2
177.5°	621.0	622.5	624.1	626.6
180°	626.1	626.1	626.1	626.1



TEST NUMBER: P1428524  
 CATALOG NUMBER: SQ2W-WBM-K-050U-125D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.91	8.79	8.66	9.53	10.42	7.89	8.77	8.64	9.51	10.41
	3H	8.61	9.38	9.37	10.14	11.06	8.52	9.30	9.29	10.06	10.98
	4H	8.98	9.70	9.76	10.47	11.41	8.83	9.56	9.62	10.33	11.26
	6H	9.25	9.92	10.05	10.69	11.64	9.07	9.74	9.87	10.51	11.46
	8H	9.37	10.00	10.18	10.79	11.74	9.17	9.80	9.98	10.59	11.54
	12H	9.45	10.05	10.26	10.84	11.81	9.23	9.82	10.03	10.61	11.58
4H	2H	8.02	8.74	8.81	9.51	10.45	8.00	8.73	8.79	9.49	10.43
	3H	8.97	9.56	9.76	10.36	11.31	8.88	9.47	9.68	10.28	11.23
	4H	9.47	10.01	10.28	10.81	11.79	9.33	9.86	10.14	10.66	11.65
	6H	9.91	10.36	10.73	11.19	12.18	9.71	10.16	10.53	10.99	11.98
	8H	10.09	10.52	10.92	11.34	12.34	9.87	10.30	10.70	11.12	12.12
	12H	10.22	10.60	11.07	11.45	12.45	9.96	10.34	10.81	11.19	12.19
8H	4H	9.60	10.02	10.43	10.84	11.84	9.46	9.89	10.29	10.71	11.70
	6H	10.17	10.52	11.03	11.38	12.38	9.98	10.33	10.83	11.19	12.19
	8H	10.46	10.77	11.33	11.63	12.65	10.24	10.55	11.11	11.41	12.43
	12H	10.68	10.95	11.54	11.80	12.87	10.41	10.68	11.28	11.53	12.61
12H	4H	9.58	9.96	10.42	10.80	11.80	9.45	9.83	10.29	10.67	11.67
	6H	10.20	10.51	11.07	11.37	12.39	10.02	10.33	10.89	11.19	12.21
	8H	10.53	10.80	11.40	11.65	12.73	10.32	10.60	11.19	11.45	12.52