

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427523

Luminaire Tested: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427523  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5879.8 lumens  
Efficiency: N/A  
Efficacy: 114.8 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 51.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	100	96	93	90	92	89	87	84	76	75	73	64	63	62	53	53	52	47				
2	93	87	82	77	86	81	76	73	70	66	64	59	57	55	50	48	47	43				
3	86	78	72	67	80	73	68	63	63	59	56	54	52	49	46	44	43	39				
4	80	71	64	59	74	66	60	56	58	53	50	50	47	44	43	40	39	35				
5	74	64	57	52	69	60	54	50	53	48	45	46	43	40	40	37	35	32				
6	69	59	51	46	64	55	49	44	49	44	40	42	39	36	37	34	32	29				
7	64	54	46	42	60	50	44	40	45	40	36	39	36	33	34	31	29	27				
8	60	49	42	37	56	46	40	36	41	36	33	36	33	30	32	29	27	25				
9	56	45	39	34	53	43	37	33	38	33	30	34	30	27	30	27	25	23				
10	53	42	35	31	49	40	34	30	35	31	27	32	28	25	28	25	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	32275	32275	32275	32275
5°	32528	32577	32528	32577
10°	32937	32888	32937	32888
15°	33530	32862	33530	32862
20°	33573	32267	33573	32267
25°	32743	31461	32743	31461
30°	30780	29345	30780	29345
35°	27318	26293	27318	26293
40°	22404	21203	22404	21203
45°	13357	12535	13357	12535
50°	4170	3944	4170	3944
55°	1576	1576	1576	1576
60°	97	32	97	32
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 15638 cd/sqm



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.1	3.3
10°-20°	559.9	9.5
20°-30°	823.7	14.0
30°-40°	841.9	14.3
40°-50°	485.0	8.2
50°-60°	83.5	1.4
60°-70°	3.0	0.1
70°-80°	0.0	0.0
80°-90°	5.3	0.1
90°-100°	78.7	1.3
100°-110°	229.5	3.9
110°-120°	374.6	6.4
120°-130°	475.3	8.1
130°-140°	508.6	8.7
140°-150°	474.9	8.1
150°-160°	390.8	6.6
160°-170°	262.1	4.5
170°-180°	93.1	1.6
0°-30°	1574.7	26.8
0°-40°	2416.6	41.1
0°-60°	2985.0	50.8
0°-90°	2993.3	50.9
90°-120°	682.8	11.6
90°-150°	2141.7	36.4
90°-180°	2888.0	49.1
0°-180°	5879.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1999	1999	1999	1999	1999	
5°	2007	2010	2007	2010	2007	192
15°	2006	1966	2006	1966	2006	565
25°	1838	1766	1838	1766	1838	839
35°	1386	1334	1386	1334	1386	856
45°	585	549	585	549	585	453
55°	56	56	56	56	56	59
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	22	3	43	3	2
95°	31	23	31	135	31	37
105°	146	234	146	322	146	155
115°	280	388	280	478	280	276
125°	414	614	414	585	414	370
135°	562	804	562	648	562	435
145°	718	927	718	662	718	449
155°	853	1007	853	687	853	392
165°	943	1050	943	791	943	265
175°	986	1028	986	928	986	94
180°	989	989	989	989	989	



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0
2.5°	2007.8	2005.3	2002.8	1996.9	1989.8	1990.3	1998.5	2004.2	2002.4	2000.6	2002.4
5°	2007.0	2004.8	2002.6	1996.3	1988.8	1991.0	2003.0	2011.8	2010.9	2010.0	2010.9
7.5°	2005.8	2004.3	2002.8	1998.4	1993.1	1995.3	2005.2	2012.0	2009.8	2007.6	2009.8
10°	2009.0	2008.6	2008.1	2001.3	1992.4	1993.1	2003.3	2010.4	2008.2	2006.0	2008.2
12.5°	2010.6	2013.4	2016.1	2006.4	1992.5	1989.6	1997.7	2002.8	1998.8	1994.8	1998.8
15°	2006.0	2013.6	2021.1	2007.3	1986.4	1976.7	1978.0	1977.6	1971.8	1966.0	1971.8
17.5°	1983.6	1994.3	2004.9	1986.7	1958.9	1942.6	1937.7	1932.0	1923.8	1915.6	1923.8
20°	1954.0	1966.4	1978.9	1959.0	1928.3	1908.8	1900.3	1892.2	1885.1	1878.0	1885.1
22.5°	1912.4	1923.8	1935.2	1916.1	1886.8	1866.9	1856.3	1847.0	1841.3	1835.6	1841.3
25°	1838.0	1845.6	1853.1	1833.7	1805.2	1787.0	1779.0	1772.2	1769.1	1766.0	1769.1
27.5°	1732.6	1734.7	1736.9	1721.4	1700.1	1684.4	1674.5	1666.0	1662.0	1658.0	1662.0
30°	1651.0	1651.0	1651.0	1639.0	1623.0	1609.7	1599.0	1589.1	1581.6	1574.0	1581.6
32.5°	1555.8	1554.7	1553.7	1544.9	1533.5	1521.9	1510.2	1499.5	1492.0	1484.4	1492.0
35°	1386.0	1390.9	1395.8	1389.7	1379.9	1369.2	1357.7	1347.3	1340.7	1334.0	1340.7
37.5°	1202.2	1204.1	1205.9	1200.9	1193.5	1183.6	1171.1	1160.4	1154.8	1149.2	1154.8
40°	1063.0	1063.4	1063.9	1057.7	1049.2	1040.6	1031.7	1022.9	1014.4	1006.0	1014.4
42.5°	900.6	909.6	918.6	914.7	906.6	895.5	881.3	869.7	866.3	862.8	866.3
45°	585.0	624.6	664.1	678.7	684.9	680.0	664.0	640.6	594.8	549.0	594.8
47.5°	294.0	343.2	392.5	426.6	455.7	447.4	401.8	355.5	307.0	258.6	307.0
50°	166.0	195.3	224.7	270.3	321.4	313.0	245.0	189.9	173.4	157.0	173.4
52.5°	110.8	123.8	136.8	173.5	218.2	215.3	164.7	124.5	115.1	105.8	115.1
55°	56.0	59.6	63.1	79.3	99.8	99.3	78.0	61.3	58.7	56.0	58.7
57.5°	19.0	23.8	28.6	35.8	43.8	44.0	36.5	29.7	25.4	21.0	25.4
60°	3.0	7.4	11.9	17.7	23.9	23.2	15.7	9.0	5.0	1.0	5.0
62.5°	0.6	1.8	3.1	7.8	13.7	13.5	7.4	2.5	1.4	0.2	1.4
65°	0.0	0.0	0.0	0.3	0.8	0.8	0.3	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	1.4	2.4	3.2	3.8	4.0	4.0	4.2	4.4	4.4	4.4
90°	3.0	7.0	12.0	16.0	19.0	20.0	20.0	21.0	22.0	22.0	22.0
92.5°	11.0	17.4	17.6	17.6	21.4	23.2	24.8	25.0	26.0	26.0	26.0
95°	31.0	34.0	50.9	49.9	34.0	27.0	23.0	23.0	23.0	23.0	23.0
97.5°	59.1	63.5	66.3	88.9	93.9	90.7	73.9	62.1	55.5	52.5	55.5
100°	83.9	85.9	91.9	92.9	117.9	141.9	129.9	114.9	109.9	106.9	109.9
102.5°	108.7	109.9	119.1	123.3	129.1	142.7	184.2	179.6	176.2	175.6	176.2
105°	145.8	146.8	163.8	171.8	175.8	175.8	174.8	194.8	226.8	233.8	226.8
107.5°	185.6	190.2	210.2	231.6	236.2	237.4	232.2	229.2	228.0	228.8	228.0
110°	212.8	219.8	243.7	270.7	277.7	279.7	277.7	274.7	272.7	272.7	272.7



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	239.2	249.3	276.5	307.5	319.3	325.3	320.9	318.7	316.7	318.3	316.7
115°	279.7	294.7	330.7	362.6	386.6	389.6	388.6	388.6	387.6	387.6	387.6
117.5°	317.3	341.2	381.6	418.8	446.5	454.5	458.5	457.3	456.1	458.1	456.1
120°	343.6	371.6	417.6	459.5	486.5	498.5	502.5	500.5	502.5	500.5	502.5
122.5°	371.6	406.0	451.1	494.7	526.5	540.0	544.8	545.2	545.6	544.4	545.6
125°	413.6	455.5	508.5	553.4	586.4	602.4	606.4	607.4	609.4	614.4	609.4
127.5°	455.9	503.5	561.6	605.0	638.7	658.1	664.3	666.5	670.7	672.9	670.7
130°	485.5	539.4	598.4	639.3	672.3	693.3	704.3	707.3	712.3	711.3	712.3
132.5°	516.7	573.0	632.7	675.3	705.9	728.4	737.8	746.4	748.2	749.6	748.2
135°	562.4	623.4	683.3	725.3	754.2	776.2	788.2	796.2	801.2	804.2	801.2
137.5°	610.6	674.9	732.4	769.8	799.0	818.0	831.5	839.9	845.1	847.5	845.1
140°	643.3	705.3	761.2	800.2	826.1	845.1	857.1	867.1	873.1	873.1	873.1
142.5°	674.5	735.6	790.0	828.9	851.7	869.1	881.9	889.5	896.3	896.3	896.3
145°	718.3	779.2	829.1	868.1	887.1	903.1	917.1	923.0	927.0	927.0	927.0
147.5°	764.0	818.0	863.5	900.9	916.9	935.6	946.6	951.4	956.4	954.2	956.4
150°	791.2	841.1	885.1	920.1	936.0	954.0	965.0	969.0	974.0	971.0	974.0
152.5°	817.6	865.1	905.1	937.6	951.2	969.2	981.8	985.8	989.2	987.0	989.2
155°	853.1	895.1	932.0	962.0	974.0	991.0	1003.0	1008.0	1012.0	1007.0	1012.0
157.5°	884.9	921.0	953.2	980.8	993.6	1008.2	1019.3	1025.5	1029.5	1027.3	1029.5
160°	904.1	937.0	966.0	992.0	1004.0	1017.0	1028.9	1035.9	1039.9	1036.9	1039.9
162.5°	920.1	949.8	977.2	1000.8	1011.2	1022.5	1036.9	1043.1	1047.1	1043.3	1047.1
165°	943.0	967.0	991.0	1011.0	1019.9	1028.9	1043.9	1050.9	1053.9	1049.9	1053.9
167.5°	960.4	978.8	998.2	1015.4	1021.9	1030.7	1045.7	1051.5	1055.3	1050.3	1055.3
170°	970.0	986.0	1003.0	1017.0	1021.9	1029.9	1044.9	1049.9	1052.9	1047.9	1052.9
172.5°	978.0	990.0	1003.8	1016.2	1018.7	1025.1	1039.3	1044.3	1046.5	1042.3	1046.5
175°	986.0	993.0	1003.0	1011.0	1010.0	1014.0	1025.9	1029.9	1033.9	1027.9	1033.9
177.5°	989.8	993.0	996.2	1001.0	997.8	997.8	1006.6	1009.0	1009.8	1006.6	1009.8
180°	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0
2.5°	2004.2	1998.5	1990.3	1989.8	1996.9	2002.8	2005.3	2007.8	2005.3	2002.8	1996.9
5°	2011.8	2003.0	1991.0	1988.8	1996.3	2002.6	2004.8	2007.0	2004.8	2002.6	1996.3
7.5°	2012.0	2005.2	1995.3	1993.1	1998.4	2002.8	2004.3	2005.8	2004.3	2002.8	1998.4
10°	2010.4	2003.3	1993.1	1992.4	2001.3	2008.1	2008.6	2009.0	2008.6	2008.1	2001.3
12.5°	2002.8	1997.7	1989.6	1992.5	2006.4	2016.1	2013.4	2010.6	2013.4	2016.1	2006.4
15°	1977.6	1978.0	1976.7	1986.4	2007.3	2021.1	2013.6	2006.0	2013.6	2021.1	2007.3
17.5°	1932.0	1937.7	1942.6	1958.9	1986.7	2004.9	1994.3	1983.6	1994.3	2004.9	1986.7
20°	1892.2	1900.3	1908.8	1928.3	1959.0	1978.9	1966.4	1954.0	1966.4	1978.9	1959.0
22.5°	1847.0	1856.3	1866.9	1886.8	1916.1	1935.2	1923.8	1912.4	1923.8	1935.2	1916.1
25°	1772.2	1779.0	1787.0	1805.2	1833.7	1853.1	1845.6	1838.0	1845.6	1853.1	1833.7
27.5°	1666.0	1674.5	1684.4	1700.1	1721.4	1736.9	1734.7	1732.6	1734.7	1736.9	1721.4
30°	1589.1	1599.0	1609.7	1623.0	1639.0	1651.0	1651.0	1651.0	1651.0	1651.0	1639.0
32.5°	1499.5	1510.2	1521.9	1533.5	1544.9	1553.7	1554.7	1555.8	1554.7	1553.7	1544.9
35°	1347.3	1357.7	1369.2	1379.9	1389.7	1395.8	1390.9	1386.0	1390.9	1395.8	1389.7
37.5°	1160.4	1171.1	1183.6	1193.5	1200.9	1205.9	1204.1	1202.2	1204.1	1205.9	1200.9
40°	1022.9	1031.7	1040.6	1049.2	1057.7	1063.9	1063.4	1063.0	1063.4	1063.9	1057.7
42.5°	869.7	881.3	895.5	906.6	914.7	918.6	909.6	900.6	909.6	918.6	914.7
45°	640.6	664.0	680.0	684.9	678.7	664.1	624.6	585.0	624.6	664.1	678.7
47.5°	355.5	401.8	447.4	455.7	426.6	392.5	343.2	294.0	343.2	392.5	426.6
50°	189.9	245.0	313.0	321.4	270.3	224.7	195.3	166.0	195.3	224.7	270.3
52.5°	124.5	164.7	215.3	218.2	173.5	136.8	123.8	110.8	123.8	136.8	173.5
55°	61.3	78.0	99.3	99.8	79.3	63.1	59.6	56.0	59.6	63.1	79.3
57.5°	29.7	36.5	44.0	43.8	35.8	28.6	23.8	19.0	23.8	28.6	35.8
60°	9.0	15.7	23.2	23.9	17.7	11.9	7.4	3.0	7.4	11.9	17.7
62.5°	2.5	7.4	13.5	13.7	7.8	3.1	1.8	0.6	1.8	3.1	7.8
65°	0.0	0.3	0.8	0.8	0.3	0.0	0.0	0.0	0.0	0.0	0.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.2	4.0	4.0	3.8	3.2	2.4	1.4	0.6	1.4	2.2	3.6
90°	21.0	20.0	20.0	19.0	16.0	12.0	7.0	3.0	7.0	11.0	18.0
92.5°	25.0	24.8	23.2	21.4	17.6	17.6	17.4	11.0	19.0	27.0	38.8
95°	23.0	23.0	27.0	34.0	49.9	50.9	34.0	31.0	44.0	61.9	77.9
97.5°	62.1	73.9	90.7	93.9	88.9	66.3	63.5	59.1	80.5	98.3	124.1
100°	114.9	129.9	141.9	117.9	92.9	91.9	85.9	83.9	106.9	123.9	148.8
102.5°	179.6	184.2	142.7	129.1	123.3	119.1	109.9	108.7	131.7	155.0	176.0
105°	194.8	174.8	175.8	175.8	171.8	163.8	146.8	145.8	171.8	198.8	224.8
107.5°	229.2	232.2	237.4	236.2	231.6	210.2	190.2	185.6	209.0	241.4	269.9
110°	274.7	277.7	279.7	277.7	270.7	243.7	219.8	212.8	233.8	267.7	298.7



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	318.7	320.9	325.3	319.3	307.5	276.5	249.3	239.2	260.1	294.9	326.7
115°	388.6	388.6	389.6	386.6	362.6	330.7	294.7	279.7	297.7	329.7	364.6
117.5°	457.3	458.5	454.5	446.5	418.8	381.6	341.2	317.3	331.5	365.2	401.2
120°	500.5	502.5	498.5	486.5	459.5	417.6	371.6	343.6	354.6	387.6	423.6
122.5°	545.2	544.8	540.0	526.5	494.7	451.1	406.0	371.6	376.2	406.8	441.9
125°	607.4	606.4	602.4	586.4	553.4	508.5	455.5	413.6	407.6	433.6	469.5
127.5°	666.5	664.3	658.1	638.7	605.0	561.6	503.5	455.9	442.5	458.9	491.9
130°	707.3	704.3	693.3	672.3	639.3	598.4	539.4	485.5	466.5	476.5	505.5
132.5°	746.4	737.8	728.4	705.9	675.3	632.7	573.0	516.7	490.5	494.9	517.5
135°	796.2	788.2	776.2	754.2	725.3	683.3	623.4	562.4	526.5	522.5	535.4
137.5°	839.9	831.5	818.0	799.0	769.8	732.4	674.9	610.6	565.2	551.8	556.8
140°	867.1	857.1	845.1	826.1	800.2	761.2	705.3	643.3	592.4	573.4	570.4
142.5°	889.5	881.9	869.1	851.7	828.9	790.0	735.6	674.5	620.4	595.8	588.8
145°	923.0	917.1	903.1	887.1	868.1	829.1	779.2	718.3	664.3	632.3	617.4
147.5°	951.4	946.6	935.6	916.9	900.9	863.5	818.0	764.0	708.7	669.1	649.7
150°	969.0	965.0	954.0	936.0	920.1	885.1	841.1	791.2	738.2	696.3	671.3
152.5°	985.8	981.8	969.2	951.2	937.6	905.1	865.1	817.6	763.8	721.9	696.1
155°	1008.0	1003.0	991.0	974.0	962.0	932.0	895.1	853.1	807.2	763.2	734.2
157.5°	1025.5	1019.3	1008.2	993.6	980.8	953.2	921.0	884.9	844.7	802.8	773.2
160°	1035.9	1028.9	1017.0	1004.0	992.0	966.0	937.0	904.1	867.1	829.1	797.2
162.5°	1043.1	1036.9	1022.5	1011.2	1000.8	977.2	949.8	920.1	887.1	853.9	824.3
165°	1050.9	1043.9	1028.9	1019.9	1011.0	991.0	967.0	943.0	915.1	888.1	864.1
167.5°	1051.5	1045.7	1030.7	1021.9	1015.4	998.2	978.8	960.4	938.6	917.5	897.5
170°	1049.9	1044.9	1029.9	1021.9	1017.0	1003.0	986.0	970.0	953.0	935.0	919.1
172.5°	1044.3	1039.3	1025.1	1018.7	1016.2	1003.8	990.0	978.0	963.4	950.2	937.4
175°	1029.9	1025.9	1014.0	1010.0	1011.0	1003.0	993.0	986.0	977.0	969.0	962.0
177.5°	1009.0	1006.6	997.8	997.8	1001.0	996.2	993.0	989.8	985.8	983.4	981.0
180°	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0
2.5°	1989.8	1990.3	1998.5	2004.2	2002.4	2000.6	2002.4	2004.2	1998.5	1990.3	1989.8
5°	1988.8	1991.0	2003.0	2011.8	2010.9	2010.0	2010.9	2011.8	2003.0	1991.0	1988.8
7.5°	1993.1	1995.3	2005.2	2012.0	2009.8	2007.6	2009.8	2012.0	2005.2	1995.3	1993.1
10°	1992.4	1993.1	2003.3	2010.4	2008.2	2006.0	2008.2	2010.4	2003.3	1993.1	1992.4
12.5°	1992.5	1989.6	1997.7	2002.8	1998.8	1994.8	1998.8	2002.8	1997.7	1989.6	1992.5
15°	1986.4	1976.7	1978.0	1977.6	1971.8	1966.0	1971.8	1977.6	1978.0	1976.7	1986.4
17.5°	1958.9	1942.6	1937.7	1932.0	1923.8	1915.6	1923.8	1932.0	1937.7	1942.6	1958.9
20°	1928.3	1908.8	1900.3	1892.2	1885.1	1878.0	1885.1	1892.2	1900.3	1908.8	1928.3
22.5°	1886.8	1866.9	1856.3	1847.0	1841.3	1835.6	1841.3	1847.0	1856.3	1866.9	1886.8
25°	1805.2	1787.0	1779.0	1772.2	1769.1	1766.0	1769.1	1772.2	1779.0	1787.0	1805.2
27.5°	1700.1	1684.4	1674.5	1666.0	1662.0	1658.0	1662.0	1666.0	1674.5	1684.4	1700.1
30°	1623.0	1609.7	1599.0	1589.1	1581.6	1574.0	1581.6	1589.1	1599.0	1609.7	1623.0
32.5°	1533.5	1521.9	1510.2	1499.5	1492.0	1484.4	1492.0	1499.5	1510.2	1521.9	1533.5
35°	1379.9	1369.2	1357.7	1347.3	1340.7	1334.0	1340.7	1347.3	1357.7	1369.2	1379.9
37.5°	1193.5	1183.6	1171.1	1160.4	1154.8	1149.2	1154.8	1160.4	1171.1	1183.6	1193.5
40°	1049.2	1040.6	1031.7	1022.9	1014.4	1006.0	1014.4	1022.9	1031.7	1040.6	1049.2
42.5°	906.6	895.5	881.3	869.7	866.3	862.8	866.3	869.7	881.3	895.5	906.6
45°	684.9	680.0	664.0	640.6	594.8	549.0	594.8	640.6	664.0	680.0	684.9
47.5°	455.7	447.4	401.8	355.5	307.0	258.6	307.0	355.5	401.8	447.4	455.7
50°	321.4	313.0	245.0	189.9	173.4	157.0	173.4	189.9	245.0	313.0	321.4
52.5°	218.2	215.3	164.7	124.5	115.1	105.8	115.1	124.5	164.7	215.3	218.2
55°	99.8	99.3	78.0	61.3	58.7	56.0	58.7	61.3	78.0	99.3	99.8
57.5°	43.8	44.0	36.5	29.7	25.4	21.0	25.4	29.7	36.5	44.0	43.8
60°	23.9	23.2	15.7	9.0	5.0	1.0	5.0	9.0	15.7	23.2	23.9
62.5°	13.7	13.5	7.4	2.5	1.4	0.2	1.4	2.5	7.4	13.5	13.7
65°	0.8	0.8	0.3	0.0	0.0	0.0	0.0	0.0	0.3	0.8	0.8
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.6	6.0	7.4	8.2	9.0	8.6	9.0	8.2	7.4	6.0	4.6
90°	23.0	30.0	37.0	41.0	45.0	43.0	45.0	41.0	37.0	30.0	23.0
92.5°	46.2	57.9	66.5	73.7	76.9	76.5	76.9	73.7	66.5	57.9	46.2
95°	92.9	106.9	120.9	130.9	136.9	134.9	136.9	130.9	120.9	106.9	92.9
97.5°	143.3	162.0	177.6	187.0	193.0	197.0	193.0	187.0	177.6	162.0	143.3
100°	176.8	194.8	212.8	223.8	233.8	237.8	233.8	223.8	212.8	194.8	176.8
102.5°	204.0	227.6	247.1	258.9	267.3	271.3	267.3	258.9	247.1	227.6	204.0
105°	248.7	273.7	294.7	309.7	318.7	321.7	318.7	309.7	294.7	273.7	248.7
107.5°	293.5	319.3	338.7	355.2	366.2	372.6	366.2	355.2	338.7	319.3	293.5
110°	328.7	349.6	370.6	385.6	396.6	400.6	396.6	385.6	370.6	349.6	328.7



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	358.2	381.6	402.6	417.6	430.2	435.8	430.2	417.6	402.6	381.6	358.2
115°	399.6	430.6	449.5	463.5	472.5	477.5	472.5	463.5	449.5	430.6	399.6
117.5°	434.0	466.3	487.1	497.9	502.1	505.7	502.1	497.9	487.1	466.3	434.0
120°	455.5	485.5	509.5	523.5	528.5	530.5	528.5	523.5	509.5	485.5	455.5
122.5°	475.5	503.9	527.1	544.2	552.4	554.4	552.4	544.2	527.1	503.9	475.5
125°	503.5	530.5	554.4	571.4	580.4	585.4	580.4	571.4	554.4	530.5	503.5
127.5°	527.9	557.0	579.0	594.4	603.2	607.2	603.2	594.4	579.0	557.0	527.9
130°	541.4	571.4	593.4	610.4	618.4	622.4	618.4	610.4	593.4	571.4	541.4
132.5°	551.8	583.4	606.2	621.6	630.3	634.3	630.3	621.6	606.2	583.4	551.8
135°	564.4	597.4	621.4	636.3	644.3	648.3	644.3	636.3	621.4	597.4	564.4
137.5°	575.4	605.4	630.3	646.1	653.3	655.9	653.3	646.1	630.3	605.4	575.4
140°	583.4	609.4	634.3	649.3	657.3	658.3	657.3	649.3	634.3	609.4	583.4
142.5°	593.8	614.2	635.9	650.9	658.9	660.7	658.9	650.9	635.9	614.2	593.8
145°	612.4	624.4	639.3	653.3	660.3	662.3	660.3	653.3	639.3	624.4	612.4
147.5°	635.7	639.5	647.3	656.5	663.3	664.7	663.3	656.5	647.3	639.5	635.7
150°	653.3	652.3	655.3	661.3	667.3	666.3	667.3	661.3	655.3	652.3	653.3
152.5°	673.3	667.5	667.3	670.1	672.9	672.7	672.9	670.1	667.3	667.5	673.3
155°	707.3	696.3	690.3	688.3	688.3	687.3	688.3	688.3	690.3	696.3	707.3
157.5°	744.6	729.2	720.3	715.5	714.1	711.9	714.1	715.5	720.3	729.2	744.6
160°	770.2	753.2	744.2	736.2	733.2	730.2	733.2	736.2	744.2	753.2	770.2
162.5°	794.2	778.0	768.2	761.0	758.0	753.4	758.0	761.0	768.2	778.0	794.2
165°	833.1	816.2	805.2	799.2	795.2	791.2	795.2	799.2	805.2	816.2	833.1
167.5°	872.1	853.5	846.3	839.5	835.7	828.5	835.7	839.5	846.3	853.5	872.1
170°	896.1	879.1	875.1	869.1	862.1	854.1	862.1	869.1	875.1	879.1	896.1
172.5°	916.9	905.5	901.5	895.5	893.3	886.9	893.3	895.5	901.5	905.5	916.9
175°	947.0	938.0	938.0	937.0	934.0	928.0	934.0	937.0	938.0	938.0	947.0
177.5°	972.2	967.4	970.6	970.6	969.8	964.2	969.8	970.6	970.6	967.4	972.2
180°	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1999.0	1999.0	1999.0	1999.0
2.5°	1996.9	2002.8	2005.3	2007.8
5°	1996.3	2002.6	2004.8	2007.0
7.5°	1998.4	2002.8	2004.3	2005.8
10°	2001.3	2008.1	2008.6	2009.0
12.5°	2006.4	2016.1	2013.4	2010.6
15°	2007.3	2021.1	2013.6	2006.0
17.5°	1986.7	2004.9	1994.3	1983.6
20°	1959.0	1978.9	1966.4	1954.0
22.5°	1916.1	1935.2	1923.8	1912.4
25°	1833.7	1853.1	1845.6	1838.0
27.5°	1721.4	1736.9	1734.7	1732.6
30°	1639.0	1651.0	1651.0	1651.0
32.5°	1544.9	1553.7	1554.7	1555.8
35°	1389.7	1395.8	1390.9	1386.0
37.5°	1200.9	1205.9	1204.1	1202.2
40°	1057.7	1063.9	1063.4	1063.0
42.5°	914.7	918.6	909.6	900.6
45°	678.7	664.1	624.6	585.0
47.5°	426.6	392.5	343.2	294.0
50°	270.3	224.7	195.3	166.0
52.5°	173.5	136.8	123.8	110.8
55°	79.3	63.1	59.6	56.0
57.5°	35.8	28.6	23.8	19.0
60°	17.7	11.9	7.4	3.0
62.5°	7.8	3.1	1.8	0.6
65°	0.3	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	3.6	2.2	1.4	0.6
90°	18.0	11.0	7.0	3.0
92.5°	38.8	27.0	19.0	11.0
95°	77.9	61.9	44.0	31.0
97.5°	124.1	98.3	80.5	59.1
100°	148.8	123.9	106.9	83.9
102.5°	176.0	155.0	131.7	108.7
105°	224.8	198.8	171.8	145.8
107.5°	269.9	241.4	209.0	185.6
110°	298.7	267.7	233.8	212.8



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	326.7	294.9	260.1	239.2
115°	364.6	329.7	297.7	279.7
117.5°	401.2	365.2	331.5	317.3
120°	423.6	387.6	354.6	343.6
122.5°	441.9	406.8	376.2	371.6
125°	469.5	433.6	407.6	413.6
127.5°	491.9	458.9	442.5	455.9
130°	505.5	476.5	466.5	485.5
132.5°	517.5	494.9	490.5	516.7
135°	535.4	522.5	526.5	562.4
137.5°	556.8	551.8	565.2	610.6
140°	570.4	573.4	592.4	643.3
142.5°	588.8	595.8	620.4	674.5
145°	617.4	632.3	664.3	718.3
147.5°	649.7	669.1	708.7	764.0
150°	671.3	696.3	738.2	791.2
152.5°	696.1	721.9	763.8	817.6
155°	734.2	763.2	807.2	853.1
157.5°	773.2	802.8	844.7	884.9
160°	797.2	829.1	867.1	904.1
162.5°	824.3	853.9	887.1	920.1
165°	864.1	888.1	915.1	943.0
167.5°	897.5	917.5	938.6	960.4
170°	919.1	935.0	953.0	970.0
172.5°	937.4	950.2	963.4	978.0
175°	962.0	969.0	977.0	986.0
177.5°	981.0	983.4	985.8	989.8
180°	989.0	989.0	989.0	989.0



TEST NUMBER: P1427523

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.72	0.00	0.00	0.00	0.00	0.95
	3H	0.00	0.00	0.00	0.00	0.48	0.00	0.00	0.00	0.70	
	4H	0.00	0.00	0.00	0.00	0.35	0.00	0.00	0.00	0.57	
	6H	0.00	0.00	0.00	0.00	0.20	0.00	0.00	0.00	0.43	
	8H	0.00	0.00	0.00	0.00	0.13	0.00	0.00	0.00	0.35	
	12H	0.00	0.00	0.00	0.00	0.05	0.00	0.00	0.00	0.28	
4H	2H	0.00	0.00	0.00	0.00	0.36	0.00	0.00	0.00	0.58	
	3H	0.00	0.00	0.00	0.00	0.09	0.00	0.00	0.00	0.32	
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.18	
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.02	
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	