

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427559

Luminaire Tested: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427559  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8810.7 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 82.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	96	92	88	86	86	83	80	78	67	65	64	52	51	50	39	38	37	31
2	88	82	77	72	80	74	70	66	60	57	55	48	46	44	36	35	34	28
3	81	73	67	62	74	67	61	57	55	51	48	43	41	39	33	32	30	26
4	75	66	59	54	68	60	54	50	49	45	42	40	37	35	30	29	28	24
5	69	59	52	47	63	54	48	44	45	41	37	36	33	31	28	26	25	22
6	64	54	46	41	58	49	43	39	41	37	33	33	30	28	26	24	23	20
7	60	49	42	37	54	45	39	34	38	33	30	31	28	25	24	22	21	18
8	56	45	38	33	51	41	35	31	35	30	27	28	25	23	23	20	19	17
9	52	41	34	29	47	38	32	28	32	27	24	26	23	21	21	19	17	15
10	49	38	31	27	44	35	29	25	29	25	22	24	21	19	20	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	32275	32275	32275	32275
5°	32528	32577	32528	32577
10°	32937	32888	32937	32888
15°	33530	32862	33530	32862
20°	33573	32267	33573	32267
25°	32743	31461	32743	31461
30°	30780	29345	30780	29345
35°	27318	26293	27318	26293
40°	22404	21203	22404	21203
45°	13357	12535	13357	12535
50°	4170	3944	4170	3944
55°	1576	1576	1576	1576
60°	97	32	97	32
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 15638 cd/sqm



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.1	2.2
10°-20°	559.9	6.4
20°-30°	823.7	9.3
30°-40°	841.9	9.6
40°-50°	485.0	5.5
50°-60°	83.5	0.9
60°-70°	3.0	0.0
70°-80°	0.0	0.0
80°-90°	10.6	0.1
90°-100°	158.5	1.8
100°-110°	462.2	5.2
110°-120°	754.2	8.6
120°-130°	957.1	10.9
130°-140°	1024.1	11.6
140°-150°	956.3	10.9
150°-160°	786.9	8.9
160°-170°	527.7	6.0
170°-180°	187.4	2.1
0°-30°	1574.7	17.9
0°-40°	2416.6	27.4
0°-60°	2985.0	33.9
0°-90°	2998.6	34.0
90°-120°	1374.9	15.6
90°-150°	4312.4	48.9
90°-180°	5814.0	66.0
0°-180°	8810.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1999	1999	1999	1999	1999	
5°	2007	2010	2007	2010	2007	192
15°	2006	1966	2006	1966	2006	565
25°	1838	1766	1838	1766	1838	839
35°	1386	1334	1386	1334	1386	856
45°	585	549	585	549	585	453
55°	56	56	56	56	56	59
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	6	44	6	86	6	5
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0
2.5°	2007.8	2005.3	2002.8	1996.9	1989.8	1990.3	1998.5	2004.2	2002.4	2000.6	2002.4
5°	2007.0	2004.8	2002.6	1996.3	1988.8	1991.0	2003.0	2011.8	2010.9	2010.0	2010.9
7.5°	2005.8	2004.3	2002.8	1998.4	1993.1	1995.3	2005.2	2012.0	2009.8	2007.6	2009.8
10°	2009.0	2008.6	2008.1	2001.3	1992.4	1993.1	2003.3	2010.4	2008.2	2006.0	2008.2
12.5°	2010.6	2013.4	2016.1	2006.4	1992.5	1989.6	1997.7	2002.8	1998.8	1994.8	1998.8
15°	2006.0	2013.6	2021.1	2007.3	1986.4	1976.7	1978.0	1977.6	1971.8	1966.0	1971.8
17.5°	1983.6	1994.3	2004.9	1986.7	1958.9	1942.6	1937.7	1932.0	1923.8	1915.6	1923.8
20°	1954.0	1966.4	1978.9	1959.0	1928.3	1908.8	1900.3	1892.2	1885.1	1878.0	1885.1
22.5°	1912.4	1923.8	1935.2	1916.1	1886.8	1866.9	1856.3	1847.0	1841.3	1835.6	1841.3
25°	1838.0	1845.6	1853.1	1833.7	1805.2	1787.0	1779.0	1772.2	1769.1	1766.0	1769.1
27.5°	1732.6	1734.7	1736.9	1721.4	1700.1	1684.4	1674.5	1666.0	1662.0	1658.0	1662.0
30°	1651.0	1651.0	1651.0	1639.0	1623.0	1609.7	1599.0	1589.1	1581.6	1574.0	1581.6
32.5°	1555.8	1554.7	1553.7	1544.9	1533.5	1521.9	1510.2	1499.5	1492.0	1484.4	1492.0
35°	1386.0	1390.9	1395.8	1389.7	1379.9	1369.2	1357.7	1347.3	1340.7	1334.0	1340.7
37.5°	1202.2	1204.1	1205.9	1200.9	1193.5	1183.6	1171.1	1160.4	1154.8	1149.2	1154.8
40°	1063.0	1063.4	1063.9	1057.7	1049.2	1040.6	1031.7	1022.9	1014.4	1006.0	1014.4
42.5°	900.6	909.6	918.6	914.7	906.6	895.5	881.3	869.7	866.3	862.8	866.3
45°	585.0	624.6	664.1	678.7	684.9	680.0	664.0	640.6	594.8	549.0	594.8
47.5°	294.0	343.2	392.5	426.6	455.7	447.4	401.8	355.5	307.0	258.6	307.0
50°	166.0	195.3	224.7	270.3	321.4	313.0	245.0	189.9	173.4	157.0	173.4
52.5°	110.8	123.8	136.8	173.5	218.2	215.3	164.7	124.5	115.1	105.8	115.1
55°	56.0	59.6	63.1	79.3	99.8	99.3	78.0	61.3	58.7	56.0	58.7
57.5°	19.0	23.8	28.6	35.8	43.8	44.0	36.5	29.7	25.4	21.0	25.4
60°	3.0	7.4	11.9	17.7	23.9	23.2	15.7	9.0	5.0	1.0	5.0
62.5°	0.6	1.8	3.1	7.8	13.7	13.5	7.4	2.5	1.4	0.2	1.4
65°	0.0	0.0	0.0	0.3	0.8	0.8	0.3	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.2	2.8	4.8	6.4	7.6	8.0	8.0	8.4	8.9	8.9	8.9
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0
2.5°	2004.2	1998.5	1990.3	1989.8	1996.9	2002.8	2005.3	2007.8	2005.3	2002.8	1996.9
5°	2011.8	2003.0	1991.0	1988.8	1996.3	2002.6	2004.8	2007.0	2004.8	2002.6	1996.3
7.5°	2012.0	2005.2	1995.3	1993.1	1998.4	2002.8	2004.3	2005.8	2004.3	2002.8	1998.4
10°	2010.4	2003.3	1993.1	1992.4	2001.3	2008.1	2008.6	2009.0	2008.6	2008.1	2001.3
12.5°	2002.8	1997.7	1989.6	1992.5	2006.4	2016.1	2013.4	2010.6	2013.4	2016.1	2006.4
15°	1977.6	1978.0	1976.7	1986.4	2007.3	2021.1	2013.6	2006.0	2013.6	2021.1	2007.3
17.5°	1932.0	1937.7	1942.6	1958.9	1986.7	2004.9	1994.3	1983.6	1994.3	2004.9	1986.7
20°	1892.2	1900.3	1908.8	1928.3	1959.0	1978.9	1966.4	1954.0	1966.4	1978.9	1959.0
22.5°	1847.0	1856.3	1866.9	1886.8	1916.1	1935.2	1923.8	1912.4	1923.8	1935.2	1916.1
25°	1772.2	1779.0	1787.0	1805.2	1833.7	1853.1	1845.6	1838.0	1845.6	1853.1	1833.7
27.5°	1666.0	1674.5	1684.4	1700.1	1721.4	1736.9	1734.7	1732.6	1734.7	1736.9	1721.4
30°	1589.1	1599.0	1609.7	1623.0	1639.0	1651.0	1651.0	1651.0	1651.0	1651.0	1639.0
32.5°	1499.5	1510.2	1521.9	1533.5	1544.9	1553.7	1554.7	1555.8	1554.7	1553.7	1544.9
35°	1347.3	1357.7	1369.2	1379.9	1389.7	1395.8	1390.9	1386.0	1390.9	1395.8	1389.7
37.5°	1160.4	1171.1	1183.6	1193.5	1200.9	1205.9	1204.1	1202.2	1204.1	1205.9	1200.9
40°	1022.9	1031.7	1040.6	1049.2	1057.7	1063.9	1063.4	1063.0	1063.4	1063.9	1057.7
42.5°	869.7	881.3	895.5	906.6	914.7	918.6	909.6	900.6	909.6	918.6	914.7
45°	640.6	664.0	680.0	684.9	678.7	664.1	624.6	585.0	624.6	664.1	678.7
47.5°	355.5	401.8	447.4	455.7	426.6	392.5	343.2	294.0	343.2	392.5	426.6
50°	189.9	245.0	313.0	321.4	270.3	224.7	195.3	166.0	195.3	224.7	270.3
52.5°	124.5	164.7	215.3	218.2	173.5	136.8	123.8	110.8	123.8	136.8	173.5
55°	61.3	78.0	99.3	99.8	79.3	63.1	59.6	56.0	59.6	63.1	79.3
57.5°	29.7	36.5	44.0	43.8	35.8	28.6	23.8	19.0	23.8	28.6	35.8
60°	9.0	15.7	23.2	23.9	17.7	11.9	7.4	3.0	7.4	11.9	17.7
62.5°	2.5	7.4	13.5	13.7	7.8	3.1	1.8	0.6	1.8	3.1	7.8
65°	0.0	0.3	0.8	0.8	0.3	0.0	0.0	0.0	0.0	0.0	0.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	8.4	8.0	8.0	7.6	6.4	4.8	2.8	1.2	2.8	4.4	7.2
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0	1999.0
2.5°	1989.8	1990.3	1998.5	2004.2	2002.4	2000.6	2002.4	2004.2	1998.5	1990.3	1989.8
5°	1988.8	1991.0	2003.0	2011.8	2010.9	2010.0	2010.9	2011.8	2003.0	1991.0	1988.8
7.5°	1993.1	1995.3	2005.2	2012.0	2009.8	2007.6	2009.8	2012.0	2005.2	1995.3	1993.1
10°	1992.4	1993.1	2003.3	2010.4	2008.2	2006.0	2008.2	2010.4	2003.3	1993.1	1992.4
12.5°	1992.5	1989.6	1997.7	2002.8	1998.8	1994.8	1998.8	2002.8	1997.7	1989.6	1992.5
15°	1986.4	1976.7	1978.0	1977.6	1971.8	1966.0	1971.8	1977.6	1978.0	1976.7	1986.4
17.5°	1958.9	1942.6	1937.7	1932.0	1923.8	1915.6	1923.8	1932.0	1937.7	1942.6	1958.9
20°	1928.3	1908.8	1900.3	1892.2	1885.1	1878.0	1885.1	1892.2	1900.3	1908.8	1928.3
22.5°	1886.8	1866.9	1856.3	1847.0	1841.3	1835.6	1841.3	1847.0	1856.3	1866.9	1886.8
25°	1805.2	1787.0	1779.0	1772.2	1769.1	1766.0	1769.1	1772.2	1779.0	1787.0	1805.2
27.5°	1700.1	1684.4	1674.5	1666.0	1662.0	1658.0	1662.0	1666.0	1674.5	1684.4	1700.1
30°	1623.0	1609.7	1599.0	1589.1	1581.6	1574.0	1581.6	1589.1	1599.0	1609.7	1623.0
32.5°	1533.5	1521.9	1510.2	1499.5	1492.0	1484.4	1492.0	1499.5	1510.2	1521.9	1533.5
35°	1379.9	1369.2	1357.7	1347.3	1340.7	1334.0	1340.7	1347.3	1357.7	1369.2	1379.9
37.5°	1193.5	1183.6	1171.1	1160.4	1154.8	1149.2	1154.8	1160.4	1171.1	1183.6	1193.5
40°	1049.2	1040.6	1031.7	1022.9	1014.4	1006.0	1014.4	1022.9	1031.7	1040.6	1049.2
42.5°	906.6	895.5	881.3	869.7	866.3	862.8	866.3	869.7	881.3	895.5	906.6
45°	684.9	680.0	664.0	640.6	594.8	549.0	594.8	640.6	664.0	680.0	684.9
47.5°	455.7	447.4	401.8	355.5	307.0	258.6	307.0	355.5	401.8	447.4	455.7
50°	321.4	313.0	245.0	189.9	173.4	157.0	173.4	189.9	245.0	313.0	321.4
52.5°	218.2	215.3	164.7	124.5	115.1	105.8	115.1	124.5	164.7	215.3	218.2
55°	99.8	99.3	78.0	61.3	58.7	56.0	58.7	61.3	78.0	99.3	99.8
57.5°	43.8	44.0	36.5	29.7	25.4	21.0	25.4	29.7	36.5	44.0	43.8
60°	23.9	23.2	15.7	9.0	5.0	1.0	5.0	9.0	15.7	23.2	23.9
62.5°	13.7	13.5	7.4	2.5	1.4	0.2	1.4	2.5	7.4	13.5	13.7
65°	0.8	0.8	0.3	0.0	0.0	0.0	0.0	0.0	0.3	0.8	0.8
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	9.3	12.1	14.9	16.5	18.1	17.3	18.1	16.5	14.9	12.1	9.3
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1999.0	1999.0	1999.0	1999.0
2.5°	1996.9	2002.8	2005.3	2007.8
5°	1996.3	2002.6	2004.8	2007.0
7.5°	1998.4	2002.8	2004.3	2005.8
10°	2001.3	2008.1	2008.6	2009.0
12.5°	2006.4	2016.1	2013.4	2010.6
15°	2007.3	2021.1	2013.6	2006.0
17.5°	1986.7	2004.9	1994.3	1983.6
20°	1959.0	1978.9	1966.4	1954.0
22.5°	1916.1	1935.2	1923.8	1912.4
25°	1833.7	1853.1	1845.6	1838.0
27.5°	1721.4	1736.9	1734.7	1732.6
30°	1639.0	1651.0	1651.0	1651.0
32.5°	1544.9	1553.7	1554.7	1555.8
35°	1389.7	1395.8	1390.9	1386.0
37.5°	1200.9	1205.9	1204.1	1202.2
40°	1057.7	1063.9	1063.4	1063.0
42.5°	914.7	918.6	909.6	900.6
45°	678.7	664.1	624.6	585.0
47.5°	426.6	392.5	343.2	294.0
50°	270.3	224.7	195.3	166.0
52.5°	173.5	136.8	123.8	110.8
55°	79.3	63.1	59.6	56.0
57.5°	35.8	28.6	23.8	19.0
60°	17.7	11.9	7.4	3.0
62.5°	7.8	3.1	1.8	0.6
65°	0.3	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	7.2	4.4	2.8	1.2
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1427559

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427559  
 CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00