

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427571

Luminaire Tested: SQ2W-BBN-0U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427571
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBN-0U-075D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3001.8 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-0U-075D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-OU-075D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61
9	78	69	63	60	77	69	63	60	68	63	59	67	62	59	66	62	59	58
10	75	66	60	57	74	65	60	57	65	60	56	64	59	56	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	89661	89661	89661	89661
5°	86662	86710	86662	86710
10°	74374	74374	74374	74374
15°	57727	57594	57727	57594
20°	41664	40769	41664	40769
25°	29542	28418	29542	28418
30°	21979	21214	21979	21214
35°	17102	16312	17102	16312
40°	12656	11558	12656	11558
45°	6466	5211	6466	5211
50°	1407	1030	1407	1030
55°	394	310	394	310
60°	65	32	65	32
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 7889 cd/sqm

TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-OU-075D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	480.2	16.0
10°-20°	946.8	31.5
20°-30°	763.7	25.4
30°-40°	530.5	17.7
40°-50°	245.1	8.2
50°-60°	34.3	1.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2190.7	73.0
0°-40°	2721.2	90.7
0°-60°	3000.6	100.0
0°-90°	3001.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3001.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5553	5553	5553	5553	5553	
5°	5347	5350	5347	5350	5347	481
15°	3454	3446	3454	3446	3454	951
25°	1658	1595	1658	1595	1658	776
35°	868	828	868	828	868	543
45°	283	228	283	228	283	229
55°	14	11	14	11	14	18
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-OU-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3
2.5°	5550.1	5540.8	5531.6	5513.2	5491.9	5491.0	5510.6	5523.7	5517.7	5511.6	5517.7
5°	5347.1	5334.2	5321.3	5305.7	5289.3	5295.5	5324.4	5346.5	5348.3	5350.1	5348.3
7.5°	4899.2	4903.3	4907.5	4896.8	4881.2	4889.3	4921.4	4944.5	4941.1	4937.6	4941.1
10°	4536.5	4539.6	4542.7	4542.1	4540.4	4544.8	4555.5	4560.5	4548.5	4536.5	4548.5
12.5°	4116.2	4128.5	4140.9	4126.6	4103.5	4099.9	4116.0	4129.2	4134.3	4139.4	4134.3
15°	3453.6	3473.7	3493.7	3465.3	3420.8	3409.3	3430.6	3446.5	3446.1	3445.6	3446.1
17.5°	2832.4	2830.3	2828.3	2810.8	2788.1	2778.7	2782.7	2785.4	2784.1	2782.7	2784.1
20°	2424.9	2421.7	2418.6	2403.5	2384.4	2373.3	2370.2	2368.4	2370.6	2372.8	2370.6
22.5°	2075.8	2070.5	2065.3	2059.0	2052.3	2045.1	2037.4	2032.3	2035.2	2038.2	2035.2
25°	1658.3	1641.4	1624.5	1610.9	1598.4	1597.6	1608.2	1613.9	1604.6	1595.2	1604.6
27.5°	1331.0	1330.8	1330.5	1322.5	1311.9	1307.2	1308.3	1309.6	1311.4	1313.2	1311.4
30°	1178.9	1175.8	1172.7	1164.2	1154.0	1149.1	1149.5	1148.5	1143.2	1137.9	1143.2
32.5°	1043.6	1045.8	1048.0	1039.1	1026.3	1018.8	1016.4	1013.2	1007.9	1002.6	1007.9
35°	867.7	867.7	867.7	860.3	850.5	842.3	835.6	830.3	829.0	827.6	829.0
37.5°	704.5	703.7	702.9	697.5	690.6	682.4	673.0	665.0	661.6	658.1	661.6
40°	600.5	598.2	596.0	592.1	587.7	579.7	568.1	558.2	553.3	548.4	553.3
42.5°	482.0	487.9	493.9	492.0	487.6	479.6	468.0	457.5	450.1	442.7	450.1
45°	283.2	308.1	333.0	341.9	345.5	340.6	327.3	307.3	267.8	228.2	267.8
47.5°	121.7	149.1	176.5	199.5	221.0	214.2	179.1	144.5	111.6	78.7	111.6
50°	56.0	77.4	98.7	127.4	158.6	152.1	108.1	71.3	56.2	41.0	56.2
52.5°	32.8	43.5	54.2	81.0	113.2	110.3	72.3	41.8	33.8	25.8	33.8
55°	14.0	17.6	21.1	35.7	53.9	53.0	33.0	17.2	14.1	11.0	14.1
57.5°	5.2	7.2	9.1	14.3	20.7	20.3	13.1	7.4	5.8	4.2	5.8
60°	2.0	2.9	3.8	6.3	9.5	9.2	5.7	2.8	1.9	1.0	1.9
62.5°	0.4	0.9	1.5	2.9	4.6	4.5	2.7	1.3	0.7	0.2	0.7
65°	0.0	0.0	0.0	0.3	0.8	0.8	0.3	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-OU-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3
2.5°	5523.7	5510.6	5491.0	5491.9	5513.2	5531.6	5540.8	5550.1	5540.8	5531.6	5513.2
5°	5346.5	5324.4	5295.5	5289.3	5305.7	5321.3	5334.2	5347.1	5334.2	5321.3	5305.7
7.5°	4944.5	4921.4	4889.3	4881.2	4896.8	4907.5	4903.3	4899.2	4903.3	4907.5	4896.8
10°	4560.5	4555.5	4544.8	4540.4	4542.1	4542.7	4539.6	4536.5	4539.6	4542.7	4542.1
12.5°	4129.2	4116.0	4099.9	4103.5	4126.6	4140.9	4128.5	4116.2	4128.5	4140.9	4126.6
15°	3446.5	3430.6	3409.3	3420.8	3465.3	3493.7	3473.7	3453.6	3473.7	3493.7	3465.3
17.5°	2785.4	2782.7	2778.7	2788.1	2810.8	2828.3	2830.3	2832.4	2830.3	2828.3	2810.8
20°	2368.4	2370.2	2373.3	2384.4	2403.5	2418.6	2421.7	2424.9	2421.7	2418.6	2403.5
22.5°	2032.3	2037.4	2045.1	2052.3	2059.0	2065.3	2070.5	2075.8	2070.5	2065.3	2059.0
25°	1613.9	1608.2	1597.6	1598.4	1610.9	1624.5	1641.4	1658.3	1641.4	1624.5	1610.9
27.5°	1309.6	1308.3	1307.2	1311.9	1322.5	1330.5	1330.8	1331.0	1330.8	1330.5	1322.5
30°	1148.5	1149.5	1149.1	1154.0	1164.2	1172.7	1175.8	1178.9	1175.8	1172.7	1164.2
32.5°	1013.2	1016.4	1018.8	1026.3	1039.1	1048.0	1045.8	1043.6	1045.8	1048.0	1039.1
35°	830.3	835.6	842.3	850.5	860.3	867.7	867.7	867.7	867.7	867.7	860.3
37.5°	665.0	673.0	682.4	690.6	697.5	702.9	703.7	704.5	703.7	702.9	697.5
40°	558.2	568.1	579.7	587.7	592.1	596.0	598.2	600.5	598.2	596.0	592.1
42.5°	457.5	468.0	479.6	487.6	492.0	493.9	487.9	482.0	487.9	493.9	492.0
45°	307.3	327.3	340.6	345.5	341.9	333.0	308.1	283.2	308.1	333.0	341.9
47.5°	144.5	179.1	214.2	221.0	199.5	176.5	149.1	121.7	149.1	176.5	199.5
50°	71.3	108.1	152.1	158.6	127.4	98.7	77.4	56.0	77.4	98.7	127.4
52.5°	41.8	72.3	110.3	113.2	81.0	54.2	43.5	32.8	43.5	54.2	81.0
55°	17.2	33.0	53.0	53.9	35.7	21.1	17.6	14.0	17.6	21.1	35.7
57.5°	7.4	13.1	20.3	20.7	14.3	9.1	7.2	5.2	7.2	9.1	14.3
60°	2.8	5.7	9.2	9.5	6.3	3.8	2.9	2.0	2.9	3.8	6.3
62.5°	1.3	2.7	4.5	4.6	2.9	1.5	0.9	0.4	0.9	1.5	2.9
65°	0.0	0.3	0.8	0.8	0.3	0.0	0.0	0.0	0.0	0.0	0.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-OU-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3	5553.3
2.5°	5491.9	5491.0	5510.6	5523.7	5517.7	5511.6	5517.7	5523.7	5510.6	5491.0	5491.9
5°	5289.3	5295.5	5324.4	5346.5	5348.3	5350.1	5348.3	5346.5	5324.4	5295.5	5289.3
7.5°	4881.2	4889.3	4921.4	4944.5	4941.1	4937.6	4941.1	4944.5	4921.4	4889.3	4881.2
10°	4540.4	4544.8	4555.5	4560.5	4548.5	4536.5	4548.5	4560.5	4555.5	4544.8	4540.4
12.5°	4103.5	4099.9	4116.0	4129.2	4134.3	4139.4	4134.3	4129.2	4116.0	4099.9	4103.5
15°	3420.8	3409.3	3430.6	3446.5	3446.1	3445.6	3446.1	3446.5	3430.6	3409.3	3420.8
17.5°	2788.1	2778.7	2782.7	2785.4	2784.1	2782.7	2784.1	2785.4	2782.7	2778.7	2788.1
20°	2384.4	2373.3	2370.2	2368.4	2370.6	2372.8	2370.6	2368.4	2370.2	2373.3	2384.4
22.5°	2052.3	2045.1	2037.4	2032.3	2035.2	2038.2	2035.2	2032.3	2037.4	2045.1	2052.3
25°	1598.4	1597.6	1608.2	1613.9	1604.6	1595.2	1604.6	1613.9	1608.2	1597.6	1598.4
27.5°	1311.9	1307.2	1308.3	1309.6	1311.4	1313.2	1311.4	1309.6	1308.3	1307.2	1311.9
30°	1154.0	1149.1	1149.5	1148.5	1143.2	1137.9	1143.2	1148.5	1149.5	1149.1	1154.0
32.5°	1026.3	1018.8	1016.4	1013.2	1007.9	1002.6	1007.9	1013.2	1016.4	1018.8	1026.3
35°	850.5	842.3	835.6	830.3	829.0	827.6	829.0	830.3	835.6	842.3	850.5
37.5°	690.6	682.4	673.0	665.0	661.6	658.1	661.6	665.0	673.0	682.4	690.6
40°	587.7	579.7	568.1	558.2	553.3	548.4	553.3	558.2	568.1	579.7	587.7
42.5°	487.6	479.6	468.0	457.5	450.1	442.7	450.1	457.5	468.0	479.6	487.6
45°	345.5	340.6	327.3	307.3	267.8	228.2	267.8	307.3	327.3	340.6	345.5
47.5°	221.0	214.2	179.1	144.5	111.6	78.7	111.6	144.5	179.1	214.2	221.0
50°	158.6	152.1	108.1	71.3	56.2	41.0	56.2	71.3	108.1	152.1	158.6
52.5°	113.2	110.3	72.3	41.8	33.8	25.8	33.8	41.8	72.3	110.3	113.2
55°	53.9	53.0	33.0	17.2	14.1	11.0	14.1	17.2	33.0	53.0	53.9
57.5°	20.7	20.3	13.1	7.4	5.8	4.2	5.8	7.4	13.1	20.3	20.7
60°	9.5	9.2	5.7	2.8	1.9	1.0	1.9	2.8	5.7	9.2	9.5
62.5°	4.6	4.5	2.7	1.3	0.7	0.2	0.7	1.3	2.7	4.5	4.6
65°	0.8	0.8	0.3	0.0	0.0	0.0	0.0	0.0	0.3	0.8	0.8
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427571

CATALOG NUMBER: SQ2W-BBN-OU-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	5553.3	5553.3	5553.3	5553.3
2.5°	5513.2	5531.6	5540.8	5550.1
5°	5305.7	5321.3	5334.2	5347.1
7.5°	4896.8	4907.5	4903.3	4899.2
10°	4542.1	4542.7	4539.6	4536.5
12.5°	4126.6	4140.9	4128.5	4116.2
15°	3465.3	3493.7	3473.7	3453.6
17.5°	2810.8	2828.3	2830.3	2832.4
20°	2403.5	2418.6	2421.7	2424.9
22.5°	2059.0	2065.3	2070.5	2075.8
25°	1610.9	1624.5	1641.4	1658.3
27.5°	1322.5	1330.5	1330.8	1331.0
30°	1164.2	1172.7	1175.8	1178.9
32.5°	1039.1	1048.0	1045.8	1043.6
35°	860.3	867.7	867.7	867.7
37.5°	697.5	702.9	703.7	704.5
40°	592.1	596.0	598.2	600.5
42.5°	492.0	493.9	487.9	482.0
45°	341.9	333.0	308.1	283.2
47.5°	199.5	176.5	149.1	121.7
50°	127.4	98.7	77.4	56.0
52.5°	81.0	54.2	43.5	32.8
55°	35.7	21.1	17.6	14.0
57.5°	14.3	9.1	7.2	5.2
60°	6.3	3.8	2.9	2.0
62.5°	2.9	1.5	0.9	0.4
65°	0.3	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1427571
 CATALOG NUMBER: SQ2W-BBN-0U-075D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00