

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428656

Luminaire Tested: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428656
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10868.5 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 104.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	100	96	93	90	92	89	86	84	75	74	72	63	62	61	52	51	50	45				
2	93	87	82	78	86	81	77	73	69	66	64	59	57	55	49	47	46	42				
3	87	79	73	68	80	74	69	65	64	60	57	54	52	50	46	44	43	39				
4	81	72	66	61	75	67	62	58	59	55	52	51	48	46	43	41	40	36				
5	76	66	59	55	70	62	56	52	54	50	47	47	44	42	41	39	37	34				
6	71	61	54	49	66	57	51	47	51	46	43	44	41	39	38	36	35	32				
7	67	56	50	45	62	53	47	43	47	43	40	42	38	36	36	34	32	30				
8	63	52	46	41	59	50	44	40	44	40	37	39	36	33	34	32	30	28				
9	59	49	43	38	55	46	41	37	42	37	34	37	34	31	33	30	29	27				
10	56	46	40	35	52	43	38	34	39	35	32	35	32	29	31	29	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	146480	146480	146480	146480
5°	141432	141588	141432	141588
10°	122248	122538	122248	122538
15°	97279	94589	97279	94589
20°	69105	68691	69105	68691
25°	49717	48399	49717	48399
30°	37988	36876	37988	36876
35°	29819	28550	29819	28550
40°	22592	21201	22592	21201
45°	12643	11282	12643	11282
50°	4446	3921	4446	3921
55°	2719	2581	2719	2581
60°	2080	1921	2080	1921
65°	1906	1784	1906	1784
70°	1822	1671	1822	1671
75°	1709	1609	1709	1609
80°	1497	1497	1497	1497
85°	1482	1186	1482	1186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 14990 cd/sqm



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	787.5	7.2
10°-20°	1565.2	14.4
20°-30°	1296.2	11.9
30°-40°	932.5	8.6
40°-50°	475.0	4.4
50°-60°	123.5	1.1
60°-70°	51.3	0.5
70°-80°	28.5	0.3
80°-90°	16.4	0.2
90°-100°	152.4	1.4
100°-110°	444.5	4.1
110°-120°	725.4	6.7
120°-130°	920.5	8.5
130°-140°	985.0	9.1
140°-150°	919.8	8.5
150°-160°	756.8	7.0
160°-170°	507.6	4.7
170°-180°	180.2	1.7
0°-30°	3649.0	33.6
0°-40°	4581.5	42.2
0°-60°	5180.0	47.7
0°-90°	5276.2	48.5
90°-120°	1322.4	12.2
90°-150°	4147.7	38.2
90°-180°	5592.0	51.5
0°-180°	10868.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9072	9072	9072	9072	9072	
5°	8726	8736	8726	8736	8726	787
15°	5820	5659	5820	5659	5820	1580
25°	2791	2717	2791	2717	2791	1313
35°	1513	1448	1513	1448	1513	949
45°	554	494	554	494	554	442
55°	97	92	97	92	97	95
65°	50	47	50	47	50	50
75°	27	26	27	26	27	29
85°	8	6	8	6	8	9
90°	6	43	6	83	6	5
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5
2.5°	9058.4	9051.5	9044.6	9014.1	8975.8	8972.7	9004.7	9026.7	9018.7	9010.7	9018.7
5°	8726.5	8720.8	8715.0	8688.9	8656.0	8667.5	8723.3	8761.9	8749.0	8736.1	8749.0
7.5°	8041.2	8046.0	8050.9	8037.5	8018.1	8033.0	8082.4	8116.0	8102.2	8088.5	8102.2
10°	7456.6	7469.5	7482.4	7464.1	7435.5	7457.3	7529.6	7571.6	7523.0	7474.3	7523.0
12.5°	6811.5	6803.3	6795.0	6778.3	6758.8	6754.9	6766.5	6768.4	6741.6	6714.7	6741.6
15°	5819.8	5789.8	5759.7	5713.6	5662.1	5645.3	5663.1	5674.6	5666.7	5658.9	5666.7
17.5°	4687.7	4699.3	4710.9	4679.7	4634.2	4610.6	4608.8	4605.3	4596.5	4587.6	4596.5
20°	4022.0	4025.6	4029.2	4009.7	3982.5	3976.1	3990.4	4000.8	3999.3	3997.9	3999.3
22.5°	3486.4	3487.1	3487.8	3462.1	3427.4	3420.7	3441.9	3454.5	3441.7	3428.8	3441.7
25°	2790.8	2788.7	2786.5	2769.3	2747.2	2730.7	2720.0	2712.5	2714.6	2716.8	2714.6
27.5°	2288.6	2279.8	2270.9	2256.2	2239.7	2234.9	2242.1	2246.1	2240.8	2235.5	2240.8
30°	2037.6	2030.4	2023.3	2008.6	1991.4	1985.0	1989.3	1990.9	1984.5	1978.0	1984.5
32.5°	1812.2	1812.5	1812.8	1799.6	1781.8	1772.0	1770.0	1767.3	1762.6	1757.8	1762.6
35°	1512.9	1517.2	1521.5	1510.7	1495.0	1481.8	1471.0	1461.4	1454.9	1448.5	1454.9
37.5°	1245.7	1249.7	1253.7	1244.8	1231.4	1216.9	1201.2	1188.0	1182.6	1177.2	1182.6
40°	1071.9	1074.8	1077.6	1071.4	1062.1	1048.1	1029.5	1014.5	1010.2	1005.9	1010.2
42.5°	882.6	894.6	906.7	902.7	893.4	880.0	862.6	847.1	837.7	828.2	837.7
45°	553.7	591.6	629.5	646.5	656.5	651.8	632.5	604.3	549.2	494.1	549.2
47.5°	280.0	332.5	385.1	422.8	455.5	445.1	391.4	337.7	283.6	229.5	283.6
50°	177.0	213.5	250.0	296.1	345.5	334.8	264.0	204.8	180.4	156.1	180.4
52.5°	135.8	154.6	173.3	217.2	269.4	264.4	202.1	152.1	138.7	125.2	138.7
55°	96.6	103.7	110.9	135.2	165.2	163.4	129.8	103.2	97.5	91.7	97.5
57.5°	74.7	78.7	82.7	91.7	102.5	101.5	88.7	78.3	74.7	71.1	74.7
60°	64.4	67.2	70.1	74.6	79.6	78.9	72.4	66.7	63.1	59.5	63.1
62.5°	57.9	59.7	61.4	63.4	65.6	64.6	60.4	57.0	55.7	54.4	55.7
65°	49.9	50.6	51.3	51.5	51.5	50.8	49.4	48.1	47.4	46.7	47.4
67.5°	42.5	43.2	43.9	44.0	43.8	43.4	42.7	42.0	41.3	40.6	41.3
70°	38.6	39.3	40.1	39.7	39.0	38.3	37.6	36.8	36.1	35.4	36.1
72.5°	33.5	34.2	34.9	34.5	33.8	33.4	33.3	33.0	32.3	31.5	32.3
75°	27.4	27.4	27.4	27.4	27.4	27.0	26.3	25.8	25.8	25.8	25.8
77.5°	21.2	21.4	21.5	21.0	20.3	20.0	20.0	19.8	19.2	18.7	19.2
80°	16.1	16.8	17.5	17.2	16.5	16.1	16.1	16.1	16.1	16.1	16.1
82.5°	13.5	13.7	13.8	13.3	12.6	12.2	12.2	12.2	12.2	12.2	12.2
85°	8.0	8.0	8.0	7.5	6.8	6.8	7.5	7.9	7.2	6.4	7.2
87.5°	3.7	5.3	7.2	8.8	9.9	10.3	10.3	10.7	11.1	11.1	11.1
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5
2.5°	9026.7	9004.7	8972.7	8975.8	9014.1	9044.6	9051.5	9058.4	9051.5	9044.6	9014.1
5°	8761.9	8723.3	8667.5	8656.0	8688.9	8715.0	8720.8	8726.5	8720.8	8715.0	8688.9
7.5°	8116.0	8082.4	8033.0	8018.1	8037.5	8050.9	8046.0	8041.2	8046.0	8050.9	8037.5
10°	7571.6	7529.6	7457.3	7435.5	7464.1	7482.4	7469.5	7456.6	7469.5	7482.4	7464.1
12.5°	6768.4	6766.5	6754.9	6758.8	6778.3	6795.0	6803.3	6811.5	6803.3	6795.0	6778.3
15°	5674.6	5663.1	5645.3	5662.1	5713.6	5759.7	5789.8	5819.8	5789.8	5759.7	5713.6
17.5°	4605.3	4608.8	4610.6	4634.2	4679.7	4710.9	4699.3	4687.7	4699.3	4710.9	4679.7
20°	4000.8	3990.4	3976.1	3982.5	4009.7	4029.2	4025.6	4022.0	4025.6	4029.2	4009.7
22.5°	3454.5	3441.9	3420.7	3427.4	3462.1	3487.8	3487.1	3486.4	3487.1	3487.8	3462.1
25°	2712.5	2720.0	2730.7	2747.2	2769.3	2786.5	2788.7	2790.8	2788.7	2786.5	2769.3
27.5°	2246.1	2242.1	2234.9	2239.7	2256.2	2270.9	2279.8	2288.6	2279.8	2270.9	2256.2
30°	1990.9	1989.3	1985.0	1991.4	2008.6	2023.3	2030.4	2037.6	2030.4	2023.3	2008.6
32.5°	1767.3	1770.0	1772.0	1781.8	1799.6	1812.8	1812.5	1812.2	1812.5	1812.8	1799.6
35°	1461.4	1471.0	1481.8	1495.0	1510.7	1521.5	1517.2	1512.9	1517.2	1521.5	1510.7
37.5°	1188.0	1201.2	1216.9	1231.4	1244.8	1253.7	1249.7	1245.7	1249.7	1253.7	1244.8
40°	1014.5	1029.5	1048.1	1062.1	1071.4	1077.6	1074.8	1071.9	1074.8	1077.6	1071.4
42.5°	847.1	862.6	880.0	893.4	902.7	906.7	894.6	882.6	894.6	906.7	902.7
45°	604.3	632.5	651.8	656.5	646.5	629.5	591.6	553.7	591.6	629.5	646.5
47.5°	337.7	391.4	445.1	455.5	422.8	385.1	332.5	280.0	332.5	385.1	422.8
50°	204.8	264.0	334.8	345.5	296.1	250.0	213.5	177.0	213.5	250.0	296.1
52.5°	152.1	202.1	264.4	269.4	217.2	173.3	154.6	135.8	154.6	173.3	217.2
55°	103.2	129.8	163.4	165.2	135.2	110.9	103.7	96.6	103.7	110.9	135.2
57.5°	78.3	88.7	101.5	102.5	91.7	82.7	78.7	74.7	78.7	82.7	91.7
60°	66.7	72.4	78.9	79.6	74.6	70.1	67.2	64.4	67.2	70.1	74.6
62.5°	57.0	60.4	64.6	65.6	63.4	61.4	59.7	57.9	59.7	61.4	63.4
65°	48.1	49.4	50.8	51.5	51.5	51.3	50.6	49.9	50.6	51.3	51.5
67.5°	42.0	42.7	43.4	43.8	44.0	43.9	43.2	42.5	43.2	43.9	44.0
70°	36.8	37.6	38.3	39.0	39.7	40.1	39.3	38.6	39.3	40.1	39.7
72.5°	33.0	33.3	33.4	33.8	34.5	34.9	34.2	33.5	34.2	34.9	34.5
75°	25.8	26.3	27.0	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
77.5°	19.8	20.0	20.0	20.3	21.0	21.5	21.4	21.2	21.4	21.5	21.0
80°	16.1	16.1	16.1	16.5	17.2	17.5	16.8	16.1	16.8	17.5	17.2
82.5°	12.2	12.2	12.2	12.6	13.3	13.8	13.7	13.5	13.7	13.8	13.3
85°	7.9	7.5	6.8	6.8	7.5	8.0	8.0	8.0	8.0	8.0	7.5
87.5°	10.7	10.3	10.3	9.9	8.8	7.2	5.3	3.7	5.3	6.8	9.5
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5	9072.5
2.5°	8975.8	8972.7	9004.7	9026.7	9018.7	9010.7	9018.7	9026.7	9004.7	8972.7	8975.8
5°	8656.0	8667.5	8723.3	8761.9	8749.0	8736.1	8749.0	8761.9	8723.3	8667.5	8656.0
7.5°	8018.1	8033.0	8082.4	8116.0	8102.2	8088.5	8102.2	8116.0	8082.4	8033.0	8018.1
10°	7435.5	7457.3	7529.6	7571.6	7523.0	7474.3	7523.0	7571.6	7529.6	7457.3	7435.5
12.5°	6758.8	6754.9	6766.5	6768.4	6741.6	6714.7	6741.6	6768.4	6766.5	6754.9	6758.8
15°	5662.1	5645.3	5663.1	5674.6	5666.7	5658.9	5666.7	5674.6	5663.1	5645.3	5662.1
17.5°	4634.2	4610.6	4608.8	4605.3	4596.5	4587.6	4596.5	4605.3	4608.8	4610.6	4634.2
20°	3982.5	3976.1	3990.4	4000.8	3999.3	3997.9	3999.3	4000.8	3990.4	3976.1	3982.5
22.5°	3427.4	3420.7	3441.9	3454.5	3441.7	3428.8	3441.7	3454.5	3441.9	3420.7	3427.4
25°	2747.2	2730.7	2720.0	2712.5	2714.6	2716.8	2714.6	2712.5	2720.0	2730.7	2747.2
27.5°	2239.7	2234.9	2242.1	2246.1	2240.8	2235.5	2240.8	2246.1	2242.1	2234.9	2239.7
30°	1991.4	1985.0	1989.3	1990.9	1984.5	1978.0	1984.5	1990.9	1989.3	1985.0	1991.4
32.5°	1781.8	1772.0	1770.0	1767.3	1762.6	1757.8	1762.6	1767.3	1770.0	1772.0	1781.8
35°	1495.0	1481.8	1471.0	1461.4	1454.9	1448.5	1454.9	1461.4	1471.0	1481.8	1495.0
37.5°	1231.4	1216.9	1201.2	1188.0	1182.6	1177.2	1182.6	1188.0	1201.2	1216.9	1231.4
40°	1062.1	1048.1	1029.5	1014.5	1010.2	1005.9	1010.2	1014.5	1029.5	1048.1	1062.1
42.5°	893.4	880.0	862.6	847.1	837.7	828.2	837.7	847.1	862.6	880.0	893.4
45°	656.5	651.8	632.5	604.3	549.2	494.1	549.2	604.3	632.5	651.8	656.5
47.5°	455.5	445.1	391.4	337.7	283.6	229.5	283.6	337.7	391.4	445.1	455.5
50°	345.5	334.8	264.0	204.8	180.4	156.1	180.4	204.8	264.0	334.8	345.5
52.5°	269.4	264.4	202.1	152.1	138.7	125.2	138.7	152.1	202.1	264.4	269.4
55°	165.2	163.4	129.8	103.2	97.5	91.7	97.5	103.2	129.8	163.4	165.2
57.5°	102.5	101.5	88.7	78.3	74.7	71.1	74.7	78.3	88.7	101.5	102.5
60°	79.6	78.9	72.4	66.7	63.1	59.5	63.1	66.7	72.4	78.9	79.6
62.5°	65.6	64.6	60.4	57.0	55.7	54.4	55.7	57.0	60.4	64.6	65.6
65°	51.5	50.8	49.4	48.1	47.4	46.7	47.4	48.1	49.4	50.8	51.5
67.5°	43.8	43.4	42.7	42.0	41.3	40.6	41.3	42.0	42.7	43.4	43.8
70°	39.0	38.3	37.6	36.8	36.1	35.4	36.1	36.8	37.6	38.3	39.0
72.5°	33.8	33.4	33.3	33.0	32.3	31.5	32.3	33.0	33.3	33.4	33.8
75°	27.4	27.0	26.3	25.8	25.8	25.8	25.8	25.8	26.3	27.0	27.4
77.5°	20.3	20.0	20.0	19.8	19.2	18.7	19.2	19.8	20.0	20.0	20.3
80°	16.5	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.5
82.5°	12.6	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.6
85°	6.8	6.8	7.5	7.9	7.2	6.4	7.2	7.9	7.5	6.8	6.8
87.5°	11.5	14.2	16.9	18.4	20.0	19.2	20.0	18.4	16.9	14.2	11.5
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	128.8	112.2	89.4	
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	234.1	207.0	179.9	
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	344.0	313.8	277.4	
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	412.1	377.3	342.4	
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	478.6	440.7	395.1	
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	570.7	530.1	481.7	
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	655.8	618.3	568.4	
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	717.8	677.1	636.5	



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	9072.5	9072.5	9072.5	9072.5
2.5°	9014.1	9044.6	9051.5	9058.4
5°	8688.9	8715.0	8720.8	8726.5
7.5°	8037.5	8050.9	8046.0	8041.2
10°	7464.1	7482.4	7469.5	7456.6
12.5°	6778.3	6795.0	6803.3	6811.5
15°	5713.6	5759.7	5789.8	5819.8
17.5°	4679.7	4710.9	4699.3	4687.7
20°	4009.7	4029.2	4025.6	4022.0
22.5°	3462.1	3487.8	3487.1	3486.4
25°	2769.3	2786.5	2788.7	2790.8
27.5°	2256.2	2270.9	2279.8	2288.6
30°	2008.6	2023.3	2030.4	2037.6
32.5°	1799.6	1812.8	1812.5	1812.2
35°	1510.7	1521.5	1517.2	1512.9
37.5°	1244.8	1253.7	1249.7	1245.7
40°	1071.4	1077.6	1074.8	1071.9
42.5°	902.7	906.7	894.6	882.6
45°	646.5	629.5	591.6	553.7
47.5°	422.8	385.1	332.5	280.0
50°	296.1	250.0	213.5	177.0
52.5°	217.2	173.3	154.6	135.8
55°	135.2	110.9	103.7	96.6
57.5°	91.7	82.7	78.7	74.7
60°	74.6	70.1	67.2	64.4
62.5°	63.4	61.4	59.7	57.9
65°	51.5	51.3	50.6	49.9
67.5°	44.0	43.9	43.2	42.5
70°	39.7	40.1	39.3	38.6
72.5°	34.5	34.9	34.2	33.5
75°	27.4	27.4	27.4	27.4
77.5°	21.0	21.5	21.4	21.2
80°	17.2	17.5	16.8	16.1
82.5°	13.3	13.8	13.7	13.5
85°	7.5	8.0	8.0	8.0
87.5°	9.5	6.8	5.3	3.7
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1428656

CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1428656
 CATALOG NUMBER: SQ2W-WBN-K-150U-125D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.34	4.02	4.35	5.01	6.32	2.97	3.65	3.98	4.64	5.94
	3H	4.57	5.17	5.59	6.17	7.50	4.17	4.78	5.19	5.78	7.11
	4H	5.09	5.65	6.12	6.66	7.99	4.69	5.26	5.72	6.26	7.60
	6H	5.44	5.96	6.47	6.97	8.31	5.02	5.54	6.06	6.55	7.90
	8H	5.58	6.07	6.62	7.10	8.44	5.16	5.65	6.20	6.67	8.02
	12H	5.67	6.14	6.72	7.16	8.52	5.23	5.69	6.27	6.71	8.07
4H	2H	3.66	4.23	4.70	5.23	6.57	3.35	3.92	4.39	4.92	6.26
	3H	5.15	5.62	6.19	6.66	8.00	4.81	5.28	5.85	6.32	7.66
	4H	5.80	6.23	6.85	7.26	8.63	5.45	5.88	6.50	6.90	8.28
	6H	6.29	6.65	7.34	7.70	9.07	5.91	6.27	6.96	7.32	8.69
	8H	6.50	6.84	7.55	7.88	9.26	6.10	6.44	7.15	7.48	8.86
	12H	6.63	6.94	7.70	7.99	9.38	6.21	6.51	7.28	7.57	8.95
8H	4H	5.96	6.30	7.02	7.34	8.72	5.65	5.99	6.70	7.03	8.41
	6H	6.60	6.87	7.67	7.96	9.33	6.24	6.52	7.32	7.60	8.98
	8H	6.91	7.16	8.00	8.22	9.62	6.53	6.77	7.62	7.84	9.24
	12H	7.14	7.35	8.22	8.41	9.85	6.73	6.94	7.82	8.00	9.45
12H	4H	5.94	6.24	7.01	7.30	8.68	5.64	5.94	6.71	7.00	8.38
	6H	6.63	6.87	7.71	7.94	9.34	6.29	6.54	7.38	7.60	9.00
	8H	6.98	7.19	8.06	8.25	9.69	6.61	6.82	7.70	7.88	9.33