

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427586

Luminaire Tested: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427586
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4980.1 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	81
1	109	106	103	101	104	102	99	97	94	92	91	87	86	85	81	80	79	76
2	103	98	93	90	99	94	91	87	88	85	83	82	80	78	77	75	74	71
3	97	91	85	81	94	88	83	80	82	79	76	77	75	72	73	71	69	66
4	92	84	79	74	89	82	77	73	77	73	70	73	70	67	69	67	64	62
5	87	79	73	69	84	77	71	67	73	68	65	69	65	63	66	63	60	58
6	83	74	68	63	80	72	67	63	69	64	61	65	62	59	62	59	57	55
7	79	69	63	59	76	68	62	58	65	60	57	62	58	55	59	56	54	52
8	75	65	59	55	73	64	58	55	61	57	53	59	55	52	56	53	51	49
9	71	62	56	52	69	61	55	51	58	54	50	56	52	49	54	50	48	46
10	68	59	53	49	66	57	52	49	55	51	48	53	49	47	51	48	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	119797	119797	119797	119797
5°	115789	115854	115789	115854
10°	99371	99371	99371	99371
15°	77132	76953	77132	76953
20°	55667	54473	55667	54473
25°	39470	37970	39470	37970
30°	29365	28343	29365	28343
35°	22850	21795	22850	21795
40°	16910	15445	16910	15445
45°	8640	6962	8640	6962
50°	1881	1376	1881	1376
55°	526	414	526	414
60°	87	42	87	42
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 10540 cd/sqm



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	641.6	12.9
10°-20°	1265.0	25.4
20°-30°	1020.4	20.5
30°-40°	708.9	14.2
40°-50°	327.4	6.6
50°-60°	45.9	0.9
60°-70°	1.6	0.0
70°-80°	0.0	0.0
80°-90°	1.8	0.0
90°-100°	26.4	0.5
100°-110°	76.9	1.5
110°-120°	125.6	2.5
120°-130°	159.3	3.2
130°-140°	170.5	3.4
140°-150°	159.2	3.2
150°-160°	131.0	2.6
160°-170°	87.9	1.8
170°-180°	31.2	0.6
0°-30°	2927.0	58.8
0°-40°	3635.8	73.0
0°-60°	4009.1	80.5
0°-90°	4012.5	80.6
90°-120°	228.9	4.6
90°-150°	717.9	14.4
90°-180°	968.0	19.4
0°-180°	4980.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	7420	7420	7420	7420	7420	
5°	7144	7148	7144	7148	7144	642
15°	4614	4604	4614	4604	4614	1270
25°	2216	2131	2216	2131	2216	1037
35°	1159	1106	1159	1106	1159	725
45°	378	305	378	305	378	306
55°	19	15	19	15	19	24
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	1	14	1	1
95°	10	8	10	45	10	13
105°	49	78	49	108	49	52
115°	94	130	94	160	94	92
125°	139	206	139	196	139	124
135°	188	270	188	217	188	146
145°	241	311	241	222	241	151
155°	286	338	286	230	286	131
165°	316	352	316	265	316	89
175°	330	345	330	311	330	31
180°	332	332	332	332	332	



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8
2.5°	7415.5	7403.1	7390.8	7366.3	7337.8	7336.6	7362.7	7380.3	7372.2	7364.2	7372.2
5°	7144.3	7127.1	7109.9	7089.1	7067.1	7075.4	7114.0	7143.6	7146.0	7148.3	7146.0
7.5°	6545.8	6551.4	6557.0	6542.7	6521.8	6532.7	6575.5	6606.4	6601.8	6597.2	6601.8
10°	6061.2	6065.4	6069.6	6068.8	6066.4	6072.4	6086.7	6093.3	6077.3	6061.2	6077.3
12.5°	5499.7	5516.2	5532.7	5513.6	5482.7	5478.0	5499.4	5517.1	5523.9	5530.7	5523.9
15°	4614.5	4641.2	4668.0	4630.1	4570.6	4555.2	4583.7	4605.0	4604.4	4603.8	4604.4
17.5°	3784.4	3781.6	3778.9	3755.5	3725.2	3712.7	3718.0	3721.6	3719.8	3718.0	3719.8
20°	3239.9	3235.7	3231.6	3211.4	3185.8	3170.9	3166.8	3164.4	3167.4	3170.4	3167.4
22.5°	2773.5	2766.5	2759.5	2751.0	2742.1	2732.5	2722.1	2715.4	2719.3	2723.2	2719.3
25°	2215.6	2193.1	2170.5	2152.3	2135.7	2134.5	2148.8	2156.4	2143.9	2131.4	2143.9
27.5°	1778.4	1778.0	1777.7	1767.0	1752.8	1746.5	1748.1	1749.8	1752.2	1754.6	1752.2
30°	1575.1	1571.0	1566.8	1555.5	1541.9	1535.3	1535.9	1534.6	1527.5	1520.3	1527.5
32.5°	1394.4	1397.3	1400.3	1388.3	1371.3	1361.2	1358.0	1353.8	1346.7	1339.5	1346.7
35°	1159.3	1159.3	1159.3	1149.5	1136.4	1125.4	1116.5	1109.4	1107.6	1105.8	1107.6
37.5°	941.3	940.3	939.2	932.0	922.7	911.8	899.2	888.6	883.9	879.3	883.9
40°	802.3	799.3	796.3	791.1	785.2	774.5	759.0	745.8	739.3	732.8	739.3
42.5°	644.0	651.9	659.9	657.4	651.5	640.8	625.3	611.3	601.4	591.6	601.4
45°	378.4	411.7	445.0	456.9	461.6	455.1	437.2	410.7	357.8	304.9	357.8
47.5°	162.6	199.2	235.8	266.5	295.3	286.2	239.3	193.1	149.1	105.1	149.1
50°	74.9	103.4	131.9	170.3	211.9	203.2	144.4	95.2	75.0	54.8	75.0
52.5°	43.9	58.1	72.4	108.2	151.2	147.4	96.6	55.9	45.2	34.5	45.2
55°	18.7	23.5	28.2	47.7	72.1	70.9	44.1	23.0	18.9	14.7	18.9
57.5°	7.0	9.6	12.2	19.2	27.6	27.1	17.6	9.9	7.8	5.6	7.8
60°	2.7	3.9	5.1	8.5	12.6	12.3	7.6	3.7	2.5	1.3	2.5
62.5°	0.5	1.2	2.0	3.8	6.1	6.0	3.7	1.7	1.0	0.3	1.0
65°	0.0	0.0	0.0	0.4	1.0	1.0	0.4	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.2	0.5	0.8	1.1	1.3	1.3	1.3	1.4	1.5	1.5	1.5
90°	1.0	2.3	4.0	5.4	6.4	6.7	6.7	7.0	7.4	7.4	7.4
92.5°	3.7	5.8	5.9	5.9	7.2	7.8	8.3	8.4	8.7	8.7	8.7
95°	10.4	11.4	17.1	16.7	11.4	9.0	7.7	7.7	7.7	7.7	7.7
97.5°	19.8	21.3	22.2	29.8	31.5	30.4	24.8	20.8	18.6	17.6	18.6
100°	28.1	28.8	30.8	31.1	39.5	47.6	43.5	38.5	36.8	35.8	36.8
102.5°	36.4	36.8	39.9	41.3	43.3	47.8	61.8	60.2	59.1	58.9	59.1
105°	48.9	49.2	54.9	57.6	58.9	58.9	58.6	65.3	76.0	78.4	76.0
107.5°	62.2	63.8	70.5	77.6	79.2	79.6	77.8	76.8	76.4	76.7	76.4
110°	71.3	73.7	81.7	90.8	93.1	93.8	93.1	92.1	91.4	91.4	91.4



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	80.2	83.6	92.7	103.1	107.0	109.0	107.6	106.8	106.2	106.7	106.2
115°	93.8	98.8	110.8	121.6	129.6	130.6	130.3	130.3	129.9	129.9	129.9
117.5°	106.4	114.4	127.9	140.4	149.7	152.4	153.7	153.3	152.9	153.6	152.9
120°	115.2	124.6	140.0	154.0	163.1	167.1	168.4	167.8	168.4	167.8	168.4
122.5°	124.6	136.1	151.2	165.8	176.5	181.0	182.6	182.8	182.9	182.5	182.9
125°	138.6	152.7	170.5	185.5	196.6	201.9	203.3	203.6	204.3	206.0	204.3
127.5°	152.8	168.8	188.3	202.8	214.1	220.6	222.7	223.4	224.8	225.6	224.8
130°	162.8	180.8	200.6	214.3	225.4	232.4	236.1	237.1	238.8	238.4	238.8
132.5°	173.2	192.1	212.1	226.4	236.6	244.2	247.3	250.2	250.8	251.3	250.8
135°	188.5	209.0	229.1	243.1	252.8	260.2	264.2	266.9	268.6	269.6	268.6
137.5°	204.7	226.2	245.5	258.1	267.8	274.2	278.8	281.6	283.3	284.1	283.3
140°	215.7	236.4	255.2	268.2	276.9	283.3	287.3	290.7	292.7	292.7	292.7
142.5°	226.1	246.6	264.8	277.9	285.5	291.3	295.6	298.2	300.5	300.5	300.5
145°	240.8	261.2	277.9	291.0	297.4	302.7	307.4	309.4	310.8	310.8	310.8
147.5°	256.1	274.2	289.5	302.0	307.4	313.6	317.3	318.9	320.6	319.9	320.6
150°	265.2	282.0	296.7	308.4	313.8	319.8	323.5	324.8	326.5	325.5	326.5
152.5°	274.1	290.0	303.4	314.3	318.9	324.9	329.1	330.5	331.6	330.9	331.6
155°	286.0	300.1	312.4	322.5	326.5	332.2	336.2	337.9	339.2	337.6	339.2
157.5°	296.6	308.8	319.5	328.8	333.1	338.0	341.7	343.8	345.1	344.4	345.1
160°	303.1	314.1	323.8	332.5	336.6	340.9	344.9	347.3	348.6	347.6	348.6
162.5°	308.4	318.4	327.6	335.5	339.0	342.8	347.6	349.7	351.0	349.7	351.0
165°	316.1	324.2	332.2	338.9	341.9	344.9	349.9	352.3	353.3	352.0	353.3
167.5°	322.0	328.1	334.6	340.4	342.6	345.5	350.6	352.5	353.8	352.1	353.8
170°	325.2	330.5	336.2	340.9	342.6	345.3	350.3	352.0	353.0	351.3	353.0
172.5°	327.8	331.9	336.5	340.6	341.5	343.7	348.4	350.1	350.8	349.4	350.8
175°	330.5	332.9	336.2	338.9	338.6	339.9	343.9	345.3	346.6	344.6	346.6
177.5°	331.8	332.9	333.9	335.5	334.5	334.5	337.4	338.2	338.5	337.4	338.5
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8
2.5°	7380.3	7362.7	7336.6	7337.8	7366.3	7390.8	7403.1	7415.5	7403.1	7390.8	7366.3
5°	7143.6	7114.0	7075.4	7067.1	7089.1	7109.9	7127.1	7144.3	7127.1	7109.9	7089.1
7.5°	6606.4	6575.5	6532.7	6521.8	6542.7	6557.0	6551.4	6545.8	6551.4	6557.0	6542.7
10°	6093.3	6086.7	6072.4	6066.4	6068.8	6069.6	6065.4	6061.2	6065.4	6069.6	6068.8
12.5°	5517.1	5499.4	5478.0	5482.7	5513.6	5532.7	5516.2	5499.7	5516.2	5532.7	5513.6
15°	4605.0	4583.7	4555.2	4570.6	4630.1	4668.0	4641.2	4614.5	4641.2	4668.0	4630.1
17.5°	3721.6	3718.0	3712.7	3725.2	3755.5	3778.9	3781.6	3784.4	3781.6	3778.9	3755.5
20°	3164.4	3166.8	3170.9	3185.8	3211.4	3231.6	3235.7	3239.9	3235.7	3231.6	3211.4
22.5°	2715.4	2722.1	2732.5	2742.1	2751.0	2759.5	2766.5	2773.5	2766.5	2759.5	2751.0
25°	2156.4	2148.8	2134.5	2135.7	2152.3	2170.5	2193.1	2215.6	2193.1	2170.5	2152.3
27.5°	1749.8	1748.1	1746.5	1752.8	1767.0	1777.7	1778.0	1778.4	1778.0	1777.7	1767.0
30°	1534.6	1535.9	1535.3	1541.9	1555.5	1566.8	1571.0	1575.1	1571.0	1566.8	1555.5
32.5°	1353.8	1358.0	1361.2	1371.3	1388.3	1400.3	1397.3	1394.4	1397.3	1400.3	1388.3
35°	1109.4	1116.5	1125.4	1136.4	1149.5	1159.3	1159.3	1159.3	1159.3	1159.3	1149.5
37.5°	888.6	899.2	911.8	922.7	932.0	939.2	940.3	941.3	940.3	939.2	932.0
40°	745.8	759.0	774.5	785.2	791.1	796.3	799.3	802.3	799.3	796.3	791.1
42.5°	611.3	625.3	640.8	651.5	657.4	659.9	651.9	644.0	651.9	659.9	657.4
45°	410.7	437.2	455.1	461.6	456.9	445.0	411.7	378.4	411.7	445.0	456.9
47.5°	193.1	239.3	286.2	295.3	266.5	235.8	199.2	162.6	199.2	235.8	266.5
50°	95.2	144.4	203.2	211.9	170.3	131.9	103.4	74.9	103.4	131.9	170.3
52.5°	55.9	96.6	147.4	151.2	108.2	72.4	58.1	43.9	58.1	72.4	108.2
55°	23.0	44.1	70.9	72.1	47.7	28.2	23.5	18.7	23.5	28.2	47.7
57.5°	9.9	17.6	27.1	27.6	19.2	12.2	9.6	7.0	9.6	12.2	19.2
60°	3.7	7.6	12.3	12.6	8.5	5.1	3.9	2.7	3.9	5.1	8.5
62.5°	1.7	3.7	6.0	6.1	3.8	2.0	1.2	0.5	1.2	2.0	3.8
65°	0.0	0.4	1.0	1.0	0.4	0.0	0.0	0.0	0.0	0.0	0.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.4	1.3	1.3	1.3	1.1	0.8	0.5	0.2	0.5	0.7	1.2
90°	7.0	6.7	6.7	6.4	5.4	4.0	2.3	1.0	2.3	3.7	6.0
92.5°	8.4	8.3	7.8	7.2	5.9	5.9	5.8	3.7	6.4	9.0	13.0
95°	7.7	7.7	9.0	11.4	16.7	17.1	11.4	10.4	14.7	20.8	26.1
97.5°	20.8	24.8	30.4	31.5	29.8	22.2	21.3	19.8	27.0	33.0	41.6
100°	38.5	43.5	47.6	39.5	31.1	30.8	28.8	28.1	35.8	41.5	49.9
102.5°	60.2	61.8	47.8	43.3	41.3	39.9	36.8	36.4	44.1	52.0	59.0
105°	65.3	58.6	58.9	58.9	57.6	54.9	49.2	48.9	57.6	66.6	75.3
107.5°	76.8	77.8	79.6	79.2	77.6	70.5	63.8	62.2	70.1	80.9	90.5
110°	92.1	93.1	93.8	93.1	90.8	81.7	73.7	71.3	78.4	89.7	100.1



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	106.8	107.6	109.0	107.0	103.1	92.7	83.6	80.2	87.2	98.9	109.5
115°	130.3	130.3	130.6	129.6	121.6	110.8	98.8	93.8	99.8	110.5	122.2
117.5°	153.3	153.7	152.4	149.7	140.4	127.9	114.4	106.4	111.1	122.4	134.5
120°	167.8	168.4	167.1	163.1	154.0	140.0	124.6	115.2	118.9	129.9	142.0
122.5°	182.8	182.6	181.0	176.5	165.8	151.2	136.1	124.6	126.1	136.4	148.2
125°	203.6	203.3	201.9	196.6	185.5	170.5	152.7	138.6	136.6	145.3	157.4
127.5°	223.4	222.7	220.6	214.1	202.8	188.3	168.8	152.8	148.4	153.8	164.9
130°	237.1	236.1	232.4	225.4	214.3	200.6	180.8	162.8	156.4	159.7	169.4
132.5°	250.2	247.3	244.2	236.6	226.4	212.1	192.1	173.2	164.4	165.9	173.5
135°	266.9	264.2	260.2	252.8	243.1	229.1	209.0	188.5	176.5	175.1	179.5
137.5°	281.6	278.8	274.2	267.8	258.1	245.5	226.2	204.7	189.5	185.0	186.7
140°	290.7	287.3	283.3	276.9	268.2	255.2	236.4	215.7	198.6	192.2	191.2
142.5°	298.2	295.6	291.3	285.5	277.9	264.8	246.6	226.1	208.0	199.7	197.4
145°	309.4	307.4	302.7	297.4	291.0	277.9	261.2	240.8	222.7	212.0	207.0
147.5°	318.9	317.3	313.6	307.4	302.0	289.5	274.2	256.1	237.6	224.3	217.8
150°	324.8	323.5	319.8	313.8	308.4	296.7	282.0	265.2	247.5	233.4	225.0
152.5°	330.5	329.1	324.9	318.9	314.3	303.4	290.0	274.1	256.0	242.0	233.3
155°	337.9	336.2	332.2	326.5	322.5	312.4	300.1	286.0	270.6	255.8	246.1
157.5°	343.8	341.7	338.0	333.1	328.8	319.5	308.8	296.6	283.2	269.1	259.2
160°	347.3	344.9	340.9	336.6	332.5	323.8	314.1	303.1	290.7	277.9	267.2
162.5°	349.7	347.6	342.8	339.0	335.5	327.6	318.4	308.4	297.4	286.3	276.3
165°	352.3	349.9	344.9	341.9	338.9	332.2	324.2	316.1	306.7	297.7	289.7
167.5°	352.5	350.6	345.5	342.6	340.4	334.6	328.1	322.0	314.7	307.6	300.9
170°	352.0	350.3	345.3	342.6	340.9	336.2	330.5	325.2	319.5	313.4	308.1
172.5°	350.1	348.4	343.7	341.5	340.6	336.5	331.9	327.8	323.0	318.5	314.3
175°	345.3	343.9	339.9	338.6	338.9	336.2	332.9	330.5	327.5	324.8	322.5
177.5°	338.2	337.4	334.5	334.5	335.5	333.9	332.9	331.8	330.5	329.7	328.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8	7419.8
2.5°	7337.8	7336.6	7362.7	7380.3	7372.2	7364.2	7372.2	7380.3	7362.7	7336.6	7337.8
5°	7067.1	7075.4	7114.0	7143.6	7146.0	7148.3	7146.0	7143.6	7114.0	7075.4	7067.1
7.5°	6521.8	6532.7	6575.5	6606.4	6601.8	6597.2	6601.8	6606.4	6575.5	6532.7	6521.8
10°	6066.4	6072.4	6086.7	6093.3	6077.3	6061.2	6077.3	6093.3	6086.7	6072.4	6066.4
12.5°	5482.7	5478.0	5499.4	5517.1	5523.9	5530.7	5523.9	5517.1	5499.4	5478.0	5482.7
15°	4570.6	4555.2	4583.7	4605.0	4604.4	4603.8	4604.4	4605.0	4583.7	4555.2	4570.6
17.5°	3725.2	3712.7	3718.0	3721.6	3719.8	3718.0	3719.8	3721.6	3718.0	3712.7	3725.2
20°	3185.8	3170.9	3166.8	3164.4	3167.4	3170.4	3167.4	3164.4	3166.8	3170.9	3185.8
22.5°	2742.1	2732.5	2722.1	2715.4	2719.3	2723.2	2719.3	2715.4	2722.1	2732.5	2742.1
25°	2135.7	2134.5	2148.8	2156.4	2143.9	2131.4	2143.9	2156.4	2148.8	2134.5	2135.7
27.5°	1752.8	1746.5	1748.1	1749.8	1752.2	1754.6	1752.2	1749.8	1748.1	1746.5	1752.8
30°	1541.9	1535.3	1535.9	1534.6	1527.5	1520.3	1527.5	1534.6	1535.9	1535.3	1541.9
32.5°	1371.3	1361.2	1358.0	1353.8	1346.7	1339.5	1346.7	1353.8	1358.0	1361.2	1371.3
35°	1136.4	1125.4	1116.5	1109.4	1107.6	1105.8	1107.6	1109.4	1116.5	1125.4	1136.4
37.5°	922.7	911.8	899.2	888.6	883.9	879.3	883.9	888.6	899.2	911.8	922.7
40°	785.2	774.5	759.0	745.8	739.3	732.8	739.3	745.8	759.0	774.5	785.2
42.5°	651.5	640.8	625.3	611.3	601.4	591.6	601.4	611.3	625.3	640.8	651.5
45°	461.6	455.1	437.2	410.7	357.8	304.9	357.8	410.7	437.2	455.1	461.6
47.5°	295.3	286.2	239.3	193.1	149.1	105.1	149.1	193.1	239.3	286.2	295.3
50°	211.9	203.2	144.4	95.2	75.0	54.8	75.0	95.2	144.4	203.2	211.9
52.5°	151.2	147.4	96.6	55.9	45.2	34.5	45.2	55.9	96.6	147.4	151.2
55°	72.1	70.9	44.1	23.0	18.9	14.7	18.9	23.0	44.1	70.9	72.1
57.5°	27.6	27.1	17.6	9.9	7.8	5.6	7.8	9.9	17.6	27.1	27.6
60°	12.6	12.3	7.6	3.7	2.5	1.3	2.5	3.7	7.6	12.3	12.6
62.5°	6.1	6.0	3.7	1.7	1.0	0.3	1.0	1.7	3.7	6.0	6.1
65°	1.0	1.0	0.4	0.0	0.0	0.0	0.0	0.4	1.0	1.0	1.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.5	2.0	2.5	2.7	3.0	2.9	3.0	2.7	2.5	2.0	1.5
90°	7.7	10.0	12.4	13.7	15.1	14.4	15.1	13.7	12.4	10.0	7.7
92.5°	15.5	19.4	22.3	24.7	25.8	25.7	25.8	24.7	22.3	19.4	15.5
95°	31.1	35.8	40.5	43.9	45.9	45.2	45.9	43.9	40.5	35.8	31.1
97.5°	48.0	54.3	59.5	62.7	64.7	66.0	64.7	62.7	59.5	54.3	48.0
100°	59.3	65.3	71.3	75.0	78.4	79.7	78.4	75.0	71.3	65.3	59.3
102.5°	68.4	76.3	82.8	86.8	89.6	91.0	89.6	86.8	82.8	76.3	68.4
105°	83.4	91.8	98.8	103.8	106.8	107.8	106.8	103.8	98.8	91.8	83.4
107.5°	98.4	107.0	113.5	119.1	122.8	124.9	122.8	119.1	113.5	107.0	98.4
110°	110.2	117.2	124.2	129.3	132.9	134.3	132.9	129.3	124.2	117.2	110.2



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	120.1	127.9	135.0	140.0	144.2	146.1	144.2	140.0	135.0	127.9	120.1
115°	134.0	144.3	150.7	155.4	158.4	160.1	158.4	155.4	150.7	144.3	134.0
117.5°	145.5	156.3	163.3	166.9	168.3	169.5	168.3	166.9	163.3	156.3	145.5
120°	152.7	162.8	170.8	175.5	177.2	177.8	177.2	175.5	170.8	162.8	152.7
122.5°	159.4	168.9	176.7	182.4	185.2	185.9	185.2	182.4	176.7	168.9	159.4
125°	168.8	177.8	185.9	191.6	194.6	196.2	194.6	191.6	185.9	177.8	168.8
127.5°	176.9	186.7	194.1	199.3	202.2	203.5	202.2	199.3	194.1	186.7	176.9
130°	181.5	191.6	198.9	204.6	207.3	208.6	207.3	204.6	198.9	191.6	181.5
132.5°	185.0	195.6	203.2	208.4	211.3	212.6	211.3	208.4	203.2	195.6	185.0
135°	189.2	200.3	208.3	213.3	216.0	217.3	216.0	213.3	208.3	200.3	189.2
137.5°	192.9	202.9	211.3	216.6	219.0	219.9	219.0	216.6	211.3	202.9	192.9
140°	195.6	204.3	212.6	217.7	220.4	220.7	220.4	217.7	212.6	204.3	195.6
142.5°	199.1	205.9	213.2	218.2	220.9	221.5	220.9	218.2	213.2	205.9	199.1
145°	205.3	209.3	214.3	219.0	221.4	222.0	221.4	219.0	214.3	209.3	205.3
147.5°	213.1	214.4	217.0	220.1	222.4	222.8	222.4	220.1	217.0	214.4	213.1
150°	219.0	218.7	219.7	221.7	223.7	223.4	223.7	221.7	219.7	218.7	219.0
152.5°	225.7	223.8	223.7	224.6	225.6	225.5	225.6	224.6	223.7	223.8	225.7
155°	237.1	233.4	231.4	230.7	230.7	230.4	230.7	230.7	231.4	233.4	237.1
157.5°	249.6	244.5	241.4	239.8	239.4	238.6	239.4	239.8	241.4	244.5	249.6
160°	258.2	252.5	249.5	246.8	245.8	244.8	245.8	246.8	249.5	252.5	258.2
162.5°	266.2	260.8	257.5	255.1	254.1	252.6	254.1	255.1	257.5	260.8	266.2
165°	279.3	273.6	269.9	267.9	266.6	265.2	266.6	267.9	269.9	273.6	279.3
167.5°	292.3	286.1	283.7	281.4	280.2	277.7	280.2	281.4	283.7	286.1	292.3
170°	300.4	294.7	293.4	291.3	289.0	286.3	289.0	291.3	293.4	294.7	300.4
172.5°	307.4	303.5	302.2	300.2	299.4	297.3	299.4	300.2	302.2	303.5	307.4
175°	317.5	314.5	314.5	314.1	313.1	311.1	313.1	314.1	314.5	314.5	317.5
177.5°	325.9	324.3	325.4	325.4	325.1	323.2	325.1	325.4	325.4	324.3	325.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	7419.8	7419.8	7419.8	7419.8
2.5°	7366.3	7390.8	7403.1	7415.5
5°	7089.1	7109.9	7127.1	7144.3
7.5°	6542.7	6557.0	6551.4	6545.8
10°	6068.8	6069.6	6065.4	6061.2
12.5°	5513.6	5532.7	5516.2	5499.7
15°	4630.1	4668.0	4641.2	4614.5
17.5°	3755.5	3778.9	3781.6	3784.4
20°	3211.4	3231.6	3235.7	3239.9
22.5°	2751.0	2759.5	2766.5	2773.5
25°	2152.3	2170.5	2193.1	2215.6
27.5°	1767.0	1777.7	1778.0	1778.4
30°	1555.5	1566.8	1571.0	1575.1
32.5°	1388.3	1400.3	1397.3	1394.4
35°	1149.5	1159.3	1159.3	1159.3
37.5°	932.0	939.2	940.3	941.3
40°	791.1	796.3	799.3	802.3
42.5°	657.4	659.9	651.9	644.0
45°	456.9	445.0	411.7	378.4
47.5°	266.5	235.8	199.2	162.6
50°	170.3	131.9	103.4	74.9
52.5°	108.2	72.4	58.1	43.9
55°	47.7	28.2	23.5	18.7
57.5°	19.2	12.2	9.6	7.0
60°	8.5	5.1	3.9	2.7
62.5°	3.8	2.0	1.2	0.5
65°	0.4	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	1.2	0.7	0.5	0.2
90°	6.0	3.7	2.3	1.0
92.5°	13.0	9.0	6.4	3.7
95°	26.1	20.8	14.7	10.4
97.5°	41.6	33.0	27.0	19.8
100°	49.9	41.5	35.8	28.1
102.5°	59.0	52.0	44.1	36.4
105°	75.3	66.6	57.6	48.9
107.5°	90.5	80.9	70.1	62.2
110°	100.1	89.7	78.4	71.3



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	109.5	98.9	87.2	80.2
115°	122.2	110.5	99.8	93.8
117.5°	134.5	122.4	111.1	106.4
120°	142.0	129.9	118.9	115.2
122.5°	148.2	136.4	126.1	124.6
125°	157.4	145.3	136.6	138.6
127.5°	164.9	153.8	148.4	152.8
130°	169.4	159.7	156.4	162.8
132.5°	173.5	165.9	164.4	173.2
135°	179.5	175.1	176.5	188.5
137.5°	186.7	185.0	189.5	204.7
140°	191.2	192.2	198.6	215.7
142.5°	197.4	199.7	208.0	226.1
145°	207.0	212.0	222.7	240.8
147.5°	217.8	224.3	237.6	256.1
150°	225.0	233.4	247.5	265.2
152.5°	233.3	242.0	256.0	274.1
155°	246.1	255.8	270.6	286.0
157.5°	259.2	269.1	283.2	296.6
160°	267.2	277.9	290.7	303.1
162.5°	276.3	286.3	297.4	308.4
165°	289.7	297.7	306.7	316.1
167.5°	300.9	307.6	314.7	322.0
170°	308.1	313.4	319.5	325.2
172.5°	314.3	318.5	323.0	327.8
175°	322.5	324.8	327.5	330.5
177.5°	328.9	329.7	330.5	331.8
180°	331.5	331.5	331.5	331.5



TEST NUMBER: P1427586

CATALOG NUMBER: SQ2W-BBN-K-025U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00