

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427601

Luminaire Tested: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427601  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6922.9 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 64.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	106	103	101	98	101	98	96	94	89	88	86	81	80	79	73	73	72	68
2	100	95	91	87	96	91	87	84	83	81	78	76	74	72	70	68	67	64
3	95	88	83	78	90	84	80	76	78	74	71	72	69	67	66	64	63	60
4	89	81	76	71	85	79	73	69	73	69	66	68	65	62	63	60	59	56
5	84	76	70	65	81	73	68	64	68	64	61	64	60	58	60	57	55	53
6	80	71	65	60	77	69	63	59	64	60	56	60	57	54	57	54	52	50
7	76	66	60	56	73	64	59	55	61	56	53	57	53	51	54	51	49	47
8	72	62	56	52	69	61	55	51	57	53	49	54	50	48	51	48	46	44
9	68	59	53	49	66	57	52	48	54	50	47	51	48	45	49	46	43	42
10	65	56	50	46	63	54	49	45	52	47	44	49	45	43	47	43	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	149931	149931	149931	149931
5°	144917	144998	144917	144998
10°	124368	124368	124368	124368
15°	96533	96309	96533	96309
20°	69670	68174	69670	68174
25°	49400	47521	49400	47521
30°	36753	35474	36753	35474
35°	28597	27279	28597	27279
40°	21163	19329	21163	19329
45°	10814	8713	10814	8713
50°	2354	1723	2354	1723
55°	659	518	659	518
60°	107	55	107	55
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 13191 cd/sqm



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	803.0	11.6
10°-20°	1583.2	22.9
20°-30°	1277.1	18.4
30°-40°	887.2	12.8
40°-50°	409.8	5.9
50°-60°	57.4	0.8
60°-70°	2.0	0.0
70°-80°	0.0	0.0
80°-90°	3.5	0.0
90°-100°	51.8	0.7
100°-110°	151.1	2.2
110°-120°	246.5	3.6
120°-130°	312.9	4.5
130°-140°	334.8	4.8
140°-150°	312.6	4.5
150°-160°	257.2	3.7
160°-170°	172.5	2.5
170°-180°	61.3	0.9
0°-30°	3663.3	52.9
0°-40°	4550.4	65.7
0°-60°	5017.6	72.5
0°-90°	5023.0	72.6
90°-120°	449.4	6.5
90°-150°	1409.7	20.4
90°-180°	1901.0	27.5
0°-180°	6922.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	9286	9286	9286	9286	9286	
5°	8942	8946	8942	8946	8942	804
15°	5775	5762	5775	5762	5775	1590
25°	2773	2668	2773	2668	2773	1298
35°	1451	1384	1451	1384	1451	908
45°	474	382	474	382	474	383
55°	23	18	23	18	23	30
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	14	2	28	2	2
95°	20	15	20	89	20	25
105°	96	154	96	212	96	102
115°	184	255	184	314	184	181
125°	272	404	272	385	272	244
135°	370	529	370	427	370	286
145°	473	610	473	436	473	296
155°	562	663	562	452	562	258
165°	621	691	621	521	621	175
175°	649	677	649	611	649	62
180°	651	651	651	651	651	



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2
2.5°	9280.8	9265.4	9249.9	9219.3	9183.6	9182.1	9214.8	9236.8	9226.7	9216.6	9226.7
5°	8941.5	8919.9	8898.3	8872.3	8844.8	8855.2	8903.5	8940.5	8943.5	8946.5	8943.5
7.5°	8192.4	8199.4	8206.4	8188.5	8162.3	8176.0	8229.6	8268.3	8262.5	8256.7	8262.5
10°	7585.9	7591.1	7596.3	7595.4	7592.4	7599.9	7617.7	7626.1	7606.0	7585.9	7606.0
12.5°	6883.1	6903.7	6924.4	6900.6	6861.9	6856.0	6882.7	6904.9	6913.4	6921.9	6913.4
15°	5775.2	5808.7	5842.2	5794.7	5720.4	5701.0	5736.7	5763.3	5762.6	5761.8	5762.6
17.5°	4736.3	4732.9	4729.5	4700.2	4662.2	4646.6	4653.3	4657.8	4655.5	4653.3	4655.5
20°	4054.9	4049.7	4044.5	4019.2	3987.2	3968.6	3963.4	3960.4	3964.1	3967.8	3964.1
22.5°	3471.2	3462.4	3453.6	3443.0	3431.9	3419.8	3406.9	3398.4	3403.3	3408.2	3403.3
25°	2773.0	2744.7	2716.4	2693.8	2672.9	2671.4	2689.3	2698.8	2683.2	2667.5	2683.2
27.5°	2225.7	2225.3	2224.8	2211.5	2193.8	2185.9	2187.8	2190.0	2193.0	2196.0	2193.0
30°	1971.4	1966.2	1961.0	1946.8	1929.7	1921.5	1922.3	1920.6	1911.7	1902.8	1911.7
32.5°	1745.1	1748.8	1752.6	1737.5	1716.3	1703.6	1699.6	1694.4	1685.4	1676.5	1685.4
35°	1450.9	1450.9	1450.9	1438.6	1422.3	1408.5	1397.4	1388.4	1386.2	1384.0	1386.2
37.5°	1178.1	1176.8	1175.5	1166.4	1154.8	1141.1	1125.4	1112.1	1106.3	1100.5	1106.3
40°	1004.1	1000.4	996.7	990.1	982.7	969.3	950.0	933.4	925.3	917.1	925.3
42.5°	806.0	815.9	825.9	822.8	815.4	802.0	782.6	765.0	752.7	740.4	752.7
45°	473.6	515.2	556.9	571.8	577.7	569.5	547.2	513.9	447.8	381.6	447.8
47.5°	203.5	249.3	295.1	333.6	369.6	358.2	299.4	241.6	186.6	131.5	186.6
50°	93.7	129.4	165.1	213.1	265.2	254.4	180.7	119.2	93.9	68.6	93.9
52.5°	54.9	72.7	90.6	135.4	189.3	184.5	120.9	70.0	56.6	43.2	56.6
55°	23.4	29.4	35.3	59.7	90.2	88.7	55.2	28.8	23.6	18.4	23.6
57.5°	8.7	12.0	15.2	24.0	34.5	33.9	22.0	12.4	9.7	7.0	9.7
60°	3.3	4.8	6.3	10.6	15.8	15.4	9.5	4.6	3.2	1.7	3.2
62.5°	0.7	1.6	2.5	4.8	7.6	7.5	4.6	2.1	1.2	0.3	1.2
65°	0.0	0.0	0.0	0.6	1.3	1.3	0.6	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	0.9	1.6	2.1	2.5	2.6	2.6	2.8	2.9	2.9	2.9
90°	2.0	4.6	7.9	10.5	12.5	13.2	13.2	13.8	14.5	14.5	14.5
92.5°	7.2	11.4	11.6	11.6	14.1	15.3	16.3	16.4	17.1	17.1	17.1
95°	20.4	22.4	33.5	32.9	22.4	17.8	15.1	15.1	15.1	15.1	15.1
97.5°	38.9	41.8	43.7	58.5	61.8	59.7	48.7	40.9	36.6	34.6	36.6
100°	55.2	56.5	60.5	61.1	77.6	93.4	85.5	75.6	72.3	70.4	72.3
102.5°	71.5	72.3	78.4	81.1	85.0	93.9	121.2	118.2	116.0	115.6	116.0
105°	96.0	96.7	107.8	113.1	115.7	115.7	115.1	128.2	149.3	153.9	149.3
107.5°	122.2	125.2	138.3	152.4	155.4	156.2	152.8	150.8	150.0	150.6	150.0
110°	140.1	144.7	160.4	178.2	182.8	184.1	182.8	180.8	179.5	179.5	179.5



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	157.4	164.1	182.0	202.4	210.1	214.1	211.2	209.8	208.4	209.5	208.4
115°	184.1	194.0	217.6	238.7	254.5	256.4	255.8	255.8	255.1	255.1	255.1
117.5°	208.8	224.6	251.2	275.6	293.9	299.2	301.8	301.0	300.2	301.5	300.2
120°	226.2	244.6	274.8	302.5	320.2	328.1	330.7	329.4	330.7	329.4	330.7
122.5°	244.6	267.2	296.9	325.6	346.5	355.5	358.6	358.9	359.1	358.4	359.1
125°	272.2	299.8	334.7	364.3	386.0	396.5	399.1	399.8	401.1	404.4	401.1
127.5°	300.1	331.4	369.7	398.2	420.4	433.2	437.3	438.7	441.5	442.9	441.5
130°	319.6	355.1	393.9	420.8	442.5	456.3	463.6	465.5	468.8	468.2	468.8
132.5°	340.1	377.2	416.5	444.5	464.6	479.5	485.6	491.3	492.5	493.4	492.5
135°	370.2	410.3	449.7	477.4	496.4	510.9	518.8	524.0	527.3	529.3	527.3
137.5°	401.9	444.2	482.1	506.7	525.9	538.4	547.3	552.8	556.3	557.8	556.3
140°	423.4	464.2	501.0	526.7	543.8	556.3	564.2	570.7	574.7	574.7	574.7
142.5°	444.0	484.2	520.0	545.6	560.6	572.0	580.5	585.5	589.9	589.9	589.9
145°	472.8	512.9	545.7	571.4	583.9	594.4	603.6	607.6	610.2	610.2	610.2
147.5°	502.9	538.4	568.4	593.0	603.5	615.8	623.1	626.2	629.5	628.1	629.5
150°	520.8	553.6	582.6	605.6	616.1	627.9	635.2	637.8	641.1	639.1	641.1
152.5°	538.1	569.4	595.7	617.2	626.1	637.9	646.2	648.8	651.1	649.6	651.1
155°	561.5	589.1	613.5	633.2	641.1	652.3	660.2	663.4	666.1	662.8	666.1
157.5°	582.4	606.2	627.4	645.6	654.0	663.6	670.9	675.0	677.6	676.2	677.6
160°	595.1	616.8	635.8	652.9	660.8	669.4	677.3	681.9	684.5	682.5	684.5
162.5°	605.6	625.2	643.2	658.7	665.5	673.0	682.5	686.6	689.2	686.7	689.2
165°	620.7	636.5	652.3	665.4	671.3	677.3	687.1	691.7	693.7	691.1	693.7
167.5°	632.1	644.2	657.0	668.3	672.6	678.4	688.3	692.1	694.6	691.3	694.6
170°	638.5	649.0	660.2	669.4	672.6	677.9	687.8	691.1	693.0	689.7	693.0
172.5°	643.7	651.6	660.7	668.8	670.5	674.8	684.1	687.4	688.8	686.1	688.8
175°	649.0	653.6	660.2	665.4	664.8	667.4	675.3	677.9	680.5	676.6	680.5
177.5°	651.5	653.6	655.7	658.8	656.7	656.7	662.5	664.1	664.6	662.5	664.6
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2
2.5°	9236.8	9214.8	9182.1	9183.6	9219.3	9249.9	9265.4	9280.8	9265.4	9249.9	9219.3
5°	8940.5	8903.5	8855.2	8844.8	8872.3	8898.3	8919.9	8941.5	8919.9	8898.3	8872.3
7.5°	8268.3	8229.6	8176.0	8162.3	8188.5	8206.4	8199.4	8192.4	8199.4	8206.4	8188.5
10°	7626.1	7617.7	7599.9	7592.4	7595.4	7596.3	7591.1	7585.9	7591.1	7596.3	7595.4
12.5°	6904.9	6882.7	6856.0	6861.9	6900.6	6924.4	6903.7	6883.1	6903.7	6924.4	6900.6
15°	5763.3	5736.7	5701.0	5720.4	5794.7	5842.2	5808.7	5775.2	5808.7	5842.2	5794.7
17.5°	4657.8	4653.3	4646.6	4662.2	4700.2	4729.5	4732.9	4736.3	4732.9	4729.5	4700.2
20°	3960.4	3963.4	3968.6	3987.2	4019.2	4044.5	4049.7	4054.9	4049.7	4044.5	4019.2
22.5°	3398.4	3406.9	3419.8	3431.9	3443.0	3453.6	3462.4	3471.2	3462.4	3453.6	3443.0
25°	2698.8	2689.3	2671.4	2672.9	2693.8	2716.4	2744.7	2773.0	2744.7	2716.4	2693.8
27.5°	2190.0	2187.8	2185.9	2193.8	2211.5	2224.8	2225.3	2225.7	2225.3	2224.8	2211.5
30°	1920.6	1922.3	1921.5	1929.7	1946.8	1961.0	1966.2	1971.4	1966.2	1961.0	1946.8
32.5°	1694.4	1699.6	1703.6	1716.3	1737.5	1752.6	1748.8	1745.1	1748.8	1752.6	1737.5
35°	1388.4	1397.4	1408.5	1422.3	1438.6	1450.9	1450.9	1450.9	1450.9	1450.9	1438.6
37.5°	1112.1	1125.4	1141.1	1154.8	1166.4	1175.5	1176.8	1178.1	1176.8	1175.5	1166.4
40°	933.4	950.0	969.3	982.7	990.1	996.7	1000.4	1004.1	1000.4	996.7	990.1
42.5°	765.0	782.6	802.0	815.4	822.8	825.9	815.9	806.0	815.9	825.9	822.8
45°	513.9	547.2	569.5	577.7	571.8	556.9	515.2	473.6	515.2	556.9	571.8
47.5°	241.6	299.4	358.2	369.6	333.6	295.1	249.3	203.5	249.3	295.1	333.6
50°	119.2	180.7	254.4	265.2	213.1	165.1	129.4	93.7	129.4	165.1	213.1
52.5°	70.0	120.9	184.5	189.3	135.4	90.6	72.7	54.9	72.7	90.6	135.4
55°	28.8	55.2	88.7	90.2	59.7	35.3	29.4	23.4	29.4	35.3	59.7
57.5°	12.4	22.0	33.9	34.5	24.0	15.2	12.0	8.7	12.0	15.2	24.0
60°	4.6	9.5	15.4	15.8	10.6	6.3	4.8	3.3	4.8	6.3	10.6
62.5°	2.1	4.6	7.5	7.6	4.8	2.5	1.6	0.7	1.6	2.5	4.8
65°	0.0	0.6	1.3	1.3	0.6	0.0	0.0	0.0	0.0	0.0	0.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.8	2.6	2.6	2.5	2.1	1.6	0.9	0.4	0.9	1.4	2.4
90°	13.8	13.2	13.2	12.5	10.5	7.9	4.6	2.0	4.6	7.2	11.8
92.5°	16.4	16.3	15.3	14.1	11.6	11.6	11.4	7.2	12.5	17.8	25.5
95°	15.1	15.1	17.8	22.4	32.9	33.5	22.4	20.4	28.9	40.8	51.3
97.5°	40.9	48.7	59.7	61.8	58.5	43.7	41.8	38.9	53.0	64.7	81.7
100°	75.6	85.5	93.4	77.6	61.1	60.5	56.5	55.2	70.4	81.5	98.0
102.5°	118.2	121.2	93.9	85.0	81.1	78.4	72.3	71.5	86.7	102.0	115.9
105°	128.2	115.1	115.7	115.7	113.1	107.8	96.7	96.0	113.1	130.8	147.9
107.5°	150.8	152.8	156.2	155.4	152.4	138.3	125.2	122.2	137.6	158.9	177.7
110°	180.8	182.8	184.1	182.8	178.2	160.4	144.7	140.1	153.9	176.2	196.6



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	209.8	211.2	214.1	210.1	202.4	182.0	164.1	157.4	171.2	194.1	215.0
115°	255.8	255.8	256.4	254.5	238.7	217.6	194.0	184.1	195.9	217.0	240.0
117.5°	301.0	301.8	299.2	293.9	275.6	251.2	224.6	208.8	218.2	240.4	264.1
120°	329.4	330.7	328.1	320.2	302.5	274.8	244.6	226.2	233.4	255.1	278.8
122.5°	358.9	358.6	355.5	346.5	325.6	296.9	267.2	244.6	247.6	267.7	290.9
125°	399.8	399.1	396.5	386.0	364.3	334.7	299.8	272.2	268.3	285.4	309.0
127.5°	438.7	437.3	433.2	420.4	398.2	369.7	331.4	300.1	291.3	302.1	323.8
130°	465.5	463.6	456.3	442.5	420.8	393.9	355.1	319.6	307.1	313.6	332.7
132.5°	491.3	485.6	479.5	464.6	444.5	416.5	377.2	340.1	322.8	325.7	340.6
135°	524.0	518.8	510.9	496.4	477.4	449.7	410.3	370.2	346.5	343.9	352.4
137.5°	552.8	547.3	538.4	525.9	506.7	482.1	444.2	401.9	372.0	363.2	366.5
140°	570.7	564.2	556.3	543.8	526.7	501.0	464.2	423.4	389.9	377.4	375.4
142.5°	585.5	580.5	572.0	560.6	545.6	520.0	484.2	444.0	408.3	392.1	387.5
145°	607.6	603.6	594.4	583.9	571.4	545.7	512.9	472.8	437.3	416.2	406.4
147.5°	626.2	623.1	615.8	603.5	593.0	568.4	538.4	502.9	466.4	440.4	427.7
150°	637.8	635.2	627.9	616.1	605.6	582.6	553.6	520.8	485.9	458.3	441.9
152.5°	648.8	646.2	637.9	626.1	617.2	595.7	569.4	538.1	502.7	475.1	458.2
155°	663.4	660.2	652.3	641.1	633.2	613.5	589.1	561.5	531.3	502.3	483.3
157.5°	675.0	670.9	663.6	654.0	645.6	627.4	606.2	582.4	556.0	528.4	508.9
160°	681.9	677.3	669.4	660.8	652.9	635.8	616.8	595.1	570.7	545.7	524.7
162.5°	686.6	682.5	673.0	665.5	658.7	643.2	625.2	605.6	583.9	562.1	542.6
165°	691.7	687.1	677.3	671.3	665.4	652.3	636.5	620.7	602.3	584.5	568.8
167.5°	692.1	688.3	678.4	672.6	668.3	657.0	644.2	632.1	617.8	603.9	590.7
170°	691.1	687.8	677.9	672.6	669.4	660.2	649.0	638.5	627.3	615.4	604.9
172.5°	687.4	684.1	674.8	670.5	668.8	660.7	651.6	643.7	634.1	625.4	617.0
175°	677.9	675.3	667.4	664.8	665.4	660.2	653.6	649.0	643.1	637.8	633.2
177.5°	664.1	662.5	656.7	656.7	658.8	655.7	653.6	651.5	648.8	647.3	645.7
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2
2.5°	9183.6	9182.1	9214.8	9236.8	9226.7	9216.6	9226.7	9236.8	9214.8	9182.1	9183.6
5°	8844.8	8855.2	8903.5	8940.5	8943.5	8946.5	8943.5	8940.5	8903.5	8855.2	8844.8
7.5°	8162.3	8176.0	8229.6	8268.3	8262.5	8256.7	8262.5	8268.3	8229.6	8176.0	8162.3
10°	7592.4	7599.9	7617.7	7626.1	7606.0	7585.9	7606.0	7626.1	7617.7	7599.9	7592.4
12.5°	6861.9	6856.0	6882.7	6904.9	6913.4	6921.9	6913.4	6904.9	6882.7	6856.0	6861.9
15°	5720.4	5701.0	5736.7	5763.3	5762.6	5761.8	5762.6	5763.3	5736.7	5701.0	5720.4
17.5°	4662.2	4646.6	4653.3	4657.8	4655.5	4653.3	4655.5	4657.8	4653.3	4646.6	4662.2
20°	3987.2	3968.6	3963.4	3960.4	3964.1	3967.8	3964.1	3960.4	3963.4	3968.6	3987.2
22.5°	3431.9	3419.8	3406.9	3398.4	3403.3	3408.2	3403.3	3398.4	3406.9	3419.8	3431.9
25°	2672.9	2671.4	2689.3	2698.8	2683.2	2667.5	2683.2	2698.8	2689.3	2671.4	2672.9
27.5°	2193.8	2185.9	2187.8	2190.0	2193.0	2196.0	2193.0	2190.0	2187.8	2185.9	2193.8
30°	1929.7	1921.5	1922.3	1920.6	1911.7	1902.8	1911.7	1920.6	1922.3	1921.5	1929.7
32.5°	1716.3	1703.6	1699.6	1694.4	1685.4	1676.5	1685.4	1694.4	1699.6	1703.6	1716.3
35°	1422.3	1408.5	1397.4	1388.4	1386.2	1384.0	1386.2	1388.4	1397.4	1408.5	1422.3
37.5°	1154.8	1141.1	1125.4	1112.1	1106.3	1100.5	1106.3	1112.1	1125.4	1141.1	1154.8
40°	982.7	969.3	950.0	933.4	925.3	917.1	925.3	933.4	950.0	969.3	982.7
42.5°	815.4	802.0	782.6	765.0	752.7	740.4	752.7	765.0	782.6	802.0	815.4
45°	577.7	569.5	547.2	513.9	447.8	381.6	447.8	513.9	547.2	569.5	577.7
47.5°	369.6	358.2	299.4	241.6	186.6	131.5	186.6	241.6	299.4	358.2	369.6
50°	265.2	254.4	180.7	119.2	93.9	68.6	93.9	119.2	180.7	254.4	265.2
52.5°	189.3	184.5	120.9	70.0	56.6	43.2	56.6	70.0	120.9	184.5	189.3
55°	90.2	88.7	55.2	28.8	23.6	18.4	23.6	28.8	55.2	88.7	90.2
57.5°	34.5	33.9	22.0	12.4	9.7	7.0	9.7	12.4	22.0	33.9	34.5
60°	15.8	15.4	9.5	4.6	3.2	1.7	3.2	4.6	9.5	15.4	15.8
62.5°	7.6	7.5	4.6	2.1	1.2	0.3	1.2	2.1	4.6	7.5	7.6
65°	1.3	1.3	0.6	0.0	0.0	0.0	0.0	0.6	1.3	1.3	1.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	3.0	3.9	4.9	5.4	5.9	5.7	5.9	5.4	4.9	3.9	3.0
90°	15.1	19.7	24.3	27.0	29.6	28.3	29.6	27.0	24.3	19.7	15.1
92.5°	30.4	38.1	43.8	48.5	50.6	50.4	50.6	48.5	43.8	38.1	30.4
95°	61.1	70.4	79.6	86.1	90.1	88.8	90.1	86.1	79.6	70.4	61.1
97.5°	94.3	106.7	116.9	123.1	127.0	129.7	127.0	123.1	116.9	106.7	94.3
100°	116.4	128.2	140.1	147.3	153.9	156.5	153.9	147.3	140.1	128.2	116.4
102.5°	134.3	149.8	162.7	170.4	176.0	178.6	176.0	170.4	162.7	149.8	134.3
105°	163.7	180.2	194.0	203.8	209.8	211.7	209.8	203.8	194.0	180.2	163.7
107.5°	193.2	210.1	222.9	233.8	241.0	245.3	241.0	233.8	222.9	210.1	193.2
110°	216.3	230.1	243.9	253.8	261.0	263.7	261.0	253.8	243.9	230.1	216.3



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	235.8	251.2	265.0	274.8	283.1	286.8	283.1	274.8	265.0	251.2	235.8
115°	263.0	283.4	295.9	305.1	311.0	314.3	311.0	305.1	295.9	283.4	263.0
117.5°	285.6	306.9	320.6	327.7	330.5	332.8	330.5	327.7	320.6	306.9	285.6
120°	299.8	319.6	335.3	344.5	347.8	349.1	347.8	344.5	335.3	319.6	299.8
122.5°	313.0	331.7	346.9	358.2	363.6	364.9	363.6	358.2	346.9	331.7	313.0
125°	331.4	349.1	364.9	376.1	382.0	385.3	382.0	376.1	364.9	349.1	331.4
127.5°	347.4	366.6	381.1	391.2	397.0	399.6	397.0	391.2	381.1	366.6	347.4
130°	356.4	376.1	390.6	401.7	407.0	409.6	407.0	401.7	390.6	376.1	356.4
132.5°	363.2	384.0	399.0	409.1	414.9	417.5	414.9	409.1	399.0	384.0	363.2
135°	371.5	393.2	409.0	418.8	424.1	426.7	424.1	418.8	409.0	393.2	371.5
137.5°	378.7	398.5	414.9	425.3	430.0	431.7	430.0	425.3	414.9	398.5	378.7
140°	384.0	401.1	417.5	427.4	432.7	433.3	432.7	427.4	417.5	401.1	384.0
142.5°	390.8	404.2	418.6	428.4	433.7	434.9	433.7	428.4	418.6	404.2	390.8
145°	403.1	411.0	420.8	430.0	434.6	435.9	434.6	430.0	420.8	411.0	403.1
147.5°	418.4	420.9	426.1	432.1	436.6	437.5	436.6	432.1	426.1	420.9	418.4
150°	430.0	429.4	431.3	435.3	439.2	438.6	439.2	435.3	431.3	429.4	430.0
152.5°	443.2	439.4	439.2	441.1	442.9	442.8	442.9	441.1	439.2	439.4	443.2
155°	465.5	458.3	454.3	453.0	453.0	452.4	453.0	453.0	454.3	458.3	465.5
157.5°	490.1	480.0	474.1	470.9	470.0	468.6	470.0	470.9	474.1	480.0	490.1
160°	507.0	495.8	489.9	484.6	482.6	480.7	482.6	484.6	489.9	495.8	507.0
162.5°	522.7	512.1	505.6	500.9	498.9	495.9	498.9	500.9	505.6	512.1	522.7
165°	548.4	537.2	530.0	526.0	523.4	520.8	523.4	526.0	530.0	537.2	548.4
167.5°	574.0	561.8	557.1	552.6	550.1	545.4	550.1	552.6	557.1	561.8	574.0
170°	589.8	578.6	576.0	572.0	567.4	562.2	567.4	572.0	576.0	578.6	589.8
172.5°	603.5	596.0	593.4	589.4	588.0	583.8	588.0	589.4	593.4	596.0	603.5
175°	623.3	617.4	617.4	616.8	614.8	610.8	614.8	616.8	617.4	617.4	623.3
177.5°	639.9	636.7	638.9	638.9	638.3	634.6	638.3	638.9	638.9	636.7	639.9
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	9286.2	9286.2	9286.2	9286.2
2.5°	9219.3	9249.9	9265.4	9280.8
5°	8872.3	8898.3	8919.9	8941.5
7.5°	8188.5	8206.4	8199.4	8192.4
10°	7595.4	7596.3	7591.1	7585.9
12.5°	6900.6	6924.4	6903.7	6883.1
15°	5794.7	5842.2	5808.7	5775.2
17.5°	4700.2	4729.5	4732.9	4736.3
20°	4019.2	4044.5	4049.7	4054.9
22.5°	3443.0	3453.6	3462.4	3471.2
25°	2693.8	2716.4	2744.7	2773.0
27.5°	2211.5	2224.8	2225.3	2225.7
30°	1946.8	1961.0	1966.2	1971.4
32.5°	1737.5	1752.6	1748.8	1745.1
35°	1438.6	1450.9	1450.9	1450.9
37.5°	1166.4	1175.5	1176.8	1178.1
40°	990.1	996.7	1000.4	1004.1
42.5°	822.8	825.9	815.9	806.0
45°	571.8	556.9	515.2	473.6
47.5°	333.6	295.1	249.3	203.5
50°	213.1	165.1	129.4	93.7
52.5°	135.4	90.6	72.7	54.9
55°	59.7	35.3	29.4	23.4
57.5°	24.0	15.2	12.0	8.7
60°	10.6	6.3	4.8	3.3
62.5°	4.8	2.5	1.6	0.7
65°	0.6	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	2.4	1.4	0.9	0.4
90°	11.8	7.2	4.6	2.0
92.5°	25.5	17.8	12.5	7.2
95°	51.3	40.8	28.9	20.4
97.5°	81.7	64.7	53.0	38.9
100°	98.0	81.5	70.4	55.2
102.5°	115.9	102.0	86.7	71.5
105°	147.9	130.8	113.1	96.0
107.5°	177.7	158.9	137.6	122.2
110°	196.6	176.2	153.9	140.1



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	215.0	194.1	171.2	157.4
115°	240.0	217.0	195.9	184.1
117.5°	264.1	240.4	218.2	208.8
120°	278.8	255.1	233.4	226.2
122.5°	290.9	267.7	247.6	244.6
125°	309.0	285.4	268.3	272.2
127.5°	323.8	302.1	291.3	300.1
130°	332.7	313.6	307.1	319.6
132.5°	340.6	325.7	322.8	340.1
135°	352.4	343.9	346.5	370.2
137.5°	366.5	363.2	372.0	401.9
140°	375.4	377.4	389.9	423.4
142.5°	387.5	392.1	408.3	444.0
145°	406.4	416.2	437.3	472.8
147.5°	427.7	440.4	466.4	502.9
150°	441.9	458.3	485.9	520.8
152.5°	458.2	475.1	502.7	538.1
155°	483.3	502.3	531.3	561.5
157.5°	508.9	528.4	556.0	582.4
160°	524.7	545.7	570.7	595.1
162.5°	542.6	562.1	583.9	605.6
165°	568.8	584.5	602.3	620.7
167.5°	590.7	603.9	617.8	632.1
170°	604.9	615.4	627.3	638.5
172.5°	617.0	625.4	634.1	643.7
175°	633.2	637.8	643.1	649.0
177.5°	645.7	647.3	648.8	651.5
180°	650.9	650.9	650.9	650.9



TEST NUMBER: P1427601

CATALOG NUMBER: SQ2W-BBN-K-050U-125D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00