

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427625

Luminaire Tested: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427625  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8891.4 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57				
1	102	99	96	93	95	92	90	88	80	79	77	69	68	67	59	58	58	53				
2	96	90	85	81	89	85	81	77	74	71	69	65	63	61	56	55	54	50				
3	90	82	77	72	84	78	73	69	69	65	62	61	58	56	53	51	50	47				
4	84	76	70	65	79	72	66	62	64	60	57	57	54	52	50	48	47	44				
5	79	70	64	59	74	66	61	57	60	55	52	53	50	48	48	45	44	41				
6	74	65	58	54	70	62	56	52	56	51	48	50	47	45	45	43	41	39				
7	70	60	54	49	66	58	52	48	52	48	45	47	44	42	43	40	39	36				
8	66	56	50	46	63	54	48	44	49	45	42	45	41	39	41	38	36	34				
9	63	53	47	43	59	51	45	41	46	42	39	43	39	37	39	36	34	33				
10	60	50	44	40	57	48	42	39	44	40	37	40	37	35	37	34	33	31				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	149931	149931	149931	149931
5°	144917	144998	144917	144998
10°	124368	124368	124368	124368
15°	96533	96309	96533	96309
20°	69670	68174	69670	68174
25°	49400	47521	49400	47521
30°	36753	35474	36753	35474
35°	28597	27279	28597	27279
40°	21163	19329	21163	19329
45°	10814	8713	10814	8713
50°	2354	1723	2354	1723
55°	659	518	659	518
60°	107	55	107	55
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 13191 cd/sqm



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	803.0	9.0
10°-20°	1583.2	17.8
20°-30°	1277.1	14.4
30°-40°	887.2	10.0
40°-50°	409.8	4.6
50°-60°	57.4	0.6
60°-70°	2.0	0.0
70°-80°	0.0	0.0
80°-90°	7.0	0.1
90°-100°	105.4	1.2
100°-110°	307.3	3.5
110°-120°	501.5	5.6
120°-130°	636.4	7.2
130°-140°	681.0	7.7
140°-150°	635.9	7.2
150°-160°	523.2	5.9
160°-170°	350.9	3.9
170°-180°	124.6	1.4
0°-30°	3663.3	41.2
0°-40°	4550.4	51.2
0°-60°	5017.6	56.4
0°-90°	5026.6	56.5
90°-120°	914.2	10.3
90°-150°	2867.5	32.3
90°-180°	3866.0	43.5
0°-180°	8891.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	9286	9286	9286	9286	9286	
5°	8942	8946	8942	8946	8942	804
15°	5775	5762	5775	5762	5775	1590
25°	2773	2668	2773	2668	2773	1298
35°	1451	1384	1451	1384	1451	908
45°	474	382	474	382	474	383
55°	23	18	23	18	23	30
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	29	4	58	4	3
95°	42	31	42	181	42	50
105°	195	313	195	431	195	208
115°	374	519	374	639	374	369
125°	554	823	554	784	554	495
135°	753	1077	753	868	753	582
145°	962	1241	962	887	962	602
155°	1142	1348	1142	920	1142	525
165°	1263	1406	1263	1059	1263	355
175°	1320	1376	1320	1243	1320	125
180°	1324	1324	1324	1324	1324	



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2
2.5°	9280.8	9265.4	9249.9	9219.3	9183.6	9182.1	9214.8	9236.8	9226.7	9216.6	9226.7
5°	8941.5	8919.9	8898.3	8872.3	8844.8	8855.2	8903.5	8940.5	8943.5	8946.5	8943.5
7.5°	8192.4	8199.4	8206.4	8188.5	8162.3	8176.0	8229.6	8268.3	8262.5	8256.7	8262.5
10°	7585.9	7591.1	7596.3	7595.4	7592.4	7599.9	7617.7	7626.1	7606.0	7585.9	7606.0
12.5°	6883.1	6903.7	6924.4	6900.6	6861.9	6856.0	6882.7	6904.9	6913.4	6921.9	6913.4
15°	5775.2	5808.7	5842.2	5794.7	5720.4	5701.0	5736.7	5763.3	5762.6	5761.8	5762.6
17.5°	4736.3	4732.9	4729.5	4700.2	4662.2	4646.6	4653.3	4657.8	4655.5	4653.3	4655.5
20°	4054.9	4049.7	4044.5	4019.2	3987.2	3968.6	3963.4	3960.4	3964.1	3967.8	3964.1
22.5°	3471.2	3462.4	3453.6	3443.0	3431.9	3419.8	3406.9	3398.4	3403.3	3408.2	3403.3
25°	2773.0	2744.7	2716.4	2693.8	2672.9	2671.4	2689.3	2698.8	2683.2	2667.5	2683.2
27.5°	2225.7	2225.3	2224.8	2211.5	2193.8	2185.9	2187.8	2190.0	2193.0	2196.0	2193.0
30°	1971.4	1966.2	1961.0	1946.8	1929.7	1921.5	1922.3	1920.6	1911.7	1902.8	1911.7
32.5°	1745.1	1748.8	1752.6	1737.5	1716.3	1703.6	1699.6	1694.4	1685.4	1676.5	1685.4
35°	1450.9	1450.9	1450.9	1438.6	1422.3	1408.5	1397.4	1388.4	1386.2	1384.0	1386.2
37.5°	1178.1	1176.8	1175.5	1166.4	1154.8	1141.1	1125.4	1112.1	1106.3	1100.5	1106.3
40°	1004.1	1000.4	996.7	990.1	982.7	969.3	950.0	933.4	925.3	917.1	925.3
42.5°	806.0	815.9	825.9	822.8	815.4	802.0	782.6	765.0	752.7	740.4	752.7
45°	473.6	515.2	556.9	571.8	577.7	569.5	547.2	513.9	447.8	381.6	447.8
47.5°	203.5	249.3	295.1	333.6	369.6	358.2	299.4	241.6	186.6	131.5	186.6
50°	93.7	129.4	165.1	213.1	265.2	254.4	180.7	119.2	93.9	68.6	93.9
52.5°	54.9	72.7	90.6	135.4	189.3	184.5	120.9	70.0	56.6	43.2	56.6
55°	23.4	29.4	35.3	59.7	90.2	88.7	55.2	28.8	23.6	18.4	23.6
57.5°	8.7	12.0	15.2	24.0	34.5	33.9	22.0	12.4	9.7	7.0	9.7
60°	3.3	4.8	6.3	10.6	15.8	15.4	9.5	4.6	3.2	1.7	3.2
62.5°	0.7	1.6	2.5	4.8	7.6	7.5	4.6	2.1	1.2	0.3	1.2
65°	0.0	0.0	0.0	0.6	1.3	1.3	0.6	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.8	1.9	3.2	4.3	5.1	5.4	5.4	5.6	5.9	5.9	5.9
90°	4.0	9.4	16.1	21.4	25.4	26.8	26.8	28.1	29.4	29.4	29.4
92.5°	14.7	23.3	23.5	23.5	28.6	31.0	33.2	33.4	34.8	34.8	34.8
95°	41.5	45.5	68.2	66.9	45.5	36.1	30.8	30.8	30.8	30.8	30.8
97.5°	79.2	85.1	88.8	119.0	125.7	121.4	99.0	83.2	74.4	70.4	74.4
100°	112.4	115.0	123.1	124.4	157.8	189.9	173.9	153.8	147.1	143.1	147.1
102.5°	145.5	147.1	159.4	165.1	172.8	191.0	246.6	240.5	235.9	235.1	235.9
105°	195.3	196.6	219.4	230.1	235.4	235.4	234.1	260.8	303.6	313.0	303.6
107.5°	248.5	254.7	281.4	310.0	316.2	317.8	310.8	306.8	305.2	306.3	305.2
110°	284.9	294.3	326.4	362.5	371.8	374.5	371.8	367.8	365.1	365.1	365.1



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	320.2	333.9	370.2	411.7	427.5	435.5	429.6	426.7	424.0	426.1	424.0
115°	374.5	394.6	442.7	485.5	517.6	521.6	520.3	520.3	519.0	519.0	519.0
117.5°	424.8	456.9	510.9	560.7	597.9	608.6	613.9	612.3	610.7	613.4	610.7
120°	460.1	497.6	559.1	615.3	651.4	667.4	672.8	670.1	672.8	670.1	672.8
122.5°	497.6	543.6	604.0	662.4	704.9	723.1	729.5	730.0	730.6	729.0	730.6
125°	553.7	609.9	680.8	741.0	785.1	806.5	811.9	813.2	815.9	822.6	815.9
127.5°	610.5	674.1	752.0	810.0	855.2	881.2	889.5	892.4	898.0	901.0	898.0
130°	650.0	722.3	801.2	856.0	900.2	928.3	943.0	947.0	953.7	952.3	953.7
132.5°	691.8	767.2	847.2	904.2	945.1	975.3	987.9	999.4	1001.8	1003.7	1001.8
135°	753.0	834.6	914.9	971.1	1009.8	1039.3	1055.3	1066.0	1072.7	1076.7	1072.7
137.5°	817.5	903.6	980.7	1030.7	1069.8	1095.2	1113.4	1124.6	1131.6	1134.8	1131.6
140°	861.4	944.3	1019.2	1071.4	1106.1	1131.6	1147.6	1161.0	1169.0	1169.0	1169.0
142.5°	903.1	985.0	1057.7	1109.9	1140.4	1163.7	1180.8	1190.9	1200.0	1200.0	1200.0
145°	961.7	1043.3	1110.2	1162.3	1187.7	1209.1	1227.9	1235.9	1241.2	1241.2	1241.2
147.5°	1023.0	1095.2	1156.2	1206.2	1227.6	1252.7	1267.5	1273.9	1280.6	1277.6	1280.6
150°	1059.3	1126.2	1185.1	1231.9	1253.3	1277.4	1292.1	1297.4	1304.1	1300.1	1304.1
152.5°	1094.6	1158.3	1211.8	1255.4	1273.6	1297.7	1314.5	1319.9	1324.4	1321.5	1324.4
155°	1142.3	1198.4	1247.9	1288.1	1304.1	1326.8	1342.9	1349.6	1354.9	1348.2	1354.9
157.5°	1184.8	1233.2	1276.3	1313.2	1330.3	1349.9	1364.8	1373.1	1378.5	1375.5	1378.5
160°	1210.5	1254.6	1293.4	1328.2	1344.2	1361.6	1377.7	1387.0	1392.4	1388.4	1392.4
162.5°	1231.9	1271.7	1308.4	1340.0	1353.9	1369.1	1388.4	1396.7	1402.0	1396.9	1402.0
165°	1262.6	1294.7	1326.8	1353.6	1365.6	1377.7	1397.7	1407.1	1411.1	1405.8	1411.1
167.5°	1285.9	1310.5	1336.5	1359.5	1368.3	1380.1	1400.1	1407.9	1413.0	1406.3	1413.0
170°	1298.8	1320.2	1342.9	1361.6	1368.3	1379.0	1399.1	1405.8	1409.8	1403.1	1409.8
172.5°	1309.5	1325.5	1344.0	1360.6	1364.0	1372.6	1391.6	1398.3	1401.2	1395.6	1401.2
175°	1320.2	1329.5	1342.9	1353.6	1352.3	1357.6	1373.7	1379.0	1384.4	1376.3	1384.4
177.5°	1325.2	1329.5	1333.8	1340.2	1335.9	1335.9	1347.7	1350.9	1352.0	1347.7	1352.0
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2
2.5°	9236.8	9214.8	9182.1	9183.6	9219.3	9249.9	9265.4	9280.8	9265.4	9249.9	9219.3
5°	8940.5	8903.5	8855.2	8844.8	8872.3	8898.3	8919.9	8941.5	8919.9	8898.3	8872.3
7.5°	8268.3	8229.6	8176.0	8162.3	8188.5	8206.4	8199.4	8192.4	8199.4	8206.4	8188.5
10°	7626.1	7617.7	7599.9	7592.4	7595.4	7596.3	7591.1	7585.9	7591.1	7596.3	7595.4
12.5°	6904.9	6882.7	6856.0	6861.9	6900.6	6924.4	6903.7	6883.1	6903.7	6924.4	6900.6
15°	5763.3	5736.7	5701.0	5720.4	5794.7	5842.2	5808.7	5775.2	5808.7	5842.2	5794.7
17.5°	4657.8	4653.3	4646.6	4662.2	4700.2	4729.5	4732.9	4736.3	4732.9	4729.5	4700.2
20°	3960.4	3963.4	3968.6	3987.2	4019.2	4044.5	4049.7	4054.9	4049.7	4044.5	4019.2
22.5°	3398.4	3406.9	3419.8	3431.9	3443.0	3453.6	3462.4	3471.2	3462.4	3453.6	3443.0
25°	2698.8	2689.3	2671.4	2672.9	2693.8	2716.4	2744.7	2773.0	2744.7	2716.4	2693.8
27.5°	2190.0	2187.8	2185.9	2193.8	2211.5	2224.8	2225.3	2225.7	2225.3	2224.8	2211.5
30°	1920.6	1922.3	1921.5	1929.7	1946.8	1961.0	1966.2	1971.4	1966.2	1961.0	1946.8
32.5°	1694.4	1699.6	1703.6	1716.3	1737.5	1752.6	1748.8	1745.1	1748.8	1752.6	1737.5
35°	1388.4	1397.4	1408.5	1422.3	1438.6	1450.9	1450.9	1450.9	1450.9	1450.9	1438.6
37.5°	1112.1	1125.4	1141.1	1154.8	1166.4	1175.5	1176.8	1178.1	1176.8	1175.5	1166.4
40°	933.4	950.0	969.3	982.7	990.1	996.7	1000.4	1004.1	1000.4	996.7	990.1
42.5°	765.0	782.6	802.0	815.4	822.8	825.9	815.9	806.0	815.9	825.9	822.8
45°	513.9	547.2	569.5	577.7	571.8	556.9	515.2	473.6	515.2	556.9	571.8
47.5°	241.6	299.4	358.2	369.6	333.6	295.1	249.3	203.5	249.3	295.1	333.6
50°	119.2	180.7	254.4	265.2	213.1	165.1	129.4	93.7	129.4	165.1	213.1
52.5°	70.0	120.9	184.5	189.3	135.4	90.6	72.7	54.9	72.7	90.6	135.4
55°	28.8	55.2	88.7	90.2	59.7	35.3	29.4	23.4	29.4	35.3	59.7
57.5°	12.4	22.0	33.9	34.5	24.0	15.2	12.0	8.7	12.0	15.2	24.0
60°	4.6	9.5	15.4	15.8	10.6	6.3	4.8	3.3	4.8	6.3	10.6
62.5°	2.1	4.6	7.5	7.6	4.8	2.5	1.6	0.7	1.6	2.5	4.8
65°	0.0	0.6	1.3	1.3	0.6	0.0	0.0	0.0	0.0	0.0	0.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.6	5.4	5.4	5.1	4.3	3.2	1.9	0.8	1.9	2.9	4.8
90°	28.1	26.8	26.8	25.4	21.4	16.1	9.4	4.0	9.4	14.7	24.1
92.5°	33.4	33.2	31.0	28.6	23.5	23.5	23.3	14.7	25.4	36.1	51.9
95°	30.8	30.8	36.1	45.5	66.9	68.2	45.5	41.5	58.9	82.9	104.3
97.5°	83.2	99.0	121.4	125.7	119.0	88.8	85.1	79.2	107.8	131.6	166.1
100°	153.8	173.9	189.9	157.8	124.4	123.1	115.0	112.4	143.1	165.9	199.3
102.5°	240.5	246.6	191.0	172.8	165.1	159.4	147.1	145.5	176.3	207.6	235.7
105°	260.8	234.1	235.4	235.4	230.1	219.4	196.6	195.3	230.1	266.2	300.9
107.5°	306.8	310.8	317.8	316.2	310.0	281.4	254.7	248.5	279.8	323.2	361.4
110°	367.8	371.8	374.5	371.8	362.5	326.4	294.3	284.9	313.0	358.5	399.9



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	426.7	429.6	435.5	427.5	411.7	370.2	333.9	320.2	348.3	394.8	437.4
115°	520.3	520.3	521.6	517.6	485.5	442.7	394.6	374.5	398.6	441.4	488.2
117.5°	612.3	613.9	608.6	597.9	560.7	510.9	456.9	424.8	443.8	489.0	537.2
120°	670.1	672.8	667.4	651.4	615.3	559.1	497.6	460.1	474.8	519.0	567.1
122.5°	730.0	729.5	723.1	704.9	662.4	604.0	543.6	497.6	503.7	544.6	591.7
125°	813.2	811.9	806.5	785.1	741.0	680.8	609.9	553.7	545.7	580.5	628.6
127.5°	892.4	889.5	881.2	855.2	810.0	752.0	674.1	610.5	592.5	614.5	658.6
130°	947.0	943.0	928.3	900.2	856.0	801.2	722.3	650.0	624.6	638.0	676.8
132.5°	999.4	987.9	975.3	945.1	904.2	847.2	767.2	691.8	656.7	662.6	692.8
135°	1066.0	1055.3	1039.3	1009.8	971.1	914.9	834.6	753.0	704.9	699.5	716.9
137.5°	1124.6	1113.4	1095.2	1069.8	1030.7	980.7	903.6	817.5	756.8	738.9	745.5
140°	1161.0	1147.6	1131.6	1106.1	1071.4	1019.2	944.3	861.4	793.2	767.8	763.7
142.5°	1190.9	1180.8	1163.7	1140.4	1109.9	1057.7	985.0	903.1	830.6	797.7	788.3
145°	1235.9	1227.9	1209.1	1187.7	1162.3	1110.2	1043.3	961.7	889.5	846.7	826.6
147.5°	1273.9	1267.5	1252.7	1227.6	1206.2	1156.2	1095.2	1023.0	948.9	895.9	869.9
150°	1297.4	1292.1	1277.4	1253.3	1231.9	1185.1	1126.2	1059.3	988.4	932.3	898.8
152.5°	1319.9	1314.5	1297.7	1273.6	1255.4	1211.8	1158.3	1094.6	1022.7	966.5	932.0
155°	1349.6	1342.9	1326.8	1304.1	1288.1	1247.9	1198.4	1142.3	1080.7	1021.9	983.1
157.5°	1373.1	1364.8	1349.9	1330.3	1313.2	1276.3	1233.2	1184.8	1131.0	1074.9	1035.3
160°	1387.0	1377.7	1361.6	1344.2	1328.2	1293.4	1254.6	1210.5	1161.0	1110.2	1067.4
162.5°	1396.7	1388.4	1369.1	1353.9	1340.0	1308.4	1271.7	1231.9	1187.7	1143.3	1103.7
165°	1407.1	1397.7	1377.7	1365.6	1353.6	1326.8	1294.7	1262.6	1225.2	1189.1	1157.0
167.5°	1407.9	1400.1	1380.1	1368.3	1359.5	1336.5	1310.5	1285.9	1256.8	1228.4	1201.7
170°	1405.8	1399.1	1379.0	1368.3	1361.6	1342.9	1320.2	1298.8	1276.0	1251.9	1230.5
172.5°	1398.3	1391.6	1372.6	1364.0	1360.6	1344.0	1325.5	1309.5	1289.9	1272.3	1255.2
175°	1379.0	1373.7	1357.6	1352.3	1353.6	1342.9	1329.5	1320.2	1308.1	1297.4	1288.1
177.5°	1350.9	1347.7	1335.9	1335.9	1340.2	1333.8	1329.5	1325.2	1319.9	1316.7	1313.5
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2	9286.2
2.5°	9183.6	9182.1	9214.8	9236.8	9226.7	9216.6	9226.7	9236.8	9214.8	9182.1	9183.6
5°	8844.8	8855.2	8903.5	8940.5	8943.5	8946.5	8943.5	8940.5	8903.5	8855.2	8844.8
7.5°	8162.3	8176.0	8229.6	8268.3	8262.5	8256.7	8262.5	8268.3	8229.6	8176.0	8162.3
10°	7592.4	7599.9	7617.7	7626.1	7606.0	7585.9	7606.0	7626.1	7617.7	7599.9	7592.4
12.5°	6861.9	6856.0	6882.7	6904.9	6913.4	6921.9	6913.4	6904.9	6882.7	6856.0	6861.9
15°	5720.4	5701.0	5736.7	5763.3	5762.6	5761.8	5762.6	5763.3	5736.7	5701.0	5720.4
17.5°	4662.2	4646.6	4653.3	4657.8	4655.5	4653.3	4655.5	4657.8	4653.3	4646.6	4662.2
20°	3987.2	3968.6	3963.4	3960.4	3964.1	3967.8	3964.1	3960.4	3963.4	3968.6	3987.2
22.5°	3431.9	3419.8	3406.9	3398.4	3403.3	3408.2	3403.3	3398.4	3406.9	3419.8	3431.9
25°	2672.9	2671.4	2689.3	2698.8	2683.2	2667.5	2683.2	2698.8	2689.3	2671.4	2672.9
27.5°	2193.8	2185.9	2187.8	2190.0	2193.0	2196.0	2193.0	2190.0	2187.8	2185.9	2193.8
30°	1929.7	1921.5	1922.3	1920.6	1911.7	1902.8	1911.7	1920.6	1922.3	1921.5	1929.7
32.5°	1716.3	1703.6	1699.6	1694.4	1685.4	1676.5	1685.4	1694.4	1699.6	1703.6	1716.3
35°	1422.3	1408.5	1397.4	1388.4	1386.2	1384.0	1386.2	1388.4	1397.4	1408.5	1422.3
37.5°	1154.8	1141.1	1125.4	1112.1	1106.3	1100.5	1106.3	1112.1	1125.4	1141.1	1154.8
40°	982.7	969.3	950.0	933.4	925.3	917.1	925.3	933.4	950.0	969.3	982.7
42.5°	815.4	802.0	782.6	765.0	752.7	740.4	752.7	765.0	782.6	802.0	815.4
45°	577.7	569.5	547.2	513.9	447.8	381.6	447.8	513.9	547.2	569.5	577.7
47.5°	369.6	358.2	299.4	241.6	186.6	131.5	186.6	241.6	299.4	358.2	369.6
50°	265.2	254.4	180.7	119.2	93.9	68.6	93.9	119.2	180.7	254.4	265.2
52.5°	189.3	184.5	120.9	70.0	56.6	43.2	56.6	70.0	120.9	184.5	189.3
55°	90.2	88.7	55.2	28.8	23.6	18.4	23.6	28.8	55.2	88.7	90.2
57.5°	34.5	33.9	22.0	12.4	9.7	7.0	9.7	12.4	22.0	33.9	34.5
60°	15.8	15.4	9.5	4.6	3.2	1.7	3.2	4.6	9.5	15.4	15.8
62.5°	7.6	7.5	4.6	2.1	1.2	0.3	1.2	2.1	4.6	7.5	7.6
65°	1.3	1.3	0.6	0.0	0.0	0.0	0.0	0.6	1.3	1.3	1.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	6.2	8.0	9.9	11.0	12.0	11.5	12.0	11.0	9.9	8.0	6.2
90°	30.8	40.1	49.5	54.8	60.2	57.5	60.2	49.5	40.1	30.8	30.8
92.5°	61.8	77.6	89.1	98.7	103.0	102.5	103.0	98.7	89.1	77.6	61.8
95°	124.4	143.1	161.8	175.2	183.2	180.6	183.2	175.2	161.8	143.1	124.4
97.5°	191.8	216.9	237.8	250.4	258.4	263.8	258.4	237.8	216.9	191.8	191.8
100°	236.7	260.8	284.9	299.6	313.0	318.3	313.0	284.9	260.8	236.7	236.7
102.5°	273.1	304.7	330.9	346.7	357.9	363.3	357.9	330.9	304.7	273.1	273.1
105°	333.0	366.5	394.6	414.6	426.7	430.7	426.7	394.6	366.5	333.0	333.0
107.5°	393.0	427.5	453.4	475.6	490.3	498.9	490.3	453.4	427.5	393.0	393.0
110°	440.1	468.1	496.2	516.3	531.0	536.4	531.0	496.2	468.1	440.1	440.1



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	479.6	510.9	539.0	559.1	575.9	583.4	575.9	559.1	539.0	510.9	479.6
115°	535.0	576.5	601.9	620.6	632.7	639.3	632.7	620.6	601.9	576.5	535.0
117.5°	581.0	624.4	652.2	666.6	672.3	677.1	672.3	666.6	652.2	624.4	581.0
120°	609.9	650.0	682.1	700.9	707.6	710.2	707.6	700.9	682.1	650.0	609.9
122.5°	636.7	674.7	705.7	728.7	739.7	742.3	739.7	728.7	705.7	674.7	636.7
125°	674.1	710.2	742.3	765.1	777.1	783.8	777.1	765.1	742.3	710.2	674.1
127.5°	706.8	745.8	775.2	795.8	807.6	813.0	807.6	795.8	775.2	745.8	706.8
130°	724.9	765.1	794.5	817.2	827.9	833.3	827.9	817.2	794.5	765.1	724.9
132.5°	738.9	781.1	811.6	832.2	844.0	849.3	844.0	832.2	811.6	781.1	738.9
135°	755.7	799.9	832.0	852.0	862.7	868.1	862.7	852.0	832.0	799.9	755.7
137.5°	770.4	810.6	844.0	865.1	874.8	878.2	874.8	865.1	844.0	810.6	770.4
140°	781.1	815.9	849.3	869.4	880.1	881.4	880.1	869.4	849.3	815.9	781.1
142.5°	795.0	822.3	851.5	871.5	882.2	884.7	882.2	871.5	851.5	822.3	795.0
145°	819.9	836.0	856.0	874.8	884.1	886.8	884.1	874.8	856.0	836.0	819.9
147.5°	851.2	856.3	866.7	879.0	888.1	890.0	888.1	879.0	866.7	856.3	851.2
150°	874.8	873.4	877.4	885.5	893.5	892.1	893.5	885.5	877.4	873.4	874.8
152.5°	901.5	893.7	893.5	897.2	901.0	900.7	901.0	897.2	893.5	893.7	901.5
155°	947.0	932.3	924.2	921.6	921.6	920.2	921.6	921.6	924.2	932.3	947.0
157.5°	997.0	976.4	964.4	957.9	956.1	953.1	956.1	957.9	964.4	976.4	997.0
160°	1031.2	1008.5	996.5	985.8	981.8	977.7	981.8	985.8	996.5	1008.5	1031.2
162.5°	1063.3	1041.7	1028.6	1018.9	1014.9	1008.8	1014.9	1018.9	1028.6	1041.7	1063.3
165°	1115.5	1092.8	1078.1	1070.0	1064.7	1059.3	1064.7	1070.0	1078.1	1092.8	1115.5
167.5°	1167.7	1142.8	1133.2	1124.1	1119.0	1109.4	1119.0	1124.1	1133.2	1142.8	1167.7
170°	1199.8	1177.0	1171.7	1163.7	1154.3	1143.6	1154.3	1163.7	1171.7	1177.0	1199.8
172.5°	1227.6	1212.4	1207.0	1199.0	1196.0	1187.5	1196.0	1199.0	1207.0	1212.4	1227.6
175°	1268.0	1256.0	1256.0	1254.6	1250.6	1242.6	1250.6	1254.6	1256.0	1256.0	1268.0
177.5°	1301.7	1295.3	1299.6	1299.6	1298.5	1291.0	1298.5	1299.6	1299.6	1295.3	1301.7
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	9286.2	9286.2	9286.2	9286.2
2.5°	9219.3	9249.9	9265.4	9280.8
5°	8872.3	8898.3	8919.9	8941.5
7.5°	8188.5	8206.4	8199.4	8192.4
10°	7595.4	7596.3	7591.1	7585.9
12.5°	6900.6	6924.4	6903.7	6883.1
15°	5794.7	5842.2	5808.7	5775.2
17.5°	4700.2	4729.5	4732.9	4736.3
20°	4019.2	4044.5	4049.7	4054.9
22.5°	3443.0	3453.6	3462.4	3471.2
25°	2693.8	2716.4	2744.7	2773.0
27.5°	2211.5	2224.8	2225.3	2225.7
30°	1946.8	1961.0	1966.2	1971.4
32.5°	1737.5	1752.6	1748.8	1745.1
35°	1438.6	1450.9	1450.9	1450.9
37.5°	1166.4	1175.5	1176.8	1178.1
40°	990.1	996.7	1000.4	1004.1
42.5°	822.8	825.9	815.9	806.0
45°	571.8	556.9	515.2	473.6
47.5°	333.6	295.1	249.3	203.5
50°	213.1	165.1	129.4	93.7
52.5°	135.4	90.6	72.7	54.9
55°	59.7	35.3	29.4	23.4
57.5°	24.0	15.2	12.0	8.7
60°	10.6	6.3	4.8	3.3
62.5°	4.8	2.5	1.6	0.7
65°	0.6	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	4.8	2.9	1.9	0.8
90°	24.1	14.7	9.4	4.0
92.5°	51.9	36.1	25.4	14.7
95°	104.3	82.9	58.9	41.5
97.5°	166.1	131.6	107.8	79.2
100°	199.3	165.9	143.1	112.4
102.5°	235.7	207.6	176.3	145.5
105°	300.9	266.2	230.1	195.3
107.5°	361.4	323.2	279.8	248.5
110°	399.9	358.5	313.0	284.9



TEST NUMBER: P1427625

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	437.4	394.8	348.3	320.2
115°	488.2	441.4	398.6	374.5
117.5°	537.2	489.0	443.8	424.8
120°	567.1	519.0	474.8	460.1
122.5°	591.7	544.6	503.7	497.6
125°	628.6	580.5	545.7	553.7
127.5°	658.6	614.5	592.5	610.5
130°	676.8	638.0	624.6	650.0
132.5°	692.8	662.6	656.7	691.8
135°	716.9	699.5	704.9	753.0
137.5°	745.5	738.9	756.8	817.5
140°	763.7	767.8	793.2	861.4
142.5°	788.3	797.7	830.6	903.1
145°	826.6	846.7	889.5	961.7
147.5°	869.9	895.9	948.9	1023.0
150°	898.8	932.3	988.4	1059.3
152.5°	932.0	966.5	1022.7	1094.6
155°	983.1	1021.9	1080.7	1142.3
157.5°	1035.3	1074.9	1131.0	1184.8
160°	1067.4	1110.2	1161.0	1210.5
162.5°	1103.7	1143.3	1187.7	1231.9
165°	1157.0	1189.1	1225.2	1262.6
167.5°	1201.7	1228.4	1256.8	1285.9
170°	1230.5	1251.9	1276.0	1298.8
172.5°	1255.2	1272.3	1289.9	1309.5
175°	1288.1	1297.4	1308.1	1320.2
177.5°	1313.5	1316.7	1319.9	1325.2
180°	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427625  
 CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00