

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427742

Luminaire Tested: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427742
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8903.8 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 72.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	83	79	77	74	69	67	66	60	59	57	53
2	91	84	77	72	85	79	73	68	69	65	61	61	57	54	53	50	48	44
3	83	73	66	60	78	69	62	57	61	56	51	53	49	46	46	43	41	37
4	76	65	57	50	71	61	54	48	54	48	43	47	43	39	41	38	35	32
5	70	58	49	43	65	55	47	41	48	42	37	43	38	34	37	33	30	27
6	64	52	43	37	60	49	41	36	44	37	33	38	33	30	34	30	27	24
7	60	47	39	33	56	44	37	31	39	33	29	35	30	26	31	27	24	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	28	23	45	34	27	22	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32306	32306	32306	32306
5°	32110	32474	32110	32474
10°	31996	32365	31996	32365
15°	31821	32220	31821	32220
20°	31620	31934	31620	31934
25°	31277	31553	31277	31553
30°	30946	31157	30946	31157
35°	30551	30746	30551	30746
40°	30205	30293	30205	30293
45°	29761	29761	29761	29761
50°	29165	29235	29165	29235
55°	28478	28518	28478	28518
60°	27709	27709	27709	27709
65°	26807	26701	26807	26701
70°	25543	25279	25543	25279
75°	23824	23293	23824	23293
80°	21227	20176	21227	20176
85°	16969	14357	16969	14357

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 29962 cd/sqm



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.3	2.1
10°-20°	541.0	6.1
20°-30°	814.3	9.1
30°-40°	973.8	10.9
40°-50°	1005.5	11.3
50°-60°	906.9	10.2
60°-70°	694.7	7.8
70°-80°	401.5	4.5
80°-90°	108.9	1.2
90°-100°	89.1	1.0
100°-110°	259.7	2.9
110°-120°	423.9	4.8
120°-130°	537.9	6.0
130°-140°	575.6	6.5
140°-150°	537.5	6.0
150°-160°	442.3	5.0
160°-170°	296.6	3.3
170°-180°	105.3	1.2
0°-30°	1544.6	17.3
0°-40°	2518.3	28.3
0°-60°	4430.8	49.8
0°-90°	5636.0	63.3
90°-120°	772.7	8.7
90°-150°	2423.6	27.2
90°-180°	3268.0	36.7
0°-180°	8903.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	1981	2004	1981	2004	1981	188
15°	1904	1928	1904	1928	1904	537
25°	1756	1771	1756	1771	1756	809
35°	1550	1560	1550	1560	1550	970
45°	1303	1303	1303	1303	1303	1004
55°	1012	1013	1012	1013	1012	904
65°	702	699	702	699	702	694
75°	382	373	382	373	382	404
85°	92	78	92	78	92	107
90°	3	25	3	49	3	7
95°	35	26	35	153	35	42
105°	165	264	165	364	165	176
115°	316	439	316	540	316	312
125°	468	695	468	662	468	419
135°	636	910	636	734	636	492
145°	813	1049	813	750	813	509
155°	965	1140	965	778	965	444
165°	1067	1188	1067	895	1067	300
175°	1116	1163	1116	1050	1116	106
180°	1119	1119	1119	1119	1119	



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9
2.5°	1990.8	2000.3	2009.8	2005.8	1997.3	1994.0	1996.0	1997.8	1998.8	1999.8	1998.8
5°	1981.2	1993.7	2006.2	2001.9	1991.8	1987.5	1988.7	1991.2	1997.5	2003.7	1997.5
7.5°	1965.1	1977.7	1990.2	1986.2	1976.6	1972.6	1974.1	1976.9	1983.4	1989.9	1983.4
10°	1951.6	1964.1	1976.6	1972.3	1962.2	1958.5	1961.0	1964.1	1969.1	1974.1	1969.1
12.5°	1934.7	1947.2	1959.7	1956.1	1947.1	1943.3	1944.8	1947.3	1952.9	1958.4	1952.9
15°	1903.7	1916.2	1928.7	1925.3	1916.5	1913.1	1915.0	1917.6	1922.6	1927.6	1922.6
17.5°	1866.2	1878.0	1889.8	1886.6	1878.5	1875.4	1877.6	1880.3	1884.7	1889.0	1884.7
20°	1840.3	1851.6	1862.8	1859.5	1851.4	1847.6	1848.3	1849.8	1854.2	1858.6	1854.2
22.5°	1808.7	1820.0	1831.3	1828.3	1820.7	1816.2	1814.8	1815.1	1820.5	1825.9	1820.5
25°	1755.7	1767.0	1778.3	1775.9	1769.0	1764.7	1762.8	1762.5	1766.8	1771.2	1766.8
27.5°	1700.5	1709.9	1719.3	1717.3	1711.6	1708.0	1706.8	1706.6	1709.8	1712.9	1709.8
30°	1659.9	1669.3	1678.7	1676.4	1670.1	1666.3	1665.1	1664.9	1668.1	1671.2	1668.1
32.5°	1617.1	1626.0	1634.9	1631.6	1624.4	1620.6	1620.4	1621.1	1624.7	1628.4	1624.7
35°	1550.0	1557.5	1565.0	1561.7	1554.9	1551.7	1552.4	1553.6	1556.7	1559.9	1556.7
37.5°	1482.7	1488.4	1494.2	1490.8	1484.4	1481.2	1481.1	1481.6	1484.2	1486.9	1484.2
40°	1433.1	1439.3	1445.6	1442.0	1435.1	1431.3	1430.7	1431.0	1434.1	1437.3	1434.1
42.5°	1382.3	1387.1	1391.8	1388.6	1382.7	1380.0	1380.4	1381.0	1382.7	1384.3	1382.7
45°	1303.4	1307.8	1312.2	1309.1	1303.4	1300.6	1300.6	1300.9	1302.2	1303.4	1302.2
47.5°	1220.8	1224.2	1227.6	1225.2	1220.8	1218.2	1217.5	1217.4	1219.4	1221.4	1219.4
50°	1161.1	1165.5	1169.9	1167.7	1163.3	1160.5	1159.2	1158.9	1161.4	1163.9	1161.4
52.5°	1102.5	1107.4	1112.2	1110.2	1105.8	1102.7	1101.0	1100.2	1102.2	1104.2	1102.2
55°	1011.7	1017.4	1023.0	1021.6	1017.8	1014.7	1012.2	1010.6	1011.9	1013.1	1011.9
57.5°	919.0	924.5	930.0	929.0	925.7	922.6	919.6	917.8	919.5	921.3	919.5
60°	858.1	863.1	868.2	866.6	862.8	859.7	857.2	855.6	856.9	858.1	856.9
62.5°	796.1	801.1	806.2	804.2	800.0	796.6	794.1	792.5	793.8	795.0	793.8
65°	701.7	706.1	710.5	708.8	705.0	701.9	699.4	697.7	698.3	698.9	698.3
67.5°	606.5	610.2	614.0	612.2	608.6	604.9	601.3	598.8	599.8	600.8	599.8
70°	541.1	544.9	548.6	547.2	544.1	540.9	537.8	535.5	535.5	535.5	535.5
72.5°	478.0	481.2	484.5	482.6	478.9	475.8	473.2	471.2	471.2	471.2	471.2
75°	381.9	383.7	385.6	384.7	382.8	380.3	377.2	374.7	374.0	373.4	374.0
77.5°	289.1	289.1	289.1	287.4	285.0	282.6	280.2	278.2	277.5	276.7	277.5
80°	228.3	228.3	228.3	226.9	225.0	223.1	221.2	219.5	218.3	217.0	218.3
82.5°	171.9	170.9	169.9	168.2	166.4	164.0	161.1	159.3	160.5	161.8	160.5
85°	91.6	90.3	89.1	87.4	85.5	83.3	80.8	78.8	78.1	77.5	78.1
87.5°	28.9	28.8	28.9	28.4	27.6	26.1	24.1	22.7	22.4	21.9	22.4
90°	3.4	7.9	13.6	18.1	21.5	22.6	22.6	23.7	24.9	24.9	24.9
92.5°	12.4	19.7	19.9	19.9	24.2	26.2	28.0	28.3	29.4	29.4	29.4
95°	35.0	38.4	57.7	56.5	38.4	30.5	26.0	26.0	26.0	26.0	26.0
97.5°	66.9	71.9	75.1	100.6	106.3	102.6	83.7	70.3	62.9	59.5	62.9
100°	95.0	97.2	104.0	105.1	133.4	160.5	147.0	130.0	124.4	121.0	124.4
102.5°	123.0	124.4	134.8	139.5	146.1	161.4	208.5	203.3	199.4	198.7	199.4
105°	165.1	166.2	185.4	194.4	199.0	199.0	197.8	220.4	256.6	264.5	256.6
107.5°	210.0	215.2	237.9	262.0	267.2	268.6	262.7	259.3	258.0	258.9	258.0
110°	240.8	248.7	275.8	306.4	314.3	316.5	314.3	310.9	308.6	308.6	308.6



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	270.6	282.2	312.9	348.0	361.3	368.1	363.1	360.6	358.4	360.2	358.4
115°	316.5	333.5	374.2	410.4	437.5	440.9	439.8	439.8	438.6	438.6	438.6
117.5°	359.0	386.2	431.8	473.9	505.3	514.4	518.9	517.5	516.2	518.4	516.2
120°	388.9	420.5	472.5	520.0	550.6	564.1	568.6	566.4	568.6	566.4	568.6
122.5°	420.5	459.4	510.5	559.8	595.8	611.1	616.6	617.0	617.5	616.1	617.5
125°	468.0	515.5	575.4	626.3	663.6	681.7	686.2	687.3	689.6	695.3	689.6
127.5°	516.0	569.8	635.6	684.6	722.8	744.8	751.8	754.3	759.0	761.5	759.0
130°	549.4	610.5	677.2	723.5	760.8	784.6	797.0	800.4	806.0	804.9	806.0
132.5°	584.7	648.5	716.1	764.2	798.8	824.4	835.0	844.7	846.7	848.3	846.7
135°	636.5	705.4	773.3	820.7	853.5	878.4	892.0	901.0	906.7	910.0	906.7
137.5°	691.0	763.8	828.9	871.2	904.2	925.7	941.0	950.5	956.4	959.1	956.4
140°	728.0	798.1	861.4	905.5	934.9	956.4	970.0	981.3	988.1	988.1	988.1
142.5°	763.3	832.5	894.0	938.1	963.9	983.5	998.0	1006.6	1014.3	1014.3	1014.3
145°	812.8	881.8	938.3	982.4	1003.9	1022.0	1037.8	1044.6	1049.1	1049.1	1049.1
147.5°	864.6	925.7	977.2	1019.5	1037.6	1058.8	1071.3	1076.7	1082.3	1079.9	1082.3
150°	895.4	951.9	1001.6	1041.2	1059.3	1079.6	1092.1	1096.6	1102.2	1098.8	1102.2
152.5°	925.2	979.0	1024.2	1061.1	1076.5	1096.8	1111.1	1115.6	1119.4	1116.9	1119.4
155°	965.4	1012.9	1054.8	1088.7	1102.2	1121.5	1135.0	1140.7	1145.2	1139.5	1145.2
157.5°	1001.4	1042.3	1078.7	1109.9	1124.4	1140.9	1153.6	1160.6	1165.1	1162.6	1165.1
160°	1023.1	1060.4	1093.2	1122.6	1136.1	1150.8	1164.4	1172.3	1176.8	1173.5	1176.8
162.5°	1041.2	1074.9	1105.9	1132.5	1144.3	1157.2	1173.5	1180.5	1185.0	1180.7	1185.0
165°	1067.2	1094.3	1121.5	1144.1	1154.2	1164.4	1181.4	1189.3	1192.7	1188.2	1192.7
167.5°	1086.9	1107.7	1129.6	1149.0	1156.5	1166.4	1183.4	1190.0	1194.3	1188.6	1194.3
170°	1097.7	1115.8	1135.0	1150.8	1156.5	1165.5	1182.5	1188.2	1191.5	1185.9	1191.5
172.5°	1106.8	1120.3	1135.9	1149.9	1152.9	1160.1	1176.2	1181.8	1184.3	1179.6	1184.3
175°	1115.8	1123.7	1135.0	1144.1	1142.9	1147.5	1161.0	1165.5	1170.1	1163.3	1170.1
177.5°	1120.1	1123.7	1127.3	1132.8	1129.1	1129.1	1139.1	1141.8	1142.7	1139.1	1142.7
180°	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9
2.5°	1997.8	1996.0	1994.0	1997.3	2005.8	2009.8	2000.3	1990.8	2000.3	2009.8	2005.8
5°	1991.2	1988.7	1987.5	1991.8	2001.9	2006.2	1993.7	1981.2	1993.7	2006.2	2001.9
7.5°	1976.9	1974.1	1972.6	1976.6	1986.2	1990.2	1977.7	1965.1	1977.7	1990.2	1986.2
10°	1964.1	1961.0	1958.5	1962.2	1972.3	1976.6	1964.1	1951.6	1964.1	1976.6	1972.3
12.5°	1947.3	1944.8	1943.3	1947.1	1956.1	1959.7	1947.2	1934.7	1947.2	1959.7	1956.1
15°	1917.6	1915.0	1913.1	1916.5	1925.3	1928.7	1916.2	1903.7	1916.2	1928.7	1925.3
17.5°	1880.3	1877.6	1875.4	1878.5	1886.6	1889.8	1878.0	1866.2	1878.0	1889.8	1886.6
20°	1849.8	1848.3	1847.6	1851.4	1859.5	1862.8	1851.6	1840.3	1851.6	1862.8	1859.5
22.5°	1815.1	1814.8	1816.2	1820.7	1828.3	1831.3	1820.0	1808.7	1820.0	1831.3	1828.3
25°	1762.5	1762.8	1764.7	1769.0	1775.9	1778.3	1767.0	1755.7	1767.0	1778.3	1775.9
27.5°	1706.6	1706.8	1708.0	1711.6	1717.3	1719.3	1709.9	1700.5	1709.9	1719.3	1717.3
30°	1664.9	1665.1	1666.3	1670.1	1676.4	1678.7	1669.3	1659.9	1669.3	1678.7	1676.4
32.5°	1621.1	1620.4	1620.6	1624.4	1631.6	1634.9	1626.0	1617.1	1626.0	1634.9	1631.6
35°	1553.6	1552.4	1551.7	1554.9	1561.7	1565.0	1557.5	1550.0	1557.5	1565.0	1561.7
37.5°	1481.6	1481.1	1481.2	1484.4	1490.8	1494.2	1488.4	1482.7	1488.4	1494.2	1490.8
40°	1431.0	1430.7	1431.3	1435.1	1442.0	1445.6	1439.3	1433.1	1439.3	1445.6	1442.0
42.5°	1381.0	1380.4	1380.0	1382.7	1388.6	1391.8	1387.1	1382.3	1387.1	1391.8	1388.6
45°	1300.9	1300.6	1300.6	1303.4	1309.1	1312.2	1307.8	1303.4	1307.8	1312.2	1309.1
47.5°	1217.4	1217.5	1218.2	1220.8	1225.2	1227.6	1224.2	1220.8	1224.2	1227.6	1225.2
50°	1158.9	1159.2	1160.5	1163.3	1167.7	1169.9	1165.5	1161.1	1165.5	1169.9	1167.7
52.5°	1100.2	1101.0	1102.7	1105.8	1110.2	1112.2	1107.4	1102.5	1107.4	1112.2	1110.2
55°	1010.6	1012.2	1014.7	1017.8	1021.6	1023.0	1017.4	1011.7	1017.4	1023.0	1021.6
57.5°	917.8	919.6	922.6	925.7	929.0	930.0	924.5	919.0	924.5	930.0	929.0
60°	855.6	857.2	859.7	862.8	866.6	868.2	863.1	858.1	863.1	868.2	866.6
62.5°	792.5	794.1	796.6	800.0	804.2	806.2	801.1	796.1	801.1	806.2	804.2
65°	697.7	699.4	701.9	705.0	708.8	710.5	706.1	701.7	706.1	710.5	708.8
67.5°	598.8	601.3	604.9	608.6	612.2	614.0	610.2	606.5	610.2	614.0	612.2
70°	535.5	537.8	540.9	544.1	547.2	548.6	544.9	541.1	544.9	548.6	547.2
72.5°	471.2	473.2	475.8	478.9	482.6	484.5	481.2	478.0	481.2	484.5	482.6
75°	374.7	377.2	380.3	382.8	384.7	385.6	383.7	381.9	383.7	385.6	384.7
77.5°	278.2	280.2	282.6	285.0	287.4	289.1	289.1	289.1	289.1	289.1	287.4
80°	219.5	221.2	223.1	225.0	226.9	228.3	228.3	228.3	228.3	228.3	226.9
82.5°	159.3	161.1	164.0	166.4	168.2	169.9	170.9	171.9	170.9	169.9	168.2
85°	78.8	80.8	83.3	85.5	87.4	89.1	90.3	91.6	90.3	89.1	87.4
87.5°	22.7	24.1	26.1	27.6	28.4	28.9	28.8	28.9	28.8	28.7	28.9
90°	23.7	22.6	22.6	21.5	18.1	13.6	7.9	3.4	7.9	12.4	20.3
92.5°	28.3	28.0	26.2	24.2	19.9	19.9	19.7	12.4	21.5	30.5	43.9
95°	26.0	26.0	30.5	38.4	56.5	57.7	38.4	35.0	49.7	70.1	88.2
97.5°	70.3	83.7	102.6	106.3	100.6	75.1	71.9	66.9	91.1	111.2	140.4
100°	130.0	147.0	160.5	133.4	105.1	104.0	97.2	95.0	121.0	140.2	168.4
102.5°	203.3	208.5	161.4	146.1	139.5	134.8	124.4	123.0	149.0	175.5	199.2
105°	220.4	197.8	199.0	199.0	194.4	185.4	166.2	165.1	194.4	225.0	254.4
107.5°	259.3	262.7	268.6	267.2	262.0	237.9	215.2	210.0	236.5	273.1	305.5
110°	310.9	314.3	316.5	314.3	306.4	275.8	248.7	240.8	264.5	303.0	338.0



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	360.6	363.1	368.1	361.3	348.0	312.9	282.2	270.6	294.4	333.7	369.7
115°	439.8	439.8	440.9	437.5	410.4	374.2	333.5	316.5	336.9	373.1	412.6
117.5°	517.5	518.9	514.4	505.3	473.9	431.8	386.2	359.0	375.1	413.3	454.0
120°	566.4	568.6	564.1	550.6	520.0	472.5	420.5	388.9	401.3	438.6	479.3
122.5°	617.0	616.6	611.1	595.8	559.8	510.5	459.4	420.5	425.7	460.3	500.1
125°	687.3	686.2	681.7	663.6	626.3	575.4	515.5	468.0	461.2	490.6	531.3
127.5°	754.3	751.8	744.8	722.8	684.6	635.6	569.8	516.0	500.8	519.4	556.7
130°	800.4	797.0	784.6	760.8	723.5	677.2	610.5	549.4	527.9	539.2	572.0
132.5°	844.7	835.0	824.4	798.8	764.2	716.1	648.5	584.7	555.1	560.0	585.6
135°	901.0	892.0	878.4	853.5	820.7	773.3	705.4	636.5	595.8	591.2	605.9
137.5°	950.5	941.0	925.7	904.2	871.2	828.9	763.8	691.0	639.6	624.5	630.1
140°	981.3	970.0	956.4	934.9	905.5	861.4	798.1	728.0	670.4	648.9	645.5
142.5°	1006.6	998.0	983.5	963.9	938.1	894.0	832.5	763.3	702.0	674.2	666.3
145°	1044.6	1037.8	1022.0	1003.9	982.4	938.3	881.8	812.8	751.8	715.6	698.6
147.5°	1076.7	1071.3	1058.8	1037.6	1019.5	977.2	925.7	864.6	802.0	757.2	735.3
150°	1096.6	1092.1	1079.6	1059.3	1041.2	1001.6	951.9	895.4	835.4	788.0	759.7
152.5°	1115.6	1111.1	1096.8	1076.5	1061.1	1024.2	979.0	925.2	864.4	816.9	787.7
155°	1140.7	1135.0	1121.5	1102.2	1088.7	1054.8	1012.9	965.4	913.4	863.7	830.9
157.5°	1160.6	1153.6	1140.9	1124.4	1109.9	1078.7	1042.3	1001.4	955.9	908.5	875.0
160°	1172.3	1164.4	1150.8	1136.1	1122.6	1093.2	1060.4	1023.1	981.3	938.3	902.1
162.5°	1180.5	1173.5	1157.2	1144.3	1132.5	1105.9	1074.9	1041.2	1003.9	966.3	932.9
165°	1189.3	1181.4	1164.4	1154.2	1144.1	1121.5	1094.3	1067.2	1035.5	1005.0	977.9
167.5°	1190.0	1183.4	1166.4	1156.5	1149.0	1129.6	1107.7	1086.9	1062.2	1038.2	1015.6
170°	1188.2	1182.5	1165.5	1156.5	1150.8	1135.0	1115.8	1097.7	1078.5	1058.1	1040.1
172.5°	1181.8	1176.2	1160.1	1152.9	1149.9	1135.9	1120.3	1106.8	1090.3	1075.3	1060.9
175°	1165.5	1161.0	1147.5	1142.9	1144.1	1135.0	1123.7	1115.8	1105.6	1096.6	1088.7
177.5°	1141.8	1139.1	1129.1	1129.1	1132.8	1127.3	1123.7	1120.1	1115.6	1112.9	1110.1
180°	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9	2000.9
2.5°	1997.3	1994.0	1996.0	1997.8	1998.8	1999.8	1998.8	1997.8	1996.0	1994.0	1997.3
5°	1991.8	1987.5	1988.7	1991.2	1997.5	2003.7	1997.5	1991.2	1988.7	1987.5	1991.8
7.5°	1976.6	1972.6	1974.1	1976.9	1983.4	1989.9	1983.4	1976.9	1974.1	1972.6	1976.6
10°	1962.2	1958.5	1961.0	1964.1	1969.1	1974.1	1969.1	1964.1	1961.0	1958.5	1962.2
12.5°	1947.1	1943.3	1944.8	1947.3	1952.9	1958.4	1952.9	1947.3	1944.8	1943.3	1947.1
15°	1916.5	1913.1	1915.0	1917.6	1922.6	1927.6	1922.6	1917.6	1915.0	1913.1	1916.5
17.5°	1878.5	1875.4	1877.6	1880.3	1884.7	1889.0	1884.7	1880.3	1877.6	1875.4	1878.5
20°	1851.4	1847.6	1848.3	1849.8	1854.2	1858.6	1854.2	1849.8	1848.3	1847.6	1851.4
22.5°	1820.7	1816.2	1814.8	1815.1	1820.5	1825.9	1820.5	1815.1	1814.8	1816.2	1820.7
25°	1769.0	1764.7	1762.8	1762.5	1766.8	1771.2	1766.8	1762.5	1762.8	1764.7	1769.0
27.5°	1711.6	1708.0	1706.8	1706.6	1709.8	1712.9	1709.8	1706.6	1706.8	1708.0	1711.6
30°	1670.1	1666.3	1665.1	1664.9	1668.1	1671.2	1668.1	1664.9	1665.1	1666.3	1670.1
32.5°	1624.4	1620.6	1620.4	1621.1	1624.7	1628.4	1624.7	1621.1	1620.4	1620.6	1624.4
35°	1554.9	1551.7	1552.4	1553.6	1556.7	1559.9	1556.7	1553.6	1552.4	1551.7	1554.9
37.5°	1484.4	1481.2	1481.1	1481.6	1484.2	1486.9	1484.2	1481.6	1481.1	1481.2	1484.4
40°	1435.1	1431.3	1430.7	1431.0	1434.1	1437.3	1434.1	1431.0	1430.7	1431.3	1435.1
42.5°	1382.7	1380.0	1380.4	1381.0	1382.7	1384.3	1382.7	1381.0	1380.4	1380.0	1382.7
45°	1303.4	1300.6	1300.6	1300.9	1302.2	1303.4	1302.2	1300.9	1300.6	1300.6	1303.4
47.5°	1220.8	1218.2	1217.5	1217.4	1219.4	1221.4	1219.4	1217.4	1217.5	1218.2	1220.8
50°	1163.3	1160.5	1159.2	1158.9	1161.4	1163.9	1161.4	1158.9	1159.2	1160.5	1163.3
52.5°	1105.8	1102.7	1101.0	1100.2	1102.2	1104.2	1102.2	1100.2	1101.0	1102.7	1105.8
55°	1017.8	1014.7	1012.2	1010.6	1011.9	1013.1	1011.9	1010.6	1012.2	1014.7	1017.8
57.5°	925.7	922.6	919.6	917.8	919.5	921.3	919.5	917.8	919.6	922.6	925.7
60°	862.8	859.7	857.2	855.6	856.9	858.1	856.9	855.6	857.2	859.7	862.8
62.5°	800.0	796.6	794.1	792.5	793.8	795.0	793.8	792.5	794.1	796.6	800.0
65°	705.0	701.9	699.4	697.7	698.3	698.9	698.3	697.7	699.4	701.9	705.0
67.5°	608.6	604.9	601.3	598.8	599.8	600.8	599.8	598.8	601.3	604.9	608.6
70°	544.1	540.9	537.8	535.5	535.5	535.5	535.5	535.5	537.8	540.9	544.1
72.5°	478.9	475.8	473.2	471.2	471.2	471.2	471.2	471.2	473.2	475.8	478.9
75°	382.8	380.3	377.2	374.7	374.0	373.4	374.0	374.7	377.2	380.3	382.8
77.5°	285.0	282.6	280.2	278.2	277.5	276.7	277.5	278.2	280.2	282.6	285.0
80°	225.0	223.1	221.2	219.5	218.3	217.0	218.3	219.5	221.2	223.1	225.0
82.5°	166.4	164.0	161.1	159.3	160.5	161.8	160.5	159.3	161.1	164.0	166.4
85°	85.5	83.3	80.8	78.8	78.1	77.5	78.1	78.8	80.8	83.3	85.5
87.5°	28.5	28.3	27.9	27.2	27.6	26.6	27.6	27.2	27.9	28.3	28.5
90°	26.0	33.9	41.8	46.4	50.9	48.6	50.9	46.4	41.8	33.9	26.0
92.5°	52.2	65.6	75.3	83.4	87.0	86.6	87.0	83.4	75.3	65.6	52.2
95°	105.1	121.0	136.8	148.1	154.9	152.6	154.9	148.1	136.8	121.0	105.1
97.5°	162.1	183.4	201.0	211.6	218.4	222.9	218.4	211.6	201.0	183.4	162.1
100°	200.1	220.4	240.8	253.2	264.5	269.1	264.5	253.2	240.8	220.4	200.1
102.5°	230.8	257.5	279.7	293.0	302.5	307.0	302.5	293.0	279.7	257.5	230.8
105°	281.5	309.8	333.5	350.5	360.6	364.0	360.6	350.5	333.5	309.8	281.5
107.5°	332.1	361.3	383.2	402.0	414.4	421.7	414.4	402.0	383.2	361.3	332.1
110°	371.9	395.7	419.4	436.4	448.8	453.3	448.8	436.4	419.4	395.7	371.9



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	405.4	431.8	455.6	472.5	486.8	493.1	486.8	472.5	455.6	431.8	405.4
115°	452.2	487.2	508.7	524.6	534.7	540.4	534.7	524.6	508.7	487.2	452.2
117.5°	491.1	527.7	551.2	563.4	568.2	572.3	568.2	563.4	551.2	527.7	491.1
120°	515.5	549.4	576.6	592.4	598.0	600.3	598.0	592.4	576.6	549.4	515.5
122.5°	538.1	570.2	596.5	615.9	625.2	627.4	625.2	615.9	596.5	570.2	538.1
125°	569.8	600.3	627.4	646.6	656.8	662.5	656.8	646.6	627.4	600.3	569.8
127.5°	597.4	630.4	655.2	672.6	682.6	687.1	682.6	672.6	655.2	630.4	597.4
130°	612.7	646.6	671.5	690.7	699.8	704.3	699.8	690.7	671.5	646.6	612.7
132.5°	624.5	660.2	686.0	703.4	713.3	717.9	713.3	703.4	686.0	660.2	624.5
135°	638.7	676.0	703.2	720.1	729.2	733.7	729.2	720.1	703.2	676.0	638.7
137.5°	651.2	685.1	713.3	731.2	739.3	742.3	739.3	731.2	713.3	685.1	651.2
140°	660.2	689.6	717.9	734.8	743.9	745.0	743.9	734.8	717.9	689.6	660.2
142.5°	672.0	695.0	719.7	736.6	745.7	747.7	745.7	736.6	719.7	695.0	672.0
145°	693.0	706.6	723.5	739.3	747.3	749.5	747.3	739.3	723.5	706.6	693.0
147.5°	719.4	723.7	732.6	743.0	750.6	752.2	750.6	743.0	732.6	723.7	719.4
150°	739.3	738.2	741.6	748.4	755.2	754.0	755.2	748.4	741.6	738.2	739.3
152.5°	762.0	755.4	755.2	758.3	761.5	761.3	761.5	758.3	755.2	755.4	762.0
155°	800.4	788.0	781.2	778.9	778.9	777.8	778.9	778.9	781.2	788.0	800.4
157.5°	842.7	825.3	815.1	809.7	808.1	805.6	808.1	809.7	815.1	825.3	842.7
160°	871.6	852.4	842.2	833.2	829.8	826.4	829.8	833.2	842.2	852.4	871.6
162.5°	898.7	880.4	869.4	861.2	857.8	852.6	857.8	861.2	869.4	880.4	898.7
165°	942.8	923.6	911.2	904.4	899.9	895.4	899.9	904.4	911.2	923.6	942.8
167.5°	986.9	965.9	957.8	950.1	945.8	937.6	945.8	950.1	957.8	965.9	986.9
170°	1014.1	994.8	990.3	983.5	975.6	966.6	975.6	983.5	990.3	994.8	1014.1
172.5°	1037.6	1024.7	1020.2	1013.4	1010.9	1003.7	1010.9	1013.4	1020.2	1024.7	1037.6
175°	1071.7	1061.5	1061.5	1060.4	1057.0	1050.2	1057.0	1060.4	1061.5	1061.5	1071.7
177.5°	1100.2	1094.8	1098.4	1098.4	1097.5	1091.2	1097.5	1098.4	1098.4	1094.8	1100.2
180°	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2000.9	2000.9	2000.9	2000.9
2.5°	2005.8	2009.8	2000.3	1990.8
5°	2001.9	2006.2	1993.7	1981.2
7.5°	1986.2	1990.2	1977.7	1965.1
10°	1972.3	1976.6	1964.1	1951.6
12.5°	1956.1	1959.7	1947.2	1934.7
15°	1925.3	1928.7	1916.2	1903.7
17.5°	1886.6	1889.8	1878.0	1866.2
20°	1859.5	1862.8	1851.6	1840.3
22.5°	1828.3	1831.3	1820.0	1808.7
25°	1775.9	1778.3	1767.0	1755.7
27.5°	1717.3	1719.3	1709.9	1700.5
30°	1676.4	1678.7	1669.3	1659.9
32.5°	1631.6	1634.9	1626.0	1617.1
35°	1561.7	1565.0	1557.5	1550.0
37.5°	1490.8	1494.2	1488.4	1482.7
40°	1442.0	1445.6	1439.3	1433.1
42.5°	1388.6	1391.8	1387.1	1382.3
45°	1309.1	1312.2	1307.8	1303.4
47.5°	1225.2	1227.6	1224.2	1220.8
50°	1167.7	1169.9	1165.5	1161.1
52.5°	1110.2	1112.2	1107.4	1102.5
55°	1021.6	1023.0	1017.4	1011.7
57.5°	929.0	930.0	924.5	919.0
60°	866.6	868.2	863.1	858.1
62.5°	804.2	806.2	801.1	796.1
65°	708.8	710.5	706.1	701.7
67.5°	612.2	614.0	610.2	606.5
70°	547.2	548.6	544.9	541.1
72.5°	482.6	484.5	481.2	478.0
75°	384.7	385.6	383.7	381.9
77.5°	287.4	289.1	289.1	289.1
80°	226.9	228.3	228.3	228.3
82.5°	168.2	169.9	170.9	171.9
85°	87.4	89.1	90.3	91.6
87.5°	28.9	28.7	28.8	28.9
90°	20.3	12.4	7.9	3.4
92.5°	43.9	30.5	21.5	12.4
95°	88.2	70.1	49.7	35.0
97.5°	140.4	111.2	91.1	66.9
100°	168.4	140.2	121.0	95.0
102.5°	199.2	175.5	149.0	123.0
105°	254.4	225.0	194.4	165.1
107.5°	305.5	273.1	236.5	210.0
110°	338.0	303.0	264.5	240.8



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	369.7	333.7	294.4	270.6
115°	412.6	373.1	336.9	316.5
117.5°	454.0	413.3	375.1	359.0
120°	479.3	438.6	401.3	388.9
122.5°	500.1	460.3	425.7	420.5
125°	531.3	490.6	461.2	468.0
127.5°	556.7	519.4	500.8	516.0
130°	572.0	539.2	527.9	549.4
132.5°	585.6	560.0	555.1	584.7
135°	605.9	591.2	595.8	636.5
137.5°	630.1	624.5	639.6	691.0
140°	645.5	648.9	670.4	728.0
142.5°	666.3	674.2	702.0	763.3
145°	698.6	715.6	751.8	812.8
147.5°	735.3	757.2	802.0	864.6
150°	759.7	788.0	835.4	895.4
152.5°	787.7	816.9	864.4	925.2
155°	830.9	863.7	913.4	965.4
157.5°	875.0	908.5	955.9	1001.4
160°	902.1	938.3	981.3	1023.1
162.5°	932.9	966.3	1003.9	1041.2
165°	977.9	1005.0	1035.5	1067.2
167.5°	1015.6	1038.2	1062.2	1086.9
170°	1040.1	1058.1	1078.5	1097.7
172.5°	1060.9	1075.3	1090.3	1106.8
175°	1088.7	1096.6	1105.6	1115.8
177.5°	1110.1	1112.9	1115.6	1120.1
180°	1119.2	1119.2	1119.2	1119.2



TEST NUMBER: P1427742

CATALOG NUMBER: SQ2W-F-K-075U-125D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.08	22.09	21.91	22.94	24.01	20.99	22.00	21.82	22.86	23.92
	3H	22.88	23.79	23.72	24.65	25.74	22.77	23.68	23.62	24.55	25.64
	4H	23.58	24.44	24.44	25.31	26.41	23.46	24.32	24.32	25.20	26.30
	6H	24.02	24.82	24.90	25.70	26.81	23.88	24.68	24.76	25.55	26.67
	8H	24.19	24.94	25.07	25.84	26.96	24.03	24.79	24.91	25.69	26.80
	12H	24.28	25.00	25.16	25.89	27.03	24.10	24.82	24.99	25.71	26.86
4H	2H	21.67	22.53	22.54	23.40	24.51	21.61	22.47	22.47	23.34	24.44
	3H	23.71	24.43	24.58	25.33	26.45	23.62	24.33	24.49	25.24	26.36
	4H	24.53	25.18	25.42	26.08	27.23	24.42	25.07	25.31	25.97	27.12
	6H	25.09	25.66	25.99	26.58	27.73	24.95	25.52	25.85	26.44	27.59
	8H	25.31	25.84	26.21	26.76	27.92	25.15	25.68	26.05	26.60	27.76
	12H	25.43	25.91	26.36	26.84	28.01	25.24	25.72	26.17	26.66	27.83
8H	4H	24.79	25.31	25.69	26.23	27.40	24.69	25.22	25.59	26.14	27.30
	6H	25.48	25.92	26.41	26.88	28.04	25.35	25.79	26.28	26.75	27.91
	8H	25.79	26.18	26.73	27.13	28.31	25.63	26.02	26.58	26.97	28.15
	12H	25.98	26.32	26.92	27.26	28.49	25.79	26.13	26.73	27.07	28.30
12H	4H	24.79	25.26	25.71	26.20	27.37	24.69	25.17	25.62	26.11	27.28
	6H	25.53	25.92	26.48	26.87	28.05	25.41	25.80	26.35	26.75	27.93
	8H	25.87	26.22	26.82	27.16	28.39	25.72	26.07	26.67	27.01	28.24