

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427775

Luminaire Tested: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427775
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6969.4 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	77	71	66	76	70	65	60	55	51	48	41	39	37	29	27	26	21
3	77	68	61	55	69	61	55	50	48	44	40	36	34	31	25	24	22	17
4	70	60	52	46	63	54	47	42	43	38	34	32	29	27	23	21	19	15
5	64	53	45	39	58	48	41	36	38	33	29	29	26	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	17	17	14	13	10
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	25	21	26	21	17	20	16	14	14	12	10	8
10	44	32	25	20	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11820	11820	11820	11820
5°	11749	11883	11749	11883
10°	11707	11842	11707	11842
15°	11644	11789	11644	11789
20°	11570	11685	11570	11685
25°	11444	11546	11444	11546
30°	11324	11400	11324	11400
35°	11178	11251	11178	11251
40°	11050	11084	11050	11084
45°	10889	10889	10889	10889
50°	10670	10698	10670	10698
55°	10421	10435	10421	10435
60°	10139	10139	10139	10139
65°	9811	9769	9811	9769
70°	9347	9248	9347	9248
75°	8715	8521	8715	8521
80°	7764	7382	7764	7382
85°	6206	5261	6206	5261

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 10962 cd/sqm



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	1.0
10°-20°	197.9	2.8
20°-30°	297.9	4.3
30°-40°	356.3	5.1
40°-50°	367.9	5.3
50°-60°	331.8	4.8
60°-70°	254.2	3.6
70°-80°	146.9	2.1
80°-90°	45.1	0.6
90°-100°	133.6	1.9
100°-110°	389.6	5.6
110°-120°	635.9	9.1
120°-130°	806.9	11.6
130°-140°	863.4	12.4
140°-150°	806.2	11.6
150°-160°	663.4	9.5
160°-170°	444.9	6.4
170°-180°	158.0	2.3
0°-30°	565.2	8.1
0°-40°	921.5	13.2
0°-60°	1621.2	23.3
0°-90°	2067.4	29.7
90°-120°	1159.2	16.6
90°-150°	3635.7	52.2
90°-180°	4902.0	70.3
0°-180°	6969.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	732	732	732	732	732	
5°	725	733	725	733	725	69
15°	697	705	697	705	697	196
25°	642	648	642	648	642	296
35°	567	571	567	571	567	355
45°	477	477	477	477	477	367
55°	370	371	370	371	370	331
65°	257	256	257	256	257	254
75°	140	137	140	137	140	148
85°	34	28	34	28	34	39
90°	5	37	5	73	5	6
95°	53	39	53	229	53	63
105°	248	397	248	546	248	263
115°	475	658	475	811	475	468
125°	702	1043	702	994	702	628
135°	955	1365	955	1101	955	738
145°	1219	1574	1219	1124	1219	763
155°	1448	1709	1448	1167	1448	666
165°	1601	1782	1601	1343	1601	451
175°	1674	1745	1674	1575	1674	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	728.4	731.9	735.4	733.9	730.8	729.6	730.3	731.0	731.4	731.7	731.4
5°	724.9	729.5	734.1	732.5	728.8	727.2	727.7	728.6	730.9	733.2	730.9
7.5°	719.0	723.6	728.2	726.7	723.2	721.8	722.3	723.3	725.7	728.1	725.7
10°	714.1	718.7	723.2	721.6	718.0	716.6	717.5	718.7	720.5	722.3	720.5
12.5°	707.9	712.5	717.1	715.7	712.4	711.1	711.6	712.5	714.5	716.6	714.5
15°	696.6	701.1	705.7	704.5	701.3	700.0	700.7	701.7	703.5	705.3	703.5
17.5°	682.8	687.1	691.5	690.3	687.3	686.2	687.0	688.0	689.6	691.2	689.6
20°	673.4	677.5	681.6	680.4	677.4	676.0	676.3	676.8	678.5	680.1	678.5
22.5°	661.8	665.9	670.1	669.0	666.2	664.5	664.0	664.2	666.1	668.1	666.1
25°	642.4	646.5	650.7	649.8	647.3	645.7	645.0	644.9	646.5	648.1	646.5
27.5°	622.2	625.6	629.1	628.4	626.3	625.0	624.5	624.5	625.6	626.7	625.6
30°	607.4	610.8	614.2	613.4	611.1	609.7	609.2	609.2	610.3	611.5	610.3
32.5°	591.7	594.9	598.2	597.0	594.4	593.0	592.9	593.2	594.5	595.8	594.5
35°	567.1	569.9	572.6	571.4	568.9	567.8	568.0	568.5	569.6	570.8	569.6
37.5°	542.5	544.6	546.7	545.5	543.2	542.0	541.9	542.1	543.1	544.0	543.1
40°	524.3	526.6	528.9	527.6	525.1	523.7	523.5	523.6	524.8	525.9	524.8
42.5°	505.8	507.5	509.3	508.1	505.9	504.9	505.1	505.3	505.9	506.5	505.9
45°	476.9	478.5	480.1	479.0	476.9	475.9	475.9	476.0	476.5	476.9	476.5
47.5°	446.7	447.9	449.2	448.3	446.7	445.7	445.5	445.4	446.2	446.9	446.2
50°	424.8	426.4	428.0	427.2	425.6	424.6	424.2	424.0	425.0	425.9	425.0
52.5°	403.4	405.2	407.0	406.2	404.6	403.5	402.8	402.5	403.3	404.0	403.3
55°	370.2	372.3	374.3	373.8	372.4	371.3	370.4	369.8	370.2	370.7	370.2
57.5°	336.3	338.3	340.3	339.9	338.7	337.6	336.5	335.8	336.4	337.1	336.4
60°	314.0	315.8	317.7	317.1	315.7	314.6	313.6	313.1	313.5	314.0	313.5
62.5°	291.3	293.1	295.0	294.3	292.7	291.5	290.5	290.0	290.4	290.9	290.4
65°	256.8	258.4	260.0	259.3	258.0	256.8	255.9	255.3	255.5	255.7	255.5
67.5°	221.9	223.3	224.7	224.0	222.7	221.3	220.0	219.1	219.5	219.8	219.5
70°	198.0	199.4	200.7	200.2	199.1	197.9	196.8	195.9	195.9	195.9	195.9
72.5°	174.9	176.1	177.3	176.6	175.2	174.1	173.1	172.4	172.4	172.4	172.4
75°	139.7	140.4	141.1	140.8	140.1	139.2	138.0	137.1	136.9	136.6	136.9
77.5°	105.8	105.8	105.8	105.1	104.3	103.4	102.5	101.8	101.5	101.3	101.5
80°	83.5	83.5	83.5	83.0	82.3	81.6	80.9	80.3	79.9	79.4	79.9
82.5°	62.9	62.5	62.2	61.6	60.9	60.0	58.9	58.3	58.7	59.2	58.7
85°	33.5	33.1	32.6	32.0	31.3	30.5	29.6	28.8	28.6	28.4	28.6
87.5°	11.3	12.3	13.6	14.5	15.0	14.7	13.9	13.7	13.8	13.6	13.8
90°	5.1	11.9	20.3	27.1	32.2	33.9	33.9	35.6	37.3	37.3	37.3
92.5°	18.7	29.5	29.8	29.8	36.3	39.3	42.1	42.4	44.1	44.1	44.1
95°	52.6	57.7	86.5	84.8	57.7	45.8	39.0	39.0	39.0	39.0	39.0
97.5°	100.4	107.9	112.6	150.9	159.4	154.0	125.5	105.5	94.3	89.2	94.3
100°	142.4	145.8	156.0	157.7	200.1	240.8	220.5	195.0	186.5	181.5	186.5
102.5°	184.5	186.5	202.1	209.3	219.1	242.2	312.7	304.9	299.1	298.1	299.1
105°	247.6	249.3	278.1	291.7	298.5	298.5	296.8	330.7	385.0	396.8	385.0
107.5°	315.1	322.9	356.8	393.1	400.9	402.9	394.1	389.0	387.0	388.3	387.0
110°	361.2	373.1	413.8	459.6	471.4	474.8	471.4	466.3	463.0	463.0	463.0



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	406.0	423.3	469.4	522.0	542.0	552.2	544.7	541.0	537.6	540.3	537.6
115°	474.8	500.3	561.3	615.6	656.3	661.4	659.7	659.7	658.0	658.0	658.0
117.5°	538.6	579.3	647.8	710.9	758.0	771.6	778.4	776.3	774.3	777.7	774.3
120°	583.4	630.8	708.9	780.1	825.9	846.2	853.0	849.6	853.0	849.6	853.0
122.5°	630.8	689.2	765.8	839.8	893.7	916.8	924.9	925.6	926.3	924.2	926.3
125°	702.1	773.3	863.2	939.5	995.4	1022.6	1029.4	1031.1	1034.4	1042.9	1034.4
127.5°	774.0	854.7	953.4	1027.0	1084.3	1117.2	1127.7	1131.4	1138.6	1142.3	1138.6
130°	824.2	915.7	1015.8	1085.3	1141.3	1176.9	1195.6	1200.6	1209.1	1207.4	1209.1
132.5°	877.1	972.7	1074.1	1146.4	1198.3	1236.6	1252.5	1267.1	1270.2	1272.5	1270.2
135°	954.7	1058.2	1159.9	1231.2	1280.3	1317.7	1338.0	1351.6	1360.0	1365.1	1360.0
137.5°	1036.5	1145.7	1243.4	1306.8	1356.3	1388.5	1411.6	1425.8	1434.7	1438.7	1434.7
140°	1092.1	1197.2	1292.2	1358.3	1402.4	1434.7	1455.0	1472.0	1482.1	1482.1	1482.1
142.5°	1145.0	1248.8	1341.1	1407.2	1445.9	1475.4	1497.1	1510.0	1521.5	1521.5	1521.5
145°	1219.3	1322.7	1407.5	1473.7	1505.9	1533.0	1556.8	1566.9	1573.7	1573.7	1573.7
147.5°	1297.0	1388.5	1465.9	1529.3	1556.4	1588.3	1607.0	1615.1	1623.6	1619.8	1623.6
150°	1343.1	1427.9	1502.5	1561.8	1589.0	1619.5	1638.2	1644.9	1653.4	1648.3	1653.4
152.5°	1387.9	1468.6	1536.4	1591.7	1614.8	1645.3	1666.6	1673.4	1679.2	1675.5	1679.2
155°	1448.2	1519.5	1582.2	1633.1	1653.4	1682.3	1702.6	1711.1	1717.9	1709.4	1717.9
157.5°	1502.2	1563.5	1618.1	1665.0	1686.7	1711.4	1730.4	1740.9	1747.7	1744.0	1747.7
160°	1534.7	1590.7	1639.9	1683.9	1704.3	1726.3	1746.7	1758.6	1765.3	1760.3	1765.3
162.5°	1561.8	1612.4	1658.8	1698.9	1716.5	1735.8	1760.3	1770.8	1777.6	1771.1	1777.6
165°	1600.9	1641.6	1682.3	1716.2	1731.4	1746.7	1772.1	1784.0	1789.1	1782.3	1789.1
167.5°	1630.4	1661.6	1694.5	1723.6	1734.8	1749.7	1775.2	1785.0	1791.5	1783.0	1791.5
170°	1646.6	1673.8	1702.6	1726.3	1734.8	1748.4	1773.8	1782.3	1787.4	1778.9	1787.4
172.5°	1660.2	1680.6	1704.0	1725.0	1729.4	1740.2	1764.3	1772.8	1776.5	1769.4	1776.5
175°	1673.8	1685.6	1702.6	1716.2	1714.5	1721.3	1741.6	1748.4	1755.2	1745.0	1755.2
177.5°	1680.2	1685.6	1691.1	1699.2	1693.8	1693.8	1708.7	1712.8	1714.1	1708.7	1714.1
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	731.0	730.3	729.6	730.8	733.9	735.4	731.9	728.4	731.9	735.4	733.9
5°	728.6	727.7	727.2	728.8	732.5	734.1	729.5	724.9	729.5	734.1	732.5
7.5°	723.3	722.3	721.8	723.2	726.7	728.2	723.6	719.0	723.6	728.2	726.7
10°	718.7	717.5	716.6	718.0	721.6	723.2	718.7	714.1	718.7	723.2	721.6
12.5°	712.5	711.6	711.1	712.4	715.7	717.1	712.5	707.9	712.5	717.1	715.7
15°	701.7	700.7	700.0	701.3	704.5	705.7	701.1	696.6	701.1	705.7	704.5
17.5°	688.0	687.0	686.2	687.3	690.3	691.5	687.1	682.8	687.1	691.5	690.3
20°	676.8	676.3	676.0	677.4	680.4	681.6	677.5	673.4	677.5	681.6	680.4
22.5°	664.2	664.0	664.5	666.2	669.0	670.1	665.9	661.8	665.9	670.1	669.0
25°	644.9	645.0	645.7	647.3	649.8	650.7	646.5	642.4	646.5	650.7	649.8
27.5°	624.5	624.5	625.0	626.3	628.4	629.1	625.6	622.2	625.6	629.1	628.4
30°	609.2	609.2	609.7	611.1	613.4	614.2	610.8	607.4	610.8	614.2	613.4
32.5°	593.2	592.9	593.0	594.4	597.0	598.2	594.9	591.7	594.9	598.2	597.0
35°	568.5	568.0	567.8	568.9	571.4	572.6	569.9	567.1	569.9	572.6	571.4
37.5°	542.1	541.9	542.0	543.2	545.5	546.7	544.6	542.5	544.6	546.7	545.5
40°	523.6	523.5	523.7	525.1	527.6	528.9	526.6	524.3	526.6	528.9	527.6
42.5°	505.3	505.1	504.9	505.9	508.1	509.3	507.5	505.8	507.5	509.3	508.1
45°	476.0	475.9	475.9	476.9	479.0	480.1	478.5	476.9	478.5	480.1	479.0
47.5°	445.4	445.5	445.7	446.7	448.3	449.2	447.9	446.7	447.9	449.2	448.3
50°	424.0	424.2	424.6	425.6	427.2	428.0	426.4	424.8	426.4	428.0	427.2
52.5°	402.5	402.8	403.5	404.6	406.2	407.0	405.2	403.4	405.2	407.0	406.2
55°	369.8	370.4	371.3	372.4	373.8	374.3	372.3	370.2	372.3	374.3	373.8
57.5°	335.8	336.5	337.6	338.7	339.9	340.3	338.3	336.3	338.3	340.3	339.9
60°	313.1	313.6	314.6	315.7	317.1	317.7	315.8	314.0	315.8	317.7	317.1
62.5°	290.0	290.5	291.5	292.7	294.3	295.0	293.1	291.3	293.1	295.0	294.3
65°	255.3	255.9	256.8	258.0	259.3	260.0	258.4	256.8	258.4	260.0	259.3
67.5°	219.1	220.0	221.3	222.7	224.0	224.7	223.3	221.9	223.3	224.7	224.0
70°	195.9	196.8	197.9	199.1	200.2	200.7	199.4	198.0	199.4	200.7	200.2
72.5°	172.4	173.1	174.1	175.2	176.6	177.3	176.1	174.9	176.1	177.3	176.6
75°	137.1	138.0	139.2	140.1	140.8	141.1	140.4	139.7	140.4	141.1	140.8
77.5°	101.8	102.5	103.4	104.3	105.1	105.8	105.8	105.8	105.8	105.8	105.1
80°	80.3	80.9	81.6	82.3	83.0	83.5	83.5	83.5	83.5	83.5	83.0
82.5°	58.3	58.9	60.0	60.9	61.6	62.2	62.5	62.9	62.5	62.2	61.6
85°	28.8	29.6	30.5	31.3	32.0	32.6	33.1	33.5	33.1	32.6	32.0
87.5°	13.7	13.9	14.7	15.0	14.5	13.6	12.3	11.3	12.3	13.3	15.2
90°	35.6	33.9	33.9	32.2	27.1	20.3	11.9	5.1	11.9	18.7	30.5
92.5°	42.4	42.1	39.3	36.3	29.8	29.8	29.5	18.7	32.2	45.8	65.8
95°	39.0	39.0	45.8	57.7	84.8	86.5	57.7	52.6	74.6	105.1	132.3
97.5°	105.5	125.5	154.0	159.4	150.9	112.6	107.9	100.4	136.7	166.9	210.6
100°	195.0	220.5	240.8	200.1	157.7	156.0	145.8	142.4	181.5	210.3	252.7
102.5°	304.9	312.7	242.2	219.1	209.3	202.1	186.5	184.5	223.5	263.2	298.8
105°	330.7	296.8	298.5	298.5	291.7	278.1	249.3	247.6	291.7	337.5	381.6
107.5°	389.0	394.1	402.9	400.9	393.1	356.8	322.9	315.1	354.8	409.7	458.2
110°	466.3	471.4	474.8	471.4	459.6	413.8	373.1	361.2	396.8	454.5	507.0

TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	541.0	544.7	552.2	542.0	522.0	469.4	423.3	406.0	441.6	500.6	554.5
115°	659.7	659.7	661.4	656.3	615.6	561.3	500.3	474.8	505.4	559.6	619.0
117.5°	776.3	778.4	771.6	758.0	710.9	647.8	579.3	538.6	562.7	620.0	681.0
120°	849.6	853.0	846.2	825.9	780.1	708.9	630.8	583.4	602.0	658.0	719.0
122.5°	925.6	924.9	916.8	893.7	839.8	765.8	689.2	630.8	638.6	690.5	750.2
125°	1031.1	1029.4	1022.6	995.4	939.5	863.2	773.3	702.1	691.9	736.0	797.0
127.5°	1131.4	1127.7	1117.2	1084.3	1027.0	953.4	854.7	774.0	751.2	779.1	835.0
130°	1200.6	1195.6	1176.9	1141.3	1085.3	1015.8	915.7	824.2	791.9	808.9	858.1
132.5°	1267.1	1252.5	1236.6	1198.3	1146.4	1074.1	972.7	877.1	832.6	840.1	878.4
135°	1351.6	1338.0	1317.7	1280.3	1231.2	1159.9	1058.2	954.7	893.7	886.9	909.0
137.5°	1425.8	1411.6	1388.5	1356.3	1306.8	1243.4	1145.7	1036.5	959.5	936.8	945.2
140°	1472.0	1455.0	1434.7	1402.4	1358.3	1292.2	1197.2	1092.1	1005.6	973.4	968.3
142.5°	1510.0	1497.1	1475.4	1445.9	1407.2	1341.1	1248.8	1145.0	1053.1	1011.4	999.5
145°	1566.9	1556.8	1533.0	1505.9	1473.7	1407.5	1322.7	1219.3	1127.7	1073.5	1048.0
147.5°	1615.1	1607.0	1588.3	1556.4	1529.3	1465.9	1388.5	1297.0	1203.0	1135.9	1103.0
150°	1644.9	1638.2	1619.5	1589.0	1561.8	1502.5	1427.9	1343.1	1253.2	1182.0	1139.6
152.5°	1673.4	1666.6	1645.3	1614.8	1591.7	1536.4	1468.6	1387.9	1296.6	1225.4	1181.6
155°	1711.1	1702.6	1682.3	1653.4	1633.1	1582.2	1519.5	1448.2	1370.2	1295.6	1246.4
157.5°	1740.9	1730.4	1711.4	1686.7	1665.0	1618.1	1563.5	1502.2	1434.0	1362.8	1312.6
160°	1758.6	1746.7	1726.3	1704.3	1683.9	1639.9	1590.7	1534.7	1472.0	1407.5	1353.3
162.5°	1770.8	1760.3	1735.8	1716.5	1698.9	1658.8	1612.4	1561.8	1505.9	1449.6	1399.4
165°	1784.0	1772.1	1746.7	1731.4	1716.2	1682.3	1641.6	1600.9	1553.4	1507.6	1466.9
167.5°	1785.0	1775.2	1749.7	1734.8	1723.6	1694.5	1661.6	1630.4	1593.4	1557.4	1523.5
170°	1782.3	1773.8	1748.4	1734.8	1726.3	1702.6	1673.8	1646.6	1617.8	1587.3	1560.2
172.5°	1772.8	1764.3	1740.2	1729.4	1725.0	1704.0	1680.6	1660.2	1635.4	1613.1	1591.4
175°	1748.4	1741.6	1721.3	1714.5	1716.2	1702.6	1685.6	1673.8	1658.5	1644.9	1633.1
177.5°	1712.8	1708.7	1693.8	1693.8	1699.2	1691.1	1685.6	1680.2	1673.4	1669.4	1665.3
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	730.8	729.6	730.3	731.0	731.4	731.7	731.4	731.0	730.3	729.6	730.8
5°	728.8	727.2	727.7	728.6	730.9	733.2	730.9	728.6	727.7	727.2	728.8
7.5°	723.2	721.8	722.3	723.3	725.7	728.1	725.7	723.3	722.3	721.8	723.2
10°	718.0	716.6	717.5	718.7	720.5	722.3	720.5	718.7	717.5	716.6	718.0
12.5°	712.4	711.1	711.6	712.5	714.5	716.6	714.5	712.5	711.6	711.1	712.4
15°	701.3	700.0	700.7	701.7	703.5	705.3	703.5	701.7	700.7	700.0	701.3
17.5°	687.3	686.2	687.0	688.0	689.6	691.2	689.6	688.0	687.0	686.2	687.3
20°	677.4	676.0	676.3	676.8	678.5	680.1	678.5	676.8	676.3	676.0	677.4
22.5°	666.2	664.5	664.0	664.2	666.1	668.1	666.1	664.2	664.0	664.5	666.2
25°	647.3	645.7	645.0	644.9	646.5	648.1	646.5	644.9	645.0	645.7	647.3
27.5°	626.3	625.0	624.5	624.5	625.6	626.7	625.6	624.5	624.5	625.0	626.3
30°	611.1	609.7	609.2	609.2	610.3	611.5	610.3	609.2	609.2	609.7	611.1
32.5°	594.4	593.0	592.9	593.2	594.5	595.8	594.5	593.2	592.9	593.0	594.4
35°	568.9	567.8	568.0	568.5	569.6	570.8	569.6	568.5	568.0	567.8	568.9
37.5°	543.2	542.0	541.9	542.1	543.1	544.0	543.1	542.1	541.9	542.0	543.2
40°	525.1	523.7	523.5	523.6	524.8	525.9	524.8	523.6	523.5	523.7	525.1
42.5°	505.9	504.9	505.1	505.3	505.9	506.5	505.9	505.3	505.1	504.9	505.9
45°	476.9	475.9	475.9	476.0	476.5	476.9	476.5	476.0	475.9	475.9	476.9
47.5°	446.7	445.7	445.5	445.4	446.2	446.9	446.2	445.4	445.5	445.7	446.7
50°	425.6	424.6	424.2	424.0	425.0	425.9	425.0	424.0	424.2	424.6	425.6
52.5°	404.6	403.5	402.8	402.5	403.3	404.0	403.3	402.5	402.8	403.5	404.6
55°	372.4	371.3	370.4	369.8	370.2	370.7	370.2	369.8	370.4	371.3	372.4
57.5°	338.7	337.6	336.5	335.8	336.4	337.1	336.4	335.8	336.5	337.6	338.7
60°	315.7	314.6	313.6	313.1	313.5	314.0	313.5	313.1	313.6	314.6	315.7
62.5°	292.7	291.5	290.5	290.0	290.4	290.9	290.4	290.0	290.5	291.5	292.7
65°	258.0	256.8	255.9	255.3	255.5	255.7	255.5	255.3	255.9	256.8	258.0
67.5°	222.7	221.3	220.0	219.1	219.5	219.8	219.5	219.1	220.0	221.3	222.7
70°	199.1	197.9	196.8	195.9	195.9	195.9	195.9	195.9	196.8	197.9	199.1
72.5°	175.2	174.1	173.1	172.4	172.4	172.4	172.4	172.4	173.1	174.1	175.2
75°	140.1	139.2	138.0	137.1	136.9	136.6	136.9	137.1	138.0	139.2	140.1
77.5°	104.3	103.4	102.5	101.8	101.5	101.3	101.5	101.8	102.5	103.4	104.3
80°	82.3	81.6	80.9	80.3	79.9	79.4	79.9	80.3	80.9	81.6	82.3
82.5°	60.9	60.0	58.9	58.3	58.7	59.2	58.7	58.3	58.9	60.0	60.9
85°	31.3	30.5	29.6	28.8	28.6	28.4	28.6	28.8	29.6	30.5	31.3
87.5°	16.3	18.1	19.7	20.5	21.6	20.8	21.6	20.5	19.7	18.1	16.3
90°	39.0	50.9	62.7	69.5	76.3	72.9	76.3	69.5	62.7	50.9	39.0
92.5°	78.3	98.4	112.9	125.2	130.6	129.9	130.6	125.2	112.9	98.4	78.3
95°	157.7	181.5	205.2	222.2	232.3	228.9	232.3	222.2	205.2	181.5	157.7
97.5°	243.2	275.1	301.5	317.5	327.6	334.4	327.6	317.5	301.5	275.1	243.2
100°	300.2	330.7	361.2	379.9	396.8	403.6	396.8	379.9	361.2	330.7	300.2
102.5°	346.3	386.3	419.5	439.6	453.8	460.6	453.8	439.6	419.5	386.3	346.3
105°	422.3	464.7	500.3	525.7	541.0	546.1	541.0	525.7	500.3	464.7	422.3
107.5°	498.2	542.0	574.9	603.0	621.7	632.5	621.7	603.0	574.9	542.0	498.2
110°	557.9	593.5	629.1	654.6	673.2	680.0	673.2	654.6	629.1	593.5	557.9



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	608.1	647.8	683.4	708.9	730.2	739.7	730.2	708.9	683.4	647.8	608.1
115°	678.3	730.9	763.1	786.9	802.1	810.6	802.1	786.9	763.1	730.9	678.3
117.5°	736.7	791.6	826.9	845.2	852.3	858.4	852.3	845.2	826.9	791.6	736.7
120°	773.3	824.2	864.9	888.6	897.1	900.5	897.1	888.6	864.9	824.2	773.3
122.5°	807.2	855.4	894.7	923.9	937.8	941.2	937.8	923.9	894.7	855.4	807.2
125°	854.7	900.5	941.2	970.0	985.3	993.7	985.3	970.0	941.2	900.5	854.7
127.5°	896.1	945.6	982.9	1009.0	1023.9	1030.7	1023.9	1009.0	982.9	945.6	896.1
130°	919.1	970.0	1007.3	1036.1	1049.7	1056.5	1049.7	1036.1	1007.3	970.0	919.1
132.5°	936.8	990.4	1029.0	1055.1	1070.1	1076.8	1070.1	1055.1	1029.0	990.4	936.8
135°	958.1	1014.1	1054.8	1080.2	1093.8	1100.6	1093.8	1080.2	1054.8	1014.1	958.1
137.5°	976.8	1027.7	1070.1	1096.9	1109.1	1113.5	1109.1	1096.9	1070.1	1027.7	976.8
140°	990.4	1034.4	1076.8	1102.3	1115.8	1117.5	1115.8	1102.3	1076.8	1034.4	990.4
142.5°	1008.0	1042.6	1079.6	1105.0	1118.6	1121.6	1118.6	1105.0	1079.6	1042.6	1008.0
145°	1039.5	1059.9	1085.3	1109.1	1120.9	1124.3	1120.9	1109.1	1085.3	1059.9	1039.5
147.5°	1079.2	1085.7	1098.9	1114.5	1126.0	1128.4	1126.0	1114.5	1098.9	1085.7	1079.2
150°	1109.1	1107.4	1112.5	1122.6	1132.8	1131.1	1132.8	1122.6	1112.5	1107.4	1109.1
152.5°	1143.0	1133.1	1132.8	1137.6	1142.3	1142.0	1142.3	1137.6	1132.8	1133.1	1143.0
155°	1200.6	1182.0	1171.8	1168.4	1168.4	1166.7	1168.4	1168.4	1171.8	1182.0	1200.6
157.5°	1264.1	1237.9	1222.7	1214.5	1212.2	1208.4	1212.2	1214.5	1222.7	1237.9	1264.1
160°	1307.5	1278.6	1263.4	1249.8	1244.7	1239.6	1244.7	1249.8	1263.4	1278.6	1307.5
162.5°	1348.2	1320.7	1304.1	1291.9	1286.8	1279.0	1286.8	1291.9	1304.1	1320.7	1348.2
165°	1414.3	1385.5	1366.8	1356.7	1349.9	1343.1	1349.9	1356.7	1366.8	1385.5	1414.3
167.5°	1480.4	1448.9	1436.7	1425.2	1418.7	1406.5	1418.7	1425.2	1436.7	1448.9	1480.4
170°	1521.1	1492.3	1485.5	1475.4	1463.5	1449.9	1463.5	1475.4	1485.5	1492.3	1521.1
172.5°	1556.4	1537.1	1530.3	1520.1	1516.4	1505.5	1516.4	1520.1	1530.3	1537.1	1556.4
175°	1607.6	1592.4	1592.4	1590.7	1585.6	1575.4	1585.6	1590.7	1592.4	1592.4	1607.6
177.5°	1650.4	1642.2	1647.7	1647.7	1646.3	1636.8	1646.3	1647.7	1647.7	1642.2	1650.4
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	732.1	732.1	732.1	732.1
2.5°	733.9	735.4	731.9	728.4
5°	732.5	734.1	729.5	724.9
7.5°	726.7	728.2	723.6	719.0
10°	721.6	723.2	718.7	714.1
12.5°	715.7	717.1	712.5	707.9
15°	704.5	705.7	701.1	696.6
17.5°	690.3	691.5	687.1	682.8
20°	680.4	681.6	677.5	673.4
22.5°	669.0	670.1	665.9	661.8
25°	649.8	650.7	646.5	642.4
27.5°	628.4	629.1	625.6	622.2
30°	613.4	614.2	610.8	607.4
32.5°	597.0	598.2	594.9	591.7
35°	571.4	572.6	569.9	567.1
37.5°	545.5	546.7	544.6	542.5
40°	527.6	528.9	526.6	524.3
42.5°	508.1	509.3	507.5	505.8
45°	479.0	480.1	478.5	476.9
47.5°	448.3	449.2	447.9	446.7
50°	427.2	428.0	426.4	424.8
52.5°	406.2	407.0	405.2	403.4
55°	373.8	374.3	372.3	370.2
57.5°	339.9	340.3	338.3	336.3
60°	317.1	317.7	315.8	314.0
62.5°	294.3	295.0	293.1	291.3
65°	259.3	260.0	258.4	256.8
67.5°	224.0	224.7	223.3	221.9
70°	200.2	200.7	199.4	198.0
72.5°	176.6	177.3	176.1	174.9
75°	140.8	141.1	140.4	139.7
77.5°	105.1	105.8	105.8	105.8
80°	83.0	83.5	83.5	83.5
82.5°	61.6	62.2	62.5	62.9
85°	32.0	32.6	33.1	33.5
87.5°	15.2	13.3	12.3	11.3
90°	30.5	18.7	11.9	5.1
92.5°	65.8	45.8	32.2	18.7
95°	132.3	105.1	74.6	52.6
97.5°	210.6	166.9	136.7	100.4
100°	252.7	210.3	181.5	142.4
102.5°	298.8	263.2	223.5	184.5
105°	381.6	337.5	291.7	247.6
107.5°	458.2	409.7	354.8	315.1
110°	507.0	454.5	396.8	361.2



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	554.5	500.6	441.6	406.0
115°	619.0	559.6	505.4	474.8
117.5°	681.0	620.0	562.7	538.6
120°	719.0	658.0	602.0	583.4
122.5°	750.2	690.5	638.6	630.8
125°	797.0	736.0	691.9	702.1
127.5°	835.0	779.1	751.2	774.0
130°	858.1	808.9	791.9	824.2
132.5°	878.4	840.1	832.6	877.1
135°	909.0	886.9	893.7	954.7
137.5°	945.2	936.8	959.5	1036.5
140°	968.3	973.4	1005.6	1092.1
142.5°	999.5	1011.4	1053.1	1145.0
145°	1048.0	1073.5	1127.7	1219.3
147.5°	1103.0	1135.9	1203.0	1297.0
150°	1139.6	1182.0	1253.2	1343.1
152.5°	1181.6	1225.4	1296.6	1387.9
155°	1246.4	1295.6	1370.2	1448.2
157.5°	1312.6	1362.8	1434.0	1502.2
160°	1353.3	1407.5	1472.0	1534.7
162.5°	1399.4	1449.6	1505.9	1561.8
165°	1466.9	1507.6	1553.4	1600.9
167.5°	1523.5	1557.4	1593.4	1630.4
170°	1560.2	1587.3	1617.8	1646.6
172.5°	1591.4	1613.1	1635.4	1660.2
175°	1633.1	1644.9	1658.5	1673.8
177.5°	1665.3	1669.4	1673.4	1680.2
180°	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427775

CATALOG NUMBER: SQ2W-F-K-125U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.19	14.90	15.30	16.00	17.54	14.10	14.81	15.21	15.92	17.45
	3H	15.96	16.60	17.09	17.72	19.27	15.86	16.50	16.98	17.61	19.16
	4H	16.65	17.26	17.78	18.37	19.93	16.54	17.14	17.67	18.26	19.82
	6H	17.08	17.64	18.22	18.76	20.33	16.94	17.50	18.08	18.62	20.18
	8H	17.24	17.77	18.38	18.90	20.46	17.08	17.61	18.22	18.75	20.31
	12H	17.32	17.82	18.46	18.95	20.53	17.14	17.64	18.29	18.77	20.36
4H	2H	14.75	15.35	15.88	16.47	18.02	14.68	15.29	15.82	16.40	17.96
	3H	16.75	17.26	17.90	18.40	19.97	16.66	17.17	17.80	18.31	19.88
	4H	17.56	18.03	18.71	19.16	20.75	17.45	17.92	18.60	19.05	20.64
	6H	18.11	18.50	19.26	19.66	21.24	17.96	18.36	19.12	19.52	21.10
	8H	18.32	18.69	19.47	19.84	21.43	18.16	18.53	19.31	19.68	21.27
	12H	18.42	18.76	19.59	19.92	21.52	18.24	18.57	19.41	19.73	21.33
8H	4H	17.79	18.17	18.95	19.31	20.91	17.70	18.07	18.85	19.22	20.81
	6H	18.48	18.78	19.65	19.97	21.56	18.34	18.65	19.52	19.84	21.43
	8H	18.78	19.05	19.96	20.21	21.83	18.62	18.89	19.80	20.06	21.67
	12H	18.95	19.19	20.14	20.36	22.00	18.76	19.00	19.95	20.16	21.81
12H	4H	17.78	18.12	18.95	19.28	20.88	17.69	18.02	18.86	19.18	20.78
	6H	18.52	18.79	19.70	19.96	21.57	18.40	18.67	19.58	19.84	21.45
	8H	18.85	19.09	20.03	20.25	21.90	18.70	18.94	19.88	20.10	21.75