

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427787

Luminaire Tested: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427787  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8905.3 lumens  
Efficiency: N/A  
Efficacy: 109.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 81.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	80	74	69	80	74	68	64	61	58	54	50	47	45	40	38	36	31
3	80	70	63	57	73	65	58	53	54	49	45	44	41	38	35	33	31	26
4	73	62	54	48	67	57	50	45	48	43	38	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	38	43	37	33	35	31	28	28	25	23	19
6	62	49	41	36	56	46	38	33	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15
8	53	40	33	27	48	37	30	26	32	26	22	26	22	19	21	18	16	13
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	20	16	14	12
10	46	34	27	22	42	31	25	20	27	21	18	22	18	15	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22927	22927	22927	22927
5°	22787	23047	22787	23047
10°	22707	22969	22707	22969
15°	22582	22866	22582	22866
20°	22439	22663	22439	22663
25°	22197	22393	22197	22393
30°	21962	22111	21962	22111
35°	21681	21819	21681	21819
40°	21435	21498	21435	21498
45°	21121	21121	21121	21121
50°	20697	20747	20697	20747
55°	20211	20239	20211	20239
60°	19665	19665	19665	19665
65°	19025	18949	19025	18949
70°	18127	17938	18127	17938
75°	16905	16531	16905	16531
80°	15063	14319	15063	14319
85°	12041	10189	12041	10189

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 21262 cd/sqm



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	1.5
10°-20°	383.9	4.3
20°-30°	577.9	6.5
30°-40°	691.1	7.8
40°-50°	713.6	8.0
50°-60°	643.6	7.2
60°-70°	493.0	5.5
70°-80°	285.0	3.2
80°-90°	81.0	0.9
90°-100°	133.6	1.5
100°-110°	389.6	4.4
110°-120°	635.9	7.1
120°-130°	806.9	9.1
130°-140°	863.4	9.7
140°-150°	806.2	9.1
150°-160°	663.4	7.4
160°-170°	444.9	5.0
170°-180°	158.0	1.8
0°-30°	1096.2	12.3
0°-40°	1787.2	20.1
0°-60°	3144.4	35.3
0°-90°	4003.4	45.0
90°-120°	1159.2	13.0
90°-150°	3635.7	40.8
90°-180°	4902.0	55.0
0°-180°	8905.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1420	1420	1420	1420	1420	
5°	1406	1422	1406	1422	1406	133
15°	1351	1368	1351	1368	1351	381
25°	1246	1257	1246	1257	1246	574
35°	1100	1107	1100	1107	1100	688
45°	925	925	925	925	925	713
55°	718	719	718	719	718	642
65°	498	496	498	496	498	492
75°	271	265	271	265	271	287
85°	65	55	65	55	65	76
90°	5	37	5	73	5	7
95°	53	39	53	229	53	63
105°	248	397	248	546	248	263
115°	475	658	475	811	475	468
125°	702	1043	702	994	702	628
135°	955	1365	955	1101	955	738
145°	1219	1574	1219	1124	1219	763
155°	1448	1709	1448	1167	1448	666
165°	1601	1782	1601	1343	1601	451
175°	1674	1745	1674	1575	1674	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1412.8	1419.6	1426.3	1423.5	1417.4	1415.1	1416.5	1417.8	1418.5	1419.2	1418.5
5°	1406.0	1414.9	1423.8	1420.7	1413.6	1410.4	1411.3	1413.1	1417.6	1422.0	1417.6
7.5°	1394.6	1403.5	1412.4	1409.5	1402.8	1399.9	1401.0	1403.0	1407.6	1412.2	1407.6
10°	1385.0	1393.9	1402.8	1399.7	1392.6	1389.9	1391.7	1393.9	1397.4	1401.0	1397.4
12.5°	1373.0	1381.9	1390.8	1388.2	1381.8	1379.1	1380.2	1382.0	1385.9	1389.8	1385.9
15°	1351.0	1359.9	1368.8	1366.3	1360.1	1357.7	1359.0	1360.9	1364.4	1368.0	1364.4
17.5°	1324.4	1332.8	1341.1	1338.9	1333.1	1331.0	1332.5	1334.4	1337.5	1340.6	1337.5
20°	1306.0	1314.0	1322.0	1319.7	1313.9	1311.2	1311.7	1312.8	1315.9	1319.0	1315.9
22.5°	1283.6	1291.6	1299.6	1297.5	1292.1	1288.9	1287.9	1288.2	1292.0	1295.8	1292.0
25°	1246.0	1254.0	1262.0	1260.3	1255.4	1252.3	1251.0	1250.8	1253.9	1257.0	1253.9
27.5°	1206.8	1213.5	1220.1	1218.7	1214.6	1212.2	1211.3	1211.2	1213.4	1215.6	1213.4
30°	1178.0	1184.7	1191.3	1189.7	1185.2	1182.6	1181.7	1181.6	1183.8	1186.0	1183.8
32.5°	1147.6	1153.9	1160.2	1157.9	1152.8	1150.1	1149.9	1150.4	1153.0	1155.6	1153.0
35°	1100.0	1105.3	1110.7	1108.3	1103.4	1101.2	1101.7	1102.6	1104.8	1107.0	1104.8
37.5°	1052.2	1056.3	1060.4	1058.0	1053.5	1051.2	1051.1	1051.5	1053.3	1055.2	1053.3
40°	1017.0	1021.4	1025.9	1023.3	1018.4	1015.8	1015.3	1015.6	1017.8	1020.0	1017.8
42.5°	981.0	984.4	987.8	985.5	981.3	979.3	979.6	980.1	981.2	982.4	981.2
45°	925.0	928.1	931.2	929.0	925.0	923.0	923.0	923.2	924.1	925.0	924.1
47.5°	866.4	868.8	871.2	869.5	866.4	864.5	864.0	864.0	865.4	866.8	865.4
50°	824.0	827.1	830.2	828.7	825.6	823.6	822.7	822.4	824.2	826.0	824.2
52.5°	782.4	785.9	789.3	787.9	784.8	782.6	781.3	780.8	782.2	783.6	782.2
55°	718.0	722.0	726.0	725.0	722.3	720.1	718.3	717.2	718.1	719.0	718.1
57.5°	652.2	656.1	660.0	659.3	657.0	654.7	652.6	651.3	652.6	653.8	652.6
60°	609.0	612.6	616.1	615.0	612.3	610.1	608.3	607.2	608.1	609.0	608.1
62.5°	565.0	568.6	572.1	570.7	567.7	565.3	563.5	562.4	563.3	564.2	563.3
65°	498.0	501.1	504.2	503.0	500.3	498.1	496.3	495.1	495.6	496.0	495.6
67.5°	430.4	433.1	435.7	434.5	431.9	429.3	426.7	425.0	425.7	426.4	425.7
70°	384.0	386.7	389.3	388.3	386.1	383.9	381.7	380.0	380.0	380.0	380.0
72.5°	339.2	341.5	343.8	342.5	339.9	337.7	335.8	334.4	334.4	334.4	334.4
75°	271.0	272.3	273.7	273.0	271.7	269.9	267.7	265.9	265.4	265.0	265.4
77.5°	205.2	205.2	205.2	203.9	202.2	200.6	198.9	197.5	196.9	196.4	196.9
80°	162.0	162.0	162.0	161.0	159.7	158.3	157.0	155.8	154.9	154.0	154.9
82.5°	122.0	121.3	120.6	119.4	118.1	116.4	114.3	113.0	113.9	114.8	113.9
85°	65.0	64.1	63.2	62.0	60.7	59.1	57.3	55.9	55.4	55.0	55.4
87.5°	21.0	21.7	22.6	23.0	23.0	22.1	20.6	19.8	19.8	19.5	19.8
90°	5.1	11.9	20.3	27.1	32.2	33.9	33.9	35.6	37.3	37.3	37.3
92.5°	18.7	29.5	29.8	29.8	36.3	39.3	42.1	42.4	44.1	44.1	44.1
95°	52.6	57.7	86.5	84.8	57.7	45.8	39.0	39.0	39.0	39.0	39.0
97.5°	100.4	107.9	112.6	150.9	159.4	154.0	125.5	105.5	94.3	89.2	94.3
100°	142.4	145.8	156.0	157.7	200.1	240.8	220.5	195.0	186.5	181.5	186.5
102.5°	184.5	186.5	202.1	209.3	219.1	242.2	312.7	304.9	299.1	298.1	299.1
105°	247.6	249.3	278.1	291.7	298.5	298.5	296.8	330.7	385.0	396.8	385.0
107.5°	315.1	322.9	356.8	393.1	400.9	402.9	394.1	389.0	387.0	388.3	387.0
110°	361.2	373.1	413.8	459.6	471.4	474.8	471.4	466.3	463.0	463.0	463.0



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	406.0	423.3	469.4	522.0	542.0	552.2	544.7	541.0	537.6	540.3	537.6
115°	474.8	500.3	561.3	615.6	656.3	661.4	659.7	659.7	658.0	658.0	658.0
117.5°	538.6	579.3	647.8	710.9	758.0	771.6	778.4	776.3	774.3	777.7	774.3
120°	583.4	630.8	708.9	780.1	825.9	846.2	853.0	849.6	853.0	849.6	853.0
122.5°	630.8	689.2	765.8	839.8	893.7	916.8	924.9	925.6	926.3	924.2	926.3
125°	702.1	773.3	863.2	939.5	995.4	1022.6	1029.4	1031.1	1034.4	1042.9	1034.4
127.5°	774.0	854.7	953.4	1027.0	1084.3	1117.2	1127.7	1131.4	1138.6	1142.3	1138.6
130°	824.2	915.7	1015.8	1085.3	1141.3	1176.9	1195.6	1200.6	1209.1	1207.4	1209.1
132.5°	877.1	972.7	1074.1	1146.4	1198.3	1236.6	1252.5	1267.1	1270.2	1272.5	1270.2
135°	954.7	1058.2	1159.9	1231.2	1280.3	1317.7	1338.0	1351.6	1360.0	1365.1	1360.0
137.5°	1036.5	1145.7	1243.4	1306.8	1356.3	1388.5	1411.6	1425.8	1434.7	1438.7	1434.7
140°	1092.1	1197.2	1292.2	1358.3	1402.4	1434.7	1455.0	1472.0	1482.1	1482.1	1482.1
142.5°	1145.0	1248.8	1341.1	1407.2	1445.9	1475.4	1497.1	1510.0	1521.5	1521.5	1521.5
145°	1219.3	1322.7	1407.5	1473.7	1505.9	1533.0	1556.8	1566.9	1573.7	1573.7	1573.7
147.5°	1297.0	1388.5	1465.9	1529.3	1556.4	1588.3	1607.0	1615.1	1623.6	1619.8	1623.6
150°	1343.1	1427.9	1502.5	1561.8	1589.0	1619.5	1638.2	1644.9	1653.4	1648.3	1653.4
152.5°	1387.9	1468.6	1536.4	1591.7	1614.8	1645.3	1666.6	1673.4	1679.2	1675.5	1679.2
155°	1448.2	1519.5	1582.2	1633.1	1653.4	1682.3	1702.6	1711.1	1717.9	1709.4	1717.9
157.5°	1502.2	1563.5	1618.1	1665.0	1686.7	1711.4	1730.4	1740.9	1747.7	1744.0	1747.7
160°	1534.7	1590.7	1639.9	1683.9	1704.3	1726.3	1746.7	1758.6	1765.3	1760.3	1765.3
162.5°	1561.8	1612.4	1658.8	1698.9	1716.5	1735.8	1760.3	1770.8	1777.6	1771.1	1777.6
165°	1600.9	1641.6	1682.3	1716.2	1731.4	1746.7	1772.1	1784.0	1789.1	1782.3	1789.1
167.5°	1630.4	1661.6	1694.5	1723.6	1734.8	1749.7	1775.2	1785.0	1791.5	1783.0	1791.5
170°	1646.6	1673.8	1702.6	1726.3	1734.8	1748.4	1773.8	1782.3	1787.4	1778.9	1787.4
172.5°	1660.2	1680.6	1704.0	1725.0	1729.4	1740.2	1764.3	1772.8	1776.5	1769.4	1776.5
175°	1673.8	1685.6	1702.6	1716.2	1714.5	1721.3	1741.6	1748.4	1755.2	1745.0	1755.2
177.5°	1680.2	1685.6	1691.1	1699.2	1693.8	1693.8	1708.7	1712.8	1714.1	1708.7	1714.1
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1417.8	1416.5	1415.1	1417.4	1423.5	1426.3	1419.6	1412.8	1419.6	1426.3	1423.5
5°	1413.1	1411.3	1410.4	1413.6	1420.7	1423.8	1414.9	1406.0	1414.9	1423.8	1420.7
7.5°	1403.0	1401.0	1399.9	1402.8	1409.5	1412.4	1403.5	1394.6	1403.5	1412.4	1409.5
10°	1393.9	1391.7	1389.9	1392.6	1399.7	1402.8	1393.9	1385.0	1393.9	1402.8	1399.7
12.5°	1382.0	1380.2	1379.1	1381.8	1388.2	1390.8	1381.9	1373.0	1381.9	1390.8	1388.2
15°	1360.9	1359.0	1357.7	1360.1	1366.3	1368.8	1359.9	1351.0	1359.9	1368.8	1366.3
17.5°	1334.4	1332.5	1331.0	1333.1	1338.9	1341.1	1332.8	1324.4	1332.8	1341.1	1338.9
20°	1312.8	1311.7	1311.2	1313.9	1319.7	1322.0	1314.0	1306.0	1314.0	1322.0	1319.7
22.5°	1288.2	1287.9	1288.9	1292.1	1297.5	1299.6	1291.6	1283.6	1291.6	1299.6	1297.5
25°	1250.8	1251.0	1252.3	1255.4	1260.3	1262.0	1254.0	1246.0	1254.0	1262.0	1260.3
27.5°	1211.2	1211.3	1212.2	1214.6	1218.7	1220.1	1213.5	1206.8	1213.5	1220.1	1218.7
30°	1181.6	1181.7	1182.6	1185.2	1189.7	1191.3	1184.7	1178.0	1184.7	1191.3	1189.7
32.5°	1150.4	1149.9	1150.1	1152.8	1157.9	1160.2	1153.9	1147.6	1153.9	1160.2	1157.9
35°	1102.6	1101.7	1101.2	1103.4	1108.3	1110.7	1105.3	1100.0	1105.3	1110.7	1108.3
37.5°	1051.5	1051.1	1051.2	1053.5	1058.0	1060.4	1056.3	1052.2	1056.3	1060.4	1058.0
40°	1015.6	1015.3	1015.8	1018.4	1023.3	1025.9	1021.4	1017.0	1021.4	1025.9	1023.3
42.5°	980.1	979.6	979.3	981.3	985.5	987.8	984.4	981.0	984.4	987.8	985.5
45°	923.2	923.0	923.0	925.0	929.0	931.2	928.1	925.0	928.1	931.2	929.0
47.5°	864.0	864.0	864.5	866.4	869.5	871.2	868.8	866.4	868.8	871.2	869.5
50°	822.4	822.7	823.6	825.6	828.7	830.2	827.1	824.0	827.1	830.2	828.7
52.5°	780.8	781.3	782.6	784.8	787.9	789.3	785.9	782.4	785.9	789.3	787.9
55°	717.2	718.3	720.1	722.3	725.0	726.0	722.0	718.0	722.0	726.0	725.0
57.5°	651.3	652.6	654.7	657.0	659.3	660.0	656.1	652.2	656.1	660.0	659.3
60°	607.2	608.3	610.1	612.3	615.0	616.1	612.6	609.0	612.6	616.1	615.0
62.5°	562.4	563.5	565.3	567.7	570.7	572.1	568.6	565.0	568.6	572.1	570.7
65°	495.1	496.3	498.1	500.3	503.0	504.2	501.1	498.0	501.1	504.2	503.0
67.5°	425.0	426.7	429.3	431.9	434.5	435.7	433.1	430.4	433.1	435.7	434.5
70°	380.0	381.7	383.9	386.1	388.3	389.3	386.7	384.0	386.7	389.3	388.3
72.5°	334.4	335.8	337.7	339.9	342.5	343.8	341.5	339.2	341.5	343.8	342.5
75°	265.9	267.7	269.9	271.7	273.0	273.7	272.3	271.0	272.3	273.7	273.0
77.5°	197.5	198.9	200.6	202.2	203.9	205.2	205.2	205.2	205.2	205.2	203.9
80°	155.8	157.0	158.3	159.7	161.0	162.0	162.0	162.0	162.0	162.0	161.0
82.5°	113.0	114.3	116.4	118.1	119.4	120.6	121.3	122.0	121.3	120.6	119.4
85°	55.9	57.3	59.1	60.7	62.0	63.2	64.1	65.0	64.1	63.2	62.0
87.5°	19.8	20.6	22.1	23.0	23.0	22.6	21.7	21.0	21.7	22.3	23.7
90°	35.6	33.9	33.9	32.2	27.1	20.3	11.9	5.1	11.9	18.7	30.5
92.5°	42.4	42.1	39.3	36.3	29.8	29.8	29.5	18.7	32.2	45.8	65.8
95°	39.0	39.0	45.8	57.7	84.8	86.5	57.7	52.6	74.6	105.1	132.3
97.5°	105.5	125.5	154.0	159.4	150.9	112.6	107.9	100.4	136.7	166.9	210.6
100°	195.0	220.5	240.8	200.1	157.7	156.0	145.8	142.4	181.5	210.3	252.7
102.5°	304.9	312.7	242.2	219.1	209.3	202.1	186.5	184.5	223.5	263.2	298.8
105°	330.7	296.8	298.5	298.5	291.7	278.1	249.3	247.6	291.7	337.5	381.6
107.5°	389.0	394.1	402.9	400.9	393.1	356.8	322.9	315.1	354.8	409.7	458.2
110°	466.3	471.4	474.8	471.4	459.6	413.8	373.1	361.2	396.8	454.5	507.0



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	541.0	544.7	552.2	542.0	522.0	469.4	423.3	406.0	441.6	500.6	554.5
115°	659.7	659.7	661.4	656.3	615.6	561.3	500.3	474.8	505.4	559.6	619.0
117.5°	776.3	778.4	771.6	758.0	710.9	647.8	579.3	538.6	562.7	620.0	681.0
120°	849.6	853.0	846.2	825.9	780.1	708.9	630.8	583.4	602.0	658.0	719.0
122.5°	925.6	924.9	916.8	893.7	839.8	765.8	689.2	630.8	638.6	690.5	750.2
125°	1031.1	1029.4	1022.6	995.4	939.5	863.2	773.3	702.1	691.9	736.0	797.0
127.5°	1131.4	1127.7	1117.2	1084.3	1027.0	953.4	854.7	774.0	751.2	779.1	835.0
130°	1200.6	1195.6	1176.9	1141.3	1085.3	1015.8	915.7	824.2	791.9	808.9	858.1
132.5°	1267.1	1252.5	1236.6	1198.3	1146.4	1074.1	972.7	877.1	832.6	840.1	878.4
135°	1351.6	1338.0	1317.7	1280.3	1231.2	1159.9	1058.2	954.7	893.7	886.9	909.0
137.5°	1425.8	1411.6	1388.5	1356.3	1306.8	1243.4	1145.7	1036.5	959.5	936.8	945.2
140°	1472.0	1455.0	1434.7	1402.4	1358.3	1292.2	1197.2	1092.1	1005.6	973.4	968.3
142.5°	1510.0	1497.1	1475.4	1445.9	1407.2	1341.1	1248.8	1145.0	1053.1	1011.4	999.5
145°	1566.9	1556.8	1533.0	1505.9	1473.7	1407.5	1322.7	1219.3	1127.7	1073.5	1048.0
147.5°	1615.1	1607.0	1588.3	1556.4	1529.3	1465.9	1388.5	1297.0	1203.0	1135.9	1103.0
150°	1644.9	1638.2	1619.5	1589.0	1561.8	1502.5	1427.9	1343.1	1253.2	1182.0	1139.6
152.5°	1673.4	1666.6	1645.3	1614.8	1591.7	1536.4	1468.6	1387.9	1296.6	1225.4	1181.6
155°	1711.1	1702.6	1682.3	1653.4	1633.1	1582.2	1519.5	1448.2	1370.2	1295.6	1246.4
157.5°	1740.9	1730.4	1711.4	1686.7	1665.0	1618.1	1563.5	1502.2	1434.0	1362.8	1312.6
160°	1758.6	1746.7	1726.3	1704.3	1683.9	1639.9	1590.7	1534.7	1472.0	1407.5	1353.3
162.5°	1770.8	1760.3	1735.8	1716.5	1698.9	1658.8	1612.4	1561.8	1505.9	1449.6	1399.4
165°	1784.0	1772.1	1746.7	1731.4	1716.2	1682.3	1641.6	1600.9	1553.4	1507.6	1466.9
167.5°	1785.0	1775.2	1749.7	1734.8	1723.6	1694.5	1661.6	1630.4	1593.4	1557.4	1523.5
170°	1782.3	1773.8	1748.4	1734.8	1726.3	1702.6	1673.8	1646.6	1617.8	1587.3	1560.2
172.5°	1772.8	1764.3	1740.2	1729.4	1725.0	1704.0	1680.6	1660.2	1635.4	1613.1	1591.4
175°	1748.4	1741.6	1721.3	1714.5	1716.2	1702.6	1685.6	1673.8	1658.5	1644.9	1633.1
177.5°	1712.8	1708.7	1693.8	1693.8	1699.2	1691.1	1685.6	1680.2	1673.4	1669.4	1665.3
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1417.4	1415.1	1416.5	1417.8	1418.5	1419.2	1418.5	1417.8	1416.5	1415.1	1417.4
5°	1413.6	1410.4	1411.3	1413.1	1417.6	1422.0	1417.6	1413.1	1411.3	1410.4	1413.6
7.5°	1402.8	1399.9	1401.0	1403.0	1407.6	1412.2	1407.6	1403.0	1401.0	1399.9	1402.8
10°	1392.6	1389.9	1391.7	1393.9	1397.4	1401.0	1397.4	1393.9	1391.7	1389.9	1392.6
12.5°	1381.8	1379.1	1380.2	1382.0	1385.9	1389.8	1385.9	1382.0	1380.2	1379.1	1381.8
15°	1360.1	1357.7	1359.0	1360.9	1364.4	1368.0	1364.4	1360.9	1359.0	1357.7	1360.1
17.5°	1333.1	1331.0	1332.5	1334.4	1337.5	1340.6	1337.5	1334.4	1332.5	1331.0	1333.1
20°	1313.9	1311.2	1311.7	1312.8	1315.9	1319.0	1315.9	1312.8	1311.7	1311.2	1313.9
22.5°	1292.1	1288.9	1287.9	1288.2	1292.0	1295.8	1292.0	1288.2	1287.9	1288.9	1292.1
25°	1255.4	1252.3	1251.0	1250.8	1253.9	1257.0	1253.9	1250.8	1251.0	1252.3	1255.4
27.5°	1214.6	1212.2	1211.3	1211.2	1213.4	1215.6	1213.4	1211.2	1211.3	1212.2	1214.6
30°	1185.2	1182.6	1181.7	1181.6	1183.8	1186.0	1183.8	1181.6	1181.7	1182.6	1185.2
32.5°	1152.8	1150.1	1149.9	1150.4	1153.0	1155.6	1153.0	1150.4	1149.9	1150.1	1152.8
35°	1103.4	1101.2	1101.7	1102.6	1104.8	1107.0	1104.8	1102.6	1101.7	1101.2	1103.4
37.5°	1053.5	1051.2	1051.1	1051.5	1053.3	1055.2	1053.3	1051.5	1051.1	1051.2	1053.5
40°	1018.4	1015.8	1015.3	1015.6	1017.8	1020.0	1017.8	1015.6	1015.3	1015.8	1018.4
42.5°	981.3	979.3	979.6	980.1	981.2	982.4	981.2	980.1	979.6	979.3	981.3
45°	925.0	923.0	923.0	923.2	924.1	925.0	924.1	923.2	923.0	923.0	925.0
47.5°	866.4	864.5	864.0	864.0	865.4	866.8	865.4	864.0	864.0	864.5	866.4
50°	825.6	823.6	822.7	822.4	824.2	826.0	824.2	822.4	822.7	823.6	825.6
52.5°	784.8	782.6	781.3	780.8	782.2	783.6	782.2	780.8	781.3	782.6	784.8
55°	722.3	720.1	718.3	717.2	718.1	719.0	718.1	717.2	718.3	720.1	722.3
57.5°	657.0	654.7	652.6	651.3	652.6	653.8	652.6	651.3	652.6	654.7	657.0
60°	612.3	610.1	608.3	607.2	608.1	609.0	608.1	607.2	608.3	610.1	612.3
62.5°	567.7	565.3	563.5	562.4	563.3	564.2	563.3	562.4	563.5	565.3	567.7
65°	500.3	498.1	496.3	495.1	495.6	496.0	495.6	495.1	496.3	498.1	500.3
67.5°	431.9	429.3	426.7	425.0	425.7	426.4	425.7	425.0	426.7	429.3	431.9
70°	386.1	383.9	381.7	380.0	380.0	380.0	380.0	380.0	381.7	383.9	386.1
72.5°	339.9	337.7	335.8	334.4	334.4	334.4	334.4	334.4	335.8	337.7	339.9
75°	271.7	269.9	267.7	265.9	265.4	265.0	265.4	265.9	267.7	269.9	271.7
77.5°	202.2	200.6	198.9	197.5	196.9	196.4	196.9	197.5	198.9	200.6	202.2
80°	159.7	158.3	157.0	155.8	154.9	154.0	154.9	155.8	157.0	158.3	159.7
82.5°	118.1	116.4	114.3	113.0	113.9	114.8	113.9	113.0	114.3	116.4	118.1
85°	60.7	59.1	57.3	55.9	55.4	55.0	55.4	55.9	57.3	59.1	60.7
87.5°	24.3	25.5	26.4	26.6	27.6	26.6	27.6	26.6	26.4	25.5	24.3
90°	39.0	50.9	62.7	69.5	76.3	72.9	76.3	69.5	62.7	50.9	39.0
92.5°	78.3	98.4	112.9	125.2	130.6	129.9	130.6	125.2	112.9	98.4	78.3
95°	157.7	181.5	205.2	222.2	232.3	228.9	232.3	222.2	205.2	181.5	157.7
97.5°	243.2	275.1	301.5	317.5	327.6	334.4	327.6	317.5	301.5	275.1	243.2
100°	300.2	330.7	361.2	379.9	396.8	403.6	396.8	379.9	361.2	330.7	300.2
102.5°	346.3	386.3	419.5	439.6	453.8	460.6	453.8	439.6	419.5	386.3	346.3
105°	422.3	464.7	500.3	525.7	541.0	546.1	541.0	525.7	500.3	464.7	422.3
107.5°	498.2	542.0	574.9	603.0	621.7	632.5	621.7	603.0	574.9	542.0	498.2
110°	557.9	593.5	629.1	654.6	673.2	680.0	673.2	654.6	629.1	593.5	557.9



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	608.1	647.8	683.4	708.9	730.2	739.7	730.2	708.9	683.4	647.8	608.1
115°	678.3	730.9	763.1	786.9	802.1	810.6	802.1	786.9	763.1	730.9	678.3
117.5°	736.7	791.6	826.9	845.2	852.3	858.4	852.3	845.2	826.9	791.6	736.7
120°	773.3	824.2	864.9	888.6	897.1	900.5	897.1	888.6	864.9	824.2	773.3
122.5°	807.2	855.4	894.7	923.9	937.8	941.2	937.8	923.9	894.7	855.4	807.2
125°	854.7	900.5	941.2	970.0	985.3	993.7	985.3	970.0	941.2	900.5	854.7
127.5°	896.1	945.6	982.9	1009.0	1023.9	1030.7	1023.9	1009.0	982.9	945.6	896.1
130°	919.1	970.0	1007.3	1036.1	1049.7	1056.5	1049.7	1036.1	1007.3	970.0	919.1
132.5°	936.8	990.4	1029.0	1055.1	1070.1	1076.8	1070.1	1055.1	1029.0	990.4	936.8
135°	958.1	1014.1	1054.8	1080.2	1093.8	1100.6	1093.8	1080.2	1054.8	1014.1	958.1
137.5°	976.8	1027.7	1070.1	1096.9	1109.1	1113.5	1109.1	1096.9	1070.1	1027.7	976.8
140°	990.4	1034.4	1076.8	1102.3	1115.8	1117.5	1115.8	1102.3	1076.8	1034.4	990.4
142.5°	1008.0	1042.6	1079.6	1105.0	1118.6	1121.6	1118.6	1105.0	1079.6	1042.6	1008.0
145°	1039.5	1059.9	1085.3	1109.1	1120.9	1124.3	1120.9	1109.1	1085.3	1059.9	1039.5
147.5°	1079.2	1085.7	1098.9	1114.5	1126.0	1128.4	1126.0	1114.5	1098.9	1085.7	1079.2
150°	1109.1	1107.4	1112.5	1122.6	1132.8	1131.1	1132.8	1122.6	1112.5	1107.4	1109.1
152.5°	1143.0	1133.1	1132.8	1137.6	1142.3	1142.0	1142.3	1137.6	1132.8	1133.1	1143.0
155°	1200.6	1182.0	1171.8	1168.4	1168.4	1166.7	1168.4	1168.4	1171.8	1182.0	1200.6
157.5°	1264.1	1237.9	1222.7	1214.5	1212.2	1208.4	1212.2	1214.5	1222.7	1237.9	1264.1
160°	1307.5	1278.6	1263.4	1249.8	1244.7	1239.6	1244.7	1249.8	1263.4	1278.6	1307.5
162.5°	1348.2	1320.7	1304.1	1291.9	1286.8	1279.0	1286.8	1291.9	1304.1	1320.7	1348.2
165°	1414.3	1385.5	1366.8	1356.7	1349.9	1343.1	1349.9	1356.7	1366.8	1385.5	1414.3
167.5°	1480.4	1448.9	1436.7	1425.2	1418.7	1406.5	1418.7	1425.2	1436.7	1448.9	1480.4
170°	1521.1	1492.3	1485.5	1475.4	1463.5	1449.9	1463.5	1475.4	1485.5	1492.3	1521.1
172.5°	1556.4	1537.1	1530.3	1520.1	1516.4	1505.5	1516.4	1520.1	1530.3	1537.1	1556.4
175°	1607.6	1592.4	1592.4	1590.7	1585.6	1575.4	1585.6	1590.7	1592.4	1592.4	1607.6
177.5°	1650.4	1642.2	1647.7	1647.7	1646.3	1636.8	1646.3	1647.7	1647.7	1642.2	1650.4
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1420.0	1420.0	1420.0	1420.0
2.5°	1423.5	1426.3	1419.6	1412.8
5°	1420.7	1423.8	1414.9	1406.0
7.5°	1409.5	1412.4	1403.5	1394.6
10°	1399.7	1402.8	1393.9	1385.0
12.5°	1388.2	1390.8	1381.9	1373.0
15°	1366.3	1368.8	1359.9	1351.0
17.5°	1338.9	1341.1	1332.8	1324.4
20°	1319.7	1322.0	1314.0	1306.0
22.5°	1297.5	1299.6	1291.6	1283.6
25°	1260.3	1262.0	1254.0	1246.0
27.5°	1218.7	1220.1	1213.5	1206.8
30°	1189.7	1191.3	1184.7	1178.0
32.5°	1157.9	1160.2	1153.9	1147.6
35°	1108.3	1110.7	1105.3	1100.0
37.5°	1058.0	1060.4	1056.3	1052.2
40°	1023.3	1025.9	1021.4	1017.0
42.5°	985.5	987.8	984.4	981.0
45°	929.0	931.2	928.1	925.0
47.5°	869.5	871.2	868.8	866.4
50°	828.7	830.2	827.1	824.0
52.5°	787.9	789.3	785.9	782.4
55°	725.0	726.0	722.0	718.0
57.5°	659.3	660.0	656.1	652.2
60°	615.0	616.1	612.6	609.0
62.5°	570.7	572.1	568.6	565.0
65°	503.0	504.2	501.1	498.0
67.5°	434.5	435.7	433.1	430.4
70°	388.3	389.3	386.7	384.0
72.5°	342.5	343.8	341.5	339.2
75°	273.0	273.7	272.3	271.0
77.5°	203.9	205.2	205.2	205.2
80°	161.0	162.0	162.0	162.0
82.5°	119.4	120.6	121.3	122.0
85°	62.0	63.2	64.1	65.0
87.5°	23.7	22.3	21.7	21.0
90°	30.5	18.7	11.9	5.1
92.5°	65.8	45.8	32.2	18.7
95°	132.3	105.1	74.6	52.6
97.5°	210.6	166.9	136.7	100.4
100°	252.7	210.3	181.5	142.4
102.5°	298.8	263.2	223.5	184.5
105°	381.6	337.5	291.7	247.6
107.5°	458.2	409.7	354.8	315.1
110°	507.0	454.5	396.8	361.2



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	554.5	500.6	441.6	406.0
115°	619.0	559.6	505.4	474.8
117.5°	681.0	620.0	562.7	538.6
120°	719.0	658.0	602.0	583.4
122.5°	750.2	690.5	638.6	630.8
125°	797.0	736.0	691.9	702.1
127.5°	835.0	779.1	751.2	774.0
130°	858.1	808.9	791.9	824.2
132.5°	878.4	840.1	832.6	877.1
135°	909.0	886.9	893.7	954.7
137.5°	945.2	936.8	959.5	1036.5
140°	968.3	973.4	1005.6	1092.1
142.5°	999.5	1011.4	1053.1	1145.0
145°	1048.0	1073.5	1127.7	1219.3
147.5°	1103.0	1135.9	1203.0	1297.0
150°	1139.6	1182.0	1253.2	1343.1
152.5°	1181.6	1225.4	1296.6	1387.9
155°	1246.4	1295.6	1370.2	1448.2
157.5°	1312.6	1362.8	1434.0	1502.2
160°	1353.3	1407.5	1472.0	1534.7
162.5°	1399.4	1449.6	1505.9	1561.8
165°	1466.9	1507.6	1553.4	1600.9
167.5°	1523.5	1557.4	1593.4	1630.4
170°	1560.2	1587.3	1617.8	1646.6
172.5°	1591.4	1613.1	1635.4	1660.2
175°	1633.1	1644.9	1658.5	1673.8
177.5°	1665.3	1669.4	1673.4	1680.2
180°	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427787

CATALOG NUMBER: SQ2W-F-K-125U-100D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.26	19.09	19.26	20.10	21.44	18.18	19.00	19.17	20.01	21.35
	3H	20.05	20.79	21.05	21.81	23.17	19.94	20.69	20.95	21.71	23.07
	4H	20.74	21.45	21.76	22.47	23.84	20.63	21.33	21.65	22.35	23.72
	6H	21.18	21.83	22.21	22.85	24.23	21.04	21.68	22.07	22.71	24.09
	8H	21.34	21.95	22.37	23.00	24.37	21.18	21.80	22.22	22.84	24.22
	12H	21.42	22.01	22.46	23.04	24.45	21.24	21.83	22.28	22.87	24.27
4H	2H	18.84	19.54	19.86	20.56	21.93	18.77	19.47	19.80	20.50	21.86
	3H	20.85	21.44	21.89	22.49	23.88	20.76	21.35	21.80	22.40	23.78
	4H	21.67	22.21	22.71	23.25	24.65	21.56	22.10	22.60	23.14	24.54
	6H	22.22	22.68	23.27	23.75	25.15	22.08	22.54	23.13	23.61	25.01
	8H	22.43	22.86	23.48	23.92	25.34	22.27	22.70	23.32	23.76	25.18
	12H	22.54	22.94	23.61	24.01	25.43	22.36	22.75	23.43	23.82	25.24
8H	4H	21.91	22.34	22.96	23.40	24.82	21.81	22.24	22.86	23.30	24.72
	6H	22.60	22.95	23.67	24.05	25.47	22.47	22.82	23.54	23.92	25.34
	8H	22.90	23.22	23.98	24.30	25.73	22.74	23.06	23.83	24.14	25.58
	12H	23.08	23.36	24.17	24.44	25.91	22.89	23.17	23.98	24.25	25.72
12H	4H	21.90	22.29	22.97	23.37	24.79	21.81	22.20	22.88	23.27	24.69
	6H	22.65	22.96	23.73	24.04	25.48	22.52	22.84	23.60	23.92	25.35
	8H	22.98	23.26	24.07	24.33	25.81	22.83	23.10	23.92	24.18	25.66