

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435863

Luminaire Tested: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435863  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7755.8 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 72.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	60	54	50	47	43	39	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12568	12568	12568	12568
5°	12420	13008	12420	10366
10°	12366	13158	12366	9399
15°	12154	13263	12154	10388
20°	11819	13166	11819	10835
25°	11234	13062	11234	10965
30°	10351	12769	10351	11082
35°	9157	12488	9157	10882
40°	7885	12146	7885	11002
45°	7784	11711	7784	11022
50°	7427	11140	7427	11064
55°	7389	10277	7389	10956
60°	6626	9158	6626	10911
65°	5646	8069	5646	10605
70°	4555	6835	4555	9828
75°	3955	5646	3955	9033
80°	3366	4212	3366	7290
85°	2242	2242	2242	4465

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 12079 cd/sqm



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.0	0.9
10°-20°	195.7	2.5
20°-30°	297.2	3.8
30°-40°	348.9	4.5
40°-50°	354.1	4.6
50°-60°	310.2	4.0
60°-70°	220.0	2.8
70°-80°	113.3	1.5
80°-90°	32.0	0.4
90°-100°	158.5	2.0
100°-110°	462.2	6.0
110°-120°	754.2	9.7
120°-130°	957.1	12.3
130°-140°	1024.1	13.2
140°-150°	956.3	12.3
150°-160°	786.9	10.1
160°-170°	527.7	6.8
170°-180°	187.4	2.4
0°-30°	562.9	7.3
0°-40°	911.9	11.8
0°-60°	1576.1	20.3
0°-90°	1941.4	25.0
90°-120°	1374.9	17.7
90°-150°	4312.4	55.6
90°-180°	5814.0	75.0
0°-180°	7755.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	778	778	778	778	778	
5°	766	803	766	640	766	73
15°	727	794	727	622	727	204
25°	631	733	631	616	631	288
35°	465	634	465	552	465	289
45°	341	513	341	483	341	261
55°	262	365	262	389	262	227
65°	148	211	148	278	148	148
75°	63	90	63	145	63	69
85°	12	12	12	24	12	15
90°	6	44	6	86	6	5
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	773.6	779.0	784.3	785.7	785.7	785.7	785.7	785.7	785.7	785.7	785.7
5°	766.3	775.7	785.1	789.5	792.2	794.2	795.5	797.2	799.9	802.6	799.9
7.5°	759.1	771.7	784.3	790.5	794.5	797.7	800.1	802.3	803.6	805.0	803.6
10°	754.3	769.0	783.8	790.5	794.5	797.2	798.5	799.9	801.2	802.6	801.2
12.5°	747.0	762.9	778.7	786.5	791.6	794.8	796.1	797.5	798.8	800.1	798.8
15°	727.1	748.6	770.0	778.4	782.4	785.8	788.5	790.8	792.2	793.5	792.2
17.5°	702.4	728.4	754.4	764.9	770.3	774.2	776.6	778.7	779.8	780.8	779.8
20°	687.9	716.1	744.2	755.3	760.7	764.0	765.3	766.3	766.3	766.3	766.3
22.5°	668.6	700.0	731.4	743.2	748.6	751.4	751.7	752.1	753.2	754.3	753.2
25°	630.6	666.8	703.0	718.1	726.1	729.5	728.1	727.8	730.5	733.2	730.5
27.5°	584.1	629.7	675.3	690.7	696.1	699.4	700.8	701.8	701.8	701.8	701.8
30°	555.2	606.1	657.1	673.8	679.2	682.5	683.9	684.9	684.9	684.9	684.9
32.5°	518.9	579.6	640.2	658.5	662.8	665.1	665.4	665.6	665.6	665.6	665.6
35°	464.6	538.4	612.1	632.6	635.3	636.6	636.6	636.3	634.9	633.6	634.9
37.5°	410.3	494.0	577.7	601.6	605.6	606.7	604.8	603.1	601.7	600.4	601.7
40°	374.1	465.3	556.5	582.3	586.3	586.3	582.3	579.0	577.6	576.3	577.6
42.5°	354.8	444.9	535.0	560.6	564.6	564.1	559.0	554.8	553.5	552.1	553.5
45°	340.9	421.4	501.8	525.0	529.0	528.3	523.0	518.3	515.6	512.9	515.6
47.5°	319.8	390.6	461.4	484.1	490.9	490.2	482.1	475.4	472.7	470.1	472.7
50°	295.7	365.4	435.1	457.6	464.3	463.6	455.6	448.9	446.2	443.5	446.2
52.5°	278.8	344.2	409.7	430.2	435.9	434.1	425.0	417.5	414.8	412.1	414.8
55°	262.5	317.5	372.4	389.2	393.2	390.5	381.2	373.1	369.1	365.1	369.1
57.5°	224.5	276.8	329.1	345.4	349.7	346.4	335.7	326.5	322.0	317.4	322.0
60°	205.2	252.1	299.0	314.8	320.2	317.5	306.7	297.0	290.3	283.6	290.3
62.5°	183.4	225.0	266.6	282.6	290.1	288.5	277.8	268.1	261.3	254.6	261.3
65°	147.8	184.0	220.2	236.3	245.7	245.1	234.3	224.6	217.9	211.2	217.9
67.5°	115.9	147.0	178.1	193.9	204.6	204.1	192.3	182.1	176.7	171.4	176.7
70°	96.5	123.4	150.2	164.9	175.7	175.7	164.9	155.5	150.2	144.8	150.2
72.5°	84.5	104.9	125.2	139.2	151.0	151.0	139.2	129.3	125.0	120.7	125.0
75°	63.4	75.4	87.5	100.6	114.0	115.3	104.6	95.9	93.2	90.5	93.2
77.5°	45.9	51.5	57.1	67.4	79.2	80.5	71.4	64.3	63.2	62.2	63.2
80°	36.2	37.5	38.9	47.3	58.0	59.3	51.3	45.3	45.3	45.3	45.3
82.5°	24.1	25.5	26.8	32.8	40.3	41.1	35.2	30.5	29.4	28.4	29.4
85°	12.1	12.1	12.1	14.1	16.8	16.8	14.1	12.1	12.1	12.1	12.1
87.5°	3.6	5.2	7.2	9.7	11.9	12.3	11.3	10.9	11.3	11.3	11.3
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	785.7	785.7	785.7	785.7	785.7	784.3	779.0	773.6	773.6	773.6	769.6
5°	797.2	795.5	794.2	792.2	789.5	785.1	775.7	766.3	762.3	758.3	741.2
7.5°	802.3	800.1	797.7	794.5	790.5	784.3	771.7	759.1	741.1	723.2	685.1
10°	799.9	798.5	797.2	794.5	790.5	783.8	769.0	754.3	718.1	681.9	645.7
12.5°	797.5	796.1	794.8	791.6	786.5	778.7	762.9	747.0	695.8	644.6	611.9
15°	790.8	788.5	785.8	782.4	778.4	770.0	748.6	727.1	669.5	611.8	584.3
17.5°	778.7	776.6	774.2	770.3	764.9	754.4	728.4	702.4	642.0	581.7	564.0
20°	766.3	765.3	764.0	760.7	755.3	744.2	716.1	687.9	627.6	567.2	559.2
22.5°	752.1	751.7	751.4	748.6	743.2	731.4	700.0	668.6	609.3	550.1	550.3
25°	727.8	728.1	729.5	726.1	718.1	703.0	666.8	630.6	578.3	526.0	535.0
27.5°	701.8	700.8	699.4	696.1	690.7	675.3	629.7	584.1	542.8	501.5	516.5
30°	684.9	683.9	682.5	679.2	673.8	657.1	606.1	555.2	520.3	485.4	502.9
32.5°	665.6	665.4	665.1	662.8	658.5	640.2	579.6	518.9	493.7	468.5	486.8
35°	636.3	636.6	636.6	635.3	632.6	612.1	538.4	464.6	453.9	443.2	464.6
37.5°	603.1	604.8	606.7	605.6	601.6	577.7	494.0	410.3	413.8	417.3	443.3
40°	579.0	582.3	586.3	586.3	582.3	556.5	465.3	374.1	386.2	398.3	426.4
42.5°	554.8	559.0	564.1	564.6	560.6	535.0	444.9	354.8	368.0	381.1	410.3
45°	518.3	523.0	528.3	529.0	525.0	501.8	421.4	340.9	349.0	357.0	385.2
47.5°	475.4	482.1	490.2	490.9	484.1	461.4	390.6	319.8	325.7	331.6	360.4
50°	448.9	455.6	463.6	464.3	457.6	435.1	365.4	295.7	303.7	311.8	341.9
52.5°	417.5	425.0	434.1	435.9	430.2	409.7	344.2	278.8	283.6	288.4	321.0
55°	373.1	381.2	390.5	393.2	389.2	372.4	317.5	262.5	258.5	254.4	287.6
57.5°	326.5	335.7	346.4	349.7	345.4	329.1	276.8	224.5	221.0	217.5	253.4
60°	297.0	306.7	317.5	320.2	314.8	299.0	252.1	205.2	198.5	191.8	229.3
62.5°	268.1	277.8	288.5	290.1	282.6	266.6	225.0	183.4	178.9	174.3	210.8
65°	224.6	234.3	245.1	245.7	236.3	220.2	184.0	147.8	150.5	153.2	186.1
67.5°	182.1	192.3	204.1	204.6	193.9	178.1	147.0	115.9	124.7	133.6	163.1
70°	155.5	164.9	175.7	175.7	164.9	150.2	123.4	96.5	108.6	120.7	147.8
72.5°	129.3	139.2	151.0	151.0	139.2	125.2	104.9	84.5	96.5	108.6	130.9
75°	95.9	104.6	115.3	114.0	100.6	87.5	75.4	63.4	75.4	87.5	104.6
77.5°	64.3	71.4	80.5	79.2	67.4	57.1	51.5	45.9	55.8	65.7	77.6
80°	45.3	51.3	59.3	58.0	47.3	38.9	37.5	36.2	42.9	49.6	58.3
82.5°	30.5	35.2	41.1	40.3	32.8	26.8	25.5	24.1	29.8	35.4	41.4
85°	12.1	14.1	16.8	16.8	14.1	12.1	12.1	12.1	14.8	17.4	20.1
87.5°	10.9	11.3	12.3	11.9	9.7	7.2	5.2	3.6	6.3	9.0	12.1
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	764.2	759.9	756.7	754.0	752.9	751.9	752.9	754.0	756.7	759.9	764.2
5°	719.8	697.0	672.8	653.0	646.3	639.6	646.3	653.0	672.8	697.0	719.8
7.5°	640.3	612.8	602.6	594.4	592.3	590.1	592.3	594.4	602.6	612.8	640.3
10°	609.5	587.3	579.3	573.3	573.3	573.3	573.3	573.3	579.3	587.3	609.5
12.5°	585.3	571.8	571.2	572.2	577.5	582.9	577.5	572.2	571.2	571.8	585.3
15°	566.9	568.9	590.4	608.1	614.8	621.5	614.8	608.1	590.4	568.9	566.9
17.5°	560.5	572.0	598.6	619.9	625.2	630.6	625.2	619.9	598.6	572.0	560.5
20°	568.6	583.3	603.4	619.9	625.2	630.6	625.2	619.9	603.4	583.3	568.6
22.5°	570.4	588.4	604.2	617.4	622.8	628.2	622.8	617.4	604.2	588.4	570.4
25°	564.5	586.0	599.4	610.1	612.8	615.5	612.8	610.1	599.4	586.0	564.5
27.5°	550.3	573.9	587.3	597.9	599.7	601.6	599.7	597.9	587.3	573.9	550.3
30°	537.7	561.9	575.3	586.3	590.4	594.4	590.4	586.3	575.3	561.9	537.7
32.5°	519.5	544.2	560.8	573.5	574.3	575.1	574.3	573.5	560.8	544.2	519.5
35°	496.8	522.3	541.1	554.8	553.5	552.1	553.5	554.8	541.1	522.3	496.8
37.5°	476.8	501.8	518.1	530.8	532.4	534.0	532.4	530.8	518.1	501.8	476.8
40°	459.9	485.4	502.9	516.6	519.3	522.0	519.3	516.6	502.9	485.4	459.9
42.5°	444.9	470.9	488.4	502.1	504.8	507.5	504.8	502.1	488.4	470.9	444.9
45°	420.1	446.9	465.6	480.1	481.4	482.7	481.4	480.1	465.6	446.9	420.1
47.5°	396.9	423.9	441.3	454.7	456.1	457.4	456.1	454.7	441.3	423.9	396.9
50°	379.5	407.0	424.4	437.8	439.2	440.5	439.2	437.8	424.4	407.0	379.5
52.5°	362.9	391.4	406.7	418.5	419.8	421.2	419.8	418.5	406.7	391.4	362.9
55°	333.2	363.4	378.1	389.2	389.2	389.2	389.2	389.2	378.1	363.4	333.2
57.5°	302.5	333.5	346.4	356.4	358.0	359.6	358.0	356.4	346.4	333.5	302.5
60°	281.6	313.1	323.8	332.6	335.2	337.9	335.2	332.6	323.8	313.1	281.6
62.5°	260.9	291.4	302.1	310.6	312.2	313.8	312.2	310.6	302.1	291.4	260.9
65°	229.0	255.8	266.5	274.9	276.2	277.6	276.2	274.9	266.5	255.8	229.0
67.5°	199.6	221.6	229.1	235.0	236.1	237.1	236.1	235.0	229.1	221.6	199.6
70°	180.0	198.8	204.2	208.2	208.2	208.2	208.2	208.2	204.2	198.8	180.0
72.5°	156.7	172.2	177.6	181.9	183.0	184.0	183.0	181.9	177.6	172.2	156.7
75°	123.4	134.8	138.8	142.1	143.5	144.8	143.5	142.1	138.8	134.8	123.4
77.5°	90.2	97.8	100.2	102.3	103.7	105.0	103.7	102.3	100.2	97.8	90.2
80°	67.7	73.1	74.4	75.8	77.1	78.4	77.1	75.8	74.4	73.1	67.7
82.5°	47.6	51.4	52.7	53.8	54.0	54.3	54.0	53.8	52.7	51.4	47.6
85°	22.8	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	22.8
87.5°	14.1	16.9	19.7	21.3	22.9	22.1	22.9	21.3	19.7	16.9	14.1
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	778.4	778.4	778.4	778.4
2.5°	769.6	773.6	773.6	773.6
5°	741.2	758.3	762.3	766.3
7.5°	685.1	723.2	741.1	759.1
10°	645.7	681.9	718.1	754.3
12.5°	611.9	644.6	695.8	747.0
15°	584.3	611.8	669.5	727.1
17.5°	564.0	581.7	642.0	702.4
20°	559.2	567.2	627.6	687.9
22.5°	550.3	550.1	609.3	668.6
25°	535.0	526.0	578.3	630.6
27.5°	516.5	501.5	542.8	584.1
30°	502.9	485.4	520.3	555.2
32.5°	486.8	468.5	493.7	518.9
35°	464.6	443.2	453.9	464.6
37.5°	443.3	417.3	413.8	410.3
40°	426.4	398.3	386.2	374.1
42.5°	410.3	381.1	368.0	354.8
45°	385.2	357.0	349.0	340.9
47.5°	360.4	331.6	325.7	319.8
50°	341.9	311.8	303.7	295.7
52.5°	321.0	288.4	283.6	278.8
55°	287.6	254.4	258.5	262.5
57.5°	253.4	217.5	221.0	224.5
60°	229.3	191.8	198.5	205.2
62.5°	210.8	174.3	178.9	183.4
65°	186.1	153.2	150.5	147.8
67.5°	163.1	133.6	124.7	115.9
70°	147.8	120.7	108.6	96.5
72.5°	130.9	108.6	96.5	84.5
75°	104.6	87.5	75.4	63.4
77.5°	77.6	65.7	55.8	45.9
80°	58.3	49.6	42.9	36.2
82.5°	41.4	35.4	29.8	24.1
85°	20.1	17.4	14.8	12.1
87.5°	12.1	9.0	6.3	3.6
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1435863

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1435863  
 CATALOG NUMBER: SQ2W-FA-K-150U-050D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.22	12.89	13.37	14.03	15.62	13.42	14.09	14.56	15.23	16.82
	3H	13.29	13.90	14.45	15.04	16.64	14.65	15.25	15.80	16.39	18.00
	4H	13.64	14.21	14.80	15.35	16.96	15.03	15.60	16.19	16.74	18.35
	6H	13.79	14.32	14.96	15.46	17.08	15.18	15.71	16.35	16.85	18.47
	8H	13.82	14.32	14.99	15.48	17.09	15.20	15.70	16.37	16.86	18.47
	12H	13.81	14.28	14.98	15.44	17.07	15.18	15.65	16.35	16.81	18.44
4H	2H	13.06	13.64	14.23	14.78	16.39	13.98	14.55	15.15	15.69	17.30
	3H	14.43	14.91	15.61	16.08	17.70	15.42	15.90	16.60	17.07	18.69
	4H	14.88	15.32	16.06	16.48	18.12	15.89	16.33	17.07	17.49	19.13
	6H	15.10	15.48	16.28	16.66	18.28	16.10	16.48	17.28	17.66	19.29
	8H	15.15	15.50	16.33	16.67	18.32	16.15	16.50	17.33	17.67	19.31
	12H	15.15	15.46	16.34	16.65	18.30	16.13	16.45	17.32	17.63	19.28
8H	4H	15.25	15.60	16.43	16.77	18.42	16.07	16.42	17.25	17.59	19.24
	6H	15.59	15.88	16.79	17.09	18.74	16.38	16.67	17.58	17.88	19.52
	8H	15.71	15.96	16.91	17.15	18.81	16.47	16.72	17.68	17.91	19.58
	12H	15.74	15.96	16.95	17.15	18.84	16.48	16.70	17.69	17.89	19.58
12H	4H	15.24	15.56	16.44	16.74	18.39	16.03	16.35	17.23	17.53	19.18
	6H	15.66	15.91	16.87	17.10	18.77	16.39	16.65	17.60	17.84	19.50
	8H	15.80	16.02	17.01	17.21	18.90	16.50	16.72	17.71	17.91	19.60