

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435935

Luminaire Tested: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3957.7 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58	52
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	50	49	43
2	89	81	75	70	82	75	70	65	64	60	56	54	51	48	44	42	40	36
3	81	71	63	57	74	66	59	54	56	51	47	47	43	40	39	36	34	30
4	74	62	54	48	68	58	51	45	49	44	39	42	37	34	34	31	29	25
5	67	55	47	41	62	51	44	38	44	38	34	37	32	29	31	27	24	21
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	27	24	21	18
7	57	44	36	30	52	41	34	29	35	29	25	30	25	22	25	21	19	16
8	53	40	32	27	49	37	30	25	32	26	22	27	23	19	23	19	16	14
9	49	36	29	23	45	34	27	22	29	24	20	25	20	17	21	17	15	12
10	46	33	26	21	42	31	24	20	27	21	17	23	18	15	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3358	3358	3358	3358
5°	3274	5948	3274	5948
10°	3066	11575	3066	11575
15°	2775	13322	2775	13322
20°	2457	13952	2457	13952
25°	2173	14180	2173	14180
30°	1920	14355	1920	14355
35°	1715	15433	1715	15433
40°	1560	16398	1560	16398
45°	1438	17171	1438	17171
50°	1356	17482	1356	17482
55°	1323	17621	1323	17621
60°	1356	17534	1356	17534
65°	1414	17039	1414	17039
70°	1463	12887	1463	12887
75°	1622	7112	1622	7112
80°	1674	6601	1674	6601
85°	1667	2779	1667	2779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 17780 cd/sqm



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.8	0.9
10°-20°	159.0	4.0
20°-30°	279.8	7.1
30°-40°	362.2	9.2
40°-50°	399.5	10.1
50°-60°	372.8	9.4
60°-70°	288.0	7.3
70°-80°	132.8	3.4
80°-90°	28.1	0.7
90°-100°	51.8	1.3
100°-110°	151.1	3.8
110°-120°	246.5	6.2
120°-130°	312.9	7.9
130°-140°	334.8	8.5
140°-150°	312.6	7.9
150°-160°	257.2	6.5
160°-170°	172.5	4.4
170°-180°	61.3	1.5
0°-30°	473.7	12.0
0°-40°	835.9	21.1
0°-60°	1608.1	40.6
0°-90°	2057.0	52.0
90°-120°	449.4	11.4
90°-150°	1409.7	35.6
90°-180°	1901.0	48.0
0°-180°	3957.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	208	208	208	208	208	
5°	202	367	202	367	202	19
15°	166	797	166	797	166	46
25°	122	796	122	796	122	56
35°	87	783	87	783	87	55
45°	63	752	63	752	63	49
55°	47	626	47	626	47	42
65°	37	446	37	446	37	36
75°	26	114	26	114	26	27
85°	9	15	9	15	9	9
90°	2	14	2	28	2	2
95°	20	15	20	89	20	25
105°	96	154	96	212	96	102
115°	184	255	184	314	184	181
125°	272	404	272	385	272	244
135°	370	529	370	427	370	286
145°	473	610	473	436	473	296
155°	562	663	562	452	562	258
165°	621	691	621	521	621	175
175°	649	677	649	611	649	62
180°	651	651	651	651	651	



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0
2.5°	206.4	210.3	214.2	218.4	222.7	227.3	232.3	236.5	238.7	240.8	238.7
5°	202.0	215.3	228.7	248.0	269.3	293.6	320.7	343.9	355.4	367.0	355.4
7.5°	194.2	221.3	248.4	305.9	373.4	443.6	516.3	576.6	599.7	622.8	599.7
10°	187.0	224.8	262.6	360.0	477.3	567.6	630.7	681.1	693.6	706.0	693.6
12.5°	179.0	230.3	281.6	401.9	545.2	638.9	683.2	719.6	732.4	745.2	732.4
15°	166.0	239.3	312.7	448.7	605.6	702.0	738.0	768.6	782.8	797.0	782.8
17.5°	152.6	250.2	347.8	486.5	639.0	733.0	768.7	797.3	805.1	812.8	805.1
20°	143.0	257.7	372.3	511.3	658.4	747.3	778.0	802.2	807.1	812.0	807.1
22.5°	134.2	262.4	390.6	529.7	672.6	755.6	778.8	797.5	802.8	808.0	802.8
25°	122.0	266.4	410.9	549.7	686.6	762.3	777.0	788.9	792.5	796.0	792.5
27.5°	110.2	262.8	415.4	552.5	684.3	755.0	764.6	772.7	776.1	779.6	776.1
30°	103.0	258.1	413.2	549.0	678.3	746.6	753.7	760.2	765.1	770.0	765.1
32.5°	96.6	252.4	408.2	542.3	669.2	736.0	742.7	750.5	761.0	771.6	761.0
35°	87.0	240.3	393.7	526.3	652.1	720.3	731.0	743.9	763.5	783.0	763.5
37.5°	78.8	224.8	370.9	502.2	628.6	703.0	725.3	746.7	765.6	784.4	765.6
40°	74.0	214.0	354.0	484.3	611.4	689.9	719.7	746.0	762.0	778.0	762.0
42.5°	69.2	201.7	334.3	463.5	591.7	673.2	707.9	738.0	754.0	770.0	754.0
45°	63.0	182.1	301.2	429.3	560.4	646.4	687.3	721.8	736.9	752.0	736.9
47.5°	57.2	160.7	264.1	392.8	529.9	620.1	663.5	698.8	709.8	720.8	709.8
50°	54.0	146.4	238.9	368.0	509.3	601.3	644.0	678.2	687.1	696.0	687.1
52.5°	50.8	132.6	214.4	343.7	489.0	581.7	621.9	654.0	662.2	670.4	662.2
55°	47.0	113.7	180.3	308.3	456.8	548.6	583.7	611.8	618.9	626.0	618.9
57.5°	43.6	97.4	151.2	275.1	422.5	511.2	541.1	565.0	570.8	576.6	570.8
60°	42.0	88.7	135.3	254.3	397.4	482.6	509.7	531.4	537.2	543.0	537.2
62.5°	39.6	80.2	120.8	233.5	370.2	451.1	476.1	496.2	501.6	507.0	501.6
65°	37.0	69.9	102.8	204.3	328.8	401.4	422.3	438.9	442.4	446.0	442.4
67.5°	33.4	61.3	89.2	177.6	286.1	346.9	359.9	367.9	361.3	354.6	361.3
70°	31.0	56.8	82.6	161.3	257.8	308.2	312.7	311.2	292.1	273.0	292.1
72.5°	29.4	52.3	75.3	143.5	226.8	263.5	253.7	237.4	201.2	165.0	201.2
75°	26.0	44.7	63.3	114.7	176.9	186.7	144.0	112.2	113.1	114.0	113.1
77.5°	21.2	35.2	49.1	80.7	118.1	125.5	102.9	86.2	87.0	87.8	87.0
80°	18.0	29.1	40.2	52.7	65.6	71.6	70.7	70.1	70.6	71.0	70.6
82.5°	14.8	23.1	31.3	38.8	46.0	50.0	50.9	51.4	50.8	50.2	50.8
85°	9.0	13.9	18.8	21.7	23.9	23.2	19.7	16.8	15.9	15.0	15.9
87.5°	3.6	5.9	8.3	8.2	7.2	6.6	6.6	6.8	6.9	6.9	6.9
90°	2.0	4.6	7.9	10.5	12.5	13.2	13.2	13.8	14.5	14.5	14.5
92.5°	7.2	11.4	11.6	11.6	14.1	15.3	16.3	16.4	17.1	17.1	17.1
95°	20.4	22.4	33.5	32.9	22.4	17.8	15.1	15.1	15.1	15.1	15.1
97.5°	38.9	41.8	43.7	58.5	61.8	59.7	48.7	40.9	36.6	34.6	36.6
100°	55.2	56.5	60.5	61.1	77.6	93.4	85.5	75.6	72.3	70.4	72.3
102.5°	71.5	72.3	78.4	81.1	85.0	93.9	121.2	118.2	116.0	115.6	116.0
105°	96.0	96.7	107.8	113.1	115.7	115.7	115.1	128.2	149.3	153.9	149.3
107.5°	122.2	125.2	138.3	152.4	155.4	156.2	152.8	150.8	150.0	150.6	150.0
110°	140.1	144.7	160.4	178.2	182.8	184.1	182.8	180.8	179.5	179.5	179.5



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	157.4	164.1	182.0	202.4	210.1	214.1	211.2	209.8	208.4	209.5	208.4
115°	184.1	194.0	217.6	238.7	254.5	256.4	255.8	255.8	255.1	255.1	255.1
117.5°	208.8	224.6	251.2	275.6	293.9	299.2	301.8	301.0	300.2	301.5	300.2
120°	226.2	244.6	274.8	302.5	320.2	328.1	330.7	329.4	330.7	329.4	330.7
122.5°	244.6	267.2	296.9	325.6	346.5	355.5	358.6	358.9	359.1	358.4	359.1
125°	272.2	299.8	334.7	364.3	386.0	396.5	399.1	399.8	401.1	404.4	401.1
127.5°	300.1	331.4	369.7	398.2	420.4	433.2	437.3	438.7	441.5	442.9	441.5
130°	319.6	355.1	393.9	420.8	442.5	456.3	463.6	465.5	468.8	468.2	468.8
132.5°	340.1	377.2	416.5	444.5	464.6	479.5	485.6	491.3	492.5	493.4	492.5
135°	370.2	410.3	449.7	477.4	496.4	510.9	518.8	524.0	527.3	529.3	527.3
137.5°	401.9	444.2	482.1	506.7	525.9	538.4	547.3	552.8	556.3	557.8	556.3
140°	423.4	464.2	501.0	526.7	543.8	556.3	564.2	570.7	574.7	574.7	574.7
142.5°	444.0	484.2	520.0	545.6	560.6	572.0	580.5	585.5	589.9	589.9	589.9
145°	472.8	512.9	545.7	571.4	583.9	594.4	603.6	607.6	610.2	610.2	610.2
147.5°	502.9	538.4	568.4	593.0	603.5	615.8	623.1	626.2	629.5	628.1	629.5
150°	520.8	553.6	582.6	605.6	616.1	627.9	635.2	637.8	641.1	639.1	641.1
152.5°	538.1	569.4	595.7	617.2	626.1	637.9	646.2	648.8	651.1	649.6	651.1
155°	561.5	589.1	613.5	633.2	641.1	652.3	660.2	663.4	666.1	662.8	666.1
157.5°	582.4	606.2	627.4	645.6	654.0	663.6	670.9	675.0	677.6	676.2	677.6
160°	595.1	616.8	635.8	652.9	660.8	669.4	677.3	681.9	684.5	682.5	684.5
162.5°	605.6	625.2	643.2	658.7	665.5	673.0	682.5	686.6	689.2	686.7	689.2
165°	620.7	636.5	652.3	665.4	671.3	677.3	687.1	691.7	693.7	691.1	693.7
167.5°	632.1	644.2	657.0	668.3	672.6	678.4	688.3	692.1	694.6	691.3	694.6
170°	638.5	649.0	660.2	669.4	672.6	677.9	687.8	691.1	693.0	689.7	693.0
172.5°	643.7	651.6	660.7	668.8	670.5	674.8	684.1	687.4	688.8	686.1	688.8
175°	649.0	653.6	660.2	665.4	664.8	667.4	675.3	677.9	680.5	676.6	680.5
177.5°	651.5	653.6	655.7	658.8	656.7	656.7	662.5	664.1	664.6	662.5	664.6
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0
2.5°	236.5	232.3	227.3	222.7	218.4	214.2	210.3	206.4	210.3	214.2	218.4
5°	343.9	320.7	293.6	269.3	248.0	228.7	215.3	202.0	215.3	228.7	248.0
7.5°	576.6	516.3	443.6	373.4	305.9	248.4	221.3	194.2	221.3	248.4	305.9
10°	681.1	630.7	567.6	477.3	360.0	262.6	224.8	187.0	224.8	262.6	360.0
12.5°	719.6	683.2	638.9	545.2	401.9	281.6	230.3	179.0	230.3	281.6	401.9
15°	768.6	738.0	702.0	605.6	448.7	312.7	239.3	166.0	239.3	312.7	448.7
17.5°	797.3	768.7	733.0	639.0	486.5	347.8	250.2	152.6	250.2	347.8	486.5
20°	802.2	778.0	747.3	658.4	511.3	372.3	257.7	143.0	257.7	372.3	511.3
22.5°	797.5	778.8	755.6	672.6	529.7	390.6	262.4	134.2	262.4	390.6	529.7
25°	788.9	777.0	762.3	686.6	549.7	410.9	266.4	122.0	266.4	410.9	549.7
27.5°	772.7	764.6	755.0	684.3	552.5	415.4	262.8	110.2	262.8	415.4	552.5
30°	760.2	753.7	746.6	678.3	549.0	413.2	258.1	103.0	258.1	413.2	549.0
32.5°	750.5	742.7	736.0	669.2	542.3	408.2	252.4	96.6	252.4	408.2	542.3
35°	743.9	731.0	720.3	652.1	526.3	393.7	240.3	87.0	240.3	393.7	526.3
37.5°	746.7	725.3	703.0	628.6	502.2	370.9	224.8	78.8	224.8	370.9	502.2
40°	746.0	719.7	689.9	611.4	484.3	354.0	214.0	74.0	214.0	354.0	484.3
42.5°	738.0	707.9	673.2	591.7	463.5	334.3	201.7	69.2	201.7	334.3	463.5
45°	721.8	687.3	646.4	560.4	429.3	301.2	182.1	63.0	182.1	301.2	429.3
47.5°	698.8	663.5	620.1	529.9	392.8	264.1	160.7	57.2	160.7	264.1	392.8
50°	678.2	644.0	601.3	509.3	368.0	238.9	146.4	54.0	146.4	238.9	368.0
52.5°	654.0	621.9	581.7	489.0	343.7	214.4	132.6	50.8	132.6	214.4	343.7
55°	611.8	583.7	548.6	456.8	308.3	180.3	113.7	47.0	113.7	180.3	308.3
57.5°	565.0	541.1	511.2	422.5	275.1	151.2	97.4	43.6	97.4	151.2	275.1
60°	531.4	509.7	482.6	397.4	254.3	135.3	88.7	42.0	88.7	135.3	254.3
62.5°	496.2	476.1	451.1	370.2	233.5	120.8	80.2	39.6	80.2	120.8	233.5
65°	438.9	422.3	401.4	328.8	204.3	102.8	69.9	37.0	69.9	102.8	204.3
67.5°	367.9	359.9	346.9	286.1	177.6	89.2	61.3	33.4	61.3	89.2	177.6
70°	311.2	312.7	308.2	257.8	161.3	82.6	56.8	31.0	56.8	82.6	161.3
72.5°	237.4	253.7	263.5	226.8	143.5	75.3	52.3	29.4	52.3	75.3	143.5
75°	112.2	144.0	186.7	176.9	114.7	63.3	44.7	26.0	44.7	63.3	114.7
77.5°	86.2	102.9	125.5	118.1	80.7	49.1	35.2	21.2	35.2	49.1	80.7
80°	70.1	70.7	71.6	65.6	52.7	40.2	29.1	18.0	29.1	40.2	52.7
82.5°	51.4	50.9	50.0	46.0	38.8	31.3	23.1	14.8	23.1	31.3	38.8
85°	16.8	19.7	23.2	23.9	21.7	18.8	13.9	9.0	13.9	18.8	21.7
87.5°	6.8	6.6	6.6	7.2	8.2	8.3	5.9	3.6	5.9	8.2	8.5
90°	13.8	13.2	13.2	12.5	10.5	7.9	4.6	2.0	4.6	7.2	11.8
92.5°	16.4	16.3	15.3	14.1	11.6	11.6	11.4	7.2	12.5	17.8	25.5
95°	15.1	15.1	17.8	22.4	32.9	33.5	22.4	20.4	28.9	40.8	51.3
97.5°	40.9	48.7	59.7	61.8	58.5	43.7	41.8	38.9	53.0	64.7	81.7
100°	75.6	85.5	93.4	77.6	61.1	60.5	56.5	55.2	70.4	81.5	98.0
102.5°	118.2	121.2	93.9	85.0	81.1	78.4	72.3	71.5	86.7	102.0	115.9
105°	128.2	115.1	115.7	115.7	113.1	107.8	96.7	96.0	113.1	130.8	147.9
107.5°	150.8	152.8	156.2	155.4	152.4	138.3	125.2	122.2	137.6	158.9	177.7
110°	180.8	182.8	184.1	182.8	178.2	160.4	144.7	140.1	153.9	176.2	196.6



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	209.8	211.2	214.1	210.1	202.4	182.0	164.1	157.4	171.2	194.1	215.0
115°	255.8	255.8	256.4	254.5	238.7	217.6	194.0	184.1	195.9	217.0	240.0
117.5°	301.0	301.8	299.2	293.9	275.6	251.2	224.6	208.8	218.2	240.4	264.1
120°	329.4	330.7	328.1	320.2	302.5	274.8	244.6	226.2	233.4	255.1	278.8
122.5°	358.9	358.6	355.5	346.5	325.6	296.9	267.2	244.6	247.6	267.7	290.9
125°	399.8	399.1	396.5	386.0	364.3	334.7	299.8	272.2	268.3	285.4	309.0
127.5°	438.7	437.3	433.2	420.4	398.2	369.7	331.4	300.1	291.3	302.1	323.8
130°	465.5	463.6	456.3	442.5	420.8	393.9	355.1	319.6	307.1	313.6	332.7
132.5°	491.3	485.6	479.5	464.6	444.5	416.5	377.2	340.1	322.8	325.7	340.6
135°	524.0	518.8	510.9	496.4	477.4	449.7	410.3	370.2	346.5	343.9	352.4
137.5°	552.8	547.3	538.4	525.9	506.7	482.1	444.2	401.9	372.0	363.2	366.5
140°	570.7	564.2	556.3	543.8	526.7	501.0	464.2	423.4	389.9	377.4	375.4
142.5°	585.5	580.5	572.0	560.6	545.6	520.0	484.2	444.0	408.3	392.1	387.5
145°	607.6	603.6	594.4	583.9	571.4	545.7	512.9	472.8	437.3	416.2	406.4
147.5°	626.2	623.1	615.8	603.5	593.0	568.4	538.4	502.9	466.4	440.4	427.7
150°	637.8	635.2	627.9	616.1	605.6	582.6	553.6	520.8	485.9	458.3	441.9
152.5°	648.8	646.2	637.9	626.1	617.2	595.7	569.4	538.1	502.7	475.1	458.2
155°	663.4	660.2	652.3	641.1	633.2	613.5	589.1	561.5	531.3	502.3	483.3
157.5°	675.0	670.9	663.6	654.0	645.6	627.4	606.2	582.4	556.0	528.4	508.9
160°	681.9	677.3	669.4	660.8	652.9	635.8	616.8	595.1	570.7	545.7	524.7
162.5°	686.6	682.5	673.0	665.5	658.7	643.2	625.2	605.6	583.9	562.1	542.6
165°	691.7	687.1	677.3	671.3	665.4	652.3	636.5	620.7	602.3	584.5	568.8
167.5°	692.1	688.3	678.4	672.6	668.3	657.0	644.2	632.1	617.8	603.9	590.7
170°	691.1	687.8	677.9	672.6	669.4	660.2	649.0	638.5	627.3	615.4	604.9
172.5°	687.4	684.1	674.8	670.5	668.8	660.7	651.6	643.7	634.1	625.4	617.0
175°	677.9	675.3	667.4	664.8	665.4	660.2	653.6	649.0	643.1	637.8	633.2
177.5°	664.1	662.5	656.7	656.7	658.8	655.7	653.6	651.5	648.8	647.3	645.7
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0
2.5°	222.7	227.3	232.3	236.5	238.7	240.8	238.7	236.5	232.3	227.3	222.7
5°	269.3	293.6	320.7	343.9	355.4	367.0	355.4	343.9	320.7	293.6	269.3
7.5°	373.4	443.6	516.3	576.6	599.7	622.8	599.7	576.6	516.3	443.6	373.4
10°	477.3	567.6	630.7	681.1	693.6	706.0	693.6	681.1	630.7	567.6	477.3
12.5°	545.2	638.9	683.2	719.6	732.4	745.2	732.4	719.6	683.2	638.9	545.2
15°	605.6	702.0	738.0	768.6	782.8	797.0	782.8	768.6	738.0	702.0	605.6
17.5°	639.0	733.0	768.7	797.3	805.1	812.8	805.1	797.3	768.7	733.0	639.0
20°	658.4	747.3	778.0	802.2	807.1	812.0	807.1	802.2	778.0	747.3	658.4
22.5°	672.6	755.6	778.8	797.5	802.8	808.0	802.8	797.5	778.8	755.6	672.6
25°	686.6	762.3	777.0	788.9	792.5	796.0	792.5	788.9	777.0	762.3	686.6
27.5°	684.3	755.0	764.6	772.7	776.1	779.6	776.1	772.7	764.6	755.0	684.3
30°	678.3	746.6	753.7	760.2	765.1	770.0	765.1	760.2	753.7	746.6	678.3
32.5°	669.2	736.0	742.7	750.5	761.0	771.6	761.0	750.5	742.7	736.0	669.2
35°	652.1	720.3	731.0	743.9	763.5	783.0	763.5	743.9	731.0	720.3	652.1
37.5°	628.6	703.0	725.3	746.7	765.6	784.4	765.6	746.7	725.3	703.0	628.6
40°	611.4	689.9	719.7	746.0	762.0	778.0	762.0	746.0	719.7	689.9	611.4
42.5°	591.7	673.2	707.9	738.0	754.0	770.0	754.0	738.0	707.9	673.2	591.7
45°	560.4	646.4	687.3	721.8	736.9	752.0	736.9	721.8	687.3	646.4	560.4
47.5°	529.9	620.1	663.5	698.8	709.8	720.8	709.8	698.8	663.5	620.1	529.9
50°	509.3	601.3	644.0	678.2	687.1	696.0	687.1	678.2	644.0	601.3	509.3
52.5°	489.0	581.7	621.9	654.0	662.2	670.4	662.2	654.0	621.9	581.7	489.0
55°	456.8	548.6	583.7	611.8	618.9	626.0	618.9	611.8	583.7	548.6	456.8
57.5°	422.5	511.2	541.1	565.0	570.8	576.6	570.8	565.0	541.1	511.2	422.5
60°	397.4	482.6	509.7	531.4	537.2	543.0	537.2	531.4	509.7	482.6	397.4
62.5°	370.2	451.1	476.1	496.2	501.6	507.0	501.6	496.2	476.1	451.1	370.2
65°	328.8	401.4	422.3	438.9	442.4	446.0	442.4	438.9	422.3	401.4	328.8
67.5°	286.1	346.9	359.9	367.9	361.3	354.6	361.3	367.9	359.9	346.9	286.1
70°	257.8	308.2	312.7	311.2	292.1	273.0	292.1	311.2	312.7	308.2	257.8
72.5°	226.8	263.5	253.7	237.4	201.2	165.0	201.2	237.4	253.7	263.5	226.8
75°	176.9	186.7	144.0	112.2	113.1	114.0	113.1	112.2	144.0	186.7	176.9
77.5°	118.1	125.5	102.9	86.2	87.0	87.8	87.0	86.2	102.9	125.5	118.1
80°	65.6	71.6	70.7	70.1	70.6	71.0	70.6	70.1	70.7	71.6	65.6
82.5°	46.0	50.0	50.9	51.4	50.8	50.2	50.8	51.4	50.9	50.0	46.0
85°	23.9	23.2	19.7	16.8	15.9	15.0	15.9	16.8	19.7	23.2	23.9
87.5°	7.7	7.9	8.9	9.4	9.9	9.7	9.9	9.4	8.9	7.9	7.7
90°	15.1	19.7	24.3	27.0	29.6	28.3	29.6	27.0	24.3	19.7	15.1
92.5°	30.4	38.1	43.8	48.5	50.6	50.4	50.6	48.5	43.8	38.1	30.4
95°	61.1	70.4	79.6	86.1	90.1	88.8	90.1	86.1	79.6	70.4	61.1
97.5°	94.3	106.7	116.9	123.1	127.0	129.7	127.0	123.1	116.9	106.7	94.3
100°	116.4	128.2	140.1	147.3	153.9	156.5	153.9	147.3	140.1	128.2	116.4
102.5°	134.3	149.8	162.7	170.4	176.0	178.6	176.0	170.4	162.7	149.8	134.3
105°	163.7	180.2	194.0	203.8	209.8	211.7	209.8	203.8	194.0	180.2	163.7
107.5°	193.2	210.1	222.9	233.8	241.0	245.3	241.0	233.8	222.9	210.1	193.2
110°	216.3	230.1	243.9	253.8	261.0	263.7	261.0	253.8	243.9	230.1	216.3



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	235.8	251.2	265.0	274.8	283.1	286.8	283.1	274.8	265.0	251.2	235.8
115°	263.0	283.4	295.9	305.1	311.0	314.3	311.0	305.1	295.9	283.4	263.0
117.5°	285.6	306.9	320.6	327.7	330.5	332.8	330.5	327.7	320.6	306.9	285.6
120°	299.8	319.6	335.3	344.5	347.8	349.1	347.8	344.5	335.3	319.6	299.8
122.5°	313.0	331.7	346.9	358.2	363.6	364.9	363.6	358.2	346.9	331.7	313.0
125°	331.4	349.1	364.9	376.1	382.0	385.3	382.0	376.1	364.9	349.1	331.4
127.5°	347.4	366.6	381.1	391.2	397.0	399.6	397.0	391.2	381.1	366.6	347.4
130°	356.4	376.1	390.6	401.7	407.0	409.6	407.0	401.7	390.6	376.1	356.4
132.5°	363.2	384.0	399.0	409.1	414.9	417.5	414.9	409.1	399.0	384.0	363.2
135°	371.5	393.2	409.0	418.8	424.1	426.7	424.1	418.8	409.0	393.2	371.5
137.5°	378.7	398.5	414.9	425.3	430.0	431.7	430.0	425.3	414.9	398.5	378.7
140°	384.0	401.1	417.5	427.4	432.7	433.3	432.7	427.4	401.1	384.0	384.0
142.5°	390.8	404.2	418.6	428.4	433.7	434.9	433.7	428.4	418.6	404.2	390.8
145°	403.1	411.0	420.8	430.0	434.6	435.9	434.6	430.0	420.8	411.0	403.1
147.5°	418.4	420.9	426.1	432.1	436.6	437.5	436.6	432.1	426.1	420.9	418.4
150°	430.0	429.4	431.3	435.3	439.2	438.6	439.2	435.3	431.3	429.4	430.0
152.5°	443.2	439.4	439.2	441.1	442.9	442.8	442.9	441.1	439.2	439.4	443.2
155°	465.5	458.3	454.3	453.0	453.0	452.4	453.0	453.0	454.3	458.3	465.5
157.5°	490.1	480.0	474.1	470.9	470.0	468.6	470.0	470.9	474.1	480.0	490.1
160°	507.0	495.8	489.9	484.6	482.6	480.7	482.6	484.6	489.9	495.8	507.0
162.5°	522.7	512.1	505.6	500.9	498.9	495.9	498.9	500.9	505.6	512.1	522.7
165°	548.4	537.2	530.0	526.0	523.4	520.8	523.4	526.0	530.0	537.2	548.4
167.5°	574.0	561.8	557.1	552.6	550.1	545.4	550.1	552.6	557.1	561.8	574.0
170°	589.8	578.6	576.0	572.0	567.4	562.2	567.4	572.0	576.0	578.6	589.8
172.5°	603.5	596.0	593.4	589.4	588.0	583.8	588.0	589.4	593.4	596.0	603.5
175°	623.3	617.4	617.4	616.8	614.8	610.8	614.8	616.8	617.4	617.4	623.3
177.5°	639.9	636.7	638.9	638.9	638.3	634.6	638.3	638.9	638.9	636.7	639.9
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	208.0	208.0	208.0	208.0
2.5°	218.4	214.2	210.3	206.4
5°	248.0	228.7	215.3	202.0
7.5°	305.9	248.4	221.3	194.2
10°	360.0	262.6	224.8	187.0
12.5°	401.9	281.6	230.3	179.0
15°	448.7	312.7	239.3	166.0
17.5°	486.5	347.8	250.2	152.6
20°	511.3	372.3	257.7	143.0
22.5°	529.7	390.6	262.4	134.2
25°	549.7	410.9	266.4	122.0
27.5°	552.5	415.4	262.8	110.2
30°	549.0	413.2	258.1	103.0
32.5°	542.3	408.2	252.4	96.6
35°	526.3	393.7	240.3	87.0
37.5°	502.2	370.9	224.8	78.8
40°	484.3	354.0	214.0	74.0
42.5°	463.5	334.3	201.7	69.2
45°	429.3	301.2	182.1	63.0
47.5°	392.8	264.1	160.7	57.2
50°	368.0	238.9	146.4	54.0
52.5°	343.7	214.4	132.6	50.8
55°	308.3	180.3	113.7	47.0
57.5°	275.1	151.2	97.4	43.6
60°	254.3	135.3	88.7	42.0
62.5°	233.5	120.8	80.2	39.6
65°	204.3	102.8	69.9	37.0
67.5°	177.6	89.2	61.3	33.4
70°	161.3	82.6	56.8	31.0
72.5°	143.5	75.3	52.3	29.4
75°	114.7	63.3	44.7	26.0
77.5°	80.7	49.1	35.2	21.2
80°	52.7	40.2	29.1	18.0
82.5°	38.8	31.3	23.1	14.8
85°	21.7	18.8	13.9	9.0
87.5°	8.5	8.2	5.9	3.6
90°	11.8	7.2	4.6	2.0
92.5°	25.5	17.8	12.5	7.2
95°	51.3	40.8	28.9	20.4
97.5°	81.7	64.7	53.0	38.9
100°	98.0	81.5	70.4	55.2
102.5°	115.9	102.0	86.7	71.5
105°	147.9	130.8	113.1	96.0
107.5°	177.7	158.9	137.6	122.2
110°	196.6	176.2	153.9	140.1

TEST NUMBER: P1435935

CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	215.0	194.1	171.2	157.4
115°	240.0	217.0	195.9	184.1
117.5°	264.1	240.4	218.2	208.8
120°	278.8	255.1	233.4	226.2
122.5°	290.9	267.7	247.6	244.6
125°	309.0	285.4	268.3	272.2
127.5°	323.8	302.1	291.3	300.1
130°	332.7	313.6	307.1	319.6
132.5°	340.6	325.7	322.8	340.1
135°	352.4	343.9	346.5	370.2
137.5°	366.5	363.2	372.0	401.9
140°	375.4	377.4	389.9	423.4
142.5°	387.5	392.1	408.3	444.0
145°	406.4	416.2	437.3	472.8
147.5°	427.7	440.4	466.4	502.9
150°	441.9	458.3	485.9	520.8
152.5°	458.2	475.1	502.7	538.1
155°	483.3	502.3	531.3	561.5
157.5°	508.9	528.4	556.0	582.4
160°	524.7	545.7	570.7	595.1
162.5°	542.6	562.1	583.9	605.6
165°	568.8	584.5	602.3	620.7
167.5°	590.7	603.9	617.8	632.1
170°	604.9	615.4	627.3	638.5
172.5°	617.0	625.4	634.1	643.7
175°	633.2	637.8	643.1	649.0
177.5°	645.7	647.3	648.8	651.5
180°	650.9	650.9	650.9	650.9



TEST NUMBER: P1435935
 CATALOG NUMBER: SQ2W-FB-K-050U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.56	11.47	11.50	12.43	13.67	20.16	21.07	21.09	22.02	23.26
	3H	11.51	12.32	12.45	13.29	14.55	21.77	22.58	22.71	23.55	24.81
	4H	11.91	12.68	12.87	13.65	14.92	21.95	22.72	22.91	23.69	24.96
	6H	12.16	12.87	13.14	13.85	15.13	22.03	22.74	23.00	23.71	25.00
	8H	12.26	12.93	13.24	13.93	15.21	22.04	22.72	23.02	23.71	25.00
	12H	12.31	12.95	13.29	13.94	15.25	22.02	22.67	23.01	23.65	24.96
4H	2H	15.29	16.06	16.25	17.03	18.30	20.53	21.30	21.50	22.27	23.54
	3H	16.42	17.06	17.40	18.06	19.35	22.42	23.06	23.40	24.06	25.35
	4H	16.71	17.29	17.69	18.28	19.59	22.65	23.23	23.63	24.23	25.54
	6H	16.84	17.35	17.84	18.36	19.67	22.78	23.29	23.78	24.30	25.61
	8H	16.88	17.36	17.88	18.36	19.69	22.83	23.30	23.83	24.31	25.63
	12H	16.89	17.31	17.91	18.34	19.67	22.81	23.24	23.83	24.26	25.59
8H	4H	17.90	18.37	18.90	19.38	20.71	22.74	23.21	23.74	24.22	25.55
	6H	18.16	18.55	19.19	19.60	20.92	22.94	23.33	23.97	24.38	25.70
	8H	18.26	18.60	19.29	19.64	20.98	23.03	23.37	24.07	24.41	25.75
	12H	18.31	18.61	19.34	19.64	21.02	23.04	23.34	24.08	24.37	25.76
12H	4H	17.93	18.35	18.95	19.38	20.71	22.70	23.12	23.71	24.15	25.48
	6H	18.27	18.61	19.30	19.65	20.99	22.92	23.27	23.96	24.30	25.65
	8H	18.41	18.71	19.45	19.74	21.13	23.03	23.33	24.06	24.36	25.74