

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435995

Luminaire Tested: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435995  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7856.3 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 70.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	49	48	42				
2	89	81	75	69	82	75	70	65	64	60	56	53	50	48	43	41	40	35				
3	81	71	63	57	74	66	59	54	56	51	47	47	43	40	38	35	33	29				
4	73	62	54	48	67	58	51	45	49	44	39	41	37	33	34	31	28	24				
5	67	55	47	41	62	51	44	38	44	38	33	37	32	29	30	27	24	21				
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	23	21	18				
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	24	21	18	16				
8	53	40	32	26	48	37	30	25	32	26	22	27	22	19	22	19	16	14				
9	49	36	29	23	45	34	27	22	29	23	19	25	20	17	20	17	14	12				
10	45	33	26	21	42	31	24	20	27	21	17	23	18	15	19	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6513	6513	6513	6513
5°	6350	11536	6350	11536
10°	5946	22449	5946	22449
15°	5382	25838	5382	25838
20°	4766	27060	4766	27060
25°	4215	27504	4215	27504
30°	3725	27844	3725	27844
35°	3325	29934	3325	29934
40°	3024	31804	3024	31804
45°	2790	33305	2790	33305
50°	2630	33907	2630	33907
55°	2567	34178	2567	34178
60°	2632	34009	2632	34009
65°	2743	33046	2743	33046
70°	2837	24996	2837	24996
75°	3144	13793	3144	13793
80°	3245	12803	3245	12803
85°	3242	5391	3242	5391

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 34487 cd/sqm



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.6	0.9
10°-20°	308.4	3.9
20°-30°	542.7	6.9
30°-40°	702.5	8.9
40°-50°	774.8	9.9
50°-60°	723.1	9.2
60°-70°	558.7	7.1
70°-80°	257.5	3.3
80°-90°	54.7	0.7
90°-100°	105.4	1.3
100°-110°	307.3	3.9
110°-120°	501.5	6.4
120°-130°	636.4	8.1
130°-140°	681.0	8.7
140°-150°	635.9	8.1
150°-160°	523.2	6.7
160°-170°	350.9	4.5
170°-180°	124.6	1.6
0°-30°	918.7	11.7
0°-40°	1621.2	20.6
0°-60°	3119.1	39.7
0°-90°	3990.0	50.8
90°-120°	914.2	11.6
90°-150°	2867.5	36.5
90°-180°	3866.0	49.2
0°-180°	7856.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	403	403	403	403	403	
5°	392	712	392	712	392	36
15°	322	1546	322	1546	322	90
25°	237	1544	237	1544	237	109
35°	169	1519	169	1519	169	106
45°	122	1459	122	1459	122	95
55°	91	1214	91	1214	91	82
65°	72	865	72	865	72	70
75°	50	221	50	221	50	52
85°	18	29	18	29	18	18
90°	4	29	4	58	4	4
95°	42	31	42	181	42	50
105°	195	313	195	431	195	208
115°	374	519	374	639	374	369
125°	554	823	554	784	554	495
135°	753	1077	753	868	753	582
145°	962	1241	962	887	962	602
155°	1142	1348	1142	920	1142	525
165°	1263	1406	1263	1059	1263	355
175°	1320	1376	1320	1243	1320	125
180°	1324	1324	1324	1324	1324	



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4
2.5°	400.3	407.9	415.5	423.6	431.9	440.8	450.5	458.8	462.9	467.0	462.9
5°	391.8	417.7	443.5	481.0	522.4	569.4	622.0	667.0	689.4	711.8	689.4
7.5°	376.7	429.2	481.8	593.2	724.3	860.3	1001.3	1118.3	1163.1	1208.0	1163.1
10°	362.7	436.0	509.2	698.2	925.8	1100.8	1223.2	1321.1	1345.2	1369.3	1345.2
12.5°	347.2	446.7	546.1	779.4	1057.4	1239.3	1325.1	1395.7	1420.5	1445.4	1420.5
15°	322.0	464.2	606.4	870.2	1174.5	1361.6	1431.4	1490.7	1518.2	1545.8	1518.2
17.5°	296.0	485.3	674.6	943.7	1239.3	1421.7	1490.9	1546.5	1561.5	1576.5	1561.5
20°	277.4	499.8	722.2	991.8	1277.1	1449.5	1509.0	1556.0	1565.4	1574.9	1565.4
22.5°	260.3	508.9	757.5	1027.5	1304.5	1465.5	1510.5	1546.8	1557.0	1567.2	1557.0
25°	236.6	516.8	796.9	1066.1	1331.6	1478.6	1507.0	1530.1	1537.0	1543.9	1537.0
27.5°	213.7	509.8	805.8	1071.5	1327.2	1464.4	1483.0	1498.6	1505.4	1512.1	1505.4
30°	199.8	500.6	801.5	1064.8	1315.7	1448.0	1461.8	1474.5	1484.0	1493.5	1484.0
32.5°	187.4	489.6	791.8	1051.9	1297.9	1427.5	1440.6	1455.5	1476.1	1496.6	1476.1
35°	168.7	466.1	763.5	1020.9	1264.8	1397.1	1417.8	1442.8	1480.7	1518.7	1480.7
37.5°	152.8	436.1	719.4	974.0	1219.2	1363.4	1406.7	1448.3	1484.8	1521.4	1484.8
40°	143.5	415.1	686.6	939.4	1185.9	1338.1	1395.8	1446.9	1477.9	1509.0	1477.9
42.5°	134.2	391.3	648.3	899.1	1147.7	1305.7	1373.1	1431.4	1462.4	1493.5	1462.4
45°	122.2	353.2	584.2	832.7	1087.0	1253.8	1333.1	1399.9	1429.2	1458.6	1429.2
47.5°	110.9	311.6	512.3	761.9	1027.7	1202.7	1286.8	1355.3	1376.7	1398.0	1376.7
50°	104.7	284.0	463.3	713.8	987.9	1166.3	1249.1	1315.5	1332.7	1349.9	1332.7
52.5°	98.5	257.1	415.8	666.7	948.4	1128.2	1206.2	1268.6	1284.4	1300.3	1284.4
55°	91.2	220.5	349.8	598.0	885.9	1064.0	1132.1	1186.6	1200.4	1214.2	1200.4
57.5°	84.6	188.9	293.2	533.6	819.5	991.5	1049.6	1095.9	1107.1	1118.4	1107.1
60°	81.5	172.0	262.5	493.3	770.9	935.9	988.5	1030.8	1042.0	1053.2	1042.0
62.5°	76.8	155.6	234.4	453.0	718.1	874.9	923.4	962.3	972.8	983.4	972.8
65°	71.8	135.6	199.3	396.3	637.7	778.6	819.1	851.3	858.1	865.0	858.1
67.5°	64.8	118.9	173.1	344.5	555.0	672.8	698.0	713.6	700.7	687.8	700.7
70°	60.1	110.1	160.1	312.9	500.0	597.8	606.4	603.6	566.6	529.5	566.6
72.5°	57.0	101.5	146.0	278.3	439.8	511.1	492.1	460.4	390.2	320.0	390.2
75°	50.4	86.6	122.8	222.4	343.1	362.1	279.3	217.7	219.4	221.1	219.4
77.5°	41.1	68.2	95.3	156.5	229.0	243.4	199.6	167.2	168.7	170.3	168.7
80°	34.9	56.5	78.0	102.2	127.1	138.8	137.1	136.0	136.8	137.7	136.8
82.5°	28.7	44.7	60.8	75.3	89.2	97.1	98.8	99.8	98.6	97.4	98.6
85°	17.5	26.9	36.4	42.0	46.3	45.0	38.1	32.5	30.8	29.1	30.8
87.5°	7.0	11.5	16.3	16.2	14.2	13.1	13.1	13.4	13.6	13.6	13.6
90°	4.0	9.4	16.1	21.4	25.4	26.8	26.8	28.1	29.4	29.4	29.4
92.5°	14.7	23.3	23.5	23.5	28.6	31.0	33.2	33.4	34.8	34.8	34.8
95°	41.5	45.5	68.2	66.9	45.5	36.1	30.8	30.8	30.8	30.8	30.8
97.5°	79.2	85.1	88.8	119.0	125.7	121.4	99.0	83.2	74.4	70.4	74.4
100°	112.4	115.0	123.1	124.4	157.8	189.9	173.9	153.8	147.1	143.1	147.1
102.5°	145.5	147.1	159.4	165.1	172.8	191.0	246.6	240.5	235.9	235.1	235.9
105°	195.3	196.6	219.4	230.1	235.4	235.4	234.1	260.8	303.6	313.0	303.6
107.5°	248.5	254.7	281.4	310.0	316.2	317.8	310.8	306.8	305.2	306.3	305.2
110°	284.9	294.3	326.4	362.5	371.8	374.5	371.8	367.8	365.1	365.1	365.1



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	320.2	333.9	370.2	411.7	427.5	435.5	429.6	426.7	424.0	426.1	424.0
115°	374.5	394.6	442.7	485.5	517.6	521.6	520.3	520.3	519.0	519.0	519.0
117.5°	424.8	456.9	510.9	560.7	597.9	608.6	613.9	612.3	610.7	613.4	610.7
120°	460.1	497.6	559.1	615.3	651.4	667.4	672.8	670.1	672.8	670.1	672.8
122.5°	497.6	543.6	604.0	662.4	704.9	723.1	729.5	730.0	730.6	729.0	730.6
125°	553.7	609.9	680.8	741.0	785.1	806.5	811.9	813.2	815.9	822.6	815.9
127.5°	610.5	674.1	752.0	810.0	855.2	881.2	889.5	892.4	898.0	901.0	898.0
130°	650.0	722.3	801.2	856.0	900.2	928.3	943.0	947.0	953.7	952.3	953.7
132.5°	691.8	767.2	847.2	904.2	945.1	975.3	987.9	999.4	1001.8	1003.7	1001.8
135°	753.0	834.6	914.9	971.1	1009.8	1039.3	1055.3	1066.0	1072.7	1076.7	1072.7
137.5°	817.5	903.6	980.7	1030.7	1069.8	1095.2	1113.4	1124.6	1131.6	1134.8	1131.6
140°	861.4	944.3	1019.2	1071.4	1106.1	1131.6	1147.6	1161.0	1169.0	1169.0	1169.0
142.5°	903.1	985.0	1057.7	1109.9	1140.4	1163.7	1180.8	1190.9	1200.0	1200.0	1200.0
145°	961.7	1043.3	1110.2	1162.3	1187.7	1209.1	1227.9	1235.9	1241.2	1241.2	1241.2
147.5°	1023.0	1095.2	1156.2	1206.2	1227.6	1252.7	1267.5	1273.9	1280.6	1277.6	1280.6
150°	1059.3	1126.2	1185.1	1231.9	1253.3	1277.4	1292.1	1297.4	1304.1	1300.1	1304.1
152.5°	1094.6	1158.3	1211.8	1255.4	1273.6	1297.7	1314.5	1319.9	1324.4	1321.5	1324.4
155°	1142.3	1198.4	1247.9	1288.1	1304.1	1326.8	1342.9	1349.6	1354.9	1348.2	1354.9
157.5°	1184.8	1233.2	1276.3	1313.2	1330.3	1349.9	1364.8	1373.1	1378.5	1375.5	1378.5
160°	1210.5	1254.6	1293.4	1328.2	1344.2	1361.6	1377.7	1387.0	1392.4	1388.4	1392.4
162.5°	1231.9	1271.7	1308.4	1340.0	1353.9	1369.1	1388.4	1396.7	1402.0	1396.9	1402.0
165°	1262.6	1294.7	1326.8	1353.6	1365.6	1377.7	1397.7	1407.1	1411.1	1405.8	1411.1
167.5°	1285.9	1310.5	1336.5	1359.5	1368.3	1380.1	1400.1	1407.9	1413.0	1406.3	1413.0
170°	1298.8	1320.2	1342.9	1361.6	1368.3	1379.0	1399.1	1405.8	1409.8	1403.1	1409.8
172.5°	1309.5	1325.5	1344.0	1360.6	1364.0	1372.6	1391.6	1398.3	1401.2	1395.6	1401.2
175°	1320.2	1329.5	1342.9	1353.6	1352.3	1357.6	1373.7	1379.0	1384.4	1376.3	1384.4
177.5°	1325.2	1329.5	1333.8	1340.2	1335.9	1335.9	1347.7	1350.9	1352.0	1347.7	1352.0
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4
2.5°	458.8	450.5	440.8	431.9	423.6	415.5	407.9	400.3	407.9	415.5	423.6
5°	667.0	622.0	569.4	522.4	481.0	443.5	417.7	391.8	417.7	443.5	481.0
7.5°	1118.3	1001.3	860.3	724.3	593.2	481.8	429.2	376.7	429.2	481.8	593.2
10°	1321.1	1223.2	1100.8	925.8	698.2	509.2	436.0	362.7	436.0	509.2	698.2
12.5°	1395.7	1325.1	1239.3	1057.4	779.4	546.1	446.7	347.2	446.7	546.1	779.4
15°	1490.7	1431.4	1361.6	1174.5	870.2	606.4	464.2	322.0	464.2	606.4	870.2
17.5°	1546.5	1490.9	1421.7	1239.3	943.7	674.6	485.3	296.0	485.3	674.6	943.7
20°	1556.0	1509.0	1449.5	1277.1	991.8	722.2	499.8	277.4	499.8	722.2	991.8
22.5°	1546.8	1510.5	1465.5	1304.5	1027.5	757.5	508.9	260.3	508.9	757.5	1027.5
25°	1530.1	1507.0	1478.6	1331.6	1066.1	796.9	516.8	236.6	516.8	796.9	1066.1
27.5°	1498.6	1483.0	1464.4	1327.2	1071.5	805.8	509.8	213.7	509.8	805.8	1071.5
30°	1474.5	1461.8	1448.0	1315.7	1064.8	801.5	500.6	199.8	500.6	801.5	1064.8
32.5°	1455.5	1440.6	1427.5	1297.9	1051.9	791.8	489.6	187.4	489.6	791.8	1051.9
35°	1442.8	1417.8	1397.1	1264.8	1020.9	763.5	466.1	168.7	466.1	763.5	1020.9
37.5°	1448.3	1406.7	1363.4	1219.2	974.0	719.4	436.1	152.8	436.1	719.4	974.0
40°	1446.9	1395.8	1338.1	1185.9	939.4	686.6	415.1	143.5	415.1	686.6	939.4
42.5°	1431.4	1373.1	1305.7	1147.7	899.1	648.3	391.3	134.2	391.3	648.3	899.1
45°	1399.9	1333.1	1253.8	1087.0	832.7	584.2	353.2	122.2	353.2	584.2	832.7
47.5°	1355.3	1286.8	1202.7	1027.7	761.9	512.3	311.6	110.9	311.6	512.3	761.9
50°	1315.5	1249.1	1166.3	987.9	713.8	463.3	284.0	104.7	284.0	463.3	713.8
52.5°	1268.6	1206.2	1128.2	948.4	666.7	415.8	257.1	98.5	257.1	415.8	666.7
55°	1186.6	1132.1	1064.0	885.9	598.0	349.8	220.5	91.2	220.5	349.8	598.0
57.5°	1095.9	1049.6	991.5	819.5	533.6	293.2	188.9	84.6	188.9	293.2	533.6
60°	1030.8	988.5	935.9	770.9	493.3	262.5	172.0	81.5	172.0	262.5	493.3
62.5°	962.3	923.4	874.9	718.1	453.0	234.4	155.6	76.8	155.6	234.4	453.0
65°	851.3	819.1	778.6	637.7	396.3	199.3	135.6	71.8	135.6	199.3	396.3
67.5°	713.6	698.0	672.8	555.0	344.5	173.1	118.9	64.8	118.9	173.1	344.5
70°	603.6	606.4	597.8	500.0	312.9	160.1	110.1	60.1	110.1	160.1	312.9
72.5°	460.4	492.1	511.1	439.8	278.3	146.0	101.5	57.0	101.5	146.0	278.3
75°	217.7	279.3	362.1	343.1	222.4	122.8	86.6	50.4	86.6	122.8	222.4
77.5°	167.2	199.6	243.4	229.0	156.5	95.3	68.2	41.1	68.2	95.3	156.5
80°	136.0	137.1	138.8	127.1	102.2	78.0	56.5	34.9	56.5	78.0	102.2
82.5°	99.8	98.8	97.1	89.2	75.3	60.8	44.7	28.7	44.7	60.8	75.3
85°	32.5	38.1	45.0	46.3	42.0	36.4	26.9	17.5	26.9	36.4	42.0
87.5°	13.4	13.1	13.1	14.2	16.2	16.3	11.5	7.0	11.5	16.0	16.7
90°	28.1	26.8	26.8	25.4	21.4	16.1	9.4	4.0	9.4	14.7	24.1
92.5°	33.4	33.2	31.0	28.6	23.5	23.5	23.3	14.7	25.4	36.1	51.9
95°	30.8	30.8	36.1	45.5	66.9	68.2	45.5	41.5	58.9	82.9	104.3
97.5°	83.2	99.0	121.4	125.7	119.0	88.8	85.1	79.2	107.8	131.6	166.1
100°	153.8	173.9	189.9	157.8	124.4	123.1	115.0	112.4	143.1	165.9	199.3
102.5°	240.5	246.6	191.0	172.8	165.1	159.4	147.1	145.5	176.3	207.6	235.7
105°	260.8	234.1	235.4	235.4	230.1	219.4	196.6	195.3	230.1	266.2	300.9
107.5°	306.8	310.8	317.8	316.2	310.0	281.4	254.7	248.5	279.8	323.2	361.4
110°	367.8	371.8	374.5	371.8	362.5	326.4	294.3	284.9	313.0	358.5	399.9



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	426.7	429.6	435.5	427.5	411.7	370.2	333.9	320.2	348.3	394.8	437.4
115°	520.3	520.3	521.6	517.6	485.5	442.7	394.6	374.5	398.6	441.4	488.2
117.5°	612.3	613.9	608.6	597.9	560.7	510.9	456.9	424.8	443.8	489.0	537.2
120°	670.1	672.8	667.4	651.4	615.3	559.1	497.6	460.1	474.8	519.0	567.1
122.5°	730.0	729.5	723.1	704.9	662.4	604.0	543.6	497.6	503.7	544.6	591.7
125°	813.2	811.9	806.5	785.1	741.0	680.8	609.9	553.7	545.7	580.5	628.6
127.5°	892.4	889.5	881.2	855.2	810.0	752.0	674.1	610.5	592.5	614.5	658.6
130°	947.0	943.0	928.3	900.2	856.0	801.2	722.3	650.0	624.6	638.0	676.8
132.5°	999.4	987.9	975.3	945.1	904.2	847.2	767.2	691.8	656.7	662.6	692.8
135°	1066.0	1055.3	1039.3	1009.8	971.1	914.9	834.6	753.0	704.9	699.5	716.9
137.5°	1124.6	1113.4	1095.2	1069.8	1030.7	980.7	903.6	817.5	756.8	738.9	745.5
140°	1161.0	1147.6	1131.6	1106.1	1071.4	1019.2	944.3	861.4	793.2	767.8	763.7
142.5°	1190.9	1180.8	1163.7	1140.4	1109.9	1057.7	985.0	903.1	830.6	797.7	788.3
145°	1235.9	1227.9	1209.1	1187.7	1162.3	1110.2	1043.3	961.7	889.5	846.7	826.6
147.5°	1273.9	1267.5	1252.7	1227.6	1206.2	1156.2	1095.2	1023.0	948.9	895.9	869.9
150°	1297.4	1292.1	1277.4	1253.3	1231.9	1185.1	1126.2	1059.3	988.4	932.3	898.8
152.5°	1319.9	1314.5	1297.7	1273.6	1255.4	1211.8	1158.3	1094.6	1022.7	966.5	932.0
155°	1349.6	1342.9	1326.8	1304.1	1288.1	1247.9	1198.4	1142.3	1080.7	1021.9	983.1
157.5°	1373.1	1364.8	1349.9	1330.3	1313.2	1276.3	1233.2	1184.8	1131.0	1074.9	1035.3
160°	1387.0	1377.7	1361.6	1344.2	1328.2	1293.4	1254.6	1210.5	1161.0	1110.2	1067.4
162.5°	1396.7	1388.4	1369.1	1353.9	1340.0	1308.4	1271.7	1231.9	1187.7	1143.3	1103.7
165°	1407.1	1397.7	1377.7	1365.6	1353.6	1326.8	1294.7	1262.6	1225.2	1189.1	1157.0
167.5°	1407.9	1400.1	1380.1	1368.3	1359.5	1336.5	1310.5	1285.9	1256.8	1228.4	1201.7
170°	1405.8	1399.1	1379.0	1368.3	1361.6	1342.9	1320.2	1298.8	1276.0	1251.9	1230.5
172.5°	1398.3	1391.6	1372.6	1364.0	1360.6	1344.0	1325.5	1309.5	1289.9	1272.3	1255.2
175°	1379.0	1373.7	1357.6	1352.3	1353.6	1342.9	1329.5	1320.2	1308.1	1297.4	1288.1
177.5°	1350.9	1347.7	1335.9	1335.9	1340.2	1333.8	1329.5	1325.2	1319.9	1316.7	1313.5
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4
2.5°	431.9	440.8	450.5	458.8	462.9	467.0	462.9	458.8	450.5	440.8	431.9
5°	522.4	569.4	622.0	667.0	689.4	711.8	689.4	667.0	622.0	569.4	522.4
7.5°	724.3	860.3	1001.3	1118.3	1163.1	1208.0	1163.1	1118.3	1001.3	860.3	724.3
10°	925.8	1100.8	1223.2	1321.1	1345.2	1369.3	1345.2	1321.1	1223.2	1100.8	925.8
12.5°	1057.4	1239.3	1325.1	1395.7	1420.5	1445.4	1420.5	1395.7	1325.1	1239.3	1057.4
15°	1174.5	1361.6	1431.4	1490.7	1518.2	1545.8	1518.2	1490.7	1431.4	1361.6	1174.5
17.5°	1239.3	1421.7	1490.9	1546.5	1561.5	1576.5	1561.5	1546.5	1490.9	1421.7	1239.3
20°	1277.1	1449.5	1509.0	1556.0	1565.4	1574.9	1565.4	1556.0	1509.0	1449.5	1277.1
22.5°	1304.5	1465.5	1510.5	1546.8	1557.0	1567.2	1557.0	1546.8	1510.5	1465.5	1304.5
25°	1331.6	1478.6	1507.0	1530.1	1537.0	1543.9	1537.0	1530.1	1507.0	1478.6	1331.6
27.5°	1327.2	1464.4	1483.0	1498.6	1505.4	1512.1	1505.4	1498.6	1483.0	1464.4	1327.2
30°	1315.7	1448.0	1461.8	1474.5	1484.0	1493.5	1484.0	1474.5	1461.8	1448.0	1315.7
32.5°	1297.9	1427.5	1440.6	1455.5	1476.1	1496.6	1476.1	1455.5	1440.6	1427.5	1297.9
35°	1264.8	1397.1	1417.8	1442.8	1480.7	1518.7	1480.7	1442.8	1417.8	1397.1	1264.8
37.5°	1219.2	1363.4	1406.7	1448.3	1484.8	1521.4	1484.8	1448.3	1406.7	1363.4	1219.2
40°	1185.9	1338.1	1395.8	1446.9	1477.9	1509.0	1477.9	1446.9	1395.8	1338.1	1185.9
42.5°	1147.7	1305.7	1373.1	1431.4	1462.4	1493.5	1462.4	1431.4	1373.1	1305.7	1147.7
45°	1087.0	1253.8	1333.1	1399.9	1429.2	1458.6	1429.2	1399.9	1333.1	1253.8	1087.0
47.5°	1027.7	1202.7	1286.8	1355.3	1376.7	1398.0	1376.7	1355.3	1286.8	1202.7	1027.7
50°	987.9	1166.3	1249.1	1315.5	1332.7	1349.9	1332.7	1315.5	1249.1	1166.3	987.9
52.5°	948.4	1128.2	1206.2	1268.6	1284.4	1300.3	1284.4	1268.6	1206.2	1128.2	948.4
55°	885.9	1064.0	1132.1	1186.6	1200.4	1214.2	1200.4	1186.6	1132.1	1064.0	885.9
57.5°	819.5	991.5	1049.6	1095.9	1107.1	1118.4	1107.1	1095.9	1049.6	991.5	819.5
60°	770.9	935.9	988.5	1030.8	1042.0	1053.2	1042.0	1030.8	988.5	935.9	770.9
62.5°	718.1	874.9	923.4	962.3	972.8	983.4	972.8	962.3	923.4	874.9	718.1
65°	637.7	778.6	819.1	851.3	858.1	865.0	858.1	851.3	819.1	778.6	637.7
67.5°	555.0	672.8	698.0	713.6	700.7	687.8	700.7	713.6	698.0	672.8	555.0
70°	500.0	597.8	606.4	603.6	566.6	529.5	566.6	603.6	606.4	597.8	500.0
72.5°	439.8	511.1	492.1	460.4	390.2	320.0	390.2	460.4	492.1	511.1	439.8
75°	343.1	362.1	279.3	217.7	219.4	221.1	219.4	217.7	279.3	362.1	343.1
77.5°	229.0	243.4	199.6	167.2	168.7	170.3	168.7	167.2	199.6	243.4	229.0
80°	127.1	138.8	137.1	136.0	136.8	137.7	136.8	136.0	137.1	138.8	127.1
82.5°	89.2	97.1	98.8	99.8	98.6	97.4	98.6	99.8	98.8	97.1	89.2
85°	46.3	45.0	38.1	32.5	30.8	29.1	30.8	32.5	38.1	45.0	46.3
87.5°	15.3	15.8	17.7	18.7	19.8	19.3	19.8	18.7	17.7	15.8	15.3
90°	30.8	40.1	49.5	54.8	60.2	57.5	60.2	54.8	49.5	40.1	30.8
92.5°	61.8	77.6	89.1	98.7	103.0	102.5	103.0	98.7	89.1	77.6	61.8
95°	124.4	143.1	161.8	175.2	183.2	180.6	183.2	175.2	161.8	143.1	124.4
97.5°	191.8	216.9	237.8	250.4	258.4	263.8	258.4	250.4	237.8	216.9	191.8
100°	236.7	260.8	284.9	299.6	313.0	318.3	313.0	299.6	284.9	260.8	236.7
102.5°	273.1	304.7	330.9	346.7	357.9	363.3	357.9	346.7	330.9	304.7	273.1
105°	333.0	366.5	394.6	414.6	426.7	430.7	426.7	414.6	394.6	366.5	333.0
107.5°	393.0	427.5	453.4	475.6	490.3	498.9	490.3	475.6	453.4	427.5	393.0
110°	440.1	468.1	496.2	516.3	531.0	536.4	531.0	516.3	496.2	468.1	440.1



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	479.6	510.9	539.0	559.1	575.9	583.4	575.9	559.1	539.0	510.9	479.6
115°	535.0	576.5	601.9	620.6	632.7	639.3	632.7	620.6	601.9	576.5	535.0
117.5°	581.0	624.4	652.2	666.6	672.3	677.1	672.3	666.6	652.2	624.4	581.0
120°	609.9	650.0	682.1	700.9	707.6	710.2	707.6	700.9	682.1	650.0	609.9
122.5°	636.7	674.7	705.7	728.7	739.7	742.3	739.7	728.7	705.7	674.7	636.7
125°	674.1	710.2	742.3	765.1	777.1	783.8	777.1	765.1	742.3	710.2	674.1
127.5°	706.8	745.8	775.2	795.8	807.6	813.0	807.6	795.8	775.2	745.8	706.8
130°	724.9	765.1	794.5	817.2	827.9	833.3	827.9	817.2	794.5	765.1	724.9
132.5°	738.9	781.1	811.6	832.2	844.0	849.3	844.0	832.2	811.6	781.1	738.9
135°	755.7	799.9	832.0	852.0	862.7	868.1	862.7	852.0	832.0	799.9	755.7
137.5°	770.4	810.6	844.0	865.1	874.8	878.2	874.8	865.1	844.0	810.6	770.4
140°	781.1	815.9	849.3	869.4	880.1	881.4	880.1	869.4	849.3	815.9	781.1
142.5°	795.0	822.3	851.5	871.5	882.2	884.7	882.2	871.5	851.5	822.3	795.0
145°	819.9	836.0	856.0	874.8	884.1	886.8	884.1	874.8	856.0	836.0	819.9
147.5°	851.2	856.3	866.7	879.0	888.1	890.0	888.1	879.0	866.7	856.3	851.2
150°	874.8	873.4	877.4	885.5	893.5	892.1	893.5	885.5	877.4	873.4	874.8
152.5°	901.5	893.7	893.5	897.2	901.0	900.7	901.0	897.2	893.5	893.7	901.5
155°	947.0	932.3	924.2	921.6	921.6	920.2	921.6	921.6	924.2	932.3	947.0
157.5°	997.0	976.4	964.4	957.9	956.1	953.1	956.1	957.9	964.4	976.4	997.0
160°	1031.2	1008.5	996.5	985.8	981.8	977.7	981.8	985.8	996.5	1008.5	1031.2
162.5°	1063.3	1041.7	1028.6	1018.9	1014.9	1008.8	1014.9	1018.9	1028.6	1041.7	1063.3
165°	1115.5	1092.8	1078.1	1070.0	1064.7	1059.3	1064.7	1070.0	1078.1	1092.8	1115.5
167.5°	1167.7	1142.8	1133.2	1124.1	1119.0	1109.4	1119.0	1124.1	1133.2	1142.8	1167.7
170°	1199.8	1177.0	1171.7	1163.7	1154.3	1143.6	1154.3	1163.7	1171.7	1177.0	1199.8
172.5°	1227.6	1212.4	1207.0	1199.0	1196.0	1187.5	1196.0	1199.0	1207.0	1212.4	1227.6
175°	1268.0	1256.0	1256.0	1254.6	1250.6	1242.6	1250.6	1254.6	1256.0	1256.0	1268.0
177.5°	1301.7	1295.3	1299.6	1299.6	1298.5	1291.0	1298.5	1299.6	1299.6	1295.3	1301.7
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2

TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	403.4	403.4	403.4	403.4
2.5°	423.6	415.5	407.9	400.3
5°	481.0	443.5	417.7	391.8
7.5°	593.2	481.8	429.2	376.7
10°	698.2	509.2	436.0	362.7
12.5°	779.4	546.1	446.7	347.2
15°	870.2	606.4	464.2	322.0
17.5°	943.7	674.6	485.3	296.0
20°	991.8	722.2	499.8	277.4
22.5°	1027.5	757.5	508.9	260.3
25°	1066.1	796.9	516.8	236.6
27.5°	1071.5	805.8	509.8	213.7
30°	1064.8	801.5	500.6	199.8
32.5°	1051.9	791.8	489.6	187.4
35°	1020.9	763.5	466.1	168.7
37.5°	974.0	719.4	436.1	152.8
40°	939.4	686.6	415.1	143.5
42.5°	899.1	648.3	391.3	134.2
45°	832.7	584.2	353.2	122.2
47.5°	761.9	512.3	311.6	110.9
50°	713.8	463.3	284.0	104.7
52.5°	666.7	415.8	257.1	98.5
55°	598.0	349.8	220.5	91.2
57.5°	533.6	293.2	188.9	84.6
60°	493.3	262.5	172.0	81.5
62.5°	453.0	234.4	155.6	76.8
65°	396.3	199.3	135.6	71.8
67.5°	344.5	173.1	118.9	64.8
70°	312.9	160.1	110.1	60.1
72.5°	278.3	146.0	101.5	57.0
75°	222.4	122.8	86.6	50.4
77.5°	156.5	95.3	68.2	41.1
80°	102.2	78.0	56.5	34.9
82.5°	75.3	60.8	44.7	28.7
85°	42.0	36.4	26.9	17.5
87.5°	16.7	16.0	11.5	7.0
90°	24.1	14.7	9.4	4.0
92.5°	51.9	36.1	25.4	14.7
95°	104.3	82.9	58.9	41.5
97.5°	166.1	131.6	107.8	79.2
100°	199.3	165.9	143.1	112.4
102.5°	235.7	207.6	176.3	145.5
105°	300.9	266.2	230.1	195.3
107.5°	361.4	323.2	279.8	248.5
110°	399.9	358.5	313.0	284.9



TEST NUMBER: P1435995

CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	437.4	394.8	348.3	320.2
115°	488.2	441.4	398.6	374.5
117.5°	537.2	489.0	443.8	424.8
120°	567.1	519.0	474.8	460.1
122.5°	591.7	544.6	503.7	497.6
125°	628.6	580.5	545.7	553.7
127.5°	658.6	614.5	592.5	610.5
130°	676.8	638.0	624.6	650.0
132.5°	692.8	662.6	656.7	691.8
135°	716.9	699.5	704.9	753.0
137.5°	745.5	738.9	756.8	817.5
140°	763.7	767.8	793.2	861.4
142.5°	788.3	797.7	830.6	903.1
145°	826.6	846.7	889.5	961.7
147.5°	869.9	895.9	948.9	1023.0
150°	898.8	932.3	988.4	1059.3
152.5°	932.0	966.5	1022.7	1094.6
155°	983.1	1021.9	1080.7	1142.3
157.5°	1035.3	1074.9	1131.0	1184.8
160°	1067.4	1110.2	1161.0	1210.5
162.5°	1103.7	1143.3	1187.7	1231.9
165°	1157.0	1189.1	1225.2	1262.6
167.5°	1201.7	1228.4	1256.8	1285.9
170°	1230.5	1251.9	1276.0	1298.8
172.5°	1255.2	1272.3	1289.9	1309.5
175°	1288.1	1297.4	1308.1	1320.2
177.5°	1313.5	1316.7	1319.9	1325.2
180°	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1435995  
 CATALOG NUMBER: SQ2W-FB-K-100U-100D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.76	13.65	13.70	14.62	15.88	22.35	23.25	23.30	24.21	25.47
	3H	13.70	14.50	14.65	15.48	16.76	23.96	24.77	24.92	25.74	27.02
	4H	14.10	14.86	15.07	15.84	17.13	24.14	24.90	25.11	25.88	27.17
	6H	14.35	15.05	15.34	16.04	17.34	24.22	24.92	25.20	25.90	27.20
	8H	14.45	15.11	15.44	16.12	17.41	24.24	24.90	25.22	25.91	27.20
	12H	14.50	15.13	15.49	16.13	17.45	24.22	24.85	25.21	25.85	27.17
4H	2H	17.48	18.24	18.46	19.22	20.51	22.72	23.48	23.70	24.46	25.75
	3H	18.61	19.25	19.60	20.25	21.56	24.61	25.25	25.60	26.26	27.56
	4H	18.90	19.48	19.89	20.48	21.80	24.84	25.42	25.83	26.42	27.74
	6H	19.03	19.53	20.04	20.56	21.88	24.97	25.47	25.98	26.49	27.82
	8H	19.07	19.54	20.08	20.56	21.90	25.02	25.48	26.03	26.50	27.84
	12H	19.08	19.50	20.11	20.53	21.88	25.00	25.42	26.03	26.45	27.80
8H	4H	20.09	20.56	21.10	21.57	22.91	24.93	25.40	25.94	26.41	27.75
	6H	20.35	20.74	21.39	21.80	23.13	25.13	25.51	26.16	26.57	27.91
	8H	20.45	20.79	21.49	21.83	23.19	25.22	25.56	26.26	26.60	27.96
	12H	20.49	20.79	21.54	21.83	23.23	25.23	25.52	26.27	26.57	27.96
12H	4H	20.12	20.54	21.15	21.57	22.92	24.88	25.31	25.91	26.34	27.68
	6H	20.46	20.80	21.50	21.84	23.20	25.11	25.45	26.16	26.50	27.85
	8H	20.60	20.90	21.64	21.94	23.33	25.22	25.51	26.26	26.55	27.95