

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1436025

Luminaire Tested: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1436025  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9870.2 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 93.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	50	48	47	42
2	89	81	75	69	81	75	69	65	63	59	56	53	50	47	43	41	39	35
3	81	71	63	57	74	65	59	54	56	51	46	46	43	39	38	35	33	29
4	73	62	54	48	67	58	50	45	49	43	39	41	37	33	33	30	28	24
5	67	55	47	41	62	51	44	38	43	38	33	36	32	28	30	26	24	21
6	62	49	41	35	56	46	38	33	39	33	29	33	28	25	27	23	21	18
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	15
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	19	16	13
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	19	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8110	8110	8110	8110
5°	7906	14364	7906	14364
10°	7404	27953	7404	27953
15°	6701	32173	6701	32173
20°	5935	33693	5935	33693
25°	5248	34247	5248	34247
30°	4638	34669	4638	34669
35°	4141	37272	4141	37272
40°	3766	39601	3766	39601
45°	3473	41467	3473	41467
50°	3275	42221	3275	42221
55°	3195	42556	3195	42556
60°	3274	42347	3274	42347
65°	3415	41149	3415	41149
70°	3536	31123	3536	31123
75°	3918	17174	3918	17174
80°	4045	15946	4045	15946
85°	4020	6706	4020	6706

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 42942 cd/sqm



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.2	0.9
10°-20°	384.0	3.9
20°-30°	675.7	6.8
30°-40°	874.7	8.9
40°-50°	964.7	9.8
50°-60°	900.4	9.1
60°-70°	695.6	7.0
70°-80°	320.7	3.2
80°-90°	68.2	0.7
90°-100°	133.6	1.4
100°-110°	389.6	3.9
110°-120°	635.9	6.4
120°-130°	806.9	8.2
130°-140°	863.4	8.7
140°-150°	806.2	8.2
150°-160°	663.4	6.7
160°-170°	444.9	4.5
170°-180°	158.0	1.6
0°-30°	1143.9	11.6
0°-40°	2018.6	20.5
0°-60°	3883.7	39.3
0°-90°	4968.2	50.3
90°-120°	1159.2	11.7
90°-150°	3635.7	36.8
90°-180°	4902.0	49.7
0°-180°	9870.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	502	502	502	502	502	
5°	488	886	488	886	488	45
15°	401	1925	401	1925	401	112
25°	295	1922	295	1922	295	135
35°	210	1891	210	1891	210	132
45°	152	1816	152	1816	152	118
55°	114	1512	114	1512	114	102
65°	89	1077	89	1077	89	88
75°	63	275	63	275	63	64
85°	22	36	22	36	22	23
90°	5	37	5	73	5	5
95°	53	39	53	229	53	63
105°	248	397	248	546	248	263
115°	475	658	475	811	475	468
125°	702	1043	702	994	702	628
135°	955	1365	955	1101	955	738
145°	1219	1574	1219	1124	1219	763
155°	1448	1709	1448	1167	1448	666
165°	1601	1782	1601	1343	1601	451
175°	1674	1745	1674	1575	1674	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
2.5°	498.5	507.9	517.4	527.4	537.8	548.9	560.9	571.2	576.4	581.5	576.4
5°	487.8	520.0	552.2	598.9	650.5	709.0	774.4	830.5	858.4	886.3	858.4
7.5°	469.0	534.5	600.0	738.7	901.8	1071.2	1246.8	1392.5	1448.3	1504.1	1448.3
10°	451.6	542.9	634.1	869.4	1152.8	1370.7	1523.1	1644.9	1675.0	1705.0	1675.0
12.5°	432.3	556.2	680.0	970.5	1316.6	1543.1	1650.0	1737.9	1768.8	1799.7	1768.8
15°	400.9	578.0	755.1	1083.6	1462.4	1695.4	1782.3	1856.1	1890.5	1924.8	1890.5
17.5°	368.5	604.2	840.0	1175.0	1543.2	1770.3	1856.4	1925.6	1944.3	1963.0	1944.3
20°	345.4	622.3	899.2	1234.9	1590.2	1804.9	1878.9	1937.4	1949.2	1961.0	1949.2
22.5°	324.1	633.7	943.2	1279.3	1624.3	1824.8	1880.8	1926.0	1938.7	1951.4	1938.7
25°	294.6	643.5	992.3	1327.5	1658.1	1841.1	1876.5	1905.2	1913.8	1922.4	1913.8
27.5°	266.1	634.7	1003.3	1334.2	1652.6	1823.4	1846.6	1866.0	1874.4	1882.8	1874.4
30°	248.8	623.4	998.0	1325.9	1638.2	1803.0	1820.1	1836.0	1847.8	1859.6	1847.8
32.5°	233.3	609.6	985.9	1309.8	1616.1	1777.4	1793.7	1812.4	1837.9	1863.5	1837.9
35°	210.1	580.4	950.7	1271.1	1574.9	1739.6	1765.4	1796.5	1843.8	1891.0	1843.8
37.5°	190.3	543.0	895.7	1212.8	1518.1	1697.7	1751.6	1803.3	1848.9	1894.4	1848.9
40°	178.7	516.8	854.9	1169.7	1476.7	1666.1	1738.0	1801.6	1840.3	1878.9	1840.3
42.5°	167.1	487.2	807.3	1119.5	1429.0	1625.8	1709.7	1782.3	1821.0	1859.6	1821.0
45°	152.1	439.8	727.5	1036.9	1353.5	1561.2	1659.9	1743.1	1779.6	1816.1	1779.6
47.5°	138.1	388.0	637.9	948.6	1279.7	1497.5	1602.3	1687.5	1714.2	1740.8	1714.2
50°	130.4	353.7	576.9	888.7	1230.1	1452.3	1555.3	1637.9	1659.4	1680.9	1659.4
52.5°	122.7	320.2	517.7	830.1	1180.9	1404.8	1501.8	1579.6	1599.3	1619.1	1599.3
55°	113.5	274.5	435.5	744.6	1103.1	1324.8	1409.6	1477.5	1494.7	1511.8	1494.7
57.5°	105.3	235.2	365.0	664.5	1020.4	1234.5	1306.9	1364.6	1378.6	1392.5	1378.6
60°	101.4	214.1	326.8	614.2	959.9	1165.4	1230.9	1283.5	1297.4	1311.4	1297.4
62.5°	95.6	193.7	291.8	564.0	894.2	1089.4	1149.7	1198.2	1211.3	1224.4	1211.3
65°	89.4	168.8	248.2	493.5	794.0	969.5	1020.0	1059.9	1068.5	1077.1	1068.5
67.5°	80.7	148.1	215.5	428.9	691.0	837.8	869.1	888.6	872.5	856.4	872.5
70°	74.9	137.1	199.4	389.6	622.5	744.4	755.1	751.6	705.5	659.3	705.5
72.5°	71.0	126.4	181.8	346.5	547.6	636.4	612.8	573.2	485.9	398.5	485.9
75°	62.8	107.9	153.0	276.9	427.2	450.8	347.8	271.0	273.2	275.3	273.2
77.5°	51.2	84.9	118.6	194.8	285.2	303.1	248.6	208.2	210.1	212.0	210.1
80°	43.5	70.3	97.1	127.2	158.3	172.8	170.7	169.3	170.4	171.5	170.4
82.5°	35.7	55.7	75.7	93.7	111.1	120.9	123.0	124.2	122.7	121.2	122.7
85°	21.7	33.5	45.3	52.3	57.7	56.1	47.5	40.5	38.4	36.2	38.4
87.5°	8.7	14.4	20.4	20.2	17.8	16.4	16.4	16.8	17.1	17.1	17.1
90°	5.1	11.9	20.3	27.1	32.2	33.9	33.9	35.6	37.3	37.3	37.3
92.5°	18.7	29.5	29.8	29.8	36.3	39.3	42.1	42.4	44.1	44.1	44.1
95°	52.6	57.7	86.5	84.8	57.7	45.8	39.0	39.0	39.0	39.0	39.0
97.5°	100.4	107.9	112.6	150.9	159.4	154.0	125.5	105.5	94.3	89.2	94.3
100°	142.4	145.8	156.0	157.7	200.1	240.8	220.5	195.0	186.5	181.5	186.5
102.5°	184.5	186.5	202.1	209.3	219.1	242.2	312.7	304.9	299.1	298.1	299.1
105°	247.6	249.3	278.1	291.7	298.5	298.5	296.8	330.7	385.0	396.8	385.0
107.5°	315.1	322.9	356.8	393.1	400.9	402.9	394.1	389.0	387.0	388.3	387.0
110°	361.2	373.1	413.8	459.6	471.4	474.8	471.4	466.3	463.0	463.0	463.0



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	406.0	423.3	469.4	522.0	542.0	552.2	544.7	541.0	537.6	540.3	537.6
115°	474.8	500.3	561.3	615.6	656.3	661.4	659.7	659.7	658.0	658.0	658.0
117.5°	538.6	579.3	647.8	710.9	758.0	771.6	778.4	776.3	774.3	777.7	774.3
120°	583.4	630.8	708.9	780.1	825.9	846.2	853.0	849.6	853.0	849.6	853.0
122.5°	630.8	689.2	765.8	839.8	893.7	916.8	924.9	925.6	926.3	924.2	926.3
125°	702.1	773.3	863.2	939.5	995.4	1022.6	1029.4	1031.1	1034.4	1042.9	1034.4
127.5°	774.0	854.7	953.4	1027.0	1084.3	1117.2	1127.7	1131.4	1138.6	1142.3	1138.6
130°	824.2	915.7	1015.8	1085.3	1141.3	1176.9	1195.6	1200.6	1209.1	1207.4	1209.1
132.5°	877.1	972.7	1074.1	1146.4	1198.3	1236.6	1252.5	1267.1	1270.2	1272.5	1270.2
135°	954.7	1058.2	1159.9	1231.2	1280.3	1317.7	1338.0	1351.6	1360.0	1365.1	1360.0
137.5°	1036.5	1145.7	1243.4	1306.8	1356.3	1388.5	1411.6	1425.8	1434.7	1438.7	1434.7
140°	1092.1	1197.2	1292.2	1358.3	1402.4	1434.7	1455.0	1472.0	1482.1	1482.1	1482.1
142.5°	1145.0	1248.8	1341.1	1407.2	1445.9	1475.4	1497.1	1510.0	1521.5	1521.5	1521.5
145°	1219.3	1322.7	1407.5	1473.7	1505.9	1533.0	1556.8	1566.9	1573.7	1573.7	1573.7
147.5°	1297.0	1388.5	1465.9	1529.3	1556.4	1588.3	1607.0	1615.1	1623.6	1619.8	1623.6
150°	1343.1	1427.9	1502.5	1561.8	1589.0	1619.5	1638.2	1644.9	1653.4	1648.3	1653.4
152.5°	1387.9	1468.6	1536.4	1591.7	1614.8	1645.3	1666.6	1673.4	1679.2	1675.5	1679.2
155°	1448.2	1519.5	1582.2	1633.1	1653.4	1682.3	1702.6	1711.1	1717.9	1709.4	1717.9
157.5°	1502.2	1563.5	1618.1	1665.0	1686.7	1711.4	1730.4	1740.9	1747.7	1744.0	1747.7
160°	1534.7	1590.7	1639.9	1683.9	1704.3	1726.3	1746.7	1758.6	1765.3	1760.3	1765.3
162.5°	1561.8	1612.4	1658.8	1698.9	1716.5	1735.8	1760.3	1770.8	1777.6	1771.1	1777.6
165°	1600.9	1641.6	1682.3	1716.2	1731.4	1746.7	1772.1	1784.0	1789.1	1782.3	1789.1
167.5°	1630.4	1661.6	1694.5	1723.6	1734.8	1749.7	1775.2	1785.0	1791.5	1783.0	1791.5
170°	1646.6	1673.8	1702.6	1726.3	1734.8	1748.4	1773.8	1782.3	1787.4	1778.9	1787.4
172.5°	1660.2	1680.6	1704.0	1725.0	1729.4	1740.2	1764.3	1772.8	1776.5	1769.4	1776.5
175°	1673.8	1685.6	1702.6	1716.2	1714.5	1721.3	1741.6	1748.4	1755.2	1745.0	1755.2
177.5°	1680.2	1685.6	1691.1	1699.2	1693.8	1693.8	1708.7	1712.8	1714.1	1708.7	1714.1
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
2.5°	571.2	560.9	548.9	537.8	527.4	517.4	507.9	498.5	507.9	517.4	527.4
5°	830.5	774.4	709.0	650.5	598.9	552.2	520.0	487.8	520.0	552.2	598.9
7.5°	1392.5	1246.8	1071.2	901.8	738.7	600.0	534.5	469.0	534.5	600.0	738.7
10°	1644.9	1523.1	1370.7	1152.8	869.4	634.1	542.9	451.6	542.9	634.1	869.4
12.5°	1737.9	1650.0	1543.1	1316.6	970.5	680.0	556.2	432.3	556.2	680.0	970.5
15°	1856.1	1782.3	1695.4	1462.4	1083.6	755.1	578.0	400.9	578.0	755.1	1083.6
17.5°	1925.6	1856.4	1770.3	1543.2	1175.0	840.0	604.2	368.5	604.2	840.0	1175.0
20°	1937.4	1878.9	1804.9	1590.2	1234.9	899.2	622.3	345.4	622.3	899.2	1234.9
22.5°	1926.0	1880.8	1824.8	1624.3	1279.3	943.2	633.7	324.1	633.7	943.2	1279.3
25°	1905.2	1876.5	1841.1	1658.1	1327.5	992.3	643.5	294.6	643.5	992.3	1327.5
27.5°	1866.0	1846.6	1823.4	1652.6	1334.2	1003.3	634.7	266.1	634.7	1003.3	1334.2
30°	1836.0	1820.1	1803.0	1638.2	1325.9	998.0	623.4	248.8	623.4	998.0	1325.9
32.5°	1812.4	1793.7	1777.4	1616.1	1309.8	985.9	609.6	233.3	609.6	985.9	1309.8
35°	1796.5	1765.4	1739.6	1574.9	1271.1	950.7	580.4	210.1	580.4	950.7	1271.1
37.5°	1803.3	1751.6	1697.7	1518.1	1212.8	895.7	543.0	190.3	543.0	895.7	1212.8
40°	1801.6	1738.0	1666.1	1476.7	1169.7	854.9	516.8	178.7	516.8	854.9	1169.7
42.5°	1782.3	1709.7	1625.8	1429.0	1119.5	807.3	487.2	167.1	487.2	807.3	1119.5
45°	1743.1	1659.9	1561.2	1353.5	1036.9	727.5	439.8	152.1	439.8	727.5	1036.9
47.5°	1687.5	1602.3	1497.5	1279.7	948.6	637.9	388.0	138.1	388.0	637.9	948.6
50°	1637.9	1555.3	1452.3	1230.1	888.7	576.9	353.7	130.4	353.7	576.9	888.7
52.5°	1579.6	1501.8	1404.8	1180.9	830.1	517.7	320.2	122.7	320.2	517.7	830.1
55°	1477.5	1409.6	1324.8	1103.1	744.6	435.5	274.5	113.5	274.5	435.5	744.6
57.5°	1364.6	1306.9	1234.5	1020.4	664.5	365.0	235.2	105.3	235.2	365.0	664.5
60°	1283.5	1230.9	1165.4	959.9	614.2	326.8	214.1	101.4	214.1	326.8	614.2
62.5°	1198.2	1149.7	1089.4	894.2	564.0	291.8	193.7	95.6	193.7	291.8	564.0
65°	1059.9	1020.0	969.5	794.0	493.5	248.2	168.8	89.4	168.8	248.2	493.5
67.5°	888.6	869.1	837.8	691.0	428.9	215.5	148.1	80.7	148.1	215.5	428.9
70°	751.6	755.1	744.4	622.5	389.6	199.4	137.1	74.9	137.1	199.4	389.6
72.5°	573.2	612.8	636.4	547.6	346.5	181.8	126.4	71.0	126.4	181.8	346.5
75°	271.0	347.8	450.8	427.2	276.9	153.0	107.9	62.8	107.9	153.0	276.9
77.5°	208.2	248.6	303.1	285.2	194.8	118.6	84.9	51.2	84.9	118.6	194.8
80°	169.3	170.7	172.8	158.3	127.2	97.1	70.3	43.5	70.3	97.1	127.2
82.5°	124.2	123.0	120.9	111.1	93.7	75.7	55.7	35.7	55.7	75.7	93.7
85°	40.5	47.5	56.1	57.7	52.3	45.3	33.5	21.7	33.5	45.3	52.3
87.5°	16.8	16.4	16.4	17.8	20.2	20.4	14.4	8.7	14.4	20.0	20.9
90°	35.6	33.9	33.9	32.2	27.1	20.3	11.9	5.1	11.9	18.7	30.5
92.5°	42.4	42.1	39.3	36.3	29.8	29.8	29.5	18.7	32.2	45.8	65.8
95°	39.0	39.0	45.8	57.7	84.8	86.5	57.7	52.6	74.6	105.1	132.3
97.5°	105.5	125.5	154.0	159.4	150.9	112.6	107.9	100.4	136.7	166.9	210.6
100°	195.0	220.5	240.8	200.1	157.7	156.0	145.8	142.4	181.5	210.3	252.7
102.5°	304.9	312.7	242.2	219.1	209.3	202.1	186.5	184.5	223.5	263.2	298.8
105°	330.7	296.8	298.5	298.5	291.7	278.1	249.3	247.6	291.7	337.5	381.6
107.5°	389.0	394.1	402.9	400.9	393.1	356.8	322.9	315.1	354.8	409.7	458.2
110°	466.3	471.4	474.8	471.4	459.6	413.8	373.1	361.2	396.8	454.5	507.0



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	541.0	544.7	552.2	542.0	522.0	469.4	423.3	406.0	441.6	500.6	554.5
115°	659.7	659.7	661.4	656.3	615.6	561.3	500.3	474.8	505.4	559.6	619.0
117.5°	776.3	778.4	771.6	758.0	710.9	647.8	579.3	538.6	562.7	620.0	681.0
120°	849.6	853.0	846.2	825.9	780.1	708.9	630.8	583.4	602.0	658.0	719.0
122.5°	925.6	924.9	916.8	893.7	839.8	765.8	689.2	630.8	638.6	690.5	750.2
125°	1031.1	1029.4	1022.6	995.4	939.5	863.2	773.3	702.1	691.9	736.0	797.0
127.5°	1131.4	1127.7	1117.2	1084.3	1027.0	953.4	854.7	774.0	751.2	779.1	835.0
130°	1200.6	1195.6	1176.9	1141.3	1085.3	1015.8	915.7	824.2	791.9	808.9	858.1
132.5°	1267.1	1252.5	1236.6	1198.3	1146.4	1074.1	972.7	877.1	832.6	840.1	878.4
135°	1351.6	1338.0	1317.7	1280.3	1231.2	1159.9	1058.2	954.7	893.7	886.9	909.0
137.5°	1425.8	1411.6	1388.5	1356.3	1306.8	1243.4	1145.7	1036.5	959.5	936.8	945.2
140°	1472.0	1455.0	1434.7	1402.4	1358.3	1292.2	1197.2	1092.1	1005.6	973.4	968.3
142.5°	1510.0	1497.1	1475.4	1445.9	1407.2	1341.1	1248.8	1145.0	1053.1	1011.4	999.5
145°	1566.9	1556.8	1533.0	1505.9	1473.7	1407.5	1322.7	1219.3	1127.7	1073.5	1048.0
147.5°	1615.1	1607.0	1588.3	1556.4	1529.3	1465.9	1388.5	1297.0	1203.0	1135.9	1103.0
150°	1644.9	1638.2	1619.5	1589.0	1561.8	1502.5	1427.9	1343.1	1253.2	1182.0	1139.6
152.5°	1673.4	1666.6	1645.3	1614.8	1591.7	1536.4	1468.6	1387.9	1296.6	1225.4	1181.6
155°	1711.1	1702.6	1682.3	1653.4	1633.1	1582.2	1519.5	1448.2	1370.2	1295.6	1246.4
157.5°	1740.9	1730.4	1711.4	1686.7	1665.0	1618.1	1563.5	1502.2	1434.0	1362.8	1312.6
160°	1758.6	1746.7	1726.3	1704.3	1683.9	1639.9	1590.7	1534.7	1472.0	1407.5	1353.3
162.5°	1770.8	1760.3	1735.8	1716.5	1698.9	1658.8	1612.4	1561.8	1505.9	1449.6	1399.4
165°	1784.0	1772.1	1746.7	1731.4	1716.2	1682.3	1641.6	1600.9	1553.4	1507.6	1466.9
167.5°	1785.0	1775.2	1749.7	1734.8	1723.6	1694.5	1661.6	1630.4	1593.4	1557.4	1523.5
170°	1782.3	1773.8	1748.4	1734.8	1726.3	1702.6	1673.8	1646.6	1617.8	1587.3	1560.2
172.5°	1772.8	1764.3	1740.2	1729.4	1725.0	1704.0	1680.6	1660.2	1635.4	1613.1	1591.4
175°	1748.4	1741.6	1721.3	1714.5	1716.2	1702.6	1685.6	1673.8	1658.5	1644.9	1633.1
177.5°	1712.8	1708.7	1693.8	1693.8	1699.2	1691.1	1685.6	1680.2	1673.4	1669.4	1665.3
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
2.5°	537.8	548.9	560.9	571.2	576.4	581.5	576.4	571.2	560.9	548.9	537.8
5°	650.5	709.0	774.4	830.5	858.4	886.3	858.4	830.5	774.4	709.0	650.5
7.5°	901.8	1071.2	1246.8	1392.5	1448.3	1504.1	1448.3	1392.5	1246.8	1071.2	901.8
10°	1152.8	1370.7	1523.1	1644.9	1675.0	1705.0	1675.0	1644.9	1523.1	1370.7	1152.8
12.5°	1316.6	1543.1	1650.0	1737.9	1768.8	1799.7	1768.8	1737.9	1650.0	1543.1	1316.6
15°	1462.4	1695.4	1782.3	1856.1	1890.5	1924.8	1890.5	1856.1	1782.3	1695.4	1462.4
17.5°	1543.2	1770.3	1856.4	1925.6	1944.3	1963.0	1944.3	1925.6	1856.4	1770.3	1543.2
20°	1590.2	1804.9	1878.9	1937.4	1949.2	1961.0	1949.2	1937.4	1878.9	1804.9	1590.2
22.5°	1624.3	1824.8	1880.8	1926.0	1938.7	1951.4	1938.7	1926.0	1880.8	1824.8	1624.3
25°	1658.1	1841.1	1876.5	1905.2	1913.8	1922.4	1913.8	1905.2	1876.5	1841.1	1658.1
27.5°	1652.6	1823.4	1846.6	1866.0	1874.4	1882.8	1874.4	1866.0	1846.6	1823.4	1652.6
30°	1638.2	1803.0	1820.1	1836.0	1847.8	1859.6	1847.8	1836.0	1820.1	1803.0	1638.2
32.5°	1616.1	1777.4	1793.7	1812.4	1837.9	1863.5	1837.9	1812.4	1793.7	1777.4	1616.1
35°	1574.9	1739.6	1765.4	1796.5	1843.8	1891.0	1843.8	1796.5	1765.4	1739.6	1574.9
37.5°	1518.1	1697.7	1751.6	1803.3	1848.9	1894.4	1848.9	1803.3	1751.6	1697.7	1518.1
40°	1476.7	1666.1	1738.0	1801.6	1840.3	1878.9	1840.3	1801.6	1738.0	1666.1	1476.7
42.5°	1429.0	1625.8	1709.7	1782.3	1821.0	1859.6	1821.0	1782.3	1709.7	1625.8	1429.0
45°	1353.5	1561.2	1659.9	1743.1	1779.6	1816.1	1779.6	1743.1	1659.9	1561.2	1353.5
47.5°	1279.7	1497.5	1602.3	1687.5	1714.2	1740.8	1714.2	1687.5	1602.3	1497.5	1279.7
50°	1230.1	1452.3	1555.3	1637.9	1659.4	1680.9	1659.4	1637.9	1555.3	1452.3	1230.1
52.5°	1180.9	1404.8	1501.8	1579.6	1599.3	1619.1	1599.3	1579.6	1501.8	1404.8	1180.9
55°	1103.1	1324.8	1409.6	1477.5	1494.7	1511.8	1494.7	1477.5	1409.6	1324.8	1103.1
57.5°	1020.4	1234.5	1306.9	1364.6	1378.6	1392.5	1378.6	1364.6	1306.9	1234.5	1020.4
60°	959.9	1165.4	1230.9	1283.5	1297.4	1311.4	1297.4	1283.5	1230.9	1165.4	959.9
62.5°	894.2	1089.4	1149.7	1198.2	1211.3	1224.4	1211.3	1198.2	1149.7	1089.4	894.2
65°	794.0	969.5	1020.0	1059.9	1068.5	1077.1	1068.5	1059.9	1020.0	969.5	794.0
67.5°	691.0	837.8	869.1	888.6	872.5	856.4	872.5	888.6	869.1	837.8	691.0
70°	622.5	744.4	755.1	751.6	705.5	659.3	705.5	751.6	755.1	744.4	622.5
72.5°	547.6	636.4	612.8	573.2	485.9	398.5	485.9	573.2	612.8	636.4	547.6
75°	427.2	450.8	347.8	271.0	273.2	275.3	273.2	271.0	347.8	450.8	427.2
77.5°	285.2	303.1	248.6	208.2	210.1	212.0	210.1	208.2	248.6	303.1	285.2
80°	158.3	172.8	170.7	169.3	170.4	171.5	170.4	169.3	170.7	172.8	158.3
82.5°	111.1	120.9	123.0	124.2	122.7	121.2	122.7	124.2	123.0	120.9	111.1
85°	57.7	56.1	47.5	40.5	38.4	36.2	38.4	40.5	47.5	56.1	57.7
87.5°	19.2	19.8	22.2	23.6	24.9	24.2	24.9	23.6	22.2	19.8	19.2
90°	39.0	50.9	62.7	69.5	76.3	72.9	76.3	69.5	62.7	50.9	39.0
92.5°	78.3	98.4	112.9	125.2	130.6	129.9	130.6	125.2	112.9	98.4	78.3
95°	157.7	181.5	205.2	222.2	232.3	228.9	232.3	222.2	205.2	181.5	157.7
97.5°	243.2	275.1	301.5	317.5	327.6	334.4	327.6	317.5	301.5	275.1	243.2
100°	300.2	330.7	361.2	379.9	396.8	403.6	396.8	379.9	361.2	330.7	300.2
102.5°	346.3	386.3	419.5	439.6	453.8	460.6	453.8	439.6	419.5	386.3	346.3
105°	422.3	464.7	500.3	525.7	541.0	546.1	541.0	525.7	500.3	464.7	422.3
107.5°	498.2	542.0	574.9	603.0	621.7	632.5	621.7	603.0	574.9	542.0	498.2
110°	557.9	593.5	629.1	654.6	673.2	680.0	673.2	654.6	629.1	593.5	557.9



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	608.1	647.8	683.4	708.9	730.2	739.7	730.2	708.9	683.4	647.8	608.1
115°	678.3	730.9	763.1	786.9	802.1	810.6	802.1	786.9	763.1	730.9	678.3
117.5°	736.7	791.6	826.9	845.2	852.3	858.4	852.3	845.2	826.9	791.6	736.7
120°	773.3	824.2	864.9	888.6	897.1	900.5	897.1	888.6	864.9	824.2	773.3
122.5°	807.2	855.4	894.7	923.9	937.8	941.2	937.8	923.9	894.7	855.4	807.2
125°	854.7	900.5	941.2	970.0	985.3	993.7	985.3	970.0	941.2	900.5	854.7
127.5°	896.1	945.6	982.9	1009.0	1023.9	1030.7	1023.9	1009.0	982.9	945.6	896.1
130°	919.1	970.0	1007.3	1036.1	1049.7	1056.5	1049.7	1036.1	1007.3	970.0	919.1
132.5°	936.8	990.4	1029.0	1055.1	1070.1	1076.8	1070.1	1055.1	1029.0	990.4	936.8
135°	958.1	1014.1	1054.8	1080.2	1093.8	1100.6	1093.8	1080.2	1054.8	1014.1	958.1
137.5°	976.8	1027.7	1070.1	1096.9	1109.1	1113.5	1109.1	1096.9	1070.1	1027.7	976.8
140°	990.4	1034.4	1076.8	1102.3	1115.8	1117.5	1115.8	1102.3	1076.8	1034.4	990.4
142.5°	1008.0	1042.6	1079.6	1105.0	1118.6	1121.6	1118.6	1105.0	1079.6	1042.6	1008.0
145°	1039.5	1059.9	1085.3	1109.1	1120.9	1124.3	1120.9	1109.1	1085.3	1059.9	1039.5
147.5°	1079.2	1085.7	1098.9	1114.5	1126.0	1128.4	1126.0	1114.5	1098.9	1085.7	1079.2
150°	1109.1	1107.4	1112.5	1122.6	1132.8	1131.1	1132.8	1122.6	1112.5	1107.4	1109.1
152.5°	1143.0	1133.1	1132.8	1137.6	1142.3	1142.0	1142.3	1137.6	1132.8	1133.1	1143.0
155°	1200.6	1182.0	1171.8	1168.4	1168.4	1166.7	1168.4	1168.4	1171.8	1182.0	1200.6
157.5°	1264.1	1237.9	1222.7	1214.5	1212.2	1208.4	1212.2	1214.5	1222.7	1237.9	1264.1
160°	1307.5	1278.6	1263.4	1249.8	1244.7	1239.6	1244.7	1249.8	1263.4	1278.6	1307.5
162.5°	1348.2	1320.7	1304.1	1291.9	1286.8	1279.0	1286.8	1291.9	1304.1	1320.7	1348.2
165°	1414.3	1385.5	1366.8	1356.7	1349.9	1343.1	1349.9	1356.7	1366.8	1385.5	1414.3
167.5°	1480.4	1448.9	1436.7	1425.2	1418.7	1406.5	1418.7	1425.2	1436.7	1448.9	1480.4
170°	1521.1	1492.3	1485.5	1475.4	1463.5	1449.9	1463.5	1475.4	1485.5	1492.3	1521.1
172.5°	1556.4	1537.1	1530.3	1520.1	1516.4	1505.5	1516.4	1520.1	1530.3	1537.1	1556.4
175°	1607.6	1592.4	1592.4	1590.7	1585.6	1575.4	1585.6	1590.7	1592.4	1592.4	1607.6
177.5°	1650.4	1642.2	1647.7	1647.7	1646.3	1636.8	1646.3	1647.7	1647.7	1642.2	1650.4
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	502.3	502.3	502.3	502.3
2.5°	527.4	517.4	507.9	498.5
5°	598.9	552.2	520.0	487.8
7.5°	738.7	600.0	534.5	469.0
10°	869.4	634.1	542.9	451.6
12.5°	970.5	680.0	556.2	432.3
15°	1083.6	755.1	578.0	400.9
17.5°	1175.0	840.0	604.2	368.5
20°	1234.9	899.2	622.3	345.4
22.5°	1279.3	943.2	633.7	324.1
25°	1327.5	992.3	643.5	294.6
27.5°	1334.2	1003.3	634.7	266.1
30°	1325.9	998.0	623.4	248.8
32.5°	1309.8	985.9	609.6	233.3
35°	1271.1	950.7	580.4	210.1
37.5°	1212.8	895.7	543.0	190.3
40°	1169.7	854.9	516.8	178.7
42.5°	1119.5	807.3	487.2	167.1
45°	1036.9	727.5	439.8	152.1
47.5°	948.6	637.9	388.0	138.1
50°	888.7	576.9	353.7	130.4
52.5°	830.1	517.7	320.2	122.7
55°	744.6	435.5	274.5	113.5
57.5°	664.5	365.0	235.2	105.3
60°	614.2	326.8	214.1	101.4
62.5°	564.0	291.8	193.7	95.6
65°	493.5	248.2	168.8	89.4
67.5°	428.9	215.5	148.1	80.7
70°	389.6	199.4	137.1	74.9
72.5°	346.5	181.8	126.4	71.0
75°	276.9	153.0	107.9	62.8
77.5°	194.8	118.6	84.9	51.2
80°	127.2	97.1	70.3	43.5
82.5°	93.7	75.7	55.7	35.7
85°	52.3	45.3	33.5	21.7
87.5°	20.9	20.0	14.4	8.7
90°	30.5	18.7	11.9	5.1
92.5°	65.8	45.8	32.2	18.7
95°	132.3	105.1	74.6	52.6
97.5°	210.6	166.9	136.7	100.4
100°	252.7	210.3	181.5	142.4
102.5°	298.8	263.2	223.5	184.5
105°	381.6	337.5	291.7	247.6
107.5°	458.2	409.7	354.8	315.1
110°	507.0	454.5	396.8	361.2



TEST NUMBER: P1436025

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	554.5	500.6	441.6	406.0
115°	619.0	559.6	505.4	474.8
117.5°	681.0	620.0	562.7	538.6
120°	719.0	658.0	602.0	583.4
122.5°	750.2	690.5	638.6	630.8
125°	797.0	736.0	691.9	702.1
127.5°	835.0	779.1	751.2	774.0
130°	858.1	808.9	791.9	824.2
132.5°	878.4	840.1	832.6	877.1
135°	909.0	886.9	893.7	954.7
137.5°	945.2	936.8	959.5	1036.5
140°	968.3	973.4	1005.6	1092.1
142.5°	999.5	1011.4	1053.1	1145.0
145°	1048.0	1073.5	1127.7	1219.3
147.5°	1103.0	1135.9	1203.0	1297.0
150°	1139.6	1182.0	1253.2	1343.1
152.5°	1181.6	1225.4	1296.6	1387.9
155°	1246.4	1295.6	1370.2	1448.2
157.5°	1312.6	1362.8	1434.0	1502.2
160°	1353.3	1407.5	1472.0	1534.7
162.5°	1399.4	1449.6	1505.9	1561.8
165°	1466.9	1507.6	1553.4	1600.9
167.5°	1523.5	1557.4	1593.4	1630.4
170°	1560.2	1587.3	1617.8	1646.6
172.5°	1591.4	1613.1	1635.4	1660.2
175°	1633.1	1644.9	1658.5	1673.8
177.5°	1665.3	1669.4	1673.4	1680.2
180°	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1436025  
 CATALOG NUMBER: SQ2W-FB-K-125U-125D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.48	14.37	14.42	15.34	16.60	23.07	23.96	24.02	24.93	26.20
	3H	14.42	15.22	15.38	16.20	17.48	24.68	25.48	25.64	26.46	27.75
	4H	14.82	15.57	15.79	16.56	17.85	24.86	25.62	25.83	26.60	27.89
	6H	15.07	15.77	16.06	16.76	18.07	24.94	25.63	25.92	26.62	27.93
	8H	15.17	15.83	16.16	16.84	18.14	24.96	25.62	25.95	26.62	27.93
	12H	15.22	15.85	16.21	16.85	18.18	24.94	25.57	25.93	26.56	27.90
4H	2H	18.20	18.96	19.18	19.94	21.23	23.44	24.20	24.42	25.18	26.48
	3H	19.33	19.96	20.32	20.97	22.28	25.33	25.96	26.32	26.98	28.29
	4H	19.62	20.19	20.61	21.20	22.53	25.56	26.13	26.56	27.14	28.47
	6H	19.75	20.25	20.76	21.28	22.61	25.69	26.19	26.70	27.21	28.54
	8H	19.79	20.26	20.80	21.28	22.62	25.74	26.20	26.75	27.22	28.57
	12H	19.80	20.21	20.83	21.25	22.60	25.72	26.14	26.75	27.17	28.53
8H	4H	20.81	21.27	21.82	22.29	23.64	25.65	26.11	26.66	27.13	28.48
	6H	21.07	21.45	22.11	22.52	23.86	25.85	26.23	26.89	27.29	28.64
	8H	21.17	21.50	22.21	22.55	23.92	25.94	26.28	26.99	27.32	28.69
	12H	21.21	21.51	22.26	22.55	23.96	25.95	26.24	27.00	27.29	28.69
12H	4H	20.84	21.25	21.87	22.29	23.64	25.60	26.02	26.64	27.06	28.41
	6H	21.18	21.51	22.22	22.56	23.93	25.83	26.17	26.88	27.22	28.58
	8H	21.32	21.61	22.37	22.66	24.06	25.93	26.23	26.98	27.27	28.68