

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1436028

Luminaire Tested: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1436028
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8914.1 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26				
1	92	88	84	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22				
2	84	77	71	66	75	69	64	59	53	50	47	39	37	35	26	25	24	18				
3	76	67	60	54	68	60	54	49	47	42	39	34	32	29	23	21	20	15				
4	70	59	51	45	62	53	46	41	41	37	33	30	27	25	20	18	17	13				
5	64	52	44	39	56	47	40	35	37	32	28	27	24	21	18	16	14	11				
6	58	47	39	33	52	42	35	30	33	28	24	24	21	18	16	14	13	9				
7	54	42	34	29	48	37	31	26	29	24	21	22	18	16	15	13	11	8				
8	50	38	30	25	44	34	27	23	27	22	18	20	16	14	13	11	10	7				
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	12	10	9	6				
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3801	3801	3801	3801
5°	3705	6731	3705	6731
10°	3469	13099	3469	13099
15°	3141	15075	3141	15075
20°	2780	15788	2780	15788
25°	2460	16047	2460	16047
30°	2174	16246	2174	16246
35°	1941	17465	1941	17465
40°	1764	18556	1764	18556
45°	1628	19431	1628	19431
50°	1535	19783	1535	19783
55°	1498	19941	1498	19941
60°	1534	19843	1534	19843
65°	1601	19281	1601	19281
70°	1657	14582	1657	14582
75°	1834	8047	1834	8047
80°	1897	7466	1897	7466
85°	1890	3149	1890	3149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 20122 cd/sqm



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	0.4
10°-20°	179.9	2.0
20°-30°	316.6	3.6
30°-40°	409.9	4.6
40°-50°	452.0	5.1
50°-60°	421.9	4.7
60°-70°	326.0	3.7
70°-80°	150.3	1.7
80°-90°	38.0	0.4
90°-100°	179.4	2.0
100°-110°	523.0	5.9
110°-120°	853.6	9.6
120°-130°	1083.1	12.2
130°-140°	1158.9	13.0
140°-150°	1082.2	12.1
150°-160°	890.5	10.0
160°-170°	597.2	6.7
170°-180°	212.1	2.4
0°-30°	536.0	6.0
0°-40°	945.9	10.6
0°-60°	1819.9	20.4
0°-90°	2334.1	26.2
90°-120°	1556.0	17.5
90°-150°	4880.2	54.7
90°-180°	6580.0	73.8
0°-180°	8914.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	235	235	235	235	235	
5°	229	415	229	415	229	21
15°	188	902	188	902	188	52
25°	138	901	138	901	138	63
35°	98	886	98	886	98	62
45°	71	851	71	851	71	55
55°	53	708	53	708	53	48
65°	42	505	42	505	42	41
75°	29	129	29	129	29	30
85°	10	17	10	17	10	11
90°	7	50	7	98	7	6
95°	71	52	71	307	71	85
105°	332	533	332	733	332	353
115°	637	883	637	1088	637	628
125°	942	1400	942	1334	942	843
135°	1282	1832	1282	1477	1282	990
145°	1637	2112	1637	1509	1637	1024
155°	1944	2294	1944	1566	1944	894
165°	2149	2392	2149	1803	2149	605
175°	2247	2342	2247	2115	2247	213
180°	2254	2254	2254	2254	2254	



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4
2.5°	233.6	238.0	242.4	247.2	252.0	257.2	262.8	267.7	270.1	272.5	270.1
5°	228.6	243.7	258.8	280.7	304.8	332.2	362.9	389.2	402.2	415.3	402.2
7.5°	219.8	250.5	281.1	346.1	422.6	502.0	584.2	652.5	678.7	704.8	678.7
10°	211.6	254.4	297.1	407.4	540.2	642.3	713.7	770.8	784.9	799.0	784.9
12.5°	202.6	260.6	318.7	454.8	616.9	723.1	773.2	814.4	828.8	843.3	828.8
15°	187.9	270.8	353.8	507.7	685.3	794.4	835.2	869.8	885.8	901.9	885.8
17.5°	172.7	283.1	393.6	550.6	723.1	829.5	869.9	902.3	911.1	919.8	911.1
20°	161.8	291.6	421.4	578.7	745.1	845.7	880.4	907.9	913.4	918.9	913.4
22.5°	151.9	296.9	442.0	599.5	761.1	855.1	881.3	902.5	908.5	914.4	908.5
25°	138.1	301.5	465.0	622.0	777.0	862.7	879.3	892.8	896.8	900.8	896.8
27.5°	124.7	297.4	470.1	625.2	774.4	854.4	865.3	874.4	878.3	882.3	878.3
30°	116.6	292.1	467.6	621.3	767.7	844.9	852.9	860.3	865.9	871.4	865.9
32.5°	109.3	285.7	462.0	613.7	757.3	832.9	840.5	849.3	861.2	873.2	861.2
35°	98.5	272.0	445.5	595.6	738.0	815.2	827.3	841.8	864.0	886.1	864.0
37.5°	89.2	254.5	419.7	568.3	711.4	795.5	820.8	845.0	866.4	887.7	866.4
40°	83.7	242.2	400.6	548.1	692.0	780.7	814.4	844.2	862.3	880.4	862.3
42.5°	78.3	228.3	378.3	524.6	669.6	761.8	801.1	835.2	853.3	871.4	853.3
45°	71.3	206.1	340.9	485.9	634.2	731.6	777.8	816.8	833.9	851.0	833.9
47.5°	64.7	181.8	298.9	444.5	599.6	701.7	750.8	790.8	803.2	815.7	803.2
50°	61.1	165.7	270.3	416.5	576.4	680.5	728.8	767.5	777.6	787.6	777.6
52.5°	57.5	150.0	242.6	389.0	553.4	658.3	703.7	740.2	749.4	758.7	749.4
55°	53.2	128.6	204.1	348.9	516.9	620.8	660.5	692.3	700.4	708.4	700.4
57.5°	49.3	110.2	171.1	311.4	478.1	578.5	612.4	639.4	646.0	652.5	646.0
60°	47.5	100.3	153.2	287.8	449.8	546.1	576.8	601.4	608.0	614.5	608.0
62.5°	44.8	90.8	136.8	264.3	419.0	510.5	538.8	561.5	567.6	573.8	567.6
65°	41.9	79.1	116.3	231.2	372.1	454.3	477.9	496.7	500.7	504.7	500.7
67.5°	37.8	69.4	101.0	201.0	323.8	392.6	407.3	416.4	408.8	401.3	408.8
70°	35.1	64.3	93.4	182.6	291.7	348.8	353.8	352.2	330.6	308.9	330.6
72.5°	33.3	59.2	85.2	162.4	256.6	298.2	287.1	268.6	227.7	186.7	227.7
75°	29.4	50.5	71.7	129.8	200.2	211.2	163.0	127.0	128.0	129.0	128.0
77.5°	24.0	39.8	55.6	91.3	133.6	142.0	116.5	97.6	98.5	99.4	98.5
80°	20.4	32.9	45.5	59.6	74.2	81.0	80.0	79.3	79.8	80.3	79.8
82.5°	16.7	26.1	35.5	43.9	52.1	56.6	57.6	58.2	57.5	56.8	57.5
85°	10.2	15.7	21.3	24.5	27.0	26.3	22.3	19.0	18.0	17.0	18.0
87.5°	5.0	8.8	13.1	14.2	14.0	13.6	13.6	14.1	14.5	14.5	14.5
90°	6.8	15.9	27.3	36.4	43.3	45.5	45.5	47.8	50.1	50.1	50.1
92.5°	25.0	39.6	40.1	40.1	48.7	52.8	56.5	56.9	59.2	59.2	59.2
95°	70.6	77.4	116.1	113.8	77.4	61.5	52.4	52.4	52.4	52.4	52.4
97.5°	134.8	144.8	151.1	202.6	214.0	206.7	168.4	141.6	126.6	119.7	126.6
100°	191.2	195.8	209.4	211.7	268.6	323.2	295.9	261.8	250.4	243.6	250.4
102.5°	247.7	250.4	271.3	280.9	294.1	325.1	419.8	409.3	401.5	400.2	401.5
105°	332.3	334.6	373.3	391.5	400.6	400.6	398.4	443.9	516.7	532.7	516.7
107.5°	422.9	433.4	478.9	527.7	538.1	540.9	529.0	522.2	519.5	521.3	519.5
110°	484.9	500.8	555.4	616.9	632.8	637.4	632.8	626.0	621.4	621.4	621.4



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	545.0	568.2	630.1	700.7	727.5	741.2	731.2	726.1	721.6	725.2	721.6
115°	637.4	671.5	753.5	826.3	880.9	887.8	885.5	885.5	883.2	883.2	883.2
117.5°	723.0	777.6	869.6	954.2	1017.5	1035.7	1044.8	1042.1	1039.4	1043.9	1039.4
120°	783.1	846.8	951.5	1047.1	1108.6	1135.9	1145.0	1140.4	1145.0	1140.4	1145.0
122.5°	846.8	925.1	1028.0	1127.2	1199.6	1230.6	1241.5	1242.4	1243.3	1240.6	1243.3
125°	942.4	1038.0	1158.6	1261.1	1336.2	1372.6	1381.7	1384.0	1388.6	1399.9	1388.6
127.5°	1038.9	1147.3	1279.7	1378.5	1455.5	1499.6	1513.8	1518.8	1528.3	1533.3	1528.3
130°	1106.3	1229.2	1363.5	1456.8	1532.0	1579.8	1604.8	1611.6	1623.0	1620.7	1623.0
132.5°	1177.3	1305.7	1441.8	1538.8	1608.4	1659.9	1681.3	1700.9	1705.0	1708.2	1705.0
135°	1281.6	1420.4	1557.0	1652.6	1718.6	1768.7	1796.0	1814.2	1825.6	1832.4	1825.6
137.5°	1391.3	1537.9	1669.0	1754.1	1820.6	1863.9	1894.8	1913.9	1925.8	1931.2	1925.8
140°	1466.0	1607.1	1734.6	1823.3	1882.5	1925.8	1953.1	1975.8	1989.5	1989.5	1989.5
142.5°	1537.0	1676.3	1800.1	1888.9	1940.8	1980.4	2009.5	2026.8	2042.3	2042.3	2042.3
145°	1636.7	1775.5	1889.3	1978.1	2021.4	2057.8	2089.7	2103.3	2112.4	2112.4	2112.4
147.5°	1740.9	1863.9	1967.7	2052.8	2089.2	2132.0	2157.0	2168.0	2179.4	2174.3	2179.4
150°	1802.8	1916.7	2016.8	2096.5	2132.9	2173.9	2198.9	2208.0	2219.4	2212.6	2219.4
152.5°	1862.9	1971.3	2062.3	2136.6	2167.5	2208.5	2237.2	2246.3	2254.0	2249.0	2254.0
155°	1944.0	2039.6	2123.8	2192.1	2219.4	2258.1	2285.4	2296.8	2305.9	2294.5	2305.9
157.5°	2016.4	2098.8	2172.1	2234.9	2264.0	2297.3	2322.8	2336.9	2346.0	2341.0	2346.0
160°	2060.1	2135.2	2201.2	2260.4	2287.7	2317.3	2344.6	2360.5	2369.7	2362.8	2369.7
162.5°	2096.5	2164.3	2226.7	2280.4	2304.1	2330.0	2362.8	2376.9	2386.0	2377.4	2386.0
165°	2148.8	2203.5	2258.1	2303.6	2324.1	2344.6	2378.8	2394.7	2401.5	2392.4	2401.5
167.5°	2188.5	2230.3	2274.5	2313.7	2328.7	2348.7	2382.9	2396.1	2404.7	2393.3	2404.7
170°	2210.3	2246.7	2285.4	2317.3	2328.7	2346.9	2381.0	2392.4	2399.2	2387.9	2399.2
172.5°	2228.5	2255.8	2287.2	2315.5	2321.4	2336.0	2368.3	2379.7	2384.7	2375.1	2384.7
175°	2246.7	2262.7	2285.4	2303.6	2301.4	2310.5	2337.8	2346.9	2356.0	2342.3	2356.0
177.5°	2255.4	2262.7	2269.9	2280.9	2273.6	2273.6	2293.6	2299.1	2300.9	2293.6	2300.9
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4
2.5°	267.7	262.8	257.2	252.0	247.2	242.4	238.0	233.6	238.0	242.4	247.2
5°	389.2	362.9	332.2	304.8	280.7	258.8	243.7	228.6	243.7	258.8	280.7
7.5°	652.5	584.2	502.0	422.6	346.1	281.1	250.5	219.8	250.5	281.1	346.1
10°	770.8	713.7	642.3	540.2	407.4	297.1	254.4	211.6	254.4	297.1	407.4
12.5°	814.4	773.2	723.1	616.9	454.8	318.7	260.6	202.6	260.6	318.7	454.8
15°	869.8	835.2	794.4	685.3	507.7	353.8	270.8	187.9	270.8	353.8	507.7
17.5°	902.3	869.9	829.5	723.1	550.6	393.6	283.1	172.7	283.1	393.6	550.6
20°	907.9	880.4	845.7	745.1	578.7	421.4	291.6	161.8	291.6	421.4	578.7
22.5°	902.5	881.3	855.1	761.1	599.5	442.0	296.9	151.9	296.9	442.0	599.5
25°	892.8	879.3	862.7	777.0	622.0	465.0	301.5	138.1	301.5	465.0	622.0
27.5°	874.4	865.3	854.4	774.4	625.2	470.1	297.4	124.7	297.4	470.1	625.2
30°	860.3	852.9	844.9	767.7	621.3	467.6	292.1	116.6	292.1	467.6	621.3
32.5°	849.3	840.5	832.9	757.3	613.7	462.0	285.7	109.3	285.7	462.0	613.7
35°	841.8	827.3	815.2	738.0	595.6	445.5	272.0	98.5	272.0	445.5	595.6
37.5°	845.0	820.8	795.5	711.4	568.3	419.7	254.5	89.2	254.5	419.7	568.3
40°	844.2	814.4	780.7	692.0	548.1	400.6	242.2	83.7	242.2	400.6	548.1
42.5°	835.2	801.1	761.8	669.6	524.6	378.3	228.3	78.3	228.3	378.3	524.6
45°	816.8	777.8	731.6	634.2	485.9	340.9	206.1	71.3	206.1	340.9	485.9
47.5°	790.8	750.8	701.7	599.6	444.5	298.9	181.8	64.7	181.8	298.9	444.5
50°	767.5	728.8	680.5	576.4	416.5	270.3	165.7	61.1	165.7	270.3	416.5
52.5°	740.2	703.7	658.3	553.4	389.0	242.6	150.0	57.5	150.0	242.6	389.0
55°	692.3	660.5	620.8	516.9	348.9	204.1	128.6	53.2	128.6	204.1	348.9
57.5°	639.4	612.4	578.5	478.1	311.4	171.1	110.2	49.3	110.2	171.1	311.4
60°	601.4	576.8	546.1	449.8	287.8	153.2	100.3	47.5	100.3	153.2	287.8
62.5°	561.5	538.8	510.5	419.0	264.3	136.8	90.8	44.8	90.8	136.8	264.3
65°	496.7	477.9	454.3	372.1	231.2	116.3	79.1	41.9	79.1	116.3	231.2
67.5°	416.4	407.3	392.6	323.8	201.0	101.0	69.4	37.8	69.4	101.0	201.0
70°	352.2	353.8	348.8	291.7	182.6	93.4	64.3	35.1	64.3	93.4	182.6
72.5°	268.6	287.1	298.2	256.6	162.4	85.2	59.2	33.3	59.2	85.2	162.4
75°	127.0	163.0	211.2	200.2	129.8	71.7	50.5	29.4	50.5	71.7	129.8
77.5°	97.6	116.5	142.0	133.6	91.3	55.6	39.8	24.0	39.8	55.6	91.3
80°	79.3	80.0	81.0	74.2	59.6	45.5	32.9	20.4	32.9	45.5	59.6
82.5°	58.2	57.6	56.6	52.1	43.9	35.5	26.1	16.7	26.1	35.5	43.9
85°	19.0	22.3	26.3	27.0	24.5	21.3	15.7	10.2	15.7	21.3	24.5
87.5°	14.1	13.6	13.6	14.0	14.2	13.1	8.8	5.0	8.8	12.7	15.1
90°	47.8	45.5	45.5	43.3	36.4	27.3	15.9	6.8	15.9	25.0	41.0
92.5°	56.9	56.5	52.8	48.7	40.1	40.1	39.6	25.0	43.3	61.5	88.3
95°	52.4	52.4	61.5	77.4	113.8	116.1	77.4	70.6	100.2	141.1	177.6
97.5°	141.6	168.4	206.7	214.0	202.6	151.1	144.8	134.8	183.5	224.0	282.7
100°	261.8	295.9	323.2	268.6	211.7	209.4	195.8	191.2	243.6	282.3	339.2
102.5°	409.3	419.8	325.1	294.1	280.9	271.3	250.4	247.7	300.0	353.3	401.1
105°	443.9	398.4	400.6	400.6	391.5	373.3	334.6	332.3	391.5	453.0	512.2
107.5°	522.2	529.0	540.9	538.1	527.7	478.9	433.4	422.9	476.2	550.0	615.1
110°	626.0	632.8	637.4	632.8	616.9	555.4	500.8	484.9	532.7	610.1	680.6



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	726.1	731.2	741.2	727.5	700.7	630.1	568.2	545.0	592.8	672.0	744.4
115°	885.5	885.5	887.8	880.9	826.3	753.5	671.5	637.4	678.3	751.2	830.9
117.5°	1042.1	1044.8	1035.7	1017.5	954.2	869.6	777.6	723.0	755.3	832.2	914.2
120°	1140.4	1145.0	1135.9	1108.6	1047.1	951.5	846.8	783.1	808.1	883.2	965.2
122.5°	1242.4	1241.5	1230.6	1199.6	1127.2	1028.0	925.1	846.8	857.3	926.9	1007.0
125°	1384.0	1381.7	1372.6	1336.2	1261.1	1158.6	1038.0	942.4	928.7	987.9	1069.9
127.5°	1518.8	1513.8	1499.6	1455.5	1378.5	1279.7	1147.3	1038.9	1008.4	1045.7	1120.9
130°	1611.6	1604.8	1579.8	1532.0	1456.8	1363.5	1229.2	1106.3	1063.0	1085.8	1151.8
132.5°	1700.9	1681.3	1659.9	1608.4	1538.8	1441.8	1305.7	1177.3	1117.7	1127.7	1179.1
135°	1814.2	1796.0	1768.7	1718.6	1652.6	1557.0	1420.4	1281.6	1199.6	1190.5	1220.1
137.5°	1913.9	1894.8	1863.9	1820.6	1754.1	1669.0	1537.9	1391.3	1287.9	1257.4	1268.8
140°	1975.8	1953.1	1925.8	1882.5	1823.3	1734.6	1607.1	1466.0	1349.9	1306.6	1299.8
142.5°	2026.8	2009.5	1980.4	1940.8	1888.9	1800.1	1676.3	1537.0	1413.6	1357.6	1341.7
145°	2103.3	2089.7	2057.8	2021.4	1978.1	1889.3	1775.5	1636.7	1513.8	1440.9	1406.8
147.5°	2168.0	2157.0	2132.0	2089.2	2052.8	1967.7	1863.9	1740.9	1614.8	1524.7	1480.5
150°	2208.0	2198.9	2173.9	2132.9	2096.5	2016.8	1916.7	1802.8	1682.2	1586.6	1529.7
152.5°	2246.3	2237.2	2208.5	2167.5	2136.6	2062.3	1971.3	1862.9	1740.5	1644.9	1586.1
155°	2296.8	2285.4	2258.1	2219.4	2192.1	2123.8	2039.6	1944.0	1839.3	1739.1	1673.1
157.5°	2336.9	2322.8	2297.3	2264.0	2234.9	2172.1	2098.8	2016.4	1924.9	1829.3	1761.9
160°	2360.5	2344.6	2317.3	2287.7	2260.4	2201.2	2135.2	2060.1	1975.8	1889.3	1816.5
162.5°	2376.9	2362.8	2330.0	2304.1	2280.4	2226.7	2164.3	2096.5	2021.4	1945.8	1878.4
165°	2394.7	2378.8	2344.6	2324.1	2303.6	2258.1	2203.5	2148.8	2085.1	2023.7	1969.0
167.5°	2396.1	2382.9	2348.7	2328.7	2313.7	2274.5	2230.3	2188.5	2138.8	2090.6	2045.0
170°	2392.4	2381.0	2346.9	2328.7	2317.3	2285.4	2246.7	2210.3	2171.6	2130.6	2094.2
172.5°	2379.7	2368.3	2336.0	2321.4	2315.5	2287.2	2255.8	2228.5	2195.3	2165.2	2136.1
175°	2346.9	2337.8	2310.5	2301.4	2303.6	2285.4	2262.7	2246.7	2226.2	2208.0	2192.1
177.5°	2299.1	2293.6	2273.6	2273.6	2280.9	2269.9	2262.7	2255.4	2246.3	2240.8	2235.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4
2.5°	252.0	257.2	262.8	267.7	270.1	272.5	270.1	267.7	262.8	257.2	252.0
5°	304.8	332.2	362.9	389.2	402.2	415.3	402.2	389.2	362.9	332.2	304.8
7.5°	422.6	502.0	584.2	652.5	678.7	704.8	678.7	652.5	584.2	502.0	422.6
10°	540.2	642.3	713.7	770.8	784.9	799.0	784.9	770.8	713.7	642.3	540.2
12.5°	616.9	723.1	773.2	814.4	828.8	843.3	828.8	814.4	773.2	723.1	616.9
15°	685.3	794.4	835.2	869.8	885.8	901.9	885.8	869.8	835.2	794.4	685.3
17.5°	723.1	829.5	869.9	902.3	911.1	919.8	911.1	902.3	869.9	829.5	723.1
20°	745.1	845.7	880.4	907.9	913.4	918.9	913.4	907.9	880.4	845.7	745.1
22.5°	761.1	855.1	881.3	902.5	908.5	914.4	908.5	902.5	881.3	855.1	761.1
25°	777.0	862.7	879.3	892.8	896.8	900.8	896.8	892.8	879.3	862.7	777.0
27.5°	774.4	854.4	865.3	874.4	878.3	882.3	878.3	874.4	865.3	854.4	774.4
30°	767.7	844.9	852.9	860.3	865.9	871.4	865.9	860.3	852.9	844.9	767.7
32.5°	757.3	832.9	840.5	849.3	861.2	873.2	861.2	849.3	840.5	832.9	757.3
35°	738.0	815.2	827.3	841.8	864.0	886.1	864.0	841.8	827.3	815.2	738.0
37.5°	711.4	795.5	820.8	845.0	866.4	887.7	866.4	845.0	820.8	795.5	711.4
40°	692.0	780.7	814.4	844.2	862.3	880.4	862.3	844.2	814.4	780.7	692.0
42.5°	669.6	761.8	801.1	835.2	853.3	871.4	853.3	835.2	801.1	761.8	669.6
45°	634.2	731.6	777.8	816.8	833.9	851.0	833.9	816.8	777.8	731.6	634.2
47.5°	599.6	701.7	750.8	790.8	803.2	815.7	803.2	790.8	750.8	701.7	599.6
50°	576.4	680.5	728.8	767.5	777.6	787.6	777.6	767.5	728.8	680.5	576.4
52.5°	553.4	658.3	703.7	740.2	749.4	758.7	749.4	740.2	703.7	658.3	553.4
55°	516.9	620.8	660.5	692.3	700.4	708.4	700.4	692.3	660.5	620.8	516.9
57.5°	478.1	578.5	612.4	639.4	646.0	652.5	646.0	639.4	612.4	578.5	478.1
60°	449.8	546.1	576.8	601.4	608.0	614.5	608.0	601.4	576.8	546.1	449.8
62.5°	419.0	510.5	538.8	561.5	567.6	573.8	567.6	561.5	538.8	510.5	419.0
65°	372.1	454.3	477.9	496.7	500.7	504.7	500.7	496.7	477.9	454.3	372.1
67.5°	323.8	392.6	407.3	416.4	408.8	401.3	408.8	416.4	407.3	392.6	323.8
70°	291.7	348.8	353.8	352.2	330.6	308.9	330.6	352.2	353.8	348.8	291.7
72.5°	256.6	298.2	287.1	268.6	227.7	186.7	227.7	268.6	287.1	298.2	256.6
75°	200.2	211.2	163.0	127.0	128.0	129.0	128.0	127.0	163.0	211.2	200.2
77.5°	133.6	142.0	116.5	97.6	98.5	99.4	98.5	97.6	116.5	142.0	133.6
80°	74.2	81.0	80.0	79.3	79.8	80.3	79.8	79.3	80.0	81.0	74.2
82.5°	52.1	56.6	57.6	58.2	57.5	56.8	57.5	58.2	57.6	56.6	52.1
85°	27.0	26.3	22.3	19.0	18.0	17.0	18.0	19.0	22.3	26.3	27.0
87.5°	15.8	18.2	21.4	23.2	25.0	24.1	25.0	23.2	21.4	18.2	15.8
90°	52.4	68.3	84.2	93.3	102.4	97.9	102.4	93.3	84.2	68.3	52.4
92.5°	105.2	132.0	151.6	168.0	175.3	174.4	175.3	168.0	151.6	132.0	105.2
95°	211.7	243.6	275.4	298.2	311.9	307.3	311.9	298.2	275.4	243.6	211.7
97.5°	326.4	369.2	404.7	426.1	439.8	448.9	439.8	426.1	404.7	369.2	326.4
100°	402.9	443.9	484.9	509.9	532.7	541.8	532.7	509.9	484.9	443.9	402.9
102.5°	464.8	518.5	563.2	590.0	609.1	618.2	609.1	590.0	563.2	518.5	464.8
105°	566.8	623.7	671.5	705.7	726.1	733.0	726.1	705.7	671.5	623.7	566.8
107.5°	668.8	727.5	771.7	809.5	834.5	849.1	834.5	809.5	771.7	727.5	668.8
110°	748.9	796.7	844.5	878.7	903.7	912.8	903.7	878.7	844.5	796.7	748.9



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	816.3	869.6	917.4	951.5	980.2	992.9	980.2	951.5	917.4	869.6	816.3
115°	910.5	981.1	1024.3	1056.2	1076.7	1088.1	1076.7	1056.2	1024.3	981.1	910.5
117.5°	988.8	1062.6	1109.9	1134.5	1144.1	1152.3	1144.1	1134.5	1109.9	1062.6	988.8
120°	1038.0	1106.3	1160.9	1192.8	1204.2	1208.7	1204.2	1192.8	1160.9	1106.3	1038.0
122.5°	1083.5	1148.2	1201.0	1240.1	1258.8	1263.4	1258.8	1240.1	1201.0	1148.2	1083.5
125°	1147.3	1208.7	1263.4	1302.1	1322.5	1333.9	1322.5	1302.1	1263.4	1208.7	1147.3
127.5°	1202.8	1269.3	1319.4	1354.4	1374.4	1383.5	1374.4	1354.4	1319.4	1269.3	1202.8
130°	1233.8	1302.1	1352.1	1390.8	1409.0	1418.1	1409.0	1390.8	1352.1	1302.1	1233.8
132.5°	1257.4	1329.4	1381.3	1416.3	1436.4	1445.5	1436.4	1416.3	1381.3	1329.4	1257.4
135°	1286.1	1361.2	1415.9	1450.0	1468.2	1477.3	1468.2	1450.0	1415.9	1361.2	1286.1
137.5°	1311.2	1379.5	1436.4	1472.3	1488.7	1494.6	1488.7	1472.3	1436.4	1379.5	1311.2
140°	1329.4	1388.6	1445.5	1479.6	1497.8	1500.1	1497.8	1479.6	1445.5	1388.6	1329.4
142.5°	1353.0	1399.5	1449.1	1483.3	1501.5	1505.6	1501.5	1483.3	1449.1	1399.5	1353.0
145°	1395.4	1422.7	1456.8	1488.7	1504.6	1509.2	1504.6	1488.7	1456.8	1422.7	1395.4
147.5°	1448.7	1457.3	1475.1	1496.0	1511.5	1514.7	1511.5	1496.0	1475.1	1457.3	1448.7
150°	1488.7	1486.4	1493.3	1506.9	1520.6	1518.3	1520.6	1506.9	1493.3	1486.4	1488.7
152.5°	1534.2	1521.0	1520.6	1527.0	1533.3	1532.9	1533.3	1527.0	1520.6	1521.0	1534.2
155°	1611.6	1586.6	1572.9	1568.4	1568.4	1566.1	1568.4	1568.4	1572.9	1586.6	1611.6
157.5°	1696.8	1661.7	1641.2	1630.3	1627.1	1622.1	1627.1	1630.3	1641.2	1661.7	1696.8
160°	1755.0	1716.3	1695.9	1677.6	1670.8	1664.0	1670.8	1677.6	1695.9	1716.3	1755.0
162.5°	1809.7	1772.8	1750.5	1734.1	1727.3	1716.8	1727.3	1734.1	1750.5	1772.8	1809.7
165°	1898.5	1859.8	1834.7	1821.1	1812.0	1802.8	1812.0	1821.1	1834.7	1859.8	1898.5
167.5°	1987.2	1944.9	1928.5	1913.0	1904.4	1888.0	1904.4	1913.0	1928.5	1944.9	1987.2
170°	2041.9	2003.2	1994.1	1980.4	1964.5	1946.3	1964.5	1980.4	1994.1	2003.2	2041.9
172.5°	2089.2	2063.3	2054.2	2040.5	2035.5	2020.9	2035.5	2040.5	2054.2	2063.3	2089.2
175°	2158.0	2137.5	2137.5	2135.2	2128.4	2114.7	2128.4	2135.2	2137.5	2137.5	2158.0
177.5°	2215.3	2204.4	2211.7	2211.7	2209.9	2197.1	2209.9	2211.7	2211.7	2204.4	2215.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	235.4	235.4	235.4	235.4
2.5°	247.2	242.4	238.0	233.6
5°	280.7	258.8	243.7	228.6
7.5°	346.1	281.1	250.5	219.8
10°	407.4	297.1	254.4	211.6
12.5°	454.8	318.7	260.6	202.6
15°	507.7	353.8	270.8	187.9
17.5°	550.6	393.6	283.1	172.7
20°	578.7	421.4	291.6	161.8
22.5°	599.5	442.0	296.9	151.9
25°	622.0	465.0	301.5	138.1
27.5°	625.2	470.1	297.4	124.7
30°	621.3	467.6	292.1	116.6
32.5°	613.7	462.0	285.7	109.3
35°	595.6	445.5	272.0	98.5
37.5°	568.3	419.7	254.5	89.2
40°	548.1	400.6	242.2	83.7
42.5°	524.6	378.3	228.3	78.3
45°	485.9	340.9	206.1	71.3
47.5°	444.5	298.9	181.8	64.7
50°	416.5	270.3	165.7	61.1
52.5°	389.0	242.6	150.0	57.5
55°	348.9	204.1	128.6	53.2
57.5°	311.4	171.1	110.2	49.3
60°	287.8	153.2	100.3	47.5
62.5°	264.3	136.8	90.8	44.8
65°	231.2	116.3	79.1	41.9
67.5°	201.0	101.0	69.4	37.8
70°	182.6	93.4	64.3	35.1
72.5°	162.4	85.2	59.2	33.3
75°	129.8	71.7	50.5	29.4
77.5°	91.3	55.6	39.8	24.0
80°	59.6	45.5	32.9	20.4
82.5°	43.9	35.5	26.1	16.7
85°	24.5	21.3	15.7	10.2
87.5°	15.1	12.7	8.8	5.0
90°	41.0	25.0	15.9	6.8
92.5°	88.3	61.5	43.3	25.0
95°	177.6	141.1	100.2	70.6
97.5°	282.7	224.0	183.5	134.8
100°	339.2	282.3	243.6	191.2
102.5°	401.1	353.3	300.0	247.7
105°	512.2	453.0	391.5	332.3
107.5°	615.1	550.0	476.2	422.9
110°	680.6	610.1	532.7	484.9



TEST NUMBER: P1436028

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	744.4	672.0	592.8	545.0
115°	830.9	751.2	678.3	637.4
117.5°	914.2	832.2	755.3	723.0
120°	965.2	883.2	808.1	783.1
122.5°	1007.0	926.9	857.3	846.8
125°	1069.9	987.9	928.7	942.4
127.5°	1120.9	1045.7	1008.4	1038.9
130°	1151.8	1085.8	1063.0	1106.3
132.5°	1179.1	1127.7	1117.7	1177.3
135°	1220.1	1190.5	1199.6	1281.6
137.5°	1268.8	1257.4	1287.9	1391.3
140°	1299.8	1306.6	1349.9	1466.0
142.5°	1341.7	1357.6	1413.6	1537.0
145°	1406.8	1440.9	1513.8	1636.7
147.5°	1480.5	1524.7	1614.8	1740.9
150°	1529.7	1586.6	1682.2	1802.8
152.5°	1586.1	1644.9	1740.5	1862.9
155°	1673.1	1739.1	1839.3	1944.0
157.5°	1761.9	1829.3	1924.9	2016.4
160°	1816.5	1889.3	1975.8	2060.1
162.5°	1878.4	1945.8	2021.4	2096.5
165°	1969.0	2023.7	2085.1	2148.8
167.5°	2045.0	2090.6	2138.8	2188.5
170°	2094.2	2130.6	2171.6	2210.3
172.5°	2136.1	2165.2	2195.3	2228.5
175°	2192.1	2208.0	2226.2	2246.7
177.5°	2235.3	2240.8	2246.3	2255.4
180°	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1436028
 CATALOG NUMBER: SQ2W-FB-K-150U-050D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.06	8.76	9.20	9.88	11.46	17.66	18.35	18.79	19.48	21.05
	3H	8.99	9.61	10.13	10.74	12.33	19.25	19.87	20.39	21.01	22.60
	4H	9.38	9.97	10.53	11.10	12.70	19.42	20.01	20.57	21.14	22.74
	6H	9.62	10.16	10.78	11.30	12.91	19.48	20.03	20.64	21.17	22.77
	8H	9.71	10.22	10.87	11.38	12.98	19.50	20.01	20.66	21.17	22.77
	12H	9.75	10.24	10.92	11.39	13.01	19.47	19.96	20.63	21.11	22.73
4H	2H	12.76	13.35	13.92	14.49	16.08	18.00	18.59	19.16	19.73	21.32
	3H	13.87	14.36	15.04	15.53	17.13	19.87	20.36	21.04	21.53	23.13
	4H	14.14	14.60	15.31	15.75	17.37	20.08	20.54	21.25	21.69	23.31
	6H	14.27	14.66	15.44	15.83	17.45	20.21	20.59	21.38	21.77	23.38
	8H	14.30	14.67	15.48	15.83	17.46	20.25	20.61	21.42	21.77	23.41
	12H	14.30	14.63	15.49	15.80	17.44	20.22	20.55	21.41	21.72	23.36
8H	4H	15.32	15.68	16.49	16.85	18.48	20.16	20.52	21.33	21.69	23.32
	6H	15.57	15.87	16.76	17.08	18.71	20.35	20.65	21.54	21.86	23.48
	8H	15.67	15.93	16.86	17.11	18.76	20.44	20.70	21.64	21.88	23.53
	12H	15.70	15.93	16.90	17.11	18.79	20.44	20.66	21.64	21.85	23.53
12H	4H	15.34	15.67	16.53	16.84	18.48	20.10	20.43	21.29	21.61	23.25
	6H	15.68	15.94	16.87	17.12	18.77	20.33	20.59	21.53	21.78	23.43
	8H	15.81	16.03	17.01	17.22	18.90	20.42	20.65	21.62	21.83	23.51