

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427949

Luminaire Tested: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427949  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE HEX LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8261.3 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 70.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	24480	24480	24480	24480
5°	24619	22374	24619	22374
10°	24053	20339	24053	20339
15°	24162	19941	24162	19941
20°	23298	20101	23298	20101
25°	22872	19634	22872	19634
30°	22376	19794	22376	19794
35°	22207	23201	22207	23201
40°	22225	18396	22225	18396
45°	22233	15844	22233	15844
50°	21923	14857	21923	14857
55°	21644	14252	21644	14252
60°	21428	13369	21428	13369
65°	21054	11629	21054	11629
70°	19883	8308	19883	8308
75°	17729	6301	17729	6301
80°	14486	5904	14486	5904
85°	9077	4001	9077	4001

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22233 cd/sqm



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.4	1.6
10°-20°	350.9	4.2
20°-30°	514.5	6.2
30°-40°	623.0	7.5
40°-50°	612.6	7.4
50°-60°	532.9	6.5
60°-70°	370.6	4.5
70°-80°	175.8	2.1
80°-90°	45.7	0.6
90°-100°	133.6	1.6
100°-110°	389.6	4.7
110°-120°	635.9	7.7
120°-130°	806.9	9.8
130°-140°	863.4	10.5
140°-150°	806.2	9.8
150°-160°	663.4	8.0
160°-170°	444.9	5.4
170°-180°	158.0	1.9
0°-30°	998.8	12.1
0°-40°	1621.8	19.6
0°-60°	2767.2	33.5
0°-90°	3359.3	40.7
90°-120°	1159.2	14.0
90°-150°	3635.7	44.0
90°-180°	4902.0	59.3
0°-180°	8261.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1516	1516	1516	1516	1516	
5°	1519	1380	1519	1380	1519	143
15°	1446	1193	1446	1193	1446	403
25°	1284	1102	1284	1102	1284	590
35°	1127	1177	1127	1177	1127	706
45°	974	694	974	694	974	748
55°	769	506	769	506	769	687
65°	551	304	551	304	551	541
75°	284	101	284	101	284	301
85°	49	22	49	22	49	66
90°	5	37	5	73	5	6
95°	53	39	53	229	53	63
105°	248	397	248	546	248	263
115°	475	658	475	811	475	468
125°	702	1043	702	994	702	628
135°	955	1365	955	1101	955	738
145°	1219	1574	1219	1124	1219	763
155°	1448	1709	1448	1167	1448	666
165°	1601	1782	1601	1343	1601	451
175°	1674	1745	1674	1575	1674	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2
2.5°	1512.7	1519.9	1527.1	1516.9	1501.0	1490.0	1483.8	1479.0	1477.9	1476.9	1477.9
5°	1519.0	1518.4	1517.8	1487.8	1448.0	1418.2	1398.3	1383.1	1381.8	1380.5	1381.8
7.5°	1491.3	1471.5	1451.6	1411.3	1364.3	1329.8	1307.8	1291.1	1290.1	1289.1	1290.1
10°	1467.1	1437.0	1406.8	1361.3	1310.7	1275.4	1255.5	1240.6	1240.6	1240.6	1240.6
12.5°	1461.3	1413.8	1366.2	1316.3	1265.7	1233.0	1218.2	1207.9	1211.0	1214.1	1211.0
15°	1445.5	1373.7	1301.8	1251.2	1207.6	1183.9	1180.0	1178.9	1186.0	1193.0	1186.0
17.5°	1393.0	1315.6	1238.3	1193.8	1160.2	1147.5	1155.7	1163.9	1172.1	1180.3	1172.1
20°	1356.0	1279.7	1203.4	1162.2	1132.7	1125.7	1141.1	1154.5	1162.2	1169.9	1162.2
22.5°	1324.9	1247.5	1170.2	1133.8	1110.9	1108.0	1124.9	1138.6	1142.7	1146.9	1142.7
25°	1283.9	1196.7	1109.5	1082.9	1076.5	1080.7	1095.4	1106.0	1104.1	1102.1	1104.1
27.5°	1234.8	1143.8	1052.8	1035.7	1043.2	1051.5	1060.5	1067.5	1068.7	1069.8	1068.7
30°	1200.2	1109.2	1018.1	1004.5	1016.7	1027.3	1036.3	1045.1	1053.4	1061.7	1053.4
32.5°	1166.8	1072.6	978.5	968.7	987.1	1006.9	1028.2	1048.9	1068.0	1087.1	1068.0
35°	1126.7	1028.6	930.5	922.8	945.2	974.1	1009.3	1051.5	1114.3	1177.1	1114.3
37.5°	1084.5	979.4	874.2	870.7	901.1	931.5	961.9	989.7	1009.7	1029.7	1009.7
40°	1054.5	944.2	834.0	833.8	870.4	908.2	947.3	965.1	918.9	872.8	918.9
42.5°	1022.2	911.9	801.7	798.4	830.9	872.5	923.4	942.1	864.2	786.2	864.2
45°	973.7	859.0	744.2	740.0	772.7	795.8	809.3	805.4	749.7	693.9	749.7
47.5°	916.6	807.2	697.9	697.0	732.2	734.8	704.7	676.6	654.8	633.0	654.8
50°	872.8	769.5	666.3	670.8	711.2	707.3	659.3	619.7	605.6	591.5	605.6
52.5°	830.1	732.0	633.9	645.8	694.4	686.7	622.7	572.4	562.9	553.4	562.9
55°	768.9	674.6	580.4	607.3	674.6	664.4	576.6	510.2	508.3	506.3	508.3
57.5°	704.0	614.9	525.7	544.4	599.1	588.3	512.1	455.8	459.2	462.5	459.2
60°	663.6	577.0	490.5	492.9	524.9	514.7	462.1	421.7	417.9	414.0	417.9
62.5°	620.9	538.4	456.0	444.0	455.6	443.5	407.9	380.2	376.3	372.5	376.3
65°	551.1	476.1	401.0	378.4	373.3	356.0	326.5	304.4	304.4	304.4	304.4
67.5°	474.3	408.9	343.5	318.2	306.3	289.1	266.7	246.0	230.6	215.2	230.6
70°	421.2	363.5	305.8	279.4	263.4	242.8	217.8	196.5	186.3	176.0	186.3
72.5°	364.7	315.2	265.7	238.6	219.0	199.0	178.6	160.4	148.6	136.8	148.6
75°	284.2	244.4	204.7	178.4	156.6	136.4	117.8	103.5	102.3	101.0	102.3
77.5°	205.4	176.4	147.5	126.2	107.5	93.4	84.1	77.1	77.2	77.3	77.2
80°	155.8	134.0	112.2	92.3	73.1	63.2	62.5	62.2	62.8	63.5	62.8
82.5°	109.6	93.5	77.3	64.6	53.1	47.8	48.7	49.4	49.5	49.6	49.5
85°	49.0	41.4	33.7	30.8	29.5	27.6	25.0	22.9	22.3	21.6	22.3
87.5°	11.4	12.2	13.4	13.5	13.0	12.6	12.6	12.9	13.2	13.2	13.2
90°	5.1	11.9	20.3	27.1	32.2	33.9	33.9	35.6	37.3	37.3	37.3
92.5°	18.7	29.5	29.8	29.8	36.3	39.3	42.1	42.4	44.1	44.1	44.1
95°	52.6	57.7	86.5	84.8	57.7	45.8	39.0	39.0	39.0	39.0	39.0
97.5°	100.4	107.9	112.6	150.9	159.4	154.0	125.5	105.5	94.3	89.2	94.3
100°	142.4	145.8	156.0	157.7	200.1	240.8	220.5	195.0	186.5	181.5	186.5
102.5°	184.5	186.5	202.1	209.3	219.1	242.2	312.7	304.9	299.1	298.1	299.1
105°	247.6	249.3	278.1	291.7	298.5	298.5	296.8	330.7	385.0	396.8	385.0
107.5°	315.1	322.9	356.8	393.1	400.9	402.9	394.1	389.0	387.0	388.3	387.0
110°	361.2	373.1	413.8	459.6	471.4	474.8	471.4	466.3	463.0	463.0	463.0



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	406.0	423.3	469.4	522.0	542.0	552.2	544.7	541.0	537.6	540.3	537.6
115°	474.8	500.3	561.3	615.6	656.3	661.4	659.7	659.7	658.0	658.0	658.0
117.5°	538.6	579.3	647.8	710.9	758.0	771.6	778.4	776.3	774.3	777.7	774.3
120°	583.4	630.8	708.9	780.1	825.9	846.2	853.0	849.6	853.0	849.6	853.0
122.5°	630.8	689.2	765.8	839.8	893.7	916.8	924.9	925.6	926.3	924.2	926.3
125°	702.1	773.3	863.2	939.5	995.4	1022.6	1029.4	1031.1	1034.4	1042.9	1034.4
127.5°	774.0	854.7	953.4	1027.0	1084.3	1117.2	1127.7	1131.4	1138.6	1142.3	1138.6
130°	824.2	915.7	1015.8	1085.3	1141.3	1176.9	1195.6	1200.6	1209.1	1207.4	1209.1
132.5°	877.1	972.7	1074.1	1146.4	1198.3	1236.6	1252.5	1267.1	1270.2	1272.5	1270.2
135°	954.7	1058.2	1159.9	1231.2	1280.3	1317.7	1338.0	1351.6	1360.0	1365.1	1360.0
137.5°	1036.5	1145.7	1243.4	1306.8	1356.3	1388.5	1411.6	1425.8	1434.7	1438.7	1434.7
140°	1092.1	1197.2	1292.2	1358.3	1402.4	1434.7	1455.0	1472.0	1482.1	1482.1	1482.1
142.5°	1145.0	1248.8	1341.1	1407.2	1445.9	1475.4	1497.1	1510.0	1521.5	1521.5	1521.5
145°	1219.3	1322.7	1407.5	1473.7	1505.9	1533.0	1556.8	1566.9	1573.7	1573.7	1573.7
147.5°	1297.0	1388.5	1465.9	1529.3	1556.4	1588.3	1607.0	1615.1	1623.6	1619.8	1623.6
150°	1343.1	1427.9	1502.5	1561.8	1589.0	1619.5	1638.2	1644.9	1653.4	1648.3	1653.4
152.5°	1387.9	1468.6	1536.4	1591.7	1614.8	1645.3	1666.6	1673.4	1679.2	1675.5	1679.2
155°	1448.2	1519.5	1582.2	1633.1	1653.4	1682.3	1702.6	1711.1	1717.9	1709.4	1717.9
157.5°	1502.2	1563.5	1618.1	1665.0	1686.7	1711.4	1730.4	1740.9	1747.7	1744.0	1747.7
160°	1534.7	1590.7	1639.9	1683.9	1704.3	1726.3	1746.7	1758.6	1765.3	1760.3	1765.3
162.5°	1561.8	1612.4	1658.8	1698.9	1716.5	1735.8	1760.3	1770.8	1777.6	1771.1	1777.6
165°	1600.9	1641.6	1682.3	1716.2	1731.4	1746.7	1772.1	1784.0	1789.1	1782.3	1789.1
167.5°	1630.4	1661.6	1694.5	1723.6	1734.8	1749.7	1775.2	1785.0	1791.5	1783.0	1791.5
170°	1646.6	1673.8	1702.6	1726.3	1734.8	1748.4	1773.8	1782.3	1787.4	1778.9	1787.4
172.5°	1660.2	1680.6	1704.0	1725.0	1729.4	1740.2	1764.3	1772.8	1776.5	1769.4	1776.5
175°	1673.8	1685.6	1702.6	1716.2	1714.5	1721.3	1741.6	1748.4	1755.2	1745.0	1755.2
177.5°	1680.2	1685.6	1691.1	1699.2	1693.8	1693.8	1708.7	1712.8	1714.1	1708.7	1714.1
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2
2.5°	1479.0	1483.8	1490.0	1501.0	1516.9	1527.1	1519.9	1512.7	1519.9	1527.1	1516.9
5°	1383.1	1398.3	1418.2	1448.0	1487.8	1517.8	1518.4	1519.0	1518.4	1517.8	1487.8
7.5°	1291.1	1307.8	1329.8	1364.3	1411.3	1451.6	1471.5	1491.3	1471.5	1451.6	1411.3
10°	1240.6	1255.5	1275.4	1310.7	1361.3	1406.8	1437.0	1467.1	1437.0	1406.8	1361.3
12.5°	1207.9	1218.2	1233.0	1265.7	1316.3	1366.2	1413.8	1461.3	1413.8	1366.2	1316.3
15°	1178.9	1180.0	1183.9	1207.6	1251.2	1301.8	1373.7	1445.5	1373.7	1301.8	1251.2
17.5°	1163.9	1155.7	1147.5	1160.2	1193.8	1238.3	1315.6	1393.0	1315.6	1238.3	1193.8
20°	1154.5	1141.1	1125.7	1132.7	1162.2	1203.4	1279.7	1356.0	1279.7	1203.4	1162.2
22.5°	1138.6	1124.9	1108.0	1110.9	1133.8	1170.2	1247.5	1324.9	1247.5	1170.2	1133.8
25°	1106.0	1095.4	1080.7	1076.5	1082.9	1109.5	1196.7	1283.9	1196.7	1109.5	1082.9
27.5°	1067.5	1060.5	1051.5	1043.2	1035.7	1052.8	1143.8	1234.8	1143.8	1052.8	1035.7
30°	1045.1	1036.3	1027.3	1016.7	1004.5	1018.1	1109.2	1200.2	1109.2	1018.1	1004.5
32.5°	1048.9	1028.2	1006.9	987.1	968.7	978.5	1072.6	1166.8	1072.6	978.5	968.7
35°	1051.5	1009.3	974.1	945.2	922.8	930.5	1028.6	1126.7	1028.6	930.5	922.8
37.5°	989.7	961.9	931.5	901.1	870.7	874.2	979.4	1084.5	979.4	874.2	870.7
40°	965.1	947.3	908.2	870.4	833.8	834.0	944.2	1054.5	944.2	834.0	833.8
42.5°	942.1	923.4	872.5	830.9	798.4	801.7	911.9	1022.2	911.9	801.7	798.4
45°	805.4	809.3	795.8	772.7	740.0	744.2	859.0	973.7	859.0	744.2	740.0
47.5°	676.6	704.7	734.8	732.2	697.0	697.9	807.2	916.6	807.2	697.9	697.0
50°	619.7	659.3	707.3	711.2	670.8	666.3	769.5	872.8	769.5	666.3	670.8
52.5°	572.4	622.7	686.7	694.4	645.8	633.9	732.0	830.1	732.0	633.9	645.8
55°	510.2	576.6	664.4	674.6	607.3	580.4	674.6	768.9	674.6	580.4	607.3
57.5°	455.8	512.1	588.3	599.1	544.4	525.7	614.9	704.0	614.9	525.7	544.4
60°	421.7	462.1	514.7	524.9	492.9	490.5	577.0	663.6	577.0	490.5	492.9
62.5°	380.2	407.9	443.5	455.6	444.0	456.0	538.4	620.9	538.4	456.0	444.0
65°	304.4	326.5	356.0	373.3	378.4	401.0	476.1	551.1	476.1	401.0	378.4
67.5°	246.0	266.7	289.1	306.3	318.2	343.5	408.9	474.3	408.9	343.5	318.2
70°	196.5	217.8	242.8	263.4	279.4	305.8	363.5	421.2	363.5	305.8	279.4
72.5°	160.4	178.6	199.0	219.0	238.6	265.7	315.2	364.7	315.2	265.7	238.6
75°	103.5	117.8	136.4	156.6	178.4	204.7	244.4	284.2	244.4	204.7	178.4
77.5°	77.1	84.1	93.4	107.5	126.2	147.5	176.4	205.4	176.4	147.5	126.2
80°	62.2	62.5	63.2	73.1	92.3	112.2	134.0	155.8	134.0	112.2	92.3
82.5°	49.4	48.7	47.8	53.1	64.6	77.3	93.5	109.6	93.5	77.3	64.6
85°	22.9	25.0	27.6	29.5	30.8	33.7	41.4	49.0	41.4	33.7	30.8
87.5°	12.9	12.6	12.6	13.0	13.5	13.4	12.2	11.4	12.2	13.1	14.2
90°	35.6	33.9	33.9	32.2	27.1	20.3	11.9	5.1	11.9	18.7	30.5
92.5°	42.4	42.1	39.3	36.3	29.8	29.8	29.5	18.7	32.2	45.8	65.8
95°	39.0	39.0	45.8	57.7	84.8	86.5	57.7	52.6	74.6	105.1	132.3
97.5°	105.5	125.5	154.0	159.4	150.9	112.6	107.9	100.4	136.7	166.9	210.6
100°	195.0	220.5	240.8	200.1	157.7	156.0	145.8	142.4	181.5	210.3	252.7
102.5°	304.9	312.7	242.2	219.1	209.3	202.1	186.5	184.5	223.5	263.2	298.8
105°	330.7	296.8	298.5	298.5	291.7	278.1	249.3	247.6	291.7	337.5	381.6
107.5°	389.0	394.1	402.9	400.9	393.1	356.8	322.9	315.1	354.8	409.7	458.2
110°	466.3	471.4	474.8	471.4	459.6	413.8	373.1	361.2	396.8	454.5	507.0

TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	541.0	544.7	552.2	542.0	522.0	469.4	423.3	406.0	441.6	500.6	554.5
115°	659.7	659.7	661.4	656.3	615.6	561.3	500.3	474.8	505.4	559.6	619.0
117.5°	776.3	778.4	771.6	758.0	710.9	647.8	579.3	538.6	562.7	620.0	681.0
120°	849.6	853.0	846.2	825.9	780.1	708.9	630.8	583.4	602.0	658.0	719.0
122.5°	925.6	924.9	916.8	893.7	839.8	765.8	689.2	630.8	638.6	690.5	750.2
125°	1031.1	1029.4	1022.6	995.4	939.5	863.2	773.3	702.1	691.9	736.0	797.0
127.5°	1131.4	1127.7	1117.2	1084.3	1027.0	953.4	854.7	774.0	751.2	779.1	835.0
130°	1200.6	1195.6	1176.9	1141.3	1085.3	1015.8	915.7	824.2	791.9	808.9	858.1
132.5°	1267.1	1252.5	1236.6	1198.3	1146.4	1074.1	972.7	877.1	832.6	840.1	878.4
135°	1351.6	1338.0	1317.7	1280.3	1231.2	1159.9	1058.2	954.7	893.7	886.9	909.0
137.5°	1425.8	1411.6	1388.5	1356.3	1306.8	1243.4	1145.7	1036.5	959.5	936.8	945.2
140°	1472.0	1455.0	1434.7	1402.4	1358.3	1292.2	1197.2	1092.1	1005.6	973.4	968.3
142.5°	1510.0	1497.1	1475.4	1445.9	1407.2	1341.1	1248.8	1145.0	1053.1	1011.4	999.5
145°	1566.9	1556.8	1533.0	1505.9	1473.7	1407.5	1322.7	1219.3	1127.7	1073.5	1048.0
147.5°	1615.1	1607.0	1588.3	1556.4	1529.3	1465.9	1388.5	1297.0	1203.0	1135.9	1103.0
150°	1644.9	1638.2	1619.5	1589.0	1561.8	1502.5	1427.9	1343.1	1253.2	1182.0	1139.6
152.5°	1673.4	1666.6	1645.3	1614.8	1591.7	1536.4	1468.6	1387.9	1296.6	1225.4	1181.6
155°	1711.1	1702.6	1682.3	1653.4	1633.1	1582.2	1519.5	1448.2	1370.2	1295.6	1246.4
157.5°	1740.9	1730.4	1711.4	1686.7	1665.0	1618.1	1563.5	1502.2	1434.0	1362.8	1312.6
160°	1758.6	1746.7	1726.3	1704.3	1683.9	1639.9	1590.7	1534.7	1472.0	1407.5	1353.3
162.5°	1770.8	1760.3	1735.8	1716.5	1698.9	1658.8	1612.4	1561.8	1505.9	1449.6	1399.4
165°	1784.0	1772.1	1746.7	1731.4	1716.2	1682.3	1641.6	1600.9	1553.4	1507.6	1466.9
167.5°	1785.0	1775.2	1749.7	1734.8	1723.6	1694.5	1661.6	1630.4	1593.4	1557.4	1523.5
170°	1782.3	1773.8	1748.4	1734.8	1726.3	1702.6	1673.8	1646.6	1617.8	1587.3	1560.2
172.5°	1772.8	1764.3	1740.2	1729.4	1725.0	1704.0	1680.6	1660.2	1635.4	1613.1	1591.4
175°	1748.4	1741.6	1721.3	1714.5	1716.2	1702.6	1685.6	1673.8	1658.5	1644.9	1633.1
177.5°	1712.8	1708.7	1693.8	1693.8	1699.2	1691.1	1685.6	1680.2	1673.4	1669.4	1665.3
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2	1516.2
2.5°	1501.0	1490.0	1483.8	1479.0	1477.9	1476.9	1477.9	1479.0	1483.8	1490.0	1501.0
5°	1448.0	1418.2	1398.3	1383.1	1381.8	1380.5	1381.8	1383.1	1398.3	1418.2	1448.0
7.5°	1364.3	1329.8	1307.8	1291.1	1290.1	1289.1	1290.1	1291.1	1307.8	1329.8	1364.3
10°	1310.7	1275.4	1255.5	1240.6	1240.6	1240.6	1240.6	1240.6	1255.5	1275.4	1310.7
12.5°	1265.7	1233.0	1218.2	1207.9	1211.0	1214.1	1211.0	1207.9	1218.2	1233.0	1265.7
15°	1207.6	1183.9	1180.0	1178.9	1186.0	1193.0	1186.0	1178.9	1180.0	1183.9	1207.6
17.5°	1160.2	1147.5	1155.7	1163.9	1172.1	1180.3	1172.1	1163.9	1155.7	1147.5	1160.2
20°	1132.7	1125.7	1141.1	1154.5	1162.2	1169.9	1162.2	1154.5	1141.1	1125.7	1132.7
22.5°	1110.9	1108.0	1124.9	1138.6	1142.7	1146.9	1142.7	1138.6	1124.9	1108.0	1110.9
25°	1076.5	1080.7	1095.4	1106.0	1104.1	1102.1	1104.1	1106.0	1095.4	1080.7	1076.5
27.5°	1043.2	1051.5	1060.5	1067.5	1068.7	1069.8	1068.7	1067.5	1060.5	1051.5	1043.2
30°	1016.7	1027.3	1036.3	1045.1	1053.4	1061.7	1053.4	1045.1	1036.3	1027.3	1016.7
32.5°	987.1	1006.9	1028.2	1048.9	1068.0	1087.1	1068.0	1048.9	1028.2	1006.9	987.1
35°	945.2	974.1	1009.3	1051.5	1114.3	1177.1	1114.3	1051.5	1009.3	974.1	945.2
37.5°	901.1	931.5	961.9	989.7	1009.7	1029.7	1009.7	989.7	961.9	931.5	901.1
40°	870.4	908.2	947.3	965.1	918.9	872.8	918.9	965.1	947.3	908.2	870.4
42.5°	830.9	872.5	923.4	942.1	864.2	786.2	864.2	942.1	923.4	872.5	830.9
45°	772.7	795.8	809.3	805.4	749.7	693.9	749.7	805.4	809.3	795.8	772.7
47.5°	732.2	734.8	704.7	676.6	654.8	633.0	654.8	704.7	734.8	732.2	732.2
50°	711.2	707.3	659.3	619.7	605.6	591.5	605.6	619.7	659.3	707.3	711.2
52.5°	694.4	686.7	622.7	572.4	562.9	553.4	562.9	622.7	686.7	694.4	694.4
55°	674.6	664.4	576.6	510.2	508.3	506.3	508.3	510.2	576.6	664.4	674.6
57.5°	599.1	588.3	512.1	455.8	459.2	462.5	459.2	512.1	588.3	599.1	599.1
60°	524.9	514.7	462.1	421.7	417.9	414.0	417.9	462.1	514.7	524.9	524.9
62.5°	455.6	443.5	407.9	380.2	376.3	372.5	376.3	407.9	443.5	455.6	455.6
65°	373.3	356.0	326.5	304.4	304.4	304.4	304.4	326.5	356.0	373.3	373.3
67.5°	306.3	289.1	266.7	246.0	230.6	215.2	230.6	266.7	289.1	306.3	306.3
70°	263.4	242.8	217.8	196.5	186.3	176.0	186.3	217.8	242.8	263.4	263.4
72.5°	219.0	199.0	178.6	160.4	148.6	136.8	148.6	178.6	199.0	219.0	219.0
75°	156.6	136.4	117.8	103.5	102.3	101.0	102.3	117.8	136.4	156.6	156.6
77.5°	107.5	93.4	84.1	77.1	77.2	77.3	77.2	84.1	93.4	107.5	107.5
80°	73.1	63.2	62.5	62.2	62.8	63.5	62.8	62.2	62.5	63.2	73.1
82.5°	53.1	47.8	48.7	49.4	49.5	49.6	49.5	47.8	47.8	53.1	53.1
85°	29.5	27.6	25.0	22.9	22.3	21.6	22.3	25.0	27.6	29.5	29.5
87.5°	14.3	15.9	18.3	19.7	21.0	20.4	21.0	18.3	15.9	14.3	14.3
90°	39.0	50.9	62.7	69.5	76.3	72.9	76.3	62.7	50.9	39.0	39.0
92.5°	78.3	98.4	112.9	125.2	130.6	129.9	130.6	112.9	98.4	78.3	78.3
95°	157.7	181.5	205.2	222.2	232.3	228.9	232.3	205.2	181.5	157.7	157.7
97.5°	243.2	275.1	301.5	317.5	327.6	334.4	327.6	301.5	275.1	243.2	243.2
100°	300.2	330.7	361.2	379.9	396.8	403.6	396.8	361.2	330.7	300.2	300.2
102.5°	346.3	386.3	419.5	439.6	453.8	460.6	453.8	419.5	386.3	346.3	346.3
105°	422.3	464.7	500.3	525.7	541.0	546.1	541.0	500.3	464.7	422.3	422.3
107.5°	498.2	542.0	574.9	603.0	621.7	632.5	621.7	574.9	542.0	498.2	498.2
110°	557.9	593.5	629.1	654.6	673.2	680.0	673.2	629.1	593.5	557.9	557.9



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	608.1	647.8	683.4	708.9	730.2	739.7	730.2	708.9	683.4	647.8	608.1
115°	678.3	730.9	763.1	786.9	802.1	810.6	802.1	786.9	763.1	730.9	678.3
117.5°	736.7	791.6	826.9	845.2	852.3	858.4	852.3	845.2	826.9	791.6	736.7
120°	773.3	824.2	864.9	888.6	897.1	900.5	897.1	888.6	864.9	824.2	773.3
122.5°	807.2	855.4	894.7	923.9	937.8	941.2	937.8	923.9	894.7	855.4	807.2
125°	854.7	900.5	941.2	970.0	985.3	993.7	985.3	970.0	941.2	900.5	854.7
127.5°	896.1	945.6	982.9	1009.0	1023.9	1030.7	1023.9	1009.0	982.9	945.6	896.1
130°	919.1	970.0	1007.3	1036.1	1049.7	1056.5	1049.7	1036.1	1007.3	970.0	919.1
132.5°	936.8	990.4	1029.0	1055.1	1070.1	1076.8	1070.1	1055.1	1029.0	990.4	936.8
135°	958.1	1014.1	1054.8	1080.2	1093.8	1100.6	1093.8	1080.2	1054.8	1014.1	958.1
137.5°	976.8	1027.7	1070.1	1096.9	1109.1	1113.5	1109.1	1096.9	1070.1	1027.7	976.8
140°	990.4	1034.4	1076.8	1102.3	1115.8	1117.5	1115.8	1102.3	1076.8	1034.4	990.4
142.5°	1008.0	1042.6	1079.6	1105.0	1118.6	1121.6	1118.6	1105.0	1079.6	1042.6	1008.0
145°	1039.5	1059.9	1085.3	1109.1	1120.9	1124.3	1120.9	1109.1	1085.3	1059.9	1039.5
147.5°	1079.2	1085.7	1098.9	1114.5	1126.0	1128.4	1126.0	1114.5	1098.9	1085.7	1079.2
150°	1109.1	1107.4	1112.5	1122.6	1132.8	1131.1	1132.8	1122.6	1112.5	1107.4	1109.1
152.5°	1143.0	1133.1	1132.8	1137.6	1142.3	1142.0	1142.3	1137.6	1132.8	1133.1	1143.0
155°	1200.6	1182.0	1171.8	1168.4	1168.4	1166.7	1168.4	1168.4	1171.8	1182.0	1200.6
157.5°	1264.1	1237.9	1222.7	1214.5	1212.2	1208.4	1212.2	1214.5	1222.7	1237.9	1264.1
160°	1307.5	1278.6	1263.4	1249.8	1244.7	1239.6	1244.7	1249.8	1263.4	1278.6	1307.5
162.5°	1348.2	1320.7	1304.1	1291.9	1286.8	1279.0	1286.8	1291.9	1304.1	1320.7	1348.2
165°	1414.3	1385.5	1366.8	1356.7	1349.9	1343.1	1349.9	1356.7	1366.8	1385.5	1414.3
167.5°	1480.4	1448.9	1436.7	1425.2	1418.7	1406.5	1418.7	1425.2	1436.7	1448.9	1480.4
170°	1521.1	1492.3	1485.5	1475.4	1463.5	1449.9	1463.5	1475.4	1485.5	1492.3	1521.1
172.5°	1556.4	1537.1	1530.3	1520.1	1516.4	1505.5	1516.4	1520.1	1530.3	1537.1	1556.4
175°	1607.6	1592.4	1592.4	1590.7	1585.6	1575.4	1585.6	1590.7	1592.4	1592.4	1607.6
177.5°	1650.4	1642.2	1647.7	1647.7	1646.3	1636.8	1646.3	1647.7	1647.7	1642.2	1650.4
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1516.2	1516.2	1516.2	1516.2
2.5°	1516.9	1527.1	1519.9	1512.7
5°	1487.8	1517.8	1518.4	1519.0
7.5°	1411.3	1451.6	1471.5	1491.3
10°	1361.3	1406.8	1437.0	1467.1
12.5°	1316.3	1366.2	1413.8	1461.3
15°	1251.2	1301.8	1373.7	1445.5
17.5°	1193.8	1238.3	1315.6	1393.0
20°	1162.2	1203.4	1279.7	1356.0
22.5°	1133.8	1170.2	1247.5	1324.9
25°	1082.9	1109.5	1196.7	1283.9
27.5°	1035.7	1052.8	1143.8	1234.8
30°	1004.5	1018.1	1109.2	1200.2
32.5°	968.7	978.5	1072.6	1166.8
35°	922.8	930.5	1028.6	1126.7
37.5°	870.7	874.2	979.4	1084.5
40°	833.8	834.0	944.2	1054.5
42.5°	798.4	801.7	911.9	1022.2
45°	740.0	744.2	859.0	973.7
47.5°	697.0	697.9	807.2	916.6
50°	670.8	666.3	769.5	872.8
52.5°	645.8	633.9	732.0	830.1
55°	607.3	580.4	674.6	768.9
57.5°	544.4	525.7	614.9	704.0
60°	492.9	490.5	577.0	663.6
62.5°	444.0	456.0	538.4	620.9
65°	378.4	401.0	476.1	551.1
67.5°	318.2	343.5	408.9	474.3
70°	279.4	305.8	363.5	421.2
72.5°	238.6	265.7	315.2	364.7
75°	178.4	204.7	244.4	284.2
77.5°	126.2	147.5	176.4	205.4
80°	92.3	112.2	134.0	155.8
82.5°	64.6	77.3	93.5	109.6
85°	30.8	33.7	41.4	49.0
87.5°	14.2	13.1	12.2	11.4
90°	30.5	18.7	11.9	5.1
92.5°	65.8	45.8	32.2	18.7
95°	132.3	105.1	74.6	52.6
97.5°	210.6	166.9	136.7	100.4
100°	252.7	210.3	181.5	142.4
102.5°	298.8	263.2	223.5	184.5
105°	381.6	337.5	291.7	247.6
107.5°	458.2	409.7	354.8	315.1
110°	507.0	454.5	396.8	361.2



TEST NUMBER: P1427949

CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	554.5	500.6	441.6	406.0
115°	619.0	559.6	505.4	474.8
117.5°	681.0	620.0	562.7	538.6
120°	719.0	658.0	602.0	583.4
122.5°	750.2	690.5	638.6	630.8
125°	797.0	736.0	691.9	702.1
127.5°	835.0	779.1	751.2	774.0
130°	858.1	808.9	791.9	824.2
132.5°	878.4	840.1	832.6	877.1
135°	909.0	886.9	893.7	954.7
137.5°	945.2	936.8	959.5	1036.5
140°	968.3	973.4	1005.6	1092.1
142.5°	999.5	1011.4	1053.1	1145.0
145°	1048.0	1073.5	1127.7	1219.3
147.5°	1103.0	1135.9	1203.0	1297.0
150°	1139.6	1182.0	1253.2	1343.1
152.5°	1181.6	1225.4	1296.6	1387.9
155°	1246.4	1295.6	1370.2	1448.2
157.5°	1312.6	1362.8	1434.0	1502.2
160°	1353.3	1407.5	1472.0	1534.7
162.5°	1399.4	1449.6	1505.9	1561.8
165°	1466.9	1507.6	1553.4	1600.9
167.5°	1523.5	1557.4	1593.4	1630.4
170°	1560.2	1587.3	1617.8	1646.6
172.5°	1591.4	1613.1	1635.4	1660.2
175°	1633.1	1644.9	1658.5	1673.8
177.5°	1665.3	1669.4	1673.4	1680.2
180°	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1427949  
 CATALOG NUMBER: SQ2W-PH1-K-125U-075D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.05	17.83	18.09	18.87	20.27	15.88	16.66	16.92	17.70	19.10
	3H	19.22	19.92	20.26	20.97	22.38	16.92	17.62	17.97	18.67	20.09
	4H	20.03	20.69	21.09	21.74	23.17	17.17	17.82	18.22	18.88	20.30
	6H	20.49	21.10	21.56	22.15	23.59	17.30	17.91	18.37	18.96	20.40
	8H	20.64	21.22	21.71	22.29	23.72	17.36	17.94	18.43	19.01	20.44
	12H	20.70	21.25	21.77	22.31	23.77	17.37	17.91	18.44	18.98	20.44
4H	2H	17.48	18.14	18.54	19.19	20.61	16.55	17.21	17.62	18.27	19.69
	3H	19.72	20.27	20.79	21.35	22.79	17.78	18.32	18.85	19.40	20.84
	4H	20.59	21.09	21.67	22.16	23.62	18.06	18.57	19.14	19.64	21.10
	6H	21.15	21.58	22.23	22.67	24.12	18.26	18.69	19.34	19.78	21.24
	8H	21.35	21.75	22.43	22.83	24.30	18.35	18.75	19.43	19.83	21.30
	12H	21.43	21.79	22.53	22.89	24.36	18.37	18.73	19.47	19.83	21.30
8H	4H	20.61	21.01	21.69	22.09	23.56	18.29	18.69	19.37	19.77	21.24
	6H	21.23	21.56	22.34	22.69	24.16	18.55	18.88	19.66	20.01	21.48
	8H	21.49	21.79	22.61	22.89	24.38	18.70	18.99	19.81	20.10	21.58
	12H	21.62	21.88	22.74	22.98	24.51	18.76	19.01	19.88	20.12	21.64
12H	4H	20.55	20.92	21.66	22.02	23.49	18.28	18.64	19.38	19.74	21.22
	6H	21.21	21.50	22.32	22.61	24.10	18.59	18.88	19.70	19.99	21.47
	8H	21.48	21.73	22.59	22.84	24.36	18.74	19.00	19.86	20.11	21.63