

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427979

Luminaire Tested: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427979
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10329.9 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	36	32	29	28	26	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	50	37	30	25	45	35	28	24	29	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	18	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32913	32913	32913	32913
5°	33102	30084	33102	30084
10°	32338	27346	32338	27346
15°	32484	26811	32484	26811
20°	31326	27027	31326	27027
25°	30752	26398	30752	26398
30°	30085	26613	30085	26613
35°	29857	31195	29857	31195
40°	29882	24731	29882	24731
45°	29893	21301	29893	21301
50°	29473	19974	29473	19974
55°	29100	19164	29100	19164
60°	28810	17976	28810	17976
65°	28305	15633	28305	15633
70°	26738	11169	26738	11169
75°	23836	8471	23836	8471
80°	19479	7931	19479	7931
85°	12208	5391	12208	5391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29893 cd/sqm



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.4	1.7
10°-20°	471.8	4.6
20°-30°	691.7	6.7
30°-40°	837.6	8.1
40°-50°	823.6	8.0
50°-60°	716.4	6.9
60°-70°	498.3	4.8
70°-80°	236.3	2.3
80°-90°	60.3	0.6
90°-100°	158.5	1.5
100°-110°	462.2	4.5
110°-120°	754.2	7.3
120°-130°	957.1	9.3
130°-140°	1024.1	9.9
140°-150°	956.3	9.3
150°-160°	786.9	7.6
160°-170°	527.7	5.1
170°-180°	187.4	1.8
0°-30°	1342.9	13.0
0°-40°	2180.5	21.1
0°-60°	3720.6	36.0
0°-90°	4515.5	43.7
90°-120°	1374.9	13.3
90°-150°	4312.4	41.7
90°-180°	5814.0	56.3
0°-180°	10329.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2038	2038	2038	2038	2038	
5°	2042	1856	2042	1856	2042	192
15°	1943	1604	1943	1604	1943	542
25°	1726	1482	1726	1482	1726	794
35°	1515	1583	1515	1583	1515	949
45°	1309	933	1309	933	1309	1006
55°	1034	681	1034	681	1034	924
65°	741	409	741	409	741	728
75°	382	136	382	136	382	405
85°	66	29	66	29	66	89
90°	6	44	6	86	6	7
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	2033.8	2043.5	2053.1	2039.5	2018.1	2003.3	1995.0	1988.5	1987.1	1985.7	1987.1
5°	2042.4	2041.5	2040.6	2000.3	1946.9	1906.8	1880.1	1859.6	1857.9	1856.2	1857.9
7.5°	2005.1	1978.4	1951.7	1897.5	1834.3	1787.9	1758.4	1736.0	1734.6	1733.2	1734.6
10°	1972.5	1932.0	1891.5	1830.3	1762.2	1714.8	1688.1	1668.0	1668.0	1668.0	1668.0
12.5°	1964.8	1900.8	1836.9	1769.8	1701.7	1657.7	1637.9	1624.1	1628.2	1632.3	1628.2
15°	1943.4	1846.9	1750.3	1682.2	1623.6	1591.7	1586.6	1585.1	1594.5	1604.0	1594.5
17.5°	1872.8	1768.9	1664.9	1605.1	1559.9	1542.8	1553.9	1564.9	1575.9	1587.0	1575.9
20°	1823.2	1720.6	1618.0	1562.6	1523.0	1513.5	1534.2	1552.3	1562.6	1573.0	1562.6
22.5°	1781.3	1677.3	1573.4	1524.4	1493.7	1489.7	1512.5	1530.9	1536.4	1542.0	1536.4
25°	1726.2	1609.0	1491.7	1456.0	1447.3	1452.9	1472.8	1487.0	1484.4	1481.8	1484.4
27.5°	1660.3	1537.9	1415.5	1392.5	1402.7	1413.8	1425.8	1435.3	1436.8	1438.4	1436.8
30°	1613.7	1491.3	1368.9	1350.6	1367.0	1381.2	1393.3	1405.1	1416.3	1427.5	1416.3
32.5°	1568.7	1442.2	1315.6	1302.5	1327.1	1353.8	1382.4	1410.3	1436.0	1461.7	1436.0
35°	1514.8	1382.9	1251.0	1240.7	1270.8	1309.6	1357.0	1413.7	1498.2	1582.7	1498.2
37.5°	1458.2	1316.8	1175.4	1170.7	1211.6	1252.4	1293.3	1330.7	1357.6	1384.5	1357.6
40°	1417.8	1269.6	1121.3	1121.1	1170.2	1221.1	1273.6	1297.6	1235.5	1173.4	1235.5
42.5°	1374.4	1226.1	1077.8	1073.5	1117.1	1173.1	1241.6	1266.7	1161.9	1057.1	1161.9
45°	1309.2	1154.9	1000.6	995.0	1039.0	1070.0	1088.1	1082.9	1007.9	932.9	1007.9
47.5°	1232.4	1085.3	938.3	937.1	984.5	987.9	947.4	909.7	880.4	851.1	880.4
50°	1173.4	1034.7	895.9	901.9	956.2	951.0	886.4	833.2	814.2	795.2	814.2
52.5°	1116.0	984.1	852.2	868.3	933.6	923.3	837.2	769.5	756.8	744.0	756.8
55°	1033.8	907.1	780.4	816.6	907.1	893.3	775.2	686.0	683.4	680.8	683.4
57.5°	946.5	826.7	706.9	732.0	805.4	791.0	688.5	612.9	617.3	621.8	617.3
60°	892.2	775.8	659.5	662.7	705.8	692.0	621.3	567.0	561.8	556.7	561.8
62.5°	834.8	723.9	613.1	597.0	612.5	596.3	548.4	511.1	506.0	500.8	506.0
65°	740.9	640.1	539.2	508.8	501.9	478.6	439.0	409.2	409.2	409.2	409.2
67.5°	637.7	549.8	461.9	427.9	411.8	388.7	358.6	330.8	310.1	289.4	310.1
70°	566.4	488.8	411.2	375.6	354.1	326.5	292.9	264.2	250.4	236.6	250.4
72.5°	490.3	423.8	357.2	320.8	294.4	267.5	240.1	215.6	199.7	183.9	199.7
75°	382.1	328.6	275.2	239.9	210.6	183.4	158.4	139.2	137.5	135.8	137.5
77.5°	276.2	237.2	198.3	169.6	144.5	125.6	113.0	103.6	103.8	104.0	103.8
80°	209.5	180.2	150.9	124.1	98.3	84.9	84.0	83.6	84.5	85.3	84.5
82.5°	147.4	125.7	104.0	86.9	71.4	64.2	65.4	66.4	66.5	66.7	66.5
85°	65.9	55.6	45.3	41.4	39.7	37.1	33.6	30.8	30.0	29.1	30.0
87.5°	15.2	16.1	17.4	17.3	16.4	15.8	15.8	16.2	16.6	16.6	16.6
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	1988.5	1995.0	2003.3	2018.1	2039.5	2053.1	2043.5	2033.8	2043.5	2053.1	2039.5
5°	1859.6	1880.1	1906.8	1946.9	2000.3	2040.6	2041.5	2042.4	2041.5	2040.6	2000.3
7.5°	1736.0	1758.4	1787.9	1834.3	1897.5	1951.7	1978.4	2005.1	1978.4	1951.7	1897.5
10°	1668.0	1688.1	1714.8	1762.2	1830.3	1891.5	1932.0	1972.5	1932.0	1891.5	1830.3
12.5°	1624.1	1637.9	1657.7	1701.7	1769.8	1836.9	1900.8	1964.8	1900.8	1836.9	1769.8
15°	1585.1	1586.6	1591.7	1623.6	1682.2	1750.3	1846.9	1943.4	1846.9	1750.3	1682.2
17.5°	1564.9	1553.9	1542.8	1559.9	1605.1	1664.9	1768.9	1872.8	1768.9	1664.9	1605.1
20°	1552.3	1534.2	1513.5	1523.0	1562.6	1618.0	1720.6	1823.2	1720.6	1618.0	1562.6
22.5°	1530.9	1512.5	1489.7	1493.7	1524.4	1573.4	1677.3	1781.3	1677.3	1573.4	1524.4
25°	1487.0	1472.8	1452.9	1447.3	1456.0	1491.7	1609.0	1726.2	1609.0	1491.7	1456.0
27.5°	1435.3	1425.8	1413.8	1402.7	1392.5	1415.5	1537.9	1660.3	1537.9	1415.5	1392.5
30°	1405.1	1393.3	1381.2	1367.0	1350.6	1368.9	1491.3	1613.7	1491.3	1368.9	1350.6
32.5°	1410.3	1382.4	1353.8	1327.1	1302.5	1315.6	1442.2	1568.7	1442.2	1315.6	1302.5
35°	1413.7	1357.0	1309.6	1270.8	1240.7	1251.0	1382.9	1514.8	1382.9	1251.0	1240.7
37.5°	1330.7	1293.3	1252.4	1211.6	1170.7	1175.4	1316.8	1458.2	1316.8	1175.4	1170.7
40°	1297.6	1273.6	1221.1	1170.2	1121.1	1121.3	1269.6	1417.8	1269.6	1121.3	1121.1
42.5°	1266.7	1241.6	1173.1	1117.1	1073.5	1077.8	1226.1	1374.4	1226.1	1077.8	1073.5
45°	1082.9	1088.1	1070.0	1039.0	995.0	1000.6	1154.9	1309.2	1154.9	1000.6	995.0
47.5°	909.7	947.4	987.9	984.5	937.1	938.3	1085.3	1232.4	1085.3	938.3	937.1
50°	833.2	886.4	951.0	956.2	901.9	895.9	1034.7	1173.4	1034.7	895.9	901.9
52.5°	769.5	837.2	923.3	933.6	868.3	852.2	984.1	1116.0	984.1	852.2	868.3
55°	686.0	775.2	893.3	907.1	816.6	780.4	907.1	1033.8	907.1	780.4	816.6
57.5°	612.9	688.5	791.0	805.4	732.0	706.9	826.7	946.5	826.7	706.9	732.0
60°	567.0	621.3	692.0	705.8	662.7	659.5	775.8	892.2	775.8	659.5	662.7
62.5°	511.1	548.4	596.3	612.5	597.0	613.1	723.9	834.8	723.9	613.1	597.0
65°	409.2	439.0	478.6	501.9	508.8	539.2	640.1	740.9	640.1	539.2	508.8
67.5°	330.8	358.6	388.7	411.8	427.9	461.9	549.8	637.7	549.8	461.9	427.9
70°	264.2	292.9	326.5	354.1	375.6	411.2	488.8	566.4	488.8	411.2	375.6
72.5°	215.6	240.1	267.5	294.4	320.8	357.2	423.8	490.3	423.8	357.2	320.8
75°	139.2	158.4	183.4	210.6	239.9	275.2	328.6	382.1	328.6	275.2	239.9
77.5°	103.6	113.0	125.6	144.5	169.6	198.3	237.2	276.2	237.2	198.3	169.6
80°	83.6	84.0	84.9	98.3	124.1	150.9	180.2	209.5	180.2	150.9	124.1
82.5°	66.4	65.4	64.2	71.4	86.9	104.0	125.7	147.4	125.7	104.0	86.9
85°	30.8	33.6	37.1	39.7	41.4	45.3	55.6	65.9	55.6	45.3	41.4
87.5°	16.2	15.8	15.8	16.4	17.3	17.4	16.1	15.2	16.1	17.0	18.1
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	2018.1	2003.3	1995.0	1988.5	1987.1	1985.7	1987.1	1988.5	1995.0	2003.3	2018.1
5°	1946.9	1906.8	1880.1	1859.6	1857.9	1856.2	1857.9	1859.6	1880.1	1906.8	1946.9
7.5°	1834.3	1787.9	1758.4	1736.0	1734.6	1733.2	1734.6	1736.0	1758.4	1787.9	1834.3
10°	1762.2	1714.8	1688.1	1668.0	1668.0	1668.0	1668.0	1668.0	1688.1	1714.8	1762.2
12.5°	1701.7	1657.7	1637.9	1624.1	1628.2	1632.3	1628.2	1624.1	1637.9	1657.7	1701.7
15°	1623.6	1591.7	1586.6	1585.1	1594.5	1604.0	1594.5	1585.1	1586.6	1591.7	1623.6
17.5°	1559.9	1542.8	1553.9	1564.9	1575.9	1587.0	1575.9	1564.9	1553.9	1542.8	1559.9
20°	1523.0	1513.5	1534.2	1552.3	1562.6	1573.0	1562.6	1552.3	1534.2	1513.5	1523.0
22.5°	1493.7	1489.7	1512.5	1530.9	1536.4	1542.0	1536.4	1530.9	1512.5	1489.7	1493.7
25°	1447.3	1452.9	1472.8	1487.0	1484.4	1481.8	1484.4	1487.0	1472.8	1452.9	1447.3
27.5°	1402.7	1413.8	1425.8	1435.3	1436.8	1438.4	1436.8	1435.3	1425.8	1413.8	1402.7
30°	1367.0	1381.2	1393.3	1405.1	1416.3	1427.5	1416.3	1405.1	1393.3	1381.2	1367.0
32.5°	1327.1	1353.8	1382.4	1410.3	1436.0	1461.7	1436.0	1410.3	1382.4	1353.8	1327.1
35°	1270.8	1309.6	1357.0	1413.7	1498.2	1582.7	1498.2	1413.7	1357.0	1309.6	1270.8
37.5°	1211.6	1252.4	1293.3	1330.7	1357.6	1384.5	1357.6	1330.7	1293.3	1252.4	1211.6
40°	1170.2	1221.1	1273.6	1297.6	1235.5	1173.4	1235.5	1297.6	1273.6	1221.1	1170.2
42.5°	1117.1	1173.1	1241.6	1266.7	1161.9	1057.1	1161.9	1266.7	1241.6	1173.1	1117.1
45°	1039.0	1070.0	1088.1	1082.9	1007.9	932.9	1007.9	1082.9	1088.1	1070.0	1039.0
47.5°	984.5	987.9	947.4	909.7	880.4	851.1	880.4	909.7	947.4	987.9	984.5
50°	956.2	951.0	886.4	833.2	814.2	795.2	814.2	833.2	886.4	951.0	956.2
52.5°	933.6	923.3	837.2	769.5	756.8	744.0	756.8	769.5	837.2	923.3	933.6
55°	907.1	893.3	775.2	686.0	683.4	680.8	683.4	686.0	775.2	893.3	907.1
57.5°	805.4	791.0	688.5	612.9	617.3	621.8	617.3	612.9	688.5	791.0	805.4
60°	705.8	692.0	621.3	567.0	561.8	556.7	561.8	567.0	621.3	692.0	705.8
62.5°	612.5	596.3	548.4	511.1	506.0	500.8	506.0	511.1	548.4	596.3	612.5
65°	501.9	478.6	439.0	409.2	409.2	409.2	409.2	409.2	439.0	478.6	501.9
67.5°	411.8	388.7	358.6	330.8	310.1	289.4	310.1	330.8	358.6	388.7	411.8
70°	354.1	326.5	292.9	264.2	250.4	236.6	250.4	264.2	292.9	326.5	354.1
72.5°	294.4	267.5	240.1	215.6	199.7	183.9	199.7	215.6	240.1	267.5	294.4
75°	210.6	183.4	158.4	139.2	137.5	135.8	137.5	139.2	158.4	183.4	210.6
77.5°	144.5	125.6	113.0	103.6	103.8	104.0	103.8	103.6	113.0	125.6	144.5
80°	98.3	84.9	84.0	83.6	84.5	85.3	84.5	83.6	84.0	84.9	98.3
82.5°	71.4	64.2	65.4	66.4	66.5	66.7	66.5	66.4	65.4	64.2	71.4
85°	39.7	37.1	33.6	30.8	30.0	29.1	30.0	30.8	33.6	37.1	39.7
87.5°	18.0	19.8	22.6	24.3	25.9	25.1	25.9	24.3	22.6	19.8	18.0
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2038.5	2038.5	2038.5	2038.5
2.5°	2039.5	2053.1	2043.5	2033.8
5°	2000.3	2040.6	2041.5	2042.4
7.5°	1897.5	1951.7	1978.4	2005.1
10°	1830.3	1891.5	1932.0	1972.5
12.5°	1769.8	1836.9	1900.8	1964.8
15°	1682.2	1750.3	1846.9	1943.4
17.5°	1605.1	1664.9	1768.9	1872.8
20°	1562.6	1618.0	1720.6	1823.2
22.5°	1524.4	1573.4	1677.3	1781.3
25°	1456.0	1491.7	1609.0	1726.2
27.5°	1392.5	1415.5	1537.9	1660.3
30°	1350.6	1368.9	1491.3	1613.7
32.5°	1302.5	1315.6	1442.2	1568.7
35°	1240.7	1251.0	1382.9	1514.8
37.5°	1170.7	1175.4	1316.8	1458.2
40°	1121.1	1121.3	1269.6	1417.8
42.5°	1073.5	1077.8	1226.1	1374.4
45°	995.0	1000.6	1154.9	1309.2
47.5°	937.1	938.3	1085.3	1232.4
50°	901.9	895.9	1034.7	1173.4
52.5°	868.3	852.2	984.1	1116.0
55°	816.6	780.4	907.1	1033.8
57.5°	732.0	706.9	826.7	946.5
60°	662.7	659.5	775.8	892.2
62.5°	597.0	613.1	723.9	834.8
65°	508.8	539.2	640.1	740.9
67.5°	427.9	461.9	549.8	637.7
70°	375.6	411.2	488.8	566.4
72.5°	320.8	357.2	423.8	490.3
75°	239.9	275.2	328.6	382.1
77.5°	169.6	198.3	237.2	276.2
80°	124.1	150.9	180.2	209.5
82.5°	86.9	104.0	125.7	147.4
85°	41.4	45.3	55.6	65.9
87.5°	18.1	17.0	16.1	15.2
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1427979

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427979
 CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.40	19.20	19.41	20.22	21.58	17.23	18.03	18.24	19.05	20.41
	3H	20.57	21.29	21.59	22.32	23.70	18.28	18.99	19.30	20.02	21.40
	4H	21.38	22.06	22.42	23.09	24.48	18.52	19.20	19.55	20.23	21.61
	6H	21.85	22.47	22.89	23.51	24.91	18.66	19.28	19.70	20.32	21.71
	8H	22.00	22.59	23.05	23.64	25.04	18.71	19.31	19.76	20.36	21.75
	12H	22.05	22.62	23.11	23.66	25.08	18.72	19.29	19.78	20.33	21.75
4H	2H	18.83	19.51	19.87	20.54	21.93	17.91	18.59	18.95	19.62	21.00
	3H	21.08	21.64	22.12	22.70	24.10	19.13	19.70	20.18	20.75	22.15
	4H	21.95	22.46	23.00	23.51	24.94	19.42	19.94	20.47	20.99	22.41
	6H	22.50	22.95	23.57	24.02	25.44	19.61	20.06	20.68	21.13	22.55
	8H	22.70	23.12	23.77	24.18	25.62	19.70	20.12	20.77	21.18	22.62
	12H	22.78	23.16	23.87	24.24	25.68	19.72	20.10	20.81	21.18	22.62
8H	4H	21.96	22.38	23.03	23.44	24.88	19.64	20.06	20.71	21.12	22.56
	6H	22.59	22.93	23.68	24.04	25.47	19.91	20.25	21.00	21.36	22.79
	8H	22.85	23.15	23.95	24.24	25.69	20.06	20.36	21.15	21.45	22.90
	12H	22.98	23.25	24.08	24.33	25.82	20.12	20.38	21.22	21.47	22.96
12H	4H	21.91	22.29	23.00	23.37	24.81	19.64	20.01	20.72	21.09	22.53
	6H	22.57	22.87	23.66	23.96	25.41	19.94	20.24	21.04	21.34	22.79
	8H	22.84	23.10	23.93	24.19	25.68	20.10	20.37	21.20	21.45	22.94