

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427928

Luminaire Tested: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427928
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9482.3 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46				
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	66	60	76	68	61	56	58	54	50	50	46	43	42	39	37	33				
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28				
5	69	58	49	43	64	54	47	41	47	41	37	40	36	32	34	30	28	25				
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	31	27	24	22				
7	59	47	39	33	55	44	37	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17				
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	15				
10	48	36	28	24	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	37246	37246	37246	37246
5°	37460	34045	37460	34045
10°	36596	30946	36596	30946
15°	36762	30341	36762	30341
20°	35449	30585	35449	30585
25°	34801	29873	34801	29873
30°	34046	30118	34046	30118
35°	33787	35303	33787	35303
40°	33817	27988	33817	27988
45°	33830	24107	33830	24107
50°	33354	22604	33354	22604
55°	32931	21686	32931	21686
60°	32604	20340	32604	20340
65°	32034	17692	32034	17692
70°	30255	12642	30255	12642
75°	26974	9582	26974	9582
80°	22045	8982	22045	8982
85°	13820	6095	13820	6095

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33830 cd/sqm



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	2.1
10°-20°	533.9	5.6
20°-30°	782.8	8.3
30°-40°	947.9	10.0
40°-50°	932.1	9.8
50°-60°	810.8	8.6
60°-70°	563.9	5.9
70°-80°	267.4	2.8
80°-90°	65.2	0.7
90°-100°	119.3	1.3
100°-110°	347.8	3.7
110°-120°	567.6	6.0
120°-130°	720.2	7.6
130°-140°	770.6	8.1
140°-150°	719.6	7.6
150°-160°	592.1	6.2
160°-170°	397.1	4.2
170°-180°	141.0	1.5
0°-30°	1519.7	16.0
0°-40°	2467.6	26.0
0°-60°	4210.4	44.4
0°-90°	5106.9	53.9
90°-120°	1034.6	10.9
90°-150°	3245.1	34.2
90°-180°	4375.0	46.1
0°-180°	9482.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2307	2307	2307	2307	2307	
5°	2311	2101	2311	2101	2311	217
15°	2199	1815	2199	1815	2199	613
25°	1954	1677	1954	1677	1954	898
35°	1714	1791	1714	1791	1714	1074
45°	1482	1056	1482	1056	1482	1139
55°	1170	770	1170	770	1170	1045
65°	838	463	838	463	838	824
75°	432	154	432	154	432	458
85°	75	33	75	33	75	100
90°	4	33	4	65	4	6
95°	47	35	47	204	47	57
105°	221	354	221	487	221	235
115°	424	587	424	724	424	418
125°	627	931	627	887	627	561
135°	852	1218	852	982	852	659
145°	1088	1405	1088	1004	1088	681
155°	1293	1526	1293	1041	1293	594
165°	1429	1591	1429	1199	1429	402
175°	1494	1558	1494	1406	1494	142
180°	1498	1498	1498	1498	1498	



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9
2.5°	2301.6	2312.5	2323.5	2308.0	2283.9	2267.1	2257.7	2250.3	2248.7	2247.2	2248.7
5°	2311.3	2310.3	2309.3	2263.7	2203.2	2157.9	2127.6	2104.5	2102.5	2100.6	2102.5
7.5°	2269.1	2238.9	2208.6	2147.4	2075.8	2023.3	1989.9	1964.5	1963.0	1961.4	1963.0
10°	2232.2	2186.4	2140.5	2071.3	1994.2	1940.6	1910.3	1887.6	1887.6	1887.6	1887.6
12.5°	2223.5	2151.1	2078.7	2002.8	1925.7	1876.0	1853.5	1837.9	1842.6	1847.3	1842.6
15°	2199.3	2090.1	1980.8	1903.7	1837.4	1801.3	1795.5	1793.7	1804.5	1815.2	1804.5
17.5°	2119.4	2001.8	1884.1	1816.4	1765.3	1745.9	1758.4	1770.9	1783.4	1795.9	1783.4
20°	2063.2	1947.2	1831.1	1768.4	1723.5	1712.8	1736.2	1756.7	1768.4	1780.1	1768.4
22.5°	2015.8	1898.2	1780.5	1725.1	1690.3	1685.9	1711.6	1732.5	1738.7	1745.0	1738.7
25°	1953.5	1820.8	1688.1	1647.7	1637.9	1644.3	1666.7	1682.8	1679.9	1676.9	1679.9
27.5°	1878.9	1740.3	1601.8	1575.8	1587.3	1599.9	1613.6	1624.3	1626.0	1627.8	1626.0
30°	1826.2	1687.7	1549.1	1528.4	1546.9	1563.0	1576.7	1590.1	1602.8	1615.5	1602.8
32.5°	1775.3	1632.1	1488.8	1474.0	1501.9	1532.0	1564.4	1596.0	1625.0	1654.1	1625.0
35°	1714.2	1565.0	1415.7	1404.0	1438.2	1482.1	1535.7	1599.9	1695.5	1791.1	1695.5
37.5°	1650.2	1490.2	1330.2	1324.9	1371.1	1417.3	1463.6	1505.9	1536.3	1566.7	1536.3
40°	1604.5	1436.7	1268.9	1268.7	1324.3	1381.8	1441.3	1468.4	1398.2	1327.9	1398.2
42.5°	1555.3	1387.5	1219.7	1214.8	1264.2	1327.6	1405.1	1433.5	1314.9	1196.2	1314.9
45°	1481.6	1307.0	1132.3	1126.0	1175.8	1210.9	1231.4	1225.5	1140.6	1055.8	1140.6
47.5°	1394.7	1228.2	1061.8	1060.4	1114.1	1118.0	1072.2	1029.5	996.3	963.1	996.3
50°	1327.9	1170.9	1013.8	1020.6	1082.1	1076.2	1003.1	942.8	921.4	899.9	921.4
52.5°	1263.0	1113.7	964.5	982.6	1056.5	1044.8	947.5	870.9	856.4	842.0	856.4
55°	1169.9	1026.5	883.1	924.1	1026.5	1010.9	877.2	776.3	773.3	770.4	773.3
57.5°	1071.1	935.5	799.9	828.4	911.5	895.1	779.2	693.6	698.6	703.7	698.6
60°	1009.7	878.0	746.3	749.9	798.7	783.1	703.1	641.7	635.8	629.9	635.8
62.5°	944.7	819.2	693.8	675.6	693.2	674.8	620.6	578.4	572.6	566.7	572.6
65°	838.5	724.3	610.2	575.8	568.0	541.7	496.8	463.1	463.1	463.1	463.1
67.5°	721.7	622.2	522.7	484.2	466.1	439.9	405.8	374.3	350.9	327.5	350.9
70°	640.9	553.1	465.3	425.1	400.7	369.5	331.4	299.0	283.4	267.8	283.4
72.5°	554.9	479.6	404.3	363.0	333.2	302.8	271.7	244.0	226.0	208.1	226.0
75°	432.4	371.9	311.4	271.4	238.3	207.5	179.3	157.5	155.6	153.6	155.6
77.5°	312.6	268.5	224.4	192.0	163.5	142.1	127.9	117.3	117.5	117.6	117.5
80°	237.1	203.9	170.7	140.5	111.2	96.1	95.1	94.6	95.6	96.6	95.6
82.5°	166.8	142.2	117.6	98.3	80.8	72.7	74.0	75.1	75.3	75.5	75.3
85°	74.6	62.9	51.2	46.8	44.9	41.9	38.0	34.9	33.9	32.9	33.9
87.5°	16.7	17.1	17.9	17.1	15.7	14.8	14.8	15.1	15.4	15.4	15.4
90°	4.5	10.6	18.2	24.2	28.8	30.3	30.3	31.8	33.3	33.3	33.3
92.5°	16.7	26.3	26.6	26.6	32.4	35.1	37.5	37.8	39.4	39.4	39.4
95°	46.9	51.5	77.2	75.7	51.5	40.9	34.8	34.8	34.8	34.8	34.8
97.5°	89.6	96.3	100.5	134.7	142.3	137.4	112.0	94.1	84.2	79.6	84.2
100°	127.1	130.2	139.3	140.8	178.6	214.9	196.8	174.1	166.5	162.0	166.5
102.5°	164.7	166.5	180.4	186.8	195.6	216.1	279.1	272.2	267.0	266.1	267.0
105°	221.0	222.5	248.2	260.3	266.4	266.4	264.9	295.2	343.6	354.2	343.6
107.5°	281.2	288.2	318.5	350.9	357.8	359.6	351.8	347.2	345.4	346.6	345.4
110°	322.4	333.0	369.3	410.2	420.8	423.8	420.8	416.3	413.2	413.2	413.2



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	362.4	377.8	419.0	465.9	483.8	492.8	486.2	482.9	479.8	482.2	479.8
115°	423.8	446.5	501.0	549.5	585.8	590.3	588.8	588.8	587.3	587.3	587.3
117.5°	480.7	517.1	578.2	634.5	676.6	688.7	694.8	692.9	691.1	694.2	691.1
120°	520.7	563.1	632.7	696.3	737.1	755.3	761.4	758.3	761.4	758.3	761.4
122.5°	563.1	615.1	683.6	749.6	797.7	818.3	825.5	826.2	826.8	824.9	826.8
125°	626.7	690.2	770.4	838.6	888.5	912.7	918.8	920.3	923.3	930.9	923.3
127.5°	690.8	762.9	851.0	916.7	967.8	997.2	1006.6	1009.9	1016.3	1019.6	1016.3
130°	735.6	817.4	906.7	968.7	1018.7	1050.5	1067.1	1071.7	1079.2	1077.7	1079.2
132.5°	782.9	868.2	958.7	1023.2	1069.5	1103.8	1118.0	1131.0	1133.7	1135.8	1133.7
135°	852.2	944.5	1035.3	1098.9	1142.8	1176.1	1194.3	1206.4	1213.9	1218.5	1213.9
137.5°	925.1	1022.6	1109.8	1166.4	1210.6	1239.4	1260.0	1272.7	1280.5	1284.2	1280.5
140°	974.8	1068.6	1153.4	1212.4	1251.8	1280.5	1298.7	1313.8	1322.9	1322.9	1322.9
142.5°	1022.0	1114.7	1197.0	1256.0	1290.5	1316.9	1336.3	1347.8	1358.0	1358.0	1358.0
145°	1088.3	1180.6	1256.3	1315.4	1344.1	1368.3	1389.5	1398.6	1404.7	1404.7	1404.7
147.5°	1157.6	1239.4	1308.4	1365.0	1389.2	1417.7	1434.3	1441.6	1449.2	1445.8	1449.2
150°	1198.8	1274.5	1341.1	1394.1	1418.3	1445.5	1462.2	1468.2	1475.8	1471.3	1475.8
152.5°	1238.8	1310.8	1371.4	1420.7	1441.3	1468.5	1487.6	1493.7	1498.8	1495.5	1498.8
155°	1292.7	1356.2	1412.2	1457.6	1475.8	1501.5	1519.7	1527.3	1533.3	1525.8	1533.3
157.5°	1340.8	1395.6	1444.3	1486.1	1505.5	1527.6	1544.5	1553.9	1560.0	1556.6	1560.0
160°	1369.9	1419.8	1463.7	1503.1	1521.2	1540.9	1559.1	1569.7	1575.7	1571.2	1575.7
162.5°	1394.1	1439.2	1480.7	1516.4	1532.1	1549.4	1571.2	1580.6	1586.6	1580.9	1586.6
165°	1428.9	1465.2	1501.5	1531.8	1545.4	1559.1	1581.8	1592.4	1596.9	1590.8	1596.9
167.5°	1455.2	1483.1	1512.4	1538.5	1548.5	1561.8	1584.5	1593.3	1599.0	1591.5	1599.0
170°	1469.8	1494.0	1519.7	1540.9	1548.5	1560.6	1583.3	1590.8	1595.4	1587.8	1595.4
172.5°	1481.9	1500.0	1520.9	1539.7	1543.6	1553.3	1574.8	1582.4	1585.7	1579.3	1585.7
175°	1494.0	1504.6	1519.7	1531.8	1530.3	1536.4	1554.5	1560.6	1566.6	1557.5	1566.6
177.5°	1499.7	1504.6	1509.4	1516.7	1511.8	1511.8	1525.2	1528.8	1530.0	1525.2	1530.0
180°	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9
2.5°	2250.3	2257.7	2267.1	2283.9	2308.0	2323.5	2312.5	2301.6	2312.5	2323.5	2308.0
5°	2104.5	2127.6	2157.9	2203.2	2263.7	2309.3	2310.3	2311.3	2310.3	2309.3	2263.7
7.5°	1964.5	1989.9	2023.3	2075.8	2147.4	2208.6	2238.9	2269.1	2238.9	2208.6	2147.4
10°	1887.6	1910.3	1940.6	1994.2	2071.3	2140.5	2186.4	2232.2	2186.4	2140.5	2071.3
12.5°	1837.9	1853.5	1876.0	1925.7	2002.8	2078.7	2151.1	2223.5	2151.1	2078.7	2002.8
15°	1793.7	1795.5	1801.3	1837.4	1903.7	1980.8	2090.1	2199.3	2090.1	1980.8	1903.7
17.5°	1770.9	1758.4	1745.9	1765.3	1816.4	1884.1	2001.8	2119.4	2001.8	1884.1	1816.4
20°	1756.7	1736.2	1712.8	1723.5	1768.4	1831.1	1947.2	2063.2	1947.2	1831.1	1768.4
22.5°	1732.5	1711.6	1685.9	1690.3	1725.1	1780.5	1898.2	2015.8	1898.2	1780.5	1725.1
25°	1682.8	1666.7	1644.3	1637.9	1647.7	1688.1	1820.8	1953.5	1820.8	1688.1	1647.7
27.5°	1624.3	1613.6	1599.9	1587.3	1575.8	1601.8	1740.3	1878.9	1740.3	1601.8	1575.8
30°	1590.1	1576.7	1563.0	1546.9	1528.4	1549.1	1687.7	1826.2	1687.7	1549.1	1528.4
32.5°	1596.0	1564.4	1532.0	1501.9	1474.0	1488.8	1632.1	1775.3	1632.1	1488.8	1474.0
35°	1599.9	1535.7	1482.1	1438.2	1404.0	1415.7	1565.0	1714.2	1565.0	1415.7	1404.0
37.5°	1505.9	1463.6	1417.3	1371.1	1324.9	1330.2	1490.2	1650.2	1490.2	1330.2	1324.9
40°	1468.4	1441.3	1381.8	1324.3	1268.7	1268.9	1436.7	1604.5	1436.7	1268.9	1268.7
42.5°	1433.5	1405.1	1327.6	1264.2	1214.8	1219.7	1387.5	1555.3	1387.5	1219.7	1214.8
45°	1225.5	1231.4	1210.9	1175.8	1126.0	1132.3	1307.0	1481.6	1307.0	1132.3	1126.0
47.5°	1029.5	1072.2	1118.0	1114.1	1060.4	1061.8	1228.2	1394.7	1228.2	1061.8	1060.4
50°	942.8	1003.1	1076.2	1082.1	1020.6	1013.8	1170.9	1327.9	1170.9	1013.8	1020.6
52.5°	870.9	947.5	1044.8	1056.5	982.6	964.5	1113.7	1263.0	1113.7	964.5	982.6
55°	776.3	877.2	1010.9	1026.5	924.1	883.1	1026.5	1169.9	1026.5	883.1	924.1
57.5°	693.6	779.2	895.1	911.5	828.4	799.9	935.5	1071.1	935.5	799.9	828.4
60°	641.7	703.1	783.1	798.7	749.9	746.3	878.0	1009.7	878.0	746.3	749.9
62.5°	578.4	620.6	674.8	693.2	675.6	693.8	819.2	944.7	819.2	693.8	675.6
65°	463.1	496.8	541.7	568.0	575.8	610.2	724.3	838.5	724.3	610.2	575.8
67.5°	374.3	405.8	439.9	466.1	484.2	522.7	622.2	721.7	622.2	522.7	484.2
70°	299.0	331.4	369.5	400.7	425.1	465.3	553.1	640.9	553.1	465.3	425.1
72.5°	244.0	271.7	302.8	333.2	363.0	404.3	479.6	554.9	479.6	404.3	363.0
75°	157.5	179.3	207.5	238.3	271.4	311.4	371.9	432.4	371.9	311.4	271.4
77.5°	117.3	127.9	142.1	163.5	192.0	224.4	268.5	312.6	268.5	224.4	192.0
80°	94.6	95.1	96.1	111.2	140.5	170.7	203.9	237.1	203.9	170.7	140.5
82.5°	75.1	74.0	72.7	80.8	98.3	117.6	142.2	166.8	142.2	117.6	98.3
85°	34.9	38.0	41.9	44.9	46.8	51.2	62.9	74.6	62.9	51.2	46.8
87.5°	15.1	14.8	14.8	15.7	17.1	17.9	17.1	16.7	17.1	17.6	17.7
90°	31.8	30.3	30.3	28.8	24.2	18.2	10.6	4.5	10.6	16.7	27.2
92.5°	37.8	37.5	35.1	32.4	26.6	26.6	26.3	16.7	28.8	40.9	58.7
95°	34.8	34.8	40.9	51.5	75.7	77.2	51.5	46.9	66.6	93.8	118.1
97.5°	94.1	112.0	137.4	142.3	134.7	100.5	96.3	89.6	122.0	148.9	188.0
100°	174.1	196.8	214.9	178.6	140.8	139.3	130.2	127.1	162.0	187.7	225.5
102.5°	272.2	279.1	216.1	195.6	186.8	180.4	166.5	164.7	199.5	234.9	266.7
105°	295.2	264.9	266.4	266.4	260.3	248.2	222.5	221.0	260.3	301.2	340.6
107.5°	347.2	351.8	359.6	357.8	350.9	318.5	288.2	281.2	316.7	365.7	409.0
110°	416.3	420.8	423.8	420.8	410.2	369.3	333.0	322.4	354.2	405.7	452.6



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	482.9	486.2	492.8	483.8	465.9	419.0	377.8	362.4	394.2	446.8	495.0
115°	588.8	588.8	590.3	585.8	549.5	501.0	446.5	423.8	451.1	499.5	552.5
117.5°	692.9	694.8	688.7	676.6	634.5	578.2	517.1	480.7	502.2	553.4	607.9
120°	758.3	761.4	755.3	737.1	696.3	632.7	563.1	520.7	537.3	587.3	641.8
122.5°	826.2	825.5	818.3	797.7	749.6	683.6	615.1	563.1	570.0	616.4	669.6
125°	920.3	918.8	912.7	888.5	838.6	770.4	690.2	626.7	617.6	656.9	711.4
127.5°	1009.9	1006.6	997.2	967.8	916.7	851.0	762.9	690.8	670.5	695.4	745.3
130°	1071.7	1067.1	1050.5	1018.7	968.7	906.7	817.4	735.6	706.9	722.0	765.9
132.5°	1131.0	1118.0	1103.8	1069.5	1023.2	958.7	868.2	782.9	743.2	749.9	784.1
135°	1206.4	1194.3	1176.1	1142.8	1098.9	1035.3	944.5	852.2	797.7	791.6	811.3
137.5°	1272.7	1260.0	1239.4	1210.6	1166.4	1109.8	1022.6	925.1	856.4	836.1	843.7
140°	1313.8	1298.7	1280.5	1251.8	1212.4	1153.4	1068.6	974.8	897.6	868.8	864.3
142.5°	1347.8	1336.3	1316.9	1290.5	1256.0	1197.0	1114.7	1022.0	940.0	902.7	892.1
145°	1398.6	1389.5	1368.3	1344.1	1315.4	1256.3	1180.6	1088.3	1006.6	958.1	935.4
147.5°	1441.6	1434.3	1417.7	1389.2	1365.0	1308.4	1239.4	1157.6	1073.8	1013.8	984.5
150°	1468.2	1462.2	1445.5	1418.3	1394.1	1341.1	1274.5	1198.8	1118.6	1055.0	1017.2
152.5°	1493.7	1487.6	1468.5	1441.3	1420.7	1371.4	1310.8	1238.8	1157.3	1093.8	1054.7
155°	1527.3	1519.7	1501.5	1475.8	1457.6	1412.2	1356.2	1292.7	1223.0	1156.4	1112.5
157.5°	1553.9	1544.5	1527.6	1505.5	1486.1	1444.3	1395.6	1340.8	1279.9	1216.4	1171.6
160°	1569.7	1559.1	1540.9	1521.2	1503.1	1463.7	1419.8	1369.9	1313.8	1256.3	1207.9
162.5°	1580.6	1571.2	1549.4	1532.1	1516.4	1480.7	1439.2	1394.1	1344.1	1293.9	1249.1
165°	1592.4	1581.8	1559.1	1545.4	1531.8	1501.5	1465.2	1428.9	1386.5	1345.6	1309.3
167.5°	1593.3	1584.5	1561.8	1548.5	1538.5	1512.4	1483.1	1455.2	1422.2	1390.1	1359.9
170°	1590.8	1583.3	1560.6	1548.5	1540.9	1519.7	1494.0	1469.8	1444.0	1416.8	1392.6
172.5°	1582.4	1574.8	1553.3	1543.6	1539.7	1520.9	1500.0	1481.9	1459.8	1439.8	1420.4
175°	1560.6	1554.5	1536.4	1530.3	1531.8	1519.7	1504.6	1494.0	1480.4	1468.2	1457.6
177.5°	1528.8	1525.2	1511.8	1511.8	1516.7	1509.4	1504.6	1499.7	1493.7	1490.0	1486.4
180°	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9	2306.9
2.5°	2283.9	2267.1	2257.7	2250.3	2248.7	2247.2	2248.7	2250.3	2257.7	2267.1	2283.9
5°	2203.2	2157.9	2127.6	2104.5	2102.5	2100.6	2102.5	2104.5	2127.6	2157.9	2203.2
7.5°	2075.8	2023.3	1989.9	1964.5	1963.0	1961.4	1963.0	1964.5	1989.9	2023.3	2075.8
10°	1994.2	1940.6	1910.3	1887.6	1887.6	1887.6	1887.6	1887.6	1910.3	1940.6	1994.2
12.5°	1925.7	1876.0	1853.5	1837.9	1842.6	1847.3	1842.6	1837.9	1853.5	1876.0	1925.7
15°	1837.4	1801.3	1795.5	1793.7	1804.5	1815.2	1804.5	1793.7	1795.5	1801.3	1837.4
17.5°	1765.3	1745.9	1758.4	1770.9	1783.4	1795.9	1783.4	1770.9	1758.4	1745.9	1765.3
20°	1723.5	1712.8	1736.2	1756.7	1768.4	1780.1	1768.4	1756.7	1736.2	1712.8	1723.5
22.5°	1690.3	1685.9	1711.6	1732.5	1738.7	1745.0	1738.7	1732.5	1711.6	1685.9	1690.3
25°	1637.9	1644.3	1666.7	1682.8	1679.9	1676.9	1679.9	1682.8	1666.7	1644.3	1637.9
27.5°	1587.3	1599.9	1613.6	1624.3	1626.0	1627.8	1626.0	1624.3	1613.6	1599.9	1587.3
30°	1546.9	1563.0	1576.7	1590.1	1602.8	1615.5	1602.8	1590.1	1576.7	1563.0	1546.9
32.5°	1501.9	1532.0	1564.4	1596.0	1625.0	1654.1	1625.0	1596.0	1564.4	1532.0	1501.9
35°	1438.2	1482.1	1535.7	1599.9	1695.5	1791.1	1695.5	1599.9	1535.7	1482.1	1438.2
37.5°	1371.1	1417.3	1463.6	1505.9	1536.3	1566.7	1536.3	1505.9	1463.6	1417.3	1371.1
40°	1324.3	1381.8	1441.3	1468.4	1398.2	1327.9	1398.2	1468.4	1441.3	1381.8	1324.3
42.5°	1264.2	1327.6	1405.1	1433.5	1314.9	1196.2	1314.9	1433.5	1405.1	1327.6	1264.2
45°	1175.8	1210.9	1231.4	1225.5	1140.6	1055.8	1140.6	1225.5	1231.4	1210.9	1175.8
47.5°	1114.1	1118.0	1072.2	1029.5	996.3	963.1	996.3	1029.5	1072.2	1118.0	1114.1
50°	1082.1	1076.2	1003.1	942.8	921.4	899.9	921.4	942.8	1003.1	1076.2	1082.1
52.5°	1056.5	1044.8	947.5	870.9	856.4	842.0	856.4	870.9	947.5	1044.8	1056.5
55°	1026.5	1010.9	877.2	776.3	773.3	770.4	773.3	776.3	877.2	1010.9	1026.5
57.5°	911.5	895.1	779.2	693.6	698.6	703.7	698.6	693.6	779.2	895.1	911.5
60°	798.7	783.1	703.1	641.7	635.8	629.9	635.8	641.7	703.1	783.1	798.7
62.5°	693.2	674.8	620.6	578.4	572.6	566.7	572.6	578.4	620.6	674.8	693.2
65°	568.0	541.7	496.8	463.1	463.1	463.1	463.1	496.8	541.7	568.0	568.0
67.5°	466.1	439.9	405.8	374.3	350.9	327.5	350.9	374.3	405.8	439.9	466.1
70°	400.7	369.5	331.4	299.0	283.4	267.8	283.4	299.0	331.4	369.5	400.7
72.5°	333.2	302.8	271.7	244.0	226.0	208.1	226.0	244.0	271.7	302.8	333.2
75°	238.3	207.5	179.3	157.5	155.6	153.6	155.6	157.5	179.3	207.5	238.3
77.5°	163.5	142.1	127.9	117.3	117.5	117.6	117.5	117.3	127.9	142.1	163.5
80°	111.2	96.1	95.1	94.6	95.6	96.6	95.6	94.6	95.1	96.1	111.2
82.5°	80.8	72.7	74.0	75.1	75.3	75.5	75.3	75.1	74.0	72.7	80.8
85°	44.9	41.9	38.0	34.9	33.9	32.9	33.9	34.9	38.0	41.9	44.9
87.5°	16.9	17.9	20.0	21.2	22.4	21.8	22.4	21.2	20.0	17.9	16.9
90°	34.8	45.4	56.0	62.1	68.1	65.1	68.1	62.1	56.0	45.4	34.8
92.5°	69.9	87.8	100.8	111.7	116.6	115.9	116.6	111.7	100.8	87.8	69.9
95°	140.8	162.0	183.2	198.3	207.4	204.3	207.4	198.3	162.0	140.8	140.8
97.5°	217.1	245.5	269.1	283.4	292.4	298.5	292.4	283.4	269.1	245.5	217.1
100°	267.9	295.2	322.4	339.1	354.2	360.2	354.2	339.1	322.4	295.2	267.9
102.5°	309.1	344.8	374.5	392.3	405.1	411.1	405.1	392.3	374.5	344.8	309.1
105°	376.9	414.7	446.5	469.2	482.9	487.4	482.9	469.2	446.5	414.7	376.9
107.5°	444.7	483.8	513.1	538.3	554.9	564.6	554.9	538.3	513.1	483.8	444.7
110°	498.0	529.8	561.6	584.3	600.9	607.0	600.9	584.3	561.6	529.8	498.0



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	542.8	578.2	610.0	632.7	651.8	660.3	651.8	632.7	610.0	578.2	542.8
115°	605.5	652.4	681.1	702.3	716.0	723.5	716.0	702.3	681.1	652.4	605.5
117.5°	657.5	706.6	738.1	754.4	760.8	766.2	760.8	754.4	738.1	706.6	657.5
120°	690.2	735.6	772.0	793.2	800.7	803.7	800.7	793.2	772.0	735.6	690.2
122.5°	720.5	763.5	798.6	824.6	837.0	840.1	837.0	824.6	798.6	763.5	720.5
125°	762.9	803.7	840.1	865.8	879.4	887.0	879.4	865.8	840.1	803.7	762.9
127.5°	799.8	844.0	877.3	900.6	913.9	920.0	913.9	900.6	877.3	844.0	799.8
130°	820.4	865.8	899.1	924.8	937.0	943.0	937.0	924.8	899.1	865.8	820.4
132.5°	836.1	884.0	918.5	941.8	955.1	961.2	955.1	941.8	918.5	884.0	836.1
135°	855.2	905.2	941.5	964.2	976.3	982.4	976.3	964.2	941.5	905.2	855.2
137.5°	871.9	917.3	955.1	979.0	989.9	993.9	989.9	979.0	955.1	917.3	871.9
140°	884.0	923.3	961.2	983.9	996.0	997.5	996.0	983.9	961.2	923.3	884.0
142.5°	899.7	930.6	963.6	986.3	998.4	1001.1	998.4	986.3	963.6	930.6	899.7
145°	927.9	946.0	968.7	989.9	1000.5	1003.6	1000.5	989.9	968.7	946.0	927.9
147.5°	963.3	969.0	980.8	994.8	1005.1	1007.2	1005.1	994.8	980.8	969.0	963.3
150°	989.9	988.4	993.0	1002.0	1011.1	1009.6	1011.1	1002.0	993.0	988.4	989.9
152.5°	1020.2	1011.4	1011.1	1015.4	1019.6	1019.3	1019.6	1015.4	1011.1	1011.4	1020.2
155°	1071.7	1055.0	1045.9	1042.9	1042.9	1041.4	1042.9	1042.9	1045.9	1055.0	1071.7
157.5°	1128.3	1105.0	1091.3	1084.1	1082.0	1078.6	1082.0	1084.1	1091.3	1105.0	1128.3
160°	1167.0	1141.3	1127.7	1115.6	1111.0	1106.5	1111.0	1115.6	1127.7	1141.3	1167.0
162.5°	1203.4	1178.8	1164.0	1153.1	1148.6	1141.6	1148.6	1153.1	1164.0	1178.8	1203.4
165°	1262.4	1236.7	1220.0	1210.9	1204.9	1198.8	1204.9	1210.9	1220.0	1236.7	1262.4
167.5°	1321.4	1293.3	1282.4	1272.1	1266.3	1255.4	1266.3	1272.1	1282.4	1293.3	1321.4
170°	1357.7	1332.0	1326.0	1316.9	1306.3	1294.2	1306.3	1316.9	1326.0	1332.0	1357.7
172.5°	1389.2	1372.0	1365.9	1356.8	1353.5	1343.8	1353.5	1356.8	1365.9	1372.0	1389.2
175°	1434.9	1421.3	1421.3	1419.8	1415.3	1406.2	1415.3	1419.8	1421.3	1421.3	1434.9
177.5°	1473.1	1465.8	1470.7	1470.7	1469.5	1461.0	1469.5	1470.7	1470.7	1465.8	1473.1
180°	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2306.9	2306.9	2306.9	2306.9
2.5°	2308.0	2323.5	2312.5	2301.6
5°	2263.7	2309.3	2310.3	2311.3
7.5°	2147.4	2208.6	2238.9	2269.1
10°	2071.3	2140.5	2186.4	2232.2
12.5°	2002.8	2078.7	2151.1	2223.5
15°	1903.7	1980.8	2090.1	2199.3
17.5°	1816.4	1884.1	2001.8	2119.4
20°	1768.4	1831.1	1947.2	2063.2
22.5°	1725.1	1780.5	1898.2	2015.8
25°	1647.7	1688.1	1820.8	1953.5
27.5°	1575.8	1601.8	1740.3	1878.9
30°	1528.4	1549.1	1687.7	1826.2
32.5°	1474.0	1488.8	1632.1	1775.3
35°	1404.0	1415.7	1565.0	1714.2
37.5°	1324.9	1330.2	1490.2	1650.2
40°	1268.7	1268.9	1436.7	1604.5
42.5°	1214.8	1219.7	1387.5	1555.3
45°	1126.0	1132.3	1307.0	1481.6
47.5°	1060.4	1061.8	1228.2	1394.7
50°	1020.6	1013.8	1170.9	1327.9
52.5°	982.6	964.5	1113.7	1263.0
55°	924.1	883.1	1026.5	1169.9
57.5°	828.4	799.9	935.5	1071.1
60°	749.9	746.3	878.0	1009.7
62.5°	675.6	693.8	819.2	944.7
65°	575.8	610.2	724.3	838.5
67.5°	484.2	522.7	622.2	721.7
70°	425.1	465.3	553.1	640.9
72.5°	363.0	404.3	479.6	554.9
75°	271.4	311.4	371.9	432.4
77.5°	192.0	224.4	268.5	312.6
80°	140.5	170.7	203.9	237.1
82.5°	98.3	117.6	142.2	166.8
85°	46.8	51.2	62.9	74.6
87.5°	17.7	17.6	17.1	16.7
90°	27.2	16.7	10.6	4.5
92.5°	58.7	40.9	28.8	16.7
95°	118.1	93.8	66.6	46.9
97.5°	188.0	148.9	122.0	89.6
100°	225.5	187.7	162.0	127.1
102.5°	266.7	234.9	199.5	164.7
105°	340.6	301.2	260.3	221.0
107.5°	409.0	365.7	316.7	281.2
110°	452.6	405.7	354.2	322.4



TEST NUMBER: P1427928

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	495.0	446.8	394.2	362.4
115°	552.5	499.5	451.1	423.8
117.5°	607.9	553.4	502.2	480.7
120°	641.8	587.3	537.3	520.7
122.5°	669.6	616.4	570.0	563.1
125°	711.4	656.9	617.6	626.7
127.5°	745.3	695.4	670.5	690.8
130°	765.9	722.0	706.9	735.6
132.5°	784.1	749.9	743.2	782.9
135°	811.3	791.6	797.7	852.2
137.5°	843.7	836.1	856.4	925.1
140°	864.3	868.8	897.6	974.8
142.5°	892.1	902.7	940.0	1022.0
145°	935.4	958.1	1006.6	1088.3
147.5°	984.5	1013.8	1073.8	1157.6
150°	1017.2	1055.0	1118.6	1198.8
152.5°	1054.7	1093.8	1157.3	1238.8
155°	1112.5	1156.4	1223.0	1292.7
157.5°	1171.6	1216.4	1279.9	1340.8
160°	1207.9	1256.3	1313.8	1369.9
162.5°	1249.1	1293.9	1344.1	1394.1
165°	1309.3	1345.6	1386.5	1428.9
167.5°	1359.9	1390.1	1422.2	1455.2
170°	1392.6	1416.8	1444.0	1469.8
172.5°	1420.4	1439.8	1459.8	1481.9
175°	1457.6	1468.2	1480.4	1494.0
177.5°	1486.4	1490.0	1493.7	1499.7
180°	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1427928
 CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.79	20.68	20.72	21.63	22.84	18.62	19.51	19.55	20.45	21.67
	3H	21.97	22.77	22.91	23.72	24.96	19.68	20.47	20.61	21.42	22.66
	4H	22.79	23.54	23.74	24.49	25.74	19.92	20.67	20.87	21.63	22.88
	6H	23.25	23.95	24.22	24.91	26.17	20.06	20.76	21.03	21.72	22.98
	8H	23.41	24.07	24.38	25.05	26.30	20.12	20.78	21.09	21.76	23.02
	12H	23.47	24.09	24.44	25.07	26.35	20.14	20.76	21.11	21.74	23.02
4H	2H	20.23	20.99	21.19	21.94	23.19	19.31	20.06	20.27	21.02	22.27
	3H	22.49	23.11	23.45	24.10	25.36	20.54	21.17	21.51	22.16	23.42
	4H	23.36	23.93	24.34	24.91	26.20	20.84	21.41	21.81	22.39	23.67
	6H	23.92	24.41	24.91	25.42	26.70	21.04	21.53	22.02	22.53	23.82
	8H	24.13	24.58	25.12	25.58	26.88	21.13	21.59	22.12	22.58	23.88
	12H	24.21	24.63	25.22	25.64	26.94	21.15	21.57	22.16	22.58	23.88
8H	4H	23.39	23.85	24.38	24.84	26.14	21.07	21.53	22.06	22.52	23.82
	6H	24.02	24.40	25.03	25.43	26.73	21.34	21.71	22.35	22.75	24.05
	8H	24.28	24.61	25.30	25.64	26.96	21.48	21.82	22.51	22.84	24.16
	12H	24.41	24.71	25.44	25.73	27.09	21.55	21.84	22.58	22.86	24.22
12H	4H	23.34	23.75	24.35	24.77	26.07	21.06	21.48	22.07	22.49	23.80
	6H	23.99	24.33	25.02	25.35	26.67	21.37	21.71	22.40	22.73	24.05
	8H	24.27	24.56	25.29	25.58	26.94	21.54	21.83	22.56	22.85	24.21