

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428183

Luminaire Tested: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428183
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3329.5 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71				
1	103	99	96	92	98	94	91	88	85	82	80	76	74	73	68	67	65	62				
2	95	88	82	77	90	83	78	74	75	71	68	68	65	62	61	59	56	53				
3	87	78	71	65	82	74	68	63	67	62	58	61	57	53	55	52	49	46				
4	80	70	62	56	76	66	59	54	60	55	50	55	50	46	49	46	43	40				
5	74	62	54	48	70	60	52	47	54	48	44	49	45	41	45	41	38	35				
6	68	56	48	43	65	54	47	41	49	43	39	45	40	36	41	37	34	31				
7	63	51	43	38	60	49	42	37	45	39	34	41	36	32	37	33	30	28				
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25				
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23				
10	52	39	32	27	49	38	31	27	35	29	25	32	27	24	30	25	22	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15839	15839	15839	15839
5°	15818	16110	15818	16110
10°	15985	16641	15985	16641
15°	15980	16197	15980	16197
20°	15721	16494	15721	16494
25°	15677	17173	15677	17173
30°	15660	17338	15660	17338
35°	15512	16143	15512	16143
40°	15154	14206	15154	14206
45°	14339	11234	14339	11234
50°	13036	8716	13036	8716
55°	11457	6784	11457	6784
60°	9913	5586	9913	5586
65°	8558	4890	8558	4890
70°	7695	4343	7695	4343
75°	7049	3992	7049	3992
80°	6137	3905	6137	3905
85°	4446	1852	4446	1852

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 15394 cd/sqm



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	2.8
10°-20°	274.3	8.2
20°-30°	423.9	12.7
30°-40°	509.8	15.3
40°-50°	457.8	13.8
50°-60°	306.8	9.2
60°-70°	178.5	5.4
70°-80°	91.7	2.8
80°-90°	24.0	0.7
90°-100°	26.4	0.8
100°-110°	76.9	2.3
110°-120°	125.6	3.8
120°-130°	159.3	4.8
130°-140°	170.5	5.1
140°-150°	159.2	4.8
150°-160°	131.0	3.9
160°-170°	87.9	2.6
170°-180°	31.2	0.9
0°-30°	792.9	23.8
0°-40°	1302.8	39.1
0°-60°	2067.4	62.1
0°-90°	2361.5	70.9
90°-120°	228.9	6.9
90°-150°	717.9	21.6
90°-180°	968.0	29.1
0°-180°	3329.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	976	994	976	994	976	93
15°	956	969	956	969	956	268
25°	880	964	880	964	880	406
35°	787	819	787	819	787	491
45°	628	492	628	492	628	480
55°	407	241	407	241	407	366
65°	224	128	224	128	224	227
75°	113	64	113	64	113	120
85°	24	10	24	10	24	30
90°	1	7	1	14	1	2
95°	10	8	10	45	10	13
105°	49	78	49	108	49	52
115°	94	130	94	160	94	92
125°	139	206	139	196	139	124
135°	188	270	188	217	188	146
145°	241	311	241	222	241	151
155°	286	338	286	230	286	131
165°	316	352	316	265	316	89
175°	330	345	330	311	330	31
180°	332	332	332	332	332	



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0
2.5°	977.0	982.3	987.7	985.3	980.3	978.0	978.3	978.9	979.9	981.0	979.9
5°	976.0	983.6	991.1	989.3	984.5	982.5	983.3	985.1	989.6	994.0	989.6
7.5°	975.8	986.6	997.3	998.1	995.7	995.7	998.3	1001.7	1007.5	1013.4	1007.5
10°	975.0	987.9	1000.8	1002.7	1000.9	1000.2	1000.7	1002.6	1008.8	1015.0	1008.8
12.5°	970.2	985.2	1000.3	998.7	991.6	987.7	987.1	987.5	990.8	994.2	990.8
15°	956.0	973.8	991.6	984.3	968.8	961.7	963.0	964.6	966.8	969.0	966.8
17.5°	931.0	949.6	968.2	961.7	946.8	941.8	946.6	951.3	955.7	960.0	955.7
20°	915.0	933.2	951.5	947.0	935.0	932.1	938.3	944.9	952.5	960.0	952.5
22.5°	900.6	918.8	937.1	934.2	924.3	923.8	932.5	941.6	952.0	962.4	952.0
25°	880.0	896.0	912.0	912.3	907.5	912.3	927.0	940.9	952.5	964.0	952.5
27.5°	858.4	867.8	877.3	883.5	888.6	901.1	920.9	937.8	945.9	954.0	945.9
30°	840.0	846.2	852.5	864.0	877.3	892.7	910.0	923.8	926.9	930.0	926.9
32.5°	820.0	823.7	827.5	843.7	864.2	879.0	888.1	894.0	890.0	886.0	890.0
35°	787.0	790.1	793.2	814.0	840.7	850.5	843.3	835.9	827.5	819.0	827.5
37.5°	747.8	754.2	760.6	777.5	798.0	797.8	777.0	759.0	749.3	739.6	749.3
40°	719.0	729.7	740.3	751.7	763.2	753.5	722.3	696.2	685.1	674.0	685.1
42.5°	683.8	700.9	717.9	720.5	718.2	697.2	657.5	624.4	610.8	597.2	610.8
45°	628.0	651.1	674.2	661.0	635.7	601.4	558.3	522.2	507.1	492.0	507.1
47.5°	562.2	585.9	609.7	584.7	543.6	503.8	465.3	432.9	418.7	404.6	418.7
50°	519.0	538.1	557.2	529.0	485.0	445.0	409.0	378.1	362.6	347.0	362.6
52.5°	475.0	488.8	502.6	474.6	432.7	393.8	357.8	327.3	313.1	299.0	313.1
55°	407.0	414.1	421.2	395.3	358.4	322.9	288.7	260.6	250.8	241.0	250.8
57.5°	344.6	349.1	353.7	329.1	294.9	263.3	234.2	210.6	203.4	196.2	203.4
60°	307.0	310.1	313.2	288.3	254.1	225.7	203.0	184.6	178.8	173.0	178.8
62.5°	272.6	275.0	277.4	253.4	220.6	195.2	177.1	162.5	158.2	153.8	158.2
65°	224.0	226.2	228.4	208.0	180.0	159.1	145.3	134.2	131.1	128.0	131.1
67.5°	185.4	186.6	187.7	170.9	148.0	131.2	120.3	111.5	108.5	105.6	108.5
70°	163.0	163.4	163.9	149.0	129.0	114.1	104.3	96.4	94.2	92.0	94.2
72.5°	143.0	142.4	141.8	128.5	111.0	98.2	90.2	83.8	82.3	80.8	82.3
75°	113.0	111.7	110.3	99.3	85.1	75.3	70.0	65.8	64.9	64.0	64.9
77.5°	84.4	83.0	81.6	72.4	60.7	53.9	52.1	50.8	50.8	50.8	50.8
80°	66.0	64.2	62.4	55.3	46.4	42.0	42.0	42.0	42.0	42.0	42.0
82.5°	49.2	46.7	44.2	39.9	34.9	32.4	32.4	32.3	32.0	31.6	32.0
85°	24.0	21.8	19.6	19.0	19.0	17.7	15.0	12.7	11.3	10.0	11.3
87.5°	6.6	6.9	7.2	6.1	4.6	3.7	3.7	3.8	3.9	3.9	3.9
90°	1.0	2.3	4.0	5.4	6.4	6.7	6.7	7.0	7.4	7.4	7.4
92.5°	3.7	5.8	5.9	5.9	7.2	7.8	8.3	8.4	8.7	8.7	8.7
95°	10.4	11.4	17.1	16.7	11.4	9.0	7.7	7.7	7.7	7.7	7.7
97.5°	19.8	21.3	22.2	29.8	31.5	30.4	24.8	20.8	18.6	17.6	18.6
100°	28.1	28.8	30.8	31.1	39.5	47.6	43.5	38.5	36.8	35.8	36.8
102.5°	36.4	36.8	39.9	41.3	43.3	47.8	61.8	60.2	59.1	58.9	59.1
105°	48.9	49.2	54.9	57.6	58.9	58.9	58.6	65.3	76.0	78.4	76.0
107.5°	62.2	63.8	70.5	77.6	79.2	79.6	77.8	76.8	76.4	76.7	76.4
110°	71.3	73.7	81.7	90.8	93.1	93.8	93.1	92.1	91.4	91.4	91.4



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	80.2	83.6	92.7	103.1	107.0	109.0	107.6	106.8	106.2	106.7	106.2
115°	93.8	98.8	110.8	121.6	129.6	130.6	130.3	130.3	129.9	129.9	129.9
117.5°	106.4	114.4	127.9	140.4	149.7	152.4	153.7	153.3	152.9	153.6	152.9
120°	115.2	124.6	140.0	154.0	163.1	167.1	168.4	167.8	168.4	167.8	168.4
122.5°	124.6	136.1	151.2	165.8	176.5	181.0	182.6	182.8	182.9	182.5	182.9
125°	138.6	152.7	170.5	185.5	196.6	201.9	203.3	203.6	204.3	206.0	204.3
127.5°	152.8	168.8	188.3	202.8	214.1	220.6	222.7	223.4	224.8	225.6	224.8
130°	162.8	180.8	200.6	214.3	225.4	232.4	236.1	237.1	238.8	238.4	238.8
132.5°	173.2	192.1	212.1	226.4	236.6	244.2	247.3	250.2	250.8	251.3	250.8
135°	188.5	209.0	229.1	243.1	252.8	260.2	264.2	266.9	268.6	269.6	268.6
137.5°	204.7	226.2	245.5	258.1	267.8	274.2	278.8	281.6	283.3	284.1	283.3
140°	215.7	236.4	255.2	268.2	276.9	283.3	287.3	290.7	292.7	292.7	292.7
142.5°	226.1	246.6	264.8	277.9	285.5	291.3	295.6	298.2	300.5	300.5	300.5
145°	240.8	261.2	277.9	291.0	297.4	302.7	307.4	309.4	310.8	310.8	310.8
147.5°	256.1	274.2	289.5	302.0	307.4	313.6	317.3	318.9	320.6	319.9	320.6
150°	265.2	282.0	296.7	308.4	313.8	319.8	323.5	324.8	326.5	325.5	326.5
152.5°	274.1	290.0	303.4	314.3	318.9	324.9	329.1	330.5	331.6	330.9	331.6
155°	286.0	300.1	312.4	322.5	326.5	332.2	336.2	337.9	339.2	337.6	339.2
157.5°	296.6	308.8	319.5	328.8	333.1	338.0	341.7	343.8	345.1	344.4	345.1
160°	303.1	314.1	323.8	332.5	336.6	340.9	344.9	347.3	348.6	347.6	348.6
162.5°	308.4	318.4	327.6	335.5	339.0	342.8	347.6	349.7	351.0	349.7	351.0
165°	316.1	324.2	332.2	338.9	341.9	344.9	349.9	352.3	353.3	352.0	353.3
167.5°	322.0	328.1	334.6	340.4	342.6	345.5	350.6	352.5	353.8	352.1	353.8
170°	325.2	330.5	336.2	340.9	342.6	345.3	350.3	352.0	353.0	351.3	353.0
172.5°	327.8	331.9	336.5	340.6	341.5	343.7	348.4	350.1	350.8	349.4	350.8
175°	330.5	332.9	336.2	338.9	338.6	339.9	343.9	345.3	346.6	344.6	346.6
177.5°	331.8	332.9	333.9	335.5	334.5	334.5	337.4	338.2	338.5	337.4	338.5
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0
2.5°	978.9	978.3	978.0	980.3	985.3	987.7	982.3	977.0	982.3	987.7	985.3
5°	985.1	983.3	982.5	984.5	989.3	991.1	983.6	976.0	983.6	991.1	989.3
7.5°	1001.7	998.3	995.7	995.7	998.1	997.3	986.6	975.8	986.6	997.3	998.1
10°	1002.6	1000.7	1000.2	1000.9	1002.7	1000.8	987.9	975.0	987.9	1000.8	1002.7
12.5°	987.5	987.1	987.7	991.6	998.7	1000.3	985.2	970.2	985.2	1000.3	998.7
15°	964.6	963.0	961.7	968.8	984.3	991.6	973.8	956.0	973.8	991.6	984.3
17.5°	951.3	946.6	941.8	946.8	961.7	968.2	949.6	931.0	949.6	968.2	961.7
20°	944.9	938.3	932.1	935.0	947.0	951.5	933.2	915.0	933.2	951.5	947.0
22.5°	941.6	932.5	923.8	924.3	934.2	937.1	918.8	900.6	918.8	937.1	934.2
25°	940.9	927.0	912.3	907.5	912.3	912.0	896.0	880.0	896.0	912.0	912.3
27.5°	937.8	920.9	901.1	888.6	883.5	877.3	867.8	858.4	867.8	877.3	883.5
30°	923.8	910.0	892.7	877.3	864.0	852.5	846.2	840.0	846.2	852.5	864.0
32.5°	894.0	888.1	879.0	864.2	843.7	827.5	823.7	820.0	823.7	827.5	843.7
35°	835.9	843.3	850.5	840.7	814.0	793.2	790.1	787.0	790.1	793.2	814.0
37.5°	759.0	777.0	797.8	798.0	777.5	760.6	754.2	747.8	754.2	760.6	777.5
40°	696.2	722.3	753.5	763.2	751.7	740.3	729.7	719.0	729.7	740.3	751.7
42.5°	624.4	657.5	697.2	718.2	720.5	717.9	700.9	683.8	700.9	717.9	720.5
45°	522.2	558.3	601.4	635.7	661.0	674.2	651.1	628.0	651.1	674.2	661.0
47.5°	432.9	465.3	503.8	543.6	584.7	609.7	585.9	562.2	585.9	609.7	584.7
50°	378.1	409.0	445.0	485.0	529.0	557.2	538.1	519.0	538.1	557.2	529.0
52.5°	327.3	357.8	393.8	432.7	474.6	502.6	488.8	475.0	488.8	502.6	474.6
55°	260.6	288.7	322.9	358.4	395.3	421.2	414.1	407.0	414.1	421.2	395.3
57.5°	210.6	234.2	263.3	294.9	329.1	353.7	349.1	344.6	349.1	353.7	329.1
60°	184.6	203.0	225.7	254.1	288.3	313.2	310.1	307.0	310.1	313.2	288.3
62.5°	162.5	177.1	195.2	220.6	253.4	277.4	275.0	272.6	275.0	277.4	253.4
65°	134.2	145.3	159.1	180.0	208.0	228.4	226.2	224.0	226.2	228.4	208.0
67.5°	111.5	120.3	131.2	148.0	170.9	187.7	186.6	185.4	186.6	187.7	170.9
70°	96.4	104.3	114.1	129.0	149.0	163.9	163.4	163.0	163.4	163.9	149.0
72.5°	83.8	90.2	98.2	111.0	128.5	141.8	142.4	143.0	142.4	141.8	128.5
75°	65.8	70.0	75.3	85.1	99.3	110.3	111.7	113.0	111.7	110.3	99.3
77.5°	50.8	52.1	53.9	60.7	72.4	81.6	83.0	84.4	83.0	81.6	72.4
80°	42.0	42.0	42.0	46.4	55.3	62.4	64.2	66.0	64.2	62.4	55.3
82.5°	32.3	32.4	32.4	34.9	39.9	44.2	46.7	49.2	46.7	44.2	39.9
85°	12.7	15.0	17.7	19.0	19.0	19.6	21.8	24.0	21.8	19.6	19.0
87.5°	3.8	3.7	3.7	4.6	6.1	7.2	6.9	6.6	6.9	7.1	6.3
90°	7.0	6.7	6.7	6.4	5.4	4.0	2.3	1.0	2.3	3.7	6.0
92.5°	8.4	8.3	7.8	7.2	5.9	5.9	5.8	3.7	6.4	9.0	13.0
95°	7.7	7.7	9.0	11.4	16.7	17.1	11.4	10.4	14.7	20.8	26.1
97.5°	20.8	24.8	30.4	31.5	29.8	22.2	21.3	19.8	27.0	33.0	41.6
100°	38.5	43.5	47.6	39.5	31.1	30.8	28.8	28.1	35.8	41.5	49.9
102.5°	60.2	61.8	47.8	43.3	41.3	39.9	36.8	36.4	44.1	52.0	59.0
105°	65.3	58.6	58.9	58.9	57.6	54.9	49.2	48.9	57.6	66.6	75.3
107.5°	76.8	77.8	79.6	79.2	77.6	70.5	63.8	62.2	70.1	80.9	90.5
110°	92.1	93.1	93.8	93.1	90.8	81.7	73.7	71.3	78.4	89.7	100.1



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	106.8	107.6	109.0	107.0	103.1	92.7	83.6	80.2	87.2	98.9	109.5
115°	130.3	130.3	130.6	129.6	121.6	110.8	98.8	93.8	99.8	110.5	122.2
117.5°	153.3	153.7	152.4	149.7	140.4	127.9	114.4	106.4	111.1	122.4	134.5
120°	167.8	168.4	167.1	163.1	154.0	140.0	124.6	115.2	118.9	129.9	142.0
122.5°	182.8	182.6	181.0	176.5	165.8	151.2	136.1	124.6	126.1	136.4	148.2
125°	203.6	203.3	201.9	196.6	185.5	170.5	152.7	138.6	136.6	145.3	157.4
127.5°	223.4	222.7	220.6	214.1	202.8	188.3	168.8	152.8	148.4	153.8	164.9
130°	237.1	236.1	232.4	225.4	214.3	200.6	180.8	162.8	156.4	159.7	169.4
132.5°	250.2	247.3	244.2	236.6	226.4	212.1	192.1	173.2	164.4	165.9	173.5
135°	266.9	264.2	260.2	252.8	243.1	229.1	209.0	188.5	176.5	175.1	179.5
137.5°	281.6	278.8	274.2	267.8	258.1	245.5	226.2	204.7	189.5	185.0	186.7
140°	290.7	287.3	283.3	276.9	268.2	255.2	236.4	215.7	198.6	192.2	191.2
142.5°	298.2	295.6	291.3	285.5	277.9	264.8	246.6	226.1	208.0	199.7	197.4
145°	309.4	307.4	302.7	297.4	291.0	277.9	261.2	240.8	222.7	212.0	207.0
147.5°	318.9	317.3	313.6	307.4	302.0	289.5	274.2	256.1	237.6	224.3	217.8
150°	324.8	323.5	319.8	313.8	308.4	296.7	282.0	265.2	247.5	233.4	225.0
152.5°	330.5	329.1	324.9	318.9	314.3	303.4	290.0	274.1	256.0	242.0	233.3
155°	337.9	336.2	332.2	326.5	322.5	312.4	300.1	286.0	270.6	255.8	246.1
157.5°	343.8	341.7	338.0	333.1	328.8	319.5	308.8	296.6	283.2	269.1	259.2
160°	347.3	344.9	340.9	336.6	332.5	323.8	314.1	303.1	290.7	277.9	267.2
162.5°	349.7	347.6	342.8	339.0	335.5	327.6	318.4	308.4	297.4	286.3	276.3
165°	352.3	349.9	344.9	341.9	338.9	332.2	324.2	316.1	306.7	297.7	289.7
167.5°	352.5	350.6	345.5	342.6	340.4	334.6	328.1	322.0	314.7	307.6	300.9
170°	352.0	350.3	345.3	342.6	340.9	336.2	330.5	325.2	319.5	313.4	308.1
172.5°	350.1	348.4	343.7	341.5	340.6	336.5	331.9	327.8	323.0	318.5	314.3
175°	345.3	343.9	339.9	338.6	338.9	336.2	332.9	330.5	327.5	324.8	322.5
177.5°	338.2	337.4	334.5	334.5	335.5	333.9	332.9	331.8	330.5	329.7	328.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0
2.5°	980.3	978.0	978.3	978.9	979.9	981.0	979.9	978.9	978.3	978.0	980.3
5°	984.5	982.5	983.3	985.1	989.6	994.0	989.6	985.1	983.3	982.5	984.5
7.5°	995.7	995.7	998.3	1001.7	1007.5	1013.4	1007.5	1001.7	998.3	995.7	995.7
10°	1000.9	1000.2	1000.7	1002.6	1008.8	1015.0	1008.8	1002.6	1000.7	1000.2	1000.9
12.5°	991.6	987.7	987.1	987.5	990.8	994.2	990.8	987.5	987.1	987.7	991.6
15°	968.8	961.7	963.0	964.6	966.8	969.0	966.8	964.6	963.0	961.7	968.8
17.5°	946.8	941.8	946.6	951.3	955.7	960.0	955.7	951.3	946.6	941.8	946.8
20°	935.0	932.1	938.3	944.9	952.5	960.0	952.5	944.9	938.3	932.1	935.0
22.5°	924.3	923.8	932.5	941.6	952.0	962.4	952.0	941.6	932.5	923.8	924.3
25°	907.5	912.3	927.0	940.9	952.5	964.0	952.5	940.9	927.0	912.3	907.5
27.5°	888.6	901.1	920.9	937.8	945.9	954.0	945.9	937.8	920.9	901.1	888.6
30°	877.3	892.7	910.0	923.8	926.9	930.0	926.9	923.8	910.0	892.7	877.3
32.5°	864.2	879.0	888.1	894.0	890.0	886.0	890.0	894.0	888.1	879.0	864.2
35°	840.7	850.5	843.3	835.9	827.5	819.0	827.5	835.9	843.3	850.5	840.7
37.5°	798.0	797.8	777.0	759.0	749.3	739.6	749.3	759.0	777.0	797.8	798.0
40°	763.2	753.5	722.3	696.2	685.1	674.0	685.1	696.2	722.3	753.5	763.2
42.5°	718.2	697.2	657.5	624.4	610.8	597.2	610.8	624.4	657.5	697.2	718.2
45°	635.7	601.4	558.3	522.2	507.1	492.0	507.1	522.2	558.3	601.4	635.7
47.5°	543.6	503.8	465.3	432.9	418.7	404.6	418.7	432.9	465.3	503.8	543.6
50°	485.0	445.0	409.0	378.1	362.6	347.0	362.6	378.1	409.0	445.0	485.0
52.5°	432.7	393.8	357.8	327.3	313.1	299.0	313.1	327.3	357.8	393.8	432.7
55°	358.4	322.9	288.7	260.6	250.8	241.0	250.8	260.6	288.7	322.9	358.4
57.5°	294.9	263.3	234.2	210.6	203.4	196.2	203.4	210.6	234.2	263.3	294.9
60°	254.1	225.7	203.0	184.6	178.8	173.0	178.8	184.6	203.0	225.7	254.1
62.5°	220.6	195.2	177.1	162.5	158.2	153.8	158.2	162.5	177.1	195.2	220.6
65°	180.0	159.1	145.3	134.2	131.1	128.0	131.1	134.2	145.3	159.1	180.0
67.5°	148.0	131.2	120.3	111.5	108.5	105.6	108.5	111.5	120.3	131.2	148.0
70°	129.0	114.1	104.3	96.4	94.2	92.0	94.2	96.4	104.3	114.1	129.0
72.5°	111.0	98.2	90.2	83.8	82.3	80.8	82.3	83.8	90.2	98.2	111.0
75°	85.1	75.3	70.0	65.8	64.9	64.0	64.9	65.8	70.0	75.3	85.1
77.5°	60.7	53.9	52.1	50.8	50.8	50.8	50.8	50.8	52.1	53.9	60.7
80°	46.4	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	46.4
82.5°	34.9	32.4	32.4	32.3	32.0	31.6	32.0	32.3	32.4	32.4	34.9
85°	19.0	17.7	15.0	12.7	11.3	10.0	11.3	12.7	15.0	17.7	19.0
87.5°	4.8	4.4	4.9	5.1	5.4	5.3	5.4	5.1	4.9	4.4	4.8
90°	7.7	10.0	12.4	13.7	15.1	14.4	15.1	13.7	12.4	10.0	7.7
92.5°	15.5	19.4	22.3	24.7	25.8	25.7	25.8	24.7	22.3	19.4	15.5
95°	31.1	35.8	40.5	43.9	45.9	45.2	45.9	43.9	40.5	35.8	31.1
97.5°	48.0	54.3	59.5	62.7	64.7	66.0	64.7	62.7	59.5	54.3	48.0
100°	59.3	65.3	71.3	75.0	78.4	79.7	78.4	75.0	71.3	65.3	59.3
102.5°	68.4	76.3	82.8	86.8	89.6	91.0	89.6	86.8	82.8	76.3	68.4
105°	83.4	91.8	98.8	103.8	106.8	107.8	106.8	103.8	98.8	91.8	83.4
107.5°	98.4	107.0	113.5	119.1	122.8	124.9	122.8	119.1	113.5	107.0	98.4
110°	110.2	117.2	124.2	129.3	132.9	134.3	132.9	129.3	124.2	117.2	110.2



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	120.1	127.9	135.0	140.0	144.2	146.1	144.2	140.0	135.0	127.9	120.1
115°	134.0	144.3	150.7	155.4	158.4	160.1	158.4	155.4	150.7	144.3	134.0
117.5°	145.5	156.3	163.3	166.9	168.3	169.5	168.3	166.9	163.3	156.3	145.5
120°	152.7	162.8	170.8	175.5	177.2	177.8	177.2	175.5	170.8	162.8	152.7
122.5°	159.4	168.9	176.7	182.4	185.2	185.9	185.2	182.4	176.7	168.9	159.4
125°	168.8	177.8	185.9	191.6	194.6	196.2	194.6	191.6	185.9	177.8	168.8
127.5°	176.9	186.7	194.1	199.3	202.2	203.5	202.2	199.3	194.1	186.7	176.9
130°	181.5	191.6	198.9	204.6	207.3	208.6	207.3	204.6	198.9	191.6	181.5
132.5°	185.0	195.6	203.2	208.4	211.3	212.6	211.3	208.4	203.2	195.6	185.0
135°	189.2	200.3	208.3	213.3	216.0	217.3	216.0	213.3	208.3	200.3	189.2
137.5°	192.9	202.9	211.3	216.6	219.0	219.9	219.0	216.6	211.3	202.9	192.9
140°	195.6	204.3	212.6	217.7	220.4	220.7	220.4	217.7	212.6	204.3	195.6
142.5°	199.1	205.9	213.2	218.2	220.9	221.5	220.9	218.2	213.2	205.9	199.1
145°	205.3	209.3	214.3	219.0	221.4	222.0	221.4	219.0	214.3	209.3	205.3
147.5°	213.1	214.4	217.0	220.1	222.4	222.8	222.4	220.1	217.0	214.4	213.1
150°	219.0	218.7	219.7	221.7	223.7	223.4	223.7	221.7	219.7	218.7	219.0
152.5°	225.7	223.8	223.7	224.6	225.6	225.5	225.6	224.6	223.7	223.8	225.7
155°	237.1	233.4	231.4	230.7	230.7	230.4	230.7	230.7	231.4	233.4	237.1
157.5°	249.6	244.5	241.4	239.8	239.4	238.6	239.4	239.8	241.4	244.5	249.6
160°	258.2	252.5	249.5	246.8	245.8	244.8	245.8	246.8	249.5	252.5	258.2
162.5°	266.2	260.8	257.5	255.1	254.1	252.6	254.1	255.1	257.5	260.8	266.2
165°	279.3	273.6	269.9	267.9	266.6	265.2	266.6	267.9	269.9	273.6	279.3
167.5°	292.3	286.1	283.7	281.4	280.2	277.7	280.2	281.4	283.7	286.1	292.3
170°	300.4	294.7	293.4	291.3	289.0	286.3	289.0	291.3	293.4	294.7	300.4
172.5°	307.4	303.5	302.2	300.2	299.4	297.3	299.4	300.2	302.2	303.5	307.4
175°	317.5	314.5	314.5	314.1	313.1	311.1	313.1	314.1	314.5	314.5	317.5
177.5°	325.9	324.3	325.4	325.4	325.1	323.2	325.1	325.4	325.4	324.3	325.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	981.0	981.0	981.0	981.0
2.5°	985.3	987.7	982.3	977.0
5°	989.3	991.1	983.6	976.0
7.5°	998.1	997.3	986.6	975.8
10°	1002.7	1000.8	987.9	975.0
12.5°	998.7	1000.3	985.2	970.2
15°	984.3	991.6	973.8	956.0
17.5°	961.7	968.2	949.6	931.0
20°	947.0	951.5	933.2	915.0
22.5°	934.2	937.1	918.8	900.6
25°	912.3	912.0	896.0	880.0
27.5°	883.5	877.3	867.8	858.4
30°	864.0	852.5	846.2	840.0
32.5°	843.7	827.5	823.7	820.0
35°	814.0	793.2	790.1	787.0
37.5°	777.5	760.6	754.2	747.8
40°	751.7	740.3	729.7	719.0
42.5°	720.5	717.9	700.9	683.8
45°	661.0	674.2	651.1	628.0
47.5°	584.7	609.7	585.9	562.2
50°	529.0	557.2	538.1	519.0
52.5°	474.6	502.6	488.8	475.0
55°	395.3	421.2	414.1	407.0
57.5°	329.1	353.7	349.1	344.6
60°	288.3	313.2	310.1	307.0
62.5°	253.4	277.4	275.0	272.6
65°	208.0	228.4	226.2	224.0
67.5°	170.9	187.7	186.6	185.4
70°	149.0	163.9	163.4	163.0
72.5°	128.5	141.8	142.4	143.0
75°	99.3	110.3	111.7	113.0
77.5°	72.4	81.6	83.0	84.4
80°	55.3	62.4	64.2	66.0
82.5°	39.9	44.2	46.7	49.2
85°	19.0	19.6	21.8	24.0
87.5°	6.3	7.1	6.9	6.6
90°	6.0	3.7	2.3	1.0
92.5°	13.0	9.0	6.4	3.7
95°	26.1	20.8	14.7	10.4
97.5°	41.6	33.0	27.0	19.8
100°	49.9	41.5	35.8	28.1
102.5°	59.0	52.0	44.1	36.4
105°	75.3	66.6	57.6	48.9
107.5°	90.5	80.9	70.1	62.2
110°	100.1	89.7	78.4	71.3



TEST NUMBER: P1428183

CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	109.5	98.9	87.2	80.2
115°	122.2	110.5	99.8	93.8
117.5°	134.5	122.4	111.1	106.4
120°	142.0	129.9	118.9	115.2
122.5°	148.2	136.4	126.1	124.6
125°	157.4	145.3	136.6	138.6
127.5°	164.9	153.8	148.4	152.8
130°	169.4	159.7	156.4	162.8
132.5°	173.5	165.9	164.4	173.2
135°	179.5	175.1	176.5	188.5
137.5°	186.7	185.0	189.5	204.7
140°	191.2	192.2	198.6	215.7
142.5°	197.4	199.7	208.0	226.1
145°	207.0	212.0	222.7	240.8
147.5°	217.8	224.3	237.6	256.1
150°	225.0	233.4	247.5	265.2
152.5°	233.3	242.0	256.0	274.1
155°	246.1	255.8	270.6	286.0
157.5°	259.2	269.1	283.2	296.6
160°	267.2	277.9	290.7	303.1
162.5°	276.3	286.3	297.4	308.4
165°	289.7	297.7	306.7	316.1
167.5°	300.9	307.6	314.7	322.0
170°	308.1	313.4	319.5	325.2
172.5°	314.3	318.5	323.0	327.8
175°	322.5	324.8	327.5	330.5
177.5°	328.9	329.7	330.5	331.8
180°	331.5	331.5	331.5	331.5



TEST NUMBER: P1428183
 CATALOG NUMBER: SQ2W-PR1-K-025U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.04	19.06	18.81	19.84	20.78	14.41	15.43	15.17	16.21	17.15
	3H	19.26	20.17	20.04	20.96	21.93	15.59	16.50	16.36	17.29	18.26
	4H	19.75	20.61	20.55	21.41	22.39	16.06	16.91	16.85	17.71	18.70
	6H	20.06	20.85	20.87	21.66	22.65	16.41	17.20	17.21	18.00	19.00
	8H	20.17	20.92	20.99	21.74	22.74	16.55	17.30	17.37	18.12	19.12
	12H	20.21	20.93	21.03	21.75	22.77	16.58	17.30	17.41	18.12	19.14
4H	2H	18.17	19.02	18.97	19.82	20.81	15.14	16.00	15.94	16.80	17.78
	3H	19.64	20.35	20.45	21.18	22.18	16.51	17.22	17.32	18.05	19.05
	4H	20.28	20.92	21.10	21.75	22.78	17.06	17.71	17.89	18.54	19.57
	6H	20.72	21.27	21.56	22.13	23.16	17.51	18.06	18.35	18.92	19.95
	8H	20.88	21.40	21.72	22.25	23.29	17.69	18.21	18.54	19.06	20.11
	12H	20.95	21.42	21.81	22.29	23.34	17.75	18.21	18.61	19.08	20.13
8H	4H	20.31	20.83	21.16	21.68	22.73	17.40	17.92	18.25	18.77	19.82
	6H	20.85	21.28	21.72	22.17	23.22	17.95	18.38	18.82	19.27	20.31
	8H	21.08	21.46	21.97	22.35	23.41	18.21	18.59	19.09	19.48	20.54
	12H	21.21	21.55	22.09	22.42	23.54	18.31	18.65	19.19	19.52	20.64
12H	4H	20.28	20.74	21.14	21.61	22.66	17.43	17.89	18.29	18.77	19.82
	6H	20.84	21.22	21.72	22.11	23.17	18.02	18.40	18.90	19.29	20.35
	8H	21.10	21.43	21.98	22.31	23.43	18.32	18.65	19.20	19.53	20.65