

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428243

Luminaire Tested: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428243
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7469.3 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61				
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53				
2	93	86	80	75	87	80	75	71	71	67	64	62	59	57	54	52	50	46				
3	85	76	69	63	79	71	65	60	63	58	54	55	52	49	48	46	43	40				
4	78	68	60	54	73	64	57	52	57	51	47	50	46	42	44	40	38	35				
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	33	30				
6	67	55	47	41	62	52	45	39	46	40	36	41	36	33	36	32	30	27				
7	62	50	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	24				
8	57	45	37	32	54	43	36	31	38	33	29	34	30	26	30	27	24	22				
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30720	30720	30720	30720
5°	30680	31246	30680	31246
10°	31004	32276	31004	32276
15°	30993	31414	30993	31414
20°	30492	31992	30492	31992
25°	30406	33308	30406	33308
30°	30374	33629	30374	33629
35°	30085	31309	30085	31309
40°	29391	27553	29391	27553
45°	27811	21790	27811	21790
50°	25284	16904	25284	16904
55°	22221	13157	22221	13157
60°	19226	10834	19226	10834
65°	16599	9486	16599	9486
70°	14922	8422	14922	8422
75°	13674	7742	13674	7742
80°	11901	7578	11901	7578
85°	8614	3594	8614	3594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 29859 cd/sqm



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.5
10°-20°	531.9	7.1
20°-30°	822.3	11.0
30°-40°	988.9	13.2
40°-50°	888.0	11.9
50°-60°	595.0	8.0
60°-70°	346.1	4.6
70°-80°	177.8	2.4
80°-90°	48.0	0.6
90°-100°	78.7	1.1
100°-110°	229.5	3.1
110°-120°	374.6	5.0
120°-130°	475.3	6.4
130°-140°	508.6	6.8
140°-150°	474.9	6.4
150°-160°	390.8	5.2
160°-170°	262.1	3.5
170°-180°	93.1	1.2
0°-30°	1538.0	20.6
0°-40°	2526.8	33.8
0°-60°	4009.8	53.7
0°-90°	4581.7	61.3
90°-120°	682.8	9.1
90°-150°	2141.7	28.7
90°-180°	2888.0	38.7
0°-180°	7469.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1903	1903	1903	1903	1903	
5°	1893	1928	1893	1928	1893	181
15°	1854	1879	1854	1879	1854	521
25°	1707	1870	1707	1870	1707	787
35°	1526	1588	1526	1588	1526	952
45°	1218	954	1218	954	1218	932
55°	789	467	789	467	789	709
65°	434	248	434	248	434	439
75°	219	124	219	124	219	233
85°	46	19	46	19	46	58
90°	3	22	3	43	3	4
95°	31	23	31	135	31	37
105°	146	234	146	322	146	155
115°	280	388	280	478	280	276
125°	414	614	414	585	414	370
135°	562	804	562	648	562	435
145°	718	927	718	662	718	449
155°	853	1007	853	687	853	392
165°	943	1050	943	791	943	265
175°	986	1028	986	928	986	94
180°	989	989	989	989	989	



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1895.0	1905.3	1915.6	1911.0	1901.3	1896.9	1897.5	1898.6	1900.6	1902.7	1900.6
5°	1893.0	1907.7	1922.3	1918.9	1909.4	1905.5	1907.2	1910.7	1919.3	1927.9	1919.3
7.5°	1892.6	1913.5	1934.4	1935.9	1931.1	1931.2	1936.2	1942.8	1954.2	1965.6	1954.2
10°	1891.1	1916.1	1941.1	1944.7	1941.3	1940.0	1940.9	1944.5	1956.6	1968.7	1956.6
12.5°	1881.8	1910.9	1940.0	1937.0	1923.2	1915.7	1914.5	1915.2	1921.8	1928.3	1921.8
15°	1854.2	1888.7	1923.2	1909.2	1879.0	1865.2	1867.8	1870.8	1875.1	1879.4	1875.1
17.5°	1805.7	1841.8	1877.8	1865.2	1836.4	1826.7	1836.0	1845.1	1853.5	1862.0	1853.5
20°	1774.7	1810.0	1845.4	1836.8	1813.5	1807.9	1820.0	1832.7	1847.3	1862.0	1847.3
22.5°	1746.8	1782.1	1817.5	1811.9	1792.8	1791.7	1808.6	1826.3	1846.5	1866.6	1846.5
25°	1706.8	1737.9	1768.9	1769.5	1760.0	1769.5	1798.0	1824.9	1847.3	1869.7	1847.3
27.5°	1664.9	1683.2	1701.5	1713.5	1723.5	1747.8	1786.2	1819.0	1834.7	1850.3	1834.7
30°	1629.2	1641.3	1653.4	1675.8	1701.6	1731.4	1765.0	1791.7	1797.8	1803.8	1797.8
32.5°	1590.4	1597.7	1604.9	1636.5	1676.1	1704.8	1722.6	1734.0	1726.2	1718.5	1726.2
35°	1526.4	1532.5	1538.5	1578.8	1630.5	1649.5	1635.7	1621.3	1604.9	1588.5	1604.9
37.5°	1450.4	1462.8	1475.2	1508.1	1547.7	1547.4	1507.0	1472.1	1453.3	1434.5	1453.3
40°	1394.5	1415.2	1435.9	1457.9	1480.3	1461.4	1401.0	1350.4	1328.8	1307.3	1328.8
42.5°	1326.3	1359.4	1392.5	1397.4	1392.9	1352.2	1275.3	1211.1	1184.7	1158.3	1184.7
45°	1218.0	1262.9	1307.7	1282.1	1232.9	1166.5	1082.9	1012.9	983.6	954.3	983.6
47.5°	1090.4	1136.5	1182.5	1134.1	1054.3	977.1	902.4	839.6	812.2	784.7	812.2
50°	1006.6	1043.7	1080.8	1026.0	940.7	863.1	793.3	733.4	703.2	673.0	703.2
52.5°	921.3	948.0	974.7	920.5	839.3	763.8	694.0	634.8	607.3	579.9	607.3
55°	789.4	803.2	817.0	766.8	695.2	626.3	559.9	505.4	486.4	467.4	486.4
57.5°	668.4	677.2	686.0	638.4	572.0	510.6	454.2	408.5	394.5	380.5	394.5
60°	595.4	601.5	607.5	559.2	492.9	437.7	393.7	358.0	346.8	335.5	346.8
62.5°	528.7	533.4	538.0	491.5	427.9	378.6	343.6	315.2	306.8	298.3	306.8
65°	434.5	438.8	443.1	403.4	349.1	308.6	281.9	260.3	254.3	248.3	254.3
67.5°	359.6	361.8	364.1	331.4	287.1	254.4	233.4	216.2	210.5	204.8	210.5
70°	316.1	317.0	317.9	289.0	250.2	221.3	202.4	187.1	182.8	178.4	182.8
72.5°	277.4	276.2	274.9	249.2	215.2	190.5	174.9	162.6	159.6	156.7	159.6
75°	219.2	216.6	214.0	192.7	165.1	146.1	135.8	127.6	125.9	124.1	125.9
77.5°	163.7	160.9	158.2	140.4	117.7	104.6	101.1	98.5	98.5	98.5	98.5
80°	128.0	124.6	121.1	107.3	90.1	81.5	81.5	81.5	81.5	81.5	81.5
82.5°	95.4	90.6	85.8	77.3	67.7	62.8	62.8	62.7	62.0	61.3	62.0
85°	46.5	42.2	37.9	36.9	36.9	34.3	29.1	24.6	22.0	19.4	22.0
87.5°	13.0	13.8	14.8	13.0	10.2	8.7	8.7	8.9	9.1	9.1	9.1
90°	3.0	7.0	12.0	16.0	19.0	20.0	20.0	21.0	22.0	22.0	22.0
92.5°	11.0	17.4	17.6	17.6	21.4	23.2	24.8	25.0	26.0	26.0	26.0
95°	31.0	34.0	50.9	49.9	34.0	27.0	23.0	23.0	23.0	23.0	23.0
97.5°	59.1	63.5	66.3	88.9	93.9	90.7	73.9	62.1	55.5	52.5	55.5
100°	83.9	85.9	91.9	92.9	117.9	141.9	129.9	114.9	109.9	106.9	109.9
102.5°	108.7	109.9	119.1	123.3	129.1	142.7	184.2	179.6	176.2	175.6	176.2
105°	145.8	146.8	163.8	171.8	175.8	175.8	174.8	194.8	226.8	233.8	226.8
107.5°	185.6	190.2	210.2	231.6	236.2	237.4	232.2	229.2	228.0	228.8	228.0
110°	212.8	219.8	243.7	270.7	277.7	279.7	277.7	274.7	272.7	272.7	272.7



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	239.2	249.3	276.5	307.5	319.3	325.3	320.9	318.7	316.7	318.3	316.7
115°	279.7	294.7	330.7	362.6	386.6	389.6	388.6	388.6	387.6	387.6	387.6
117.5°	317.3	341.2	381.6	418.8	446.5	454.5	458.5	457.3	456.1	458.1	456.1
120°	343.6	371.6	417.6	459.5	486.5	498.5	502.5	500.5	502.5	500.5	502.5
122.5°	371.6	406.0	451.1	494.7	526.5	540.0	544.8	545.2	545.6	544.4	545.6
125°	413.6	455.5	508.5	553.4	586.4	602.4	606.4	607.4	609.4	614.4	609.4
127.5°	455.9	503.5	561.6	605.0	638.7	658.1	664.3	666.5	670.7	672.9	670.7
130°	485.5	539.4	598.4	639.3	672.3	693.3	704.3	707.3	712.3	711.3	712.3
132.5°	516.7	573.0	632.7	675.3	705.9	728.4	737.8	746.4	748.2	749.6	748.2
135°	562.4	623.4	683.3	725.3	754.2	776.2	788.2	796.2	801.2	804.2	801.2
137.5°	610.6	674.9	732.4	769.8	799.0	818.0	831.5	839.9	845.1	847.5	845.1
140°	643.3	705.3	761.2	800.2	826.1	845.1	857.1	867.1	873.1	873.1	873.1
142.5°	674.5	735.6	790.0	828.9	851.7	869.1	881.9	889.5	896.3	896.3	896.3
145°	718.3	779.2	829.1	868.1	887.1	903.1	917.1	923.0	927.0	927.0	927.0
147.5°	764.0	818.0	863.5	900.9	916.9	935.6	946.6	951.4	956.4	954.2	956.4
150°	791.2	841.1	885.1	920.1	936.0	954.0	965.0	969.0	974.0	971.0	974.0
152.5°	817.6	865.1	905.1	937.6	951.2	969.2	981.8	985.8	989.2	987.0	989.2
155°	853.1	895.1	932.0	962.0	974.0	991.0	1003.0	1008.0	1012.0	1007.0	1012.0
157.5°	884.9	921.0	953.2	980.8	993.6	1008.2	1019.3	1025.5	1029.5	1027.3	1029.5
160°	904.1	937.0	966.0	992.0	1004.0	1017.0	1028.9	1035.9	1039.9	1036.9	1039.9
162.5°	920.1	949.8	977.2	1000.8	1011.2	1022.5	1036.9	1043.1	1047.1	1043.3	1047.1
165°	943.0	967.0	991.0	1011.0	1019.9	1028.9	1043.9	1050.9	1053.9	1049.9	1053.9
167.5°	960.4	978.8	998.2	1015.4	1021.9	1030.7	1045.7	1051.5	1055.3	1050.3	1055.3
170°	970.0	986.0	1003.0	1017.0	1021.9	1029.9	1044.9	1049.9	1052.9	1047.9	1052.9
172.5°	978.0	990.0	1003.8	1016.2	1018.7	1025.1	1039.3	1044.3	1046.5	1042.3	1046.5
175°	986.0	993.0	1003.0	1011.0	1010.0	1014.0	1025.9	1029.9	1033.9	1027.9	1033.9
177.5°	989.8	993.0	996.2	1001.0	997.8	997.8	1006.6	1009.0	1009.8	1006.6	1009.8
180°	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1898.6	1897.5	1896.9	1901.3	1911.0	1915.6	1905.3	1895.0	1905.3	1915.6	1911.0
5°	1910.7	1907.2	1905.5	1909.4	1918.9	1922.3	1907.7	1893.0	1907.7	1922.3	1918.9
7.5°	1942.8	1936.2	1931.2	1931.1	1935.9	1934.4	1913.5	1892.6	1913.5	1934.4	1935.9
10°	1944.5	1940.9	1940.0	1941.3	1944.7	1941.1	1916.1	1891.1	1916.1	1941.1	1944.7
12.5°	1915.2	1914.5	1915.7	1923.2	1937.0	1940.0	1910.9	1881.8	1910.9	1940.0	1937.0
15°	1870.8	1867.8	1865.2	1879.0	1909.2	1923.2	1888.7	1854.2	1888.7	1923.2	1909.2
17.5°	1845.1	1836.0	1826.7	1836.4	1865.2	1877.8	1841.8	1805.7	1841.8	1877.8	1865.2
20°	1832.7	1820.0	1807.9	1813.5	1836.8	1845.4	1810.0	1774.7	1810.0	1845.4	1836.8
22.5°	1826.3	1808.6	1791.7	1792.8	1811.9	1817.5	1782.1	1746.8	1782.1	1817.5	1811.9
25°	1824.9	1798.0	1769.5	1760.0	1769.5	1768.9	1737.9	1706.8	1737.9	1768.9	1769.5
27.5°	1819.0	1786.2	1747.8	1723.5	1713.5	1701.5	1683.2	1664.9	1683.2	1701.5	1713.5
30°	1791.7	1765.0	1731.4	1701.6	1675.8	1653.4	1641.3	1629.2	1641.3	1653.4	1675.8
32.5°	1734.0	1722.6	1704.8	1676.1	1636.5	1604.9	1597.7	1590.4	1597.7	1604.9	1636.5
35°	1621.3	1635.7	1649.5	1630.5	1578.8	1538.5	1532.5	1526.4	1532.5	1538.5	1578.8
37.5°	1472.1	1507.0	1547.4	1547.7	1508.1	1475.2	1462.8	1450.4	1462.8	1475.2	1508.1
40°	1350.4	1401.0	1461.4	1480.3	1457.9	1435.9	1415.2	1394.5	1415.2	1435.9	1457.9
42.5°	1211.1	1275.3	1352.2	1392.9	1397.4	1392.5	1359.4	1326.3	1359.4	1392.5	1397.4
45°	1012.9	1082.9	1166.5	1232.9	1282.1	1307.7	1262.9	1218.0	1262.9	1307.7	1282.1
47.5°	839.6	902.4	977.1	1054.3	1134.1	1182.5	1136.5	1090.4	1136.5	1182.5	1134.1
50°	733.4	793.3	863.1	940.7	1026.0	1080.8	1043.7	1006.6	1043.7	1080.8	1026.0
52.5°	634.8	694.0	763.8	839.3	920.5	974.7	948.0	921.3	948.0	974.7	920.5
55°	505.4	559.9	626.3	695.2	766.8	817.0	803.2	789.4	803.2	817.0	766.8
57.5°	408.5	454.2	510.6	572.0	638.4	686.0	677.2	668.4	677.2	686.0	638.4
60°	358.0	393.7	437.7	492.9	559.2	607.5	601.5	595.4	601.5	607.5	559.2
62.5°	315.2	343.6	378.6	427.9	491.5	538.0	533.4	528.7	533.4	538.0	491.5
65°	260.3	281.9	308.6	349.1	403.4	443.1	438.8	434.5	438.8	443.1	403.4
67.5°	216.2	233.4	254.4	287.1	331.4	364.1	361.8	359.6	361.8	364.1	331.4
70°	187.1	202.4	221.3	250.2	289.0	317.9	317.0	316.1	317.0	317.9	289.0
72.5°	162.6	174.9	190.5	215.2	249.2	274.9	276.2	277.4	276.2	274.9	249.2
75°	127.6	135.8	146.1	165.1	192.7	214.0	216.6	219.2	216.6	214.0	192.7
77.5°	98.5	101.1	104.6	117.7	140.4	158.2	160.9	163.7	160.9	158.2	140.4
80°	81.5	81.5	81.5	90.1	107.3	121.1	124.6	128.0	124.6	121.1	107.3
82.5°	62.7	62.8	62.8	67.7	77.3	85.8	90.6	95.4	90.6	85.8	77.3
85°	24.6	29.1	34.3	36.9	36.9	37.9	42.2	46.5	42.2	37.9	36.9
87.5°	8.9	8.7	8.7	10.2	13.0	14.8	13.8	13.0	13.8	14.6	13.4
90°	21.0	20.0	20.0	19.0	16.0	12.0	7.0	3.0	7.0	11.0	18.0
92.5°	25.0	24.8	23.2	21.4	17.6	17.6	17.4	11.0	19.0	27.0	38.8
95°	23.0	23.0	27.0	34.0	49.9	50.9	34.0	31.0	44.0	61.9	77.9
97.5°	62.1	73.9	90.7	93.9	88.9	66.3	63.5	59.1	80.5	98.3	124.1
100°	114.9	129.9	141.9	117.9	92.9	91.9	85.9	83.9	106.9	123.9	148.8
102.5°	179.6	184.2	142.7	129.1	123.3	119.1	109.9	108.7	131.7	155.0	176.0
105°	194.8	174.8	175.8	175.8	171.8	163.8	146.8	145.8	171.8	198.8	224.8
107.5°	229.2	232.2	237.4	236.2	231.6	210.2	190.2	185.6	209.0	241.4	269.9
110°	274.7	277.7	279.7	277.7	270.7	243.7	219.8	212.8	233.8	267.7	298.7



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	318.7	320.9	325.3	319.3	307.5	276.5	249.3	239.2	260.1	294.9	326.7
115°	388.6	388.6	389.6	386.6	362.6	330.7	294.7	279.7	297.7	329.7	364.6
117.5°	457.3	458.5	454.5	446.5	418.8	381.6	341.2	317.3	331.5	365.2	401.2
120°	500.5	502.5	498.5	486.5	459.5	417.6	371.6	343.6	354.6	387.6	423.6
122.5°	545.2	544.8	540.0	526.5	494.7	451.1	406.0	371.6	376.2	406.8	441.9
125°	607.4	606.4	602.4	586.4	553.4	508.5	455.5	413.6	407.6	433.6	469.5
127.5°	666.5	664.3	658.1	638.7	605.0	561.6	503.5	455.9	442.5	458.9	491.9
130°	707.3	704.3	693.3	672.3	639.3	598.4	539.4	485.5	466.5	476.5	505.5
132.5°	746.4	737.8	728.4	705.9	675.3	632.7	573.0	516.7	490.5	494.9	517.5
135°	796.2	788.2	776.2	754.2	725.3	683.3	623.4	562.4	526.5	522.5	535.4
137.5°	839.9	831.5	818.0	799.0	769.8	732.4	674.9	610.6	565.2	551.8	556.8
140°	867.1	857.1	845.1	826.1	800.2	761.2	705.3	643.3	592.4	573.4	570.4
142.5°	889.5	881.9	869.1	851.7	828.9	790.0	735.6	674.5	620.4	595.8	588.8
145°	923.0	917.1	903.1	887.1	868.1	829.1	779.2	718.3	664.3	632.3	617.4
147.5°	951.4	946.6	935.6	916.9	900.9	863.5	818.0	764.0	708.7	669.1	649.7
150°	969.0	965.0	954.0	936.0	920.1	885.1	841.1	791.2	738.2	696.3	671.3
152.5°	985.8	981.8	969.2	951.2	937.6	905.1	865.1	817.6	763.8	721.9	696.1
155°	1008.0	1003.0	991.0	974.0	962.0	932.0	895.1	853.1	807.2	763.2	734.2
157.5°	1025.5	1019.3	1008.2	993.6	980.8	953.2	921.0	884.9	844.7	802.8	773.2
160°	1035.9	1028.9	1017.0	1004.0	992.0	966.0	937.0	904.1	867.1	829.1	797.2
162.5°	1043.1	1036.9	1022.5	1011.2	1000.8	977.2	949.8	920.1	887.1	853.9	824.3
165°	1050.9	1043.9	1028.9	1019.9	1011.0	991.0	967.0	943.0	915.1	888.1	864.1
167.5°	1051.5	1045.7	1030.7	1021.9	1015.4	998.2	978.8	960.4	938.6	917.5	897.5
170°	1049.9	1044.9	1029.9	1021.9	1017.0	1003.0	986.0	970.0	953.0	935.0	919.1
172.5°	1044.3	1039.3	1025.1	1018.7	1016.2	1003.8	990.0	978.0	963.4	950.2	937.4
175°	1029.9	1025.9	1014.0	1010.0	1011.0	1003.0	993.0	986.0	977.0	969.0	962.0
177.5°	1009.0	1006.6	997.8	997.8	1001.0	996.2	993.0	989.8	985.8	983.4	981.0
180°	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1901.3	1896.9	1897.5	1898.6	1900.6	1902.7	1900.6	1898.6	1897.5	1896.9	1901.3
5°	1909.4	1905.5	1907.2	1910.7	1919.3	1927.9	1919.3	1910.7	1907.2	1905.5	1909.4
7.5°	1931.1	1931.2	1936.2	1942.8	1954.2	1965.6	1954.2	1942.8	1936.2	1931.2	1931.1
10°	1941.3	1940.0	1940.9	1944.5	1956.6	1968.7	1956.6	1944.5	1940.9	1940.0	1941.3
12.5°	1923.2	1915.7	1914.5	1915.2	1921.8	1928.3	1921.8	1915.2	1914.5	1915.7	1923.2
15°	1879.0	1865.2	1867.8	1870.8	1875.1	1879.4	1875.1	1870.8	1867.8	1865.2	1879.0
17.5°	1836.4	1826.7	1836.0	1845.1	1853.5	1862.0	1853.5	1845.1	1836.0	1826.7	1836.4
20°	1813.5	1807.9	1820.0	1832.7	1847.3	1862.0	1847.3	1832.7	1820.0	1807.9	1813.5
22.5°	1792.8	1791.7	1808.6	1826.3	1846.5	1866.6	1846.5	1826.3	1808.6	1791.7	1792.8
25°	1760.0	1769.5	1798.0	1824.9	1847.3	1869.7	1847.3	1824.9	1798.0	1769.5	1760.0
27.5°	1723.5	1747.8	1786.2	1819.0	1834.7	1850.3	1834.7	1819.0	1786.2	1747.8	1723.5
30°	1701.6	1731.4	1765.0	1791.7	1797.8	1803.8	1797.8	1791.7	1765.0	1731.4	1701.6
32.5°	1676.1	1704.8	1722.6	1734.0	1726.2	1718.5	1726.2	1734.0	1722.6	1704.8	1676.1
35°	1630.5	1649.5	1635.7	1621.3	1604.9	1588.5	1604.9	1621.3	1635.7	1649.5	1630.5
37.5°	1547.7	1547.4	1507.0	1472.1	1453.3	1434.5	1453.3	1472.1	1507.0	1547.4	1547.7
40°	1480.3	1461.4	1401.0	1350.4	1328.8	1307.3	1328.8	1350.4	1401.0	1461.4	1480.3
42.5°	1392.9	1352.2	1275.3	1211.1	1184.7	1158.3	1184.7	1211.1	1275.3	1352.2	1392.9
45°	1232.9	1166.5	1082.9	1012.9	983.6	954.3	983.6	1012.9	1082.9	1166.5	1232.9
47.5°	1054.3	977.1	902.4	839.6	812.2	784.7	812.2	902.4	977.1	1054.3	
50°	940.7	863.1	793.3	733.4	703.2	673.0	703.2	793.3	863.1	940.7	
52.5°	839.3	763.8	694.0	634.8	607.3	579.9	607.3	694.0	763.8	839.3	
55°	695.2	626.3	559.9	505.4	486.4	467.4	486.4	559.9	626.3	695.2	
57.5°	572.0	510.6	454.2	408.5	394.5	380.5	394.5	454.2	510.6	572.0	
60°	492.9	437.7	393.7	358.0	346.8	335.5	346.8	393.7	437.7	492.9	
62.5°	427.9	378.6	343.6	315.2	306.8	298.3	306.8	343.6	378.6	427.9	
65°	349.1	308.6	281.9	260.3	254.3	248.3	254.3	281.9	308.6	349.1	
67.5°	287.1	254.4	233.4	216.2	210.5	204.8	210.5	233.4	254.4	287.1	
70°	250.2	221.3	202.4	187.1	182.8	178.4	182.8	202.4	221.3	250.2	
72.5°	215.2	190.5	174.9	162.6	159.6	156.7	159.6	174.9	190.5	215.2	
75°	165.1	146.1	135.8	127.6	125.9	124.1	125.9	135.8	146.1	165.1	
77.5°	117.7	104.6	101.1	98.5	98.5	98.5	98.5	101.1	104.6	117.7	
80°	90.1	81.5	81.5	81.5	81.5	81.5	81.5	81.5	81.5	81.5	90.1
82.5°	67.7	62.8	62.8	62.7	62.0	61.3	62.0	62.7	62.8	62.8	67.7
85°	36.9	34.3	29.1	24.6	22.0	19.4	22.0	24.6	29.1	34.3	36.9
87.5°	11.0	10.6	12.0	12.8	13.6	13.2	13.6	12.8	10.6	11.0	
90°	23.0	30.0	37.0	41.0	45.0	43.0	45.0	41.0	30.0	23.0	
92.5°	46.2	57.9	66.5	73.7	76.9	76.5	76.9	66.5	57.9	46.2	
95°	92.9	106.9	120.9	130.9	136.9	134.9	136.9	120.9	106.9	92.9	
97.5°	143.3	162.0	177.6	187.0	193.0	197.0	193.0	177.6	162.0	143.3	
100°	176.8	194.8	212.8	223.8	233.8	237.8	233.8	212.8	194.8	176.8	
102.5°	204.0	227.6	247.1	258.9	267.3	271.3	267.3	247.1	227.6	204.0	
105°	248.7	273.7	294.7	309.7	318.7	321.7	318.7	294.7	273.7	248.7	
107.5°	293.5	319.3	338.7	355.2	366.2	372.6	366.2	338.7	319.3	293.5	
110°	328.7	349.6	370.6	385.6	396.6	400.6	396.6	370.6	349.6	328.7	



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	358.2	381.6	402.6	417.6	430.2	435.8	430.2	417.6	402.6	381.6	358.2
115°	399.6	430.6	449.5	463.5	472.5	477.5	472.5	463.5	449.5	430.6	399.6
117.5°	434.0	466.3	487.1	497.9	502.1	505.7	502.1	497.9	487.1	466.3	434.0
120°	455.5	485.5	509.5	523.5	528.5	530.5	528.5	523.5	509.5	485.5	455.5
122.5°	475.5	503.9	527.1	544.2	552.4	554.4	552.4	544.2	527.1	503.9	475.5
125°	503.5	530.5	554.4	571.4	580.4	585.4	580.4	571.4	554.4	530.5	503.5
127.5°	527.9	557.0	579.0	594.4	603.2	607.2	603.2	594.4	579.0	557.0	527.9
130°	541.4	571.4	593.4	610.4	618.4	622.4	618.4	610.4	593.4	571.4	541.4
132.5°	551.8	583.4	606.2	621.6	630.3	634.3	630.3	621.6	606.2	583.4	551.8
135°	564.4	597.4	621.4	636.3	644.3	648.3	644.3	636.3	621.4	597.4	564.4
137.5°	575.4	605.4	630.3	646.1	653.3	655.9	653.3	646.1	630.3	605.4	575.4
140°	583.4	609.4	634.3	649.3	657.3	658.3	657.3	649.3	634.3	609.4	583.4
142.5°	593.8	614.2	635.9	650.9	658.9	660.7	658.9	650.9	635.9	614.2	593.8
145°	612.4	624.4	639.3	653.3	660.3	662.3	660.3	653.3	639.3	624.4	612.4
147.5°	635.7	639.5	647.3	656.5	663.3	664.7	663.3	656.5	647.3	639.5	635.7
150°	653.3	652.3	655.3	661.3	667.3	666.3	667.3	661.3	655.3	652.3	653.3
152.5°	673.3	667.5	667.3	670.1	672.9	672.7	672.9	670.1	667.3	667.5	673.3
155°	707.3	696.3	690.3	688.3	688.3	687.3	688.3	688.3	690.3	696.3	707.3
157.5°	744.6	729.2	720.3	715.5	714.1	711.9	714.1	715.5	720.3	729.2	744.6
160°	770.2	753.2	744.2	736.2	733.2	730.2	733.2	736.2	744.2	753.2	770.2
162.5°	794.2	778.0	768.2	761.0	758.0	753.4	758.0	761.0	768.2	778.0	794.2
165°	833.1	816.2	805.2	799.2	795.2	791.2	795.2	799.2	805.2	816.2	833.1
167.5°	872.1	853.5	846.3	839.5	835.7	828.5	835.7	839.5	846.3	853.5	872.1
170°	896.1	879.1	875.1	869.1	862.1	854.1	862.1	869.1	875.1	879.1	896.1
172.5°	916.9	905.5	901.5	895.5	893.3	886.9	893.3	895.5	901.5	905.5	916.9
175°	947.0	938.0	938.0	937.0	934.0	928.0	934.0	937.0	938.0	938.0	947.0
177.5°	972.2	967.4	970.6	970.6	969.8	964.2	969.8	970.6	970.6	967.4	972.2
180°	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0	989.0



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1902.7	1902.7	1902.7	1902.7
2.5°	1911.0	1915.6	1905.3	1895.0
5°	1918.9	1922.3	1907.7	1893.0
7.5°	1935.9	1934.4	1913.5	1892.6
10°	1944.7	1941.1	1916.1	1891.1
12.5°	1937.0	1940.0	1910.9	1881.8
15°	1909.2	1923.2	1888.7	1854.2
17.5°	1865.2	1877.8	1841.8	1805.7
20°	1836.8	1845.4	1810.0	1774.7
22.5°	1811.9	1817.5	1782.1	1746.8
25°	1769.5	1768.9	1737.9	1706.8
27.5°	1713.5	1701.5	1683.2	1664.9
30°	1675.8	1653.4	1641.3	1629.2
32.5°	1636.5	1604.9	1597.7	1590.4
35°	1578.8	1538.5	1532.5	1526.4
37.5°	1508.1	1475.2	1462.8	1450.4
40°	1457.9	1435.9	1415.2	1394.5
42.5°	1397.4	1392.5	1359.4	1326.3
45°	1282.1	1307.7	1262.9	1218.0
47.5°	1134.1	1182.5	1136.5	1090.4
50°	1026.0	1080.8	1043.7	1006.6
52.5°	920.5	974.7	948.0	921.3
55°	766.8	817.0	803.2	789.4
57.5°	638.4	686.0	677.2	668.4
60°	559.2	607.5	601.5	595.4
62.5°	491.5	538.0	533.4	528.7
65°	403.4	443.1	438.8	434.5
67.5°	331.4	364.1	361.8	359.6
70°	289.0	317.9	317.0	316.1
72.5°	249.2	274.9	276.2	277.4
75°	192.7	214.0	216.6	219.2
77.5°	140.4	158.2	160.9	163.7
80°	107.3	121.1	124.6	128.0
82.5°	77.3	85.8	90.6	95.4
85°	36.9	37.9	42.2	46.5
87.5°	13.4	14.6	13.8	13.0
90°	18.0	11.0	7.0	3.0
92.5°	38.8	27.0	19.0	11.0
95°	77.9	61.9	44.0	31.0
97.5°	124.1	98.3	80.5	59.1
100°	148.8	123.9	106.9	83.9
102.5°	176.0	155.0	131.7	108.7
105°	224.8	198.8	171.8	145.8
107.5°	269.9	241.4	209.0	185.6
110°	298.7	267.7	233.8	212.8



TEST NUMBER: P1428243

CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	326.7	294.9	260.1	239.2
115°	364.6	329.7	297.7	279.7
117.5°	401.2	365.2	331.5	317.3
120°	423.6	387.6	354.6	343.6
122.5°	441.9	406.8	376.2	371.6
125°	469.5	433.6	407.6	413.6
127.5°	491.9	458.9	442.5	455.9
130°	505.5	476.5	466.5	485.5
132.5°	517.5	494.9	490.5	516.7
135°	535.4	522.5	526.5	562.4
137.5°	556.8	551.8	565.2	610.6
140°	570.4	573.4	592.4	643.3
142.5°	588.8	595.8	620.4	674.5
145°	617.4	632.3	664.3	718.3
147.5°	649.7	669.1	708.7	764.0
150°	671.3	696.3	738.2	791.2
152.5°	696.1	721.9	763.8	817.6
155°	734.2	763.2	807.2	853.1
157.5°	773.2	802.8	844.7	884.9
160°	797.2	829.1	867.1	904.1
162.5°	824.3	853.9	887.1	920.1
165°	864.1	888.1	915.1	943.0
167.5°	897.5	917.5	938.6	960.4
170°	919.1	935.0	953.0	970.0
172.5°	937.4	950.2	963.4	978.0
175°	962.0	969.0	977.0	986.0
177.5°	981.0	983.4	985.8	989.8
180°	989.0	989.0	989.0	989.0



TEST NUMBER: P1428243
 CATALOG NUMBER: SQ2W-PR1-K-075U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.57	20.49	20.43	21.37	22.47	15.94	16.86	16.80	17.74	18.84
	3H	20.78	21.61	21.66	22.49	23.62	17.11	17.93	17.98	18.82	19.95
	4H	21.27	22.05	22.16	22.94	24.08	17.58	18.35	18.47	19.24	20.38
	6H	21.57	22.29	22.48	23.19	24.34	17.92	18.63	18.82	19.53	20.69
	8H	21.68	22.36	22.59	23.27	24.42	18.06	18.74	18.97	19.65	20.81
	12H	21.72	22.36	22.63	23.27	24.45	18.09	18.74	19.01	19.65	20.82
4H	2H	19.68	20.46	20.58	21.35	22.49	16.66	17.43	17.56	18.33	19.47
	3H	21.15	21.79	22.06	22.72	23.87	18.02	18.66	18.93	19.59	20.74
	4H	21.78	22.36	22.70	23.28	24.47	18.57	19.15	19.49	20.07	21.25
	6H	22.22	22.72	23.15	23.66	24.84	19.01	19.51	19.94	20.45	21.63
	8H	22.37	22.84	23.31	23.78	24.98	19.19	19.66	20.12	20.60	21.79
	12H	22.44	22.86	23.40	23.82	25.02	19.24	19.66	20.19	20.62	21.82
8H	4H	21.81	22.28	22.74	23.22	24.41	18.90	19.37	19.83	20.31	21.50
	6H	22.34	22.73	23.30	23.71	24.91	19.44	19.83	20.40	20.81	22.01
	8H	22.58	22.92	23.55	23.89	25.10	19.71	20.05	20.67	21.02	22.23
	12H	22.70	23.00	23.67	23.97	25.23	19.80	20.10	20.77	21.07	22.33
12H	4H	21.77	22.19	22.72	23.15	24.35	18.92	19.34	19.88	20.30	21.50
	6H	22.33	22.68	23.30	23.65	24.86	19.51	19.86	20.48	20.83	22.04
	8H	22.59	22.89	23.56	23.85	25.11	19.81	20.11	20.78	21.07	22.33