

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428300

Luminaire Tested: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428300
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9260.2 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	93	89	86	82	84	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	22				
3	78	69	62	57	70	62	56	52	49	45	42	37	35	33	26	25	23	19				
4	71	61	54	48	64	55	49	44	44	40	36	33	31	28	24	22	20	16				
5	66	55	47	41	59	49	43	38	39	35	31	30	27	24	21	20	18	14				
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16	13				
7	56	44	37	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11				
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10				
9	48	36	29	24	43	33	27	23	27	22	19	21	17	15	15	13	11	9				
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17925	17925	17925	17925
5°	17901	18232	17901	18232
10°	18090	18831	18090	18831
15°	18084	18330	18084	18330
20°	17792	18666	17792	18666
25°	17742	19434	17742	19434
30°	17722	19622	17722	19622
35°	17554	18267	17554	18267
40°	17150	16075	17150	16075
45°	16228	12714	16228	12714
50°	14752	9864	14752	9864
55°	12965	7676	12965	7676
60°	11218	6323	11218	6323
65°	9685	5536	9685	5536
70°	8710	4914	8710	4914
75°	7979	4516	7979	4516
80°	6945	4416	6945	4416
85°	5039	2093	5039	2093

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 17422 cd/sqm



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	1.2
10°-20°	310.4	3.4
20°-30°	479.8	5.2
30°-40°	577.0	6.2
40°-50°	518.1	5.6
50°-60°	347.2	3.7
60°-70°	202.0	2.2
70°-80°	103.7	1.1
80°-90°	34.9	0.4
90°-100°	179.4	1.9
100°-110°	523.0	5.6
110°-120°	853.6	9.2
120°-130°	1083.1	11.7
130°-140°	1158.9	12.5
140°-150°	1082.2	11.7
150°-160°	890.5	9.6
160°-170°	597.2	6.4
170°-180°	212.1	2.3
0°-30°	897.3	9.7
0°-40°	1474.3	15.9
0°-60°	2339.6	25.3
0°-90°	2680.2	28.9
90°-120°	1556.0	16.8
90°-150°	4880.2	52.7
90°-180°	6580.0	71.1
0°-180°	9260.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1110	1110	1110	1110	1110	
5°	1104	1125	1104	1125	1104	105
15°	1082	1097	1082	1097	1082	304
25°	996	1091	996	1091	996	459
35°	891	927	891	927	891	555
45°	711	557	711	557	711	544
55°	461	273	461	273	461	414
65°	254	145	254	145	254	256
75°	128	72	128	72	128	136
85°	27	11	27	11	27	34
90°	7	50	7	98	7	6
95°	71	52	71	307	71	85
105°	332	533	332	733	332	353
115°	637	883	637	1088	637	628
125°	942	1400	942	1334	942	843
135°	1282	1832	1282	1477	1282	990
145°	1637	2112	1637	1509	1637	1024
155°	1944	2294	1944	1566	1944	894
165°	2149	2392	2149	1803	2149	605
175°	2247	2342	2247	2115	2247	213
180°	2254	2254	2254	2254	2254	



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1105.6	1111.7	1117.7	1115.0	1109.4	1106.8	1107.2	1107.8	1109.0	1110.2	1109.0
5°	1104.5	1113.1	1121.6	1119.6	1114.1	1111.8	1112.8	1114.8	1119.9	1124.9	1119.9
7.5°	1104.3	1116.5	1128.6	1129.6	1126.7	1126.8	1129.7	1133.6	1140.2	1146.8	1140.2
10°	1103.4	1118.0	1132.6	1134.7	1132.7	1131.9	1132.4	1134.6	1141.6	1148.6	1141.6
12.5°	1097.9	1114.9	1132.0	1130.2	1122.1	1117.7	1117.0	1117.5	1121.3	1125.1	1121.3
15°	1081.9	1102.0	1122.1	1113.9	1096.3	1088.3	1089.8	1091.6	1094.1	1096.6	1094.1
17.5°	1053.6	1074.6	1095.6	1088.3	1071.5	1065.8	1071.2	1076.5	1081.5	1086.4	1081.5
20°	1035.5	1056.1	1076.7	1071.7	1058.1	1054.8	1061.9	1069.3	1077.9	1086.4	1077.9
22.5°	1019.2	1039.8	1060.4	1057.2	1046.0	1045.4	1055.2	1065.6	1077.4	1089.1	1077.4
25°	995.9	1014.0	1032.1	1032.5	1026.9	1032.5	1049.1	1064.8	1077.9	1090.9	1077.9
27.5°	971.4	982.1	992.8	999.8	1005.6	1019.8	1042.2	1061.3	1070.5	1079.6	1070.5
30°	950.6	957.6	964.7	977.8	992.9	1010.2	1029.8	1045.4	1048.9	1052.5	1048.9
32.5°	928.0	932.2	936.4	954.8	978.0	994.7	1005.1	1011.7	1007.2	1002.7	1007.2
35°	890.6	894.1	897.7	921.2	951.4	962.4	954.4	946.0	936.4	926.8	936.4
37.5°	846.3	853.5	860.8	879.9	903.1	902.8	879.3	858.9	848.0	837.0	848.0
40°	813.7	825.7	837.8	850.6	863.7	852.7	817.4	787.9	775.3	762.7	775.3
42.5°	773.8	793.2	812.5	815.3	812.7	789.0	744.1	706.6	691.2	675.8	691.2
45°	710.7	736.8	763.0	748.0	719.4	680.6	631.9	591.0	573.9	556.8	573.9
47.5°	636.2	663.1	689.9	661.7	615.2	570.1	526.5	489.9	473.9	457.9	473.9
50°	587.3	609.0	630.6	598.7	548.9	503.6	462.9	427.9	410.3	392.7	410.3
52.5°	537.5	553.1	568.7	537.1	489.7	445.7	404.9	370.4	354.4	338.4	354.4
55°	460.6	468.6	476.7	447.4	405.6	365.4	326.7	294.9	283.8	272.7	283.8
57.5°	390.0	395.1	400.2	372.5	333.7	297.9	265.0	238.3	230.2	222.0	230.2
60°	347.4	350.9	354.5	326.3	287.6	255.4	229.7	208.9	202.3	195.8	202.3
62.5°	308.5	311.2	313.9	286.8	249.6	220.9	200.5	183.9	179.0	174.1	179.0
65°	253.5	256.0	258.5	235.4	203.7	180.1	164.5	151.9	148.4	144.9	148.4
67.5°	209.8	211.1	212.4	193.4	167.5	148.5	136.2	126.1	122.8	119.5	122.8
70°	184.5	185.0	185.5	168.6	146.0	129.1	118.1	109.1	106.6	104.1	106.6
72.5°	161.8	161.1	160.4	145.4	125.6	111.1	102.1	94.9	93.1	91.4	93.1
75°	127.9	126.4	124.9	112.4	96.3	85.3	79.2	74.4	73.4	72.4	73.4
77.5°	95.5	93.9	92.3	81.9	68.7	61.0	59.0	57.5	57.5	57.5	57.5
80°	74.7	72.7	70.7	62.6	52.6	47.5	47.5	47.5	47.5	47.5	47.5
82.5°	55.7	52.9	50.0	45.1	39.5	36.7	36.7	36.6	36.2	35.8	36.2
85°	27.2	24.6	22.1	21.5	21.5	20.0	17.0	14.3	12.8	11.3	12.8
87.5°	8.6	10.4	12.7	13.0	12.4	11.8	11.8	12.3	12.7	12.7	12.7
90°	6.8	15.9	27.3	36.4	43.3	45.5	45.5	47.8	50.1	50.1	50.1
92.5°	25.0	39.6	40.1	40.1	48.7	52.8	56.5	56.9	59.2	59.2	59.2
95°	70.6	77.4	116.1	113.8	77.4	61.5	52.4	52.4	52.4	52.4	52.4
97.5°	134.8	144.8	151.1	202.6	214.0	206.7	168.4	141.6	126.6	119.7	126.6
100°	191.2	195.8	209.4	211.7	268.6	323.2	295.9	261.8	250.4	243.6	250.4
102.5°	247.7	250.4	271.3	280.9	294.1	325.1	419.8	409.3	401.5	400.2	401.5
105°	332.3	334.6	373.3	391.5	400.6	400.6	398.4	443.9	516.7	532.7	516.7
107.5°	422.9	433.4	478.9	527.7	538.1	540.9	529.0	522.2	519.5	521.3	519.5
110°	484.9	500.8	555.4	616.9	632.8	637.4	632.8	626.0	621.4	621.4	621.4



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	545.0	568.2	630.1	700.7	727.5	741.2	731.2	726.1	721.6	725.2	721.6
115°	637.4	671.5	753.5	826.3	880.9	887.8	885.5	885.5	883.2	883.2	883.2
117.5°	723.0	777.6	869.6	954.2	1017.5	1035.7	1044.8	1042.1	1039.4	1043.9	1039.4
120°	783.1	846.8	951.5	1047.1	1108.6	1135.9	1145.0	1140.4	1145.0	1140.4	1145.0
122.5°	846.8	925.1	1028.0	1127.2	1199.6	1230.6	1241.5	1242.4	1243.3	1240.6	1243.3
125°	942.4	1038.0	1158.6	1261.1	1336.2	1372.6	1381.7	1384.0	1388.6	1399.9	1388.6
127.5°	1038.9	1147.3	1279.7	1378.5	1455.5	1499.6	1513.8	1518.8	1528.3	1533.3	1528.3
130°	1106.3	1229.2	1363.5	1456.8	1532.0	1579.8	1604.8	1611.6	1623.0	1620.7	1623.0
132.5°	1177.3	1305.7	1441.8	1538.8	1608.4	1659.9	1681.3	1700.9	1705.0	1708.2	1705.0
135°	1281.6	1420.4	1557.0	1652.6	1718.6	1768.7	1796.0	1814.2	1825.6	1832.4	1825.6
137.5°	1391.3	1537.9	1669.0	1754.1	1820.6	1863.9	1894.8	1913.9	1925.8	1931.2	1925.8
140°	1466.0	1607.1	1734.6	1823.3	1882.5	1925.8	1953.1	1975.8	1989.5	1989.5	1989.5
142.5°	1537.0	1676.3	1800.1	1888.9	1940.8	1980.4	2009.5	2026.8	2042.3	2042.3	2042.3
145°	1636.7	1775.5	1889.3	1978.1	2021.4	2057.8	2089.7	2103.3	2112.4	2112.4	2112.4
147.5°	1740.9	1863.9	1967.7	2052.8	2089.2	2132.0	2157.0	2168.0	2179.4	2174.3	2179.4
150°	1802.8	1916.7	2016.8	2096.5	2132.9	2173.9	2198.9	2208.0	2219.4	2212.6	2219.4
152.5°	1862.9	1971.3	2062.3	2136.6	2167.5	2208.5	2237.2	2246.3	2254.0	2249.0	2254.0
155°	1944.0	2039.6	2123.8	2192.1	2219.4	2258.1	2285.4	2296.8	2305.9	2294.5	2305.9
157.5°	2016.4	2098.8	2172.1	2234.9	2264.0	2297.3	2322.8	2336.9	2346.0	2341.0	2346.0
160°	2060.1	2135.2	2201.2	2260.4	2287.7	2317.3	2344.6	2360.5	2369.7	2362.8	2369.7
162.5°	2096.5	2164.3	2226.7	2280.4	2304.1	2330.0	2362.8	2376.9	2386.0	2377.4	2386.0
165°	2148.8	2203.5	2258.1	2303.6	2324.1	2344.6	2378.8	2394.7	2401.5	2392.4	2401.5
167.5°	2188.5	2230.3	2274.5	2313.7	2328.7	2348.7	2382.9	2396.1	2404.7	2393.3	2404.7
170°	2210.3	2246.7	2285.4	2317.3	2328.7	2346.9	2381.0	2392.4	2399.2	2387.9	2399.2
172.5°	2228.5	2255.8	2287.2	2315.5	2321.4	2336.0	2368.3	2379.7	2384.7	2375.1	2384.7
175°	2246.7	2262.7	2285.4	2303.6	2301.4	2310.5	2337.8	2346.9	2356.0	2342.3	2356.0
177.5°	2255.4	2262.7	2269.9	2280.9	2273.6	2273.6	2293.6	2299.1	2300.9	2293.6	2300.9
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1107.8	1107.2	1106.8	1109.4	1115.0	1117.7	1111.7	1105.6	1111.7	1117.7	1115.0
5°	1114.8	1112.8	1111.8	1114.1	1119.6	1121.6	1113.1	1104.5	1113.1	1121.6	1119.6
7.5°	1133.6	1129.7	1126.8	1126.7	1129.6	1128.6	1116.5	1104.3	1116.5	1128.6	1129.6
10°	1134.6	1132.4	1131.9	1132.7	1134.7	1132.6	1118.0	1103.4	1118.0	1132.6	1134.7
12.5°	1117.5	1117.0	1117.7	1122.1	1130.2	1132.0	1114.9	1097.9	1114.9	1132.0	1130.2
15°	1091.6	1089.8	1088.3	1096.3	1113.9	1122.1	1102.0	1081.9	1102.0	1122.1	1113.9
17.5°	1076.5	1071.2	1065.8	1071.5	1088.3	1095.6	1074.6	1053.6	1074.6	1095.6	1088.3
20°	1069.3	1061.9	1054.8	1058.1	1071.7	1076.7	1056.1	1035.5	1056.1	1076.7	1071.7
22.5°	1065.6	1055.2	1045.4	1046.0	1057.2	1060.4	1039.8	1019.2	1039.8	1060.4	1057.2
25°	1064.8	1049.1	1032.5	1026.9	1032.5	1032.1	1014.0	995.9	1014.0	1032.1	1032.5
27.5°	1061.3	1042.2	1019.8	1005.6	999.8	992.8	982.1	971.4	982.1	992.8	999.8
30°	1045.4	1029.8	1010.2	992.9	977.8	964.7	957.6	950.6	957.6	964.7	977.8
32.5°	1011.7	1005.1	994.7	978.0	954.8	936.4	932.2	928.0	932.2	936.4	954.8
35°	946.0	954.4	962.4	951.4	921.2	897.7	894.1	890.6	894.1	897.7	921.2
37.5°	858.9	879.3	902.8	903.1	879.9	860.8	853.5	846.3	853.5	860.8	879.9
40°	787.9	817.4	852.7	863.7	850.6	837.8	825.7	813.7	825.7	837.8	850.6
42.5°	706.6	744.1	789.0	812.7	815.3	812.5	793.2	773.8	793.2	812.5	815.3
45°	591.0	631.9	680.6	719.4	748.0	763.0	736.8	710.7	736.8	763.0	748.0
47.5°	489.9	526.5	570.1	615.2	661.7	689.9	663.1	636.2	663.1	689.9	661.7
50°	427.9	462.9	503.6	548.9	598.7	630.6	609.0	587.3	609.0	630.6	598.7
52.5°	370.4	404.9	445.7	489.7	537.1	568.7	553.1	537.5	553.1	568.7	537.1
55°	294.9	326.7	365.4	405.6	447.4	476.7	468.6	460.6	468.6	476.7	447.4
57.5°	238.3	265.0	297.9	333.7	372.5	400.2	395.1	390.0	395.1	400.2	372.5
60°	208.9	229.7	255.4	287.6	326.3	354.5	350.9	347.4	350.9	354.5	326.3
62.5°	183.9	200.5	220.9	249.6	286.8	313.9	311.2	308.5	311.2	313.9	286.8
65°	151.9	164.5	180.1	203.7	235.4	258.5	256.0	253.5	256.0	258.5	235.4
67.5°	126.1	136.2	148.5	167.5	193.4	212.4	211.1	209.8	211.1	212.4	193.4
70°	109.1	118.1	129.1	146.0	168.6	185.5	185.0	184.5	185.0	185.5	168.6
72.5°	94.9	102.1	111.1	125.6	145.4	160.4	161.1	161.8	161.1	160.4	145.4
75°	74.4	79.2	85.3	96.3	112.4	124.9	126.4	127.9	126.4	124.9	112.4
77.5°	57.5	59.0	61.0	68.7	81.9	92.3	93.9	95.5	93.9	92.3	81.9
80°	47.5	47.5	47.5	52.6	62.6	70.7	72.7	74.7	72.7	70.7	62.6
82.5°	36.6	36.7	36.7	39.5	45.1	50.0	52.9	55.7	52.9	50.0	45.1
85°	14.3	17.0	20.0	21.5	21.5	22.1	24.6	27.2	24.6	22.1	21.5
87.5°	12.3	11.8	11.8	12.4	13.0	12.7	10.4	8.6	10.4	12.3	13.9
90°	47.8	45.5	45.5	43.3	36.4	27.3	15.9	6.8	15.9	25.0	41.0
92.5°	56.9	56.5	52.8	48.7	40.1	40.1	39.6	25.0	43.3	61.5	88.3
95°	52.4	52.4	61.5	77.4	113.8	116.1	77.4	70.6	100.2	141.1	177.6
97.5°	141.6	168.4	206.7	214.0	202.6	151.1	144.8	134.8	183.5	224.0	282.7
100°	261.8	295.9	323.2	268.6	211.7	209.4	195.8	191.2	243.6	282.3	339.2
102.5°	409.3	419.8	325.1	294.1	280.9	271.3	250.4	247.7	300.0	353.3	401.1
105°	443.9	398.4	400.6	400.6	391.5	373.3	334.6	332.3	391.5	453.0	512.2
107.5°	522.2	529.0	540.9	538.1	527.7	478.9	433.4	422.9	476.2	550.0	615.1
110°	626.0	632.8	637.4	632.8	616.9	555.4	500.8	484.9	532.7	610.1	680.6



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	726.1	731.2	741.2	727.5	700.7	630.1	568.2	545.0	592.8	672.0	744.4
115°	885.5	885.5	887.8	880.9	826.3	753.5	671.5	637.4	678.3	751.2	830.9
117.5°	1042.1	1044.8	1035.7	1017.5	954.2	869.6	777.6	723.0	755.3	832.2	914.2
120°	1140.4	1145.0	1135.9	1108.6	1047.1	951.5	846.8	783.1	808.1	883.2	965.2
122.5°	1242.4	1241.5	1230.6	1199.6	1127.2	1028.0	925.1	846.8	857.3	926.9	1007.0
125°	1384.0	1381.7	1372.6	1336.2	1261.1	1158.6	1038.0	942.4	928.7	987.9	1069.9
127.5°	1518.8	1513.8	1499.6	1455.5	1378.5	1279.7	1147.3	1038.9	1008.4	1045.7	1120.9
130°	1611.6	1604.8	1579.8	1532.0	1456.8	1363.5	1229.2	1106.3	1063.0	1085.8	1151.8
132.5°	1700.9	1681.3	1659.9	1608.4	1538.8	1441.8	1305.7	1177.3	1117.7	1127.7	1179.1
135°	1814.2	1796.0	1768.7	1718.6	1652.6	1557.0	1420.4	1281.6	1199.6	1190.5	1220.1
137.5°	1913.9	1894.8	1863.9	1820.6	1754.1	1669.0	1537.9	1391.3	1287.9	1257.4	1268.8
140°	1975.8	1953.1	1925.8	1882.5	1823.3	1734.6	1607.1	1466.0	1349.9	1306.6	1299.8
142.5°	2026.8	2009.5	1980.4	1940.8	1888.9	1800.1	1676.3	1537.0	1413.6	1357.6	1341.7
145°	2103.3	2089.7	2057.8	2021.4	1978.1	1889.3	1775.5	1636.7	1513.8	1440.9	1406.8
147.5°	2168.0	2157.0	2132.0	2089.2	2052.8	1967.7	1863.9	1740.9	1614.8	1524.7	1480.5
150°	2208.0	2198.9	2173.9	2132.9	2096.5	2016.8	1916.7	1802.8	1682.2	1586.6	1529.7
152.5°	2246.3	2237.2	2208.5	2167.5	2136.6	2062.3	1971.3	1862.9	1740.5	1644.9	1586.1
155°	2296.8	2285.4	2258.1	2219.4	2192.1	2123.8	2039.6	1944.0	1839.3	1739.1	1673.1
157.5°	2336.9	2322.8	2297.3	2264.0	2234.9	2172.1	2098.8	2016.4	1924.9	1829.3	1761.9
160°	2360.5	2344.6	2317.3	2287.7	2260.4	2201.2	2135.2	2060.1	1975.8	1889.3	1816.5
162.5°	2376.9	2362.8	2330.0	2304.1	2280.4	2226.7	2164.3	2096.5	2021.4	1945.8	1878.4
165°	2394.7	2378.8	2344.6	2324.1	2303.6	2258.1	2203.5	2148.8	2085.1	2023.7	1969.0
167.5°	2396.1	2382.9	2348.7	2328.7	2313.7	2274.5	2230.3	2188.5	2138.8	2090.6	2045.0
170°	2392.4	2381.0	2346.9	2328.7	2317.3	2285.4	2246.7	2210.3	2171.6	2130.6	2094.2
172.5°	2379.7	2368.3	2336.0	2321.4	2315.5	2287.2	2255.8	2228.5	2195.3	2165.2	2136.1
175°	2346.9	2337.8	2310.5	2301.4	2303.6	2285.4	2262.7	2246.7	2226.2	2208.0	2192.1
177.5°	2299.1	2293.6	2273.6	2273.6	2280.9	2269.9	2262.7	2255.4	2246.3	2240.8	2235.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1109.4	1106.8	1107.2	1107.8	1109.0	1110.2	1109.0	1107.8	1107.2	1106.8	1109.4
5°	1114.1	1111.8	1112.8	1114.8	1119.9	1124.9	1119.9	1114.8	1112.8	1111.8	1114.1
7.5°	1126.7	1126.8	1129.7	1133.6	1140.2	1146.8	1140.2	1133.6	1129.7	1126.8	1126.7
10°	1132.7	1131.9	1132.4	1134.6	1141.6	1148.6	1141.6	1134.6	1132.4	1131.9	1132.7
12.5°	1122.1	1117.7	1117.0	1117.5	1121.3	1125.1	1121.3	1117.5	1117.0	1117.7	1122.1
15°	1096.3	1088.3	1089.8	1091.6	1094.1	1096.6	1094.1	1091.6	1089.8	1088.3	1096.3
17.5°	1071.5	1065.8	1071.2	1076.5	1081.5	1086.4	1081.5	1076.5	1071.2	1065.8	1071.5
20°	1058.1	1054.8	1061.9	1069.3	1077.9	1086.4	1077.9	1069.3	1061.9	1054.8	1058.1
22.5°	1046.0	1045.4	1055.2	1065.6	1077.4	1089.1	1077.4	1065.6	1055.2	1045.4	1046.0
25°	1026.9	1032.5	1049.1	1064.8	1077.9	1090.9	1077.9	1064.8	1049.1	1032.5	1026.9
27.5°	1005.6	1019.8	1042.2	1061.3	1070.5	1079.6	1070.5	1061.3	1042.2	1019.8	1005.6
30°	992.9	1010.2	1029.8	1045.4	1048.9	1052.5	1048.9	1045.4	1029.8	1010.2	992.9
32.5°	978.0	994.7	1005.1	1011.7	1007.2	1002.7	1007.2	1011.7	1005.1	994.7	978.0
35°	951.4	962.4	954.4	946.0	936.4	926.8	936.4	946.0	954.4	962.4	951.4
37.5°	903.1	902.8	879.3	858.9	848.0	837.0	848.0	858.9	879.3	902.8	903.1
40°	863.7	852.7	817.4	787.9	775.3	762.7	775.3	787.9	817.4	852.7	863.7
42.5°	812.7	789.0	744.1	706.6	691.2	675.8	691.2	706.6	744.1	789.0	812.7
45°	719.4	680.6	631.9	591.0	573.9	556.8	573.9	591.0	631.9	680.6	719.4
47.5°	615.2	570.1	526.5	489.9	473.9	457.9	473.9	489.9	526.5	570.1	615.2
50°	548.9	503.6	462.9	427.9	410.3	392.7	410.3	427.9	462.9	503.6	548.9
52.5°	489.7	445.7	404.9	370.4	354.4	338.4	354.4	370.4	404.9	445.7	489.7
55°	405.6	365.4	326.7	294.9	283.8	272.7	283.8	294.9	326.7	365.4	405.6
57.5°	333.7	297.9	265.0	238.3	230.2	222.0	230.2	238.3	265.0	297.9	333.7
60°	287.6	255.4	229.7	208.9	202.3	195.8	202.3	208.9	229.7	255.4	287.6
62.5°	249.6	220.9	200.5	183.9	179.0	174.1	179.0	183.9	200.5	220.9	249.6
65°	203.7	180.1	164.5	151.9	148.4	144.9	148.4	151.9	164.5	180.1	203.7
67.5°	167.5	148.5	136.2	126.1	122.8	119.5	122.8	126.1	136.2	148.5	167.5
70°	146.0	129.1	118.1	109.1	106.6	104.1	106.6	109.1	118.1	129.1	146.0
72.5°	125.6	111.1	102.1	94.9	93.1	91.4	93.1	94.9	102.1	111.1	125.6
75°	96.3	85.3	79.2	74.4	73.4	72.4	73.4	74.4	79.2	85.3	96.3
77.5°	68.7	61.0	59.0	57.5	57.5	57.5	57.5	57.5	59.0	61.0	68.7
80°	52.6	47.5	47.5	47.5	47.5	47.5	47.5	47.5	47.5	47.5	52.6
82.5°	39.5	36.7	36.7	36.6	36.2	35.8	36.2	36.6	36.7	36.7	39.5
85°	21.5	20.0	17.0	14.3	12.8	11.3	12.8	14.3	17.0	20.0	21.5
87.5°	14.2	16.4	19.6	21.4	23.2	22.3	23.2	21.4	19.6	16.4	14.2
90°	52.4	68.3	84.2	93.3	102.4	97.9	102.4	93.3	84.2	68.3	52.4
92.5°	105.2	132.0	151.6	168.0	175.3	174.4	175.3	168.0	151.6	132.0	105.2
95°	211.7	243.6	275.4	298.2	311.9	307.3	311.9	298.2	275.4	243.6	211.7
97.5°	326.4	369.2	404.7	426.1	439.8	448.9	439.8	426.1	404.7	369.2	326.4
100°	402.9	443.9	484.9	509.9	532.7	541.8	532.7	509.9	484.9	443.9	402.9
102.5°	464.8	518.5	563.2	590.0	609.1	618.2	609.1	590.0	563.2	518.5	464.8
105°	566.8	623.7	671.5	705.7	726.1	733.0	726.1	705.7	671.5	623.7	566.8
107.5°	668.8	727.5	771.7	809.5	834.5	849.1	834.5	809.5	771.7	727.5	668.8
110°	748.9	796.7	844.5	878.7	903.7	912.8	903.7	878.7	844.5	796.7	748.9



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	816.3	869.6	917.4	951.5	980.2	992.9	980.2	951.5	917.4	869.6	816.3
115°	910.5	981.1	1024.3	1056.2	1076.7	1088.1	1076.7	1056.2	1024.3	981.1	910.5
117.5°	988.8	1062.6	1109.9	1134.5	1144.1	1152.3	1144.1	1134.5	1109.9	1062.6	988.8
120°	1038.0	1106.3	1160.9	1192.8	1204.2	1208.7	1204.2	1192.8	1160.9	1106.3	1038.0
122.5°	1083.5	1148.2	1201.0	1240.1	1258.8	1263.4	1258.8	1240.1	1201.0	1148.2	1083.5
125°	1147.3	1208.7	1263.4	1302.1	1322.5	1333.9	1322.5	1302.1	1263.4	1208.7	1147.3
127.5°	1202.8	1269.3	1319.4	1354.4	1374.4	1383.5	1374.4	1354.4	1319.4	1269.3	1202.8
130°	1233.8	1302.1	1352.1	1390.8	1409.0	1418.1	1409.0	1390.8	1352.1	1302.1	1233.8
132.5°	1257.4	1329.4	1381.3	1416.3	1436.4	1445.5	1436.4	1416.3	1381.3	1329.4	1257.4
135°	1286.1	1361.2	1415.9	1450.0	1468.2	1477.3	1468.2	1450.0	1415.9	1361.2	1286.1
137.5°	1311.2	1379.5	1436.4	1472.3	1488.7	1494.6	1488.7	1472.3	1436.4	1379.5	1311.2
140°	1329.4	1388.6	1445.5	1479.6	1497.8	1500.1	1497.8	1479.6	1445.5	1388.6	1329.4
142.5°	1353.0	1399.5	1449.1	1483.3	1501.5	1505.6	1501.5	1483.3	1449.1	1399.5	1353.0
145°	1395.4	1422.7	1456.8	1488.7	1504.6	1509.2	1504.6	1488.7	1456.8	1422.7	1395.4
147.5°	1448.7	1457.3	1475.1	1496.0	1511.5	1514.7	1511.5	1496.0	1475.1	1457.3	1448.7
150°	1488.7	1486.4	1493.3	1506.9	1520.6	1518.3	1520.6	1506.9	1493.3	1486.4	1488.7
152.5°	1534.2	1521.0	1520.6	1527.0	1533.3	1532.9	1533.3	1527.0	1520.6	1521.0	1534.2
155°	1611.6	1586.6	1572.9	1568.4	1568.4	1566.1	1568.4	1568.4	1572.9	1586.6	1611.6
157.5°	1696.8	1661.7	1641.2	1630.3	1627.1	1622.1	1627.1	1630.3	1641.2	1661.7	1696.8
160°	1755.0	1716.3	1695.9	1677.6	1670.8	1664.0	1670.8	1677.6	1695.9	1716.3	1755.0
162.5°	1809.7	1772.8	1750.5	1734.1	1727.3	1716.8	1727.3	1734.1	1750.5	1772.8	1809.7
165°	1898.5	1859.8	1834.7	1821.1	1812.0	1802.8	1812.0	1821.1	1834.7	1859.8	1898.5
167.5°	1987.2	1944.9	1928.5	1913.0	1904.4	1888.0	1904.4	1913.0	1928.5	1944.9	1987.2
170°	2041.9	2003.2	1994.1	1980.4	1964.5	1946.3	1964.5	1980.4	1994.1	2003.2	2041.9
172.5°	2089.2	2063.3	2054.2	2040.5	2035.5	2020.9	2035.5	2040.5	2054.2	2063.3	2089.2
175°	2158.0	2137.5	2137.5	2135.2	2128.4	2114.7	2128.4	2135.2	2137.5	2137.5	2158.0
177.5°	2215.3	2204.4	2211.7	2211.7	2209.9	2197.1	2209.9	2211.7	2211.7	2204.4	2215.3
180°	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1110.2	1110.2	1110.2	1110.2
2.5°	1115.0	1117.7	1111.7	1105.6
5°	1119.6	1121.6	1113.1	1104.5
7.5°	1129.6	1128.6	1116.5	1104.3
10°	1134.7	1132.6	1118.0	1103.4
12.5°	1130.2	1132.0	1114.9	1097.9
15°	1113.9	1122.1	1102.0	1081.9
17.5°	1088.3	1095.6	1074.6	1053.6
20°	1071.7	1076.7	1056.1	1035.5
22.5°	1057.2	1060.4	1039.8	1019.2
25°	1032.5	1032.1	1014.0	995.9
27.5°	999.8	992.8	982.1	971.4
30°	977.8	964.7	957.6	950.6
32.5°	954.8	936.4	932.2	928.0
35°	921.2	897.7	894.1	890.6
37.5°	879.9	860.8	853.5	846.3
40°	850.6	837.8	825.7	813.7
42.5°	815.3	812.5	793.2	773.8
45°	748.0	763.0	736.8	710.7
47.5°	661.7	689.9	663.1	636.2
50°	598.7	630.6	609.0	587.3
52.5°	537.1	568.7	553.1	537.5
55°	447.4	476.7	468.6	460.6
57.5°	372.5	400.2	395.1	390.0
60°	326.3	354.5	350.9	347.4
62.5°	286.8	313.9	311.2	308.5
65°	235.4	258.5	256.0	253.5
67.5°	193.4	212.4	211.1	209.8
70°	168.6	185.5	185.0	184.5
72.5°	145.4	160.4	161.1	161.8
75°	112.4	124.9	126.4	127.9
77.5°	81.9	92.3	93.9	95.5
80°	62.6	70.7	72.7	74.7
82.5°	45.1	50.0	52.9	55.7
85°	21.5	22.1	24.6	27.2
87.5°	13.9	12.3	10.4	8.6
90°	41.0	25.0	15.9	6.8
92.5°	88.3	61.5	43.3	25.0
95°	177.6	141.1	100.2	70.6
97.5°	282.7	224.0	183.5	134.8
100°	339.2	282.3	243.6	191.2
102.5°	401.1	353.3	300.0	247.7
105°	512.2	453.0	391.5	332.3
107.5°	615.1	550.0	476.2	422.9
110°	680.6	610.1	532.7	484.9



TEST NUMBER: P1428300

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	744.4	672.0	592.8	545.0
115°	830.9	751.2	678.3	637.4
117.5°	914.2	832.2	755.3	723.0
120°	965.2	883.2	808.1	783.1
122.5°	1007.0	926.9	857.3	846.8
125°	1069.9	987.9	928.7	942.4
127.5°	1120.9	1045.7	1008.4	1038.9
130°	1151.8	1085.8	1063.0	1106.3
132.5°	1179.1	1127.7	1117.7	1177.3
135°	1220.1	1190.5	1199.6	1281.6
137.5°	1268.8	1257.4	1287.9	1391.3
140°	1299.8	1306.6	1349.9	1466.0
142.5°	1341.7	1357.6	1413.6	1537.0
145°	1406.8	1440.9	1513.8	1636.7
147.5°	1480.5	1524.7	1614.8	1740.9
150°	1529.7	1586.6	1682.2	1802.8
152.5°	1586.1	1644.9	1740.5	1862.9
155°	1673.1	1739.1	1839.3	1944.0
157.5°	1761.9	1829.3	1924.9	2016.4
160°	1816.5	1889.3	1975.8	2060.1
162.5°	1878.4	1945.8	2021.4	2096.5
165°	1969.0	2023.7	2085.1	2148.8
167.5°	2045.0	2090.6	2138.8	2188.5
170°	2094.2	2130.6	2171.6	2210.3
172.5°	2136.1	2165.2	2195.3	2228.5
175°	2192.1	2208.0	2226.2	2246.7
177.5°	2235.3	2240.8	2246.3	2255.4
180°	2253.6	2253.6	2253.6	2253.6



TEST NUMBER: P1428300
 CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.31	14.99	15.43	16.10	17.65	10.68	11.36	11.80	12.47	14.02
	3H	15.50	16.11	16.63	17.23	18.79	11.83	12.43	12.96	13.55	15.12
	4H	15.98	16.55	17.12	17.68	19.24	12.28	12.86	13.42	13.98	15.55
	6H	16.27	16.80	17.42	17.92	19.50	12.61	13.14	13.76	14.27	15.85
	8H	16.36	16.87	17.52	18.01	19.58	12.74	13.25	13.90	14.39	15.96
	12H	16.40	16.88	17.56	18.01	19.60	12.77	13.25	13.93	14.38	15.97
4H	2H	14.39	14.96	15.54	16.09	17.65	11.37	11.94	12.52	13.06	14.63
	3H	15.83	16.31	16.99	17.46	19.04	12.70	13.18	13.86	14.33	15.91
	4H	16.45	16.89	17.61	18.03	19.63	13.24	13.68	14.40	14.82	16.42
	6H	16.88	17.25	18.04	18.41	20.00	13.67	14.04	14.83	15.20	16.79
	8H	17.03	17.38	18.19	18.53	20.14	13.85	14.20	15.01	15.35	16.95
	12H	17.09	17.41	18.27	18.57	20.18	13.89	14.20	15.06	15.37	16.98
8H	4H	16.47	16.82	17.63	17.97	19.58	13.56	13.91	14.72	15.06	16.67
	6H	16.99	17.28	18.18	18.48	20.08	14.09	14.38	15.27	15.58	17.18
	8H	17.23	17.48	18.41	18.65	20.28	14.35	14.61	15.54	15.78	17.40
	12H	17.34	17.56	18.53	18.73	20.39	14.44	14.66	15.63	15.83	17.49
12H	4H	16.42	16.74	17.60	17.90	19.51	13.57	13.89	14.75	15.05	16.66
	6H	16.98	17.24	18.17	18.41	20.03	14.16	14.42	15.35	15.59	17.21
	8H	17.23	17.45	18.42	18.62	20.27	14.45	14.67	15.64	15.84	17.49