

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428255

Luminaire Tested: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428255
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6231.9 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	96	91	88	85	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	75	70	79	73	68	64	60	56	53	48	45	43	36	35	33	28				
3	80	71	64	59	72	65	59	54	53	49	45	42	40	37	32	31	29	24				
4	73	63	56	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21				
5	67	56	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19				
6	62	50	43	37	56	46	40	35	38	33	30	31	27	25	24	22	20	17				
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				
9	49	38	31	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12				
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15839	15839	15839	15839
5°	15818	16110	15818	16110
10°	15985	16641	15985	16641
15°	15980	16197	15980	16197
20°	15721	16494	15721	16494
25°	15677	17173	15677	17173
30°	15660	17338	15660	17338
35°	15512	16143	15512	16143
40°	15154	14206	15154	14206
45°	14339	11234	14339	11234
50°	13036	8716	13036	8716
55°	11457	6784	11457	6784
60°	9913	5586	9913	5586
65°	8558	4890	8558	4890
70°	7695	4343	7695	4343
75°	7049	3992	7049	3992
80°	6137	3905	6137	3905
85°	4446	1852	4446	1852

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 15394 cd/sqm



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.5
10°-20°	274.3	4.4
20°-30°	423.9	6.8
30°-40°	509.8	8.2
40°-50°	457.8	7.3
50°-60°	306.8	4.9
60°-70°	178.5	2.9
70°-80°	91.7	1.5
80°-90°	28.1	0.5
90°-100°	105.4	1.7
100°-110°	307.3	4.9
110°-120°	501.5	8.0
120°-130°	636.4	10.2
130°-140°	681.0	10.9
140°-150°	635.9	10.2
150°-160°	523.2	8.4
160°-170°	350.9	5.6
170°-180°	124.6	2.0
0°-30°	792.9	12.7
0°-40°	1302.8	20.9
0°-60°	2067.4	33.2
0°-90°	2365.6	38.0
90°-120°	914.2	14.7
90°-150°	2867.5	46.0
90°-180°	3866.0	62.0
0°-180°	6231.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	976	994	976	994	976	93
15°	956	969	956	969	956	268
25°	880	964	880	964	880	406
35°	787	819	787	819	787	491
45°	628	492	628	492	628	480
55°	407	241	407	241	407	366
65°	224	128	224	128	224	227
75°	113	64	113	64	113	120
85°	24	10	24	10	24	30
90°	4	29	4	58	4	4
95°	42	31	42	181	42	50
105°	195	313	195	431	195	208
115°	374	519	374	639	374	369
125°	554	823	554	784	554	495
135°	753	1077	753	868	753	582
145°	962	1241	962	887	962	602
155°	1142	1348	1142	920	1142	525
165°	1263	1406	1263	1059	1263	355
175°	1320	1376	1320	1243	1320	125
180°	1324	1324	1324	1324	1324	



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0
2.5°	977.0	982.3	987.7	985.3	980.3	978.0	978.3	978.9	979.9	981.0	979.9
5°	976.0	983.6	991.1	989.3	984.5	982.5	983.3	985.1	989.6	994.0	989.6
7.5°	975.8	986.6	997.3	998.1	995.7	995.7	998.3	1001.7	1007.5	1013.4	1007.5
10°	975.0	987.9	1000.8	1002.7	1000.9	1000.2	1000.7	1002.6	1008.8	1015.0	1008.8
12.5°	970.2	985.2	1000.3	998.7	991.6	987.7	987.1	987.5	990.8	994.2	990.8
15°	956.0	973.8	991.6	984.3	968.8	961.7	963.0	964.6	966.8	969.0	966.8
17.5°	931.0	949.6	968.2	961.7	946.8	941.8	946.6	951.3	955.7	960.0	955.7
20°	915.0	933.2	951.5	947.0	935.0	932.1	938.3	944.9	952.5	960.0	952.5
22.5°	900.6	918.8	937.1	934.2	924.3	923.8	932.5	941.6	952.0	962.4	952.0
25°	880.0	896.0	912.0	912.3	907.5	912.3	927.0	940.9	952.5	964.0	952.5
27.5°	858.4	867.8	877.3	883.5	888.6	901.1	920.9	937.8	945.9	954.0	945.9
30°	840.0	846.2	852.5	864.0	877.3	892.7	910.0	923.8	926.9	930.0	926.9
32.5°	820.0	823.7	827.5	843.7	864.2	879.0	888.1	894.0	890.0	886.0	890.0
35°	787.0	790.1	793.2	814.0	840.7	850.5	843.3	835.9	827.5	819.0	827.5
37.5°	747.8	754.2	760.6	777.5	798.0	797.8	777.0	759.0	749.3	739.6	749.3
40°	719.0	729.7	740.3	751.7	763.2	753.5	722.3	696.2	685.1	674.0	685.1
42.5°	683.8	700.9	717.9	720.5	718.2	697.2	657.5	624.4	610.8	597.2	610.8
45°	628.0	651.1	674.2	661.0	635.7	601.4	558.3	522.2	507.1	492.0	507.1
47.5°	562.2	585.9	609.7	584.7	543.6	503.8	465.3	432.9	418.7	404.6	418.7
50°	519.0	538.1	557.2	529.0	485.0	445.0	409.0	378.1	362.6	347.0	362.6
52.5°	475.0	488.8	502.6	474.6	432.7	393.8	357.8	327.3	313.1	299.0	313.1
55°	407.0	414.1	421.2	395.3	358.4	322.9	288.7	260.6	250.8	241.0	250.8
57.5°	344.6	349.1	353.7	329.1	294.9	263.3	234.2	210.6	203.4	196.2	203.4
60°	307.0	310.1	313.2	288.3	254.1	225.7	203.0	184.6	178.8	173.0	178.8
62.5°	272.6	275.0	277.4	253.4	220.6	195.2	177.1	162.5	158.2	153.8	158.2
65°	224.0	226.2	228.4	208.0	180.0	159.1	145.3	134.2	131.1	128.0	131.1
67.5°	185.4	186.6	187.7	170.9	148.0	131.2	120.3	111.5	108.5	105.6	108.5
70°	163.0	163.4	163.9	149.0	129.0	114.1	104.3	96.4	94.2	92.0	94.2
72.5°	143.0	142.4	141.8	128.5	111.0	98.2	90.2	83.8	82.3	80.8	82.3
75°	113.0	111.7	110.3	99.3	85.1	75.3	70.0	65.8	64.9	64.0	64.9
77.5°	84.4	83.0	81.6	72.4	60.7	53.9	52.1	50.8	50.8	50.8	50.8
80°	66.0	64.2	62.4	55.3	46.4	42.0	42.0	42.0	42.0	42.0	42.0
82.5°	49.2	46.7	44.2	39.9	34.9	32.4	32.4	32.3	32.0	31.6	32.0
85°	24.0	21.8	19.6	19.0	19.0	17.7	15.0	12.7	11.3	10.0	11.3
87.5°	7.2	8.3	9.6	9.3	8.4	7.8	7.8	8.0	8.3	8.3	8.3
90°	4.0	9.4	16.1	21.4	25.4	26.8	26.8	28.1	29.4	29.4	29.4
92.5°	14.7	23.3	23.5	23.5	28.6	31.0	33.2	33.4	34.8	34.8	34.8
95°	41.5	45.5	68.2	66.9	45.5	36.1	30.8	30.8	30.8	30.8	30.8
97.5°	79.2	85.1	88.8	119.0	125.7	121.4	99.0	83.2	74.4	70.4	74.4
100°	112.4	115.0	123.1	124.4	157.8	189.9	173.9	153.8	147.1	143.1	147.1
102.5°	145.5	147.1	159.4	165.1	172.8	191.0	246.6	240.5	235.9	235.1	235.9
105°	195.3	196.6	219.4	230.1	235.4	235.4	234.1	260.8	303.6	313.0	303.6
107.5°	248.5	254.7	281.4	310.0	316.2	317.8	310.8	306.8	305.2	306.3	305.2
110°	284.9	294.3	326.4	362.5	371.8	374.5	371.8	367.8	365.1	365.1	365.1



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	320.2	333.9	370.2	411.7	427.5	435.5	429.6	426.7	424.0	426.1	424.0
115°	374.5	394.6	442.7	485.5	517.6	521.6	520.3	520.3	519.0	519.0	519.0
117.5°	424.8	456.9	510.9	560.7	597.9	608.6	613.9	612.3	610.7	613.4	610.7
120°	460.1	497.6	559.1	615.3	651.4	667.4	672.8	670.1	672.8	670.1	672.8
122.5°	497.6	543.6	604.0	662.4	704.9	723.1	729.5	730.0	730.6	729.0	730.6
125°	553.7	609.9	680.8	741.0	785.1	806.5	811.9	813.2	815.9	822.6	815.9
127.5°	610.5	674.1	752.0	810.0	855.2	881.2	889.5	892.4	898.0	901.0	898.0
130°	650.0	722.3	801.2	856.0	900.2	928.3	943.0	947.0	953.7	952.3	953.7
132.5°	691.8	767.2	847.2	904.2	945.1	975.3	987.9	999.4	1001.8	1003.7	1001.8
135°	753.0	834.6	914.9	971.1	1009.8	1039.3	1055.3	1066.0	1072.7	1076.7	1072.7
137.5°	817.5	903.6	980.7	1030.7	1069.8	1095.2	1113.4	1124.6	1131.6	1134.8	1131.6
140°	861.4	944.3	1019.2	1071.4	1106.1	1131.6	1147.6	1161.0	1169.0	1169.0	1169.0
142.5°	903.1	985.0	1057.7	1109.9	1140.4	1163.7	1180.8	1190.9	1200.0	1200.0	1200.0
145°	961.7	1043.3	1110.2	1162.3	1187.7	1209.1	1227.9	1235.9	1241.2	1241.2	1241.2
147.5°	1023.0	1095.2	1156.2	1206.2	1227.6	1252.7	1267.5	1273.9	1280.6	1277.6	1280.6
150°	1059.3	1126.2	1185.1	1231.9	1253.3	1277.4	1292.1	1297.4	1304.1	1300.1	1304.1
152.5°	1094.6	1158.3	1211.8	1255.4	1273.6	1297.7	1314.5	1319.9	1324.4	1321.5	1324.4
155°	1142.3	1198.4	1247.9	1288.1	1304.1	1326.8	1342.9	1349.6	1354.9	1348.2	1354.9
157.5°	1184.8	1233.2	1276.3	1313.2	1330.3	1349.9	1364.8	1373.1	1378.5	1375.5	1378.5
160°	1210.5	1254.6	1293.4	1328.2	1344.2	1361.6	1377.7	1387.0	1392.4	1388.4	1392.4
162.5°	1231.9	1271.7	1308.4	1340.0	1353.9	1369.1	1388.4	1396.7	1402.0	1396.9	1402.0
165°	1262.6	1294.7	1326.8	1353.6	1365.6	1377.7	1397.7	1407.1	1411.1	1405.8	1411.1
167.5°	1285.9	1310.5	1336.5	1359.5	1368.3	1380.1	1400.1	1407.9	1413.0	1406.3	1413.0
170°	1298.8	1320.2	1342.9	1361.6	1368.3	1379.0	1399.1	1405.8	1409.8	1403.1	1409.8
172.5°	1309.5	1325.5	1344.0	1360.6	1364.0	1372.6	1391.6	1398.3	1401.2	1395.6	1401.2
175°	1320.2	1329.5	1342.9	1353.6	1352.3	1357.6	1373.7	1379.0	1384.4	1376.3	1384.4
177.5°	1325.2	1329.5	1333.8	1340.2	1335.9	1335.9	1347.7	1350.9	1352.0	1347.7	1352.0
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0
2.5°	978.9	978.3	978.0	980.3	985.3	987.7	982.3	977.0	982.3	987.7	985.3
5°	985.1	983.3	982.5	984.5	989.3	991.1	983.6	976.0	983.6	991.1	989.3
7.5°	1001.7	998.3	995.7	995.7	998.1	997.3	986.6	975.8	986.6	997.3	998.1
10°	1002.6	1000.7	1000.2	1000.9	1002.7	1000.8	987.9	975.0	987.9	1000.8	1002.7
12.5°	987.5	987.1	987.7	991.6	998.7	1000.3	985.2	970.2	985.2	1000.3	998.7
15°	964.6	963.0	961.7	968.8	984.3	991.6	973.8	956.0	973.8	991.6	984.3
17.5°	951.3	946.6	941.8	946.8	961.7	968.2	949.6	931.0	949.6	968.2	961.7
20°	944.9	938.3	932.1	935.0	947.0	951.5	933.2	915.0	933.2	951.5	947.0
22.5°	941.6	932.5	923.8	924.3	934.2	937.1	918.8	900.6	918.8	937.1	934.2
25°	940.9	927.0	912.3	907.5	912.3	912.0	896.0	880.0	896.0	912.0	912.3
27.5°	937.8	920.9	901.1	888.6	883.5	877.3	867.8	858.4	867.8	877.3	883.5
30°	923.8	910.0	892.7	877.3	864.0	852.5	846.2	840.0	846.2	852.5	864.0
32.5°	894.0	888.1	879.0	864.2	843.7	827.5	823.7	820.0	823.7	827.5	843.7
35°	835.9	843.3	850.5	840.7	814.0	793.2	790.1	787.0	790.1	793.2	814.0
37.5°	759.0	777.0	797.8	798.0	777.5	760.6	754.2	747.8	754.2	760.6	777.5
40°	696.2	722.3	753.5	763.2	751.7	740.3	729.7	719.0	729.7	740.3	751.7
42.5°	624.4	657.5	697.2	718.2	720.5	717.9	700.9	683.8	700.9	717.9	720.5
45°	522.2	558.3	601.4	635.7	661.0	674.2	651.1	628.0	651.1	674.2	661.0
47.5°	432.9	465.3	503.8	543.6	584.7	609.7	585.9	562.2	585.9	609.7	584.7
50°	378.1	409.0	445.0	485.0	529.0	557.2	538.1	519.0	538.1	557.2	529.0
52.5°	327.3	357.8	393.8	432.7	474.6	502.6	488.8	475.0	488.8	502.6	474.6
55°	260.6	288.7	322.9	358.4	395.3	421.2	414.1	407.0	414.1	421.2	395.3
57.5°	210.6	234.2	263.3	294.9	329.1	353.7	349.1	344.6	349.1	353.7	329.1
60°	184.6	203.0	225.7	254.1	288.3	313.2	310.1	307.0	310.1	313.2	288.3
62.5°	162.5	177.1	195.2	220.6	253.4	277.4	275.0	272.6	275.0	277.4	253.4
65°	134.2	145.3	159.1	180.0	208.0	228.4	226.2	224.0	226.2	228.4	208.0
67.5°	111.5	120.3	131.2	148.0	170.9	187.7	186.6	185.4	186.6	187.7	170.9
70°	96.4	104.3	114.1	129.0	149.0	163.9	163.4	163.0	163.4	163.9	149.0
72.5°	83.8	90.2	98.2	111.0	128.5	141.8	142.4	143.0	142.4	141.8	128.5
75°	65.8	70.0	75.3	85.1	99.3	110.3	111.7	113.0	111.7	110.3	99.3
77.5°	50.8	52.1	53.9	60.7	72.4	81.6	83.0	84.4	83.0	81.6	72.4
80°	42.0	42.0	42.0	46.4	55.3	62.4	64.2	66.0	64.2	62.4	55.3
82.5°	32.3	32.4	32.4	34.9	39.9	44.2	46.7	49.2	46.7	44.2	39.9
85°	12.7	15.0	17.7	19.0	19.0	19.6	21.8	24.0	21.8	19.6	19.0
87.5°	8.0	7.8	7.8	8.4	9.3	9.6	8.3	7.2	8.3	9.3	9.9
90°	28.1	26.8	26.8	25.4	21.4	16.1	9.4	4.0	9.4	14.7	24.1
92.5°	33.4	33.2	31.0	28.6	23.5	23.5	23.3	14.7	25.4	36.1	51.9
95°	30.8	30.8	36.1	45.5	66.9	68.2	45.5	41.5	58.9	82.9	104.3
97.5°	83.2	99.0	121.4	125.7	119.0	88.8	85.1	79.2	107.8	131.6	166.1
100°	153.8	173.9	189.9	157.8	124.4	123.1	115.0	112.4	143.1	165.9	199.3
102.5°	240.5	246.6	191.0	172.8	165.1	159.4	147.1	145.5	176.3	207.6	235.7
105°	260.8	234.1	235.4	235.4	230.1	219.4	196.6	195.3	230.1	266.2	300.9
107.5°	306.8	310.8	317.8	316.2	310.0	281.4	254.7	248.5	279.8	323.2	361.4
110°	367.8	371.8	374.5	371.8	362.5	326.4	294.3	284.9	313.0	358.5	399.9



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	426.7	429.6	435.5	427.5	411.7	370.2	333.9	320.2	348.3	394.8	437.4
115°	520.3	520.3	521.6	517.6	485.5	442.7	394.6	374.5	398.6	441.4	488.2
117.5°	612.3	613.9	608.6	597.9	560.7	510.9	456.9	424.8	443.8	489.0	537.2
120°	670.1	672.8	667.4	651.4	615.3	559.1	497.6	460.1	474.8	519.0	567.1
122.5°	730.0	729.5	723.1	704.9	662.4	604.0	543.6	497.6	503.7	544.6	591.7
125°	813.2	811.9	806.5	785.1	741.0	680.8	609.9	553.7	545.7	580.5	628.6
127.5°	892.4	889.5	881.2	855.2	810.0	752.0	674.1	610.5	592.5	614.5	658.6
130°	947.0	943.0	928.3	900.2	856.0	801.2	722.3	650.0	624.6	638.0	676.8
132.5°	999.4	987.9	975.3	945.1	904.2	847.2	767.2	691.8	656.7	662.6	692.8
135°	1066.0	1055.3	1039.3	1009.8	971.1	914.9	834.6	753.0	704.9	699.5	716.9
137.5°	1124.6	1113.4	1095.2	1069.8	1030.7	980.7	903.6	817.5	756.8	738.9	745.5
140°	1161.0	1147.6	1131.6	1106.1	1071.4	1019.2	944.3	861.4	793.2	767.8	763.7
142.5°	1190.9	1180.8	1163.7	1140.4	1109.9	1057.7	985.0	903.1	830.6	797.7	788.3
145°	1235.9	1227.9	1209.1	1187.7	1162.3	1110.2	1043.3	961.7	889.5	846.7	826.6
147.5°	1273.9	1267.5	1252.7	1227.6	1206.2	1156.2	1095.2	1023.0	948.9	895.9	869.9
150°	1297.4	1292.1	1277.4	1253.3	1231.9	1185.1	1126.2	1059.3	988.4	932.3	898.8
152.5°	1319.9	1314.5	1297.7	1273.6	1255.4	1211.8	1158.3	1094.6	1022.7	966.5	932.0
155°	1349.6	1342.9	1326.8	1304.1	1288.1	1247.9	1198.4	1142.3	1080.7	1021.9	983.1
157.5°	1373.1	1364.8	1349.9	1330.3	1313.2	1276.3	1233.2	1184.8	1131.0	1074.9	1035.3
160°	1387.0	1377.7	1361.6	1344.2	1328.2	1293.4	1254.6	1210.5	1161.0	1110.2	1067.4
162.5°	1396.7	1388.4	1369.1	1353.9	1340.0	1308.4	1271.7	1231.9	1187.7	1143.3	1103.7
165°	1407.1	1397.7	1377.7	1365.6	1353.6	1326.8	1294.7	1262.6	1225.2	1189.1	1157.0
167.5°	1407.9	1400.1	1380.1	1368.3	1359.5	1336.5	1310.5	1285.9	1256.8	1228.4	1201.7
170°	1405.8	1399.1	1379.0	1368.3	1361.6	1342.9	1320.2	1298.8	1276.0	1251.9	1230.5
172.5°	1398.3	1391.6	1372.6	1364.0	1360.6	1344.0	1325.5	1309.5	1289.9	1272.3	1255.2
175°	1379.0	1373.7	1357.6	1352.3	1353.6	1342.9	1329.5	1320.2	1308.1	1297.4	1288.1
177.5°	1350.9	1347.7	1335.9	1335.9	1340.2	1333.8	1329.5	1325.2	1319.9	1316.7	1313.5
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0	981.0
2.5°	980.3	978.0	978.3	978.9	979.9	981.0	979.9	978.9	978.3	978.0	980.3
5°	984.5	982.5	983.3	985.1	989.6	994.0	989.6	985.1	983.3	982.5	984.5
7.5°	995.7	995.7	998.3	1001.7	1007.5	1013.4	1007.5	1001.7	998.3	995.7	995.7
10°	1000.9	1000.2	1000.7	1002.6	1008.8	1015.0	1008.8	1002.6	1000.7	1000.2	1000.9
12.5°	991.6	987.7	987.1	987.5	990.8	994.2	990.8	987.5	987.1	987.7	991.6
15°	968.8	961.7	963.0	964.6	966.8	969.0	966.8	964.6	963.0	961.7	968.8
17.5°	946.8	941.8	946.6	951.3	955.7	960.0	955.7	951.3	946.6	941.8	946.8
20°	935.0	932.1	938.3	944.9	952.5	960.0	952.5	944.9	938.3	932.1	935.0
22.5°	924.3	923.8	932.5	941.6	952.0	962.4	952.0	941.6	932.5	923.8	924.3
25°	907.5	912.3	927.0	940.9	952.5	964.0	952.5	940.9	927.0	912.3	907.5
27.5°	888.6	901.1	920.9	937.8	945.9	954.0	945.9	937.8	920.9	901.1	888.6
30°	877.3	892.7	910.0	923.8	926.9	930.0	926.9	923.8	910.0	892.7	877.3
32.5°	864.2	879.0	888.1	894.0	890.0	886.0	890.0	894.0	888.1	879.0	864.2
35°	840.7	850.5	843.3	835.9	827.5	819.0	827.5	835.9	843.3	850.5	840.7
37.5°	798.0	797.8	777.0	759.0	749.3	739.6	749.3	759.0	777.0	797.8	798.0
40°	763.2	753.5	722.3	696.2	685.1	674.0	685.1	696.2	722.3	753.5	763.2
42.5°	718.2	697.2	657.5	624.4	610.8	597.2	610.8	624.4	657.5	697.2	718.2
45°	635.7	601.4	558.3	522.2	507.1	492.0	507.1	522.2	558.3	601.4	635.7
47.5°	543.6	503.8	465.3	432.9	418.7	404.6	418.7	432.9	465.3	503.8	543.6
50°	485.0	445.0	409.0	378.1	362.6	347.0	362.6	378.1	409.0	445.0	485.0
52.5°	432.7	393.8	357.8	327.3	313.1	299.0	313.1	327.3	357.8	393.8	432.7
55°	358.4	322.9	288.7	260.6	250.8	241.0	250.8	260.6	288.7	322.9	358.4
57.5°	294.9	263.3	234.2	210.6	203.4	196.2	203.4	210.6	234.2	263.3	294.9
60°	254.1	225.7	203.0	184.6	178.8	173.0	178.8	184.6	203.0	225.7	254.1
62.5°	220.6	195.2	177.1	162.5	158.2	153.8	158.2	162.5	177.1	195.2	220.6
65°	180.0	159.1	145.3	134.2	131.1	128.0	131.1	134.2	145.3	159.1	180.0
67.5°	148.0	131.2	120.3	111.5	108.5	105.6	108.5	111.5	120.3	131.2	148.0
70°	129.0	114.1	104.3	96.4	94.2	92.0	94.2	96.4	104.3	114.1	129.0
72.5°	111.0	98.2	90.2	83.8	82.3	80.8	82.3	83.8	90.2	98.2	111.0
75°	85.1	75.3	70.0	65.8	64.9	64.0	64.9	65.8	70.0	75.3	85.1
77.5°	60.7	53.9	52.1	50.8	50.8	50.8	50.8	50.8	52.1	53.9	60.7
80°	46.4	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	46.4
82.5°	34.9	32.4	32.4	32.3	32.0	31.6	32.0	32.3	32.4	32.4	34.9
85°	19.0	17.7	15.0	12.7	11.3	10.0	11.3	12.7	15.0	17.7	19.0
87.5°	9.4	10.4	12.3	13.4	14.4	13.9	14.4	13.4	12.3	10.4	9.4
90°	30.8	40.1	49.5	54.8	60.2	57.5	60.2	54.8	49.5	40.1	30.8
92.5°	61.8	77.6	89.1	98.7	103.0	102.5	103.0	98.7	89.1	77.6	61.8
95°	124.4	143.1	161.8	175.2	183.2	180.6	183.2	175.2	161.8	143.1	124.4
97.5°	191.8	216.9	237.8	250.4	258.4	263.8	258.4	250.4	237.8	216.9	191.8
100°	236.7	260.8	284.9	299.6	313.0	318.3	313.0	299.6	284.9	260.8	236.7
102.5°	273.1	304.7	330.9	346.7	357.9	363.3	357.9	346.7	330.9	304.7	273.1
105°	333.0	366.5	394.6	414.6	426.7	430.7	426.7	414.6	394.6	366.5	333.0
107.5°	393.0	427.5	453.4	475.6	490.3	498.9	490.3	475.6	453.4	427.5	393.0
110°	440.1	468.1	496.2	516.3	531.0	536.4	531.0	516.3	496.2	468.1	440.1



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	479.6	510.9	539.0	559.1	575.9	583.4	575.9	559.1	539.0	510.9	479.6
115°	535.0	576.5	601.9	620.6	632.7	639.3	632.7	620.6	601.9	576.5	535.0
117.5°	581.0	624.4	652.2	666.6	672.3	677.1	672.3	666.6	652.2	624.4	581.0
120°	609.9	650.0	682.1	700.9	707.6	710.2	707.6	700.9	682.1	650.0	609.9
122.5°	636.7	674.7	705.7	728.7	739.7	742.3	739.7	728.7	705.7	674.7	636.7
125°	674.1	710.2	742.3	765.1	777.1	783.8	777.1	765.1	742.3	710.2	674.1
127.5°	706.8	745.8	775.2	795.8	807.6	813.0	807.6	795.8	775.2	745.8	706.8
130°	724.9	765.1	794.5	817.2	827.9	833.3	827.9	817.2	794.5	765.1	724.9
132.5°	738.9	781.1	811.6	832.2	844.0	849.3	844.0	832.2	811.6	781.1	738.9
135°	755.7	799.9	832.0	852.0	862.7	868.1	862.7	852.0	832.0	799.9	755.7
137.5°	770.4	810.6	844.0	865.1	874.8	878.2	874.8	865.1	844.0	810.6	770.4
140°	781.1	815.9	849.3	869.4	880.1	881.4	880.1	869.4	849.3	815.9	781.1
142.5°	795.0	822.3	851.5	871.5	882.2	884.7	882.2	871.5	851.5	822.3	795.0
145°	819.9	836.0	856.0	874.8	884.1	886.8	884.1	874.8	856.0	836.0	819.9
147.5°	851.2	856.3	866.7	879.0	888.1	890.0	888.1	879.0	866.7	856.3	851.2
150°	874.8	873.4	877.4	885.5	893.5	892.1	893.5	885.5	877.4	873.4	874.8
152.5°	901.5	893.7	893.5	897.2	901.0	900.7	901.0	897.2	893.5	893.7	901.5
155°	947.0	932.3	924.2	921.6	921.6	920.2	921.6	921.6	924.2	932.3	947.0
157.5°	997.0	976.4	964.4	957.9	956.1	953.1	956.1	957.9	964.4	976.4	997.0
160°	1031.2	1008.5	996.5	985.8	981.8	977.7	981.8	985.8	996.5	1008.5	1031.2
162.5°	1063.3	1041.7	1028.6	1018.9	1014.9	1008.8	1014.9	1018.9	1028.6	1041.7	1063.3
165°	1115.5	1092.8	1078.1	1070.0	1064.7	1059.3	1064.7	1070.0	1078.1	1092.8	1115.5
167.5°	1167.7	1142.8	1133.2	1124.1	1119.0	1109.4	1119.0	1124.1	1133.2	1142.8	1167.7
170°	1199.8	1177.0	1171.7	1163.7	1154.3	1143.6	1154.3	1163.7	1171.7	1177.0	1199.8
172.5°	1227.6	1212.4	1207.0	1199.0	1196.0	1187.5	1196.0	1199.0	1207.0	1212.4	1227.6
175°	1268.0	1256.0	1256.0	1254.6	1250.6	1242.6	1250.6	1254.6	1256.0	1256.0	1268.0
177.5°	1301.7	1295.3	1299.6	1299.6	1298.5	1291.0	1298.5	1299.6	1299.6	1295.3	1301.7
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	981.0	981.0	981.0	981.0
2.5°	985.3	987.7	982.3	977.0
5°	989.3	991.1	983.6	976.0
7.5°	998.1	997.3	986.6	975.8
10°	1002.7	1000.8	987.9	975.0
12.5°	998.7	1000.3	985.2	970.2
15°	984.3	991.6	973.8	956.0
17.5°	961.7	968.2	949.6	931.0
20°	947.0	951.5	933.2	915.0
22.5°	934.2	937.1	918.8	900.6
25°	912.3	912.0	896.0	880.0
27.5°	883.5	877.3	867.8	858.4
30°	864.0	852.5	846.2	840.0
32.5°	843.7	827.5	823.7	820.0
35°	814.0	793.2	790.1	787.0
37.5°	777.5	760.6	754.2	747.8
40°	751.7	740.3	729.7	719.0
42.5°	720.5	717.9	700.9	683.8
45°	661.0	674.2	651.1	628.0
47.5°	584.7	609.7	585.9	562.2
50°	529.0	557.2	538.1	519.0
52.5°	474.6	502.6	488.8	475.0
55°	395.3	421.2	414.1	407.0
57.5°	329.1	353.7	349.1	344.6
60°	288.3	313.2	310.1	307.0
62.5°	253.4	277.4	275.0	272.6
65°	208.0	228.4	226.2	224.0
67.5°	170.9	187.7	186.6	185.4
70°	149.0	163.9	163.4	163.0
72.5°	128.5	141.8	142.4	143.0
75°	99.3	110.3	111.7	113.0
77.5°	72.4	81.6	83.0	84.4
80°	55.3	62.4	64.2	66.0
82.5°	39.9	44.2	46.7	49.2
85°	19.0	19.6	21.8	24.0
87.5°	9.9	9.3	8.3	7.2
90°	24.1	14.7	9.4	4.0
92.5°	51.9	36.1	25.4	14.7
95°	104.3	82.9	58.9	41.5
97.5°	166.1	131.6	107.8	79.2
100°	199.3	165.9	143.1	112.4
102.5°	235.7	207.6	176.3	145.5
105°	300.9	266.2	230.1	195.3
107.5°	361.4	323.2	279.8	248.5
110°	399.9	358.5	313.0	284.9



TEST NUMBER: P1428255

CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	437.4	394.8	348.3	320.2
115°	488.2	441.4	398.6	374.5
117.5°	537.2	489.0	443.8	424.8
120°	567.1	519.0	474.8	460.1
122.5°	591.7	544.6	503.7	497.6
125°	628.6	580.5	545.7	553.7
127.5°	658.6	614.5	592.5	610.5
130°	676.8	638.0	624.6	650.0
132.5°	692.8	662.6	656.7	691.8
135°	716.9	699.5	704.9	753.0
137.5°	745.5	738.9	756.8	817.5
140°	763.7	767.8	793.2	861.4
142.5°	788.3	797.7	830.6	903.1
145°	826.6	846.7	889.5	961.7
147.5°	869.9	895.9	948.9	1023.0
150°	898.8	932.3	988.4	1059.3
152.5°	932.0	966.5	1022.7	1094.6
155°	983.1	1021.9	1080.7	1142.3
157.5°	1035.3	1074.9	1131.0	1184.8
160°	1067.4	1110.2	1161.0	1210.5
162.5°	1103.7	1143.3	1187.7	1231.9
165°	1157.0	1189.1	1225.2	1262.6
167.5°	1201.7	1228.4	1256.8	1285.9
170°	1230.5	1251.9	1276.0	1298.8
172.5°	1255.2	1272.3	1289.9	1309.5
175°	1288.1	1297.4	1308.1	1320.2
177.5°	1313.5	1316.7	1319.9	1325.2
180°	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428255
 CATALOG NUMBER: SQ2W-PR1-K-100U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.02	15.76	16.09	16.82	18.25	11.39	12.13	12.45	13.19	14.62
	3H	16.22	16.88	17.29	17.95	19.40	12.54	13.20	13.62	14.27	15.72
	4H	16.70	17.32	17.78	18.39	19.85	13.00	13.62	14.08	14.69	16.16
	6H	16.99	17.56	18.08	18.64	20.11	13.34	13.91	14.43	14.98	16.46
	8H	17.09	17.63	18.19	18.72	20.19	13.47	14.01	14.57	15.10	16.57
	12H	17.13	17.64	18.23	18.73	20.22	13.50	14.01	14.60	15.10	16.59
4H	2H	15.11	15.73	16.20	16.80	18.26	12.09	12.71	13.18	13.78	15.24
	3H	16.56	17.08	17.66	18.17	19.65	13.43	13.95	14.53	15.04	16.52
	4H	17.18	17.66	18.28	18.74	20.24	13.97	14.45	15.07	15.53	17.03
	6H	17.61	18.01	18.72	19.12	20.61	14.40	14.80	15.51	15.91	17.40
	8H	17.77	18.14	18.87	19.25	20.75	14.58	14.96	15.69	16.06	17.56
	12H	17.83	18.17	18.95	19.28	20.79	14.62	14.96	15.75	16.08	17.59
8H	4H	17.20	17.58	18.31	18.68	20.19	14.29	14.67	15.40	15.77	17.27
	6H	17.73	18.04	18.86	19.19	20.69	14.83	15.14	15.96	16.28	17.78
	8H	17.96	18.24	19.10	19.36	20.88	15.09	15.36	16.22	16.49	18.01
	12H	18.08	18.32	19.22	19.44	21.00	15.18	15.42	16.32	16.54	18.10
12H	4H	17.15	17.50	18.28	18.61	20.12	14.30	14.65	15.43	15.76	17.27
	6H	17.72	17.99	18.85	19.12	20.64	14.90	15.17	16.03	16.30	17.82
	8H	17.96	18.20	19.10	19.33	20.88	15.18	15.42	16.32	16.55	18.10