

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428324

Luminaire Tested: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428324
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2636.7 lumens
Efficiency: N/A
Efficacy: 148.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	46	41	39
8	64	52	44	38	63	51	43	38	50	43	38	48	42	37	47	42	37	35
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32
10	57	44	37	32	55	44	36	31	43	36	31	42	36	31	41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19186	19186	19186	19186
5°	19056	19387	19056	19387
10°	19092	19556	19092	19556
15°	19087	19672	19087	19672
20°	19094	19288	19094	19288
25°	18990	17923	18990	17923
30°	18861	16203	18861	16203
35°	18715	14633	18715	14633
40°	18343	12928	18343	12928
45°	17623	11291	17623	11291
50°	16402	9665	16402	9665
55°	15003	7837	15003	7837
60°	13449	6762	13449	6762
65°	11759	6009	11759	6009
70°	9616	5448	9616	5448
75°	7486	5009	7486	5009
80°	5579	4416	5579	4416
85°	3779	2519	3779	2519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17623 cd/sqm



TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	4.3
10°-20°	327.8	12.4
20°-30°	482.5	18.3
30°-40°	527.5	20.0
40°-50°	473.2	17.9
50°-60°	353.0	13.4
60°-70°	223.1	8.5
70°-80°	110.5	4.2
80°-90°	25.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	923.5	35.0
0°-40°	1451.0	55.0
0°-60°	2277.2	86.4
0°-90°	2636.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2636.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1188	1188	1188	1188	1188	
5°	1176	1196	1176	1196	1176	112
15°	1142	1177	1142	1177	1142	322
25°	1066	1006	1066	1006	1066	491
35°	950	742	950	742	950	592
45°	772	494	772	494	772	592
55°	533	278	533	278	533	476
65°	308	157	308	157	308	305
75°	120	80	120	80	120	132
85°	20	14	20	14	20	27
90°	0	0	0	0	0	



TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-OU-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1180.1	1187.0	1193.8	1192.2	1187.8	1185.7	1186.1	1186.8	1188.0	1189.2	1188.0
5°	1175.8	1184.4	1192.9	1191.7	1187.1	1185.1	1185.6	1187.1	1191.7	1196.2	1191.7
7.5°	1169.9	1178.6	1187.2	1186.8	1183.4	1182.6	1184.3	1186.7	1191.1	1195.5	1191.1
10°	1164.5	1173.5	1182.6	1182.6	1179.6	1179.3	1181.8	1184.7	1188.8	1192.8	1188.8
12.5°	1157.3	1166.7	1176.2	1176.9	1174.7	1175.0	1177.9	1181.1	1185.1	1189.2	1185.1
15°	1141.9	1151.9	1162.0	1164.1	1163.6	1165.1	1168.6	1171.9	1174.4	1176.9	1174.4
17.5°	1124.0	1134.0	1144.1	1146.1	1145.4	1145.5	1146.4	1147.4	1148.6	1149.8	1148.6
20°	1111.3	1121.4	1131.4	1132.8	1131.3	1128.8	1125.3	1122.6	1122.6	1122.6	1122.6
22.5°	1093.2	1104.1	1114.9	1115.0	1111.5	1104.9	1095.4	1087.4	1084.2	1081.0	1084.2
25°	1066.0	1076.6	1087.2	1082.3	1072.2	1057.4	1037.7	1021.1	1013.6	1006.1	1013.6
27.5°	1034.4	1042.9	1051.5	1038.7	1018.7	994.8	967.0	943.5	933.0	922.5	933.0
30°	1011.7	1018.3	1024.8	1004.6	975.4	945.5	914.8	889.2	879.2	869.1	879.2
32.5°	988.2	990.7	993.2	966.5	930.1	896.0	864.1	837.4	826.6	815.7	826.6
35°	949.5	945.0	940.4	905.0	859.2	820.2	788.0	761.5	751.9	742.4	751.9
37.5°	903.8	890.3	876.8	836.8	788.0	746.8	713.1	685.2	674.6	664.1	674.6
40°	870.3	851.1	832.0	789.2	738.4	696.1	662.4	634.5	623.9	613.4	623.9
42.5°	833.1	809.2	785.3	741.2	690.4	648.1	614.4	586.4	575.4	564.5	575.4
45°	771.8	743.6	715.5	669.6	617.8	575.5	542.8	515.7	505.1	494.5	505.1
47.5°	702.8	674.8	646.8	601.1	549.4	507.7	476.0	450.0	440.9	431.8	440.9
50°	653.0	625.8	598.7	554.9	505.6	465.1	433.4	406.9	395.8	384.8	395.8
52.5°	602.3	577.9	553.6	511.4	463.4	423.1	390.6	362.4	347.3	332.3	347.3
55°	533.0	509.9	486.7	447.0	401.7	361.0	324.8	295.5	286.9	278.4	286.9
57.5°	461.7	441.7	421.7	386.0	345.0	308.1	275.2	248.8	241.8	234.7	241.8
60°	416.5	398.9	381.2	347.0	307.3	273.6	246.0	223.4	216.4	209.4	216.4
62.5°	373.0	357.4	341.8	309.0	270.5	240.2	218.2	200.2	194.4	188.5	194.4
65°	307.8	296.2	284.7	257.6	225.5	200.3	182.2	167.4	162.3	157.3	162.3
67.5°	244.4	238.0	231.6	211.3	186.5	166.1	150.2	137.5	134.1	130.8	134.1
70°	203.7	201.7	199.7	183.0	161.3	144.0	130.9	120.5	117.9	115.4	117.9
72.5°	168.4	169.2	170.0	156.1	137.3	122.7	112.5	104.4	102.7	100.9	102.7
75°	120.0	124.0	128.0	118.8	105.2	94.9	87.9	82.4	81.4	80.3	81.4
77.5°	81.7	87.7	93.8	87.8	77.9	70.3	65.0	60.9	60.1	59.3	60.1
80°	60.0	66.0	72.1	67.9	60.4	54.6	50.5	47.5	47.5	47.5	47.5
82.5°	41.9	46.7	51.5	48.6	43.1	39.3	37.3	35.8	35.8	35.8	35.8
85°	20.4	22.9	25.4	24.5	22.5	20.0	17.0	14.6	14.1	13.6	14.1
87.5°	5.4	6.6	7.8	6.6	4.6	3.4	3.0	2.7	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-OU-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1186.8	1186.1	1185.7	1187.8	1192.2	1193.8	1187.0	1180.1	1187.0	1193.8	1192.2
5°	1187.1	1185.6	1185.1	1187.1	1191.7	1192.9	1184.4	1175.8	1184.4	1192.9	1191.7
7.5°	1186.7	1184.3	1182.6	1183.4	1186.8	1187.2	1178.6	1169.9	1178.6	1187.2	1186.8
10°	1184.7	1181.8	1179.3	1179.6	1182.6	1182.6	1173.5	1164.5	1173.5	1182.6	1182.6
12.5°	1181.1	1177.9	1175.0	1174.7	1176.9	1176.2	1166.7	1157.3	1166.7	1176.2	1176.9
15°	1171.9	1168.6	1165.1	1163.6	1164.1	1162.0	1151.9	1141.9	1151.9	1162.0	1164.1
17.5°	1147.4	1146.4	1145.5	1145.4	1146.1	1144.1	1134.0	1124.0	1134.0	1144.1	1146.1
20°	1122.6	1125.3	1128.8	1131.3	1132.8	1131.4	1121.4	1111.3	1121.4	1131.4	1132.8
22.5°	1087.4	1095.4	1104.9	1111.5	1115.0	1114.9	1104.1	1093.2	1104.1	1114.9	1115.0
25°	1021.1	1037.7	1057.4	1072.2	1082.3	1087.2	1076.6	1066.0	1076.6	1087.2	1082.3
27.5°	943.5	967.0	994.8	1018.7	1038.7	1051.5	1042.9	1034.4	1042.9	1051.5	1038.7
30°	889.2	914.8	945.5	975.4	1004.6	1024.8	1018.3	1011.7	1018.3	1024.8	1004.6
32.5°	837.4	864.1	896.0	930.1	966.5	993.2	990.7	988.2	990.7	993.2	966.5
35°	761.5	788.0	820.2	859.2	905.0	940.4	945.0	949.5	945.0	940.4	905.0
37.5°	685.2	713.1	746.8	788.0	836.8	876.8	890.3	903.8	890.3	876.8	836.8
40°	634.5	662.4	696.1	738.4	789.2	832.0	851.1	870.3	851.1	832.0	789.2
42.5°	586.4	614.4	648.1	690.4	741.2	785.3	809.2	833.1	809.2	785.3	741.2
45°	515.7	542.8	575.5	617.8	669.6	715.5	743.6	771.8	743.6	715.5	669.6
47.5°	450.0	476.0	507.7	549.4	601.1	646.8	674.8	702.8	674.8	646.8	601.1
50°	406.9	433.4	465.1	505.6	554.9	598.7	625.8	653.0	625.8	598.7	554.9
52.5°	362.4	390.6	423.1	463.4	511.4	553.6	577.9	602.3	577.9	553.6	511.4
55°	295.5	324.8	361.0	401.7	447.0	486.7	509.9	533.0	509.9	486.7	447.0
57.5°	248.8	275.2	308.1	345.0	386.0	421.7	441.7	461.7	441.7	421.7	386.0
60°	223.4	246.0	273.6	307.3	347.0	381.2	398.9	416.5	398.9	381.2	347.0
62.5°	200.2	218.2	240.2	270.5	309.0	341.8	357.4	373.0	357.4	341.8	309.0
65°	167.4	182.2	200.3	225.5	257.6	284.7	296.2	307.8	296.2	284.7	257.6
67.5°	137.5	150.2	166.1	186.5	211.3	231.6	238.0	244.4	238.0	231.6	211.3
70°	120.5	130.9	144.0	161.3	183.0	199.7	201.7	203.7	201.7	199.7	183.0
72.5°	104.4	112.5	122.7	137.3	156.1	170.0	169.2	168.4	169.2	170.0	156.1
75°	82.4	87.9	94.9	105.2	118.8	128.0	124.0	120.0	124.0	128.0	118.8
77.5°	60.9	65.0	70.3	77.9	87.8	93.8	87.7	81.7	87.7	93.8	87.8
80°	47.5	50.5	54.6	60.4	67.9	72.1	66.0	60.0	66.0	72.1	67.9
82.5°	35.8	37.3	39.3	43.1	48.6	51.5	46.7	41.9	46.7	51.5	48.6
85°	14.6	17.0	20.0	22.5	24.5	25.4	22.9	20.4	22.9	25.4	24.5
87.5°	2.7	3.0	3.4	4.6	6.6	7.8	6.6	5.4	6.6	7.8	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-OU-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1187.8	1185.7	1186.1	1186.8	1188.0	1189.2	1188.0	1186.8	1186.1	1185.7	1187.8
5°	1187.1	1185.1	1185.6	1187.1	1191.7	1196.2	1191.7	1187.1	1185.6	1185.1	1187.1
7.5°	1183.4	1182.6	1184.3	1186.7	1191.1	1195.5	1191.1	1186.7	1184.3	1182.6	1183.4
10°	1179.6	1179.3	1181.8	1184.7	1188.8	1192.8	1188.8	1184.7	1181.8	1179.3	1179.6
12.5°	1174.7	1175.0	1177.9	1181.1	1185.1	1189.2	1185.1	1181.1	1177.9	1175.0	1174.7
15°	1163.6	1165.1	1168.6	1171.9	1174.4	1176.9	1174.4	1171.9	1168.6	1165.1	1163.6
17.5°	1145.4	1145.5	1146.4	1147.4	1148.6	1149.8	1148.6	1147.4	1146.4	1145.5	1145.4
20°	1131.3	1128.8	1125.3	1122.6	1122.6	1122.6	1122.6	1122.6	1125.3	1128.8	1131.3
22.5°	1111.5	1104.9	1095.4	1087.4	1084.2	1081.0	1084.2	1087.4	1095.4	1104.9	1111.5
25°	1072.2	1057.4	1037.7	1021.1	1013.6	1006.1	1013.6	1021.1	1037.7	1057.4	1072.2
27.5°	1018.7	994.8	967.0	943.5	933.0	922.5	933.0	943.5	967.0	994.8	1018.7
30°	975.4	945.5	914.8	889.2	879.2	869.1	879.2	889.2	914.8	945.5	975.4
32.5°	930.1	896.0	864.1	837.4	826.6	815.7	826.6	837.4	864.1	896.0	930.1
35°	859.2	820.2	788.0	761.5	751.9	742.4	751.9	761.5	788.0	820.2	859.2
37.5°	788.0	746.8	713.1	685.2	674.6	664.1	674.6	685.2	713.1	746.8	788.0
40°	738.4	696.1	662.4	634.5	623.9	613.4	623.9	634.5	662.4	696.1	738.4
42.5°	690.4	648.1	614.4	586.4	575.4	564.5	575.4	586.4	614.4	648.1	690.4
45°	617.8	575.5	542.8	515.7	505.1	494.5	505.1	515.7	542.8	575.5	617.8
47.5°	549.4	507.7	476.0	450.0	440.9	431.8	440.9	450.0	476.0	507.7	549.4
50°	505.6	465.1	433.4	406.9	395.8	384.8	395.8	406.9	433.4	465.1	505.6
52.5°	463.4	423.1	390.6	362.4	347.3	332.3	347.3	362.4	390.6	423.1	463.4
55°	401.7	361.0	324.8	295.5	286.9	278.4	286.9	295.5	324.8	361.0	401.7
57.5°	345.0	308.1	275.2	248.8	241.8	234.7	241.8	248.8	275.2	308.1	345.0
60°	307.3	273.6	246.0	223.4	216.4	209.4	216.4	223.4	246.0	273.6	307.3
62.5°	270.5	240.2	218.2	200.2	194.4	188.5	194.4	200.2	218.2	240.2	270.5
65°	225.5	200.3	182.2	167.4	162.3	157.3	162.3	167.4	182.2	200.3	225.5
67.5°	186.5	166.1	150.2	137.5	134.1	130.8	134.1	137.5	150.2	166.1	186.5
70°	161.3	144.0	130.9	120.5	117.9	115.4	117.9	120.5	130.9	144.0	161.3
72.5°	137.3	122.7	112.5	104.4	102.7	100.9	102.7	104.4	112.5	122.7	137.3
75°	105.2	94.9	87.9	82.4	81.4	80.3	81.4	82.4	87.9	94.9	105.2
77.5°	77.9	70.3	65.0	60.9	60.1	59.3	60.1	60.9	65.0	70.3	77.9
80°	60.4	54.6	50.5	47.5	47.5	47.5	47.5	47.5	50.5	54.6	60.4
82.5°	43.1	39.3	37.3	35.8	35.8	35.8	35.8	35.8	37.3	39.3	43.1
85°	22.5	20.0	17.0	14.6	14.1	13.6	14.1	14.6	17.0	20.0	22.5
87.5°	4.6	3.4	3.0	2.7	2.7	2.7	2.7	2.7	3.0	3.4	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428324

CATALOG NUMBER: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1188.3	1188.3	1188.3	1188.3
2.5°	1192.2	1193.8	1187.0	1180.1
5°	1191.7	1192.9	1184.4	1175.8
7.5°	1186.8	1187.2	1178.6	1169.9
10°	1182.6	1182.6	1173.5	1164.5
12.5°	1176.9	1176.2	1166.7	1157.3
15°	1164.1	1162.0	1151.9	1141.9
17.5°	1146.1	1144.1	1134.0	1124.0
20°	1132.8	1131.4	1121.4	1111.3
22.5°	1115.0	1114.9	1104.1	1093.2
25°	1082.3	1087.2	1076.6	1066.0
27.5°	1038.7	1051.5	1042.9	1034.4
30°	1004.6	1024.8	1018.3	1011.7
32.5°	966.5	993.2	990.7	988.2
35°	905.0	940.4	945.0	949.5
37.5°	836.8	876.8	890.3	903.8
40°	789.2	832.0	851.1	870.3
42.5°	741.2	785.3	809.2	833.1
45°	669.6	715.5	743.6	771.8
47.5°	601.1	646.8	674.8	702.8
50°	554.9	598.7	625.8	653.0
52.5°	511.4	553.6	577.9	602.3
55°	447.0	486.7	509.9	533.0
57.5°	386.0	421.7	441.7	461.7
60°	347.0	381.2	398.9	416.5
62.5°	309.0	341.8	357.4	373.0
65°	257.6	284.7	296.2	307.8
67.5°	211.3	231.6	238.0	244.4
70°	183.0	199.7	201.7	203.7
72.5°	156.1	170.0	169.2	168.4
75°	118.8	128.0	124.0	120.0
77.5°	87.8	93.8	87.7	81.7
80°	67.9	72.1	66.0	60.0
82.5°	48.6	51.5	46.7	41.9
85°	24.5	25.4	22.9	20.4
87.5°	6.6	7.8	6.6	5.4
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428324
 CATALOG NUMBER: SQ2W-PW1-0U-050D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.10	22.60	21.46	22.92	23.23	17.35	18.85	17.71	19.16	19.48
	3H	22.45	23.79	22.82	24.12	24.48	18.66	20.01	19.04	20.34	20.70
	4H	22.88	24.14	23.28	24.49	24.87	19.20	20.46	19.60	20.81	21.19
	6H	23.09	24.26	23.51	24.62	25.02	19.53	20.70	19.95	21.07	21.46
	8H	23.15	24.26	23.58	24.65	25.05	19.67	20.77	20.09	21.16	21.57
	12H	23.17	24.23	23.60	24.62	25.05	19.72	20.78	20.15	21.16	21.59
4H	2H	21.30	22.57	21.70	22.91	23.29	18.23	19.49	18.63	19.84	20.22
	3H	22.90	23.94	23.31	24.34	24.74	19.73	20.78	20.14	21.18	21.58
	4H	23.47	24.41	23.90	24.82	25.26	20.33	21.27	20.77	21.69	22.13
	6H	23.81	24.63	24.27	25.07	25.53	20.75	21.57	21.21	22.01	22.47
	8H	23.92	24.68	24.38	25.12	25.59	20.91	21.67	21.38	22.12	22.59
	12H	23.97	24.64	24.45	25.12	25.60	20.98	21.66	21.47	22.14	22.61
8H	4H	23.55	24.31	24.02	24.76	25.23	20.72	21.48	21.19	21.93	22.40
	6H	24.00	24.62	24.49	25.12	25.59	21.24	21.86	21.73	22.36	22.83
	8H	24.17	24.73	24.68	25.24	25.73	21.46	22.02	21.97	22.53	23.02
	12H	24.27	24.77	24.78	25.26	25.83	21.57	22.07	22.08	22.56	23.12
12H	4H	23.54	24.22	24.02	24.70	25.17	20.77	21.45	21.25	21.93	22.40
	6H	23.99	24.55	24.50	25.06	25.55	21.31	21.88	21.83	22.39	22.88
	8H	24.21	24.71	24.72	25.20	25.76	21.58	22.08	22.09	22.58	23.14